



	Best	Best	Best	Better
	SoftView	SlenderForm Canopy	SlenderForm Canopy Recessed	G3
Prefix	SVPG	SFC	SFRC	G3
Lumen Output Range	2,030-17,900	4,630-14,700	4,630-14,700	2,750-13,200
Efficacy	83-148	107-125	107-125	104-148
Distribution	Type 1R, 3, 5, Concentrated Downlight	Type 3, 5 Rectangular, 5 Wide, Concentrated Downlight	Type 3, 5 Rectangular, 5 Wide, Concentrated Downlight	Type 5 Square, Concentrated Downlight, Type 1R, Type 3
Color Temperature	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000
Uplight	✓	-	-	-
Motion Response	✓	✓	-	✓
Wireless Controls	✓	-	-	✓
Photocell	-	Button	-	Button
Additional Options	Shielding, various Bird Guards, Wire Guard	Diffuse lens, Bird Guard	Diffuse lens, Bird Guard	Bird Guard, Balanced offset j-box for pendant
Mounting	Surface Mount, Pendant Mount, Trunnion Mount, Wall Mount	Surface Mount	Recessed	Surface Mount
Vibration	Normal or Bridge/Overpass	-	-	Bridge/Overpass option
Finish	Bronze, White, Medium Grey	Medium Grey	Medium Grey	Bronze, White, Black, Medium Grey
IP Rating	IP66			
IK Rating	IK10	-	-	-
Surge Protection	10kV/10kA	20kV/10kA option	10kV/10kA	10kV/20kA
DLC Listing	Standard and Premium	Standard	Standard	Standard and Premium
Certifications	cULus			
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h
Luminaire Useful Life	100,000+ hours accounting for LED life, driver life, etc. - see specification sheet for details			
Limited Warranty	5 years			
Link				