


Hadco features a wide variety of decorative poles, suitable for any outdoor project, all designed, manufactured, and tested for superior quality, to withstand the test of time.



	Good	Good	Good	Better	Better	Better	Better	Better	Best	Best	Better	Better	Better	Best	Better	Better	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Best	Good	Better	Better	Good	Good	Best	Best										
Series	P100	P100	P100	P1100	P1500	P1500	P1500	P1500	P1500	P1500	P1600	P1600	P1700	P1700	P1700	P2000	P2000	P2000	P2000	P2000	P2100	P2100	P2500	P2500	P2500	P2500	P2500	P3100	P3100	P4000	P4000	P4000	P4100	P4100	P4100	P4100	P4100	P4400	P4400	P4400	P5000	P5000	P5000	P9000	P9000	Anchor Base Post 306	Anchor Base Post 754						
Prefix	P120	P150	P195	P150	P1511	P1516	P1521	P1526	P1561	P1566	P1600	P1610	P1711	P1761	P1791	P2025	P2060	P2061	P2063	P2065	P2071	P2165	P2170	P2520	P2525	P2540	P2550	P2555	P2560	P2565	P3120	P4030	P4031	P4120	P4130	P4131	P4131	P4420	P4420	P4465	P5020	P5065	P5092	P9300	P9300	P9500							
Pole Style	Tapered	Straight	Straight	Tapered	Straight	Straight	Tapered	Tapered	Straight Fluted	Straight Fluted	Tapered	Straight	Tapered	Straight Fluted	Tapered	Tapered	Straight Fluted	Straight Fluted	Straight Flat Fluted	Straight Flat Fluted	Straight Fluted	Straight Flat Fluted	Tapered	Tapered	Tapered	Straight Flat Fluted	Straight Flat Fluted	Straight Flat Fluted	Straight Fluted	Straight	Straight	Tapered	Straight	Straight	Tapered	Straight	Straight	Tapered	Straight Flat Fluted	Tapered	Straight Flat Fluted	Tapered Fluted	Straight Flat Fluted	Straight Flat Fluted	Straight Fluted	Straight Flat Fluted							
Base Style	Simple	Simple	Simple	Candlestick	Fluted Bottleneck & Square Cover	Fluted Bottleneck & Round Cover	Fluted Bottleneck & Square Cover	Fluted Bottleneck & Round Cover	Fluted Bottleneck & Square Cover	Fluted Bottleneck & Round Cover	Pedestal	Pedestal	Octagon	Fluted Bottleneck & Square Cover	Fluted Bottleneck & Square Cover	Fluted	Fluted	Fluted	Fluted	Fluted	Fluted	Fluted	Fluted	Fluted	Fluted	Fluted	Fluted	Fluted	Fluted	Bottleneck	Bottleneck	Bottleneck	Bottleneck	Bottleneck	Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Fluted	Fluted	Fluted	Simple Round	Simple Square	Fluted	Fluted Bottleneck									
Pole Height	8', 10', 12', 14'	8', 10'	12', 14', 15', 16', 18', 20'	8'6", 10'6", 12'6"	8', 10', 12'	8', 10', 12'	8', 10', 12', 14'	8', 10', 12', 14'	8', 10', 12'	8', 10', 12'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	8', 10', 12', 14', 16'	8', 10', 12', 14', 16'									
Pole Diameter	4-3" Tapered	3"	4"	4-3" Tapered	3"	3"	4-3" Tapered	4-3" Tapered	3"	3"	4-3" Tapered	4"	5-3" Tapered	4-3" Tapered	3"	4"	4"	4"	4"	4"	4"	5"	5-3" Tapered	5-3" Tapered	5-3" Tapered	5-3" Tapered	5"	4"	4"	4"	4"	4"	5"	5-3" Tapered	5"	4"	4"	4"	5-3" Tapered	4"	4"	6-4" Tapered	4"	4"									
Pole Tenon	3"	3"	4"	3"	3"	3"	3"	3"	3"	3"	3"	4"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"	3"		
Wall Thickness	0.125"	0.125"	0.188"	0.125"	0.125"	0.125"	0.125", 0.188" (14")	0.125", 0.188" (14")	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.188"-0.313"	0.188"-0.267"	0.125"	0.188"-0.267"	0.125"	0.188"-0.313"	0.188"-0.267"	0.188"-0.267"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"	0.125"
Base Size	11 1/2" dia. x 2 3/8"	9 5/8" dia. x 1 3/8"	11 1/2" dia. x 2 3/8"	11" dia. x 30"	8 1/4" sq. x 27 3/8"	8 1/4" sq. x 27 3/8"	8 1/4" sq. x 27 3/8"	8 1/4" sq. x 27 3/8"	8 1/4" sq. x 27 3/8"	8 1/4" sq. x 27 3/8"	16" dia. x 22"	16" dia. x 22"	10 1/2" sq. x 49"	10 1/2" sq. x 49"	16" dia. x 21"	16" dia. x 21"	16" dia. x 21"	16" dia. x 21"	16" dia. x 21"	20 dia. x 25 3/8"	20 dia. x 25 3/8"	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"	17" dia. x 29"	17" dia. x 29"	15" dia. x 46 1/8"	15" dia. x 46 1/8"	15" dia. x 46 1/8"	19" dia. x 54 1/2"	19" dia. x 54 1/2"	19" dia. x 54 1/2"	15 1/2" dia. x 48"	15 1/2" dia. x 48"	17" dia. x 21"	17" dia. x 21"	17" dia. x 21"	9" dia.	9" sq.	17" dia x 21-5/8"	17" dia x 18-3/4"								
Bot Circle	7 1/2" - 9 1/2"	7"	7 1/2" - 9 1/2"	7"	9-3/8"	9-3/8"	9-3/8"	9-3/8"	9-3/8"	9-3/8"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-16"	8-16"	11-14"	11-14"	11-14"	11-14"	11-14"	11-14"	11-14"	11-14"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	8-12"	7"	7"	7"	7"				
Base Cover	Included 12 1/8" dia. x 3 1/4"	Included 10 1/4" dia. x 2 3/4"	-	-	Included 9" sq. x 3"	Included 12 3/4" dia. x 5 1/2"	Included 9" sq. x 3"	Included 12 3/4" dia. x 5 1/2"	-	-	Included 11 1/2" sq. x 2 1/2"	-	-	-	-	-	-	-	-	-	-	Included 14" sq. x 9 3/8"	Included 19" dia. x 9 1/4"	Included 14" sq. x 9 3/8"	Included 14" sq. x 9 3/8"	Included 19" dia. x 9 1/4"	Included 14" sq. x 9 3/8"	Included 19" dia. x 9 1/4"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
EPA @ 80 MPH	4.11-9.78	2.19-3.19	2.17-6.45	5.55-9.06	6.64-9.99	6.64-9.99	7.57-10.24	7.57-10.24	6.50-9.77	6.50-9.77	5.21-12.53	5.21-12.53	11.65-24.75	3.10-8.54	3.10-8.54	9.90-14.91	4.46-8.23	4.62-11.29	8.84-19.19	11.78-25.34	5.34-12.29	8.78-18.42	9.38-12.81	12.76-27.80	12.76-27.80	5.54-13.78	10.65-23.42	10.65-23.42	5.54-13.78	5.54-13.78	9.71-13.77	18.99-36.78	8.40-18.69	8.40-18.69	8.40-18.69	6.72-15.28	7.53-16.74	7.53-16.74	10.59-23.29	10.59-23.29	6.80-13.77	13.99-28.22	11.61-20.55	7.38-16.65	11.44-24.87	6.86-19.69	12.35-38.53						
EPA @ 100 MPH	2.01-6.10	1.07-1.80	0.93-3.88	2.95-5.42	3.72-5.84	3.72-5.84	4.26-5.78	4.26-5.78	3.65-5.72	3.65-5.72	2.64-7.52	2.64-7.52	6.71-15.39	1.23-4.99	1.23-4.99	5.38-8.83	2.24-4.47	1.93-6.17	4.69-11.29	6.34-15.00	2.42-6.74	4.43-10.56	4.90-7.47	7.46-17.27	7.46-17.27	2.72-8.34	5.99-14.48	5.99-14.48	2.72-8.34	2.72-8.34	5.11-8.09	10.98-22.32	4.83-11.61	4.83-11.61	4.83-11.61	3.51-9.33	4.03-10.26	5.95-14.40	5.95-14.40	3.67-8.12	7.60-16.70	6.41-12.12	4.03-10.15	7.03-15.71	2.42-9.94	5.55-20.07							
EPA @ 110 MPH	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
Outlet Location (Optional)	T	T	T	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B	T, B		
Outlet Options (Optional)	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex			
Finish	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green			
Link																																																					