

Hadco post top families feature a range of traditional designs, providing style and elegance to parks, downtown streets; residential communities. They also offer a range of optical distributions and aesthetic options such as cages, finials, globes, and panels to accessorize your solution.

																										
	Good	Good	Good	Good	Good	Good	Good	Good	Good	Good	Good	Good	Good	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better
Category	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Historical	Transitional	Historical	Historical	Historical	Historical	Historical	Transitional
Style	Hexagon	Caged Acorn	Square Lantern	Square Lantern	Acorn	Hexagon	Hexagon	Cage Acorn	Square Lantern	Acorn	Acorn	Acorn	Acorn	Hexagon	Square Lantern	Square Lantern	Caged Globe	Caged Acorn	Open	Caged Acorn	Caged Acorn	Caged Acorn	Square Lantern	Square Lantern	Open	
Product	Grande Manor	Grosse Point	Independence	Indian Wells	MainView	Manor	New London	New Oxford	Savanah	Victoria Small	Victoria Large	Victoria Small	Victoria Small	Architectural	Baltimore Large	Baltimore Small	CityPost	Hagerstown	Hagerstown	Refractive Globe	Refractive Globe	Refractive Globe	TownView	TownView	UXI	
Prefix	6134	3100	VX151/VX152	28738	MV	5534	VX8911	VX022	VX671	VL71	VL72	V71	V72	VX600	VX681	VX651	TX1	TX03	TX03C	CL32/CL52)	RL32/RL52	RL34/RL54	TVLN, TVLC	TVPC, TVPR	UX1	
Light Engine	LED Lamp Included	LED Lamp Included	LEDgine	LED Lamp Included	Vertcial Light Engine	LED Lamp Included	LEDgine	LEDgine	LEDgine	EcoSwap	EcoSwap	LED Lamp Included	LED Lamp Included	LEDgine	LEDgine	LEDgine	LEDgine	LEDgine	Comfort	Lumilock (GX4)	Lumilock (GX4)	Lumilock (GX4)	LEDgine	LEDgine	LEDgine	
Lumen Output Range	Up to 4,408	Up to 6,264	Up to 13,325	Up to 3,393	Up to 11,723	Up to 4,7213	Up to 12,767	Up to 14,287	Up to 110 LPW	Up to 7,769	Up to 7,769	Up to 7,812	Up to 7,905	Up to 11,427	Up to 16,613	Up to 13,325	Up to 15,575	Up to 19012	Up to 8,467	Up to 9,859	Up to 10,405	Up to 12,316	Up to 12,808	Up to 12,381	Up to 14,065	
Efficacy	Up to 91 LPW	Up to 121 LPW	Up to 137 LPW	Up to 87 LPW	Up to 149 LPW	Up to 91 LPW	Up to 101 LPW	Up to 115 LPW	Up to 16613	Up to 121 LPW	Up to 121 LPW	Up to 139 LPW	Up to 140 LPW	Up to 117 LPW	Up to 115 LPW	Up to 137 LPW	Up to 127 LPW	Up to 128 LPW	Up to 102 LPW	Up to 107 LPW	Up to 103 LPW	Up to 130 LPW	Up to 125 LPW	Up to 121 LPW	Up to 114 LPW	
Distribution	5	5	2, 3, 3W, 4, 5	5	3, 5	5	2, 3, 3W, 4, 5	2, 3, 3W, 4, 5	2, 3, 3W, 4, 5	3,5	3,5	5	5	2, 3, 3W, 4, 5	2, 3, 3W, 4, 5	2, 3, 3W, 4, 5	2, 3, 3W, 4, 5	2, 2H, 3, 3H, 3W, 3WH, 4, 5	1, 2, 3, 4, 5	3, 5	3, 5 Short & Wide	3, 5 Short & Wide	23, 3S,3W,5, 2H, 3SH, 3WH	23, 3S,3W,5, 2H, 3SH, 3WH	2, 3, 3W, 4, 5	
Color Temperature	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	2700K, 3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K,4000K	3000K,4000K	3000K,4000K	3000K,4000K	3000K,4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	2700K, 3000K, 4000K	2700K, 3000K, 4000K	3000K, 4000K	
Globe/Panels	Opal, Prismatic	Decorative, Ribbed	Clear, Frosted, Ribbed	Opal, Prismatic	Visual Comfort Acorn	Opal, Prismatic	Clear, Frosted	Ribbed	Clear, Frosted, Ribbed	Acrylic	Acrylic	Clear, Visual Comfort	Clear, Visual Comfort	Clear, Frosted	Clear, Frosted, Ribbed	Clear, Frosted, Ribbed	Opal, Clear, Ribbed	Ribbed	Open	Ribbed	Narrow Body	Wide Body	Open, Comfort Lens	Comfort Panel, Ribbed	Open, Clear/Frosted Glass	
Fitter/POD	Standard	D, R	Standard	Standard	G	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	H, J, L, S	A, B, C, D, E, G, H, J, L, T	B, H	M, P, R	A, B, C, D, G, H, L, T	A, B, H, L, T	A, L4, L3, S2, S3, S4	A, L4, L3, S2, S3, S4	Standard	
Roof	Standard	Standard	Standard	Standard	-	Standard	Standard	Standard	Standard	-	-	-	-	Standard	Standard	Standard	L	Standard	C,D	Short, Round, Flt, Cone, with/without Brim	A, B, C, D	A, B, C, D, G	Square, Curved	Square, Curved	Standard	
Cage/Band	Standard	✓	Standard	Standard	-	-	-	Standard	-	-	-	-	-	Standard	Standard	Standard	P, Q	✓	Q, HP	4 Legs, 8 Legs	A, B, E, F, H, N	B, E, F, G, I, J, N	-	-	-	
Fininal	Standard	A, M, P, N	Standard	-	-	Standard	Standard	Standard	Standard	-	-	-	-	Standard	Standard	Standard	A, B, C, D, E, G, H, N	A, B, C, D, E, G, H, N	A, B,C,D, E, F, G, H, N	-	A, B, C, D, E, F, G, H, N	A, B, C, D, E, F, G, H, N	Cupola	Cupola	Standard	
Mounting Height Range	10' ~ 20'	10' ~ 15'	15' ~ 25'	10' ~ 15'	10' ~ 25'	10' ~ 20'	10' ~ 20'	10' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 30'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	15' ~ 25'	
0 Uplight	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	✓	-	-	-	-	-	-	
Field Adjustable Wattage Selector (FAWS)	-	-	-	-	✓	-	✓	-	-	-	-	-	-	-	✓	✓	-	✓	-	✓	✓	✓	✓	✓	-	
DALI	-	-	✓	-	✓	-	✓	✓	✓	✓	-	-	-	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	
Sensor Ready Driver	-	-	-	-	✓	-	✓	✓	✓	✓	-	-	-	✓	✓	✓	✓	✓	✓	-	-	-	✓	✓	✓	
Sensor Ready Receptacle (TLRSR)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	✓	
Service Tag	-	-	-	-	✓	-	-	-	-	-	-	-	-	-	-	-	-	✓	✓	✓	✓	✓	✓	✓	-	
Photocell	Button Eye	Button Eye	Button Eye, Twist Lock	Button Eye	3 Pin, 7 Pin	Button Eye	Button Eye, Twist Lock	Button Eye, Twist Lock	Button Eye, Twist Lock	Button Eye	Button Eye	Button Eye	Button Eye	Button Eye	Button Eye	Button Eye	Button Eye, Twist Lock	Button Eye, Twist Lock	Button Eye, Twist Lock	Button Eye, Twist Lock	Button Eye, Twist Lock	Button Eye, Twist Lock	Twist Lock	Twist Lock	Button Eye, Twist Lock	
Receptacle	-	-	3 Pin, 7 Pin	7 Pin	7 Pin	-	3 Pin, 7 Pin	3 Pin, 7 Pin	3 Pin, 7 Pin	3 Pin, 7 Pin	-	-	-	3 Pin, 7 Pin	3 Pin, 7 Pin	3 Pin, 7 Pin	3 Pin, 7 Pin	7 Pin	7 Pin	3 pin, 7 pin	3 pin, 7 pin	3 pin, 7 pin	7 Pin	7 Pin	3 Pin, 7 Pin	
Shielding	-	-	H	-	H	-	H	H	H	-	-	-	-	H	H	H	H	H	-	H	H	H	H	H	H	
Additional Surge Protection	-	-	✓	-	✓	-	✓	✓	✓	-	-	-	-	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	
Finish	Black, White, Verde, Bronze, Forest Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, Bronz, Forest Green, Verde, White	Black, White, Bronze, Green (Smooth & Textured)	Black, Bronz, Forest Green, Verde, White	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Bronze, Green, Grey	Black, White, Bronze, Green, Grey	Black, White, Bronze, Green, Grey	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Bronze, Green (Smooth, Textured)	Black, White, Bronze, Green (Smooth, Textured)	Black, White, Verde, Bronze, Green, Grey	
IP Rating	-	-	IP66	-	IP66	-	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	
Vibration	-	-	-	-	-	-	-	1.5G	-	-	-	-	-	1.5G	1.5G	1.5G	1.5G	1.5G	1.5G	1.5G	1.5G	1.5G	3G	3G	1.5G	
DLC Listing	-	-	✓	-	✓	-	✓	✓	✓	✓	✓	-	-	✓	✓	✓	✓	✓	-	✓	✓	✓	✓	✓	✓	
Certifications	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL	
Lifetime Per TM21	L70 > 50,000 hours	L70 > 50,000 hours	L70 > 60,000 hours	L70 > 50,000 hours	L70 > 50,000 hours	L70 > 50,000 hours	L70 > 50,000 hours	L70 > 50,000 hours	L70 > 60,000 hours	L70 > 54,000 hours	L70 > 54,000 hours	L70 > 50,000 hours	L70 > 50,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 54,000 hours	L70 > 54,000 hours	L70 > 54,000 hours		
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	
Link																										