

Hadco features a wide variety of pendants with elegant and sophisticated looks that are suitable to provide style and performance to work in urban applications, including residential streets, city streets, campuses, parking lots, and retail centers.



	Better	Better	Better	Better	Better	Better	Better	Better
Category	Transitional	Transitional	Transitional	Transitional	Transitional	Transitional	Transitional	Transitional
Style	Straight	Straight	Straight	Curved	Curved	Teardrop	Curved	Curved
Product	PIMA Large	Pima Small	Pima Small -Comfort	Swan	Swan-Comfort	Tear Drop Large	Westbrooke	Westbrooke - Comfort
Prefix	CXF5	CXF6	CXF6-C	CXF4	CXF4-C	TXF9	CXF14/CX15	CXF14/CXF15-C
Light Engine	LEDgine	LEDgine	Comfort	LEDgine	Comfort	LEDgine	LEDgine	Comfort
Lumen Output Range	Up to 19,539	Up to 19,539	Up to 8,899	Up to 19,593	Up to 8,899	Up to 23,464	Up to 20,022	Up to 8,899
Efficacy	Up to 129 LPW	Up to 129 LPW	Up to 107 LPW	Up to 129 LPW	Up to 107 LPW	Up to 152 LPW	Up to 168 LPW	Up to 107 LPW
Distribution	2, 3, 3W, 4, 5	2, 3, 4, 5	1,2, 3, 4, 5	2, 3, 4, 5	1,2, 3, 4, 5	2, 3, 3W,4, 5	2, 3, 4, 5	1,2, 3, 4, 5
Color Temperature	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K
Globe/Panels	Flat Glass	Flat Glass	Flat Glass	Flat Glass	Flat Glass	Flat Glass, Acylic Long Globe	Flat Glass	Flat Glass
Roof	Straight Side	Straight Side	Straight Side	Curved Side	Curved Side	Die Cast	Curved Side	Curved Side
Mounting Height Range	15' - 30'	15' - 30'	15' - 25'	15' - 30'	15' - 25'	20' - 30'	15' - 30'	15' - 25'
0 Uplight	✓	✓	✓	✓	✓	Flat Glass	✓	✓
Field Adjustable Wattage Selector (FAWS)	✓	✓	-	✓	-	✓	✓	-
DALI	✓	✓	✓	✓	✓	✓	✓	✓
Sensor Ready Driver	✓	✓	-	✓	-	✓	✓	-
Sensor Ready Receptacle (TLRSR)	-	-	-	-	-	✓	-	-
Receptacle	7 Pin On Arm	7 Pin On Arm	7 Pin On Arm	7 Pin On Arm	7 Pin On Arm	7 Pin On Arm	7 Pin On Arm	7 Pin On Arm
Shielding	H	H	-	H	-	H	H	-
Additional Surge Protection	✓	✓	✓	✓	✓	✓	✓	✓
Finish	Black, White, Verde, Bronze, Grey, Green	Black, White, Verde, Bronze, Grey, Green	Black, White, Verde, Bronze, Grey, Green	Black, White, Verde, Bronze, Grey, Green	Black, White, Verde, Bronze, Grey, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Grey, Green	Black, White, Verde, Bronze, Grey, Green
IP Rating	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66
Vibration	1.5G	1.5G	-	1.5G	-	1.5G	-	-
DLC Listing	✓	✓	✓	✓	✓	✓	✓	✓
Certifications	ETL	ETL	ETL	ETL	ETL	ETL	ETL	ETL
Lifetime Per TM21	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years
Link								