

# LUMEC

by  Signify

Outdoor

Roadway Security Light

Product Selection Guide



	Good	Good
Product	Roadway Security Light Small	Roadway Security Light Medium
Prefix	RSLS	RSLM
Lumen Output Range	UP to 4,682	Up to 8,456
Efficacy	Up to 125 LPW	UP to 128 LPW
Distribution	R3M, 5	R3M, 5
Color Temperature	3000K, 4000K	3000K, 4000K
Mounting Height Range	15' - 25'	20' - 35'
0 Uplight	✓	✓
Photocell	PH8	PH8
Receptacle	TLRD7	TLRD7
Shielding	Prismatic Lens	Prismatic Lens
API (Factory Label)	Standard	Standard
Pre-Package Available	✓	✓
Finish	Grey	Grey
IP Rating	IP66	IP66
Vibration Rating	3G	3G
DLC Listing	Standard	Standard
Certification	Dark Skies	Dark Skies
Lifetime per TM21	L70 > 36,000 hours	L70 > 36,000 hours
Limited Warranty	5 years	5 years
Link		



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.