

Lumec offers a range of pendant designs to compliment the wide assortment of urban luminaires to harmonize the elegance and provide flexibility and design options. Suitable for projects, including parks, residential communities, downtown areas, commercial developments, and more.



	Good	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better
Category	Tansitional	Historical	Historical	Historical	Transitional	Transitional	Transitional	Transitional	Transitional	Transitional	Transitional	Transitional	Transitional	Historical	Historical	Contemporary	Contemporary
Style	Tear drop	Tear drop	Caged Acorn	Open	Other	Other	Dome	Dome	Dome	Dome	Dome	Open	Open	Square Lantern	Caged Globe	Open	Open
Product	Renaissance Small	Renaissance Large	Ancestra	Ancestra - Comfort	Candela	Candela	Domus Large	Domus Large - Comfort	Domus Large	Domus Large - Comfort	Domus Small	MetroScope	MetroScope - Comfort	Square Lantern	Transit	UrbanScape	UrbanScape - Comfort
Prefix	RNS20	RN20-RN30	AT50	AT50-C	CAND1	CAND3	DMS50	DMS50-C	DMS55	DMS55-C	DOS	MSR	MSR-C	S26P	TR20	MSC	MSC-C
Light Engine	LEDgine	LEDgine	LEDgine	Comfort	EcoSwap	EcoSwap	LEDgine	Comfort	LEDgine	Comfort	LEDgine	LEDgine	Comfort	LEDgine	LEDgine	LEDgine	Comfort
Lumen Output Range	Up to 5,273	Up to 22,713	UP to 11,058	Up to 7,840	Up to 8,042	Up to 7490	Up to 23,243	Up to 8,899	Up to 23,243	Up to 8,899	Need Update	Up to 28,042	Up to 9,831	Up to 11,674	Up to 11,058	Up to 28,042	Up to 8,988
Efficacy	Up to 102 LPW	Up to 130 LPW	Up to 138 LPW	Up to 94 LPW	Up to 118 LPW	Up to 110 LPW	Up to 152 LPW	Up to 107 LPW	Up to 152 LPW	Up to 107 LPW	Need Update	Up to 153 LPW	Up to 109 LPW	Up to 117 LPW	Up to 172 LPW	Up to 153 LPW	Up to 108 LPW
Distribution	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type III, V	Type III, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, III Wide, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, III Wide, IV, V	Type II, III, IV, V
Color Temperature	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000k	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K
Globe/Panels	Acrylic Globe, Glass Globe	Acrylic Globe, Glass Lens	Acrylic Globe, Flat Glass, Sag Glass	Open	Clear, Satin	Polycarbonate	Acrylic Globe, Flat Glass, Sag Glass	Flat	Acrylic Globe, Flat Glass, Sag Glass	Flat	Flat	Flat, Sag Lens	Flat	Clear, Satin Clear	Acrylic, Flat Glass, Sag Lens	Flat Lens, Sag Lens	Flat
Roof	Die Cast	Die Cast	Metal	Metal	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast
Cage/Band	Die Cast	Die Cast	CR20, CR30, CR40, DA, GRD	CR20, CR30, CR40, DA, GRD	Spun Aluminum	Spun Aluminum	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	-	-	-	-
Mounting Height Range	15' -25'	15' -25'	15' -25'	15' -25'	15' - 25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	10' - 20'	15' -30'	15' -25'	15' -25'	15' -25'	15' -30'	15' -25'
O Uplight	-	Flat Lens	Flat Lens, Sag Lens	✓	-	-	Flat Lens, Sag Lens	✓	Flat Lens, Sag Lens	✓	✓	✓	✓	-	Flat Lens, Sag Lens	✓	✓
DALI	✓	✓	✓	✓	-	-	✓	✓	✓	✓	✓	✓	✓	-	-	✓	✓
Sensor Ready Driver	✓	✓	✓	✓	-	-	✓	-	✓	-	-	✓	✓	✓	✓	✓	✓
Service Tag	✓	✓	-	-	-	-	✓	-	✓	-	-	✓	✓	-	-	✓	✓
Photocell	PH8, PHXL	PH8, PHXL	PH8, PHXL	PH8, PHXL	-	-	PH7, PH8, PHXL	PH8, PHXL	PH7, PH8, PHXL	PH8, PHXL	-	PH8, PHXL	PH8, PHXL	-	-	PH8, PHXL	PH8, PHXL
Receptacle	7 Pin On Arm	7 Pin On Arm	7 Pin On Arm	7 Pin On Arm	7 Pin On Arm	7 Pin on Arm	7 Pin on Arm	7 Pin	7 Pin on Arm	7 Pin	-	7 Pin	7 Pin	7 Pin on mtg bracket	7 Pin Replace Cupala	7 Pin	7 Pin
Shielding	HS	HS	HS	-	HS	HS	HS	-	HS	-	-	HS	-	HS	HS	HS	-
Additional Surge Protection	✓	✓	✓	✓	-	-	✓	✓	✓	✓	-	✓	✓	✓	✓	✓	✓
Finish	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)
IP Rating	IP66	IP66	-	-	Wet Locaton	Wet Location	IP66	Wet Location	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP66
Vibration	1.5G	3G	-	-	-	-	3G	-	3G	-	1.5G	3G	1.5G	-	-	3G	1.5G
DLC Listing	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Certifications	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus
Lifetime Per TM21	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 54,000 hours	L70 > 54,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years
Link																	