

LUMEC




by  Signify

Outdoor

Side Arm Mount

Product Selection Guide



	Better	Better	Better
Category	Modern	Modern	Modern
Style	Contemporary	Contemporary	Contemporary
Product	Leonis	SoleCity Small	SoleCity Medium
Prefix	LEN4, LEN5, LEN6	ULS100	ULM100
Lumen Output Range	Up to 13,211	Up to 15,776	Up to 31,718
Efficacy	Up to 141 LPW	Up to 128 LPW	Up to 128 LPW
Distribution	2, 3, 4, 5	LE2, LE3, LE4	LE2, LE3, LE4
Color Temperature	3000K, 4000K	3000K, 4000K	3000K, 4000K
Mounting Height Range	20' - 30'	15' - 30'	15' - 35'
DALI	✓	✓	✓
Sensor Ready Driver	✓	-	-
Photocell	✓	✓	✓
Receptacle	✓	✓	✓
Shielding	HS	HS	HS
Additional Surge Protection	✓	✓	✓
Finish	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)
IP Rating	IP66	IP66	IP66
Vibration	1.5G	1.5G	1.5G
DLC Listing	-	✓	✓
Certifications	cUL	cUL	cUL
Lifetime Per TM21	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours
Limited Warranty	5 years	5 years	5 years
Link			



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.