


# LUMEC




by  Signify

Outdoor

Light Column

Product Selection Guide



	Good	Better	Better
Category	Modern	Modern	Modern
Style	Light Column	Light Column	Light Column
Product	<b>SoleCity Light Column</b>	<b>SleekVision Light Column (6")</b>	<b>SleekVision Light Column (10")</b>
Prefix	ULLC100	VCC06	VCC10
Lumen Output Range	Up to 12,157	Up to 7,507	Up to 8,756
Efficacy	Up to 123 LPW	Up to 153 LPW	Up to 158 LPW
Distribution	LE3, LE5	LEV3, LEV5	LEV3, LEV5
Color Temperature	3000K, 4000K	3000K, 4000K	3000K, 4000K
Mounting Height Range	10' - 20'	8' - 20'	8' - 20'
DALI	✓	✓	✓
Sensor Ready Driver	-	✓	✓
Photocell	PH8, PHXL	PH8, PHXL	PH8, PHXL
Receptacle	7 Pin	7 Pin	7 Pin
Shielding	HS	HS	HS
Finish	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White (Textured)
IP Rating	IP66	IP66	IP66
Vibration	-	1.5G	1.5G
DLC Listing	✓	✓	✓
Certifications	cUL	cUL	cUL
Lifetime Per TM21	L70 > 60,000 hours	L70 > 100,000 hours	L70 > 100,000 hours
Limited Warranty	5 years	5 years	5 years
Link			



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.