

# Stonco

by @signify

Outdoor

Wall Mount

Product Selection Guide

Stonco features a variety of wall packs to suit a range of building types. Stonco wall mount luminaires are readily available and easy to install, making them a great choice for any project.



	Good	Good	Good	Good	Better	Better	Better
	LED Square Wall Light	LED Wall Light	Tall Wall Pack	Wall Pack Dual Select	LytePro Wall Small	LytePro Wall Medium	LytePro Wall Large
Prefix	SWL	LWL	TW	WP	LPW7	LPW16	LPW32
Lumen Output Range	1178	1104	2277	3860-12800	1050	2065-4629	6472-9637
Efficacy	93	90	120	128-145	108	87-104	95-114
Distribution	-	-	Type 4	-	Type 2	Type 3.4	Type 3.4
Color Temperature	3000K	3000K	4000K	3000, 4000, 5000K	3000,4000K	3000, 4000K	3000, 4000K
Mounting Height	7-10	7-10	7-10	10-25	7-10	10-15	15-25
0 Uplight	-	-	-	-	✓	✓	✓
Emergency (0°C to 40°C)	-	-	-	-	-	-	✓
Field Adjustable Wattage Selector (FAWS)	-	-	-	✓	-	-	✓
Motion Response	-	-	-	-	-	-	✓
Photocell	Button	Button	Button	✓	Button	Button	Button
Finish	Bronze	Bronze	Bronze	Bronze	Black, Bright, Bronze, Dark Grey, Medium Grey	Black, Bright, Bronze, Dark Grey, Medium Grey	Black, White, Bronze, Dark Grey, Medium Grey
IP Rating	-	-	IP65/IP66	IP65	IP65	IP65	IP65
DLC Listing	-	-	Standard	Standard	Standard	Standard	Standard
Certifications	cULus	cULus	cULus	cULus	cETLus	cETLus	cETLus
Lifetime	L70-48000h	L70-48,000h	L70-102,000h	L70-54000h	L70-60,000h	L70-54,000h	L70-54000h
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years
Link							