



Outdoor

Bollards

Product Selection Guide

Gardco, Lumec, Hadco, and Stonco feature multiple bollards for a range of applications and architectural styles.



Brand	Gardco	Gardco	Gardco	Lumec	Lumec	Lumec	Lumec	Lumec	Lumec	Hadco	Hadco	Hadco	Hadco	Hadco	Stonco
Product	Full Cutoff Bollard	Louver Bollard BR830	PureForm Bollard	Oval	Domus	BOR	ClassicStyle	SleekVision	SoleCity	DB14	DB21	DB30	OB361	TB361	Commercial Bollard
Prefix	BR840	BRM83	PBL	UVB1	DOSB1	BOR80-W	VBR	VBC	ULB100	DB14	DB21	DB30	OB361	TB361	BL25
Lumen Output Range	986-1,999	1053-1226	500 - 4200	Not Published	Not Published	HID Only	Up to 1,493	Up to 1,915	Up to 6,020	800	800	800	Not Published	Not Published	2508
Efficacy	119-128	25-32	72-100	Not Published	Not Published	HID Only	Up to 83 LPW	Up to 106 LPW	Up to 109 LPW	84	84	84	Not Published	Not Published	97
Distribution	Type 3, 5	180° or 360°	Type 3, 5	Symmetric	Symmetric	Symmetric	3,5	3,5	LEV3, LEV5	Symmetric	Symmetric	Symmetric	Type 5 Panels, Type 5 Louvers, Opal Panels, Type V Cone	Type 5 Panels, Type 5 Louvers, Opal Panels, Type V Cone	Type 5
Color Temperature	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	Red, Blue, or White	-	-	3000K, 4000K	3000K, 4000K	3000K, 4000K	2700K	2700K	2700K	3000K, 4000K	3000K, 4000K	4000K
Height	30", 36", 42"	30", 36"	36", 42", 60"	40"	40"	40"	40"	40"	34", 40"	14"	21"	30"	40.25"	37"	42"
O Uplight	✓	-	✓	-	-	-	-	-	Uplight Deflector Option	-	-	-	-	-	-
School Option (galvanized steel tenon)	✓	✓	-	-	-	-	-	-	-	-	-	-	-	-	-
Shielding	-	-	-	-	-	Decorative Cover	HS	HS	UD	-	-	-	-	-	-
Emergency (0°C to 40°C)	-	-	✓	-	-	-	-	-	-	-	-	-	-	-	-
Field Adjustable Wattage Selector (FAWS)	-	-	✓	-	-	-	-	-	-	-	-	-	-	-	-
Auto Profile Dimming (Dynadimmer)	-	-	✓	-	-	-	✓	✓	✓	-	-	-	-	-	-
Motion Response	✓	✓	✓	-	-	-	✓	✓	-	-	-	-	-	-	-
Photocell	✓	-	✓	✓	✓	✓	✓	✓	✓	-	-	-	-	-	-
DALI	-	-	-	-	-	-	✓	✓	✓	-	-	-	-	-	-
Additional Surge Protection (20kA)	✓	✓	✓	-	-	-	✓	✓	-	-	-	-	-	-	-
Additional Options	-	-	GFCI Outlet	Vandal Proof Hardware	Vandal Proof Hardware	Non Luminous Option Chain Handles Duplex Receptacle Vandal Proof Hardware	Decorative Cage, Decorative Base Cover, Vandal Proof Hardware, AMPD, AST, CLO		Wood Panels, Vandal Proof Screws, AST, CLO, OTL	-	-	-	-	-	-
Finish	Bronze, White, Black, Medium Grey, Dark Grey	Bronze, White, Black, Medium Grey, Dark Grey	Bronze, White, Black, Medium Grey, Dark Grey	Midnight Blue, Ocean Blue, Royal Blue, Sandstone Gold, Black, Bronze, Blue Green, Forest Green, Dark Forest Green, Green, Medium Grey, Burgundy, Scarlet, White, Natural Aluminum, Hammer-tone, Hammer-tone Silver			Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White, (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White, (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White, (Textured)	Black, Bronze	Black, Bronze	Black, Bronze	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Bronze
Environmental Location Rating	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location
DLC Listing	Standard	-	Standard	-	-	-	Standard	Standard	Standard	-	-	-	-	-	Standard
Certifications	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	cULus	ETL	ETL	ETL	ETL	ETL	cULus
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h	-	-	-	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	25,000	25,000	25,000	50,000 hrs	50,000 hrs	54,000 hrs
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years
Link															

