



Outdoor

Wall Sconces

Product Selection Guide

Gardco wall sconce luminaires blend excellent performance with aesthetics. Multiple shapes are available to blend with architecture or make a statement.



Rating	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Best	Best
Product	GeoForm Cylinder Small	GeoForm Block Small	GeoForm Wedge Small	GeoForm Cylinder Medium	GeoForm Block Medium	GeoForm Wedge Medium	111 Mini Sconce	101 LED	161 LED	121 LED	PureForm Sconce Comfort	PureForm Sconce
Prefix	GCS	GBS	GWS	GCM	GBM	GWM	111L	101L	161	121	PWS	PWS
Lumen Output Range	1,700-6,500	1,700-6,500	1,700-6,500	1,700-6,500	2,900-12,700	2,900-12,700	1,400-4,700	1,429-12,045	10,245-27,300	1,391-12,421	2,448-10,698	6,298-21,800
Efficacy	130-175	130-175	130-175	130-175	140-180	140-180	115-134	98-136	102-121	93-140	102-116	120-137
Distribution	Type 2, 3, 4, Wall Wash, Spot, Pencil	Type 2, 3, 4, Wall Wash, Spot, Pencil	Type 2, 3, 4	Type 2, 3, 4, Wall Wash, Spot, Pencil	Type 2, 3, 4, Wall Wash, Spot, Pencil	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4, BLC
Uplight Capability (wet location)	✓	✓	-	✓	✓	-	-	-	-	-	-	-
Color Temperature	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5700	3000, 4000, 5000	3000, 4000, 5000	2700, 3000, 3500, 4000, 5000, Amber	2700, 3000, 3500, 4000, 5000, Amber	2700, 3000, 3500, 4000, 5000, Amber
Mounting Height	8-12'	8-12'	8-12'	8-12'	12-24'	12-24'	8-12'	8-20'	15-25'	8-20'	8-20'	15-25'
0 Uplight	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Emergency Battery Backup (0°C to 40°C)	✓	✓	✓	-	-	-	-	-	-	-	✓	-
Emergency Cold Pack (-20°C to 40°C)	-	-	-	✓	✓	✓	-	✓	-	✓	✓	✓
Field Adjustable Wattage Selector (FAWS)	✓	✓	✓	✓	✓	✓	-	-	-	✓	✓	✓
Dual Circuit Control (DCC)	-	-	-	-	✓	✓	-	✓	✓	✓	-	✓
Auto Profile Dimming	-	-	-	✓	✓	✓	-	✓	✓	✓	✓	✓
Motion Response	-	-	-	-	✓	✓	-	✓	✓	✓	✓	✓
Interact Compatible	✓	✓	✓	✓	✓	✓	-	✓	-	✓	✓	✓
Photocell	Button	Button	Button	Button	Button	Button	Button	Button, TLRD5, TLRD7, TLRPC	Button	Button	Button	Button
Additional Options	Emergency Battery Backup	Diffusing lens, Emergency Battery Backup	Diffusing lens	Emergency Battery Backup	Emergency Battery Backup	Emergency Battery Backup	Diffusing lens	-	-	-	-	-
Finish	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray
IP Rating	IP65	IP65	IP65	IP65	IP65	IP65	IP66	IP66 LED Light Engine	IP66	IP66 LED Light Engine	IP65	IP65 housing/IP66 LED Light Engine
DLC Listing	Premium	Premium	Premium	Premium	Premium	Premium	-	Standard	Standard	Premium, Standard	Premium	Premium
Certifications	cULus	cULus	cULus	cULus	cULus	cULus	Title 24, cULus	Title 24, cULus	cULus	Title 24, cULus	UL/cUL	UL/cUL
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years
Link	Coming soon	Coming soon	Coming soon	Coming soon	Coming soon	Coming soon						

