

LIGHTOLIER

by 

Downlighting

Retrofit downlights

Product Selection Guide



		Budget-grade			Value-grade	
		Good	Good	Good	Better	Better
		Retrofit Downlight	Flat Downlight Select	Mini Gimbal & Mini Downlight	CorePro LED	Commercial Retrofit
Trims	Styles	○ 4", 5/6"	○ 3", 4", 5", 6", 8" □ 3", 4", 6", 8"	○ 3", 4", 6"	○ 4", 5", 6"	○ 4", 5", 6"
	Flanges	Matches Aperture	Matches Aperture	Matches Aperture	Matches Aperture	Matches Aperture
	Reflectors	White	White	White	White	White
	Types	Downlight Baffle	Downlight	Downlight Gimbal	Downlight	Downlight
	Beams	Wide	Wide	Wide	Wide	Wide
Performance	Applications	Residential and Hospitality				
	Lumens	700lm, 900lm	370-1300 lm (lumen field selectable)	375-1185 lm (lumen field selectable)	4": 800lm 5": 950lm 6": 800lm & 1200lm	4": 800lm 5": 950lm 6": 800lm & 1200lm
	Watts	12-18W	12-15W	8W	11-16W	11-16W
	Efficacy	up to 78lm/W	up to 70lm/W	up to 70lm/W	up to 89lm/W	up to 89lm/W
	CCTs (K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, and 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, and 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, and 5000K)	3000, 4000	3000, 4000
	CRIs	90	90	90	80, 90	80, 90
	Lifetime	50,000hrs	50,000hrs	50,000hrs	50,000hrs (L70)	50,000hrs (L70)
Technology	Dimming	ELV, TRIAC	ELV, TRIAC & 0-10V dim	ELV, TRIAC & 0-10V dim	TRIAC	TRIAC
	Installations	New Construction Remodeler Wet locations	New Construction Remodeler Wet locations	New Construction Remodeler Wet locations	Wet locations	Wet locations
	Labels	cULus listed, IC & Title 24 rated, RoHS, ENERGY STAR	cULus listed, IC & Title 24 rated, Airseal IC rated, RoHS, ENERGY STAR	cETLus listed, IC & Title 24 rated, Airseal IC rated, RoHS, ENERGY STAR	cULus listed, Title 24 rated, Airseal IC rated, RoHS, ENERGY STAR	cULus listed, Title 24 rated, Airseal IC rated, RoHS, ENERGY STAR
	Warranty	5-year limited	5-year limited	5-year limited	5-year limited	5-year limited



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600,
Bridgewater, NJ 08807
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.