

**Creativity and continuity can coexist**

**Paradox:** a situation where two facts seem to state the impossible, yet actually reveal an intriguing truth

---

The next generation of Gardo PureForm LED site and area luminaires proves that the impossible is indeed possible.

A paradox of

**creativity  
and continuity**





# Make a distinctive statement

again and again

**PureForm** is a cohesive stylish family that offers you continuity within a project, while still helping you make your own unique statement every time.

With PureForm, you can illuminate an entire site with one family, yet each individual luminaire is optimally designed. We know that your image is your reputation, and PureForm makes it easy to provide both comfort and performance while making a distinct impression. Seamlessly integrating the entire family with the latest controls solutions also makes management easy, further enhancing value and allure.







# Aesthetics that are **uniquely similar**

At a glance, **PureForm** luminaires are obviously all part of one family, but each product also makes a strong individual aesthetic statement. Your image is not sacrificed, yet your luminaire selection is simplified, saving time and hassle.

The PureForm family consists of small, medium, and large area luminaires, a wall sconce, bollard, and post top. These luminaires were designed to complement each other, yet each product fulfills its own unique purpose in style. This ensures that the luminaires bring a cohesive feeling to your project, while also enhancing your creative vision.





# Strikingly unobtrusive

Your site is a palette for your artistic vision. Luminaires are one of the mediums through which you create that vision, but they shouldn't take away from it.



PureForm boasts sleek, unobtrusive profiles that minimize distraction while creatively providing light to enhance the user experience. Providing you inspiration rather than frustration, this family complements your space day and night, while helping users have a sense of security.





# Anticipate **unexpected comfort**

Rest assured that your projects will be recognized not only for their image, but also for providing desired, yet unexpected, comfort and usability.

Comfort optics available in the small and medium area, the round arm mount and post top, and the wall sconce, reduce glare for an enhanced user experience.



# More possibilities mean **fewer choices**

Stop wasting time looking for a different luminaire for each application. With two specialized light engines and multiple lumen outputs, you have a full range of possibilities from this single family.

Precision optics



Comfort optics




From pedestrian and low glare to high performance, the PureForm family can satisfy your exact requirements while maintaining project continuity.

#### Comfort optics

- Eliminate glare to increase visual comfort for an enhanced user experience
- Best suited for pedestrian applications at lower mounting heights
- Provide flexibility of optical distributions while focusing on the capabilities needed for pedestrian applications

#### Precision optics

- Multiple lumen outputs, including higher output to accommodate higher mounting heights
- Optimized for performance, uniformity and spacing
- Provide greater control, with shielding and back light control options
- Extremely energy efficient, providing efficacy up to 150 LPW



# Completely **connected**

**PureForm** luminaires easily integrate with a full range of control options, from simple to advanced. The entire family can be controlled individually or communicate with each other, offering ease of management and significant savings.

**Compatible controls:**

- 0-10V dimming
- Dual circuit control
- Motion response
- Automatic profile dimming
- Field adjustable wattage selector





interact

## Easy. Effective. Smart.

Connectivity is the future and key to unlocking your smart building potential. Interact is a connected system with wireless luminaire level controls and integral occupancy & daylight sensing.

### Features

- No additional wiring required during installation.
- Motion, daylight sensing and grouping can be done right out of the box.
- A gateway can be added for additional features, such as scheduling and remote management.
- Set up is simple and can be done from your smart phone.
- Interact delivers a consistent experience between indoor and outdoor lighting control.
- Interact is the only system that offers wireless connectivity and control for lamps, luminaires, and retrofit kits.

## Precision optics

Higher performance optics for use at higher mounting heights or with applications requiring wider luminaire spacing

## Thermal management

Low profile housing provides excellent convection heat transfer without use of heat fins

## Rugged construction

Die-cast aluminum housing ensures high quality and corrosion resistance

Luminaire and optics are rated IP66

## ComfortEdge optics

ComfortEdge optics enhance the user experience by providing a low glare lighting solution

## Optional integral motion sensor

Integral to the luminaire

Offers energy savings and can enhance sense of security

## Emergency battery backup

Optional emergency battery back up is integral to the luminaire

## Mounting

Standard tenon fits on a 3" OD by 4" long tenon

Mounting to 2-3/8" OD by 4" tenon is optional



## Multiple finish options

Black, white, bronze, dark gray and medium gray textured finish options available, see p. 29

- **Lumen output:** 1,600-17,000 lumens
- **Efficacy:** 90-186 LPW
- **Color temperature:** 2700K, 3000K, 3500K, 4000K, 5000K
- **Color Rendering Index:** 70, 80 CRI
- **Mounting:** T2 mounts to 2-3/8" tenon  
T3 mounts to 3" x 4" tenon
- **Optical distributions:** ComfortEdge optics: Type 2, 3, 4, & 5  
Precision optics: Type 2, 3, 4, 5, & back light control
- **Emergency:** Optional emergency battery backup (cold pack available)

Prior to ordering, consult specification sheets on [gardcolighting.com/pureform](http://gardcolighting.com/pureform) for the most current information, notes, and exclusions.

**Weight:** 20 lbs





## Rugged construction

Die cast aluminum housing ensures highest quality

Optical and electrical compartments rated IP66 to ensure dust or moisture will not interfere with performance



## Emergency battery backup

Optional emergency battery back up is integral to the luminaire

## Precision optics

Higher performance optics for use at higher mounting heights or with applications requiring wider luminaire spacing

## Comfort optics

Comfort optics enhance the user experience by providing a low glare lighting solution

## Optional integral motion sensor

Integral to the luminaire  
Offers energy savings and can enhance sense of security


## Multiple finish options

Black, white, bronze, dark gray and medium gray textured finish options available, see p. 29

- **Lumen output:** 1,500–20,000 lumens
- **Efficacy:** 92–208 LPW
- **Color temperature:** 3000K, 4000K, 5000K
- **Color Rendering Index:** 70, 80 CRI
- **Mounting:** Standard arm, retrofit arm, or wall bracket
- **Optical distributions:** ComfortEdge optics: Type 2, 3, 4, & 5  
Precision optics: Type 2, 3, 4, 4W, 5, 5N, 5W, back light control, and LEED Corner Shielded

Prior to ordering, consult specification sheets on [gardcolighting.com/pureform](http://gardcolighting.com/pureform) for the most current information, notes, and exclusions.

**Weight:** With standard arm, 18 lbs





Science

## Rugged construction

Cast aluminum housing ensures highest quality

Optical and electrical compartments rated IP66 to ensure dust or moisture will not interfere with performance

## Precision optics

Multiple distribution options available with 2-4 LED modules for a range of different lumen outputs

## Emergency battery backup

Optional emergency battery back up is integral to the luminaire

## Optional integral motion sensor

Integral to the luminaire

Offers energy savings and can enhance sense of security

## Multiple finish options

Black, white, bronze, dark gray and medium gray textured finish options available, see p. 29



## Comfort optics

Comfort optics enhance the user experience by providing a low glare lighting solution

- **Lumen output:** Comfort optics: 2,200 – 10,800 lumens  
Precision optics: 1,700 – 16,500 lumens
- **Efficacy:** Comfort optics: 103–126 LPW  
Precision optics: 109–160 LPW
- **Color temperature:** 2700K, 3000K, 3500K, 4000K, 5000K
- **Mounting:** Standard arm, retrofit arm, or wall bracket
- **Optical distributions:** Comfort optics: Type 1, 2, 4, 5 Short and Type 4 Concentrated Downlight  
Precision optics: Type 2, 3 Medium, Type 4, 5 Short, BLC

Prior to ordering, consult specification sheets on [gardcolighting.com/pureform](http://gardcolighting.com/pureform) for the most current information, notes, and exclusions.

**Weight:** With precision optics and standard arm, 22 lbs  
With comfort optics and standard arm, 17 lbs





15771

## Rugged construction

Die cast aluminum housing ensures highest quality

Optical and electrical compartments rated IP66 to ensure dust or moisture will not interfere with performance

## Precision optics

Multiple distribution options available with 3-5 LED modules for a range of different lumen outputs

- **Lumen output:** Comfort optics: 2,400-10,000 lumens  
Precision optics: 8,500-28,900 lumens
- **Efficacy:** Comfort optics: 101-113 LPW  
Precision optics: 124-150 LPW
- **Color temperature:** Amber, 2700K, 3000K, 3500K, 4000K, 5000K
- **Mounting:** Standard arm, adjustable slipfitter, retrofit arm, or wall bracket
- **Optical distributions:** Comfort optics: Type 2, 3, 5  
Precision optics: Type 2, 3, 4, 5, 5W, AFR, BLC

Prior to ordering, consult specification sheets on [gardcolighting.com/pureform](http://gardcolighting.com/pureform) for the most current information, notes, and exclusions.



## Optional integral motion sensor

Integral to the luminaire  
Offers energy savings and can enhance sense of security


## Comfort optics

Comfort optics enhance the user experience by providing a low glare lighting solution

## Multiple finish options

Black, white, bronze, dark gray and medium gray textured finish options available, see p. 29


**Weight:** With standard arm, 27 lbs





# Large area luminaire

# P34



### Optional integral motion sensor

Integral to the luminaire  
Offers energy savings  
and can enhance sense  
of security

### Precision optics

Available with 6-8 LED  
modules for a range of  
different lumen outputs

### Rugged construction

Die cast aluminum housing ensures  
highest quality

Optical and electrical compartments  
rated IP66 to ensure dust or moisture  
will not interfere with performance.


### Multiple finish options

Black, white, bronze, dark  
gray and medium gray  
textured finish  
options available.  
see p. 29

- **Lumen output:** 28,900 – 50,000 lumens
- **Efficacy:** 113-133 LPW
- **Color temperature:** Amber, 2700K, 3000K, 3500K, 4000K, 5000K
- **Mounting:** Standard arm, adjustable slipfitter, retrofit arm, or wall bracket
- **Optical distributions:** Type 2, 3, 4, 5, 5W, AFR, BLC

Prior to ordering, consult specification sheets on [gardcolighting.com/pureform](http://gardcolighting.com/pureform) for the most current information, notes, and exclusions.

**Weight:** With standard arm, 35 lbs





## Rugged construction

Die-cast aluminum housing  
Light engine is rated IP66 and luminaire is rated IP65

## Multiple finish options

Black, white, bronze, dark gray and medium gray textured finish options available, see p. 29

## Emergency battery backup

Optional emergency battery back up meets path-of-egress illumination requirements and is integral to the luminaire

## Precision optics

Multiple lumen outputs allow for mounting up to 25'  
Backlight control optics available to limit spill light

## Optional integral motion sensor

Completely integral to the luminaire with comfort optics  
Does not take away from aesthetics of the luminaire

Offers energy savings and can enhance sense of security



## Comfort optics

Comfort optics enhance the user experience by providing a low glare lighting solution

- **Lumen output:** Comfort optics: 2,500-10,700 lumens  
Precision optics: 6,300-21,800 lumens
- **Efficacy:** Comfort optics: 92-111 LPW  
Precision optics: 94-137 LPW
- **Color temperature:** Amber, 2700K, 3000K, 3500K, 4000K, 5000K
- **Optical distributions:** Comfort optics: Type 2, 3, 4  
Precision optics: Type 2, 3, 4, BLC
- **Emergency:** Optional emergency battery backup (cold pack available)

Prior to ordering, consult specification sheets on [gardcolighting.com/pureform](http://gardcolighting.com/pureform) for the most current information, notes, and exclusions.

**Weight:** Precision optics luminaire, 24 lbs  
Comfort optics luminaire, 20 lbs





## Intelligent optical design

IES Type 3 and 5 distributions allow for excellent uniformity and optimal spacing

High performance optical system designed to achieve wide spacings and full cutoff performance



## Emergency battery backup

Optional emergency battery back up is integral to the luminaire

## Multiple height options

Available in 36", 42" or 60" to achieve desired performance or aesthetics

## Rugged construction

Cast aluminum housing secured with flush, tamper-resistant stainless steel fasteners

Optics are fully sealed and gasketed, rated IP66

## Optional integral motion sensor

Integral to the luminaire

Offers energy savings and can enhance sense of security

## Multiple finish options


Black, white, bronze, dark gray and medium gray textured finish options available, see p. 29



- **Height options:** 36", 42", 60"
- **Lumen output:** 500-5,000 lumens
- **Efficacy:** 95-143 LPW
- **Color temperature:** Amber, 2700K, 3000K, 3500K, 4000K, 5000K
- **Optical distributions:** Type 3, 5
- **Emergency:** Optional emergency battery backup

Prior to ordering, consult specification sheets on [gardcolighting.com/pureform](http://gardcolighting.com/pureform) for the most current information, notes, and exclusions.

- Weight:** 36" - 16 lbs (7.5 kg)  
 42" - 18 lbs (8.2 kg)  
 60" - 22 lbs (9.9 kg)





# Area luminaire mounting details and other options


### Standard arm mount



### Slipfitter mount



### Wall mount



### Retrofit arm mount




#### Retrofit arm

Allows the luminaire to be mounted using a range of existing drill patterns.

#### Hardware

Three bolts are provided to secure the luminaire to the retrofit arm, and the retrofit arm to the pole.



#### Bolster plate

The bolster plate includes an adjustable cage nut that allows you to mount the PureForm to any bolt pattern ranging from 2" to 5.2".

#### Arm cover

When installation is complete, simply tighten the two screws to lock the arm cover in place.

#### PureForm luminaire

Install the retrofit arm to the luminaire's integral arm.

It is easy to re-purpose existing poles by mounting PureForm luminaires with the retrofit arm mount (RAM). The RAM accessory can easily retrofit onto any existing drill pattern on round and square poles, eliminating the need for timely and costly pole drilling.

### Backlight control option



PureForm's backlight control (BLC) optical system can be used to eliminate backlight. These shields are ideal for applications with stringent light trespassing outside property line.

## Finishes



BK – Black



BZ – Bronze



DGY – Dark Gray



MGY – Medium Gray



WH – White

# Experience the paradox of **creativity and continuity**

Discover how Gardco PureForm luminaires make the impossible possible. Simplify your luminaire selection, and add continuity to your projects without sacrificing your creative vision. Contact your local Sales Representative for a personal demonstration or visit [gardcolighting.com/PureForm](https://gardcolighting.com/PureForm) for more information.

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PGc-1714BR - PureForm Gen 2 brochure 03/24 page B of D

**GENLYTE**  
**SOLUTIONS**  
a  **signify** business

Signify North America Corp.  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.

[www.gardcolighting.com](http://www.gardcolighting.com)