






	Good	Good	Good	Good	Good	Better
	APR4	APR5	ATR74	ATR85	ATR106	ATR-C1/ATR-C2
Pole Desc.	Round Straight	Round Straight	Round Tapered	Round Tapered	Round Tapered	Round Tapered Curved
Base Desc.	Optional Base Covers	Optional Base Covers	Bolt Covers	Bolt Covers	Bolt Covers	Bolt Covers
Market Base Name	-					
Height	8', 10', 12', 14', 15', 16', 18', 20'	12', 14', 15', 16', 18', 20'	20', 21', 22', 23', 24', 25'	25', 26', 27', 28', 29', 30', 31', 32', 33', 34'	35', 36', 37', 38', 39', 40'	16', 18', 20', 22', 24', 26', 28', 30', 32', 34'
Diameter	4"	5"	7-4" Tapered	8-5" Tapered	10-6" Tapered	6-4", 7-4", 8-5", 10-6" Tapered
Pole Tenon	-	-	-	-	-	-
Thickness	0.125", 0.226", 0.318"	0.17", 0.219", 0.247"	0.156", 0.188"	0.156", 0.188", 0.250"	0.188", 0.250"	0.156", 0.188", 0.250"
Base	10" Square	12-1/2" Square	11-1/4" Square	12" Square	13" Square	12", 14", 16" Square
Bolt Circle	8-1/2"	12-1/2"	10-1/2"	11-1/2"	14-1/2"	10-1/2", 12-1/2", 14-1/2"
Optional Bases	LBC1, LBC2, LBC3, LBC4C	LBC1, B105, B50	-	-	-	-
EPA @ 90 MPH	3.27-18.64	5.86-21.72	9.65-18.30	8.87-25.65	12.74-25.84	N/A
EPA @ 110 MPH	1.36-12.35	3.41-14.46	5.84-12.03	5.49-17.21	8.01-17.13	N/A
EPA @ 120 MPH	1.19-10.28	2.72-12.13	4.77-10.06	4.38-14.40	6.37-14.17	N/A
EPA @ 150 MPH	1.16-6.53	1.45-7.66	2.74-6.25	2.21-8.87	2.86-8.07	N/A
Options	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Hinged Base, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Hinged Base, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Mid-Pole Luminaire
Finish	Refer to Finishes on pg. 20					
eCat Page URL	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-round-straight-shaft-poles-apr-spr">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-round-straight-shaft-poles-apr-spr</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-round-straight-shaft-poles-apr-spr">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-round-straight-shaft-poles-apr-spr</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-tapered-poles-atr-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-tapered-poles-atr-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-tapered-poles-atr-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-tapered-poles-atr-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-tapered-poles-atr-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-tapered-poles-atr-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-tapered-poles-atrc1-atrc2">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-tapered-poles-atrc1-atrc2</a>

Continued on next page.






# Outdoor Aluminum Poles & Brackets



	Better	Better	Better	Better	Better	Better
	AM6/AM8	SAM8	AMT8	RA61	RAS61	TM6
Pole Desc.	Round Straight	Round Straight	Round Tapered	Round Straight	Round Straight	Round Tapered
Base Desc.	Bottleneck	Bottleneck	Bottleneck	Bottleneck	Bottleneck	Bottleneck
Market Base Name	Dorchester (Valmont)			-	-	-
Height	8', 10', 12', 13', 14', 15', 16', 18', 20'	12', 13', 14', 15', 16', 18', 20', 22', 23'	8', 10', 12', 14', 16', 18', 20'	8', 10', 12', 13', 14', 15', 16', 18', 20'	12', 13', 14', 15', 16', 18', 20', 22', 23'	8', 10', 12', 14', 16', 18', 20'
Diameter	4"	5-9/16"	6-4" Tapered	4"	5-9/16"	6-4" Tapered
Pole Tenon	-	5-9/16"	-	-	-	-
Thickness	0.125", 0.226", 0.318"	0.258"	0.125", 0.250"	0.125", 0.226", 0.318"	0.258"	0.125", 0.188", 0.250"
Base	16", 18" Round	15" Round	18" Round	18" Round	18" Round	16" Round
Bolt Circle	10-1/2", 12-1/2"	12-1/2"	12-1/2"	12-1/2"	12-1/2"	9-1/2"
Optional Bases	-	-	-	TBC1, TBC2	-	-
EPA @ 90 MPH	5.32-30.00	14.78-30.00	9.97-30.00	6.70-30.00	14.78-30.00	7.23-30.00
EPA @ 110 MPH	2.94-20.59	9.71-28.46	6.31-30.00	3.71-20.59	9.71-28.46	4.35-25.98
EPA @ 120 MPH	2.21-17.35	8.07-23.89	5.20-30.00	2.80-17.35	8.07-23.89	3.50-21.93
EPA @ 150 MPH	1.22-11.20	4.94-15.14	3.11-24.24	1.53-11.20	4.94-15.14	1.98-14.11
Options	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Hinged Base (AM6), Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire
Finish	Refer to Finishes on pg. 20					
eCat Page URL	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-small-bottleneck-poles-am6-sm6">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-small-bottleneck-poles-am6-sm6</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-large-bottleneck-poles-sam8-ssm8">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-large-bottleneck-poles-sam8-ssm8</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-medium-bottleneck-poles-am8-amt8-sm8">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-medium-bottleneck-poles-am8-amt8-sm8</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottleneck-poles-r61-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottleneck-poles-r61-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottleneck-poles-ras61-rss61">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottleneck-poles-ras61-rss61</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-tapered-poles-tm6">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-tapered-poles-tm6</a>

Continued on next page.




# Outdoor Aluminum Poles & Brackets



	Better	Better	Better	Better	Better	Better
	R80/R80A	RA804	RA805	RA856	RTA800	RTA61
Pole Desc.	Round Straight	Round Straight	Round Straight	Round Straight	Round Tapered	12-Flute Round Tapered
Base Desc.	Fluted Bottleneck & Bolt Covers or Optional Base Covers	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Bottleneck
Market Base Name	Sacramento (Valmont)					-
Height	8', 10', 12', 14', 15', 16', 18'	8', 10', 12', 13', 14', 15', 16', 18', 20'	12' - 20'	8', 10', 12', 14', 16', 18', 20', 22'	8', 10', 12', 14', 16', 18', 20'	10', 11', 12', 13', 14', 15'
Diameter	4"	4"	5"	5-9/16"	6-4" Tapered	5"
Pole Tenon	-	-	-	-	-	-
Thickness	0.125", 0.167", 0.226"	0.125", 0.226", 0.318"	0.170", 0.219", 0.247"	0.258"	0.125", 0.188", 0.250"	0.125", 0.250"
Base	15-1/2" Round	16-1/2" Round	16-1/2" Round	16-1/2" Round	16-1/2" Round	18" Round
Bolt Circle	12-1/2"	8-1/2"	12-1/2"	12-1/2"	9-1/2"	12-1/2"
Optional Bases	TBC1, TBC2	-	-	-	-	-
EPA @ 90 MPH	3.82-29.69	3.27-18.64	5.86-21.72	11.44-30.00	7.95-30.00	11.14-30.00
EPA @ 110 MPH	1.80-20.17	1.36-12.35	3.41-14.46	7.39-30.00	4.56-26.88	6.99-27.99
EPA @ 120 MPH	1.22-16.98	1.19-10.28	2.72-12.13	6.08-30.00	3.62-22.63	5.69-23.57
EPA @ 150 MPH	1.16-10.94	1.16-6.53	1.45-7.66	3.60-25.12	1.99-14.48	3.24-15.02
Options	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Shorting Cap, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire
Finish	Refer to Finishes on pg. 20					
eCat Page URL	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r80-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r80-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r61-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r61-series</a>

Continued on next page.

# Outdoor Aluminum Poles & Brackets





	Better	Best	Best	Best	Best	Best
	P135A	RA41	RA40	RTA40	RTA500	RTA608
Pole Desc.	12-Flute Round Straight	8-Flute Round Straight	12-Flute Round Straight	12-Flute Round Tapered	12-Flute Round Tapered	12-Flute Round Tapered
Base Desc.	Optional Covers	Fluted Decorative	Fluted Decorative	Fluted Decorative	Fluted Decorative	Fluted Decorative
Market Base Name	N/A	Washington (Valmont and Hanover)				
Height	8', 10', 12', 14', 15', 16', 18', 20'	8', 10', 12', 14', 15', 16', 18', 20'	8', 10', 12', 14', 16', 18', 20'	10', 11', 12', 13', 14'	12', 14', 16', 18'	22', 24', 26', 28'
Diameter	5"	4"	5"	5"	6"	8"
Pole Tenon	-	-	-	-	-	-
Thickness	0.208"	0.167"	0.208"	0.125", 0.188", 0.250"	0.125", 0.250"	0.188", 0.250"
Base	11-1/2" Square	17" Round	17" Round	17" Round	20" Round	24" Round
Bolt Circle	12-1/2"	10-1/2"	10-1/2"	10-1/2"	9-1/2"	11-1/2"
Optional Bases	LBC1, B105, B50	-	-	-	-	LBC1, B105, B50
EPA @ 90 MPH	7.40-27.56	4.52-16.98	8.75-30.00	10.33-30.00	9.59-30.00	14.61-30.00
EPA @ 110 MPH	4.03-18.40	2.13-11.25	5.02-22.78	6.43-22.60	5.49-24.27	8.31-20.88
EPA @ 120 MPH	2.97-15.40	1.39-9.36	3.85-19.15	5.18-18.97	4.20-20.20	6.34-17.04
EPA @ 150 MPH	1.02-9.61	1.33-5.81	1.65-12.11	2.89-11.96	1.90-12.43	2.60-9.67
Options	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire
Finish	Refer to Finishes on pg. 20					
eCat Page URL	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-p135a-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-p135a-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-r40-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-r40-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-r40-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-r40-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-r40-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-r40-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-rta500">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-rta500</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-rta608">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-rta608</a>

Continued on next page.



# Outdoor Aluminum Poles & Brackets



	Best	Best	Best	Best
	RAF805	RTAF800	RTA906	RTA928
Pole Desc.	12-Flute Round Straight	12-Flute Round Tapered	12-Flute Round Tapered	12-Flute Round Tapered
Base Desc.	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck
Market Base Name	Sacramento (Valmont)		-	-
Height	8', 10', 12', 14', 15', 16', 18', 20'	12', 14', 16', 18'	10', 12', 14', 16', 18', 20'	12', 14', 16', 18', 20', 22', 24', 26', 28'
Diameter	5"	6-4" Tapered	6-4" Tapered	8-4" Tapered
Pole Tenon	-	-	-	-
Thickness	0.208"	0.125", 0.250"	0.125", 0.250"	0.125", 0.156", 0.250"
Base	16-1/2" Round	16-1/2" Round	17-1/4" Round	23" Round
Bolt Circle	12-1/2"	9-1/2"	12-1/2"	12-1/2"
Optional Bases	-	-	-	-
EPA @ 90 MPH	7.40-27.56	9.77-30.00	14.11-30.00	12.49-30.00
EPA @ 110 MPH	4.03-18.40	5.55-24.26	9.01-30.00	7.34-30.00
EPA @ 120 MPH	2.97-15.40	4.29-20.20	7.37-30.00	5.67-25.24
EPA @ 150 MPH	1.02-9.61	1.98-12.47	4.20-19.26	2.45-15.95
Options	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire
Finish	Refer to Finishes on pg. 20			
eCat Page URL	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottle-neck-poles-r800-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-r90-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-r90-series</a>	<a href="https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-rta92-series">https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-rta92-series</a>



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.