



LUMEC

by 

Outdoor

Steel Poles & Brackets





Product Selection Guide



	Good	Good	Good	Good	Better	Better
	SPR4	SPR5	SPS4	SPS5	SM6	SM8
Pole Desc.	Round Straight	Round Straight	Square Straight	Square Straight	Round Straight	Round Straight
Base Desc.	Optional Base Covers	Optional Base Covers	Square Base Cover	Square Base Cover	Bottleneck	Bottleneck
Height	8', 10', 12', 14', 15', 16', 18', 20'	14', 15', 16', 18', 20', 22', 25', 30'	8', 10', 12', 14', 15', 16', 18', 20'	15', 18', 20', 25', 30'	8', 10', 12', 14', 15', 16', 18', 20'	8', 10', 12', 14', 15', 16', 18', 20'
Diameter	4"	5"	4"	5"	4"	4"
Thickness	0.120", 0.188", 0.250"	0.150", 0.188", 0.250"	0.120", 0.188", 0.250"	0.120", 0.188", 0.250"	0.120", 0.188", 0.250"	0.120", 0.188", 0.250"
Base	10" Square	12-1/2" Square	10" Square	12-1/2" Square	16" Round	18" Round
Bolt Circle	8-1/2"	12-1/2"	8-1/2"	12-1/2"	10-1/2"	12-1/2"
Optional Bases	LBC1, LBC2, LBC3, LBC4C	LBC1, B105, B50	-	-	-	-
EPA @ 90 MPH	6.43-28.85	11.41-30.00	15.10-30.00	18.85-30.00	8.64-30.00	9.10-30.00
EPA @ 110 MPH	3.50-19.40	7.25-30.00	9.65-30.00	12.47-30.00	5.14-30.00	5.49-30.00
EPA @ 120 MPH	2.56-16.27	5.96-25.56	7.90-30.00	10.38-30.00	4.03-30.00	4.32-30.00
EPA @ 150 MPH	1.36-10.44	3.48-16.47	4.56-30.00	6.47-30.00	2.37-20.32	2.56-22.17
Options	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Hinged Base, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Shorting Cap, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire
Finish	Refer to Finishes on pg. 20					
eCat Page URL	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-round-straight-shaft-poles-apr-spr	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-round-straight-shaft-poles-apr-spr	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-square-straight-shaft-poles-sps	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-square-straight-shaft-poles-sps	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-small-bottleneck-poles-am6-sm6	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-medium-bottleneck-poles-am8-amt8-sm8

Continued on next page.

Outdoor Steel Poles & Brackets



	Better	Better	Best	Best	Best	Best
	SSM8	RS61	RS804	RS805	RS856	R90
Pole Desc.	Round Straight	Round Straight	Round Straight	Round Straight	Round Straight	16-Flute Round Tapered
Base Desc.	Bottleneck	Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck
Height	18', 20', 22', 24', 26', 28'	8', 10', 12', 14', 15', 16', 18', 20'	8', 10', 12', 14', 15', 16', 18', 20'	14', 15', 16', 18', 20', 22', 25', 30'	8', 10', 12', 14', 16', 18', 20', 22'	10', 12', 14', 15', 16', 18', 20'
Diameter	5-9/16"	4"	4"	5"	5-9/16"	6-5/8"
Thickness	0.250"	0.120", 0.188", 0.250"	0.120", 0.188", 0.250"	0.150", 0.188", 0.250"	0.250"	0.120"
Base	18" Round	18" Round	16-1/2" Round	16-1/2" Round	16-1/2" Round	17-1/2" Round
Bolt Circle	12-1/2"	12-1/2"	8-1/2"	12-1/2"	12-1/2"	12-1/2"
Optional Bases	-	-	-	-	-	-
EPA @ 90 MPH	25.36-30.00	5.32-30.00	6.43-28.85	11.41-30.00	11.44-30.00	30.00
EPA @ 110 MPH	17.19-30.00	2.94-20.59	3.50-19.40	7.25-30.00	7.39-30.00	25.20-30.00
EPA @ 120 MPH	14.44-30.00	2.21-17.35	2.56-16.27	5.96-30.00	6.08-30.00	21.14-30.00
EPA @ 150 MPH	9.13-21.20	1.22-11.20	1.36-10.44	3.48-30.00	3.60-25.12	13.66-22.40
Options	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire
Finish	Refer to Finishes on pg. 20					
eCat Page URL	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/contemporary-large-bottleneck-poles-ssm8	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottleneck-poles-r61-series	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottleneck-poles-r800-series	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottleneck-poles-r800-series	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-bottleneck-poles-r800-series	https://www.signify.com/en-us/products/outdoor-luminaires/poles-brackets/urban-poles/traditional-poles-r90-series



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.