

Since
1894

**BEAUTIFUL LIGHT,
BUILT TO PERFORM**

MAZDA



GREAT LIGHT SOLID DESIGN

There's an art to creating a quality lighting scheme that exceeds your customers' expectations - without going over their budget. Now you can master it beautifully with MAZDA's portfolio of LED lamps and luminaires.

QUALITY WHEN IT COUNTS

The MAZDA name has been trusted for quality and reliability since 1894. Our solid lighting solutions are built on decades of experience in lighting. From retail and residential projects to commercial and industrial installations, they have been developed to meet the challenging requirements of a wide range of lighting applications.

We've designed our range using the very latest LED technology, from classic bulbs and elegant candles to hand-working tubes and directional spots. The MAZDA portfolio now also offers

indoor and outdoor luminaires to meet your customer's needs. So you can promise your customers excellent performance and efficiency from their lighting installation, with instant energy savings.

They'll love the light quality too. With a choice of lumens, color temperatures and beam angles, our high quality LED solutions create the perfect ambience for every space. Light that's designed to create a great first impression, with value that lasts.



MASTERING LIGHT SINCE 1894.

MAZDA has been trusted for quality and reliability since 1894. Our solid lighting solutions are built on decades of experience in lighting:

- Engineered for performance
- Up to 35,000 hours reliable lifetime
- Superb light quality
- Save up to 85% energy

CONTENTS

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps





LUMINAIRES

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



INDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

LED Batten

Most popular batten type of 1200mm, non-dimmable, 3000lm, neutral white light and with IP20 rating. Ideal for general lighting and storage areas.



LED Downlights

Energy efficient luminaires with a robust design typically used for general lighting in residential and retail applications. Comes in 6, 1200 and 2000 lumen and in a choice of 3 color temperatures from warm white to cool daylight.



LED High-bay

Nicely designed High-bay luminaire with sturdy die-casting housing and special glass cover with unique textured design to cut glare.



LED Panels

Energy saving square LED panel for general application areas, available in 5 non-dimmable types (1200 and 3200 lumen) and including an office compliant version.



LED Spots

Our LED spots come with a slim design that fits most ceiling types. Available in 4 types, from 200-350 lumen and a choice of 2 color temperatures (warm white and cool white light).



LED Wallmounts

4 types of non-dimmable wallmount luminaires, available in neutral white light, 960-1400 lm, round and oval style. Typical applications include corridors, public entrance areas and staircases. Silver trim and motion sensor included.



LED Waterproof

A robust choice for all industrial applications. Comes in 1700, 3400 and 5400 lumen, neutral white light and with IP65 rating.



INDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

LED BATTEN

A
EEI label

A⁺⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
20,000h

⚠️
non dimmable



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[lm/W]	K								
MAZDA BN007C LED30S/840 PSU L1200	3000	30	100	4000	-20 to +35 °C	IP20	0,9	I	CE	20.000 hrs	911401800480	8710163338040

LED DOWNLIGHTS

A
EEI label

A⁺⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
35,000h

⚠️
non dimmable



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[lm/W]	K								
MZD DN020B LED12/830 16W 220-240V WH	1200	16	75	3000	-20 to +40 °C	IP20 / IK03	0,5	II	CE	35.000hrs	929002219402	3139188163645
MZD DN020B LED12/840 16W 220-240V WH	1200	16	75	4000	-20 to +40 °C	IP20 / IK03	0,5	II	CE	35.000hrs	929002219502	3139188163669
MZD DN020B LED12/865 16W 220-240V WH	1200	16	75	6500	-20 to +40 °C	IP20 / IK03	0,5	II	CE	35.000hrs	929002219602	3139188163683
MZD DN020B LED20/830 24W 220-240V WH	2000	24	83	3000	-20 to +40 °C	IP20 / IK03	0,5	II	CE	35.000hrs	929002219702	3139188163706
MZD DN020B LED20/840 24W 220-240V WH	2000	24	83	4000	-20 to +40 °C	IP20 / IK03	0,5	II	CE	35.000hrs	929002219802	3139188163720
MZD DN020B LED20/865 24W 220-240V WH	2000	24	83	6500	-20 to +40 °C	IP20 / IK03	0,5	II	CE	35.000hrs	929002219902	3139188163744

LED HIGH-BAY

A
EEI label

A⁺⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
35,000h

⚠️
non dimmable



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[lm/W]	K								
MAZDA BY007P LED150S/840 PSU WB	15000	150	100	4000	-20 to +45 °C	IP65/IK06	0,95	I	CE	35.000	911401841582	8719514527829
MAZDA BY007P LED200S/840 PSU WB	20000	200	100	4000	-20 to +45 °C		0,95	I	CE	35.000	911401841682	8719514527836

INDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

A
EEI label

A⁺⁺
EEI label


80
CRI

⚡
220-240 Vac

🕒
35,000h

⚠️
non dimmable

LED PANELS



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[lm/W]	K								
MAZDA RC007B LED32S/840 PSU W60L60 NOC	3200	36	88	4000	-10 to +45 °C	IP20	0,9	II	CE	35.000 hrs	911401801280	8710163340180
MAZDA RC007B LED12S/840 PSU W30L30 NOC	1200	15	88	4000	-10 to +45 °C	IP20	0,9	II	CE	35.000 hrs	911401801380	8710163340197
MAZDA RC007C LED32S/840 PSU W60L60 NOC FR	3200	36	88	4000	-10 to +45 °C	IP20	0,9	II	CE	35.000 hrs	911401800281	8710163364704
MAZDA RC007C LED32S/840 PSU W60L60 OC FR	3200	36	88	4000	-10 to +45 °C	IP20	0,9	II	CE	35.000 hrs	911401800381	8710163364711
MAZDA RC008C LED32S/840 PSU W62L62 NOC	3200	36	88	4000	-10 to +45 °C	IP20	0,9	II	CE	35.000 hrs	911401859581	8719514507401

A
EEI label

A⁺⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
35,000h

⚠️
non dimmable

LED SPOTS



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[lm/W]	K								
MZD SL252 EC RD 070 3W 27K W HV 06	200	3	67	2700	-20 to +40 °C	IP20 / IK03	0,5	II	CE	35.000 hrs	929002222432	3139188164000
MZD SL252 EC RD 070 3W 40K W HV 06	210	3	70	4000	-20 to +40 °C	IP20 / IK03	0,5	II	CE	35.000 hrs	929002222532	3139188164024
MZD SL252 EC RD 070 5W 27K W HV 06	330	5	66	2700	-20 to +40 °C	IP20 / IK03	0,5	II	CE	35.000 hrs	929002222632	3139188164048
MZD SL252 EC RD 070 5W 40K W HV 06	350	5	70	4000	-20 to +40 °C	IP20 / IK03	0,5	II	CE	35.000 hrs	929002222732	3139188164062

INDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

A EEI label A⁺⁺ EEI label 70 CRI 80 CRI ⚡ 220-240 Vac ⌚ 20.000 or 35.000h ⚠ non dimmable

LED WALLMOUNTS



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[lm/W]	K								
MAZDA WL007C LED14S/740 PSU OVL WH	1400	15	90	4000	-20 to +40 °C	IP65 / IK06	0,9	II	CE	20.000 hrs	911401800880	8710163338088
MAZDA WL007C LED13S/740 PSU RND MDU WH	1300	15	85	4000	-20 to +40 °C	IP54 / IK06	0,9	II	CE	20.000 hrs	911401800780	8710163338071
MAZDA WL007C LED10S/840 PSU RND WH G2	960	12	80	4000	-30 to +35 °C	IP54 / IK06	0,5	II	CE	35.000 hrs	911401800081	871016336456899
MAZDA WL007C LED16S/840 PSU RND WH G2	1600	20	80	4000	-30 to +35 °C	IP54 / IK06	0,5	II	CE	35.000 hrs	911401800181	871016336457599

A EEI label A⁺⁺ EEI label 80 CRI ⚡ 220-240 Vac ⌚ 35,000h ⚠ non dimmable

LED WATERPROOF



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[lm/W]	K								
MAZDA WT007C LED17S/840 PSU L600	1700	17	90	4000	-20 to +35 °C	IP65 / IK06	0,9	II	CE	35.000 hrs	911401800980	8710163338774
MAZDA WT007C LED34S/840 PSU L1200	3400	34	90	4000	-20 to +35 °C	IP65 / IK06	0,9	II	CE	35.000 hrs	911401800580	8710163338057
MAZDA WT007C LED54S/840 PSU L1500	5400	54	90	4000	-20 to +35 °C	IP65 / IK06	0,9	II	CE	35.000 hrs	911401800680	8710163338064

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



OUTDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

LED Floodlight

Highly versatile range of robust floodlights designed to meet diverse application requirements, including building facades, parking spaces and indoor industrial workspaces. Available from 800-17000 lumen in warm white, cool white and cool daylight and with IP65 rating.




OUTDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

LED FLOODLIGHTS



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[lm/W]	K								
MAZDA BVP007 10W 3000k	800	10	80	3000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401737462	8710163337401
MAZDA BVP007 10W 4000k	850	10	85	4000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401737432	8710163337371
MAZDA BVP007 10W 6500k	850	10	85	6500	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401815581	8710163367866
MAZDA BVP007 20W 3000k	1600	20	80	3000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401737472	8710163337418
MAZDA BVP007 20W 4000k	1700	20	85	4000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401737442	8710163337388
MAZDA BVP007 20W 4000k MDU	1700	20	85	4000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401741582	8710163338200
MAZDA BVP007 20W 6500k	1700	20	85	6500	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401815681	8710163367873
MAZDA BVP007 30W 3000k	2400	30	80	3000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401741992	8710163338842
MAZDA BVP007 30W 4000k	2550	30	85	4000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401741982	8710163338835
MAZDA BVP007 30W 6500k	2550	30	85	6500	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401816081	8710163367965
MAZDA BVP007 50W 3000k	4000	50	80	3000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401737482	8710163337425
MAZDA BVP007 50W 4000k	4250	50	85	4000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401737452	8710163337395
MAZDA BVP007 50W 4000k MDU	4250	50	85	4000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401741592	8710163338217
MAZDA BVP007 50W 6500k	4250	50	85	6500	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401815781	8710163367880
MAZDA BVP007 100W 4000k	8500	100	85	4000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401741562	8710163338187
MAZDA BVP007 100W 6500k	8500	100	85	6500	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401815881	8710163367897
MAZDA BVP007 200W 4000k	17000	200	85	4000	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401741572	8710163338194
MAZDA BVP007 200W 6500k	17000	200	85	6500	-40 to +50 °C	IP65 / IK06	0,9	I	CE	35.000 hrs	911401815981	8710163367903



LAMPS

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



LED BULBS

FOR INSTANT ENERGY SAVINGS

LED Bulbs

An extensive range of non-dimmable LED bulbs that provide instant brightness in a classic design. Available with E27 fitting, 470-1521 lumen, in clear and frosted version and in 3 color temperatures from warm white to cool daylight.



A60 frosted



A60 clear



A67 frosted



A70 clear

LED BULBS

FOR INSTANT ENERGY SAVINGS

80
CRI

⚡
220-240 Vac

🕒
15,000h

⚠️
non dimmable



Product type	Lumen output	Energy consumption	Switch Cycle (times)	Efficiency	Color temperature	Operating temperature range	Power factor	Certifications	Dimensions	12NC	EAN1
	lm	W		[lm/W]	K				mm		
MZD LED 40W E27 840 A60 ND 1CT/6	470	5	15000	94	4000	-20 to +45 °C	0.5	CE	60 x 105	929002060332	3139188161436
MZD LED 40W E27 827 A60 ND 1CT/6	470	5	15000	94	2700	-20 to +45 °C	0.5	CE	60 x 105	929002061732	3139188161412
MZD LED 40W A60 E27 865 FR ND 1CT/6	470	5	15000	94	6500	-20 to +45 °C	0.5	CE	60 x 105	929002060732	3139188162266
MZD LED 60W A60 E27 827 FR ND 1CT/6	806	9	15000	89	2700	-20 to +45 °C	0.51	CE	60 x 105	929001913132	3139188161450
MZD LED 60W A60 B22 WW FR ND RF 1BC 1CT/6	806	9	15000	89	2700	-20 to +45 °C	0.51	CE	60 x 103	929001913532	3139188162969
MZD LED 60W A60 E27 CDL FR ND 1CT/6	806	9	15000	89	6500	-20 to +45 °C	0.51	CE	60 x 105	929001913432	3139188162327
MZD LED 60W A60 E27 840 FR ND 1CT/6	806	9	15000	89	4000	-20 to +45 °C	0.51	CE	60 x 105	929001913332	3139188161474
MZD LED 60W A60 E27 840 FR ND 2CT/5*	806	9	15000	89	4000	-20 to +45 °C	0,51	CE	60 x 105	929001913333	3139188163522
MZD LED 75W A60 E27 827 FR ND 1CT/6	1055	11	15000	100	2700	-20 to +45 °C	0.5	CE	60 x 120	929001365532	3139188161498
MZD LED 75W A60 E27 840 FR ND 1CT/6	1055	10	15000	105	4000	-20 to +45 °C	0.5	CE	60 x 120	929001365632	3139188161511
MZD LED 75W A60 E27 865 FR ND 1CT/6	1055	10	15000	105	6500	-20 to +45 °C	0,5	CE	60 x 120	929001359132	3139188162488
MZD LED 100W E27 827 A67 FR ND 1CT/6	1521	14	15000	108	2700	-20 to +45 °C	0.5	CE	65 x 120	929001252932	3139188161535
MZD LED 100W A60 E27 CDL FR ND 1CT/6	1521	14	15000	108	6500	-20 to +45 °C	0,5	CE	67 x 120	929001359232	3139188162501

* Multipack

LED BULBS

FOR INSTANT ENERGY SAVINGS

80
CRI

⚡
220-240 Vac

🕒
15,000h

⚠️
non dimmable



Product type	Lumen output	Energy consumption	Switch Cycle (times)	Efficiency	Color temperature	Operating temperature range	Power factor	Certifications	Dimensions	12NC	EAN1
	lm	W		[lm/W]	K				mm		
MZD LEDCLA 40W A60 E27 827 CL ND 1CT/10	470	5	20000	109	2700	-20 to +45 °C	0.52	CE	60 x 104	929001890032	3139188163768
MZD LEDCLA 40W A60 E27 840 CL ND 1CT/10	470	5	20000	109	4000	-20 to +45 °C	0.52	CE	60 x 104	929002214432	3139188163782
MZD LEDCLA 60W A60 E27 827 CL ND 1CT/10	806	7	20000	115	2700	-20 to +45 °C	0.52	CE	60 x 104	929001387332	3139188163805
MZD LEDCLA 60W A60 E27 840 CL ND 1CT/10	806	7	20000	115	4000	-20 to +45 °C	0.52	CE	60 x 104	929002062532	3139188163829
MZD LEDCLA 75W A60 E27 827 CL ND 1CT/10	1055	8	20000	131	2700	-20 to +45 °C	0.56	CE	60 x 104	929002061032	3139188163843
MZD LEDCLA 75W A60 E27 840 CL ND 1CT/10	1055	8	20000	131	4000	-20 to +45 °C	0.56	CE	60 x 104	929002060432	3139188163867
MZD LEDCLA 100W A70 E27 827 CL ND 1CT/10	1521	11	20000	138	2700	-20 to +45 °C	0.58	CE	70 x 126	929002062132	3139188164086
MZD LEDCLA 100W A70 E27 840 CL ND 1CT/10	1521	14	15000	138	4000	-20 to +45 °C	0.58	CE	70 x 126	929002214132	3139188164208

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



LED CANDLE & LUSTRE

FOR INSTANT ENERGY SAVINGS

LED Candles & Lustres

Elegant energy-saving lamps for a wide range of applications. An extensive range of non-dimmable candles and lustres, available in 250, 470 and 806 lumen, in clear and frosted version and in 3 color temperatures from warm white to cool daylight.



B35 frosted



P45 frosted



B35 frosted



B35 clear



B35 frosted



B35 clear

LED CANDLE & LUSTRE

DESIGNED FOR ATMOSPHERE

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
15,000h

⚠️
non dimmable



Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Dimensions	12NC	EAN1
		W		K		lm	[lm/W]					
MZD LED 25W E14 827 B35 FR ND 1CT/10	B35	4	15000	2700	-20 to +45 °C	250	78	0,4	CE	35x103	929001253032	3139188161351
MZD LED 25W B35 E14 CW FR ND 1CT/10	B35	3	15000	4000	-20 to +45 °C	250	83	0,4	CE	35x103	929001359432	3139188162549
MZD LED 25W B35 E14 CDL FR ND 1CT/10	B35	3	15000	6500	-20 to +45 °C	250	83	0,4	CE	35x103	929001388832	3139188162563
MZD LED 25W E27 827 P45 FR ND 1CT/10	P45	4	15000	2700	-20 to +45 °C	250	78	0,4	CE	45x79	929001253332	3139188161399
MZD LED 25W E14 827 P45 FR ND 1CT/10	P45	4	15000	2700	-20 to +45 °C	250	78	0,4	CE	45x84	929001253232	3139188161375
MZD LED 25W P45 E14 CW FR ND 1CT/10	P45	4	15000	4000	-20 to +45 °C	250	95	0,4	CE	45x84	929001263832	3139188162822
MZD LED 25W P45 E14 CDL FR ND 1CT/10	P45	3	15000	6500	-20 to +45 °C	250	83	0,4	CE	45x84	929001388932	3139188162587
MZD LED 25W B35 E14 827 CL ND 1CT/10	B35	2	20000	2700	-20 to +45 °C	250	125	0,5	CE	35x97	929001238332	3139188163942
MZD LED 25W B35 E14 840 CL ND 1CT/10	B35	2	20000	4000	-20 to +45 °C	250	125	0,5	CE	35x97	929002215232	3139188164123
MZD LEDCLA 25W P45 E14 827 CL ND 1CT/10	P45	2	20000	2700	-20 to +45 °C	250	125	0,5	CE	45x80	929001238632	3139188163881
MZD LED 25W B35 E14 840 CL ND 1CT/10	P45	2	20000	4000	-20 to +45 °C	250	125	0,5	CE	45x80	929002215132	3139188164109

LED CANDLE & LUSTRE

DESIGNED FOR ATMOSPHERE

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
15,000h

⚠️
non dimmable



Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Dimensions	12NC	EAN1
		W		K		lm	[lm/W]					
MZD LED 40W B35 E14 WW FR ND 1CT/10	B35	6	15000	2700	-20C-45C	470	85	0,5	CE	35x103	929001253632	3139188162723
MZD LED 40W B35 E14 CW FR ND 1CT/10	B35	5	15000	4000	-20C-45C	470	104	0,5	CE	35x103	929001263732	3139188162884
MZD LED 40W B35 E14 CDL FR ND 1CT/10	B35	5	15000	6500	-20C-45C	470	104	0,5	CE	35x103	929001389032	3139188162686
MZD LED 40W P45 E27 WW FR ND 1CT/10	P45	6	15000	2700	-20C-45C	470	85	0,5	CE	45x79	929001253832	3139188162808
MZD LED 40W P45 E14 WW FR ND 1CT/10	P45	6	15000	2700	-20C-45C	470	85	0,5	CE	45x84	929001253732	3139188162785
MZD LED 40W P45 E27 CW FR ND 1CT/10	P45	6	15000	4000	-20C-45C	470	85	0,5	CE	45x79	929001264032	3139188162860
MZD LED 40W P45 E14 CW FR ND 1CT/10	P45	6	15000	4000	-20C-45C	470	85	0,5	CE	45x84	929001263932	3139188162846
MZD LED 40W P45 E27 CDL FR ND 1CT/10	P45	5	15000	6500	-20C-45C	470	104	0,5	CE	45x79	929001389232	3139188162624
MZD LED 40W P45 E14 CDL FR ND 1CT/10	P45	5	15000	6500	-20C-45C	470	104	0,5	CE	45x84	929001389132	3139188162600
MZD LEDCLA 40W B35 E14 827 CL ND 1CT/10	B35	5	20000	2700	-20C-45C	470	109	0,5	CE	35x97	929001889732	3139188163966
MZD LEDCLA 40W B35 E14 840 CL ND 1CT/10	B35	5	20000	4000	-20C-45C	470	109	0,5	CE	35x97	929002214932	3139188163980
MZD LEDCLA 40W P45 E14 827 CL ND 1CT/10	P45	5	20000	2700	-20C-45C	470	109	0,5	CE	45x80	929001890432	3139188163904
MZD LED 40W P45 E14 840 CL ND 1CT/10	P45	5	20000	4000	-20C-45C	470	109	0,5	CE	45x80	929002214632	3139188163928



Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Dimensions	12NC	EAN1
		W		K		lm	[lm/W]					
MZD LED 60W B35 E14 827 FR ND 1CT/10	B35	8	15000	2700	-20 to +45 °C	806	101	0,5	CE	39x114	929001907632	3139188163201
MZD LED 60W B35 E14 840 FR ND 1CT/10 MZD	B35	8	15000	4000	-20 to +45 °C	806	101	0,5	CE	39x114	929001907732	3139188163225
MZD LED 60W B35 E14 865 FR ND 1CT/10	B35	8	15000	6500	-20 to +45 °C	806	101	0,5	CE	39x114	929001907832	3139188163249
MZD LEDCLA 60W B35 E14 827 CL ND 1CT/10	B35	6	20000	2700	-20 to +45 °C	806	134	0,5	CE	35x97	929002215332	3139188164147
MZD LED 60W B35 E14 840 CL ND 1CT/10	B35	6	20000	4000	-20 to +45 °C	806	134	0,5	CE	35x97	929002215432	3139188164161

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



LED SPOTS

FOR INSTANT ENERGY SAVINGS

LED Spots

Our LED Spots are ideal for creating lighting accents. Come in 3 versions: GU10 kit, GU10 and GU5.3, with various lumen packages, color temperatures and beam options.



GU10 kit



GU5.3



GU10

LED SPOTS

SPOTLIGHT ON STYLE

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
15,000h

⚠️
non dimmable



Product type	Lamp type	Energy consumption	beam angle	Switch Cycle (times)	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Dimensions	12NC	EAN1
		W			K		lm	[lm/W]					
MZD LEDspot50W GU10Kit_R 827 36D 1CT/10	PAR16	4,7	36	50000	2700	-20 to +45 °C	400	73	0,4	CE	91x91	929002040532	3139188163423
MZD LEDspot50W GU10Kit_R 840 36D 1CT/10	PAR16	4,7	36	50000	4000	-20 to +45 °C	430	80	0,4	CE	91x91	929002040732	3139188163447
MZD LEDspot50W GU10Kit_S 827 36D 1CT/10	PAR16	4,7	36	50000	2700	-20 to +45 °C	400	73	0,4	CE	91x91	929002040632	3139188163461
MZD LEDspot50W GU10Kit_S 840 36D 1CT/10	PAR16	4,7	36	50000	4000	-20 to +45 °C	430	80	0,4	CE	91x91	929002040832	3139188163485
MZD LED 50W GU10 827 36D ND 1CT/10	PAR16	5	36	15000	2700	-20 to +45 °C	380	73	0,4	CE	50x54	929001250432	3139188161252
MZD LED 50W GU10 840 36D ND 1CT/10	PAR16	5	36	15000	4000	-20 to +45 °C	420	80	0,4	CE	50x54	929001247032	3139188162662
MZD LED 50W GU10 865 36D ND 1CT/10	PAR16	5	36	15000	6500	-20 to +45 °C	420	80	0,4	CE	50x54	929001259132	3139188162648
MZD LED 50W GU10 WH 60D ND 1CT/10	PAR16	5	36	15000	3000	-20 to +45 °C	400	73	0,4	CE	50x55	929001912232	3139188161276
MZD LED 50W GU10 CW 60D ND 1CT/10	PAR16	5	36	15000	4000	-20 to +45 °C	430	76	0,4	CE	50x55	929001912332	3139188161290
MZD LED 65W GU10 827 36D ND 1CT/10	PAR16	6	36	15000	2700	-20 to +45 °C	460	77	0,5	CE	50x56	929001371132	3139188161634
MZD LED 65W GU10 840 36D ND 1CT/10	PAR16	6	36	15000	4000	-20 to +45 °C	460	84	0,5	CE	50x56	929001371232	3139188161658
MZD LED 500lm GU10 827 120D ND 1CT/10	PAR16	6	120	15000	2700	-20 to +45 °C	500	90	0,5	CE	50x56	929001372032	3139188161719
MZD LED 500lm GU10 840 120D ND 1CT/10	PAR16	5	120	15000	4000	-20 to +45 °C	500	100	0,5	CE	50x58	929001358632	3139188161696
MZD LED 500lm GU10 865 120D ND 1CT/10	PAR16	5	120	15000	6500	-20 to +45 °C	500	100	0,5	CE	50x58	929001372132	3139188161733
MZD LED 720lm GU10 830 120D ND 1CT/10	PAR16	8	120	15000	3000	-20 to +45 °C	720	96	0,5	CE	50x58	929002093332	3139188163584
MZD LED 720lm GU10 840 120D ND 1CT/10	PAR16	8	120	15000	4000	-20 to +45 °C	720	96	0,5	CE	50x58	929002093432	3139188163607
MZD LED 720lm GU10 865 120D ND 1CT/10	PAR16	8	120	15000	6500	-20 to +45 °C	720	96	0,5	CE	50x58	929002093532	3139188163621

LED SPOTS

SPOTLIGHT ON STYLE

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
15,000h

⚠️
non dimmable



Product type	Lamp type	Energy consumption	beam angle	Switch Cycle (times)	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Dimensions	12NC	EAN1
		W			K		lm	[lm/W]					
MZD LED 50W GU5.3 827 12V 36D ND 1CT/10	MR16	8	36	15000	2700	-20 to +45 °C	660	82	0,5	CE	50x44	929001912632	3139188163287
MZD LED 50W GU5.3 840 12V 36D ND 1CT/10	MR16	8	36	15000	4000	-20 to +45 °C	660	82	0,5	CE	50x44	929001912732	3139188163263
MZD LED 50W GU5.3 830 12V 60D ND 1CT/10	MR16	8	36	15000	3000	-20 to +45 °C	660	82	0,5	CE	50x44	929001912432	3139188161313
MZD LED 50W GU5.3 840 12V 60D ND 1CT/10	MR16	8	36	15000	4000	-20 to +45 °C	660	82	0,5	CE	50x44	929001912532	3139188161337

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



LED TUBES

FOR INSTANT ENERGY SAVINGS

LED Tubes

Our LED tubes and PLC lamps provide high quality light to illuminate any space, saving energy up to 55%. Range consists of T8 in 600, 1200, 1500mm and PLC replacements in a choice of 2 color temperatures (cool daylight and cool white).



T8 Tube



PLC

LED TUBES

FOR INSTANT ENERGY SAVINGS

T8 TUBE

A⁺
EEI label

80
CRI


220-240 Vac


25,000h


50,000x


non dimmable



Product type	Lamp type	Energy consumption	beam angle	Switch Cycle (times)	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Dimensions	12NC	EAN1
		W			K		lm	[lm/W]					
MZD LEDtube 600mm 8W 840	T8	8	/	50000	4000	-20 to +45 °C	800	100	>0.9	CE	604h / 27,80ø	929001855632	8718696717455
MZD LEDtube 600mm 8W 865	T8	8	/	50000	6500	-20 to +45 °C	800	100	>0.9	CE	604h / 27,80ø	929001855732	8718696717479
MZD LEDtube 1200mm 14.5W 840	T8	14,5	/	50000	4000	-20 to +45 °C	1600	110	>0.9	CE	1213,60h / 27,80ø	929001855832	8718696717417
MZD LEDtube 1200mm 14.5W 865	T8	14,5	/	50000	6500	-20 to +45 °C	1600	110	>0.9	CE	1213,60h / 27,80ø	929001855932	8718696717431
MZD LEDtube 1500mm 20W 840	T8	20	/	50000	4000	-20 to +45 °C	2200	110	>0.9	CE	1514,20h / 27,80ø	929001855432	8718696717370
MZD LEDtube 1500mm 20W 865	T8	20	/	50000	6500	-20 to +45 °C	2200	110	>0.9	CE	1514,20h / 27,80ø	929001855532	8718696717394

PLC LED LAMP

A⁺
EEI label

80
CRI


220-240 Vac


25,000h


50,000x


non dimmable



Product type	Lamp type	Energy consumption	beam angle	Switch Cycle (times)	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Dimensions	12NC	EAN1
		W			K		lm	[lm/W]					
MZD LED PLC 7.5W 840 2P G24d 1CT/10 PLC 7.5 70	PLC	7,5	240	50000	4000	-20 to +45 °C	806	107	>0.5	CE	115h / 37,20ø	929001879032	3139188162983
MZD LED PLC 7.5W 865 2P G24d 1CT/10	PLC	7,5	240	50000	6500	-20 to +45 °C	806	107	>0.5	CE	115h / 37,20ø	929001879132	3139188163003
MZD LED PLC 9W 840 2P G24d 1CT/10	PLC	9	240	50000	6500	-20 to +45 °C	800	100	>0.9	CE	115h / 37,20ø	929001855732	929001879332
MZD LED PLC 9W 865 2P G24d 1CT/10	PLC	9	240	50000	6500	-20 to +45 °C	1050	116	>0.5	CE	115h / 37,20ø	929001879432	3139188163041

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



LED HIGH-BAY LAMPS

FOR INSTANT ENERGY SAVINGS

LED High-bay

Quick and easy solution to replace conventional HID/CFLi lamps in industrial applications for immediate energy savings.



LED HIGH-BAY LAMPS

FOR INSTANT ENERGY SAVINGS

LED HIGH_BAY LAMPS

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
25,000h

ON
OFF
50,000x

⚠️
non dimmable



Product type	Lamp type	Energy consumption	beam angle	Switch Cycle (times)	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Input current	Frequency	Dimensions	12NC	EAN1
		W			K		lm	[lm/W]							
MZD LED 20W E27 830 HB G3 1CT/6	T shape	20	150	50000	3000	-20C-45 °C	2600	130	0,5	CE	170	50/60	139h / 80ø	929002453332	8710163540832
MZD LED 20W E27 840 HB G3 1CT/6	T shape	20	150	50000	4000	-20C-45 °C	2700	135	0,5	CE	170	50/60	139h / 80ø	929002453432	8710163540856
MZD LED 35W E27 830 HB G3 1CT/6	T shape	35	180	50000	3000	-20C-45 °C	4800	137	0,9	CE	178	50/60	193h / 118ø	929002453532	8710163540870
MZD LED 35W E27 840 HB G3 1CT/6	T shape	35	180	50000	4000	-20C-45 °C	5000	142	0,9	CE	178	50/60	193h / 118ø	929002453632	8710163540894

MAZDA | I.B.R.S. / C.C.R.I. Numéro 10461 | 5600 VB Eindhoven, the Netherlands | WWW.MAZDALIGHTING.COM

© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

All trademarks are owned by Signify Holding or their respective owners.

