

# LED SPOTS GU10

## 230V & 12V

### LAMPES



15 000h



Non gradable



Garantie



GU10

Désignation	Flux	Conso.	Efficacité Lumineuse	Température de couleur	Ouverture	Dimensions	Classe énerg.	Code
	lm	W	Lm/W	K		mm		
LED spots GU10 230V								
<b>MZD LED 50W GU10 827 36D ND</b>	380	4.7	80	2700	36	50x56		54149500
<b>MZD LED 50W GU10 840 36D ND</b>	440	4.7	93	4000	36	50x56		54147100
<b>MZD LED 65W GU10 827 36D ND</b>	460	4.9	93	2700	36	50x56		54187700
<b>MZD LED 65W GU10 840 36D ND</b>	460	4.9	93	4000	36	50x56		16165800
LED spots GU10 12V								
<b>MZD LED 50W GU5.3 827 12V 36D ND</b>	621	6.5	95	2700	36	50x45		54071900