



MAZDA LED Recessed Spot
RS25 | Mounting instruction



Model Name	Lum. Power	Total Lumen	MBCP	Beam Angle	CCT	CRI	Vol/Freq	Classification	
9290022560	4.8W	370lm	1850	24°	2700K	90	220-240V ~ 50/60Hz	Class II	0.105
9290022561	4.8W	410lm	2050	24°	4000K	90	220-240V ~ 50/60Hz	Class II	0.105
9290022562	4.8W	370lm	810	36°	2700K	90	220-240V ~ 50/60Hz	Class II	0.105
9290022563	4.8W	410lm	900	36°	4000K	90	220-240V ~ 50/60Hz	Class II	0.105
9290022564	6.8W	550lm	2260	24°	2700K	90	220-240V ~ 50/60Hz	Class II	0.137
9290022565	6.8W	600lm	2460	24°	4000K	90	220-240V ~ 50/60Hz	Class II	0.137
9290022566	6.8W	550lm	1400	36°	2700K	90	220-240V ~ 50/60Hz	Class II	0.137
9290022567	6.8W	600lm	1530	36°	4000K	90	220-240V ~ 50/60Hz	Class II	0.137
9290022568	8.1W	670lm	2680	24°	2700K	90	220-240V ~ 50/60Hz	Class II	0.17
9290022569	8.1W	770lm	3080	24°	4000K	90	220-240V ~ 50/60Hz	Class II	0.17
9290022570	8.1W	670lm	1810	36°	2700K	90	220-240V ~ 50/60Hz	Class II	0.17
9290022571	8.1W	770lm	1990	36°	4000K	90	220-240V ~ 50/60Hz	Class II	0.17

Dimensions


Unit : mm

Model Name	A	B	C	D
9290022540	0.65	41.5	36.5	51.5
9290022541	0.65	41.5	36.5	51.5
9290022543	0.65	41.5	36.5	51.5
9290022544	0.90	38	36.5	72
9290022545	0.90	38	56.5	72
9290022546	0.90	38	56.5	72
9290022547	0.90	38	56.5	72
9290022548	0.110	35	75	92
9290022549	0.110	35	75	92
9290022570	0.110	35	75	92
9290022571	0.110	35	75	92


(4.8W)

(5.8W)

(8.1W)




Installation




Unit: mm

Model Name	C(mm)	X(mm)	Y(mm)	Z(mm)	D(mm)
929002560	± 0.55mm	50	0.8-20	50	100
929002561	± 0.55mm	50	0.8-20	50	100
929002562	± 0.55mm	50	0.8-20	50	100
929002563	± 0.55mm	50	0.8-20	50	100
929002564	± 0.75mm	50	0.8-20	50	100
929002565	± 0.75mm	50	0.8-20	50	100
929002566	± 0.75mm	50	0.8-20	50	100
929002567	± 0.75mm	50	0.8-20	50	100
929002568	± 0.95mm	50	0.8-20	50	100
929002569	± 0.95mm	50	0.8-20	50	100
929002570	± 0.95mm	50	0.8-20	50	100
929002571	± 0.95mm	50	0.8-20	50	100



 This marking indicates that this product should not be disposed with other household wastes throughout the EU.

To prevent possible harm to the environment or human health from uncontrolled waste disposal, recycle it responsibly to promote the sustainable reuse of material resources. To return your used device, please use the return and collection systems or contact the retailer where the product was purchased. They can take this product for environmental safe recycling.



	9290022560 9290022561 9290022562 9290022563	9290022564 9290022565 9290022566 9290022567	9290022568 9290022569 9290022570 9290022571
Inom(Run current) (mA)	45	62	75
Ipeak (A)	4.1	6.2	5.4
Tref (ms)	0.175	0.24	0.21
AC Leakage Current (mA)	<0.7	<0.7	<0.7
MCB (Type B 16A, pcs)	186	85	98
MCB (Type C 16A, pcs)	310	142	164



1. Please read this manual before you start to install the luminaire.
 2. The luminaire is complied with IEC60598-1, IEC60598-2-2.
 3. The luminaire shall be installed by a qualified electrician according to specified step, and wired in accordance with the latest IEE electrical regulations or the national requirements.
 4. **TURN OFF** the power during installation or maintenance to avoid electrical shock.
- Luminaire must not be used or stored in corrosive environment where hazardous materials such as Sulphur, Chlorine, Phthalates, etc. are present.

DISCLAIMER:

Please note that the original Artwork was not built by SGS. SGS only made change on specific content as listed in below. Therefore, SGS does not hold any responsibility for other content in this file.
If you have any questions regarding the artwork, please contact with Philips Lighting PCC accordingly.

Author/作者	Date/日期	Revision description/更改描述
Jane	2019/12/13	follow "P0028002-C 说明书.eml" to amend, Add 12NC
Jane	2019/12/31	refer to 3241 655 95492 (5940623-1)to update the logo, check in DF

Document Info	Code 12NC:	Designer: SH SGS	Basic Info	Duplexbox: 324165607721	Change Info	Author	Date	Change number	Revision description
	324165607721	Design date: 2019-12-31		EANI number: N/A		SH SGS	2019/12/31		
	Description:			Die-Cut: N/A					
				Surface treatment: N/A					
				CRC: CRC000					

**Acrobat PDF
View Setting**
确保PDF显示正确，请按
以下设定叠印预览：

Step 1

Acrobat Pro DC File Edit

About Adobe Acrobat Pro DC

About Adobe Plug-Ins...

Preferences...

Step 2









Categories:

- Commenting
- Documents
- Full Screen
- General
- Page Display**

Step 3

☒ Use logical page numbers

Use Overprint Preview: Always

SIGNIFY			
Brand	MZD		
Product Family	LUMMINAIRES		
Shape			
Wattage			
Template Ref.	N/A		
SGS number	5945770		
21-NC.NBR	324165607721		
Masterdrawing	N/A		
CRC Ref.			
Barcode No.	N/A		
Operator(s)	janzexheng		
VERSION No.	v2		
Date in	20171110		
Date amended	20191231		
			
Black	dicut		
			
Date Check			
<input type="checkbox"/> Check briefing Traffic			
Artwork document			
<input type="checkbox"/> Legend	<input type="checkbox"/> Number of color		
<input type="checkbox"/> 12NC	<input type="checkbox"/> Trapping/Bleed		
<input type="checkbox"/> Barcode	<input type="checkbox"/> Images hires		
<input type="checkbox"/> Dicut	<input type="checkbox"/> jobsizes		
Approval			
<input type="checkbox"/> QC Lithographer <u>SGS Shanghai Production</u>			
<input type="checkbox"/> Product Manager <u>allen.lai@signify.com</u>			
<input type="checkbox"/> Traffic Manager <u>Micky He</u>			