

Please read these instructions carefully before installing this product.

Suggest you keep these instructions in a safe places for future reference.


The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.

The external flexible cable or cord of this luminaire cannot be replaced; if the cord is damaged, the luminaire shall be destroyed.


IF IN DOUBT, CONSULT A QUALIFIED ELECTRICIAN.

| Description | CCT (K) | P (W) | Dimensions in mm | | | |
|---------------------------------|---------|-------|------------------|----|-----|------|
| | | | D | H1 | H | |
| MAZDA BY007P LED150S/840 PSU WB | 4000 | 150 | 270 | 45 | 100 | 1.65 |
| MAZDA BY007P LED200S/840 PSU WB | | 200 | 320 | 50 | 102 | 2.45 |

Dimensions



Inrush current



| | 150W | 200W |
|----------------------------|------------------------------|-------|
| Electrical characteristics | | |
| I _{max} (A) | 3.52 | 3.28 |
| T _{ref} (μs) | 25.4 | 26.26 |
| MCB | Maximum number of luminaires | |
| B-16A | 13 | 10 |
| C-16A | 15 | 11 |

