



CoreLine Panel

RCI32V G6 3I_36_43S/840 PSU W60L60 OC ELB

CoreLine Panel G6 - All-in, 23.4 / 27.4/ 32.4 W, Ra80, Neutral white 4000K, non-dimmable power supply, dimensions 600x600 lay-in, Office compliant optic, basic emergency

Product data

General Information

Luminous flux (system)	3100/ 3600/ 4300 lm
Emergency output	310/ 304 lm
Luminaire efficacy	132/ 131/ 132 lm/W
Luminous flux tolerance	+/-10%
Light source colour	4000K [neutral white]
Init. Colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM≤3
Unified glare (UGR)	19 [office compliant]
Beam angle	90°
Installation	VPC [Recessed]
Connection type	5pole connection
Emergency type	ELB3 [Basic 3h emergency]
Battery type	LiFeP04
Ambient temperature range	0 to +35 °C

Controls and Dimming

Driver	Non-Dimmable
Dimming	No

Mechanical and housing

Housing material	Steel
Colour	White RAL 9003
IP rating	20
Dimensions (L x W x H)	595 x 295 x 63 mm
Weight	-

Operating and Electrical

Mains supply	230 – 240V / 50-60Hz
Power consumption	23.4/ 27.4/ 32.4 W
Power tolerance	+/-10%
Safety class	II

Light technical

Flickering	I
Stroboscopic effect	0.4

Product data

Order code	821350000074
Product name	RCI32V G6 3I_36_43S/840 PSU W60L60

Dimensions

