



# CoreLine Waterproof – the clear choice for LED

## CoreLine Waterproof

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch. Also available as an Interact Ready wireless CoreLine waterproof luminaire that works with Interact Pro lighting software and Interact Ready devices to provide a connected lighting system for SMEs

### Benefits

- Up to 64% energy savings compared with TL-D
- Reliable LED technology – maintenance-free installation and a long lifetime
- Direct replacement for conventional waterproof luminaires in terms of light performance, installation flexibility and length

### Features

- Can be used to replace traditional waterproof luminaires ranging from 18 to 58 W TL-D
- Wide-beam light distribution
- Diffuser with optical element ensures visual comfort
- Ceiling-mounted bracket and suspension hooks included
- Vandal-proof by additional mounting bracket
- Optional external connector version for easier installation (WEC)
- Optional 3 hour emergency versions available

# CoreLine Waterproof

## Application

- Underground Parking garages
- Warehouses
- General lighting
- Under canopy areas

## Warnings and Safety

- UV radiation will damage the material over time, resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

## Versions



CoreLine waterproof All in L1500






CoreLine waterproof All in L1200



CoreLine Waterproof WT120C G2 PCU -

## Dimensional drawing



CoreLine Waterproof


Product details



CoreLine waterproof All in L1500



CoreLine Waterproof WT120C G2  
PCU-7DPP



CoreLine waterproof All in,  
WT120C G2, easy lumen switch



CoreLine Waterproof WT120C G2  
PCU-3DPP



CoreLine Waterproof WT120C G2  
PCU-10DPP



CoreLine Waterproof WT120C G2  
PCU-9DPP



CoreLine Waterproof WT120C G2  
PCU-12DPP




CoreLine waterproof G2 (WT120C  
G2),MDU, Motion Detection Unit




CoreLine waterproof All in L1500

CoreLine Waterproof

Product details




CoreLine Waterproof WT120C G2  
PCU-2DPP



CoreLine Waterproof WT120C G2  
PCU-13DPP



CoreLine Waterproof WT120C G2  
PCU-8DPP



CoreLine waterproof G2 (WT120C  
G2),MDU, Motion Detection Unit



CoreLine Waterproof WT120C G2  
PCU-11DPP



CoreLine waterproof G2 (WT120C  
G2),Emergency lighting, TrustSight

## General Information

CE mark	CE mark
Driver included	Yes
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s
Light source replaceable	No
Number of gear units	Unit

## Light Technical

Colour rendering index (CRI)	>80
Flickering value (PstLM)	1

## Operating and Electrical

Line Frequency	50 or 60 Hz
----------------	-------------

## Mechanical and Housing

Housing Colour	Grey
----------------	------

## Approval and Application

Protection class IEC	Safety class I
Mech. impact protection code	IK08
Ingress protection code	IP65

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

## General Information (1/2)

Order Code	Full Product Name	Type of emergency lighting battery	Flammability mark	Lamp family code	Embedded control
50020499	WT120C G2 LED37_60S/840 PSU L1500	-	For mounting on normally flammable surfaces	-	-
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-	For mounting on easily flammable surfaces	LED27S	-
96248700	WT120C G2 LED27S/840 PSU MDU L1200	-	For mounting on easily flammable surfaces	LED27S	Movement and light sensor (On/Off)
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	Lithium	For mounting on easily flammable surfaces	LED27S	-
88307500	WT120C G2 LED27S/840 PSD L1200	-	For mounting on easily flammable surfaces	LED27S	-
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	Lithium	For mounting on easily flammable surfaces	LED27S	-
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-	For mounting on easily flammable surfaces	LED40S	-
96256200	WT120C G2 LED40S/840 PSU MDU L1200	-	For mounting on easily flammable surfaces	LED40S	Movement and light sensor (On/Off)
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-	For mounting on easily flammable surfaces	LED40S	-
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	For mounting on easily flammable surfaces	LED40S	-
88309900	WT120C G2 LED40S/840 PSD L1200	-	For mounting on easily flammable surfaces	LED40S	-
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	Lithium	For mounting on easily flammable surfaces	LED40S	-
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	Lithium	For mounting on easily flammable surfaces	LED40S	Movement and light sensor (On/Off)
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Lithium	For mounting on easily flammable surfaces	LED40S	-
97576000	WT120C G2 LED40S/840 WIA L1200	-	For mounting on easily flammable surfaces	-	-
97577700	WT120C G2 LED40S/840 WIA ELB3 L1200	Lithium	For mounting on easily flammable surfaces	-	-
97580700	WT120C G2 LED40S/840 WIA TW3 L1200	-	For mounting on easily flammable surfaces	-	-
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-	For mounting on easily flammable surfaces	-	-
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-	For mounting on easily flammable surfaces	-	-
84046600	WT120C G2 LED27S/840 PSU L1200	-	For mounting on easily flammable surfaces	-	-

Order Code	Full Product Name	Type of emergency lighting battery	Flammability mark	Lamp family code	Embedded control
84048000	WT120C G2 LED40S/840 PSU L1200	-	For mounting on easily flammable surfaces	-	-
36933499	WT120C G2 LED40S/865 PSU L1200	-	For mounting on easily flammable surfaces	-	-
50019899	WT120C G2 LED27_45S/840 PSU L1200	-	For mounting on normally flammable surfaces	-	-
96244900	WT120C G2 LED19S/840 PSU MDU L600	-	For mounting on easily flammable surfaces	LED27S	Movement and light sensor (On/Off)
88306800	WT120C G2 LED19S/840 PSD L600	-	For mounting on easily flammable surfaces	LED19S	-
84045900	WT120C G2 LED19S/840 PSU L600	-	For mounting on easily flammable surfaces	-	-
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-	For mounting on easily flammable surfaces	LED34S	-
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-	For mounting on easily flammable surfaces	LED34S	Movement and light sensor (On/Off)
88308200	WT120C G2 LED34S/840 PSD L1500	-	For mounting on easily flammable surfaces	LED34S	-
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	Lithium	For mounting on easily flammable surfaces	LED34S	-
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	Lithium	For mounting on easily flammable surfaces	LED34S	Movement and light sensor (On/Off)
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Lithium	For mounting on easily flammable surfaces	LED34S	-
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-	For mounting on easily flammable surfaces	LED60S	-
96275300	WT120C G2 LED60S/840 PSU MDU L1500	-	For mounting on easily flammable surfaces	LED60S	Movement and light sensor (On/Off)
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-	For mounting on easily flammable surfaces	LED60S	-
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	For mounting on easily flammable surfaces	LED60S	-
88310500	WT120C G2 LED60S/840 PSD L1500	-	For mounting on easily flammable surfaces	LED60S	-
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	Lithium	For mounting on easily flammable surfaces	LED60S	-
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	Lithium	For mounting on easily flammable surfaces	LED60S	Movement and light sensor (On/Off)

Order Code	Full Product Name	Type of emergency lighting	Flammability mark	Lamp family	Embedded control
		battery		code	
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	Lithium	For mounting on easily flammable surfaces	LED60S	-
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-	For mounting on easily flammable surfaces	LED80S	-
96286900	WT120C G2 LED80S/840 PSU MDU L1500	-	For mounting on easily flammable surfaces	LED80S	Movement and light sensor (On/Off)
40929600	WT120C G2 LED80S/840 PSD L1500	-	For mounting on easily flammable surfaces	LED80S	-
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	Lithium	For mounting on easily flammable surfaces	LED80S	-
97578400	WT120C G2 LED65S/840 WIA L1500	-	For mounting on easily flammable surfaces	-	-
97579100	WT120C G2 LED65S/840 WIA ELB3 L1500	Lithium	For mounting on easily flammable surfaces	-	-
97581400	WT120C G2 LED65S/840 WIA TW3 L1500	-	For mounting on easily flammable surfaces	-	-
96534800	WT120C G2 LED80S/840 WIA L1500	-	For mounting on easily flammable surfaces	-	-
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-	For mounting on easily flammable surfaces	-	-
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-	For mounting on easily flammable surfaces	-	-
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-	For mounting on easily flammable surfaces	-	-
84047300	WT120C G2 LED34S/840 PSU L1500	-	For mounting on easily flammable surfaces	-	-
84049700	WT120C G2 LED60S/840 PSU L1500	-	For mounting on easily flammable surfaces	-	-
40928900	WT120C G2 LED80S/840 PSU L1500	-	For mounting on easily flammable surfaces	-	-
36934199	WT120C G2 LED34S/865 PSU L1500	-	For mounting on easily flammable surfaces	-	-
36935899	WT120C G2 LED60S/865 PSU L1500	-	For mounting on easily flammable surfaces	-	-

## General Information (2/2)

Order Code	Full Product Name	Product family code	Order Code	Full Product Name	Product family code
50020499	WT120C G2 LED37_60S/840 PSU L1500	-	16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	WT130C
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	WT130C	88309900	WT120C G2 LED40S/840 PSD L1200	WT130C
96248700	WT120C G2 LED27S/840 PSU MDU L1200	WT130C	85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	WT130C
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	WT130C	96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	WT130C
88307500	WT120C G2 LED27S/840 PSD L1200	WT130C	88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	WT130C
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	WT130C	97576000	WT120C G2 LED40S/840 WIA L1200	WT130C
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	WT130C	97577700	WT120C G2 LED40S/840 WIA ELB3 L1200	WT130C
96256200	WT120C G2 LED40S/840 PSU MDU L1200	WT130C	97580700	WT120C G2 LED40S/840 WIA TW3 L1200	WT130C
16316700	WT120C G2 LED40S/840 PSU WEC L1200	WT130C	91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-

## CoreLine Waterproof

Order Code	Full Product Name	Product family code
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-
84046600	WT120C G2 LED27S/840 PSU L1200	-
84048000	WT120C G2 LED40S/840 PSU L1200	-
36933499	WT120C G2 LED40S/865 PSU L1200	-
50019899	WT120C G2 LED27_45S/840 PSU L1200	-
96244900	WT120C G2 LED19S/840 PSU MDU L600	WT130C
88306800	WT120C G2 LED19S/840 PSD L600	WT130C
84045900	WT120C G2 LED19S/840 PSU L600	-
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	WT130C
96267800	WT120C G2 LED34S/840 PSU MDU L1500	WT130C
88308200	WT120C G2 LED34S/840 PSD L1500	WT130C
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	WT130C
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	WT130C
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	WT130C
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	WT130C
96275300	WT120C G2 LED60S/840 PSU MDU L1500	WT130C
16318100	WT120C G2 LED60S/840 PSU WEC L1500	WT130C
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	WT130C
88310500	WT120C G2 LED60S/840 PSD L1500	WT130C

### Light Technical (1/2)

Order Code	Full Product Name	Correlated Colour Temperature	Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
50020499	WT120C G2 LED37_60S/840 PSU L1500	4000 K	140 lm/W	3,700 lm	Symmetrical
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	4000 K	126 lm/W	2,700 lm	Wide beam
96248700	WT120C G2 LED27S/840 PSU MDU L1200	4000 K	123 lm/W	2,700 lm	Wide beam
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	4000 K	104 lm/W	2,700 lm	Wide beam
88307500	WT120C G2 LED27S/840 PSD L1200	4000 K	123 lm/W	2,700 lm	Wide beam
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	4000 K	100 lm/W	2,700 lm	Wide beam
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	4000 K	133 lm/W	4,000 lm	Wide beam
96256200	WT120C G2 LED40S/840 PSU MDU L1200	4000 K	131 lm/W	4,000 lm	Wide beam

Order Code	Full Product Name	Product family code
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	WT130C
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	WT130C
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	WT130C
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	WT130C
96286900	WT120C G2 LED80S/840 PSU MDU L1500	WT130C
40929600	WT120C G2 LED80S/840 PSD L1500	WT130C
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	WT130C
97578400	WT120C G2 LED65S/840 WIA L1500	WT130C
97579100	WT120C G2 LED65S/840 WIA ELB3 L1500	WT130C
97581400	WT120C G2 LED65S/840 WIA TW3 L1500	WT130C
96534800	WT120C G2 LED80S/840 WIA L1500	WT130C
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-
84047300	WT120C G2 LED34S/840 PSU L1500	-
84049700	WT120C G2 LED60S/840 PSU L1500	-
40928900	WT120C G2 LED80S/840 PSU L1500	-
36934199	WT120C G2 LED34S/865 PSU L1500	-
36935899	WT120C G2 LED60S/865 PSU L1500	-

Order Code	Full Product Name	Correlated Colour Temperature	Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
16316700	WT120C G2 LED40S/840 PSU WEC L1200	4000 K	138 lm/W	4,000 lm	Wide beam
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	4000 K	136 lm/W	4,000 lm	Wide beam
88309900	WT120C G2 LED40S/840 PSD L1200	4000 K	131 lm/W	4,000 lm	Wide beam
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	4000 K	121 lm/W	4,000 lm	Wide beam
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	4000 K	114 lm/W	4,000 lm	Wide beam
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	4000 K	113 lm/W	4,000 lm	Wide beam
97576000	WT120C G2 LED40S/840 WIA L1200	4000 K	133 lm/W	4,000 lm	Wide beam
97577700	WT120C G2 LED40S/840 WIA ELB3 L1200	4000 K	121 lm/W	4,000 lm	Wide beam



## CoreLine Waterproof

Order Code	Full Product Name	Correlated Colour Temperature	Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
97580700	WT120C G2 LED40S/840 WIA TW3 L1200	4000 K	133 lm/W	4,000 lm	Wide beam
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	4000 K	131 lm/W	2,700 lm	Beam angle 110°
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	4000 K	140 lm/W	4,000 lm	Beam angle 110°
84046600	WT120C G2 LED27S/840 PSU L1200	4000 K	132 lm/W	2,700 lm	Wide beam
84048000	WT120C G2 LED40S/840 PSU L1200	4000 K	140 lm/W	4,000 lm	Wide beam
36933499	WT120C G2 LED40S/865 PSU L1200	6500 K	140 lm/W	4,000 lm	Wide beam
50019899	WT120C G2 LED27_45S/840 PSU L1200	4000 K	141 lm/W	2,700 lm	Symmetrical
96244900	WT120C G2 LED19S/840 PSU MDU L600	4000 K	116 lm/W	1,900 lm	Wide beam
88306800	WT120C G2 LED19S/840 PSD L600	4000 K	115 lm/W	1,900 lm	Wide beam
84045900	WT120C G2 LED19S/840 PSU L600	4000 K	127 lm/W	1,900 lm	Wide beam
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	4000 K	133 lm/W	3,400 lm	Wide beam
96267800	WT120C G2 LED34S/840 PSU MDU L1500	4000 K	131 lm/W	3,400 lm	Wide beam
88308200	WT120C G2 LED34S/840 PSD L1500	4000 K	131 lm/W	3,400 lm	Wide beam
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	4000 K	113 lm/W	3,400 lm	Wide beam
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	4000 K	110 lm/W	3,400 lm	Wide beam
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	4000 K	110 lm/W	3,400 lm	Wide beam

Order Code	Full Product Name	Correlated Colour Temperature	Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	4000 K	135 lm/W	6,000 lm	Wide beam
96275300	WT120C G2 LED60S/840 PSU MDU L1500	4000 K	133 lm/W	6,000 lm	Wide beam
16318100	WT120C G2 LED60S/840 PSU WEC L1500	4000 K	135 lm/W	6,000 lm	Wide beam
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	4000 K	136 lm/W	6,000 lm	Wide beam
88310500	WT120C G2 LED60S/840 PSD L1500	4000 K	133 lm/W	6,000 lm	Wide beam
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	4000 K	121 lm/W	6,000 lm	Wide beam
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	4000 K	120 lm/W	6,000 lm	Wide beam
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	4000 K	121 lm/W	6,000 lm	Wide beam
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	4000 K	133 lm/W	8,000 lm	Wide beam
96286900	WT120C G2 LED80S/840 PSU MDU L1500	4000 K	131 lm/W	8,000 lm	Wide beam
40929600	WT120C G2 LED80S/840 PSD L1500	4000 K	129 lm/W	8,000 lm	Wide beam
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	4000 K	126 lm/W	8,000 lm	Wide beam
97578400	WT120C G2 LED65S/840 WIA L1500	4000 K	144 lm/W	6,500 lm	Wide beam
97579100	WT120C G2 LED65S/840 WIA ELB3 L1500	4000 K	135 lm/W	6,500 lm	Wide beam
97581400	WT120C G2 LED65S/840 WIA TW3 L1500	4000 K	141 lm/W	6,500 lm	Wide beam

## CoreLine Waterproof

Order Code	Full Product Name	Correlated Colour Temperature	Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
96534800	WT120C G2 LED80S/840 WIA L1500	4000 K	131 lm/W	8,000 lm	Wide beam
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	4000 K	138 lm/W	3,400 lm	Beam angle 110°
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	4000 K	139 lm/W	6,000 lm	Beam angle 110°
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	4000 K	140 lm/W	8,000 lm	Beam angle 110°
84047300	WT120C G2 LED34S/840 PSU L1500	4000 K	140 lm/W	3,400 lm	Wide beam

Order Code	Full Product Name	Correlated Colour Temperature	Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
84049700	WT120C G2 LED60S/840 PSU L1500	4000 K	140 lm/W	6,000 lm	Wide beam
40928900	WT120C G2 LED80S/840 PSU L1500	4000 K	140 lm/W	8,000 lm	Wide beam
36934199	WT120C G2 LED34S/865 PSU L1500	6500 K	139 lm/W	3,400 lm	Wide beam
36935899	WT120C G2 LED60S/865 PSU L1500	6500 K	140 lm/W	6,000 lm	Wide beam

### Light Technical (2/2)

Order Code	Full Product Name	Stroboscopic effect
50020499	WT120C G2 LED37_60S/840 PSU L1500	0.4
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	1.6
96248700	WT120C G2 LED27S/840 PSU MDU L1200	1.6
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	1.6
88307500	WT120C G2 LED27S/840 PSD L1200	1.6
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	1.6
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	1.6
96256200	WT120C G2 LED40S/840 PSU MDU L1200	1.6
16316700	WT120C G2 LED40S/840 PSU WEC L1200	1.6
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	1.6
88309900	WT120C G2 LED40S/840 PSD L1200	1.6
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	1.6
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	1.6
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	1.6
97576000	WT120C G2 LED40S/840 WIA L1200	1.6
97577700	WT120C G2 LED40S/840 WIA ELB3 L1200	1.6
97580700	WT120C G2 LED40S/840 WIA TW3 L1200	1.6
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	1.6
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	1.6
84046600	WT120C G2 LED27S/840 PSU L1200	1.6
84048000	WT120C G2 LED40S/840 PSU L1200	1.6
36933499	WT120C G2 LED40S/865 PSU L1200	1.6
50019899	WT120C G2 LED27_45S/840 PSU L1200	0.4
96244900	WT120C G2 LED19S/840 PSU MDU L600	1.6
88306800	WT120C G2 LED19S/840 PSD L600	1.6
84045900	WT120C G2 LED19S/840 PSU L600	1.6
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	1.6
96267800	WT120C G2 LED34S/840 PSU MDU L1500	1.6

Order Code	Full Product Name	Stroboscopic effect
88308200	WT120C G2 LED34S/840 PSD L1500	1.6
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	1.6
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	1.6
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	1.6
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	1.6
96275300	WT120C G2 LED60S/840 PSU MDU L1500	1.6
16318100	WT120C G2 LED60S/840 PSU WEC L1500	1.6
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	1.6
88310500	WT120C G2 LED60S/840 PSD L1500	1.6
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	1.6
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	1.6
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	1.6
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	1.6
96286900	WT120C G2 LED80S/840 PSU MDU L1500	1.6
40929600	WT120C G2 LED80S/840 PSD L1500	1.6
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	1.6
97578400	WT120C G2 LED65S/840 WIA L1500	1.6
97579100	WT120C G2 LED65S/840 WIA ELB3 L1500	1.6
97581400	WT120C G2 LED65S/840 WIA TW3 L1500	1.6
96534800	WT120C G2 LED80S/840 WIA L1500	1.6
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	1.6
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	1.6
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	1.6
84047300	WT120C G2 LED34S/840 PSU L1500	1.6
84049700	WT120C G2 LED60S/840 PSU L1500	1.6
40928900	WT120C G2 LED80S/840 PSU L1500	1.6
36934199	WT120C G2 LED34S/865 PSU L1500	1.6
36935899	WT120C G2 LED60S/865 PSU L1500	1.6

### Operating and Electrical

## CoreLine Waterproof

Order Code	Full Product Name	Input Voltage	Power Consumption
50020499	WT120C G2 LED37_60S/840 PSU L1500	220 to 240 V	43 W
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	220 to 240 V	21.5 W
96248700	WT120C G2 LED27S/840 PSU MDU L1200	220 to 240 V	22 W
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	220 to 240 V	26 W
88307500	WT120C G2 LED27S/840 PSD L1200	220 to 240 V	22 W
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	220 to 240 V	27 W
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	220 to 240 V	30 W
96256200	WT120C G2 LED40S/840 PSU MDU L1200	220 to 240 V	30.5 W
16316700	WT120C G2 LED40S/840 PSU WEC L1200	220 to 240 V	29 W
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	220 to 240 V	29.5 W
88309900	WT120C G2 LED40S/840 PSD L1200	220 to 240 V	30.5 W
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	220 to 240 V	33 W
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	220 to 240 V	35 W
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	220 to 240 V	35.5 W
97576000	WT120C G2 LED40S/840 WIA L1200	220 to 240 V	30 W
97577700	WT120C G2 LED40S/840 WIA ELB3 L1200	220 to 240 V	33 W
97580700	WT120C G2 LED40S/840 WIA TW3 L1200	220 to 240 V	30 W
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	220 to 240 V	20.5 W
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	220 to 240 V	28.5 W
84046600	WT120C G2 LED27S/840 PSU L1200	220 to 240 V	20.5 W
84048000	WT120C G2 LED40S/840 PSU L1200	220 to 240 V	28.6 W
36933499	WT120C G2 LED40S/865 PSU L1200	220 to 240 V	28.5 W
50019899	WT120C G2 LED27_45S/840 PSU L1200	220 to 240 V	32 W
96244900	WT120C G2 LED19S/840 PSU MDU L600	220 to 240 V	16.4 W
88306800	WT120C G2 LED19S/840 PSD L600	220 to 240 V	16.5 W
84045900	WT120C G2 LED19S/840 PSU L600	220 to 240 V	15 W
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	220 to 240 V	25.5 W
96267800	WT120C G2 LED34S/840 PSU MDU L1500	220 to 240 V	26 W

Order Code	Full Product Name	Input Voltage	Power Consumption
88308200	WT120C G2 LED34S/840 PSD L1500	220 to 240 V	26 W
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	220 to 240 V	30 W
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	220 to 240 V	31 W
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	220 to 240 V	31 W
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	220 to 240 V	44.5 W
96275300	WT120C G2 LED60S/840 PSU MDU L1500	220 to 240 V	45 W
16318100	WT120C G2 LED60S/840 PSU WEC L1500	220 to 240 V	44.5 W
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	220 to 240 V	44 W
88310500	WT120C G2 LED60S/840 PSD L1500	220 to 240 V	45 W
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	220 to 240 V	49.5 W
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	220 to 240 V	50 W
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	220 to 240 V	49.5 W
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	220 to 240 V	60 W
96286900	WT120C G2 LED80S/840 PSU MDU L1500	220 to 240 V	61 W
40929600	WT120C G2 LED80S/840 PSD L1500	220 to 240 V	62 W
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	220 to 240 V	63.5 W
97578400	WT120C G2 LED65S/840 WIA L1500	220 to 240 V	45 W
97579100	WT120C G2 LED65S/840 WIA ELB3 L1500	220 to 240 V	48 W
97581400	WT120C G2 LED65S/840 WIA TW3 L1500	220 to 240 V	46 W
96534800	WT120C G2 LED80S/840 WIA L1500	220-240 V	61 W
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	220 to 240 V	24.5 W
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	220 to 240 V	43 W
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	220 to 240 V	57 W
84047300	WT120C G2 LED34S/840 PSU L1500	220 to 240 V	24.3 W
84049700	WT120C G2 LED60S/840 PSU L1500	220 to 240 V	42.9 W
40928900	WT120C G2 LED80S/840 PSU L1500	220 to 240 V	57.1 W
36934199	WT120C G2 LED34S/865 PSU L1500	220 to 240 V	24.5 W
36935899	WT120C G2 LED60S/865 PSU L1500	220 to 240 V	43 W

## Temperature

## CoreLine Waterproof

Order Code	Full Product Name	Ambient temperature range
50020499	WT120C G2 LED37_60S/840 PSU L1500	-20 to +40 °C
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-20 to +35 °C
96248700	WT120C G2 LED27S/840 PSU MDU L1200	-20 to +35 °C
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	0 to +25 °C
88307500	WT120C G2 LED27S/840 PSD L1200	-20 to +35 °C
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	0 to +25 °C
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-20 to +35 °C
96256200	WT120C G2 LED40S/840 PSU MDU L1200	-20 to +35 °C
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-20 to +35 °C
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-20 to +35 °C
88309900	WT120C G2 LED40S/840 PSD L1200	-20 to +35 °C
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	0 to +25 °C
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	0 to +25 °C
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	0 to +25 °C
97576000	WT120C G2 LED40S/840 WIA L1200	-20 to +35 °C
97577700	WT120C G2 LED40S/840 WIA ELB3 L1200	0 to +25 °C
97580700	WT120C G2 LED40S/840 WIA TW3 L1200	-20 to +35 °C
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-20 to +40 °C
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-20 to +40 °C
84046600	WT120C G2 LED27S/840 PSU L1200	-20 to +40 °C
84048000	WT120C G2 LED40S/840 PSU L1200	-20 to +40 °C
36933499	WT120C G2 LED40S/865 PSU L1200	-20 to +40 °C
50019899	WT120C G2 LED27_45S/840 PSU L1200	-20 to +40 °C
96244900	WT120C G2 LED19S/840 PSU MDU L600	-20 to +35 °C
88306800	WT120C G2 LED19S/840 PSD L600	-20 to +35 °C
84045900	WT120C G2 LED19S/840 PSU L600	-20 to +40 °C
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-20 to +35 °C
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-20 to +35 °C
88308200	WT120C G2 LED34S/840 PSD L1500	-20 to +35 °C

Order Code	Full Product Name	Ambient temperature range
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	0 to +25 °C
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	0 to +25 °C
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	0 to +25 °C
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-20 to +35 °C
96275300	WT120C G2 LED60S/840 PSU MDU L1500	-20 to +35 °C
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-20 to +35 °C
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-20 to +35 °C
88310500	WT120C G2 LED60S/840 PSD L1500	-20 to +35 °C
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	0 to +25 °C
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	0 to +25 °C
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	0 to +25 °C
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-20 to +35 °C
96286900	WT120C G2 LED80S/840 PSU MDU L1500	-20 to +35 °C
40929600	WT120C G2 LED80S/840 PSD L1500	-20 to +35 °C
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	0 to +25 °C
97578400	WT120C G2 LED65S/840 WIA L1500	-20 to +35 °C
97579100	WT120C G2 LED65S/840 WIA ELB3 L1500	0 to +25 °C
97581400	WT120C G2 LED65S/840 WIA TW3 L1500	-20 to +35 °C
96534800	WT120C G2 LED80S/840 WIA L1500	-20 to +35 °C
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-20 to +40 °C
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-20 to +40 °C
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-20 to +40 °C
84047300	WT120C G2 LED34S/840 PSU L1500	-20 to +40 °C
84049700	WT120C G2 LED60S/840 PSU L1500	-20 to +40 °C
40928900	WT120C G2 LED80S/840 PSU L1500	-20 to +40 °C
36934199	WT120C G2 LED34S/865 PSU L1500	-20 to +40 °C
36935899	WT120C G2 LED60S/865 PSU L1500	-20 to +40 °C

### Controls and Dimming

Order Code	Full Product Name	Dimmable
50020499	WT120C G2 LED37_60S/840 PSU L1500	No
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	No
96248700	WT120C G2 LED27S/840 PSU MDU L1200	No
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	No
88307500	WT120C G2 LED27S/840 PSD L1200	Yes
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	Yes
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	No
96256200	WT120C G2 LED40S/840 PSU MDU L1200	No
16316700	WT120C G2 LED40S/840 PSU WEC L1200	No
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	No
88309900	WT120C G2 LED40S/840 PSD L1200	Yes
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	No
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	No
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Yes
97576000	WT120C G2 LED40S/840 WIA L1200	Yes
97577700	WT120C G2 LED40S/840 WIA ELB3 L1200	Yes
97580700	WT120C G2 LED40S/840 WIA TW3 L1200	Yes

Order Code	Full Product Name	Dimmable
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	No
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	No
84046600	WT120C G2 LED27S/840 PSU L1200	No
84048000	WT120C G2 LED40S/840 PSU L1200	No
36933499	WT120C G2 LED40S/865 PSU L1200	No
50019899	WT120C G2 LED27_45S/840 PSU L1200	No
96244900	WT120C G2 LED19S/840 PSU MDU L600	No
88306800	WT120C G2 LED19S/840 PSD L600	Yes
84045900	WT120C G2 LED19S/840 PSU L600	No
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	No
96267800	WT120C G2 LED34S/840 PSU MDU L1500	No
88308200	WT120C G2 LED34S/840 PSD L1500	Yes
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	No
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	No
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Yes
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	No
96275300	WT120C G2 LED60S/840 PSU MDU L1500	No

## CoreLine Waterproof

Order Code	Full Product Name	Dimmable
16318100	WT120C G2 LED60S/840 PSU WEC L1500	No
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	No
88310500	WT120C G2 LED60S/840 PSD L1500	Yes
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	No
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	No
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	Yes
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	No
96286900	WT120C G2 LED80S/840 PSU MDU L1500	No
40929600	WT120C G2 LED80S/840 PSD L1500	Yes
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	No
97578400	WT120C G2 LED65S/840 WIA L1500	Yes

Order Code	Full Product Name	Dimmable
97579100	WT120C G2 LED65S/840 WIA ELB3 L1500	Yes
97581400	WT120C G2 LED65S/840 WIA TW3 L1500	Yes
96534800	WT120C G2 LED80S/840 WIA L1500	Yes
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	No
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	No
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	No
84047300	WT120C G2 LED34S/840 PSU L1500	No
84049700	WT120C G2 LED60S/840 PSU L1500	No
40928900	WT120C G2 LED80S/840 PSU L1500	No
36934199	WT120C G2 LED34S/865 PSU L1500	No
36935899	WT120C G2 LED60S/865 PSU L1500	No

### Emergency Operation

Order Code	Full Product Name	Emergency	
		Emergency flux	Power
50020499	WT120C G2 LED37_60S/840 PSU L1500	-	-
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-	-
96248700	WT120C G2 LED27S/840 PSU MDU L1200	-	-
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	500 lm	3 W
88307500	WT120C G2 LED27S/840 PSD L1200	-	-
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	500 lm	3 W
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-	-
96256200	WT120C G2 LED40S/840 PSU MDU L1200	-	-
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-	-
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	-
88309900	WT120C G2 LED40S/840 PSD L1200	-	-
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	500 lm	3 W
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	500 lm	3 W
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	500 lm	3 W
97576000	WT120C G2 LED40S/840 WIA L1200	-	-
97577700	WT120C G2 LED40S/840 WIA ELB3 L1200	500 lm	3 W
97580700	WT120C G2 LED40S/840 WIA TW3 L1200	-	-
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-	-
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-	-
84046600	WT120C G2 LED27S/840 PSU L1200	-	-
84048000	WT120C G2 LED40S/840 PSU L1200	-	-

Order Code	Full Product Name	Emergency	
		Emergency flux	Power
36933499	WT120C G2 LED40S/865 PSU L1200	-	-
50019899	WT120C G2 LED27_45S/840 PSU L1200	-	-
96244900	WT120C G2 LED19S/840 PSU MDU L600	-	-
88306800	WT120C G2 LED19S/840 PSD L600	-	-
84045900	WT120C G2 LED19S/840 PSU L600	-	-
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-	-
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-	-
88308200	WT120C G2 LED34S/840 PSD L1500	-	-
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	500 lm	3 W
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	500 lm	3 W
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	500 lm	3 W
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-	-
96275300	WT120C G2 LED60S/840 PSU MDU L1500	-	-
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-	-
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	-
88310500	WT120C G2 LED60S/840 PSD L1500	-	-
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	500 lm	3 W
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	500 lm	3 W
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	500 lm	3 W
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-	-
96286900	WT120C G2 LED80S/840 PSU MDU L1500	-	-

CoreLine Waterproof

Order Code	Full Product Name	Emergency	
		Emergency flux	Power
40929600	WT120C G2 LED80S/840 PSD L1500	-	-
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	500 lm	3 W
97578400	WT120C G2 LED65S/840 WIA L1500	-	-
97579100	WT120C G2 LED65S/840 WIA ELB3 L1500	500 lm	3 W
97581400	WT120C G2 LED65S/840 WIA TW3 L1500	-	-
96534800	WT120C G2 LED80S/840 WIA L1500	-	-
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
50020499	WT120C G2 LED37_60S/840 PSU L1500	(0.38,0.38)SDCM<=3
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
96248700	WT120C G2 LED27S/840 PSU MDU L1200	(0.38,0.38)SDCM<=3
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3
88307500	WT120C G2 LED27S/840 PSD L1200	(0.38,0.38)SDCM<=3
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
96256200	WT120C G2 LED40S/840 PSU MDU L1200	(0.38,0.38)SDCM<=3
16316700	WT120C G2 LED40S/840 PSU WEC L1200	(0.38,0.38)SDCM<=3
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	(0.38,0.38)SDCM<=3
88309900	WT120C G2 LED40S/840 PSD L1200	(0.38,0.38)SDCM<=3
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	(0.38,0.38)SDCM<=3
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3
97576000	WT120C G2 LED40S/840 WIA L1200	(0.38,0.38)SDCM<=3
97577700	WT120C G2 LED40S/840 WIA ELB3 L1200	(0.38,0.38)SDCM<=3
97580700	WT120C G2 LED40S/840 WIA TW3 L1200	(0.38,0.38)SDCM<=3
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
84046600	WT120C G2 LED27S/840 PSU L1200	(0.38,0.38)SDCM<=3
84048000	WT120C G2 LED40S/840 PSU L1200	(0.38,0.38)SDCM<=3
36933499	WT120C G2 LED40S/865 PSU L1200	(0.31,0.32)SDCM<=3
50019899	WT120C G2 LED27_45S/840 PSU L1200	(0.38,0.38)SDCM<=3
96244900	WT120C G2 LED19S/840 PSU MDU L600	(0.38,0.38)SDCM<=3
88306800	WT120C G2 LED19S/840 PSD L600	(0.38,0.38)SDCM<=3
84045900	WT120C G2 LED19S/840 PSU L600	(0.38,0.38)SDCM<=3
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
96267800	WT120C G2 LED34S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3

Application Conditions

Order Code	Full Product Name	Emergency	
		Emergency flux	Power
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-	-
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-	-
84047300	WT120C G2 LED34S/840 PSU L1500	-	-
84049700	WT120C G2 LED60S/840 PSU L1500	-	-
40928900	WT120C G2 LED80S/840 PSU L1500	-	-
36934199	WT120C G2 LED34S/865 PSU L1500	-	-
36935899	WT120C G2 LED60S/865 PSU L1500	-	-

Order Code	Full Product Name	Initial chromaticity
88308200	WT120C G2 LED34S/840 PSD L1500	(0.38,0.38)SDCM<=3
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	(0.38,0.38)SDCM<=3
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	(0.38,0.38)SDCM<=3
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	(0.38,0.38)SDCM<=3
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
96275300	WT120C G2 LED60S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
16318100	WT120C G2 LED60S/840 PSU WEC L1500	(0.38,0.38)SDCM<=3
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	(0.38,0.38)SDCM<=3
88310500	WT120C G2 LED60S/840 PSD L1500	(0.38,0.38)SDCM<=3
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	(0.38,0.38)SDCM<=3
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	(0.38,0.38)SDCM<=3
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	(0.38,0.38)SDCM<=3
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
96286900	WT120C G2 LED80S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
40929600	WT120C G2 LED80S/840 PSD L1500	(0.38,0.38)SDCM<=3
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	(0.38,0.38)SDCM<=3
97578400	WT120C G2 LED65S/840 WIA L1500	(0.38,0.38)SDCM<=3
97579100	WT120C G2 LED65S/840 WIA ELB3 L1500	(0.38,0.38)SDCM<=3
97581400	WT120C G2 LED65S/840 WIA TW3 L1500	(0.38,0.38)SDCM<=3
96534800	WT120C G2 LED80S/840 WIA L1500	(0.38,0.38)SDCM<=3
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
84047300	WT120C G2 LED34S/840 PSU L1500	(0.38,0.38)SDCM<=3
84049700	WT120C G2 LED60S/840 PSU L1500	(0.38,0.38)SDCM<=3
40928900	WT120C G2 LED80S/840 PSU L1500	(0.38,0.38)SDCM<=3
36934199	WT120C G2 LED34S/865 PSU L1500	(0.31,0.32)SDCM<=3
36935899	WT120C G2 LED60S/865 PSU L1500	(0.31,0.32)SDCM<=3

## CoreLine Waterproof

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
50020499	WT120C G2 LED37_60S/840 PSU L1500	-	Yes
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	Not applicable	Not applicable
96248700	WT120C G2 LED27S/840 PSU MDU L1200	Not applicable	Yes
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	Not applicable	Not applicable
88307500	WT120C G2 LED27S/840 PSD L1200	1%	Not applicable
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	1%	Not applicable
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	Not applicable	Not applicable
96256200	WT120C G2 LED40S/840 PSU MDU L1200	Not applicable	Yes
16316700	WT120C G2 LED40S/840 PSU WEC L1200	Not applicable	Not applicable
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	Not applicable	Not applicable
88309900	WT120C G2 LED40S/840 PSD L1200	1%	Not applicable
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	Not applicable	Not applicable
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	Not applicable	Yes
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	1%	Not applicable
97576000	WT120C G2 LED40S/840 WIA L1200	10%	Not applicable
97577700	WT120C G2 LED40S/840 WIA ELB3 L1200	10%	Not applicable
97580700	WT120C G2 LED40S/840 WIA TW3 L1200	10%	Not applicable
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	Not applicable	Not applicable
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	Not applicable	Not applicable
84046600	WT120C G2 LED27S/840 PSU L1200	Not applicable	Not applicable
84048000	WT120C G2 LED40S/840 PSU L1200	Not applicable	Not applicable
36933499	WT120C G2 LED40S/865 PSU L1200	Not applicable	Not applicable
50019899	WT120C G2 LED27_45S/840 PSU L1200	-	Yes
96244900	WT120C G2 LED19S/840 PSU MDU L600	Not applicable	Yes
88306800	WT120C G2 LED19S/840 PSD L600	1%	Not applicable
84045900	WT120C G2 LED19S/840 PSU L600	Not applicable	Not applicable
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	Not applicable	Not applicable
96267800	WT120C G2 LED34S/840 PSU MDU L1500	Not applicable	Yes

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
88308200	WT120C G2 LED34S/840 PSD L1500	1%	Not applicable
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	Not applicable	Not applicable
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	Not applicable	Yes
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	1%	Not applicable
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	Not applicable	Not applicable
96275300	WT120C G2 LED60S/840 PSU MDU L1500	Not applicable	Yes
16318100	WT120C G2 LED60S/840 PSU WEC L1500	Not applicable	Not applicable
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	Not applicable	Not applicable
88310500	WT120C G2 LED60S/840 PSD L1500	1%	Not applicable
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	Not applicable	Not applicable
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	Not applicable	Yes
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	1%	Not applicable
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	Not applicable	Not applicable
96286900	WT120C G2 LED80S/840 PSU MDU L1500	Not applicable	Yes
40929600	WT120C G2 LED80S/840 PSD L1500	1%	Not applicable
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	Not applicable	Not applicable
97578400	WT120C G2 LED65S/840 WIA L1500	10%	Not applicable
97579100	WT120C G2 LED65S/840 WIA ELB3 L1500	10%	Not applicable
97581400	WT120C G2 LED65S/840 WIA TW3 L1500	10%	Not applicable
96534800	WT120C G2 LED80S/840 WIA L1500	10%	Not applicable
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	Not applicable	Not applicable
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	Not applicable	Not applicable
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	Not applicable	Not applicable
84047300	WT120C G2 LED34S/840 PSU L1500	Not applicable	Not applicable
84049700	WT120C G2 LED60S/840 PSU L1500	Not applicable	Not applicable
40928900	WT120C G2 LED80S/840 PSU L1500	Not applicable	Not applicable
36934199	WT120C G2 LED34S/865 PSU L1500	Not applicable	Not applicable
36935899	WT120C G2 LED60S/865 PSU L1500	Not applicable	Not applicable

