



CoreLine Waterproof

WT120C G2 LED19S/840 PSU L600 ELB3

CoreLine Waterproof, 16.5 W, L600 mm, 1900lm, 4000 K, PSU, Wide beam, Frosted, IP65, IK08, TWI-ready, Basic 3h emergency

Product data

General Information

Luminous flux (system)	1900 lm
Emergency output	274 lm
Luminaire efficacy	115 lm/W
Luminous flux tolerance	+/-10%
Light source colour	4000K [neutral white]
Init. Colour rendering index	> 80
Initial chromaticity	(0.38, 0.38) SDCM≤3
Unified glare (UGR)	25
Beam angle	105 °
Optic type	Wide beam
Optical cover finish	Frosted
Installation	Surface mounted
Connection type	Push-in connector
Emergency type	ELB3 [Basic 3h emergency]
Battery type	LiFeP04
Ambient temperature range	0 to +35 °C

Controls and Dimming

Driver	PSU [Power supply unit on/off]
Dimming	No

Mechanical and housing

Housing material	Polycarbonate
Colour	Gray
IP / IK rating	IP65 IK08
Dimensions (L x W x H)	80 x 85 x 665 mm

Operating and Electrical

Mains supply	230 – 240V / 50-60Hz
Power consumption	16.5 W
Power Factor (Fraction)	0.9
Power consumption tolerance	+/-10%
Safety class	I

Over Time Performance

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

Product data

Order code	919013004518
Product name	WT120C G2 LED19S/840 PSU L600 ELB3

Dimensions

