



CoreLine highbay gen5: Easy installation. Excellent illumination.

CoreLine Highbay Gen5

CoreLine Highbay Gen5 delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, highly efficient luminaire with a very long-lifetime, it delivers great savings on energy and requires less maintenance. At the same time, CoreLine Highbay is very easy to handle. The luminaire can be installed on your existing grid and the electrical connection is a straightforward task, with no need to open the luminaire and an external IP65 connector. With a choice of two beam angles: narrow and wide beam, you can adjust your lighting plan to suit your exact needs. This range also includes Interact Ready luminaires with integrated wireless communications and integrated movement and daylight sensors. So CoreLine Highbay Gen5 is ready to be used with any Interact connected lighting system.

Benefits

- Saves on energy and maintenance costs
- Easy installation - single suspension hook and external connector, additional mounting bracket for more flexibility
- Ideal for general application projects, with a robust design and a high water and dust-proof rating (IP65)
- Choice of four product types: BY121P, BY122P, BY120P and BY122X

CoreLine Highbay Gen5







Features

- Long lifetime and high efficiency: 50,000 hours with flux at 85% min. compared to initial levels; up to 160lm/W
- Choice of beam options: narrow and wide beam, for low glare without additional accessories
- Modern, high-quality die-cast aluminium housing
- Single point mounting and IP65 external, pre-mounted electrical connector
- Optional versions: DALI dimming, integrated wireless connectivity (Interact Ready)

Application


- General manufacturing
- Exhibition halls
- Warehouses and logistics centres
- High-ceilinged lounges

Dimensional drawing




CoreLine Highbay Gen5


Dimensional drawing




Product details



CoreLine highbay gen5, IP65
connector (PSD)




CoreLine highbay gen5, with
sensor, front view



CoreLine highbay gen5, BY120P,
front view



CoreLine highbay gen5, with
sensor, side view



CoreLine highbay gen5, BY121P,
front view



CoreLine highbay gen5, IP65
connector



CoreLine highbay gen5, with
sensor, back view

CoreLine Highbay Gen5

Product details




CoreLine highbay gen5, bracket
mounting



CoreLine highbay gen5, bracket
mounting



CoreLine highbay gen5, hook
mounting



CoreLine highbay gen5, BY121P,
front view

CoreLine Highbay Gen5

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Light Technical	
Colour rendering index (CRI)	>80
Flickering value (PstLM)	0.5
Stroboscopic effect	1
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-30 to +50 °C
Mechanical and Housing	
Housing Colour	Grey
Approval and Application	
Protection class IEC	Safety class I
Ingress protection code	IP65
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Suitable for random switching	Yes

General Information

Order Code	Full Product Name	Embedded control	Number of gear units
95582000	BY122P G5 LED250S/840 PSU NB	-	Unit
95583700	BY122P G5 LED250S/840 PSU WB	-	Unit
95584400	BY122P G5 LED250S/865 PSU NB	-	Unit
95585100	BY122P G5 LED250S/865 PSU WB	-	Unit
95586800	BY122P G5 LED250S/840 PSD NB	-	2 units
95587500	BY122P G5 LED250S/840 PSD WB	-	2 units
95588200	BY122P G5 LED250S/865 PSD NB	-	2 units
95589900	BY122P G5 LED250S/865 PSD WB	-	2 units
95600100	BY122P G5 LED300S/840 PSU NB	-	Unit
95601800	BY122P G5 LED300S/840 PSU WB	-	Unit
95602500	BY122P G5 LED300S/840 PSD NB	-	2 units
95603200	BY122P G5 LED300S/840 PSD WB	-	2 units
95568400	BY121P G5 LED200S/840 PSU NB	-	Unit
95569100	BY121P G5 LED200S/840 PSU WB	-	Unit
95570700	BY121P G5 LED105S/840 PSD NB	-	Unit
95571400	BY121P G5 LED105S/840 PSD WB	-	Unit
95572100	BY121P G5 LED200S/840 PSD NB	-	Unit
95573800	BY121P G5 LED200S/840 PSD WB	-	Unit
95576900	BY121P G5 LED200S/865 PSU NB	-	Unit
95577600	BY121P G5 LED200S/865 PSU WB	-	Unit
95578300	BY121P G5 LED105S/865 PSD NB	-	Unit
95579000	BY121P G5 LED105S/865 PSD WB	-	Unit
95580600	BY121P G5 LED200S/865 PSD NB	-	Unit
95581300	BY121P G5 LED200S/865 PSD WB	-	Unit
95598100	BY121P G5 LED150S/840 PSD NB	-	Unit
95599800	BY121P G5 LED150S/840 PSD WB	-	Unit
95566000	BY120P G5 LED105S/840 PSU NB	-	Unit
95567700	BY120P G5 LED105S/840 PSU WB	-	Unit
95574500	BY120P G5 LED105S/865 PSU NB	-	Unit
95575200	BY120P G5 LED105S/865 PSU WB	-	Unit
95596700	BY120P G5 LED150S/840 PSU NB	-	Unit
95597400	BY120P G5 LED150S/840 PSU WB	-	Unit
95590500	BY122X G5 LED105S/840 SIA NB H4	Sensor SNH (R) 210	Unit
95591200	BY122X G5 LED105S/840 SIA WB H4	Sensor SNH (R) 210	Unit
95592900	BY122X G5 LED200S/840 SIA NB H4	Sensor SNH (R) 210	Unit
95593600	BY122X G5 LED200S/840 SIA WB H4	Sensor SNH (R) 210	Unit
95594300	BY122X G5 LED250S/840 SIA NB H4	Sensor SNH (R) 210	Unit
95595000	BY122X G5 LED250S/840 SIA WB H4	Sensor SNH (R) 210	Unit
95604900	BY122X G5 LED300S/840 SIA NB H4	Sensor SNH (R) 210	Unit
95605600	BY122X G5 LED300S/840 SIA WB H4	Sensor SNH (R) 210	Unit

Light Technical

		Correlated	Luminous					Correlated	Luminous		
		Colour	efficacy					Colour	efficacy		
Order Code	Full Product Name	Temperature	(rated) (nom.)	Luminous Flux	Optic type	Order Code	Full Product Name	Temperature	(rated) (nom.)	Luminous Flux	Optic type
95582000	BY122P G5 LED250S/840 PSU NB	4000 K	159 lm/W	25,000 lm	Narrow beam	95583700	BY122P G5 LED250S/840 PSU WB	4000 K	159 lm/W	25,000 lm	Wide beam

CoreLine Highbay Gen5

Order Code	Full Product Name	Correlated Colour Temperature	Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
95584400	BY122P G5 LED250S/865 PSU NB	6500 K	159 lm/W	25,000 lm	Narrow beam
95585100	BY122P G5 LED250S/865 PSU WB	6500 K	159 lm/W	25,000 lm	Wide beam
95586800	BY122P G5 LED250S/840 PSD NB	4000 K	149 lm/W	25,000 lm	Narrow beam
95587500	BY122P G5 LED250S/840 PSD WB	4000 K	149 lm/W	25,000 lm	Wide beam
95588200	BY122P G5 LED250S/865 PSD NB	6500 K	149 lm/W	25,000 lm	Narrow beam
95589900	BY122P G5 LED250S/865 PSD WB	6500 K	149 lm/W	25,000 lm	Wide beam
95600100	BY122P G5 LED300S/840 PSU NB	4000 K	156 lm/W	30,000 lm	Narrow beam
95601800	BY122P G5 LED300S/840 PSU WB	4000 K	156 lm/W	30,000 lm	Wide beam
95602500	BY122P G5 LED300S/840 PSD NB	4000 K	146 lm/W	30,000 lm	Narrow beam
95603200	BY122P G5 LED300S/840 PSD WB	4000 K	146 lm/W	30,000 lm	Wide beam
95568400	BY121P G5 LED200S/840 PSU NB	4000 K	159 lm/W	20,000 lm	Narrow beam
95569100	BY121P G5 LED200S/840 PSU WB	4000 K	159 lm/W	20,000 lm	Wide beam
95570700	BY121P G5 LED105S/840 PSD NB	4000 K	146 lm/W	10,500 lm	Narrow beam
95571400	BY121P G5 LED105S/840 PSD WB	4000 K	146 lm/W	10,500 lm	Wide beam
95572100	BY121P G5 LED200S/840 PSD NB	4000 K	149 lm/W	20,000 lm	Narrow beam
95573800	BY121P G5 LED200S/840 PSD WB	4000 K	149 lm/W	20,000 lm	Wide beam

Order Code	Full Product Name	Correlated Colour Temperature	Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
95576900	BY121P G5 LED200S/865 PSU NB	6500 K	159 lm/W	20,000 lm	Narrow beam
95577600	BY121P G5 LED200S/865 PSU WB	6500 K	159 lm/W	20,000 lm	Wide beam
95578300	BY121P G5 LED105S/865 PSD NB	6500 K	146 lm/W	10,500 lm	Narrow beam
95579000	BY121P G5 LED105S/865 PSD WB	6500 K	146 lm/W	10,500 lm	Wide beam
95580600	BY121P G5 LED200S/865 PSD NB	6500 K	149 lm/W	20,000 lm	Narrow beam
95581300	BY121P G5 LED200S/865 PSD WB	6500 K	149 lm/W	20,000 lm	Wide beam
95598100	BY121P G5 LED150S/840 PSD NB	4000 K	147 lm/W	15,000 lm	Narrow beam
95599800	BY121P G5 LED150S/840 PSD WB	4000 K	147 lm/W	15,000 lm	Wide beam
95566000	BY120P G5 LED105S/840 PSU NB	4000 K	157 lm/W	10,500 lm	Narrow beam
95567700	BY120P G5 LED105S/840 PSU WB	4000 K	157 lm/W	10,500 lm	Wide beam
95574500	BY120P G5 LED105S/865 PSU NB	6500 K	157 lm/W	10,500 lm	Narrow beam
95575200	BY120P G5 LED105S/865 PSU WB	6500 K	157 lm/W	10,500 lm	Wide beam
95596700	BY120P G5 LED150S/840 PSU NB	4000 K	158 lm/W	15,000 lm	Narrow beam
95597400	BY120P G5 LED150S/840 PSU WB	4000 K	158 lm/W	15,000 lm	Wide beam
95590500	BY122X G5 LED105S/840 SIA NB H4	4000 K	146 lm/W	10,500 lm	Narrow beam
95591200	BY122X G5 LED105S/840 SIA WB H4	4000 K	146 lm/W	10,500 lm	Wide beam

CoreLine Highbay Gen5

Order Code	Full Product Name	Correlated	Luminous	Luminous	Optic
		Colour	efficacy		
		Temperature	(rated)	Flux	type
			(nom.)		
95592900	BY122X G5 LED200S/840 SIA NB H4	4000 K	150 lm/W	20,000 lm	Narrow beam
95593600	BY122X G5 LED200S/840 SIA WB H4	4000 K	150 lm/W	20,000 lm	Wide beam
95594300	BY122X G5 LED250S/840 SIA NB H4	4000 K	151 lm/W	25,000 lm	Narrow beam

Order Code	Full Product Name	Correlated	Luminous	Luminous	Optic
		Colour	efficacy		
		Temperature	(rated)	Flux	type
			(nom.)		
95595000	BY122X G5 LED250S/840 SIA WB H4	4000 K	151 lm/W	25,000 lm	Wide beam
95604900	BY122X G5 LED300S/840 SIA NB H4	4000 K	148 lm/W	30,000 lm	Narrow beam
95605600	BY122X G5 LED300S/840 SIA WB H4	4000 K	148 lm/W	30,000 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
95582000	BY122P G5 LED250S/840 PSU NB	157 W
95583700	BY122P G5 LED250S/840 PSU WB	157 W
95584400	BY122P G5 LED250S/865 PSU NB	157 W
95585100	BY122P G5 LED250S/865 PSU WB	157 W
95586800	BY122P G5 LED250S/840 PSD NB	168 W
95587500	BY122P G5 LED250S/840 PSD WB	168 W
95588200	BY122P G5 LED250S/865 PSD NB	168 W
95589900	BY122P G5 LED250S/865 PSD WB	168 W
95600100	BY122P G5 LED300S/840 PSU NB	192 W
95601800	BY122P G5 LED300S/840 PSU WB	192 W
95602500	BY122P G5 LED300S/840 PSD NB	205 W
95603200	BY122P G5 LED300S/840 PSD WB	205 W
95568400	BY121P G5 LED200S/840 PSU NB	126 W
95569100	BY121P G5 LED200S/840 PSU WB	126 W
95570700	BY121P G5 LED105S/840 PSD NB	72 W
95571400	BY121P G5 LED105S/840 PSD WB	72 W
95572100	BY121P G5 LED200S/840 PSD NB	134 W
95573800	BY121P G5 LED200S/840 PSD WB	134 W
95576900	BY121P G5 LED200S/865 PSU NB	126 W
95577600	BY121P G5 LED200S/865 PSU WB	126 W

Order Code	Full Product Name	Power Consumption
95578300	BY121P G5 LED105S/865 PSD NB	72 W
95579000	BY121P G5 LED105S/865 PSD WB	72 W
95580600	BY121P G5 LED200S/865 PSD NB	134 W
95581300	BY121P G5 LED200S/865 PSD WB	134 W
95598100	BY121P G5 LED150S/840 PSD NB	102 W
95599800	BY121P G5 LED150S/840 PSD WB	102 W
95566000	BY120P G5 LED105S/840 PSU NB	67 W
95567700	BY120P G5 LED105S/840 PSU WB	67 W
95574500	BY120P G5 LED105S/865 PSU NB	67 W
95575200	BY120P G5 LED105S/865 PSU WB	67 W
95596700	BY120P G5 LED150S/840 PSU NB	95 W
95597400	BY120P G5 LED150S/840 PSU WB	95 W
95590500	BY122X G5 LED105S/840 SIA NB H4	72 W
95591200	BY122X G5 LED105S/840 SIA WB H4	72 W
95592900	BY122X G5 LED200S/840 SIA NB H4	133 W
95593600	BY122X G5 LED200S/840 SIA WB H4	133 W
95594300	BY122X G5 LED250S/840 SIA NB H4	166 W
95595000	BY122X G5 LED250S/840 SIA WB H4	166 W
95604900	BY122X G5 LED300S/840 SIA NB H4	203 W
95605600	BY122X G5 LED300S/840 SIA WB H4	203 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
95582000	BY122P G5 LED250S/840 PSU NB	No
95583700	BY122P G5 LED250S/840 PSU WB	No
95584400	BY122P G5 LED250S/865 PSU NB	No
95585100	BY122P G5 LED250S/865 PSU WB	No
95586800	BY122P G5 LED250S/840 PSD NB	Yes
95587500	BY122P G5 LED250S/840 PSD WB	Yes
95588200	BY122P G5 LED250S/865 PSD NB	Yes
95589900	BY122P G5 LED250S/865 PSD WB	Yes
95600100	BY122P G5 LED300S/840 PSU NB	No
95601800	BY122P G5 LED300S/840 PSU WB	No
95602500	BY122P G5 LED300S/840 PSD NB	Yes

Order Code	Full Product Name	Dimmable
95603200	BY122P G5 LED300S/840 PSD WB	Yes
95568400	BY121P G5 LED200S/840 PSU NB	No
95569100	BY121P G5 LED200S/840 PSU WB	No
95570700	BY121P G5 LED105S/840 PSD NB	Yes
95571400	BY121P G5 LED105S/840 PSD WB	Yes
95572100	BY121P G5 LED200S/840 PSD NB	Yes
95573800	BY121P G5 LED200S/840 PSD WB	Yes
95576900	BY121P G5 LED200S/865 PSU NB	No
95577600	BY121P G5 LED200S/865 PSU WB	No
95578300	BY121P G5 LED105S/865 PSD NB	Yes
95579000	BY121P G5 LED105S/865 PSD WB	Yes

CoreLine Highbay Gen5

Order Code	Full Product Name	Dimmable
95580600	BY121P G5 LED200S/865 PSD NB	Yes
95581300	BY121P G5 LED200S/865 PSD WB	Yes
95598100	BY121P G5 LED150S/840 PSD NB	Yes
95599800	BY121P G5 LED150S/840 PSD WB	Yes
95566000	BY120P G5 LED105S/840 PSU NB	No
95567700	BY120P G5 LED105S/840 PSU WB	No
95574500	BY120P G5 LED105S/865 PSU NB	No
95575200	BY120P G5 LED105S/865 PSU WB	No
95596700	BY120P G5 LED150S/840 PSU NB	No

Order Code	Full Product Name	Dimmable
95597400	BY120P G5 LED150S/840 PSU WB	No
95590500	BY122X G5 LED105S/840 SIA NB H4	Yes
95591200	BY122X G5 LED105S/840 SIA WB H4	Yes
95592900	BY122X G5 LED200S/840 SIA NB H4	Yes
95593600	BY122X G5 LED200S/840 SIA WB H4	Yes
95594300	BY122X G5 LED250S/840 SIA NB H4	Yes
95595000	BY122X G5 LED250S/840 SIA WB H4	Yes
95604900	BY122X G5 LED300S/840 SIA NB H4	Yes
95605600	BY122X G5 LED300S/840 SIA WB H4	Yes

Approval and Application

Order Code	Full Product Name	Mech. impact protection code
95582000	BY122P G5 LED250S/840 PSU NB	IK08
95583700	BY122P G5 LED250S/840 PSU WB	IK08
95584400	BY122P G5 LED250S/865 PSU NB	IK08
95585100	BY122P G5 LED250S/865 PSU WB	IK08
95586800	BY122P G5 LED250S/840 PSD NB	IK08
95587500	BY122P G5 LED250S/840 PSD WB	IK08
95588200	BY122P G5 LED250S/865 PSD NB	IK08
95589900	BY122P G5 LED250S/865 PSD WB	IK08
95600100	BY122P G5 LED300S/840 PSU NB	IK08
95601800	BY122P G5 LED300S/840 PSU WB	IK08
95602500	BY122P G5 LED300S/840 PSD NB	IK08
95603200	BY122P G5 LED300S/840 PSD WB	IK08
95568400	BY121P G5 LED200S/840 PSU NB	IK08
95569100	BY121P G5 LED200S/840 PSU WB	IK08
95570700	BY121P G5 LED105S/840 PSD NB	IK08
95571400	BY121P G5 LED105S/840 PSD WB	IK08
95572100	BY121P G5 LED200S/840 PSD NB	IK08
95573800	BY121P G5 LED200S/840 PSD WB	IK08
95576900	BY121P G5 LED200S/865 PSU NB	IK08
95577600	BY121P G5 LED200S/865 PSU WB	IK08

Order Code	Full Product Name	Mech. impact protection code
95578300	BY121P G5 LED105S/865 PSD NB	IK08
95579000	BY121P G5 LED105S/865 PSD WB	IK08
95580600	BY121P G5 LED200S/865 PSD NB	IK08
95581300	BY121P G5 LED200S/865 PSD WB	IK08
95598100	BY121P G5 LED150S/840 PSD NB	IK08
95599800	BY121P G5 LED150S/840 PSD WB	IK08
95566000	BY120P G5 LED105S/840 PSU NB	IK08
95567700	BY120P G5 LED105S/840 PSU WB	IK08
95574500	BY120P G5 LED105S/865 PSU NB	IK08
95575200	BY120P G5 LED105S/865 PSU WB	IK08
95596700	BY120P G5 LED150S/840 PSU NB	IK08
95597400	BY120P G5 LED150S/840 PSU WB	IK08
95590500	BY122X G5 LED105S/840 SIA NB H4	IK05
95591200	BY122X G5 LED105S/840 SIA WB H4	IK05
95592900	BY122X G5 LED200S/840 SIA NB H4	IK05
95593600	BY122X G5 LED200S/840 SIA WB H4	IK05
95594300	BY122X G5 LED250S/840 SIA NB H4	IK05
95595000	BY122X G5 LED250S/840 SIA WB H4	IK05
95604900	BY122X G5 LED300S/840 SIA NB H4	IK05
95605600	BY122X G5 LED300S/840 SIA WB H4	IK05

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
95582000	BY122P G5 LED250S/840 PSU NB	(0.385, 0.380) SDCM<5
95583700	BY122P G5 LED250S/840 PSU WB	(0.385, 0.380) SDCM<5
95584400	BY122P G5 LED250S/865 PSU NB	(0.316, 0.332) SDCM<5
95585100	BY122P G5 LED250S/865 PSU WB	(0.316, 0.332) SDCM<5
95586800	BY122P G5 LED250S/840 PSD NB	(0.385, 0.380) SDCM<5
95587500	BY122P G5 LED250S/840 PSD WB	(0.385, 0.380) SDCM<5
95588200	BY122P G5 LED250S/865 PSD NB	(0.316, 0.332) SDCM<5
95589900	BY122P G5 LED250S/865 PSD WB	(0.316, 0.332) SDCM<5
95600100	BY122P G5 LED300S/840 PSU NB	(0.385, 0.380) SDCM<5
95601800	BY122P G5 LED300S/840 PSU WB	(0.385, 0.380) SDCM<5
95602500	BY122P G5 LED300S/840 PSD NB	(0.385, 0.380) SDCM<5
95603200	BY122P G5 LED300S/840 PSD WB	(0.385, 0.380) SDCM<5
95568400	BY121P G5 LED200S/840 PSU NB	(0.385, 0.380) SDCM<5
95569100	BY121P G5 LED200S/840 PSU WB	(0.385, 0.380) SDCM<5

Order Code	Full Product Name	Initial chromaticity
95570700	BY121P G5 LED105S/840 PSD NB	(0.385, 0.380) SDCM<5
95571400	BY121P G5 LED105S/840 PSD WB	(0.385, 0.380) SDCM<5
95572100	BY121P G5 LED200S/840 PSD NB	(0.385, 0.380) SDCM<5
95573800	BY121P G5 LED200S/840 PSD WB	(0.385, 0.380) SDCM<5
95576900	BY121P G5 LED200S/865 PSU NB	(0.316, 0.332) SDCM<5
95577600	BY121P G5 LED200S/865 PSU WB	(0.316, 0.332) SDCM<5
95578300	BY121P G5 LED105S/865 PSD NB	(0.316, 0.332) SDCM<5
95579000	BY121P G5 LED105S/865 PSD WB	(0.316, 0.332) SDCM<5
95580600	BY121P G5 LED200S/865 PSD NB	(0.316, 0.332) SDCM<5
95581300	BY121P G5 LED200S/865 PSD WB	(0.316, 0.332) SDCM<5
95598100	BY121P G5 LED150S/840 PSD NB	(0.385, 0.380) SDCM<5
95599800	BY121P G5 LED150S/840 PSD WB	(0.385, 0.380) SDCM<5
95566000	BY120P G5 LED105S/840 PSU NB	(0.385, 0.380) SDCM<5
95567700	BY120P G5 LED105S/840 PSU WB	(0.385, 0.380) SDCM<5

CoreLine Highbay Gen5

Order Code	Full Product Name	Initial chromaticity
95574500	BY120P G5 LED105S/865 PSU NB	(0.316, 0.332) SDCM<5
95575200	BY120P G5 LED105S/865 PSU WB	(0.316, 0.332) SDCM<5
95596700	BY120P G5 LED150S/840 PSU NB	(0.385, 0.380) SDCM<5
95597400	BY120P G5 LED150S/840 PSU WB	(0.385, 0.380) SDCM<5
95590500	BY122X G5 LED105S/840 SIA NB H4	(0.385, 0.380) SDCM<5
95591200	BY122X G5 LED105S/840 SIA WB H4	(0.385, 0.380) SDCM<5

Order Code	Full Product Name	Initial chromaticity
95592900	BY122X G5 LED200S/840 SIA NB H4	(0.385, 0.380) SDCM<5
95593600	BY122X G5 LED200S/840 SIA WB H4	(0.385, 0.380) SDCM<5
95594300	BY122X G5 LED250S/840 SIA NB H4	(0.385, 0.380) SDCM<5
95595000	BY122X G5 LED250S/840 SIA WB H4	(0.385, 0.380) SDCM<5
95604900	BY122X G5 LED300S/840 SIA NB H4	(0.385, 0.380) SDCM<5
95605600	BY122X G5 LED300S/840 SIA WB H4	(0.385, 0.380) SDCM<5

Application Conditions

Order Code	Full Product Name	Maximum dim level
95582000	BY122P G5 LED250S/840 PSU NB	Not applicable
95583700	BY122P G5 LED250S/840 PSU WB	Not applicable
95584400	BY122P G5 LED250S/865 PSU NB	Not applicable
95585100	BY122P G5 LED250S/865 PSU WB	Not applicable
95586800	BY122P G5 LED250S/840 PSD NB	20%
95587500	BY122P G5 LED250S/840 PSD WB	20%
95588200	BY122P G5 LED250S/865 PSD NB	20%
95589900	BY122P G5 LED250S/865 PSD WB	20%
95600100	BY122P G5 LED300S/840 PSU NB	Not applicable
95601800	BY122P G5 LED300S/840 PSU WB	Not applicable
95602500	BY122P G5 LED300S/840 PSD NB	13%
95603200	BY122P G5 LED300S/840 PSD WB	13%
95568400	BY121P G5 LED200S/840 PSU NB	Not applicable
95569100	BY121P G5 LED200S/840 PSU WB	Not applicable
95570700	BY121P G5 LED105S/840 PSD NB	20%
95571400	BY121P G5 LED105S/840 PSD WB	20%
95572100	BY121P G5 LED200S/840 PSD NB	10%
95573800	BY121P G5 LED200S/840 PSD WB	10%
95576900	BY121P G5 LED200S/865 PSU NB	Not applicable
95577600	BY121P G5 LED200S/865 PSU WB	Not applicable

Order Code	Full Product Name	Maximum dim level
95578300	BY121P G5 LED105S/865 PSD NB	20%
95579000	BY121P G5 LED105S/865 PSD WB	20%
95580600	BY121P G5 LED200S/865 PSD NB	10%
95581300	BY121P G5 LED200S/865 PSD WB	10%
95598100	BY121P G5 LED150S/840 PSD NB	13%
95599800	BY121P G5 LED150S/840 PSD WB	13%
95566000	BY120P G5 LED105S/840 PSU NB	Not applicable
95567700	BY120P G5 LED105S/840 PSU WB	Not applicable
95574500	BY120P G5 LED105S/865 PSU NB	Not applicable
95575200	BY120P G5 LED105S/865 PSU WB	Not applicable
95596700	BY120P G5 LED150S/840 PSU NB	Not applicable
95597400	BY120P G5 LED150S/840 PSU WB	Not applicable
95590500	BY122X G5 LED105S/840 SIA NB H4	1%
95591200	BY122X G5 LED105S/840 SIA WB H4	1%
95592900	BY122X G5 LED200S/840 SIA NB H4	1%
95593600	BY122X G5 LED200S/840 SIA WB H4	1%
95594300	BY122X G5 LED250S/840 SIA NB H4	1%
95595000	BY122X G5 LED250S/840 SIA WB H4	1%
95604900	BY122X G5 LED300S/840 SIA NB H4	1%
95605600	BY122X G5 LED300S/840 SIA WB H4	1%

