



CoreLine Trunking Gen2 – Innovative LED light lines have never been so simple

CoreLine Trunking Gen2

CoreLine Trunking Gen2 is a light-line system that is designed for simplicity. It comes in a choice of lengths, flux packages and beam shapes to suit every project and application. Easy to use and integrate with spots and sensors, CoreLine Trunking Gen2 provides consistent, high-quality lighting with added protection against accidental water ingress. The innovative system is also easy to assemble and install for faster retrofits and refurbishments.

Benefits

- Optimized, efficient design and light effect
- Consistent, high-quality light – no Color over Angle or striping artefacts
- Improved light continuity
- Easy to order, assemble and install
- InterAct ready for enhanced use in Retail and Industry applications

Features


- Intuitive, single layer architecture – only 2 12NCs needed to create a line
- Choice of 3 lengths, each with 3 flux packages
- 8 different optics with consistent light quality
- Dedicated sensor units to upgrade to InterAct system propositions
- Lumen maintenance @ 50,000 hours – L80
- Available as trunking and standalone versions

CoreLine Trunking Gen2

Application

- Food and Large Retailers
- Warehouses
- Manufacturing

Dimensional drawing



Product details



CoreLine Trunking Gen2 Half Blind

CoreLine Trunking Gen2

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC plus mark
Flammability mark	-
Glow-wire test	Temperature 850 °C, duration 30 s
Light source replaceable	No
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	-20 to +35 °C
Mechanical and Housing	
Housing Color	White RAL9016
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

General Information (1/2)

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Product family code
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	-	-	1 unit	LL234X
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	-	-	1 unit	LL234X
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	-	-	1 unit	LL234X
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	-	-	1 unit	LL234X
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	-	-	1 unit	LL212X
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	-	-	1 unit	LL212X
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	-	-	1 unit	LL212X
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	-	-	1 unit	LL212X
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	-	-	1 unit	LL212X
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	-	-	1 unit	LL217X
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	-	-	1 unit	LL217X
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	-	-	1 unit	LL217X
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	120S	-	1 unit	LL217X
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	120S	-	1 unit	LL217X
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	120S	Visible light communication	1 unit	LL217X
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	120S	-	1 unit	LL217X
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	80S	-	1 unit	LL217X
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	80S	Visible light communication	1 unit	LL217X
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	80S	-	1 unit	LL217X
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	80S	-	1 unit	LL217X
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	80S	-	1 unit	LL217X
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	80S	-	1 unit	LL217X
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	80S	-	1 unit	LL217X
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	160S	-	2 units	LL234X
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	160S	-	2 units	LL234X
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	160S	Visible light communication	2 units	LL234X
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	160S	-	2 units	LL234X

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Product family code
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	160S	-	2 units	LL234X
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	240S	-	2 units	LL234X
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	240S	-	2 units	LL234X
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	240S	Visible light communication	2 units	LL234X
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	240S	-	2 units	LL234X
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	240S	-	2 units	LL234X
910925867552	LL234X 160S/840 2x PSD O 7x2.5	160S	-	2 units	LL234X
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	160S	-	2 units	LL234X
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	160S	-	2 units	LL234X
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	160S	Visible light communication	2 units	LL234X
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	160S	-	2 units	LL234X
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	160S	-	2 units	LL234X
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	80S	-	1 unit	LL217X
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	90S	-	2 units	LL234X
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	-	-	1 unit	LL234X
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	-	-	2 units	LL234X
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	-	-	1 unit	LL217X
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	-	-	2 units	LL234X
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	-	-	1 unit	LL234X
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	-	-	1 unit	LL217X
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	-	-	1 unit	LL217X
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	-	-	1 unit	LL234X
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	-	-	1 unit	LL234X
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	-	-	1 unit	LL234X
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	-	-	1 unit	LL234X
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	-	-	1 unit	LL234X
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	-	-	1 unit	LL234X

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Product family code
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	-	-	1 unit	LL234X
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	-	-	1 unit	LL234X
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	-	-	1 unit	LL234X
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	-	-	1 unit	LL234X
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	-	-	1 unit	LL217X
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	-	-	1 unit	LL212X
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	-	-	1 unit	LL212X
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	-	-	1 unit	LL212X
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	-	-	1 unit	LL212X
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	-	-	1 unit	LL212X
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	-	-	1 unit	LL212X
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	-	-	1 unit	LL217X
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	-	-	1 unit	LL217X
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	-	-	1 unit	LL217X
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	-	-	1 unit	LL217X
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	-	-	1 unit	LL217X
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	-	-	1 unit	LL217X
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	-	-	2 units	LL234X
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	-	-	2 units	LL234X
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	-	-	2 units	LL234X
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	-	-	2 units	LL234X
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	-	-	2 units	LL234X
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	-	-	2 units	LL234X
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	-	-	1 unit	LL234X
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	-	-	1 unit	LL234X
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	-	-	1 unit	LL234X
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	-	-	1 unit	LL234X
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	-	-	1 unit	LL217X
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	-	-	1 unit	LL217X
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	-	-	1 unit	LL217X
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	-	-	1 unit	LL217X
910925867498	LL217X 80S/840 1x PSD BV WB	-	-	1 unit	LL217X
910925867525	LL217X 120S/840 1x PSU BV WB HE	120S	-	1 unit	LL217X
910925867539	LL234X 240S/840 2x PSD BV WB HE	240S	-	2 units	LL234X
910925867550	LL234X 160S/840 2x PSU BV WB	160S	-	2 units	LL234X

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Product family code
910925867698	LL217X 80S/840 1X PSU BV WB TW3	-	-	1 unit	LL217X
910925867699	LL234X 160S/840 1X PSU BV WB TW3	-	-	1 unit	LL234X
910925867701	LL234X 160S/840 2X PSU BV WB TW3	-	-	2 units	LL234X
910925868236	LL217X 45S/840 1x PSU BV WB	-	-	1 unit	LL217X
910925868237	LL217X 45S/840 1x PSD BV WB	-	-	1 unit	LL217X
910925868238	LL217X 45S/840 1x PSU BV O	-	-	1 unit	LL217X
910925868239	LL217X 45S/840 1x PSD BV O	-	-	1 unit	LL217X
910925868240	LL217X 80S/840 1x PSU BV WB	-	-	1 unit	LL217X
910925868241	LL217X 80S/840 1x PSU BV O	-	-	1 unit	LL217X
910925868242	LL217X 80S/840 1x PSD BV O	-	-	1 unit	LL217X
910925868391	LL217X 120S/840 1x PSU BV WB TW3	-	-	1 unit	LL217X
910925868392	LL217X 120S/840 1x PSU BV MB TW3	-	-	1 unit	LL217X
910925868393	LL217X 120S/840 1x PSU BV NB TW3	-	-	1 unit	LL217X
910925868394	LL217X 80S/840 1x PSU BV MB TW3	-	-	1 unit	LL217X
910925868395	LL217X 80S/840 1x PSU BV NB TW3	-	-	1 unit	LL217X
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	80S	-	1 unit	LL217X
910925867535	LL217X 80S/840 1x PSD O 7x2.5	80S	-	1 unit	LL217X
910925867551	LL234X 160S/840 2x PSD O 7x1.5	160S	-	2 units	LL234X
910925867556	LL234X 160S/840 2x PSU O 5x1.5	160S	-	2 units	LL234X
910925867557	LL234X 160S/840 2x PSU O 5x2.5	160S	-	2 units	LL234X

General Information (2/2)

Order Code	Full Product Name	Service tag	Order Code	Full Product Name	Service tag
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	-	910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	Yes
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	-	910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	Yes
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	-	910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	Yes
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	-	910925867536	LL217X 80S/840 1x PSD WB 7x2.5	Yes
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	Yes	910925867537	LL217X 80S/840 1x PSU WB 5x1.5	Yes
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	Yes	910925867538	LL217X 80S/840 1x PSU WB 5x2.5	Yes
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	Yes	910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	Yes
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	Yes	910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	Yes
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	Yes	910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	Yes
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	Yes	910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	Yes
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	Yes	910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	Yes
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	Yes	910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	Yes
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	Yes	910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	Yes
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	Yes	910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	Yes
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	Yes	910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	Yes
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	Yes	910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	Yes
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	Yes	910925867552	LL234X 160S/840 2x PSD O 7x2.5	Yes

CoreLine Trunking Gen2

Order Code	Full Product Name	Service tag
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	Yes
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	Yes
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	Yes
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	Yes
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	Yes
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	Yes
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	Yes
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	Yes
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	Yes
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	Yes
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	Yes
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	Yes
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	Yes
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	Yes
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	Yes
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	Yes
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	Yes
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	Yes
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	Yes
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	Yes
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	Yes
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	Yes
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	Yes
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	Yes
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	Yes
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	Yes
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	Yes
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	Yes
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	Yes
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	Yes
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	Yes
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	Yes
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	Yes
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	Yes
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	Yes
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	Yes
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	Yes
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	Yes

Order Code	Full Product Name	Service tag
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	Yes
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	Yes
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	Yes
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	Yes
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	Yes
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	-
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	-
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	-
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	-
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	-
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	-
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	-
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	-
910925867498	LL217X 80S/840 1x PSD BV WB	Yes
910925867525	LL217X 120S/840 1x PSU BV WB HE	Yes
910925867539	LL234X 240S/840 2x PSD BV WB HE	Yes
910925867550	LL234X 160S/840 2x PSU BV WB	Yes
910925867698	LL217X 80S/840 1X PSU BV WB TW3	Yes
910925867699	LL234X 160S/840 1X PSU BV WB TW3	Yes
910925867701	LL234X 160S/840 2X PSU BV WB TW3	Yes
910925868236	LL217X 45S/840 1x PSU BV WB	Yes
910925868237	LL217X 45S/840 1x PSD BV WB	Yes
910925868238	LL217X 45S/840 1x PSU BV O	Yes
910925868239	LL217X 45S/840 1x PSD BV O	Yes
910925868240	LL217X 80S/840 1x PSU BV WB	Yes
910925868241	LL217X 80S/840 1x PSU BV O	Yes
910925868242	LL217X 80S/840 1x PSD BV O	Yes
910925868391	LL217X 120S/840 1x PSU BV WB TW3	Yes
910925868392	LL217X 120S/840 1x PSU BV MB TW3	Yes
910925868393	LL217X 120S/840 1x PSU BV NB TW3	Yes
910925868394	LL217X 80S/840 1x PSU BV MB TW3	Yes
910925868395	LL217X 80S/840 1x PSU BV NB TW3	Yes
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	Yes
910925867535	LL217X 80S/840 1x PSD O 7x2.5	Yes
910925867551	LL234X 160S/840 2x PSD O 7x1.5	Yes
910925867556	LL234X 160S/840 2x PSU O 5x1.5	Yes
910925867557	LL234X 160S/840 2x PSU O 5x2.5	Yes

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated)	Luminous	Optic type
		(Nom)	Flux	
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	161 lm/W	4,500 lm	Wide beam
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	160 lm/W	8,000 lm	Wide beam
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	161 lm/W	4,500 lm	Narrow beam
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	160 lm/W	8,000 lm	Narrow beam

Order Code	Full Product Name	Luminous Efficacy (rated)	Luminous	Optic type
		(Nom)	Flux	
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	161 lm/W	5,300 lm	Wide beam
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	156 lm/W	5,300 lm	Wide beam
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	161 lm/W	5,300 lm	Wide beam
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	161 lm/W	5,300 lm	Wide beam

CoreLine Trunking Gen2

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	161 lm/W	5,300 lm	Wide beam
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	150 lm/W	12,000 lm	Wide beam
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	160 lm/W	8,000 lm	Wide beam
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	160 lm/W	8,000 lm	Wide beam
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	152 lm/W	12,000 lm	Wide beam
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	152 lm/W	12,000 lm	Wide beam
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	152 lm/W	12,000 lm	Wide beam
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	150 lm/W	12,000 lm	Wide beam
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	165 lm/W	8,000 lm	Wide beam
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	165 lm/W	8,000 lm	Wide beam
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	163 lm/W	8,000 lm	Wide beam
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	163 lm/W	8,000 lm	Wide beam
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	160 lm/W	8,000 lm	Wide beam
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	157 lm/W	8,000 lm	Wide beam
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	157 lm/W	8,000 lm	Wide beam
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	165 lm/W	16,000 lm	Wide beam
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	165 lm/W	16,000 lm	Wide beam
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	165 lm/W	16,000 lm	Wide beam
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	165 lm/W	16,000 lm	Wide beam
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	165 lm/W	16,000 lm	Wide beam
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	152 lm/W	24,000 lm	Wide beam
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	152 lm/W	24,000 lm	Wide beam
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	152 lm/W	24,000 lm	Wide beam
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	150 lm/W	24,000 lm	Wide beam
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	150 lm/W	24,000 lm	Wide beam

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925867552	LL234X 160S/840 2x PSD O 7x2.5	150 lm/W	15,000 lm	Symmetrical
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	160 lm/W	16,000 lm	Wide beam
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	160 lm/W	16,000 lm	Wide beam
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	160 lm/W	16,000 lm	Wide beam
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	157 lm/W	16,000 lm	Wide beam
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	157 lm/W	16,000 lm	Wide beam
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	165 lm/W	8,000 lm	Wide beam
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	161 lm/W	9,000 lm	Wide beam
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	160 lm/W	16,000 lm	Wide beam
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	157 lm/W	16,000 lm	Narrow beam
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	157 lm/W	8,000 lm	Narrow beam
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	161 lm/W	9,000 lm	Wide beam
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	158 lm/W	9,000 lm	Wide beam
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	161 lm/W	4,500 lm	Wide beam
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	164 lm/W	4,500 lm	Wide beam
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	161 lm/W	4,500 lm	Wide beam
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	150 lm/W	4,500 lm	Wide beam
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	157 lm/W	8,000 lm	Wide beam
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	160 lm/W	8,000 lm	Wide beam
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	161 lm/W	4,500 lm	Narrow beam
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	150 lm/W	4,500 lm	Narrow beam
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	157 lm/W	8,000 lm	Narrow beam
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	160 lm/W	8,000 lm	Narrow beam
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	158 lm/W	9,000 lm	Narrow beam
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	160 lm/W	16,000 lm	Narrow beam

CoreLine Trunking Gen2

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	160 lm/W	8,000 lm	Narrow beam
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	161 lm/W	3,000 lm	Medium beam
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	161 lm/W	3,000 lm	Narrow beam
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	160 lm/W	5,300 lm	Medium beam
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	160 lm/W	5,300 lm	Narrow beam
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	163 lm/W	8,000 lm	Medium beam
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	163 lm/W	8,000 lm	Narrow beam
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	161 lm/W	4,500 lm	Medium beam
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	161 lm/W	4,500 lm	Narrow beam
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	157 lm/W	8,000 lm	Medium beam
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	157 lm/W	8,000 lm	Narrow beam
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	150 lm/W	12,000 lm	Medium beam
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	150 lm/W	12,000 lm	Narrow beam
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	161 lm/W	9,000 lm	Medium beam
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	161 lm/W	9,000 lm	Narrow beam
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	157 lm/W	16,000 lm	Medium beam
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	157 lm/W	16,000 lm	Narrow beam
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	150 lm/W	24,000 lm	Medium beam
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	150 lm/W	24,000 lm	Narrow beam
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	158 lm/W	9,000 lm	Wide beam
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	160 lm/W	16,000 lm	Wide beam
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	158 lm/W	9,000 lm	Narrow beam
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	160 lm/W	16,000 lm	Narrow beam
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	161 lm/W	4,500 lm	Wide beam
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	160 lm/W	8,000 lm	Wide beam
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	161 lm/W	4,500 lm	Narrow beam

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	160 lm/W	8,000 lm	Narrow beam
910925867498	LL217X 80S/840 1x PSD BV WB	160 lm/W	8,000 lm	Wide beam
910925867525	LL217X 120S/840 1x PSU BV WB HE	150 lm/W	12,000 lm	Wide beam
910925867539	LL234X 240S/840 2x PSD BV WB HE	152 lm/W	24,000 lm	Wide beam
910925867550	LL234X 160S/840 2x PSU BV WB	157 lm/W	16,000 lm	Wide beam
910925867698	LL217X 80S/840 1X PSU BV WB TW3	157 lm/W	8,000 lm	Wide beam
910925867699	LL234X 160S/840 1X PSU BV WB TW3	157 lm/W	16,000 lm	Wide beam
910925867701	LL234X 160S/840 2X PSU BV WB TW3	157 lm/W	16,000 lm	Wide beam
910925868236	LL217X 45S/840 1x PSU BV WB	161 lm/W	4,500 lm	Wide beam
910925868237	LL217X 45S/840 1x PSD BV WB	164 lm/W	4,500 lm	Wide beam
910925868238	LL217X 45S/840 1x PSU BV O	150 lm/W	4,200 lm	Symmetrical
910925868239	LL217X 45S/840 1x PSD BV O	150 lm/W	4,200 lm	Symmetrical
910925868240	LL217X 80S/840 1x PSU BV WB	157 lm/W	8,000 lm	Wide beam
910925868241	LL217X 80S/840 1x PSU BV O	148 lm/W	7,400 lm	Symmetrical
910925868242	LL217X 80S/840 1x PSD BV O	148 lm/W	7,400 lm	Symmetrical
910925868391	LL217X 120S/840 1x PSU BV WB TW3	139 lm/W	12,000 lm	Wide beam
910925868392	LL217X 120S/840 1x PSU BV MB TW3	139 lm/W	12,000 lm	Medium beam
910925868393	LL217X 120S/840 1x PSU BV NB TW3	139 lm/W	12,000 lm	Narrow beam
910925868394	LL217X 80S/840 1x PSU BV MB TW3	160 lm/W	8,000 lm	Medium beam
910925868395	LL217X 80S/840 1x PSU BV NB TW3	160 lm/W	8,000 lm	Narrow beam
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	148 lm/W	7,400 lm	Symmetrical
910925867535	LL217X 80S/840 1x PSD O 7x2.5	148 lm/W	7,400 lm	Symmetrical
910925867551	LL234X 160S/840 2x PSD O 7x1.5	150 lm/W	15,000 lm	Symmetrical
910925867556	LL234X 160S/840 2x PSU O 5x1.5	150 lm/W	15,000 lm	Symmetrical
910925867557	LL234X 160S/840 2x PSU O 5x2.5	150 lm/W	15,000 lm	Symmetrical

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	27.5 W
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	50 W
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	27.5 W
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	50 W
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	33 W
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	34 W
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	33 W
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	33 W
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	33 W
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	80 W
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	50 W
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	50 W
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	79 W
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	79 W
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	79 W
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	80 W
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	48.5 W
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	48 W
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	49 W
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	49 W
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	50 W
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	51 W
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	51 W
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	97 W
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	97 W
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	96 W
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	98 W
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	98 W
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	158 W
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	158 W
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	158 W
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	160 W
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	160 W
910925867552	LL234X 160S/840 2x PSD O 7x2.5	100 W
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	100 W
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	100 W
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	100 W
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	102 W
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	102 W
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	48.5 W
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	55 W
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	98 W
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	102 W
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	51 W
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	56 W
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	57 W
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	28 W
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	27.5 W
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	28 W
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	27.5 W
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	51 W

Order Code	Full Product Name	Power Consumption
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	50 W
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	28 W
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	27.5 W
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	51 W
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	50 W
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	57 W
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	98 W
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	50 W
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	19 W
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	19 W
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	33 W
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	33 W
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	49 W
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	49 W
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	28 W
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	28 W
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	50 W
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	50 W
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	79 W
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	79 W
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	56 W
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	56 W
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	102 W
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	102 W
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	158 W
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	158 W
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	57 W
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	100 W
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	57 W
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	100 W
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	27.5 W
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	50 W
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	27.5 W
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	50 W
910925867498	LL217X 80S/840 1x PSD BV WB	50 W
910925867525	LL217X 120S/840 1x PSU BV WB HE	80 W
910925867539	LL234X 240S/840 2x PSD BV WB HE	158 W
910925867550	LL234X 160S/840 2x PSU BV WB	102 W
910925867698	LL217X 80S/840 1X PSU BV WB TW3	51 W
910925867699	LL234X 160S/840 1X PSU BV WB TW3	102 W
910925867701	LL234X 160S/840 2X PSU BV WB TW3	102 W
910925868236	LL217X 45S/840 1x PSU BV WB	28 W
910925868237	LL217X 45S/840 1x PSD BV WB	27.5 W
910925868238	LL217X 45S/840 1x PSU BV O	28 W
910925868239	LL217X 45S/840 1x PSD BV O	27.5 W
910925868240	LL217X 80S/840 1x PSU BV WB	51 W
910925868241	LL217X 80S/840 1x PSU BV O	51 W
910925868242	LL217X 80S/840 1x PSD BV O	50 W
910925868391	LL217X 120S/840 1x PSU BV WB TW3	80 W
910925868392	LL217X 120S/840 1x PSU BV MB TW3	80 W
910925868393	LL217X 120S/840 1x PSU BV NB TW3	80 W

CoreLine Trunking Gen2

Order Code	Full Product Name	Power Consumption
910925868394	LL217X 80S/840 1x PSU BV MB TW3	50 W
910925868395	LL217X 80S/840 1x PSU BV NB TW3	50 W
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	48.5 W
910925867535	LL217X 80S/840 1x PSD O 7x2.5	50 W

Order Code	Full Product Name	Power Consumption
910925867551	LL234X 160S/840 2x PSD O 7x1.5	100 W
910925867556	LL234X 160S/840 2x PSU O 5x1.5	102 W
910925867557	LL234X 160S/840 2x PSU O 5x2.5	102 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	Yes
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	Yes
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	Yes
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	Yes
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	No
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	Yes
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	Yes
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	Yes
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	No
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	No
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	Yes
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	Yes
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	Yes
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	Yes
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	Yes
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	No
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	Yes
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	Yes
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	No
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	No
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	Yes
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	No
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	No
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	Yes
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	Yes
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	Yes
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	No
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	No
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	Yes
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	Yes
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	Yes
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	No
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	No
910925867552	LL234X 160S/840 2x PSD O 7x2.5	Yes
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	Yes
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	Yes
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	Yes
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	No
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	No
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	Yes
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	Yes
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	Yes
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	No
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	No

Order Code	Full Product Name	Dimmable
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	No
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	Yes
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	No
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	Yes
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	No
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	Yes
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	No
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	Yes
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	No
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	Yes
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	No
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	Yes
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	Yes
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	Yes
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	Yes
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	No
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	No
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	No
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	No
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	No
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	No
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	No
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	No
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	No
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	No
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	No
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	No
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	No
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	No
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	No
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	No
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	No
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	No
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	Yes
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	Yes
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	Yes
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	Yes
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	Yes
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	Yes
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	Yes
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	Yes
910925867498	LL217X 80S/840 1x PSD BV WB	Yes
910925867525	LL217X 120S/840 1x PSU BV WB HE	No
910925867539	LL234X 240S/840 2x PSD BV WB HE	Yes

CoreLine Trunking Gen2

Order Code	Full Product Name	Dimmable
910925867550	LL234X 160S/840 2x PSU BV WB	No
910925867698	LL217X 80S/840 1X PSU BV WB TW3	No
910925867699	LL234X 160S/840 1X PSU BV WB TW3	No
910925867701	LL234X 160S/840 2X PSU BV WB TW3	No
910925868236	LL217X 45S/840 1x PSU BV WB	No
910925868237	LL217X 45S/840 1x PSD BV WB	Yes
910925868238	LL217X 45S/840 1x PSU BV O	No
910925868239	LL217X 45S/840 1x PSD BV O	Yes
910925868240	LL217X 80S/840 1x PSU BV WB	No
910925868241	LL217X 80S/840 1x PSU BV O	No
910925868242	LL217X 80S/840 1x PSD BV O	Yes

Order Code	Full Product Name	Dimmable
910925868391	LL217X 120S/840 1x PSU BV WB TW3	No
910925868392	LL217X 120S/840 1x PSU BV MB TW3	No
910925868393	LL217X 120S/840 1x PSU BV NB TW3	No
910925868394	LL217X 80S/840 1x PSU BV MB TW3	No
910925868395	LL217X 80S/840 1x PSU BV NB TW3	No
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	Yes
910925867535	LL217X 80S/840 1x PSD O 7x2.5	Yes
910925867551	LL234X 160S/840 2x PSD O 7x1.5	Yes
910925867556	LL234X 160S/840 2x PSU O 5x1.5	No
910925867557	LL234X 160S/840 2x PSU O 5x2.5	No

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	Not applicable	Yes
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	Not applicable	Yes
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	Not applicable	Yes
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	Not applicable	Yes
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	Not applicable	Yes
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	Not applicable	Yes
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	Not applicable	Yes
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	Not applicable	Yes
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	Not applicable	Yes

CoreLine Trunking Gen2

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	Not applicable	Yes
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	Not applicable	Yes
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	Not applicable	Yes
910925867552	LL234X 160S/840 2x PSD O 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	Not applicable	Yes
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	Not applicable	Yes
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	Not applicable	Yes
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	Not applicable	Yes
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	Not applicable	Yes
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	Not applicable	Yes

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	Not applicable	Yes
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	Not applicable	Yes
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	Not applicable	Yes
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	Not applicable	Yes
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	Not applicable	Yes
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	Not applicable	Yes
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	Not applicable	Yes
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	Not applicable	Yes
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	Not applicable	Yes
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	Not applicable	Yes
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	Not applicable	Yes
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	Not applicable	Yes
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	Not applicable	Yes

CoreLine Trunking Gen2

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	Not applicable	Yes
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	Not applicable	Yes
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	Not applicable	Yes
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	Not applicable	Yes
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	Not applicable	Yes
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	Not applicable	Yes
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	Not applicable	Yes
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	Not applicable	Yes
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	Not applicable	Yes
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867498	LL217X 80S/840 1x PSD BV WB	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867525	LL217X 120S/840 1x PSU BV WB HE	Not applicable	Yes
910925867539	LL234X 240S/840 2x PSD BV WB HE	1%	Yes (relates to presence/movement detection and daylight harvesting)

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910925867550	LL234X 160S/840 2x PSU BV WB	Not applicable	Yes
910925867698	LL217X 80S/840 1x PSU BV WB TW3	Not applicable	Yes
910925867699	LL234X 160S/840 1x PSU BV WB TW3	Not applicable	Yes
910925867701	LL234X 160S/840 2x PSU BV WB TW3	Not applicable	Yes
910925868236	LL217X 45S/840 1x PSU BV WB	Not applicable	Yes
910925868237	LL217X 45S/840 1x PSD BV WB	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868238	LL217X 45S/840 1x PSU BV O	Not applicable	Yes
910925868239	LL217X 45S/840 1x PSD BV O	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868240	LL217X 80S/840 1x PSU BV WB	Not applicable	Yes
910925868241	LL217X 80S/840 1x PSU BV O	Not applicable	Yes
910925868242	LL217X 80S/840 1x PSD BV O	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868391	LL217X 120S/840 1x PSU BV WB TW3	Not applicable	Yes
910925868392	LL217X 120S/840 1x PSU BV MB TW3	Not applicable	Yes
910925868393	LL217X 120S/840 1x PSU BV NB TW3	Not applicable	Yes
910925868394	LL217X 80S/840 1x PSU BV MB TW3	Not applicable	Yes
910925868395	LL217X 80S/840 1x PSU BV NB TW3	Not applicable	Yes
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867535	LL217X 80S/840 1x PSD O 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867551	LL234X 160S/840 2x PSD O 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867556	LL234X 160S/840 2x PSU O 5x1.5	Not applicable	Yes
910925867557	LL234X 160S/840 2x PSU O 5x2.5	Not applicable	Yes

CoreLine Trunking Gen2

