



Philips GreenPower LED Interlighting 3.0

Length	2.0 m 1.95 m · 76.7 in	2.5 m 2.42 m · 95.3 in	Input voltage	200V – 400V	IP rating	IP66
Width	6.5 cm · 2.6 in	6.5 cm · 2.6 in	Beam angle	Bi-directional 120°	Ambient operating temp	0° C Min. · 40° C Max 40° F Min. · 104° F Max
Height	7.6 cm · 3.0 in	7.6 cm · 3.0 in	L90	36,000 hrs	Frequency	50/60 Hz
Weight	2.2 kg · 4.9 lb	2.5 kg · 5.5 lb	L70	50,000 hrs	Power factor	> 0.90
			Warranty	5 year limited	Total harmonic distortion	<10%
			UL/CSA rated	Damp/wet		

Interlighting 3.0	12 NC	Power (W)	Amps 208V	Amps 240V	Amps 277V	Amps 347V	Photon Flux μmol/s	High Efficacy μmol/J
GP LED interlighting mod DR/B 250 HO NA	9290 015 55206	100	0.48	0.42	0.36	0.29	300	3.0
GP LED interlighting mod DR/B 200 HO NA	9290 015 55506	81	0.39	0.34	0.29	0.23	240	3.0
GP LED interlighting mod DR/B 250 RO NA	9290 015 55006	79	0.38	0.33	0.29	0.23	220	2.8
GP LED interlighting mod DR/B 200 RO NA	9290 015 55306	64	0.31	0.27	0.23	0.18	175	2.7

Interlighting Accessories	12 NC
IL 3.0 Mounting Bracket 3.3 (171 mm)	9290 016 13106
IL 3.0 Mounting Bracket 3.4 (271 mm)	9290 016 13206
IL 3.0 Mains Power Cable (6.5 m)	9290 015 56606

Interlighting Accessories	12 NC
IL 3.0 Jumper Cable (1 m)	9290 015 56906
IL 3.0 Female Connector	9290 015 99406
End Cap (universal)	9290 009 15606