



# Top Selling Stock Ready Luminaires

2023 Q1 Select Edition

**LIGHTOLIER**  
by @signify

**Day-Brite**  
**CFI**  
by @signify

**KEENE**  
by @signify

# Top Stock Ready Items

**Stock, Sell, and Restock with  
Signify's best movers!**

Save time and improve efficiencies by consolidating your stock purchases with Signify's top stocking product families which includes a wide range of unique adjustable color temperature and/or lumen outputs field selectable product lines. These products are priced right and ready to go!

For the full portfolio of Stock Ready items,  
visit [www.signify.com/en-ca/support/stock-partner-program](http://www.signify.com/en-ca/support/stock-partner-program)



## A long history of excellence

As the global leader in lighting for more than 130 years, Signify has the know-how and most comprehensive portfolio to meet any application. We achieved 100% carbon neutrality in 2020. We are number 1 in conventional lamps, LED and Connected lighting. We have over 17,750 patents. We invest 4.8% of total sales in R&D which is two times our nearest competitor! We understand that partnerships are more than sales.

Let's grow together. We are ready to go with you.

Quick and reliable service out of our distribution centers.



## Find just what you need

Our Stock Ready portfolio makes it easy to find just what you need. Our products are designed for easy ordering through Signify's MyLighting portal. easy to install with minimal steps, and competitively priced to meet the demands of budget conscious projects focused on cost and energy. Distributors can also benefit from our Stock Ready program which offers deals on freight, guaranteed sales, price change reimbursement, delistment notifications, marketing support, merchandising, and more.

### Certifications & labels



interact  
ready.

Indoor luminaires



Retrofit Downlight 2




Comm. Retrofit Dwnlt 3





Flat Downlight 4



Surface Mount Downlight 5



Downlight/Gimbal 6




Select Backlit Panel 7



SDS Selectable Strip 8



FCY Value High Bay 9



NWL Wraparound 10



HCY Sealed High Bay 11

Outdoor luminaires



Wall Pack Gen2 dual select 12




Adjustable Slim Wall Pack 13



Slim Flood 14

# Indoor & Outdoor luminaires



# Retrofit Downlight

An LED retrofit as  
**easy as snap and click**

Hassle-free install will save you time  
and frustration on the job site. You may  
not even need to open your toolbox.

**Top selling  
residential  
product**



## Why choose Retrofit Downlight?

- Adjustable color temperature switch allows you to make choices while you install or afterward
- Utilizes existing frames to make replacing old downlighting and upgrading to LED a truly easy task
- Flexible springs allow for installation without tools
- Quick-connect plug and medium-based socket adapter means no extra accessories to purchase



## Retrofit Downlight

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
<b>Retrofit Downlight 4" Round</b>				
RD4R79301W	190096131976	Retrofit Downlight 4" Round 700 lumen 90CRI 3000K 120V	Energy Star	16/560
RD4R79SCT1W	190096131952	Retrofit Downlight 4" Round 700 lumen 90CRI 5CCT 120V	Energy Star	12/300
<b>Retrofit Downlight 5/6" Round</b>				
RD6R99301W	190096131983	Retrofit Downlight 6" Round 900 lumen 90CRI 3000K 120V	Energy Star	16/560
RD6R99SCT1W	190096131969	Retrofit Downlight 6" Round 900 lumen 90CRI 5CCT 120V	Energy Star	12/300



# Commercial Retrofit Downlight

**Bright, brighter, brightest**

Will reduce onsite time and headaches for busy installers with its adjustable lumen and color output switch.



## Why choose Commercial Retrofit Downlight?

- Adjustable lumen output and color temperature switch allows you to make choices while you install or afterward
- Great for different ceiling heights and different light level needs
- Sturdy metal clips provide a solid fit and easy installation
- Out-of-the-box pre-wired with flexible metal conduit
- 50,000 hour rated life (L70)


### Commercial Retrofit Downlight (dual select)

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
Commercial Retrofit Downlight (dual select) Selectable CCT Round				
CR4RLMCCT	190096131266	Commercial Retrofit Downlight DualSelect, 4" Round, 500-1000lm, 3000K / 3500K / 4000K (CRI 90), 120-347V	Energy Star	8/288
CR6RLMCCT	190096131273	Commercial Retrofit Downlight 700-1500 lumen 90CRI 3000K-3500K-4000K White Finish 120-347V	Energy Star	4/120
CR8RLMCCT	190096131280	Commercial Retrofit Downlight 1000-2000 lumen 90CRI 3000K-3500K-4000K White Finish 120-347V	Energy Star	4/72
CR10RLMCCT	190096131297	Commercial Retrofit Downlight DualSelect, 9.5" Round, 2000-3000lm, 3000K / 3500K / 4000K (CRI 90), 120-347V	Energy Star	4/48



# Flat Downlight

Make your next lighting project faster and easier, with a product from a name you can trust.



Flat Downlight dual select

## Why choose Flat Downlight?

- FD dual select: 5 field selectable CCT and multiple lumen selection options
- Quick and easy installation without frame or reflector
- Junction box clips to luminaire meeting National Electric Code (NEC)
- Dimmable to 10%
- Lifetime >50,000 hours (L70)
- IC-rated for insulation direct contact
- UL1598 wet location rated



## Flat Downlight

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
Flat Downlight Dual Select 3" Round				
FD3R4ESCT1W	190096196166	Flat Downlight Round 3" 480lm 5CCT, TRIAC to 5%, 90 CRI	Energy Star	12/288
FD3RSLMZ10SCTUW	190096131679	Flat Downlight Round Dualselect 3" 370/500 Lumen 5CCT UNV, 0-10V Dimming	Energy Star	12/288
Flat Downlight Dual Select 4" Round				
FD4R7ESCT1W	190096131686	Flat Downlight Round 4" 700 Lumen 5CCT 120V, TRIAC to 5%, 90 CRI	Energy Star	20/360
FD4RSLMZ10SCTUW	190096131693	Flat Downlight Round Dualselect 4" 540/700 Lumen 5CCT UNV, 0-10V Dimming, 90 CRI	Energy Star	12/216
Flat Downlight Dual Select 5" Round				
FD5R9ESCT1W	190096196173	Flat Downlight Round 5" 900lm 5CCT TRIAC to 5%, 90 CRI	Energy Star	6/180
FD5RSLMZ10SCTUW	190096131709	Flat Downlight Round Dualselect 5" 900/1100 Lumen 5CCT UNV, 0-10V Dimming, 90 CRI	Energy Star	6/180
Flat Downlight Dual Select 6" Round				
FD6R11ESCT1W	190096131716	Flat Downlight Round 6" 1100 Lumen 5CCT 120V, TRIAC to 5%, 90 CRI	Energy Star	10/300
FD6RSLMZ10SCTUW	190096131723	Flat Downlight Round Dualselect 6" 900/1100 Lumen 5CCT UNV, 0-10V Dimming, 90 CRI	Energy Star	6/180
Flat Downlight Dual Select 8" Round				
FD8R13ESCT1W	190096196180	Flat Downlight Round 8" 1300lm 5CCT TRIAC to 5%, 90 CRI	Energy Star	6/144
FD8RSLMZ10SCTUW	190096131730	Flat Downlight Round Dualselect 8" 1100/1300 Lumen 5CCT UNV, 0-10V Dimming, 90 CRI	Energy Star	6/144



Lumen Select Switch



CCT with Select Switch





# Surface Mount Downlight

The shallow ceiling **problem solver**

Ideal when faced with a challenging ceiling, but you still want a good-looking downlight.



## Why choose Surface Mount Downlight?

- Adjustable lumen output and color temperature switch allows you to make choices while you install or afterward
- Easy to install on standard J-boxes
- Surface mount downlight solves the problem of limited plenum space
- Glare controlling lens for comfortable light distribution
- Affordable alternative to Air-Seal IC recessed housings
- Support wire attached for easy installation

## Surface Mount Downlight

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
<b>Surface Mount Downlight 5" Round</b>				
SD5R7ESCT1W	190096131785	Surface Mount Round 5" 700 lumen 5CCT 120V	Energy Star	8/672
SD5RSLMZ10SCTUW	190096131792	Surface Mount Round Dualselect 5" 540/700 lumen 5CCT UNV	Energy Star	8/672
<b>Surface Mount Downlight 7" Round</b>				
SD7R10ESCT1W	190096131808	Surface Mount Round 7" 1000 lumen 5CCT 120V	Energy Star	8/360
SD7RSLMZ10SCTUW	190096131815	Surface Mount Round Dualselect 7" 800/1000 lumen 5CCT UNV	Energy Star	8/360
<b>Surface Mount Downlight 9" Round</b>				
SD9R12ESCT1W	190096196197	Surface Mount Round 9" 1200LM 5CCT 120V	Energy Star	8/192
SD9RSLMZ10SCTUW	190096131822	Surface Mount Round Dualselect 9" 900/1200 lumen 5CCT UNV	Energy Star	8/192
<b>Surface Mount Downlight 11" Round</b>				
SD11R15ESCT1W	190096196203	Surface Mount Round 11" 1500LM 5CCT 120V	Energy Star	6/162
SD11RSLMZ10SCTUW	190096131839	Surface Mount Round Dualselect 11" 1200/1500 lumen 5CCT UNV	Energy Star	6/162
<b>Surface Mount Downlight 14" Round</b>				
SD14R16ESCT1W	190096196210	Surface Mount Round 14" 1600LM 5CCT 120V	Energy Star	6/90
SD14RSLMZ10SCTUW	190096131846	Surface Mount Round Dualselect 14" 1600/2000 lumen 5CCT UNV	Energy Star	6/90



# Downlight and Gimbal

Provides an  
easy install solution



Downlight



Gimbal

## Why choose Downlight and Gimbal?

- Adjustable lumen output and color temperature switch allows you to make choices while your install or afterward
- Sizes: 3, 4, and 6 inch round
- Dimming: TRIAC down to 10%
- Installation: Easy to adjust at the time of installation
- Lifetime: L70 at 50,000 hours
- Listings: ENERGY STAR®, Title 24 (JA8-2016), damp location, ETL listed. Airseal IC.



## Downlight and Gimbal

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
<b>Downlight 3"</b>				
DL3R4ESCT1W	190096196234	Downlight Round 3" 400LM 5CCT 120V	Energy Star	8/320
DL3RSLMZ10SCTUW	190096131853	Downlight Round Dualselect 3" 370/500 lumen 5CCT UNV	Energy Star	8/320
<b>Downlight 4"</b>				
DL4R7ESCT1W	190096131860	Downlight Round 4" 700 lumen 5CCT 120V	Energy Star	20/640
DL4RSLMZ10SCTUW	190096131877	Downlight Round Dualselect 4" 540/700 lumen 5CCT UNV	Energy Star	8/240
<b>Downlight 6"</b>				
DL6R11ESCT1W	190096131884	Downlight Round 6" 1100 lumen 5CCT 120V	Energy Star	10/300
DL6RSLMZ10SCTUW	190096131891	Downlight Round Dualselect 6" 900/1100 lumen 5CCT UNV	Energy Star	8/160
<b>Gimbal 3"</b>				
GB3R4ESCT1W	190096196227	Gimbal Round 3" 480LM 5CCT 120V	Energy Star	8/320
GB3RSLMZ10SCTUW	190096131907	Gimbal Round Dualselect 3" 350/500 lumen 5CCT UNV	Energy Star	8/320
<b>Gimbal 4"</b>				
GB4R7ESCT1W	190096131914	Gimbal Round 4" 700 lumen 5CCT 120V	Energy Star	8/480
GB4RSLMZ10SCTUW	190096131921	Gimbal Round Dualselect 4" 540/700 lumen 5CCT UNV	Energy Star	8/240
<b>Gimbal 6"</b>				
GB6R11ESCT1W	190096131938	Gimbal Round 6" 1100 lumen 5CCT 120V	Energy Star	6/240
GB6RSLMZ10SCTUW	190096131945	Gimbal Round Dualselect 6" 900/1100 lumen 5CCT UNV	Energy Star	8/160




Lumen  
Select Switch



CCT with  
Select Switch





## Selectable Backlit Panel

Make the **easy selection** and carry less stock with more options.



### Why choose Selectable Backlit Panel?

- 3 color temperature selections, 3 wattage choices, and 3 sizes available
- Numerous options for your customers, while keeping inventory levels and SKU count low
- Available for use in recessed, suspended and surface mount applications

### Selectable Backlit Panel

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
<b>Selectable Backlit Panel 1'x4'</b>				
1SBP3040L8CS-4-UN3-DIM	190096131020	Selectable Backlit Panel (SBP) 1'x4', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UN3 (120-347V), 0-10V Dimming	DLC Standard	4/48
1SBP3040L8CS-4-UNV-DIM	190096130993	Selectable Backlit Panel (SBP) 1'x4', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UNV (120-277V), 0-10V Dimming	DLC Standard	4/48
<b>Selectable Backlit Panel 2'x2'</b>				
2SBP3040L8CS-2-UNV-DIM	190096131006	2x2, Lumens Select, 80CRI, Color Select 3500K/4000K/5000K, UNV 120-277V, 0-10V (30W/34W/39W)	DLC Standard	4/40
2SBP3040L8CS-2-UN3-DIM	190096131037	Selectable Backlit Panel (SBP) 2'x2', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UN3 (120-347V), 0-10V Dimming	DLC Standard	4/40
<b>Selectable Backlit Panel 2'x4'</b>				
2SBP3550L8CS-4-UN3-DIM	190096131044	Selectable Backlit Panel (SBP) 2'x4', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UN3 (120-347V), 0-10V Dimming	DLC Standard	4/20
2SBP3550L8CS-4-UNV-DIM	190096131013	2x4, Lumens Select, 80CRI, Color Select 3500K/4000K/5000K, UNV 120-277V, 0-10V (35W/38W/50W)	DLC Standard	4/20



## SDS Selectable Strip

**Economical luminaire**  
delivering the right light



SDS  
(Selectable Strip)

### Why choose SDS Selectable LED Strip?

- Simple form
- Convenient specification
- Ease of installation
- Ease of maintenance
- Durable construction
- Simple mounting method
- Frosted glare-free lens
- CCT & Lumen selectability



### SDS Selectable Strip

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
Linear Strip SDS				
SDS42448L8CST-UN3-DIM	190096131600	SDS Selectable Strip, 4', 2430 / 3640 / 4850lm, 3500K / 4000K / 5000K (CRI 80), UN3 120-347V, Dimmable	DLC Standard	9/144
SDS84998L8CST-UN3-DIM	190096131617	SDS Selectable Strip, 8', 4900 / 7350 / 9800lm, 3500K / 4000K / 5000K (CRI 80), UN3 120-347V, Dimmable	DLC Standard	6/180



Lumen  
Select Switch



CCT with  
Select Switch





Field CCT selectable 4000K or 5000K

## FCY Value High Bay

Update and upgrade for **real savings**

Low profile and durable design, efficiency and great price – FCX value high bay has it all.



### Why choose FCY Value High Bay?

- Die formed sheet metal housing and end plates
- Corrosion resistant gloss white paint after fabrication
- V-hooks and 48" chains supplied (set of 2) for installation
- Lumen maintenance up to 70% (L70) at 50,000 hours
- Access plate located on top of housing for easy wiring
- cULus listed for use in damp locations, -20°C to 45°C ambient

### FCY Value High Bay

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
<b>FCY Value High Bay</b>				
FCY15L8CST-UNV-DIM	190096180653	15,000 lumen, 80CRI, Color Select 4000K/5000K, 0-10V, UNV	DLC Premium	1/27
FCY22L8CST-UNV-DIM	190096180660	22,000 lumen, 80CRI, Color Select 4000K/5000K, 0-10V, UNV	DLC Premium	1/27
FCY29L8CST-UNV-DIM	190096180677	FCY LED High Bay, 29000lm, 4000K / 5000K (CRI 80), UNV, 0-10V Dimming	DLC Premium	1/36
FCY-WG	190096180721	Wire guard for FCY15 and FCY22		10/600

# NWL Selectable Wraparound

Achieve a balance of  
**performance and appeal**



NWL  
(Wraparound)  
with field on/off  
occupancy sensor

## Why choose NWL Selectable Wraparound?

- White polycarbonate housing for durability
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting included
- Field CCT selectable for 3000K, 3500K or 4000K
- cETLus listed to meet UL 1598 standards for -10°C to 35°C ambient. Suitable for damp locations



## NWL Selectable Wraparound

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
NWL Selectable Wraparound				
NWL440L8CST-UNV-DIM-OCC	190096130917	4' Wraparound, 4000 lumen, 80CRI, Color Select 3000K-3500K-4000K, UNV 120-277V, 0-10V, Occupancy sensor	DLC Standard	4/32



## HCY Sealed High Bay

Modern design and **energy savings**

A great new look with no more sacrifices and dependability you can trust.



### Why choose HCY Sealed High Bay?

- Field selectable color 4000K or 5000K
- Corrosion resistant black finish
- Heavy duty eyelet provided for connection to customer supplied suspension
- Accessory options of polycarbonate reflector and surface mount bracket
- Listed cULus for use in wet locations up to 50°C ambient, and IP65 rated

### HCY Sealed High Bay

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
<b>HCY Sealed High Bay</b>				
HCY14L8CST-UN3-DIM	190096131099	14, 000lm, 80CRI, Color Select 4000K/5000K, 0-10V UNV, 120-347V	DLC Premium	1/45
HCY21L8CST-UN3-DIM	190096131105	21, 000lm, 80CRI, Color Select 4000K/5000K, 0-10V UNV, 120-347V	DLC Premium	1/45
HCY28L8CST-UN3-DIM	190096131112	28, 000lm, 80CRI, Color Select 4000K/5000K, 0-10V UNV, 120-347V	DLC Premium	1/30
HCY33L8CST-UN3-DIM	190096131129	33, 000lm, 80CRI, Color Select 4000K/5000K, 0-10V UNV, 120-347V	DLC Premium	1/30
<b>Accessories</b>				
HCY-PRSM	190096131150	16" Clear Polycarbonate Reflector for HCY14L and HCY21L	—	10/80
HCY-PRLG	190096131167	16" Clear Polycarbonate Reflector for HCY28L and HCY33L	—	10/40
HCY-SURFACE BKT SM	190096131174	Surface Mount Bracket for HCY14L and HCY21L	—	20/720
HCY-SURFACE BKT LG	190096131181	Surface Mount Bracket for HCY28L and HCY33L	—	20/480

## Wall Pack dual select

### Classic design meets LED technology

The new Wall Pack dual select helps you upgrade from costly HID fixtures with confidence.



### Why choose Wall Pack?

- An easy switch from costly HID fixture
- Field selectable wattage and color temperature
- Flexible options, built-in photocell, and field enable or disable
- Glass refractor lens design cuts down on glare



### Wall Pack dual select

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
<b>Wall Pack dual select</b>				
WP100-SCT-G2-10-BZ	190096131341	Selectable Wattage and CCT 80-100W / 30K-40K-50K, Bronze Finish	DLC Premium	2/24
WP60-SCT-G2-10-BZ	190096131334	Selectable Wattage and CCT 28-40-60W / 30K-40K-50K, Bronze Finish	DLC Premium	2/24



## Adjustable Slim Wall Pack

### Slim, low profile LED design

Features a discreet design that will complement any building exterior. Two sizes are available, with three wattage and three CCT selectable options each.



### Why choose Adjustable Slim Wall Pack?

- Wall, surface, low level mounting
- Die-cast aluminum, hinged
- Simplified solution – dual select
- 2 housing sizes (25W & 75W)
  - 25W (15/20/25W & 1800/2400/3000 lms)
  - 75W (45/60/75W & 5400/7200/9000 lms)
- CCT Selectable (3K/4K/5K) & 120-277V
- IP65 / IK07 Rated / DLC 5.1
- Button Photocontrol w/0-90° tilt option

### Lytepro Wall Sconce

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
<b>Adjustable Slim Wall Pack</b>				
ASW25-SCT-G1-8-PCB-BW	190096182039	Adj Slim WP DS 15-25W/30-40-50K/UNV/PCB	DLC Premium	4/144
ASW75-SCT-G1-8-PCB-BW	190096182046	Adj Slim WP DS 45-75W/30-40-50K/UNV/PCB	DLC Premium	4/120



## Slim Flood

**Illuminate** with discreet and modern style

The best value for discreet and modern design on your floodlighting projects.



### Why choose Slim Flood?

- Complete family of LED floodlights ideal for illuminating signs, building facades or other dark areas
- Can be mounted on the ground, wall, or pole mounted
- All sizes arrive fully assembled and ready to install
- Fade-resistant, textured bronze finish with tempered glass lens that is heat and impact resistant
- IP65 rated, 5-year limited warranty<sup>1</sup>



### Slim Flood

Catalog Number	UPC Code	Product Description	Compliance	Case/Pallet Qty
<b>Slim Flood</b>				
TF30-NW-G1-K-FL-8-BZ	783352025951	30W, 3,000lm, 80CRI, 4000K, Knuckle Mount/Yoke Mount	DLC Standard	10/540
TF50-NW-G1-K-FL-8-BZ	783352025968	50W, 5,000lm, 80CRI, 4000K, Knuckle Mount/Yoke Mount	DLC Standard	6/330
TF100-NW-G1-Y-FL-8-BZ	783352025975	100W, 10,000lm, 80CRI, 4000K, Yoke Mount	DLC Standard	4/144
TF150-NW-G1-Y-FL-8-BZ	783352025982	150W, 15,000lm, 80CRI, 4000K, Yoke Mount	DLC Standard	2/72
TF200-NW-G1-Y-FL-8-BZ	783352025999	200W, 20,000lm, 80CRI, 4000K, Yoke Mount	DLC Standard	2/64

1. See [www.signify.com/warranties](http://www.signify.com/warranties) for details.







© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.