

PHILIPS

ProjectLine

Professional LED Luminaires

**REAL
PROs
REAL
QUALITY**



Professional quality for your project

Easy to install, energy efficient LED luminaire range.

philips.com/ProjectLine

**New
offering**

Convenience & quality converge with our pro LED luminaire range

Professional renovation projects need quality fittings. As all real pros know, reliability is everything. Philips is, as always, your trusted partner in quality assured LED performance. And we just made it easier to install our ProjectLine LED luminaires, so you can finish every job — swiftly. Our energy efficient range includes wall-mounts, floodlights, battens, and waterproof luminaires.

Look no further for a time-saving, reliable, energy efficient product for every project.



Energy efficient

Energy savings is crucial for both residential and industrial applications. We optimize energy efficiency with our latest LED technology.



Reliable quality

Philips is your trusted brand for guaranteed quality. Every key component is tested for optimal reliability and durable performance.




Easy to install

Fitting lights should be easy. Our lights are designed for swift, simple installation.

Philips ProjectLine Professional LED luminaire range




ProjectLine Wall-Mounts



ProjectLine Panels



ProjectLine Floodlights



ProjectLine Waterproofs



ProjectLine Battens



Applications				
Wall-Mounts	Panels	Floodlights	Waterproofs	Battens
Ideal for corridors, (public) entrance areas and staircases.	Suitable for standard sized visible profile ceilings, used in offices and (commercial) working locations.	Ideal to light up areas in front/back of (public) buildings such as parking lots, driveways, gardens or working locations.	Ideal for general (work) lighting, storage areas, garage, basements, work locations with high water and dust protection (IP66), combined with mechanical protection (IP65).	Ideal for general lighting for various indoor locations.

Philips ProjectLine Wall-Mount

Energy efficient, professional quality LED wall-mounts with motion sensor.



1 ProjectLine Wall-Mount Round



2 ProjectLine Wall-Mount Oval

Features:

- 4 Models
- IK06
- Non-dimmable
- Available in neutral white light
- Silver trim and motion sensor included
- Dimensions: 223 X 133 X 68 (oval), 182 X 182 X 66 (round)
- Weight: 0.18kg (round), 0.25kg (oval with sensor) 0.32kg (round with sensor and oval)

Technical specifications

Mains voltage	220-240 V / 50-60 Hz
Lifetime	35,000 hrs
Power range	15W
Temperature	-20 to +40°C
IP rating	IP54 (round/oval with sensor), IP65 (round/oval)
Power factor	0.9
Safety class	Class II
Certification	CE
Housing colour	White

Benefits:

- Available with motion sensor
 - Supports energy saving
- Available in round and oval
 - For wall and ceiling mounted



Product Type	LED	Lumen Output	Color Temp.	IP rating	EAN code
	W	lm	K		
① ProjectLine Wall-Mount					
ProjectLine Wall-Mount rnd 1400lm 4000K	15	1400	4000	IP65	8719514954311
ProjectLine Wall-Mount oval 1400lm 4000K		1400	4000	IP65	8719514954335
② ProjectLine Wall-Mount with Sensor					
ProjectLine Wall-Mount rnd 1400 4000K Sen	15	1400	4000	IP54	8719514954328
ProjectLine Wall-Mount ovl 1400 4000K Sen		1400	4000	IP54	8719514954342

Philips ProjectLine Panel

Reliable, energy efficient professional LED panels in three sizes.



1 ProjectLine Panel Square



2 ProjectLine Panel Rectangular

Features:

- 6 Models
- UGR <19 (Office compliant) and UGR <22 (Non-office compliant)
- Available in neutral white light (4000K)
- High quality light CRI >80
- Weight: 0.55kg (30X30), 1.8kg (30x120 NOC), 2kg (62X62), 2.1kg (30x120 OC)
- Dimensions: 295 X 295 X 34 (30X30), 595 X 595 X 34 (60X60 NOC), 595 X 595 X 35 (60X60 OC), 620 X 620 X 34 (62X62), 1195 X 295 X 34 (30x120 NOC), 1195 X 295 X 35 (30x120 OC)

Technical specifications

Mains voltage	220-240 V / 50-60 Hz
Lifetime	35,000 hrs
Power range	15W - 36W
Temperature	-10 to +45°C
IP rating	IP20
Power factor	0.9
Safety class	Class II
Certification	CE
Housing colour	White RAL 9003

Benefits:

- Office compliant (OC) version with UGR <19 and Non-office compliant (NOC) version UGR <22
- Supports energy saving
 - Available in four sizes



Product Type	LED	Lumen Output	Color Temp.	IP rating	EAN code
	W	lm	K		
1 ProjectLine Panel Square					
ProjectLine Panel 3030 1200lm 4000K NOC	15	1200	4000	IP20	8719514955288
ProjectLine Panel 6060 3200lm 4000K NOC		3200	4000	IP20	8719514955271
ProjectLine Panel 6060 3200lm 4000K OC	36	3200	4000	IP20	8719514955295
ProjectLine Panel 6262 3200lm 4000K OC		3200	4000	IP20	8719514955301
2 ProjectLine Panel Rectangular					
ProjectLine Panel 30120 3200lm 4000K NOC	36	3200	4000	IP20	8719514955318
ProjectLine Panel 30120 3200lm 4000K OC		3200	4000	IP20	8719514955325

Philips ProjectLine Floodlight

Pro grade LEDs in varied lumens and sensor strengths.



1 ProjectLine Floodlight



2 ProjectLine Floodlight with sensor

Features:

- 26 Models
- Available from 900-18000 lumen in warm white, neutral white and cool white
- Sensor versions available
- IP65
- Weight: From 0.3kg (10W) to 3.5kg (200W)
- Dimensions: From 106 X 98 X 40 (10W) to 455 X 331 X 58 (200W)

Without Sensor:

- From 10W to 200W
- CCTs 3000K, 4000K and 6500K
- IK06

With Sensor:

- From 10W to 50W
- CCTs 3000K, 4000K
- IK05

Technical specifications

Mains voltage	220-240 V / 50-60 Hz
Lifetime	35,000 hrs
Power range	10W - 200W
Temperature	-20 to +40°C
IP rating	IP65
Power factor	0.9
Safety class	Class I
Certification	CE
Housing colour	Black

Benefits:

- Energy Saving
- Metal robust luminaire
- Reliable quality



Product Type	LED	Lumen Output	Color Temp.	IP rating	EAN code
	W	lm	K		
1 ProjectLine Floodlight					
Standard 3000K	10	900	3000	IP65	8719514954397
Standard 4000K		950	4000	IP65	8719514954496
Standard 6500K		950	6500	IP65	8719514954588
Standard 3000K	20	1800	3000	IP65	8719514954403
Standard 4000K		1900	4000	IP65	8719514954502
Standard 6500K		1900	6500	IP65	8719514954595
Standard 3000K	30	2700	3000	IP65	8719514954441
Standard 4000K		2850	4000	IP65	8719514954526
Standard 6500K		2850	6500	IP65	8719514954601
Standard 3000K	50	4500	3000	IP65	8719514954410
Standard 4000K		4750	4000	IP65	8719514954540
Standard 6500K		4750	6500	IP65	8719514954618
Standard 3000K	100	9000	3000	IP65	8719514954465
Standard 4000K		9500	4000	IP65	8719514954564
Standard 6500K		9500	6500	IP65	8719514954625
Standard 3000K	150	13500	3000	IP65	8719514954472
Standard 4000K		14250	4000	IP65	8719514954571
Standard 6500K		14250	6500	IP65	8719514954632
Standard 3000K	200	18000	3000	IP65	8719514954489
2 ProjectLine Floodlight with Sensor					
Sensor 3000K	20	1800	3000	IP65	8719514954427
Sensor 4000K		1900	4000	IP65	8719514954519
Sensor 3000K	30	2700	3000	IP65	8719514954458
Sensor 4000K		2850	4000	IP65	8719514954533
Sensor 3000K	50	4500	3000	IP65	8719514954434
Sensor 4000K		4750	4000	IP65	8719514954557

Philips ProjectLine Waterproof

Water tight, robust LEDs for industrial use.



Features:

- 7 Models
- IP65 Dust penetration-protected, protected against water jets from any angle
- Available in warm white light (3000K), neutral white light (4000K) and cool white light (6500K)
- Dimensions: 598 X 35.5 X 44.5 (60cm), 1198 X 35.5 X 44.5 (120cm), 1498 X 35.5 X 44.5 (150cm)
- Weight: 0.25kg (60cm), 0.47kg (120cm), 0.53kg (150cm)

Technical specifications

Mains voltage	220-240 V / 50-60 Hz
Lifetime	35,000 hrs
Power range	17W - 54W
Temperature	-20 to +40°C
IP/IK rating	IK06/IP65
Power factor	0.9
Safety class	Class II
Certification	CE
Housing colour	Gray and White

Benefits:

- Robust luminaire
 - Protected from total dust ingress and protected from water spray from any direction
- Available in three sizes
 - For wall (horizontal), ceiling mounted and suspended



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EAN code
	W	lm	K		
ProjectLine Waterproof 60 1550lm 3000K	17	1550	3000	IP65	8719514955394
ProjectLine Waterproof 60 1700lm 4000K		1700	4000	IP65	8719514955417
ProjectLine Waterproof 120 3100lm 3000K		3100	3000	IP65	8719514955400
ProjectLine Waterproof 120 3400lm 4000K	34	3400	4000	IP65	8719514955424
ProjectLine Waterproof 120 3400lm 6500K	54	3400	6500	IP65	8719514955448
ProjectLine Waterproof 150 5400lm 4000K		5400	4000	IP65	8719514955431
ProjectLine Waterproof 150 5400lm 6500K		5400	6500	IP65	8719514955455

Philips ProjectLine Batten

Energy efficient, professional LEDs for varied applications.



Features:

- 4 Models
- Most popular batten type of 600mm and 1200mm
- Non-dimmable
- Available in warm white light (3000K) and neutral white light (4000K)
- Dimensions: 600 x 70 x 20 (600mm), 1200 x 70 x 20 (1200mm)
- Weight: 0.155kg (600mm), 0.255kg (1200mm)

Technical specifications

Mains voltage	220-240 V / 50-60 Hz
Lifetime	35,000 hrs
Power range	16W - 30W
Temperature	-20 to +35°C
IP rating	IP20
Power factor	0.9
Safety class	Class II
Certification	CE
Housing colour	White

Benefits:

- Applicable for wide range of applications
 - Supports energy saving
- Reliable quality
 - For wall (horizontal) and ceiling mounted



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EAN code
	W	lm	K		
ProjectLine Batten 60 1440lm 3000K	16	1440	3000	IP20	8719514954359
ProjectLine Batten 60 1600lm 4000K		1600	4000	IP20	8719514954373
ProjectLine Batten 120 2700lm 3000K	30	2700	3000	IP20	8719514954366
ProjectLine Batten 120 3000lm 4000K		3000	4000	IP20	8719514954380



© 2022 Signify Holding. All rights reserved. Signify reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

philips.com/ProjectLine