



Guaranteed performance, thinking ahead

Maxos fusion

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Benefits

- Freedom of (re-)positioning enables you to direct the light where needed
- Family of fixtures to create the desired atmosphere; wide variety of beam shapes to suit diversity of applications
- With up to 13-wire track, emergency lighting and third-party hardware can be integrated to declutter ceilings

Features

- Track system inside the trunk with up to 13 wires
- High uniformity and artefact-free light distributions
- Linear fixtures, non-linear fixtures and spots can be easily installed onto the trunk
- Eight optics, including (double) asymmetric distributions and a frosted cover
- IP54 optional, silicone-free
- StoreWise, Indoor Positioning and GreenWarehouse-ready

Maxos fusion

Application

- (Food) retail
- Industrial halls/areas
- Warehouses/distribution centers

Specifications

Type	LL512X (short linear panel, 1,15 m, IP20 version)	Xtra range Control gear 10%
	LL523X (long linear panel, 2,3 m, IP20 version)	
	LL512T (1,15 m rail, IP20 version)	
	LL523T (2,30 m rail, IP20 version)	
	LL546T (4,60 m rail, IP20 version)	
	7W = 7-W track inside rail	
	13W = 13-W track inside rail	
	LL6..X = IP54 linear panel	
	LL6..T = IP54 linear rail	
Light source	Replaceable LED module (linear LED panel)	failure rate at median
Efficacy	Maxos fusion Standard range upto 151 lm/W Maxos fusion Xtra range upto 171,5 lm/W	useful life 100000 h
Power	Diverse, depending on linear panel length and lumen flux	Xtra range Lumen L90
Beam angle	NB / MB / WB / DA25N / DA25W / DA35W / DA45 / Frosted cover	maintenance at median
Luminous flux	3100, 5000, 6150 lm (LL512X version) 6200, 10,000, 12,300 lm (LL523X version)	useful life* 50000 h
Correlated Color Temperature	3000, 4000, 5000, 6500 K	Xtra range Control gear 5%
Color Rendering Index	>80	failure rate at median
Lumen maintenance at median useful life* 50000 h	L80	useful life 50000 h
Control gear failure rate at median useful life 50000 h	5%	Performance Ambient +25 °C
XT range Lumen L70		Temperature Tq
maintenance at median useful life* 100000 h		Operating temperature range -20 to +35 °C
XT range Control gear 10%		Dimming DALI
failure rate at median useful life 100000 h		Emergency lighting EL1, EL3; option for DALI feedback PSED for central emergency
Xtra range Lumen L80		Options Built-in (self-ballasted LED-module) Philips Xitanium Driver
maintenance at median useful life* 100000 h		Material Rail: sheet metal Linear panel: sheet metal
		Color WH (RAL9003), BK (RAL9004), SI (RAL 9006), semi-gloss finish
		Optical cover Polycarbonate
		Connection Track system with up to 13 wires, panel adaptor to connect to rail Through-wiring via track system inside rail; 2,5 mm ²
		Accessories Options for suspension/profile/surface mounting/adjustable chain bracket, cable duct, spring attachment for cable guidance; external coupling piece to connect rails, starter kit begin of line, mid-entry starter kit, blind covers (possible to cut to length)
		Remarks Family of compatible spot portfolio: GreenSpace Accent Projector, StyliD, EcoStyle Compatible with non-linear panel: StoreSet

Maxos fusion

Versions



Maxos fusion Panel



Maxos fusion Panel



Maxos fusion Panel



Maxos fusion Panel



Maxos fusion Panel



Maxos fusion IP54 Panel



Maxos fusion IP54 Panel

Product details

Maxos_Fusion_Acc-LL500E_ACW-DP01.tif



Maxos_Fusion_Acc-LL500E_ACW-DP02.tif



Maxos_Fusion_Acc-LL500E_ACW-DP03.tif



Maxos_Fusion_Acc-LL500E_ACW-DP04.tif



Maxos fusion

Product details

Maxos_Fusion_Trunk-LL512T_WH-DP01.tif



Maxos_Fusion_Trunk-LL512T_WH-DP03.tif




Maxos_Fusion_Trunk-LL512T_WH-DP06.tif



Maxos_Fusion_Trunk-LL512T_WH-DP08.tif



Maxos_Fusion_Trunk-LL512T_WH-DP10.tif



Maxos_Fusion_Trunk-LL512T_WH-DP11.tif



Maxos_Fusion_Trunk-LL512T_WH-DP12.tif



Maxos_Fusion_Trunk-LL512T_WH-DP02.tif



Maxos fusion

Product details

Maxos_Fusion_Panel-
LL512X_PCO_WH-DP.tif



Maxos_Fusion_Panel-
LL512X_PCO_WH-DP03.tif



Maxos_Fusion_Panel-
LL512X_WH-DP01.tif



Maxos_Fusion_Panel-
LL512X_WH-DP06.tif



Maxos_Fusion_Panel-
LL512X_WH-DP07.tif



Maxos_Fusion_Panel-
LL512X_WB_WH-DP02.tif



Maxos_Fusion_Panel-
LL512X_WB_WH-DP03.tif



Maxos_Fusion_Panel-
LL612_LL623X-1DPP.tif



Maxos fusion

Product details



Maxos_Fusion_Panel-LL612_LL623X-2DPP.tif




Maxos_Fusion_Panel-LL612X-DPP.tif



Maxos_Fusion_Panel-LL623X-DPP.tif



Maxos_Fusion_Wave_3-LL500Z_3C-1DPP.TIF




Maxos_Fusion_Wave_3-LL500Z_3C-2DPP.TIF



Maxos_Fusion_Wave_3-LL500Z_3C-3DPP.TIF




Maxos_Fusion_Wave_3-LL500Z_3C-4DPP.TIF



Maxos_Fusion_Wave_3-LL500Z_3C-5DPP.TIF

Maxos fusion

Product details




Maxos_Fusion_Wave_3-LL500Z_3C-6DPP.TIF



Maxos_Fusion_Wave_3-LL500Z_BA-1DPP.TIF



Maxos_Fusion_Wave_3-LL500Z_BA-2DPP.TIF



Maxos_Fusion_Wave_3-LL500Z_BA-3DPP.TIF



Maxos_Fusion_Wave_3-LL500Z_MOD-1DPP.TIF



Maxos_Fusion_Wave_3-LL500Z_MOD-2DPP.TIF




Maxos_Fusion_Wave_3-LL500Z_MOD-3DPP.TIF

Maxos fusion

Accessories

LL500Z

Ordercode 910925864201,
910925864208



LL500Z

Ordercode 910925864211



LL500Z

Ordercode 910925864212




LL500Z

Ordercode 910925864213




LL500Z

Ordercode 910925864214




LL500Z

Ordercode 910925864215



LL500Z

Ordercode 910925864216



LL500Z

Ordercode 910925864218



Maxos fusion

Accessories

LL500Z

Ordercode 910925864219



LL500Z

Ordercode 910925864220



LL500Z

Ordercode 910925864221



LL500Z

Ordercode 910925864227




LL500Z

Ordercode 910925864230



LL500Z

Ordercode 910925864231



LL500Z

Ordercode 910925864232



LL500Z

Ordercode 910925864233



Maxos fusion

Accessories

LL500Z

Ordercode 910925864234



LL500Z

Ordercode 910925864235




LL500Z

Ordercode 910925864236,
910925864513, 910925864763,
910925864764, 910925864767,
910925864956, 910925864957,
910925864958



LL500Z

Ordercode 910925864237,
910925864511, 910925864514,
910925864765



LL500Z

Ordercode 910925864238,
910925864512, 910925864515,
910925864766



LL500Z

Ordercode 910925864239




LL512Z

Ordercode 910925864240,
910925864243, 910925864246



LL512Z

Ordercode 910925864241,
910925864244, 910925864247



Maxos fusion

Accessories

LL546Z

Ordercode 910925864248



LL500Z

Ordercode 910925864249



LL500Z

Ordercode 910925864252,
910925864253, 910925864254



Maxos fusion Electrical

Ordercode 910925864255



Maxos fusion Electrical

Ordercode 910925864256




Maxos fusion Rail

Ordercode 910925864257,
910925864258, 910925864259,
910925864260, 910925864261,
910925864262, 910925864277,
910925864278, 910925864279,
910925864280, 910925864649,
910925864650, 910925864657,
910925865347, 910925865348


Maxos fusion Rail

Ordercode 910925864263,
910925864265, 910925864267,
910925864651, 910925864652,
910925864653



Maxos fusion Rail

Ordercode 910925864269,
910925864271, 910925864273,
910925864654, 910925864655,
910925864656



Maxos fusion

Accessories


Maxos fusion Acc.

Ordercode 910925865353




Maxos fusion Acc.

Ordercode 910925865356



Maxos fusion Acc.

Ordercode 910925865359,
910925865360, 910925865361



Application Conditions

Ambient temperature range	-20 to +35 °C
Maximum dim level	1%

Approval and Application

Mech. impact protection code	IK02
------------------------------	------

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Input Voltage	220-240 V
---------------	-----------

General Information

Beam angle of light source	120 °
CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit

Initial Performance (IEC Compliant)

Init. Color Rendering Index	>80
Luminous flux tolerance	+/-7%

Approval and Application

Order Code	Full Product Name	Ingress protection code
910925864293	LL512X LED31S/840 PSD PCO 7 WH	IP20
910925864294	LL512X LED50S/840 PSD PCO 7 WH	IP20
910925864295	LL512X LED61S/840 PSD PCO 7 WH	IP20
910925864296	LL523X LED62S/840 PSD PCO 7 WH	IP20
910925864297	LL523X LED100S/840 PSD PCO 7 WH	IP20
910925864298	LL523X LED123S/840 PSD PCO 7 WH	IP20
910925864299	LL512X LED31S/840 PSED PCO 7 WH	IP20
910925864301	LL512X LED50S/840 PSED PCO 7 WH	IP20
910925864302	LL512X LED61S/840 PSED PCO 7 WH	IP20
910925864303	LL512X LED31S/840 PSD WB 7 WH	IP20
910925864304	LL512X LED50S/840 PSD WB 7 WH	IP20
910925864305	LL512X LED61S/840 PSD WB 7 WH	IP20
910925864309	LL512X LED31S/840 PSED WB 7 WH	IP20
910925864310	LL512X LED50S/840 PSED WB 7 WH	IP20
910925864311	LL512X LED61S/840 PSED WB 7 WH	IP20
910925864312	LL512X LED31S/840 PSD MB 7 WH	IP20
910925864313	LL512X LED50S/840 PSD MB 7 WH	IP20
910925864314	LL512X LED61S/840 PSD MB 7 WH	IP20
910925864320	LL512X LED61S/840 PSD NB 7 WH	IP20
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	IP20
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	IP20
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	IP20
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	IP20
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	IP20
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	IP20
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	IP20
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	IP20
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	IP20
910925864344	LL512X LED61S/840 PSD A20 7 WH	IP20
910925864624	LL512X LED50S/835 PSD WB 7 WH	IP20
910925864626	LL512X LED61S/840 PSD XNB 7 WH XT	IP20
910925864306	LL523X LED62S/840 PSD WB 7 WH	IP20
910925864307	LL523X LED100S/840 PSD WB 7 WH	IP20
910925864308	LL523X LED123S/840 PSD WB 7 WH	IP20
910925864315	LL523X LED62S/840 PSD MB 7 WH	IP20
910925864316	LL523X LED100S/840 PSD MB 7 WH	IP20
910925864317	LL523X LED123S/840 PSD MB 7 WH	IP20
910925864321	LL523X LED62S/840 PSD NB 7 WH	IP20
910925864322	LL523X LED100S/840 PSD NB 7 WH	IP20
910925864323	LL523X LED123S/840 PSD NB 7 WH	IP20
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	IP20
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	IP20
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	IP20
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	IP20
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	IP20
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	IP20
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	IP20
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	IP20
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	IP20
910925864346	LL523X LED100S/840 PSD A20 7 WH	IP20
910925864347	LL523X LED123S/840 PSD A20 7 WH	IP20

Order Code	Full Product Name	Ingress protection code
910925864351	LL523X LED62S/840 PSD WB 7 SI	IP20
910925864353	LL523X LED123S/840 PSD WB 7 SI	IP20
910925864625	LL523X LED100S/835 PSD WB 7 WH	IP20
910925864627	LL523X LED100S/840 PSD XNB 7 WH XT	IP20
910925864628	LL523X LED123S/840 PSD XNB 7 WH XT	IP20
910925865537	LL523X LED160S/840 PSD MB 7 WH	IP20
910925865538	LL523X LED160S/840 PSD NB 7 WH	IP20
910925865539	LL523X LED160S/840 PSD XNB 7 WH	IP20
910925865540	LL523X LED160S/830 PSD MB 7 WH	IP20
910925865541	LL523X LED160S/830 PSD NB 7 WH	IP20
910925865542	LL523X LED160S/830 PSD XNB 7 WH	IP20
910925864348	LL512X LED31S/840 PSD WB 7 SI	IP20
910925864349	LL512X LED50S/840 PSD WB 7 SI	IP20
910925864350	LL512X LED61S/840 PSD WB 7 SI	IP20
910925864352	LL523X LED100S/840 PSD WB 7 SI	IP20
910925864354	LL512X LED31S/840 PSD WB 7 BK	IP20
910925864355	LL512X LED50S/840 PSD WB 7 BK	IP20
910925864356	LL512X LED61S/840 PSD WB 7 BK	IP20
910925864357	LL523X LED62S/840 PSD WB 7 BK	IP20
910925864358	LL523X LED100S/840 PSD WB 7 BK	IP20
910925864359	LL523X LED123S/840 PSD WB 7 BK	IP20
910925864377	LL612X LED61S/840 PSD WB 7 WH	IP54
910925864378	LL612X LED61S/840 PSD MB 7 WH	IP54
910925864379	LL612X LED61S/840 PSD NB 7 WH	IP54
910925864380	LL623X LED123S/840 PSD WB 7 WH	IP54
910925864381	LL623X LED123S/840 PSD MB 7 WH	IP54
910925864382	LL623X LED123S/840 PSD NB 7 WH	IP54

General Information

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code
910925864293	LL512X LED31S/840 PSD PCO 7 WH	-	-	Symmetrical	LL512X
910925864294	LL512X LED50S/840 PSD PCO 7 WH	-	-	Symmetrical	LL512X
910925864295	LL512X LED61S/840 PSD PCO 7 WH	-	-	Symmetrical	LL512X
910925864296	LL523X LED62S/840 PSD PCO 7 WH	-	-	Symmetrical	LL523X
910925864297	LL523X LED100S/840 PSD PCO 7 WH	-	-	Symmetrical	LL523X
910925864298	LL523X LED123S/840 PSD PCO 7 WH	-	-	Symmetrical	LL523X
910925864299	LL512X LED31S/840 PSED PCO 7 WH	-	-	Symmetrical	LL512X

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code
910925864301	LL512X LED50S/840 PSED PCO 7 WH	-	-	Symmetrical	LL512X
910925864302	LL512X LED61S/840 PSED PCO 7 WH	-	-	Symmetrical	LL512X
910925864303	LL512X LED31S/840 PSD WB 7 WH	-	-	Wide beam	LL512X
910925864304	LL512X LED50S/840 PSD WB 7 WH	-	-	Wide beam	LL512X
910925864305	LL512X LED61S/840 PSD WB 7 WH	-	-	Wide beam	LL512X
910925864309	LL512X LED31S/840 PSED WB 7 WH	-	-	Wide beam	LL512X
910925864310	LL512X LED50S/840 PSED WB 7 WH	-	-	Wide beam	LL512X
910925864311	LL512X LED61S/840 PSED WB 7 WH	-	-	Wide beam	LL512X

Maxos fusion

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code
910925864312	LL512X LED31S/840 PSD MB 7 WH	-	-	Medium beam	LL512X
910925864313	LL512X LED50S/840 PSD MB 7 WH	-	-	Medium beam	LL512X
910925864314	LL512X LED61S/840 PSD MB 7 WH	-	-	Medium beam	LL512X
910925864320	LL512X LED61S/840 PSD NB 7 WH	-	-	Narrow beam	LL512X
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	-	-	Double asymmetric optic 35° wide beam	LL512X
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	-	-	Double asymmetric optic 35° wide beam	LL512X
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	-	-	Double asymmetric optic 35° wide beam	LL512X
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	-	-	Double asymmetric optic wide beam	LL512X
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	-	-	Double asymmetric optic wide beam	LL512X
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	-	-	Double asymmetric optic wide beam	LL512X
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	LED31S	1 pc	Double asymmetric optic narrow beam	LL512X
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	-	-	Double asymmetric optic narrow beam	LL512X
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	-	-	Double asymmetric optic narrow beam	LL512X
910925864344	LL512X LED61S/840 PSD A20 7 WH	-	-	Asymmetrical mirror	LL512X
910925864624	LL512X LED50S/835 PSD WB 7 WH	-	-	Wide beam	LL512X
910925864626	LL512X LED61S/840 PSD XNB 7 WH XT	-	-	Extra narrow beam	LL512X
910925864306	LL523X LED62S/840 PSD WB 7 WH	-	-	Wide beam	LL523X
910925864307	LL523X LED100S/840 PSD WB 7 WH	-	-	Wide beam	LL523X

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code
910925864308	LL523X LED123S/840 PSD WB 7 WH	-	-	Wide beam	LL523X
910925864315	LL523X LED62S/840 PSD MB 7 WH	-	-	Medium beam	LL523X
910925864316	LL523X LED100S/840 PSD MB 7 WH	-	-	Medium beam	LL523X
910925864317	LL523X LED123S/840 PSD MB 7 WH	-	-	Medium beam	LL523X
910925864321	LL523X LED62S/840 PSD NB 7 WH	-	-	Narrow beam	LL523X
910925864322	LL523X LED100S/840 PSD NB 7 WH	-	-	Narrow beam	LL523X
910925864323	LL523X LED123S/840 PSD NB 7 WH	-	-	Narrow beam	LL523X
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	-	-	Double asymmetric optic 35° wide beam	LL523X
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	-	-	Double asymmetric optic 35° wide beam	LL523X
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	-	-	Double asymmetric optic 35° wide beam	LL523X
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	-	-	Double asymmetric optic wide beam	LL523X
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	-	-	Double asymmetric optic wide beam	LL523X
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	-	-	Double asymmetric optic wide beam	LL523X
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	-	-	Double asymmetric optic narrow beam	LL523X
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	-	-	Double asymmetric optic narrow beam	LL523X
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	-	-	Double asymmetric optic narrow beam	LL523X

Maxos fusion

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code
910925864346	LL523X LED100S/840 PSD A20 7 WH	-	-	Asymmetrical mirror	LL523X
910925864347	LL523X LED123S/840 PSD A20 7 WH	-	-	Asymmetrical mirror	LL523X
910925864351	LL523X LED62S/840 PSD WB 7 SI	-	-	Wide beam	LL523X
910925864353	LL523X LED123S/840 PSD WB 7 SI	-	-	Wide beam	LL523X
910925864625	LL523X LED100S/835 PSD WB 7 WH	-	-	Wide beam	LL523X
910925864627	LL523X LED100S/840 PSD XNB 7 WH XT	-	-	Extra narrow beam	LL523X
910925864628	LL523X LED123S/840 PSD XNB 7 WH XT	-	-	Extra narrow beam	LL523X
910925865537	LL523X LED160S/840 PSD MB 7 WH	-	-	Medium beam	LL523X
910925865538	LL523X LED160S/840 PSD NB 7 WH	-	-	Narrow beam	LL523X
910925865539	LL523X LED160S/840 PSD XNB 7 WH	-	-	Extra narrow beam	LL523X
910925865540	LL523X LED160S/830 PSD MB 7 WH	-	-	Medium beam	LL523X
910925865541	LL523X LED160S/830 PSD NB 7 WH	-	-	Narrow beam	LL523X
910925865542	LL523X LED160S/830 PSD XNB 7 WH	-	-	Extra narrow beam	LL523X
910925864348	LL512X LED31S/840 PSD WB 7 SI	-	-	Wide beam	LL512X

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code
910925864349	LL512X LED50S/840 PSD WB 7 SI	-	-	Wide beam	LL512X
910925864350	LL512X LED61S/840 PSD WB 7 SI	-	-	Wide beam	LL512X
910925864352	LL523X LED100S/840 PSD WB 7 SI	-	-	Wide beam	LL523X
910925864354	LL512X LED31S/840 PSD WB 7 BK	-	-	Wide beam	LL512X
910925864355	LL512X LED50S/840 PSD WB 7 BK	-	-	Wide beam	LL512X
910925864356	LL512X LED61S/840 PSD WB 7 BK	-	-	Wide beam	LL512X
910925864357	LL523X LED62S/840 PSD WB 7 BK	-	-	Wide beam	LL523X
910925864358	LL523X LED100S/840 PSD WB 7 BK	-	-	Wide beam	LL523X
910925864359	LL523X LED123S/840 PSD WB 7 BK	-	-	Wide beam	LL523X
910925864377	LL612X LED61S/840 PSD WB 7 WH	-	-	Wide beam	LL612X
910925864378	LL612X LED61S/840 PSD MB 7 WH	-	-	Medium beam	LL612X
910925864379	LL612X LED61S/840 PSD NB 7 WH	-	-	Narrow beam	LL612X
910925864380	LL623X LED123S/840 PSD WB 7 WH	-	-	Wide beam	LL623X
910925864381	LL623X LED123S/840 PSD MB 7 WH	-	-	Medium beam	LL623X
910925864382	LL623X LED123S/840 PSD NB 7 WH	-	-	Narrow beam	LL623X

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864293	LL512X LED31S/840	(0.34, 0.35) SDCM <3	4000 K	128 lm/W	2700 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSD PCO 7 WH				

Maxos fusion

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864294	LL512X LED50S/840 PSD PCO 7 WH	(0.34, 0.35) SDCM <3	4000 K	119 lm/W	4300 lm
910925864295	LL512X LED61S/840 PSD PCO 7 WH	(0.34, 0.35) SDCM <3	4000 K	117 lm/W	5300 lm
910925864296	LL523X LED62S/840 PSD PCO 7 WH	(0.34, 0.35) SDCM <3	4000 K	129 lm/W	5300 lm
910925864297	LL523X LED100S/84 0 PSD PCO 7 WH	(0.34, 0.35) SDCM <3	4000 K	121 lm/W	8600 lm
910925864298	LL523X LED123S/84 0 PSD PCO 7 WH	(0.34, 0.35) SDCM <3	4000 K	119 lm/W	10600 lm
910925864299	LL512X LED31S/840 PSED PCO 7 WH	(0.34, 0.35) SDCM <3	4000 K	128 lm/W	2700 lm
910925864301	LL512X LED50S/840 PSED PCO 7 WH	(0.34, 0.35) SDCM <3	4000 K	119 lm/W	4300 lm
910925864302	LL512X LED61S/840 PSED PCO 7 WH	(0.34, 0.35) SDCM <3	4000 K	117 lm/W	5300 lm
910925864303	LL512X LED31S/840 PSD WB 7 WH	(0.34, 0.35) SDCM <3	4000 K	147 lm/W	3100 lm
910925864304	LL512X LED50S/840 PSD WB 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	5000 lm
910925864305	LL512X LED61S/840 PSD WB 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864309	LL512X LED31S/840 PSED WB 7 WH	(0.34, 0.35) SDCM <3	4000 K	147 lm/W	3100 lm
910925864310	LL512X LED50S/840 SDCM <3	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	5000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSED WB 7 WH				
910925864311	LL512X LED61S/840 PSED WB 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864312	LL512X LED31S/840 PSD MB 7 WH	(0.34, 0.35) SDCM <3	4000 K	147 lm/W	3100 lm
910925864313	LL512X LED50S/840 PSD MB 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	5000 lm
910925864314	LL512X LED61S/840 PSD MB 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864320	LL512X LED61S/840 PSD NB 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	(0.34, 0.35) SDCM <3	4000 K	147 lm/W	3100 lm
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	5000 lm
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	(0.34, 0.35) SDCM <3	4000 K	147 lm/W	3100 lm
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	5000 lm
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	(0.34, 0.35) SDCM <3	4000 K	147 lm/W	3100 lm

Maxos fusion

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	5000 lm
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864344	LL512X LED61S/840 PSD A20 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864624	LL512X LED50S/835 PSD WB 7 WH	(0.34, 0.35) SDCM <3	3500 K	139 lm/W	5000 lm
910925864626	LL512X LED61S/840 PSD XNB 7 WH XT	(0.34, 0.35) SDCM <3	4000 K	137 lm/W	6100 lm
910925864306	LL523X LED62S/840 PSD WB 7 WH	(0.34, 0.35) SDCM <3	4000 K	151 lm/W	6200 lm
910925864307	LL523X LED100S/84 0 PSD WB 7 WH	(0.34, 0.35) SDCM <3	4000 K	140 lm/W	10100 lm
910925864308	LL523X LED123S/84 0 PSD WB 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm
910925864315	LL523X LED62S/840 PSD MB 7 WH	(0.34, 0.35) SDCM <3	4000 K	151 lm/W	6200 lm
910925864316	LL523X LED100S/84 0 PSD MB 7 WH	(0.34, 0.35) SDCM <3	4000 K	140 lm/W	10100 lm
910925864317	LL523X LED123S/84 0 PSD MB 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm
910925864321	LL523X LED62S/840 PSD NB 7 WH	(0.34, 0.35) SDCM <3	4000 K	151 lm/W	6200 lm
910925864322	LL523X LED100S/84 SDCM <3	(0.34, 0.35) SDCM <3	4000 K	140 lm/W	10100 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	0 PSD NB 7 WH				
910925864323	LL523X LED123S/84 0 PSD NB 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	(0.34, 0.35) SDCM <3	4000 K	151 lm/W	6200 lm
910925864328	LL523X LED100S/84 0 PSD DA35W 7 WH	(0.34, 0.35) SDCM <3	4000 K	140 lm/W	10100 lm
910925864329	LL523X LED123S/84 0 PSD DA35W 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	(0.34, 0.35) SDCM <3	4000 K	151 lm/W	6200 lm
910925864334	LL523X LED100S/84 0 PSD DA25W 7 WH	(0.34, 0.35) SDCM <3	4000 K	140 lm/W	10100 lm
910925864335	LL523X LED123S/84 0 PSD DA25W 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	(0.34, 0.35) SDCM <3	4000 K	151 lm/W	6200 lm
910925864340	LL523X LED100S/84 0 PSD DA25N 7 WH	(0.34, 0.35) SDCM <3	4000 K	140 lm/W	10100 lm
910925864341	LL523X LED123S/84 0 PSD DA25N 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm
910925864346	LL523X LED100S/84 0 PSD A20 7 WH	(0.34, 0.35) SDCM <3	4000 K	140 lm/W	10100 lm

Maxos fusion

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864347	LL523X LED123S/84 0 PSD A20 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm
910925864351	LL523X LED62S/840 PSD WB 7 SI	(0.34, 0.35) SDCM <3	4000 K	151 lm/W	6200 lm
910925864353	LL523X LED123S/84 0 PSD WB 7 SI	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm
910925864625	LL523X LED100S/83 5 PSD WB 7 WH	(0.34, 0.35) SDCM <3	3500 K	141 lm/W	10000 lm
910925864627	LL523X LED100S/84 0 PSD XNB 7 WH XT	(0.34, 0.35) SDCM <3	4000 K	141 lm/W	10000 lm
910925864628	LL523X LED123S/84 0 PSD XNB 7 WH XT	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm
910925865537	LL523X LED160S/84 0 PSD MB 7 WH	(0.34, 0.35) SDCM <3	4000 K	128 lm/W	16000 lm
910925865538	LL523X LED160S/84 0 PSD NB 7 WH	(0.34, 0.35) SDCM <3	4000 K	128 lm/W	16000 lm
910925865539	LL523X LED160S/84 0 PSD XNB 7 WH	(0.34, 0.35) SDCM <3	4000 K	128 lm/W	16000 lm
910925865540	LL523X LED160S/83 0 PSD MB 7 WH	(0.4314,0.4000) SDCM	3000 K	128 lm/W	16000 lm
910925865541	LL523X LED160S/83 0 PSD NB 7 WH	(0.4314,0.4000) SDCM	3000 K	128 lm/W	16000 lm
910925865542	LL523X LED160S/83 0 PSD XNB 7 WH	(0.4314,0.4000) SDCM	3000 K	128 lm/W	16000 lm
910925864348	LL512X LED31S/840 PSD WB 7 SI	(0.34, 0.35) SDCM <3	4000 K	147 lm/W	3100 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864349	LL512X LED50S/840 PSD WB 7 SI	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	5000 lm
910925864350	LL512X LED61S/840 PSD WB 7 SI	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864352	LL523X LED100S/84 0 PSD WB 7 SI	(0.34, 0.35) SDCM <3	4000 K	140 lm/W	10100 lm
910925864354	LL512X LED31S/840 PSD WB 7 BK	(0.34, 0.35) SDCM <3	4000 K	147 lm/W	3100 lm
910925864355	LL512X LED50S/840 PSD WB 7 BK	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	5000 lm
910925864356	LL512X LED61S/840 PSD WB 7 BK	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864357	LL523X LED62S/840 PSD WB 7 BK	(0.34, 0.35) SDCM <3	4000 K	151 lm/W	6200 lm
910925864358	LL523X LED100S/84 0 PSD WB 7 BK	(0.34, 0.35) SDCM <3	4000 K	140 lm/W	10100 lm
910925864359	LL523X LED123S/84 0 PSD WB 7 BK	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm
910925864377	LL612X LED61S/840 PSD WB 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864378	LL612X LED61S/840 PSD MB 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864379	LL612X LED61S/840 PSD NB 7 WH	(0.34, 0.35) SDCM <3	4000 K	135 lm/W	6100 lm
910925864380	LL623X LED123S/84 0 PSD WB 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864381	LL623X LED123S/84 0 PSD MB 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864382	LL623X LED123S/84 0 PSD NB 7 WH	(0.34, 0.35) SDCM <3	4000 K	138 lm/W	12300 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
910925864293	LL512X LED31S/840 PSD PCO 7 WH	21 W
910925864294	LL512X LED50S/840 PSD PCO 7 WH	36 W
910925864295	LL512X LED61S/840 PSD PCO 7 WH	45 W
910925864296	LL523X LED62S/840 PSD PCO 7 WH	41 W
910925864297	LL523X LED100S/840 PSD PCO 7 WH	71 W
910925864298	LL523X LED123S/840 PSD PCO 7 WH	89 W
910925864299	LL512X LED31S/840 PSED PCO 7 WH	21 W
910925864301	LL512X LED50S/840 PSED PCO 7 WH	36 W
910925864302	LL512X LED61S/840 PSED PCO 7 WH	41 W
910925864303	LL512X LED31S/840 PSD WB 7 WH	21 W
910925864304	LL512X LED50S/840 PSD WB 7 WH	36 W
910925864305	LL512X LED61S/840 PSD WB 7 WH	45 W
910925864309	LL512X LED31S/840 PSED WB 7 WH	21 W
910925864310	LL512X LED50S/840 PSED WB 7 WH	36 W
910925864311	LL512X LED61S/840 PSED WB 7 WH	45 W
910925864312	LL512X LED31S/840 PSD MB 7 WH	21 W
910925864313	LL512X LED50S/840 PSD MB 7 WH	36 W
910925864314	LL512X LED61S/840 PSD MB 7 WH	45 W
910925864320	LL512X LED61S/840 PSD NB 7 WH	45 W
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	21 W
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	36 W
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	45 W
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	21 W
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	36 W
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	45 W
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	21 W
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	36 W
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	45 W
910925864344	LL512X LED61S/840 PSD A20 7 WH	45 W
910925864624	LL512X LED50S/835 PSD WB 7 WH	36 W
910925864626	LL512X LED61S/840 PSD XNB 7 WH XT	45 W
910925864306	LL523X LED62S/840 PSD WB 7 WH	41 W
910925864307	LL523X LED100S/840 PSD WB 7 WH	71 W
910925864308	LL523X LED123S/840 PSD WB 7 WH	89 W
910925864315	LL523X LED62S/840 PSD MB 7 WH	41 W
910925864316	LL523X LED100S/840 PSD MB 7 WH	71 W
910925864317	LL523X LED123S/840 PSD MB 7 WH	89 W
910925864321	LL523X LED62S/840 PSD NB 7 WH	41 W
910925864322	LL523X LED100S/840 PSD NB 7 WH	71 W

Order Code	Full Product Name	Initial input power
910925864323	LL523X LED123S/840 PSD NB 7 WH	89 W
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	41 W
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	71 W
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	89 W
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	41 W
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	71 W
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	89 W
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	41 W
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	71 W
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	89 W
910925864346	LL523X LED100S/840 PSD A20 7 WH	71 W
910925864347	LL523X LED123S/840 PSD A20 7 WH	89 W
910925864351	LL523X LED62S/840 PSD WB 7 SI	41 W
910925864353	LL523X LED123S/840 PSD WB 7 SI	89 W
910925864625	LL523X LED100S/835 PSD WB 7 WH	71 W
910925864627	LL523X LED100S/840 PSD XNB 7 WH XT	71 W
910925864628	LL523X LED123S/840 PSD XNB 7 WH XT	89 W
910925865537	LL523X LED160S/840 PSD MB 7 WH	127 W
910925865538	LL523X LED160S/840 PSD NB 7 WH	127 W
910925865539	LL523X LED160S/840 PSD XNB 7 WH	127 W
910925865540	LL523X LED160S/830 PSD MB 7 WH	125 W
910925865541	LL523X LED160S/830 PSD NB 7 WH	125 W
910925865542	LL523X LED160S/830 PSD XNB 7 WH	125 W
910925864348	LL512X LED31S/840 PSD WB 7 SI	21 W
910925864349	LL512X LED50S/840 PSD WB 7 SI	36 W
910925864350	LL512X LED61S/840 PSD WB 7 SI	45 W
910925864352	LL523X LED100S/840 PSD WB 7 SI	71 W
910925864354	LL512X LED31S/840 PSD WB 7 BK	21 W
910925864355	LL512X LED50S/840 PSD WB 7 BK	36 W
910925864356	LL512X LED61S/840 PSD WB 7 BK	45 W
910925864357	LL523X LED62S/840 PSD WB 7 BK	41 W
910925864358	LL523X LED100S/840 PSD WB 7 BK	71 W
910925864359	LL523X LED123S/840 PSD WB 7 BK	89 W
910925864377	LL612X LED61S/840 PSD WB 7 WH	45 W
910925864378	LL612X LED61S/840 PSD MB 7 WH	45 W
910925864379	LL612X LED61S/840 PSD NB 7 WH	45 W
910925864380	LL623X LED123S/840 PSD WB 7 WH	89 W
910925864381	LL623X LED123S/840 PSD MB 7 WH	89 W
910925864382	LL623X LED123S/840 PSD NB 7 WH	89 W

Mechanical and Housing

Maxos fusion

Order Code	Full Product Name	Color	Order Code	Full Product Name	Color
910925864293	LL512X LED31S/840 PSD PCO 7 WH	White	910925864323	LL523X LED123S/840 PSD NB 7 WH	White
910925864294	LL512X LED50S/840 PSD PCO 7 WH	White	910925864327	LL523X LED62S/840 PSD DA35W 7 WH	White
910925864295	LL512X LED61S/840 PSD PCO 7 WH	White	910925864328	LL523X LED100S/840 PSD DA35W 7 WH	White
910925864296	LL523X LED62S/840 PSD PCO 7 WH	White	910925864329	LL523X LED123S/840 PSD DA35W 7 WH	White
910925864297	LL523X LED100S/840 PSD PCO 7 WH	White	910925864333	LL523X LED62S/840 PSD DA25W 7 WH	White
910925864298	LL523X LED123S/840 PSD PCO 7 WH	White	910925864334	LL523X LED100S/840 PSD DA25W 7 WH	White
910925864299	LL512X LED31S/840 PSED PCO 7 WH	White	910925864335	LL523X LED123S/840 PSD DA25W 7 WH	White
910925864301	LL512X LED50S/840 PSED PCO 7 WH	White	910925864339	LL523X LED62S/840 PSD DA25N 7 WH	White
910925864302	LL512X LED61S/840 PSED PCO 7 WH	White	910925864340	LL523X LED100S/840 PSD DA25N 7 WH	White
910925864303	LL512X LED31S/840 PSD WB 7 WH	White	910925864341	LL523X LED123S/840 PSD DA25N 7 WH	White
910925864304	LL512X LED50S/840 PSD WB 7 WH	White	910925864346	LL523X LED100S/840 PSD A20 7 WH	White
910925864305	LL512X LED61S/840 PSD WB 7 WH	White	910925864347	LL523X LED123S/840 PSD A20 7 WH	White
910925864309	LL512X LED31S/840 PSED WB 7 WH	White	910925864351	LL523X LED62S/840 PSD WB 7 SI	Silver
910925864310	LL512X LED50S/840 PSED WB 7 WH	White	910925864353	LL523X LED123S/840 PSD WB 7 SI	Silver
910925864311	LL512X LED61S/840 PSED WB 7 WH	White	910925864625	LL523X LED100S/835 PSD WB 7 WH	White
910925864312	LL512X LED31S/840 PSD MB 7 WH	White	910925864627	LL523X LED100S/840 PSD XNB 7 WH XT	White
910925864313	LL512X LED50S/840 PSD MB 7 WH	White	910925864628	LL523X LED123S/840 PSD XNB 7 WH XT	White
910925864314	LL512X LED61S/840 PSD MB 7 WH	White	910925865537	LL523X LED160S/840 PSD MB 7 WH	White
910925864320	LL512X LED61S/840 PSD NB 7 WH	White	910925865538	LL523X LED160S/840 PSD NB 7 WH	White
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	White	910925865539	LL523X LED160S/840 PSD XNB 7 WH	White
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	White	910925865540	LL523X LED160S/830 PSD MB 7 WH	White
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	White	910925865541	LL523X LED160S/830 PSD NB 7 WH	White
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	White	910925865542	LL523X LED160S/830 PSD XNB 7 WH	White
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	White	910925864348	LL512X LED31S/840 PSD WB 7 SI	Silver
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	White	910925864349	LL512X LED50S/840 PSD WB 7 SI	Silver
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	White	910925864350	LL512X LED61S/840 PSD WB 7 SI	Silver
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	White	910925864352	LL523X LED100S/840 PSD WB 7 SI	Silver
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	White	910925864354	LL512X LED31S/840 PSD WB 7 BK	Black
910925864344	LL512X LED61S/840 PSD A20 7 WH	White	910925864355	LL512X LED50S/840 PSD WB 7 BK	Black
910925864624	LL512X LED50S/835 PSD WB 7 WH	White	910925864356	LL512X LED61S/840 PSD WB 7 BK	Black
910925864626	LL512X LED61S/840 PSD XNB 7 WH XT	White	910925864357	LL523X LED62S/840 PSD WB 7 BK	Black
910925864306	LL523X LED62S/840 PSD WB 7 WH	White	910925864358	LL523X LED100S/840 PSD WB 7 BK	Black
910925864307	LL523X LED100S/840 PSD WB 7 WH	White	910925864359	LL523X LED123S/840 PSD WB 7 BK	Black
910925864308	LL523X LED123S/840 PSD WB 7 WH	White	910925864377	LL612X LED61S/840 PSD WB 7 WH	White
910925864315	LL523X LED62S/840 PSD MB 7 WH	White	910925864378	LL612X LED61S/840 PSD MB 7 WH	White
910925864316	LL523X LED100S/840 PSD MB 7 WH	White	910925864379	LL612X LED61S/840 PSD NB 7 WH	White
910925864317	LL523X LED123S/840 PSD MB 7 WH	White	910925864380	LL623X LED123S/840 PSD WB 7 WH	White
910925864321	LL523X LED62S/840 PSD NB 7 WH	White	910925864381	LL623X LED123S/840 PSD MB 7 WH	White
910925864322	LL523X LED100S/840 PSD NB 7 WH	White	910925864382	LL623X LED123S/840 PSD NB 7 WH	White

