



PHILIPS

CoreLine




Innovative



Easy to install



High quality



Industry
Office
Parking
Retail
Outdoor

Step aside or **stay ahead?**

Real professionals choose **Philips CoreLine** for every project
where light really matters



**REAL
PROs**
**REAL
QUALITY**



Find out why real pros
rely on **Philips CoreLine:**
the full range of **innovative**
high quality and
easy-to-use LED lighting
solutions for every project
where light really
matters.



4

Introduction

6

Discover what sets CoreLine apart

See why CoreLine is raising the bar in the industry.

8

An LED light for every need

Discover the CoreLine range.



10

Recommended CoreLine products for every application area

Learn about benefits and features of every product.



24

Overview CoreLine indoor and outdoor products



No choice or no limits?

When lighting really matters, you want to offer your customers the absolute best in quality and choice. The Philips CoreLine gives you all that and more with a full range of easy to install LED luminaires for every application and situation.

Enjoy more performance and variety with Philips CoreLine – the complete range of high quality LED lighting that's **setting the reference in the market**.

www.philips.com/coreline

Now with

5
years
warranty!

A photograph of two men on a modern staircase. The man on the left, with a beard and wearing a blue and white checkered shirt under a white jacket, is holding a black tablet. The man on the right, wearing a teal V-neck sweater and grey trousers, is looking at the tablet. The background is a bright, modern interior with white walls and a metal railing.

Reliable quality meets
innovative solutions!



Easy-to-install


The efficient design of the CoreLine fixtures enables replacement of existing lights, with **no need for expensive re-wiring or new ceiling configurations.**



Innovative

With **Philips CoreLine** you get much more than high quality and easy-to-install lighting solutions – you get LED lighting that's setting **the reference** in the industry. That's why CoreLine luminaires are the first Interact Ready LED luminaires and work seamlessly with the **intuitive Interact Pro app and dashboard**. It has never been easier to bring the power of connected lighting to small and medium-sized enterprises.

How the connected lighting system comes together



High quality

At the heart of CoreLine's **high-quality light** is LED technology. Lasting up to 75,000 hours, its **long lifetime** enables you to meet every demand and provide the best lighting solution for every customer.

CoreLine –
an LED light for
every need



CoreLine
highbay



CoreLine
waterproof



CoreLine
trunking



CoreLine
batten

Industry

- Extremely durable and energy-efficient solutions
- Lighting that enhances safety and improves productivity
- Reduce costs and improve sustainability



CoreLine
recessed luminaire



CoreLine **surface-**
mounted luminaire



CoreLine
panel



CoreLine
downlight

Office

- Lighting that optimizes space and productivity
- Enhance employees well-being
- Energy-efficient lamps and luminaires support sustainability goals



CoreLine
waterproof



CoreLine **wall-**
mounted Luminaire



CoreLine **batten**

Parking

- Robust lighting that heightens safety while lowering costs
- Deliver a positive user-experience and improve visibility
- Ensure energy savings and decrease operational costs

CoreLine –
an LED light for
every need



CoreLine **projector**



CoreLine
recessed spot



CoreLine
slim downlight

interact
ready.

Retail

- Welcoming lighting for more sales and satisfaction
- Help to save on energy costs and improve operational efficiency
- Optimize store layouts and customer guidance



CoreLine **bollard**



CoreLine **malaga**



CoreLine **tempo**

Outdoor

- Save energy and improve road safety
- Reduce CO₂ emissions for a greener, more sustainable city
- Connect new and existing street lights quickly and easily

Recommended luminaires for

Industry

- ✓ Reduce costs
- ✓ Optimize operations
- ✓ Enhance health and safety
- ✓ Improve sustainability

CoreLine **highbay**

For warehouses and general manufacturing areas with medium/high height ceilings

- Highly efficient with up to 145lm/W
- **Long service life of 50,000 hrs at L80**
- Single point mounting system for simple installation
- Low glare rating and color rendering of >80
- Suitable for replacement of 250W/400W conventional highbays



Available in three sizes:

- Ø 385 mm
- Ø 450 mm
- Ø 510 mm



Easy installation

Optional DALI dimming for further energy savings



Real pros get 100 % performance in 50 % installation time

CoreLine highbay luminaires are designed for optimized installation – **saving you time and money by getting the job done twice as fast.**





CoreLine **waterproof**

Waterproof luminaire for applications such as parking garages, warehouses or general lighting

- Energy savings and longer lifetime reduce operating costs
- Refreshed, robust design enabling smarter, simpler and faster installation
- Uniform, wide-beam light distribution, which supports easy and attractive lighting design
- Optional motion detection, emergency lighting, DALI and waterproof external connector (WEC)



interact
ready.

**Energy-efficient
and long lifetime:
up to 140lm/W
and 50khrs L75
lifetime**

**Many options
available:
L600/1200/1500,
up to 8000lm,
4000K**

Enhanced product
architecture with
improved
electrical and
mechanical design
(longer sliders, better
metal locks, toolless
electrical
connections)



Real pros cut installation time in half

The CoreLine waterproof is set up 50% faster than before.
See for yourself in our [real installer video](#).





CoreLine **trunking**

Designed for supermarkets, warehouses and assembly areas

- Reduced maintenance and best lumens per € solution
- Excellent beam shapes and sparkle for product enhancement
- **Lifetime: 50,000 hours L80**



Highly efficient and reliable LED boards



Advanced optics enable precise and energy-saving beam shapes

DALI and emergency lighting options available



CoreLine **batten**

LED luminaires especially suitable for assembly lines and cove lighting

- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- Ideal for setting up seamless and aesthetic light-lines creations for warehouses and industrial spaces
- Smart product architecture for tool-free, easy and flexible installation, with through-wiring possibility
- Direct replacement for conventional battens in terms of light performance, installation, flexibility and length
- **Lifetime: 50,000 hours L70**




interact ready.



Easy light-lines creation

Homogeneous light distribution in every application through wide choice of reflectors



Openable top compartment for easy installation



Recommended luminaires for

Offices

- ✓ Optimize operations
- ✓ Enhance productivity
- ✓ Support sustainability goals
- ✓ Optimize space

CoreLine **recessed luminaire**

Recessed office LED luminaire for general lighting applications

- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- Easy connection (with looping)
- Flicker-free thanks to high performance driver
- **Lifetime: 50,000 hours L70**



interact
ready.

Slim design with
a height of less
than 35 mm

**Office compliant
optic** available –
OC version

**Suitable for
plaster ceiling
installation**



CoreLine **surface mounted luminaire**

Surface mounted LED luminaire for general lighting applications

- Easy connection (with looping)
- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- Slim design and <47 mm height
- **Lifetime: 50,000 hours L70**



interact
ready.



**Suspension set available
as an accessory**



**Recessed version also
available for use in grid
ceilings (see above)**

**DALI and
emergency
lighting options
available**





CoreLine panel

Recessed office LED luminaire for general lighting applications

- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- New option: Warm and cool white light, as well as four lumen packages in one luminaire
- New connector for simpler and faster installation
- Higher energy savings and lifetime
- Smooth surface of light for office-compliance
- Optional high-quality DALI driver
- Optional versions available: Emergency Lighting (EL) and Wieland/Adels connectors (W)
- **Lifetime: 50,000 hours L80**



New

interact
ready.



PSU MultiColor/Lumen driver



Easy connector

MultiColor/Lumen feature:

3000 K /4000 K
and different lumen
output ranging from
3400 to 4300
lumen in one single
luminaire





CoreLine **downlight**

The perfect downlight for use in general lighting applications

- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- Covers more professional applications due to dimming options and different optics (white and high gloss reflector)
- Reliable DALI and innovative connectivity options (Interact)
- IP54 and emergency lighting versions optionally available
- **Lifetime: 50,000 hours L70**
- Up to 115 lm/W



interact
ready.



White reflector



High gloss reflector

Two sizes and lumen outputs available:

- Ø 150 mm – 1100lm
- Ø 200 mm – 2200lm



Recommended luminaires for

Parking

- ✓ Optimize operations
- ✓ Enhance safety
- ✓ Decreased operational costs
- ✓ Improve visibility

CoreLine **waterproof**

Waterproof luminaire for applications such as parking garages, warehouses or general lighting

- Energy savings and longer lifetime reduce operating costs
- Refreshed, robust design enabling smarter, simpler and faster installation
- Uniform, wide-beam light distribution, which supports easy and attractive lighting design
- Optional motion detection, emergency lighting, DALI and waterproof external connector (WEC)



interact
ready.

**Energy-efficient
and long lifetime:
up to 140lm/W
and 50khrs L75
lifetime**

**Many options
available:
L600/1200/1500,
up to 8000lm,
4000K**

Enhanced product
architecture with
improved
electrical and
mechanical design
(longer sliders, better
metal locks, toolless
electrical
connections)



Real pros cut installation time in half

The CoreLine waterproof is set up 50 % faster than before.
See for yourself in our [real installer video](#).



CoreLine wall-mounted

For circulation areas such as hallways and staircases

- Universal solution covering **various application requirements**
- Direct replacement of traditional wall-mounted luminaires
- Delivering the right visual comfort in common areas
- **Water- and vandalproof** as standard (IP65/IK08)
- Optional motion detection with grouping function
- Optional emergency lighting and DALI versions
- **Lifetime: 50,000 hours L70**




Easy installation with looping-wire option



Slim version with diameter of 35 cm (1200 or 2000lm)



Deeper version with diameter 35 or 48 cm (1200, 2000 or 3400lm)



CoreLine batten

For production areas with low ceilings


- Ideal for setting up seamless and aesthetic light-lines creations
- Tool-free, easy and flexible installation, with through-wiring possibility
- Direct replacement for conventional battens in terms of light performance, installation, flexibility and length
- **Lifetime: 50,000 hours L70**



interact
ready.




Easy light-lines creation



Homogeneous light distribution in every application through wide choice of reflectors



Openable top compartment for easy installation



Recommended luminaires for

Retail

- ✓ Enhance experience
- ✓ Engage customers
- ✓ Improve sustainability
- ✓ Optimize operations

CoreLine projector

Accent lighting for retail or hospitality areas

- **Modern design** that blends in to most interiors
- Direct replacement of traditional CDM projectors
- Connectable to standard 3C track systems
- **Medium beam** (23D) or **wide beam angle** (36D) available
- Energy efficient: up to 90lm/W
- **Lifetime: 50,000 hours L70**



Recessed lens providing
visual comfort



Black version





CoreLine **recessed spot**

Recessed spot for accent lighting purposes

- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- High-end materials for decorative applications and special **anti-glare optics**
- **Flicker-free** luminaire with high-performance driver
- **Dimmable** on wide range of wall-dimmers
- Multiple rims available in white, aluminium and black
- Slim design fits most ceiling types
- **Lifetime: 50,000 hours L70**



Three lumen outputs available:

- 650lm
- 900lm
- 1200lm



CoreLine **slim downlight**

The ultra thin downlight for general lighting applications with limited built-in-height

- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- 'Surface of light' downlight solution
- Product height of less than 50 mm
- Recessed and surface mounted version available
- Slim design fits most ceiling types
- **Lifetime: 50,000 hours L70**



interact
ready.



Three sizes and lumen outputs available:

- Ø 68 mm/650lm
- Ø 150 mm/1100lm
- Ø 200 mm/2100lm



Recommended luminaires for Outdoor

- ✓ Enhance experience
- ✓ Engage customers
- ✓ Improve sustainability
- ✓ Optimize operations

CoreLine **bollard**

Professional bollard that gives guidance at night time and integrates well in most urban landscapes such as parks, squares and playgrounds, thanks to its discreet design

- **Comfortable light**

- Easy to install
- Saves energy compared to conventional lamps



Available with **symmetric and asymmetric optic**. Ground section **anchor accessory**.

- 1000lm system output
- 1 m height
- IP65 / IK10

Available in **warm white** and **neutral white**



CoreLine **malaga**

Designed for general road, street and residential application

- **Reliable quality: aluminum die-cast housing and tempered flat glass**

- **Maintainable, driver can be replaced**

- IP65 and IK08 provide durable operation



Available in **two optics** (DM and DW) and **two sizes**

Easy return on investment. The investment in the luminaire, by saving lamp changes required for SON-T lamp luminaires, is already re-paid.

Energy savings of 50% reduce yearly running costs of the installation. Available in 3700lm, 5500lm, 7500lm and 11000lm.





CoreLine tempo

Professional floodlight for general outdoor lighting, perfect for sports facilities, parking lots and industrial areas

- Replacement of conventional floodlights up to 400W
- High-performance asymmetrical and symmetrical optics
- U-shaped universal mounting bracket and external quick 3-pole IP68 connector
- Reliable quality: Die-casting aluminum housing guarantees robustness, vibration-proof, wind force protection



Product available in 4 types/sizes:

- [CoreLine tempo small](#)
BVP110 - Length 285 mm
- [CoreLine tempo medium](#)
BVP125 - Length 383 mm
- [CoreLine tempo large](#)
BVP130 - Length 486 mm
- [CoreLine tempo X-large](#)
BVP140 - Length: 583 mm

**Warm white and
neutral white
available**

**Seaside resistant
treatment and
swimming pool
protection
options available**



*Click on product type to
download family leaflet*

Overview CoreLine products

CoreLine recessed luminaire



L75 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC134B LED27S/840 PSD W30L120 OC	22	2700	4000	IP44	34812000
RC134B LED27S/840 PSD W60L60 OC		2700	4000	IP44	34810600
RC134B LED27S/830 PSD W30L120 OC	23	2700	3000	IP44	34816800
RC134B LED27S/830 PSD W60L60 OC		2700	3000	IP44	34814400
RC134B LED27S/840 PSD W30L120 ELB3 OC	25.5	2700	4000	IP44	34837300
RC134B LED27S/840 PSD W60L60 ELB3 OC		2700	4000	IP44	34822900
RC134B LED27S/840 PSD W30L120 NOC	26.5	2700	4000	IP44	34826700
RC134B LED27S/840 PSD W60L60 NOC		2700	4000	IP44	34825000
RC134B LED27S/840 PSU W30L120 NOC	27	2700	4000	IP44	34824300
RC134B LED27S/840 PSU W60L60 NOC		2700	4000	IP44	34823600
RC134B LED27S/830 PSU W30L120 NOC	28.5	2700	3000	IP44	34797000
RC134B LED27S/830 PSU W60L60 NOC		2700	3000	IP44	34795600
RC134B LED27S/830 PSD W30L120 NOC	30.5	2700	3000	IP44	34803800
RC134B LED27S/830 PSD W60L60 NOC		2700	3000	IP44	34801400
RC134B LED27S/840 PSD W30L120 ELB3 NOC		2700	4000	IP44	34835900
RC134B LED27S/840 PSD W60L60 ELB3 NOC		2700	4000	IP44	34828100
RC134B LED27S/840 PSU W30L120 ELB3 NOC		2700	4000	IP44	34833500
RC134B LED27S/840 PSU W60L60 ELB3 NOC		2700	4000	IP44	34827400
RC134B LED37S/840 PSU W30L120 OC	31.5	3700	4000	IP44	34830400
RC134B LED37S/840 PSU W60L60 OC		3700	4000	IP44	34829800
RC134B LED37S/830 PSD W30L120 OC		3700	3000	IP44	34815100
RC134B LED37S/830 PSD W60L60 OC		3700	3000	IP44	34813700
RC134B LED37S/840 PSD W30L120 OC	32	3700	4000	IP44	34811300
RC134B LED37S/840 PSD W60L60 OC		3700	4000	IP44	34804500
RC135B LED37S/840 PSD W62L62 OC	34	3700	4000	IP44	34845800
RC134B LED27S/830 PSU W30L120 ELB3 NOC		2700	3000	IP44	34839700
RC134B LED27S/830 PSD W30L120 ELB3 NOC		2700	3000	IP44	34841000
RC134B LED37S/830 PSU W30L120 NOC		3700	3000	IP44	34796300
RC134B LED37S/830 PSU W60L60 NOC	34.5	3700	3000	IP44	34794900
RC134B LED37S/840 PSU W30L120 NOC		3700	4000	IP44	34818200
RC134B LED37S/840 PSU W60L60 NOC	35	3700	4000	IP44	34817500
RC134B LED37S/830 PSU W30L120 OC		3700	3000	IP44	34832800
RC134B LED37S/830 PSU W60L60 OC	35.4	3700	3000	IP44	34831100
RC134B LED37S/830 PSD W30L120 ELB3 OC		3700	3000	IP44	34843400
RC134B LED37S/840 PSD W30L120 ELB3 OC	35.5	3700	4000	IP44	34838000
RC134B LED37S/840 PSD W60L60 ELB3 OC		3700	4000	IP44	34821200
RC135B LED37S/840 W62L62 IA1 NOC	35.5	3700	4000	IP20/44	99655300
RC135B LED37S/840 W62L62 IA1 OC		3700	4000	IP20/44	99652200
RC134B LED37S/830 PSD W30L120 NOC	35.5	3700	3000	IP44	34802100
RC134B LED37S/830 PSD W60L60 NOC		3700	3000	IP44	34800700
RC134B LED37S/840 PSD W30L120 ELB3 NOC		3700	4000	IP44	34836600
RC134B LED37S/840 PSD W30L120 NOC		3700	4000	IP44	34799400
RC134B LED37S/840 PSD W60L60 NOC		3700	4000	IP44	34798700
RC135B LED37S/840 PSD W62L62 NOC		3700	4000	IP44	34850200

CoreLine recessed luminaire – Continued



L75 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC134B LED37S/830 PSU W30L120 ELB3 NOC	38	3700	3000	IP44	34840300
RC134B LED37S/840 PSU W30L120 ELB3 NOC		3700	4000	IP44	34834200
RC134B LED37S/840 PSU W60L60 ELB3 NOC		3700	4000	IP44	34819900
RC134B LED37S/830 PSD W30L120 ELB3 NOC	39	3700	3000	IP44	34842700
RC134B LED37S/840 PSD W60L60 ELB3 NOC		3700	4000	IP44	34820500

CoreLine recessed luminaire – Accessories



1 PACK

Product Type	EOC code
RC134Z CFRM-PLC WH W60L60	98722300
RC134Z CFRM-PLC WH W30L120	98724700

CoreLine panel – Non Office Compliant (NOC)



L80 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC132V G4 LED36S/840 PSU W60L60 NOC	29	3600	4000	IP20/44	36035500
RC133V G4 LED36S/840 PSU W62L62 NOC		3600	4000	IP20/44	36038600
RC133V G4 LED34S/830 PSU W62L62 NOC		3400	3000	IP20/44	36039300
RC132V G4 LED34S/830 PSU W60L60 NOC		3400	3000	IP20/44	36036200
RC132V G4 LED36S/840 PSU W30L120 NOC		3600	4000	IP20/44	36040900
RC132V G4 LED43S/840 PSU W60L60 NOC	34.5	4300	4000	IP20/44	36037900

CoreLine panel – Office Compliant (OC)



L80 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC133V G4 LED36S/840 PSD W62L62 OC	29	3600	4000	IP20/44	36048500
RC132V G4 LED34S/830 PSD W30L120 OC		3400	3000	IP20/44	36052200
RC132V G4 LED36S/840 PSU W30L120 OC		3600	4000	IP20/44	36044700
RC133V G4 LED36S/840 PSU W62L62 OC		3600	4000	IP20/44	36043000
RC132V G4 LED34S/830 PSD W60L60 OC		3400	3000	IP20/44	36046100
RC132V G4 LED36/840 PSU W60L60 OC TP(a)		3600	4000	IP20/44	36053900
RC133V G4 LED34S/830 PSD W62L62 OC		3400	3000	IP20/44	36049200
RC132V G4 LED34S/830 PSU W60L60 OC		3400	3000	IP20/44	36042300
RC132V G4 LED36S/840 PSD W60L60 OC		3600	4000	IP20/44	36045400
RC132V G4 LED36S/840 PSU W60L60 OC		3600	4000	IP20/44	36041600
RC132V G4 LED36S/840 PSD W30L120 OC		3600	4000	IP20/44	36051500

CoreLine panel – Office Compliant (OC) – Continued



L80 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC132V G4LED34_43S/830_840 PSU W60L60 OC	30 ~ 35	3400, 3600, 4000, 4300	3000 and 4000	IP20/44	36054600
RC133V G4LED34_43S/830_840 PSU W62L62 OC		3400, 3600, 4000, 4300	3000 and 4000	IP20/44	36055300
RC132V G4LED34_43S/830_840 PSUW30L120 OC		3400, 3600, 4000, 4300	3000 and 4000	IP20/44	36056000
RC132V G4 LED36/840 PSU W60L60 OC TP(a)E	32	3600	4000	IP20/44	96722200
RC132V G4 LED36S/840 PSU W30L120 OC ELB3		3600	4000	IP20/44	96714700
RC132V G4 LED36S/840 PSU W60L60 OC ELB3		3600	4000	IP20/44	96711600
RC132V G4 LED36S/840 PSD W30L120 OC ELB3		3600	4000	IP20/44	96715400
RC132V G4 LED36S/840 PSD W60L60 OC ELB3		3600	4000	IP20/44	96710900
RC133V G4 LED43S/840 PSD W62L62 OC	34.5	4300	4000	IP20/44	36050800
RC132V G4 LED43S/840 PSD W60L60 OC		4300	4000	IP20/44	36047800
RC132V G4 LED43S/840 PSD W60L60 OC ELB3	37	4300	4000	IP20/44	96719200

CoreLine panel – Accessories



1 PACK

Product Type	EOC code
RC132Z SC - safety cable	36268799
RC132Z SME-3 WH Suspension set for 3 core wires for PSU luminaire	36270099
RC132Z SME-4 WH Suspension set with 4 core wires for PSD (dali) luminaires	36271799
RC132Z SMB W60L60 Surface Mounted Bracket	07330899
RC133Z SMB W62L62 Surface Mounted Bracket	07331599
RC132Z SMB W30L120 Surface Mounted Bracket	07332299
RC132Z SMB-PLC Plaster Ceiling Bracket	36269499

CoreLine surface-mounted luminaire – Non Office Compliant (NOC)



L75 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
SM134V LED27S/840 PSD W60L60 NOC	26.5	2700	4000	IP20	34877900
SM134V LED27S/840 PSD W20L120 NOC		2700	4000	IP20	34878600
SM134V LED27S/840 PSU W60L60 NOC	27	2700	4000	IP20	34875500
SM134V LED27S/840 PSU W20L120 NOC		2700	4000	IP20	34876200
SM134V LED27S/830 PSU W60L60 NOC	28.5	2700	3000	IP20	34852600
SM134V LED27S/830 PSU W20L120 NOC		2700	3000	IP20	34854000
SM134V LED27S/830 PSD W60L60 NOC	30.5	2700	3000	IP20	34858800
SM134V LED27S/830 PSD W20L120 NOC		2700	3000	IP20	34860100
SM134V LED27S/840 PSU W60L60 ELB3 NOC	30.5	2700	4000	IP20	34879300
SM134V LED27S/840 PSD W60L60 ELB3 NOC		2700	4000	IP20	34880900
SM134V LED27S/840 PSU W20L120 ELB3 NOC	32	2700	4000	IP20	34885400
SM134V LED27S/840 PSD W20L120 ELB3 NOC		2700	4000	IP20	34887800
SM134V LED27S/830 PSU W20L120 ELB3 NOC	32	2700	3000	IP20	34891500

CoreLine surface-mounted luminaire – Non Office Compliant (NOC) – Continued



L75 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
SM134V LED37S/830 PSU W60L60 NOC	34	3700	3000	IP20	34851900
SM134V LED37S/830 PSU W20L120 NOC		3700	3000	IP20	34853300
SM134V LED37S/840 PSU W60L60 NOC		3700	4000	IP20	34869400
SM134V LED37S/840 PSU W20L120 NOC		3700	4000	IP20	34870000
SM134V LED27S/830 PSD W20L120 ELB3 NOC		2700	3000	IP20	34893900
SM134V LED37S/840 PSD W60L60 NOC	35.5	3700	4000	IP20	34855700
SM134V LED37S/840 PSD W20L120 NOC		3700	4000	IP20	34856400
SM134V LED37S/830 PSD W60L60 NOC		3700	3000	IP20	34857100
SM134V LED37S/830 PSD W20L120 NOC		3700	3000	IP20	34859500
SM134V LED37S/840 PSD W20L120 ELB3 NOC		3700	4000	IP20	34888500
SM134V LED37S/840 PSU W60L60 ELB3 NOC	38	3700	4000	IP20	34871700
SM134V LED37S/840 PSU W20L120 ELB3 NOC		3700	4000	IP20	34886100
SM134V LED37S/830 PSU W20L120 ELB3 NOC		3700	3000	IP20	34892200
SM134V LED37S/840 PSD W60L60 ELB3 NOC	39	3700	4000	IP20	34872400
SM134V LED37S/830 PSD W20L120 ELB3 NOC		3700	3000	IP20	34894600

CoreLine surface-mounted luminaire – Office Compliant (OC)



L75 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
SM134V LED27S/840 PSD W60L60 OC	22	2700	4000	IP20	34862500
SM134V LED27S/840 PSD W20L120 OC		2700	4000	IP20	34864900
SM134V LED27S/830 PSD W60L60 OC	23	2700	3000	IP20	34866300
SM134V LED27S/830 PSD W20L120 OC		2700	3000	IP20	34868700
SM134V LED27S/840 PSD W60L60 ELB3 OC	25.5	2700	4000	IP20	34874800
SM134V LED27S/840 PSD W20L120 ELB3 OC		2700	4000	IP20	34889200
SM134V LED37S/840 PSU W60L60 OC	30.5	3700	4000	IP20	34881600
SM134V LED37S/840 PSU W20L120 OC		3700	4000	IP20	34882300
SM134V LED37S/840 PSD W60L60 OC	31.5	3700	4000	IP20	34861800
SM134V LED37S/840 PSD W20L120 OC		3700	4000	IP20	34863200
SM134V LED37S/830 PSD W60L60 OC		3700	3000	IP20	34865600
SM134V LED37S/830 PSD W20L120 OC		3700	3000	IP20	34867000
SM134V LED37S/830 PSU W60L60 OC	34.5	3700	3000	IP20	34883000
SM134V LED37S/830 PSU W20L120 OC		3700	3000	IP20	34884700
SM134V LED37S/840 PSD W60L60 ELB3 OC	35	3700	4000	IP20	34873100
SM134V LED37S/840 PSD W20L120 ELB3 OC		3700	4000	IP20	34890800

CoreLine surface-mounted luminaire – Accessories



1 PACK

Product Type	IP rating	EOC code
SM134Z SME-3	IP20	34897700
SM134Z SME-5	IP20	34895300
SM134Z SMS	IP20	34896000

CoreLine wall-mounted luminaire



L70 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
WL130V LED12S/830 PSU WH	12	1200	3000	IP65	38778599
WL130V LED12S/840 PSU WH		1200	4000	IP65	38779299
WL131V LED12S/830 PSED EL3 WH		1200	3000	IP65	40268600
WL131V LED12S/830 PSR EL3 MDU WH		1200	3000	IP65	40282200
WL131V LED12S/840 PSED EL3 WH		1200	4000	IP65	40269300
WL131V LED12S/840 PSR EL3 MDU WH		1200	4000	IP65	40283900
WL131V LED12S/830 PSED WH	13	1200	3000	IP65	38792199
WL131V LED12S/840 PSED WH		1200	4000	IP65	38793899
WL131V LED12S/830 PSR MDU WH	15	1200	3000	IP65	38786099
WL131V LED12S/840 PSR MDU WH		1200	4000	IP65	38787799
WL131V LED12S/830 PSED WH	13	1200	3000	IP65	38792199
WL131V LED12S/840 PSED WH		1200	4000	IP65	38793899
WL131V LED12S/830 PSR MDU WH	15	1200	3000	IP65	38786099
WL131V LED12S/840 PSR MDU WH		1200	4000	IP65	38787799
WL130V LED20S/830 PSU WH	22	2000	3000	IP65	38780899
WL130V LED20S/840 PSU WH		2000	4000	IP65	38781599
WL131V LED20S/830 PSED EL3 WH		2000	3000	IP65	40270900
WL131V LED20S/830 PSR EL3 MDU WH		2000	3000	IP65	40284600
WL131V LED20S/840 PSED EL3 WH		2000	4000	IP65	40271600
WL131V LED20S/840 PSR EL3 MDU WH		2000	4000	IP65	40285300
WL130V LED20S/830 PSU MDU WH	23	2000	3000	IP65	38782299
WL130V LED20S/840 PSU MDU WH		2000	4000	IP65	38783999
WL131V LED20S/830 PSED WH		2000	3000	IP65	38794599
WL131V LED20S/840 PSED WH		2000	4000	IP65	38795299
WL131V LED20S/830 PSR MDU WH	25	2000	3000	IP65	38788499
WL131V LED20S/840 PSR MDU WH		2000	4000	IP65	38789199
WL131V LED34S/830 PSED EL3 WH	36	3400	3000	IP65	40274700
WL131V LED34S/830 PSED WH		3400	3000	IP65	40272300
WL131V LED34S/830 PSR EL3 MDU WH		3400	3000	IP65	40286000
WL131V LED34S/830 PSU WH		3400	3000	IP65	38784699
WL131V LED34S/840 PSED EL3 WH		3400	4000	IP65	40275400
WL131V LED34S/840 PSED WH		3400	4000	IP65	40273000
WL131V LED34S/840 PSR EL3 MDU WH		3400	4000	IP65	40287700
WL131V LED34S/840 PSU WH		3400	4000	IP65	38785399
WL131V LED34S/830 PSR MDU WH	38	2000	3000	IP65	38790799
WL131V LED34S/840 PSR MDU WH		2000	4000	IP65	38791499

CoreLine waterproof



IK08 | 5 J
vandal-protected



L75 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
WT120C G2 LED19S/840 PSU L600	15	1900	4000	IP65	84045900
WT120C G2 LED18S/840 PSU PCO L600		1800	4000	IP65	34976399
WT120C G2 LED19S/840 PSU MDU L600	16	1900	4000	IP65	96244900
WT120C G2 LED19S/840 PSD L600		1900	4000	IP65	88306800
WT120C G2 LED27S/840 PSU L1200	20.5	2700	4000	IP65	84046600
WT120C G2 LED25S/840 PSU PCO L1200		2500	4000	IP65	34977099

CoreLine waterproof – Continued



IK08 | 5 J
vandal-protected



L75 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
WT120C G2 LED27S/840 PSU TW3 L1200	21	2700	4000	IP65	91685800
WT120C G2 LED27S/840 PSU MDU TW3 L1200		2700	4000	IP65	96249400
WT120C G2 LED27S/840 PSU MDU L1200	22	2700	4000	IP65	96248700
WT120C G2 LED27S/840 PSD L1200		2700	4000	IP65	88307500
WT120C G2 LED34S/840 PSU L1500	24.3	3400	4000	IP65	84047300
WT120C G2 LED31S/840 PSU PCO L1500		3100	4000	IP65	34978799
WT120C G2 LED34S/840 PSD L1500	25.5	3400	4000	IP65	88308200
WT120C G2 LED34S/840 PSU TW3 L1500		3400	4000	IP65	91686500
WT120C G2 LED27S/840 PSU ELB3 L1200	26	2700	4000	IP65	85418000
WT120C G2 LED34S/840 PSU MDU TW3 L1500	26.5	3400	4000	IP65	96268500
WT120C G2 LED34S/840 PSU MDU L1500		3400	4000	IP65	96267800
WT120C G2 LED27S/840 PSD ELB3 L1200	27	2700	4000	IP65	88311200
WT120C G2 LED27S/840 PSU MDU ELB3 L1200	28	2700	4000	IP65	96251700
WT120C G2 LED40S/840 PSU L1200	28.6	4000	4000	IP65	84048000
WT120C G2 LED37S/840 PSU PCO L1200		3700	4000	IP65	34979499
WT120C G2 LED40S/840 PSU TW1 WEC L1200		4000	4000	IP65	16317400
WT120C G2 LED40S/840 PSU WEC L1200	30	4000	4000	IP65	16316700
WT120C G2 LED40S/840 PSD L1200		4000	4000	IP65	88309900
WT120C G2 LED40S/840 PSU TW3 L1200		4000	4000	IP65	91687200
WT120C G2 LED34S/840 PSU ELB3 L1500	30.5	3400	4000	IP65	85420300
WT120C G2 LED34S/840 PSD ELB3 L1500	30.5	3400	4000	IP65	88313600
WT120C G2 LED40S/840 PSU MDU TW3 L1200	31	4000	4000	IP65	96257900
WT120C G2 LED40S/840 PSU MDU L1200		4000	4000	IP65	96256200
WT120C G2 LED34S/840 PSU MDU ELB3 L1500	31.5	3400	4000	IP65	96271500
WT120C G2 LED40S/840 PSD ELB3 L1200	35	4000	4000	IP65	88312900
WT120C G2 LED40S/840 PSU ELB3 L1200		4000	4000	IP65	85419700
WT120C G2 LED40S/840 PSU MDU ELB3 L1200	36	4000	4000	IP65	96263000
WT120C G2 LED60S/840 PSU L1500	42.9	6000	4000	IP65	84049700
WT120C G2 LED57S/840 PSU PCO L1500		5700	4000	IP65	34980099
WT120C G2 LED60S/840 PSU WEC L1500		6000	4000	IP65	16318100
WT120C G2 LED60S/840 PSU TW1 WEC L1500	45	6000	4000	IP65	16319800
WT120C G2 LED60S/840 PSU TW3 L1500		6000	4000	IP65	91688900
WT120C G2 LED60S/840 PSD L1500		6000	4000	IP65	88310500
WT120C G2 LED60S/840 PSU MDU L1500	46	6000	4000	IP65	96275300
WT120C G2 LED60S/840 PSU MDU TW3 L1500		6000	4000	IP65	96276000
WT120C G2 LED60S/840 PSU ELB3 L1500	50	6000	4000	IP65	85421000
WT120C G2 LED60S/840 PSU MDU ELB3 L1500	51	6000	4000	IP65	96282100
WT120C G2 LED60S/840 PSD ELB3 L1500		6000	4000	IP65	88314300
WT120C G2 LED80S/840 PSU L1500	57.1	8000	4000	IP65	40928900
WT120C G2 LED75S/840 PSU PCO L1500		7500	4000	IP65	34981799
WT120C G2 LED80S/840 PSU TW3 L1500		8000	4000	IP65	40930200
WT120C G2 LED80S/840 PSD L1500	61	8000	4000	IP65	40929600
WT120C G2 LED80S/840 PSU MDU L1500		8000	4000	IP65	96286900
WT120C G2 LED80S/840 PSU L1500 ELB3	66	8000	4000	IP65	40931900

CoreLine slim downlight



L70 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
Coreline SlimDownlight Recessed					
DN145B LED6S/830 PSU II WH	6.5	650	3000	IP20/44	33945099
DN145B LED6S/840 PSU II WH		650	4000	IP20/44	33946799
DN145B LED10S/830 PSU II WH	11	1100	3000	IP20/44	33947499
DN145B LED10S/840 PSU II WH		1100	4000	IP20/44	33948199
DN145B LED10S/830 PSD-E II WH	13	1100	3000	IP20/44	96100899
DN145B LED10S/840 PSD-E II WH		1100	4000	IP20/44	96101599
DN145B LED20S/830 PSU II WH	21	2100	3000	IP20/44	33949899
DN145B LED20S/840 PSU II WH		2100	4000	IP20/44	33950499
DN145B LED20S/830 PSD-E II WH	22.5	2100	3000	IP20/44	96102299
DN145B LED20S/840 PSD-E II WH		2100	4000	IP20/44	96103999
DN145B LED20S/830 IA1 WH	22.5	2100	3000	IP20/44	96098899
DN145B LED20S/840 IA1 WH		2100	4000	IP20/44	96099599
Coreline SlimDownlight Surface Mounted					
DN145C LED10S/830 PSU II WH	11	1100	3000	IP44	33951199
DN145C LED10S/840 PSU II WH		1100	4000	IP44	33952899
DN145C LED20S/830 PSU II WH	21	2100	3000	IP44	33953599
DN145C LED20S/840 PSU II WH		2100	4000	IP44	33954299

CoreLine downlight



L70 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
DN140B LED10S/830 PSU C IP54 PI6	9.5	1100	3000	IP20/54	32604700
DN140B LED10S/830 PSU C PI6		1100	3000	IP20	32588000
DN140B LED10S/830 PSU WR IP54 PI6		1100	3000	IP20/54	32596500
DN140B LED10S/830 PSU WR PI6		1100	3000	IP20	32580400
DN140B LED10S/840 PSU C IP54 PI6		1100	4000	IP20/54	32605400
DN140B LED10S/840 PSU C PI6		1100	4000	IP20	32589700
DN140B LED10S/840 PSU WR IP54 PI6		1100	4000	IP20/54	32597200
DN140B LED10S/840 PSU WR PI6		1100	4000	IP20	32581100
DN140B LED10S/830 PSD-E C IP54	11.5	1100	3000	IP20/54	32606100
DN140B LED10S/830 PSD-E WR IP54		1100	3000	IP20/54	32598900
DN140B LED10S/840 PSD-E C IP54		1100	4000	IP20/54	32607800
DN140B LED10S/840 PSD-E WR IP54		1100	4000	IP20/54	32599600
DN140B LED10S/830 PSD-E WR		1100	3000	IP20	32582800
DN140B LED10S/840 PSD-E WR		1100	4000	IP20	32583500
DN140B LED10S/830 PSD-E C		1100	3000	IP20	32590300
DN140B LED10S/840 PSD-E C		1100	4000	IP20	32591000
DN140B LED10S/840 PSD-E C ELB3	14.5	1100	4000	IP20	32836200
DN140B LED10S/830 PSD-E C ELB3		1100	3000	IP20	32835500
DN140B LED10S/830 PSD-E WR ELB3		1100	3000	IP20	32831700
DN140B LED10S/840 PSD-E WR ELB3		1100	4000	IP20	32832400
DN140B LED20S/830 PSU C IP54 PI6	19	2200	3000	IP20/54	32608500
DN140B LED20S/830 PSU C PI6		2200	3000	IP20	32592700
DN140B LED20S/830 PSU WR IP54 PI6		2200	3000	IP20/54	32600900
DN140B LED20S/830 PSU WR PI6		2200	3000	IP20	32584200
DN140B LED20S/840 PSU C IP54 PI6		2200	4000	IP20/54	32609200
DN140B LED20S/840 PSU C PI6		2200	4000	IP20	32593400

CoreLine downlight – Continued



L70 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
DN140B LED20S/840 PSU WR IP54 PI6	19	2200	4000	IP20/54	32601600
DN140B LED20S/840 PSU WR PI6		2200	4000	IP20	32585900
DN140B LED20S/830 PSD-E C IP54	20.5	2200	3000	IP20/54	32610800
DN140B LED20S/830 PSD-E WR IP54		2200	3000	IP20/54	32602300
DN140B LED20S/840 PSD-E C IP54		2200	4000	IP20/54	32611500
DN140B LED20S/840 PSD-E WR IP54		2200	4000	IP20/54	32603000
DN140B LED20S/830 PSD-E WR		2200	3000	IP20	32586600
DN140B LED20S/840 PSD-E WR		2200	4000	IP20	32587300
DN140B LED20S/830 PSD-E C		2200	3000	IP20	32594100
DN140B LED20S/840 PSD-E C		2200	4000	IP20	32595800
DN140B LED20S/830 WR IA1		2200	3000	IP20	32612200
DN140B LED20S/840 WR IA1		2200	4000	IP20	32613900
DN140B LED20S/830 C IA1	22	2200	3000	IP20	32614600
DN140B LED20S/840 C IA1		2200	4000	IP20	32615300
DN140B LED20S/830 PSD-E C ELB3	23.5	2200	3000	IP20	32837900
DN140B LED20S/830 PSD-E WR ELB3		2200	3000	IP20	32833100
DN140B LED20S/840 PSD-E C ELB3		2200	4000	IP20	32838600
DN140B LED20S/840 PSD-E WR ELB3		2200	4000	IP20	32834800
DN140B LED20S/830 WR ELB3 IA1	25	2200	3000	IP20	32839300
DN140B LED20S/840 WR ELB3 IA1		2200	4000	IP20	32840900
DN140B LED20S/830 C ELB3 IA1		2200	3000	IP20	32841600
DN140B LED20S/840 C ELB3 IA1		2200	4000	IP20	32842300

CoreLine recessed spot



L70 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RS140B LED6-32-/827 PSR PI6 ALU	8	650	2700	IP65	38287299
RS140B LED6-32-/827 PSR PI6 WH		650	2700	IP65	38277399
RS140B LED6-32-/830 PSR PI6 ALU		650	3000	IP65	38288999
RS140B LED6-32-/830 PSR PI6 WH		650	3000	IP65	38278099
RS140B LED6-32-/840 PSR PI6 ALU		650	4000	IP65	38289699
RS140B LED6-32-/840 PSR PI6 WH		650	4000	IP65	38279799
RS141B LED6-32-/827 PSR PI6 ALU		650	2700	IP44	38290299
RS141B LED6-32-/827 PSR PI6 WH		650	2700	IP44	38280399
RS141B LED6-32-/830 PSR PI6 ALU		650	3000	IP44	38291999
RS141B LED6-32-/830 PSR PI6 WH		650	3000	IP44	38281099
RS141B LED6-32-/840 PSR PI6 ALU		650	4000	IP44	38292699
RS141B LED6-32-/840 PSR PI6 WH		650	4000	IP44	38282799
RS142B LED6-32-/827 PSR PI6 WH FR		650	2700	IP44	38417399
RS142B LED6-32-/830 PSR PI6 WH FR		650	3000	IP44	38418099
RS140B LED9-32-/830 PSR PI6 ALU	11	900	3000	IP65	38293399
RS140B LED9-32-/830 PSR PI6 WH		900	3000	IP65	38285899
RS140B LED9-32-/840 PSR PI6 ALU		900	4000	IP65	38294099
RS140B LED9-32-/840 PSR PI6 WH		900	4000	IP65	38286599
RS141B LED9-32-/830 PSR PI6 WH		900	3000	IP44	38283499
RS141B LED9-32-/840 PSR PI6 WH		900	4000	IP44	38284199

CoreLine recessed spot – Continued



L70 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RS140B LED12-36-/830 PSR PI6 ALU	15	1200	3000	IP65	38423499
RS140B LED12-36-/830 PSR PI6 WH		1200	3000	IP65	38421099
RS140B LED12-36-/840 PSR PI6 ALU		1200	4000	IP65	38424199
RS140B LED12-36-/840 PSR PI6 WH		1200	4000	IP65	38422799
RS141B LED12-36-/830 PSR PI6 WH		1200	3000	IP44	38419799
RS141B LED12-36-/840 PSR PI6 WH		1200	4000	IP44	38420399

CoreLine recessed spot – Accessories



1 PACK

Product Type	IP rating	EOC code
1 Grid light		
RS143Z CFRM GRID 1x1 WH	IP20	38832499
RS143Z CFRM GRID 1x3 WH	IP20	38834899
RS143Z CFRM GRID 1x2 WH	IP20	38833199
2 LED Module		
RS140Z MODULE LED6-32-/827		38295799
RS140Z MODULE LED9-32-/830		38296499
RS140Z MODULE LED6-32-/840		38297199
RS140Z MODULE LED6-32-/830		38298899
RS140Z MODULE LED9-32-/840		38299599
3 Round rim black		
RS140Z CFRM RND-ADJUST D80 BK		38448799
4 Square rim white		
RS140Z CFRM SQR-ADJUST WH		38456299
5 Square rim aluminum		
RS140Z CFRM SQR-ADJUST ALU		38458699
6 Square darklight		
RS140Z CFRM SQR-FIX Darklight		38508899

CoreLine projector



L70 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
ST150T LED22S-23-/830 PSU BK	24	2200	3000	IP20	79067799
ST150T LED22S-23-/840 PSU BK		2200	4000	IP20	79068499
ST150T LED22S-23-/830 PSU WH		2200	3000	IP20	79069199
ST150T LED22S-23-/840 PSU WH		2200	4000	IP20	79070799
ST150T LED22S-36-/830 PSU BK		2200	3000	IP20	79071499
ST150T LED22S-36-/830 PSU WH		2200	3000	IP20	79073899
ST150T LED22S-36-/840 PSU BK		2200	4000	IP20	79072199
ST150T LED22S-36-/840 PSU WH		2200	4000	IP20	79074599

CoreLine bollard



L70 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BCP155 LED100/NW PSU 220–240V S 7043	12	1000	4000	IP65	38378700
BCP155 LED100/WW PSU 220–240V S 7043		1000	3000	IP65	38377000
BCP155 LED100/NW PSU 220–240V A 7043	13	1000	4000	IP65	38376300
BCP155 LED100/WW PSU 220–240V A 7043		1000	3000	IP65	38375600

CoreLine bollard – Accessories



1 PACK

Product Type	EOC code
ZCP150 ANB L500	38379400

CoreLine highbay



L80 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BY120P G4 LED100S/840 PSU NB	69	10000	4000	IP65	33571100
BY120P G4 LED100S/840 PSU WB		10000	4000	IP65	33570400
BY120P G4 LED100S/865 PSU NB		10000	6500	IP65	33567400
BY120P G4 LED100S/865 PSU WB		10000	6500	IP65	33566700
BY120P G4 LED100S/840 PSD NB	73	10000	4000	IP65	33702900
BY120P G4 LED100S/840 PSD WB		10000	4000	IP65	33703600
BY120P G4 LED100S/865 PSD NB		10000	6500	IP65	33704300
BY120P G4 LED100S/865 PSD WB		10000	6500	IP65	33705000
BY121P G4 LED200S/840 PSU NB	138	20000	4000	IP65	33569800
BY121P G4 LED200S/840 PSU WB		20000	4000	IP65	33568100
BY121P G4 LED200S/865 PSU NB		20000	6500	IP65	33565000
BY121P G4 LED200S/865 PSU WB		20000	6500	IP65	33564300
BY121P G4 LED200S/840 PSD NB	146	20000	4000	IP65	33698500
BY121P G4 LED200S/840 PSD WB		20000	4000	IP65	33699200
BY121P G4 LED200S/865 PSD NB		20000	6500	IP65	33700500
BY121P G4 LED200S/865 PSD WB		20000	6500	IP65	33701200
BY122P G4 LED250S/840 PSU NB	172	25000	4000	IP65	33664000
BY122P G4 LED250S/840 PSU WB		25000	4000	IP65	33665700
BY122P G4 LED250S/865 PSU NB		25000	6500	IP65	33666400
BY122P G4 LED250S/865 PSU WB		25000	6500	IP65	33667100
BY122P G4 LED250S/840 PSD NB	183	25000	4000	IP65	33879800
BY122P G4 LED250S/840 PSD WB		25000	4000	IP65	33880400
BY122P G4 LED250S/865 PSD NB		25000	6500	IP65	33881100
BY122P G4 LED250S/865 PSD WB		25000	6500	IP65	33882800

CoreLine batten



L70 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BN126C LED20S/830 PSU TW1 L600	17	2000	3000	IP20	911401897080
BN126C LED22S/840 PSU TW1 L600		2200	4000	IP20	911401896980
BN126C LED23S/830 PSU TW1 L1200	18	2300	3000	IP20	911401897280
BN126C LED25S/840 PSU TW1 L1200		2500	4000	IP20	911401897180
BN126C LED38S/830 PSU TW1 L1200	31	3800	3000	IP20	911401897480
BN126C LED41S/840 PSU TW1 L1200		4100	4000	IP20	911401897380
BN126C LED60S/830 PSU TW1 L1200	49	6000	3000	IP20	911401897680
BN126C LED64S/840 PSU TW1 L1200		6400	4000	IP20	911401897580
BN126C LED32S/830 PSU TW1 L1500	25.5	3200	3000	IP20	911401897880
BN126C LED35S/840 PSU TW1 L1500		3500	4000	IP20	911401897780
BN126C LED48S/830 PSU TW1 L1500	40	4800	3000	IP20	911401898080
BN126C LED52S/840 PSU TW1 L1500		5200	4000	IP20	911401897980
BN126C LED74S/830 PSU TW1 L1500	59	7400	3000	IP20	911401898280
BN126C LED80S/840 PSU TW1 L1500		8000	4000	IP20	911401898180
BN126C LED60S/830 PSU TW1 L1800	49	6000	3000	IP20	911401898480
BN126C LED64S/840 PSU TW1 L1800		6400	4000	IP20	911401898380
BN126C LED94S/830 PSU TW1 L1800	75	9400	3000	IP20	911401898680
BN126C LED100S/840 PSU TW1 L1800		10000	4000	IP20	911401898580

CoreLine trunking



L80 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
LL121X LED45S/840 1x PSD DA20 7 WH	32	4500	4000	IP20	88203900
LL121X LED45S/840 1x PSD WB 7 WH		4500	4000	IP20	88140700
LL121X LED45S/840 1x PSU DA20 5 WH	54	4500	4000	IP20	88183400
LL121X LED75S/840 1x PSD O 7 WH		7500	4000	IP20	38102100
LL121X LED76S/830 1x PSU VWB 7 WH	54	7600	3000	IP20	38169400
LL121X LED80S/840 1x PSD A 7 WH		8000	4000	IP20	38155700
LL121X LED80S/840 1x PSD DA20 7 WH	54	8000	4000	IP20	38137300
LL121X LED80S/840 1x PSD MB 7 WH		8000	4000	IP20	38124300
LL121X LED80S/840 1x PSD NB 7 WH	54	8000	4000	IP20	38120500
LL121X LED80S/840 1x PSD VWB 7 WH		8000	4000	IP20	38144100
LL121X LED80S/840 1x PSD WB 7 WH	54	8000	4000	IP20	38092500
LL121X LED80S/840 1x PSU MB 7 WH		8000	4000	IP20	38145800
LL121X LED80S/840 1x PSU NB 7 WH	54	8000	4000	IP20	38171700
LL121X LED80S/840 1x PSU VWB 7 WH		8000	4000	IP20	38176200
LL121X LED80S/840 1x PSU WB 7 WH	54	8000	4000	IP20	38157100
LL121X LED80S/840 PSU NB SMB WH KIT		8000	4000	IP20	38079600
LL121X LED80S/840 PSU NB TW3 SMB WH KIT	54	8000	4000	IP20	38083300
LL121X LED80S/840 PSU WB SMB WH KIT		8000	4000	IP20	38078900
LL121X LED80S/865 1x PSD WB 7 WH	54	8000	6500	IP20	38160100
LL122X LED80S/840 1x PSD VWB 7 WH		8000	4000	IP20	38146500
LL121X LED76S/830 1x PSD A 7 WH	54	7600	3000	IP20	38173100
LL121X LED76S/830 1x PSD WB 7 WH		7600	3000	IP20	38118200

CoreLine trunking – Continued



L80 at
50000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
LL121X LED76S/830 1x PSU VWB 7 EL3 WH	56	7600	3000	IP20	38162500
LL121X LED80S/840 1x PSU DA20 7 EL3 WH		8000	4000	IP20	38165600
LL121X LED80S/840 1x PSU MB 7 EL3 WH		8000	4000	IP20	38188500
LL121X LED80S/840 1x PSU NB 7 EL3 WH		8000	4000	IP20	38167000
LL121X LED80S/840 1x PSU WB 7 EL3 WH		8000	4000	IP20	38123600
LL120X LED90S/840 2x PSD DA20 7 VLC WH	64	9000	4000	IP20	88204600
LL120X LED90S/840 2x PSD NB 7 VLC WH		9000	4000	IP20	88190200
LL120X LED90S/840 2x PSD WB 7 VLC WH		9000	4000	IP20	88141400
LL120X LED160S/840 PSU NB SMB WH KIT	108	16000	4000	IP20	38082600
LL120X LED160S/840 PSU WB SMB WH KIT		16000	4000	IP20	38081900
LL120X LED160S/865 1x PSD MB 7 WH		16000	6500	IP20	38189200
LL120X LED160S/840 2x PSD WB 7 VLC WH		16000	4000	IP20	38087100
LL120X LED160S/840 2x PSD WB 7X2.5 VLC W		16000	4000	IP20	38086400
LL120X LED160S/840 2x PSU WB 5 WH		16000	4000	IP20	38088800
LL120X LED160S/840 2x PSU MB 5 WH		16000	4000	IP20	38091800
LL120X LED160S/840 2x PSU DA20 5 WH		16000	4000	IP20	38093200
LL120X LED160S/840 1x PSD WB 7 WH		16000	4000	IP20	38095600
LL120X LED160S/840 2x PSU NB 5 WH		16000	4000	IP20	38096300
LL120X LED160S/840 1x PSD WB 7X2.5 WH		16000	4000	IP20	38097000
LL120X LED160S/840 2x PSD MB 7 VLC WH		16000	4000	IP20	38098700
LL120X LED160S/840 2x PSD WB 9 VLC WH		16000	4000	IP20	38099400
LL120X LED152S/830 2x PSU WB 5 WH		15200	3000	IP20	38104500
LL120X LED160S/840 2x PSD VWB 7 VLC WH		16000	4000	IP20	38105200
LL120X LED160S/840 1x PSD MB 7 WH		16000	4000	IP20	38108300
LL120X LED160S/840 1x PSD NB 7 WH		16000	4000	IP20	38107600
LL120X LED152S/830 2x PSU VWB 5 WH		15200	3000	IP20	38106900
LL120X LED152S/830 2x PSU DA20 5 WH		15200	3000	IP20	38109000
LL120X LED160S/840 2x PSU WB 7 WH		16000	4000	IP20	38112000
LL120X LED160S/840 2x PSD NB 9 VLC WH	108	16000	4000	IP20	38110600
LL120X LED160S/840 2x PSD NB 7 VLC WH		16000	4000	IP20	38113700
LL120X LED160S/840 2x PSU VWB 5 WH		16000	4000	IP20	38117500
LL120X LED152S/830 2x PSD WB 7 VLC WH		15200	3000	IP20	38115100
LL120X LED160S/840 2x PSD A 7X2.5 VLC WH		16000	4000	IP20	38119900
LL120X LED160S/840 2x PSU A 5 WH		16000	4000	IP20	38129800
LL120X LED160S/840 2x PSD MB 9 VLC WH		16000	4000	IP20	38134200
LL120X LED160S/840 2x PSD DA20 7 VLC WH		16000	4000	IP20	38136600
LL120X LED160S/840 2x PSD A 7 VLC WH		16000	4000	IP20	38138000
LL120X LED150S/865 2x PSU O 5 WH		15000	6500	IP20	38142700
LL120X LED152S/830 2x PSU A 5 WH		15200	3000	IP20	38140300
LL120X LED152S/830 2x PSD DA20 7 VLC WH		15200	3000	IP20	38151900
LL120X LED160S/840 2x PSU MB 7 WH	126	16000	4000	IP20	38161800
LL120X LED160S/840 2x PSU NB 7 WH		16000	4000	IP20	38168700
LL120X LED160S/840 2x PSU VWB 7 WH		16000	4000	IP20	38175500
LL120X LED160S/840 2x PSU VWB 5X2.5 WH		16000	4000	IP20	38179300
LL120X LED160S/840 2x PSD VWB 7X2.5 VLC		16000	4000	IP20	38184700
LL120X LED150S/840 2x PSU PCO 5 WH		15000	4000	IP20	98887900
LL120X LED150S/840 2x PSD PCO 7 VLC WH		15000	4000	IP20	98766700
LL120X LED150S/840 1x PSD PCO 7 WH		15000	4000	IP20	98765000

CoreLine trunking – Accessories



1 PACK

Product Type	IP rating	EOC code
LL120Z CB WH (5PCS)	-	88161299
LL120Z MB-SW 2xEP CU7 WH	-	88146900
LL120Z SMB WH (5PCS)	-	88156899
LL121X 7 WH BC	IP20	88144500

CoreLine tempo – small



L80 at
75000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BVP110 LED42/NW A	38	4200	4000	IP65	30635300
BVP110 LED42/NW S		4200	4000	IP65	30636000

CoreLine tempo – medium



L80 at
75000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BVP125 LED80-4S/740 OFA52	63	8000	4000	IP66	45588000
BVP125 LED80-4S/740 S		8000	4000	IP66	45590300
BVP125 LED120-4S/740 OFA52	95	12000	4000	IP66	45587300
BVP125 LED120-4S/740 S		12000	4000	IP66	45589700

CoreLine tempo – large



L80 at
75000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BVP130 LED160-4S/740 A	120	16000	4000	IP66	09641000
BVP130 LED160-4S/740 S		16000	4000	IP66	09644100
BVP130 LED210-4S/740 A	162	21000	4000	IP66	09640300
BVP130 LED210-4S/740 S		21000	4000	IP66	09643400
BVP130 LED260-4S/740 A	217	26000	4000	IP66	09639700
BVP130 LED260-4S/740 S		26000	4000	IP66	09642700

CoreLine tempo - X-large



L80 at
75000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BVP140 LED360-4S 30K6/740 PSU OFA52	225	30600	4000	IP66	87280900
BVP140 LED360-4S 31K3/740 PSU S		31320	4000	IP66	87284700
BVP140 LED360-4S 30K6/740 PSD OFA52 D9		30600	4000	IP66	87288500
BVP140 LED360-4S 31K3/740 PSD S D9		31320	4000	IP66	87292200
BVP140 LED420-4S 35K3/740 PSU OFA52	250	35280	4000	IP66	87279300
BVP140 LED420-4S 36K1/740 PSD S D9		36120	4000	IP66	87291500
BVP140 LED420-4S 36K1/740 PSU S		36120	4000	IP66	87283000
BVP140 LED420-4S 35K3/740 PSD OFA52 D9		35280	4000	IP66	87287800
BVP140 LED480-4S 40K3/740 PSU OFA52	295	40320	4000	IP66	87278600
BVP140 LED480-4S 40K3/740 PSD OFA52 D9		40320	4000	IP66	87286100
BVP140 LED480-4S 41K3/740 PSU S		41280	4000	IP66	87282300
BVP140 LED480-4S 41K3/740 PSD S D9		41280	4000	IP66	87290800

CoreLine malaga



L70 at
70000h



1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BRP101 LED37/740 I DM	29.6	3054	4000	IP65	99815100
BRP102 LED55/740 I DM	39	4600	4000	IP65	99817500
BRP102 LED55/740 II DM		4600	4000	IP65	99818200
BRP102 LED75/740 I DM	56.5	6133	4000	IP65	99819900
BRP102 LED75/740 II DM		6133	4000	IP65	99820500
BRP102 LED110/740 I DM	83	9006	4000	IP65	99821200
BRP102 LED110/740 II DM		9006	4000	IP65	99822900

CoreLine malaga – Accessories



1 PACK

Product Type	EOC code
ZRP220 AD60/60 A5	62134100

