


# PHILIPS


Horticulture LED




## Philips GreenPower LED gridlighting

### Gridlighting Photosynthetic Flux Density (4' x 4' Space)


**4 x 4 Grow Tent White (60% reflection)**  
Hang height: 4 feet / 1.2192 meter




**4 x 4 Grow Tent White (60% reflection)**  
Hang height: 3 feet / 0.9144 meter




**4 x 4 Grow Tent White (60% reflection)**  
Hang height: 2 feet / 0.6096 meter



**4 x 4 Grow Tent White (60% reflection)**  
Hang height: 1 foot / 0.3048 meter




**4 x 4 Grow Tent White (60% reflection)**  
Hang height: 6 in / 0.1524 meter




# Gridlighting Photosynthetic Flux Density (4' x 8' Space)


4 x 8 rack (0% reflection) – Hang height: 4 feet / 1.2192 meter




4 x 8 rack – Hang height: 3 feet / 0.9144 meter




4 x 8 rack – Hang height: 2 feet / 0.6096 meter



4 x 8 rack – Hang height: 1 foot / 0.3048 meter



4 x 8 rack – Hang height: 6 in / 0.1524 meter



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Document order number: LED-PPFD-GL-2023  
Data subject to change.