

LUMIWARE



LED

LIGHT ON ENERGY, LOW ON PRICE.

When you need a lighting solution that high on energy savings and low on maintenance, look no further than the LUMIWARE range of lamps and tubes.



GREAT QUALITY LIGHTING DOESN'T HAVE TO COME WITH A PREMIUM PRICE TAG. HERE'S WHY.

Today's LED technology is so advanced, it's guaranteed to offer excellent performance and efficiency, which is why we've used it throughout our LUMIWARE range. It means your customers can enjoy great quality lighting that's light on energy - and low on price.

Designed for performance, the LUMIWARE range promises high light quality with a reliable lifetime of up to 25,000 hours. From LED tubes to dimmable spots, bulbs, candles and lustres, the range offers a great choice of designs, color temperatures and beam angles. Add to that up to 85% in energy savings, and you can exceed your customers' expectations, without going over budget.

4 BULBS
6 CANDLES
& LUSTRES
8 SPOTS
10 TUBES

"I know good, solid quality when I see it. LUMIWARE is a brand that I can really buy into for tenders that need high volumes of lighting for an affordable price."
Mick Taylor, Installer



A CLASSIC DESIGN FOR INSTANT ENERGY SAVINGS.

Retrofit, LED filament bulbs light relaxing spaces that can be dimmed to create a cozier ambience that saves even more on energy.



40W E27 827 A60 CL D 1CT/6
40W ▶ **4.5W** 470lm
 2700K Dimmable
 220-240V . 60x105mm . CRI80



40W E27 827 A60 FR D 1CT/6
40W ▶ **4.5W** 470lm
 2700K Dimmable
 220-240V . 60x105mm . CRI80



60W E27 827 A60 CL D 1CT/6
60W ▶ **7W** 806lm
 2700K Dimmable
 220-240V . 60x105mm . CRI80



60W E27 827 A60 FR D 1CT/6
60W ▶ **7W** 806lm
 2700K Dimmable
 220-240V . 60x105mm . CRI80



75W E27 827 A60 CL D 1CT/6
75W ▶ **9W** 1055lm
 2700K Dimmable
 220-240V . 60x105mm . CRI80



75W E27 827 A60 FR D 1CT/6
75W ▶ **9W** 1055lm
 2700K Dimmable
 220-240V . 60x105mm . CRI80

4 BULBS



15,000h



E/F
EEL label



80
CRI



20,000x & 15,000x



220-240V



dimmable



6 pack

| Product type | Replaced wattage | Lamp wattage claim | Energy consumption | Lumen | Input current | Frequency | Dimension W x H | Energy class | 12NC | EOC/6NC |
|----------------------------|------------------|--------------------|--------------------|-------|---------------|-----------|-----------------|--------------|--------------|-----------------|
| LUMIWARE LED | W | W | | lm | mA | Hz | mm | | | |
| 40W E27 827 A60 CL D 1CT/6 | 40 | 4.5 | 5 | 470 | 26 | 50/60 | 60x105 | F | 929001993462 | 872790096636700 |
| 40W E27 827 A60 FR D 1CT/6 | 40 | 4.5 | 5 | 470 | 26 | 50/60 | 60x105 | F | 929001993562 | 872790096638100 |
| 60W E27 827 A60 CL D 1CT/6 | 60 | 7.2 | 8 | 806 | 45 | 50/60 | 60x105 | E | 929003034662 | 871016355023700 |
| 60W E27 827 A60 FR D 1CT/6 | 60 | 7.2 | 8 | 806 | 45 | 50/60 | 60x105 | E | 929003034762 | 871016355021300 |
| 75W E27 827 A60 CL D 1CT/6 | 75 | 9 | 9 | 1055 | 53 | 50/60 | 60x105 | E | 929003034862 | 871016355019000 |
| 75W E27 827 A60 FR D 1CT/6 | 75 | 9 | 9 | 1055 | 53 | 50/60 | 60x105 | E | 929003034962 | 871016355017600 |



SAVE ENERGY WITHOUT COMPROMISING STYLE.

LED filament candles and lustres provide the familiar shape and warm light that customers love, for decorative fixtures that save energy without compromising style.



25W E14 827 B35 FR D 1CT10
 25W ▶ **2.8W** 250lm
 2700K Dimmable
 220-240V . 35x97mm . CRI80



40W E14 827 B35 FR D 1CT10
 40W ▶ **4.5W** 470lm
 2700K Dimmable
 220-240V . 35x97mm . CRI80



25W E14 827 P45 FR D 1CT10
 25W ▶ **2.8W** 250lm
 2700K Dimmable
 220-240V . 45x81mm . CRI80



25W E27 827 P45 FR D 1CT10
 25W ▶ **2.8W** 250lm
 2700K Dimmable
 220-240V . 45x79mm . CRI80



40W E14 827 P45 FR D 1CT10
 40W ▶ **4.5W** 470lm
 2700K Dimmable
 220-240V . 45x81mm . CRI80



40W E27 827 P45 FR D 1CT10
 40W ▶ **4.5W** 470lm
 2700K Dimmable
 220-240V . 45x79mm . CRI80

6 CANDLES & LUSTRES



15,000h



EEI label



80 CRI



20,000x & 15,000x



220-240V



dimmmable



10 pack

| Product type | Replaced wattage | Lamp wattage claim | Energy consumption | Lumen | Input current | Frequency | Dimension W x H | Energy class | 12NC | EOC/6NC |
|---------------------------|------------------|--------------------|--------------------|-------|---------------|-----------|-----------------|--------------|--------------|-----------------|
| LUMIWARE LED | W | W | | lm | mA | Hz | mm | | | |
| 25W E14 WW B35 FR D 1CT10 | 25 | 2.8 | 3 | 250 | 15 | 50/60 | 35x97 | F | 929003035062 | 871016355015200 |
| 40W E14 WW B35 FR D 1CT10 | 40 | 4.5 | 5 | 470 | 26 | 50/60 | 35x97 | F | 929001994162 | 872790096650300 |
| 25W E14 WW P45 FR D 1CT10 | 25 | 2.8 | 3 | 250 | 15 | 50/60 | 45x81 | F | 929003035262 | 871016355011400 |
| 25W E27 WW P45 FR D 1CT10 | 25 | 2.8 | 3 | 250 | 15 | 50/60 | 45x79 | F | 929003035362 | 871016355009100 |
| 40W E14 WW P45 FR D 1CT10 | 40 | 4.5 | 5 | 470 | 26 | 50/60 | 45x81 | F | 929001994462 | 872790096656500 |
| 40W E27 WW P45 FR D 1CT10 | 40 | 4.5 | 5 | 470 | 26 | 50/60 | 45x79 | F | 929001994562 | 872790096658900 |



PUT THE ACCENT ON VALUE.

LED spots are a stylish way to create energy-efficient accents and highlights in a wide range of applications.



35W GU10 35W 827 36D D 1CT/10
35W ▶ **3.6W** 230lm
 2700K Dimmable
 220-240V . 50x54mm . CRI80



50W GU10 50W 827 36D D 1CT/10
50W ▶ **5W** 350lm
 2700K Dimmable
 220-240V . 50x54mm . CRI80



35W GU10 35W 830 36D D 1CT/10
35W ▶ **3.6W** 240lm
 3000K Dimmable
 220-240V . 50x54mm . CRI80



50W GU10 50W 830 36D D 1CT/10
50W ▶ **5W** 345lm
 3000K Dimmable
 220-240V . 50x54mm . CRI80

8 SPOTS



| Product type | Lamp type | Replaced wattage | Lamp wattage claim | Energy consumption | Lumen | MBCP | Input current | Frequency | Dimension W x H | Energy class | 12NC | EOC/6NC |
|---------------------------|-----------|------------------|--------------------|--------------------|-------|------|---------------|-----------|-----------------|--------------|--------------|-----------------|
| LUMIWARE LED | | W | W | | lm | cd | mA | Hz | mm | | | |
| GU10 35W 827 36D D 1CT/10 | PAR16 | 35 | 3.6 | 4 | 230 | 500 | 19 | 50/60 | 50x54 | G | 929001994662 | 872790096632900 |
| GU10 50W 827 36D D 1CT/10 | PAR16 | 50 | 5 | 5 | 345 | 650 | 25 | 50/60 | 50x54 | G | 929001994762 | 872790096634300 |
| GU10 50W 830 36D D 1CT/10 | PAR16 | 50 | 5 | 5 | 345 | 650 | 25 | 50/60 | 50x54 | G | 929002348462 | 871016355003900 |
| GU10 35W 830 36D D 1CT/10 | PAR16 | 35 | 3.6 | 4 | 240 | 540 | 19 | 50/60 | 50x54 | G | 929002479362 | 871016355001500 |



A BRIGHT WAY TO MAKE SAVINGS.

Our LEDtubes come in a range of lengths for brighter, safer and more efficient lighting in offices, warehouses and indoor parking lots.



36W 1200mm UO 16W 840 T8
36W ▶ **15,5W** 2500lm
 4000K Non dimmable
 220-240V . 28x1213.6mm . CRI80




58W 1500mm UO 24W 840 T8
58W ▶ **23W** 3700lm
 4000K Non dimmable
 220-240V . 28x1514.2mm . CRI80

10 TUBES



| Product type | Lamp type | Replaced wattage | Lamp wattage claim | Energy consumption | Lumen | Input current | Frequency | Dimension W x H | Energy class | 12NC | EOC/6NC |
|------------------------|---------------|------------------|--------------------|--------------------|-------|---------------|-----------|-----------------|--------------|--------------|-----------------|
| | | W | W | | lm | mA | Hz | mm | | | |
| 1200mm UO 15.5W 840 T8 | Tube EM/Mains | 36 | 15.5 | 16 | 2500 | 67-73 | 50/60 | 28x1213 | C | 929002997762 | 871016355029900 |
| 1500mm UO 23W 840 T8 | Tube EM/Mains | 58 | 23 | 23 | 3700 | 99-108 | 50/60 | 28x1514 | C | 929002998062 | 871016355031200 |



LUMIWARE