

PHILIPS

LED strips

Real pros choose
**slim strips for
big performance**

The new Philips LED strips:
more performance and flexibility
for simply great lighting

New and
ready to
shine

**REAL
PROs**
**REAL
QUALITY**



The new benchmark for LED strips

The right LED strips can transform any location giving it a modern look and sophisticated flair. The new LED strips from Philips offer you a wide choice of high-quality lighting that fits diverse applications and budgets. So, whether it's the CorePro LEDstrip for great value-for-money performance or the MASTER LEDstrip with superior light quality and even more choice, you have the quality, reliability and installation ease you expect from Philips.


A wide portfolio of matching electronic components and accessories gives you the flexibility to meet every customer demand and application requirement.

System components



LED strips

- Color temperatures from 2700K to 6500K
- Luminous flux from 270 to 2,500 lm/m
- Connected capability – use Interact Ready kit* to integrate



Accessories

- Different connectors available (corner, tape-to-tape, tape to-wire)
- Mounting clips



Constant voltage LED transformers

- Dimmable DALI
- ON/OFF
- Stable output voltage
- Wide ambient temperature range
- Protection against overpower

Performance runs in the family

LED strips should not only fit their surroundings, but budgets and plans as well. That's why Philips LED strips come in two families: MASTER and CorePro. Each offers exceptional lighting with energy efficiency and installation ease, while giving every location its own, unique touch.

MASTER LEDstrip

Value and features:



Need exceptional lighting that offers diverse brightness and color options and more sustainable and smart performance? Then make the MASTER family part of your perfect solution.

- Superior light quality (CRI 90, SDCM ≤ 3)
- Five different lumen outputs (500–2,500 lm/m at 4000K) and four color temperatures (2700K–6500K) to fit a large variety of different applications
- Connected capability – use Interact Ready kit to include in smart lighting system
- Easy installation
- Hassle-free planning thanks to flexible 5 m length and cut size of only 5 cm
- Extremely durable: 60,000 hours lifetime and 5 years warranty*
- IP20 rating

CorePro LEDstrip

Value and features:



Looking for reliable, value-for-money LED strips that are slim, bright and ready to meet everyday lighting demands while saving more? Welcome to the CorePro family!

- Very good quality of light (CRI 80, SDCM ≤ 5)
- Four different lumen outputs (300–1,600 lm/m at 4000K) and four color temperatures (2700K–6500K) for greater variety in different applications
- Easy installation
- Hassle-free planning thanks to flexible 5 m length and cut size of 10 cm
- Durable: 35,000 hours lifetime and 3 years warranty*
- IP20 rating



Outstanding in every application

Whether you're using them in retail, hospitality or office spaces, Philips LED strips let every location shine in the light it deserves. Different color temperatures and up to five luminous fluxes give you the tools you need to create the right atmosphere for every demand – from energizing office to atmospheric restaurant lighting, luxurious retail experiences to relaxing hotel stays. Just right for all applications where people should feel comfortable and welcome.

Retail



Hospitality



Office



General lighting

Enjoy bright, welcoming light that adds to any atmosphere while providing the energy efficiency that is necessary for locations where lighting is on a great part of the day. Both Philips CorePro and MASTER LEDstrips offer luminous fluxes of 1,000 to 2,000 lm/m that are ideal for general lighting.

Ambient lighting

Create the right accent lighting with subdued lighting nuances: Philips LED strips come in luminous fluxes from 300 to 700 lm/m and four white light colors. A dimmable transformer lets you create even more atmospheric notes.

Cove lighting

Get the cozy, indirect lighting that sets the right accents in all areas where an intimate and private atmosphere is desired. Luminous fluxes from 500 to 1,000 lm/m are available in both ranges.



Easy installation from start to fantastic finish





Both Philips MASTER and CorePro LEDstrips offer easy and flexible out-of-the-box installation for a long lifetime of energy savings, reliability and robust durability.

- Easy handling and wiring
- Pre-wired
- Self-adhesive tape for simple mounting on most smooth surfaces
- Easy to select correct LED transformer and dimmer with one simple rule: LED strip load must not exceed 90% of maximum transformer rated power

See separate installation instructions for more detailed information



Dimensions



Attention: when using connectors please take the maximum tape length into account. Never exceed 2A or 48W for a series connection. Detailed information can be found in the installation manual.

Ordering information

MASTER LEDstrip

60,000h 10 Pack

Product type	LED/m	Lumen output	Power/1m	Power/2m	Power/3m	Power/4m	Power/5m	m/roll	EOC code
		lm/m	W	W	W	W	W		
MAS LEDstrip 4.3W927 475LM/M 5M	140	475	4.3	8.5	13	17	19	5	34432700
MAS LEDstrip 4.3W930 475LM/M 5M								5	34434100
MAS LEDstrip 4.3W940 500LM/M 5M		500						5	34436500
MAS LEDstrip 4.3W965 500LM/M 5M								5	34438900
MAS LEDstrip 8.3W927 920LM/M 5M		920	8.3	16	23	29.5	37	5	34440200
MAS LEDstrip 8.3W930 920LM/M 5M								5	34442600
MAS LEDstrip 8.3W940 1000LM/M 5M		1,000						5	34444000
MAS LEDstrip 8.3W965 950LM/M 5M		950						5	34446400
MAS LEDstrip 12.5W927 1380LM/M 5M		1,380	12.5	24	35	42	52	5	34448800
MAS LEDstrip 12.5W930 1380LM/M 5M								5	34450100
MAS LEDstrip 12.5W940 1500LM/M 5M		1,500						5	34452500
MAS LEDstrip 12.5W965 1450LM/M 5M		1,450						5	34454900
MAS LEDstrip 16.6W927 1830LM/M 5M		1,830	16.6	31	43	52	67	5	34456300
MAS LEDstrip 16.6W930 1830LM/M 5M								5	34458700
MAS LEDstrip 16.6W940 2000LM/M 5M		2,000						5	34460000
MAS LEDstrip 16.6W965 2000LM/M 5M								5	34462400
MAS LEDstrip 21.3W927 2400LM/M 5M		2,400	21.3	42	60	74	81	5	34464800
MAS LEDstrip 21.3W930 2400LM/M 5M								5	34466200
MAS LEDstrip 21.3W940 2500LM/M 5M		2,500						5	34468600
MAS LEDstrip 21.3W965 2450LM/M 5M		2,450						5	34470900

CorePro LEDstrip

35,000h 10 Pack

Product type	LED/m	Lumen output	Power/1m	Power/2m	Power/3m	Power/4m	Power/5m	m/roll	EOC code
		lm/m	W	W	W	W	W		
CorePro LEDstrip 2.3W827 270LM/M 5M	70	270	2.3	4.5	6.6	8.8	10.5	5	34400600
CorePro LEDstrip 2.3W830 270LM/M 5M								5	34402000
CorePro LEDstrip 2.3W840 300LM/M 5M		300						5	34404400
CorePro LEDstrip 2.3W865 300LM/M 5M								5	34406800
CorePro LEDstrip 6W827 750LM/M 5M		750	6	11.5	17	22	27	5	34408200
CorePro LEDstrip 6W830 750LM/M 5M								5	34410500
CorePro LEDstrip 6W840 800LM/M 5M		800						5	34412900
CorePro LEDstrip 6W865 780LM/M 5M		780						5	34414300
CorePro LEDstrip 9.2W827 1080LM/M 5M		1,080	9.2	18	25	33	39	5	34416700
CorePro LEDstrip 9.2W830 1080LM/M 5M								5	34418100
CorePro LEDstrip 9.2W840 1200LM/M 5M		1,200						5	34420400
CorePro LEDstrip 9.2W865 1180LM/M 5M		1,180						5	34422800
CorePro LEDstrip 12.3W827 1450LM/M 5M		1,450	12.3	24	35	44	52	5	34424200
CorePro LEDstrip 12.3W830 1450LM/M 5M								5	34426600
CorePro LEDstrip 12.3W840 1600LM/M 5M		1,600						5	34428000
CorePro LEDstrip 12.3W865 1580LM/M 5M		1,580						5	34430300

Accessories

50 Pack



Product type	EOC code
1 LS mounting clips IP20 50pcs EU	35497500
2 LS corner connector IP20 50pcs EU6500	35499900
3 LS tape-to-tape connector IP20 50pcs EU	35501900
4 LS tape-to-wire connector IP20 50pcs EU	35503300

Ordering information

Transformers



Product type	Pack	EOC code
1 Transformer for MASTER LEDstrip		
LED Transformer 60W 24VDC TD 220~240V	20	93150500
LED Transformer 100W 24VDC TD 220~240V	10	93152900
LED Transformer 150W 24VDC TD 220~240V	10	93154300
LED Transformer 20W 24VDC 120~277V	20	77531500
LED Transformer 40W 24VDC 120~277V	24	77532200
LED Transformer 60W 24VDC 220-240V	20	72909000
LED Transformer 120W 24VDC 220-240V	20	10202000
LED Transformer 150W 24VDC 220~240V	10	77534600
2 Transformer for CorePro LEDstrip		
CertaDrive LED Transformer 30W 24VDC	80	48803200
CertaDrive LED Transformer 60W 24VDC	60	48805600
CertaDrive LED Transformer 120W 24VDC	36	48807000
CertaDrive LED Transformer 180W 24VDC	36	48809400
CertaDrive LED Transformer 250W 24VDC	36	91779000



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

www.philips.com/ledstrip