



The 2023 bans on fluorescent are in effect!



The time is now — make the big switch!

Be prepared for the bans — with Philips LED solutions

- Highest standard LED technology offers many benefits:
 - Drastically reduced energy costs and a longer lifetime
 - Similar, or even enhanced, lighting results compared to conventional products – with lower maintenance
 - LED lamps and luminaires can be integrated into smart lighting systems
- A wide portfolio of future-proof, easy to install and outstanding quality Philips LED lamps offer a compatible replacement option for any project to ensure a smooth transition for you and your customers.

Products phasing out ¹	(RoHS) 24.02.2023	(RoHS) 24.08.2023	(SLR) 01.09.2023	Philips LED alternatives
Fluorescent lamps portfolio				
 Compact fluorescent lamps non-integrated PL-C, PL-S, PL-T, PL-L, PL-R, PL-Q				 
 Compact fluorescent lamps non-integrated – long life PL-C, PL-T, PL-L Xtra				 
 Linear fluorescent lamps T8				 
 Linear fluorescent lamps T5				 
 Linear fluorescent lamps – long life T8 Xtreme, T5 Xtra				 
 Halogen capsules G9 / G4 / GY6.35				 

¹ Products already placed on the market may still be sold after these dates, but they may no longer be placed on the market

For the full conversion list visit philips.com/ledconversion

① Re-lamping with Philips LED lamps

- ✓ Current luminaires need to be kept
- ✓ Payback period needs to be less than 1 year
- ✓ Aiming for solution with low installation effort
- ✓ Larger invest irrational (e.g. rental property or big invest planned ahead)



T5 fluorescent lamps



MASTER LEDtube Mains T5



MASTER LEDtube InstantFit HF T5

Phase out	EOC	LED recommendation	EOC	LED recommendation	EOC
MASTER TL5		MAS LEDtube		MAS LEDtube	
HE 14W/830	63938705	600mm HE 8W 830 T5	33425000	HF 600mm HE 8W 830 T5	74323200
HE 14W/840	63940005	600mm HE 8W 840 T5	33427400	HF 600mm HE 8W 840 T5	74325600
HE 28W/830	63946205	1200mm HE 16.5W 830 T5	33431100	HF 1200mm HE 16.5W 830 T5	74329400
HE 28W/840	63948605	1200mm HE 16.5W 840 T5	33433500	HF 1200mm HE 16.5W 840 T5	74331700
HE 35W/830	63950905	1500mm HE 20W 830 T5	33437300	HF 1500mm HE 20W 830 T5	74335500
HE 35W/840	63952305	1500mm HE 20W 840 T5	33439700	HF 1500mm HE 20W 840 T5	74337900
HO 49W/830	63954705	1500mm HO 26W 830 T5	81929600	HF 1500mm HO 26W 830 T5	74957600
HO 49W/840	63956105	1500mm HO 26W 840 T5	81931900	HF 1500mm HO 26W 840 T5	74959000
HO 54W/830	64316205	1200mm HO 26W 830 T5	81921000	HF 1200mm HO 26W 830 T5	74951400
HO 54W/840	64318605	1200mm HO 26W 840 T5	81923400	HF 1200mm HO 26W 840 T5	74953800
HO 80W/840	71045105	1500mm UO 36W 840 T5	29052500	HF 1500mm UO 36W 840 T5	41907000



T8 fluorescent lamps



CorePro LEDtube EM/Mains T8



MASTER Value LEDtube EM/Mains T8 Ultra Output

Phase out	EOC	LED recommendation	EOC	LED recommendation	EOC
MASTER TL-D		CorePro LEDtube		MAS LEDtube VLE	
Super 80 18W/840	63171840	600mm 8W 840	45977900	1200mm UO 15.5W 830 T8	31680500
Super 80 36W/830	63195440	1200mm 15.5W 830	48640900	1200mm UO 15.5W 840 T8	31682900
Super 80 36W/840	63201240	1200mm 15.5W 840	44807000	1200mm UO 15.5W 865 T8	31684300
Super 80 36W/865	63207440	1200mm 15.5W 865	44809400	1500mm UO 23W 830 T8	31686700
Super 80 58W/830	63213540	1500mm 20W 830	48642300	1500mm UO 23W 840 T8	31688100
Super 80 58W/840	63219740	1500mm 20W 840	45981600	1500mm UO 23W 865 T8	31690400
Super 80 58W/865	63225840	1500mm 20W 865	45983000		



T8 fluorescent lamps



MASTER LEDtube EM/Mains T8 Ultra Output



MASTER LEDtube InstantFit HF T8 Ultra Output

Phase out	EOC	LED recommendation	EOC	LED recommendation	EOC
MASTER TL-D		MAS LEDtube		MAS LEDtube HF	
Super 80 36W/830	63195440	1200mm UO 14.7W 830 T8	31656000	1200mm UO 16W 830 T8	46700200
Super 80 36W/840	63201240	1200mm UO 14.7W 840 T8	31658400	1200mm UO 16W 840 T8	46696800
Super 80 36W/865	63207440	1200mm UO 14.7W 865 T8	31660700	1200mm UO 16W 865 T8	46698200
Super 80 58W/830	63213540	1500mm UO 21.7W 830 T8	31662100	1500mm UO 24W 830 T8	46706400
Super 80 58W/840	63219740	1500mm UO 21.7W 840 T8	31664500	1500mm UO 24W 840 T8	46702600
Super 80 58W/865	63225840	1500mm UO 21.7W 865 T8	31666900	1500mm UO 24W 865 T8	46704000
Secura 36W/840	64014740	1200mm UO 14.7W 840 T8	31658400	1200mm UO 16W 840 T8	46696800
Secura 58W/840	64018540	1500mm UO 21.7W 840 T8	31664500	1500mm UO 24W 840 T8	46702600
Xtreme 36W/840	55868840	1200mm UO 14.7W 840 T8	31658400	1200mm UO 16W 840 T8	46696800
Xtreme 58W/840	55886240	1500mm UO 21.7W 840 T8	31664500	1500mm UO 24W 840 T8	46702600

① Re-lamping with Philips LED lamps

CFL-ni lamps



CorePro PLED



Phase out	EOC
MASTER	
PL-C 26W/840/4P	62336270
PL-C 18W/840/4P	62334870
PL-C 26W/840/2P	62100970
PL-L 36W/840/4P	70675140
PL-C 18W/840/2P	62093470
PL-S 9W/840/2P	26087170
PL-S 11W/840/2P	26109070
PL-L 55W/840/4P	61542840

LED recommendation	EOC
CorePro LED	
PLC 9W 840 4P G24q-3	54117300
PLC 6.5W 840 4P G24q-2	54121000
PLC 8.5W 840 2P G24d-3	54125800
PLL HF 16.5W 840 4P 2G11	73974700
PLC 6.5W 840 2P G24d-2	54129600
PLS 5W 840 2P G23	59668200
PLS 5W 840 2P G23	59668200
PLL HF 24W 840 4P 2G11	82841000

GY6.35 capsules



CorePro GY6.35 capsule non dimmable



Phase out	EOC
Caps 3000h 14.3W GY6.35 12V	82777200

LED recommendation	EOC
CorePro LEDcapsule	
LV 1.8-20W GY6.35 827	76779200
LV 1.8-20W GY6.35 830	76783900

G9 capsules



CorePro G9 capsule non dimmable



Phase out	EOC
Halogen MV	
Click 19.0W G9 230V CL	89577300
Click 29.0W G9 230V CL	86398700
Caps 44.0W G9 230V CL	33495300

LED recommendation	EOC
CorePro LEDcapsule	
2-25W ND G9 827	30389800
2-25W ND G9 830	30391100
3.2-40W ND G9 827	30393500
3.2-40W ND G9 830	30395900
4.8-60W ND G9 827	65780200
4.8-60W ND G9 830	65818200

CorePro G9 capsule dimmable



LED recommendation	EOC
CorePro LEDcapsule	
MV 2.6-25W G9 827 D	76669600
MV 4-40W G9 827 D	76673300

G4 capsules



CorePro G4 capsule non dimmable



Phase out	EOC
Halo Caps 7.1W G4 12V CL	33477900
Caps 3000h 7.1W G4 12V CL	82786400
Halo Caps 14.3W G4 12V CL	33481600
Caps 3000h 14.3W G4 12V CL	82774100

LED recommendation	EOC
CorePro LEDcapsule	
LV 1-10W G4 827	76761700
LV 1-10W G4 830	76759400
LV 1-10W G4 827	76761700
LV 1-10W G4 830	76759400
LV 1.8-20W G4 827	76765500
LV 1.8-20W G4 830	76769300
LV 1.8-20W G4 827	76765500
LV 1.8-20W G4 830	76769300

CorePro G4 capsule dimmable



LED recommendation	EOC
CorePro LEDcapsule	
LV 2.1-20W G4 827 D	76753200
LV 2.1-20W G4 827 D	76753200

② Renovation with Philips LED luminaires

- ✓ Interested in modernization
- ✓ Medium installation effort estimated

- ✓ Ideal for older installations especially if current standards are not met

CFL-ni lamps



CoreLine downlight

[Go to family page >](#)



CoreLine slim downlight

[Go to family page >](#)



CFL-ni lamps



Ledinaire slim downlight

[Go to family page >](#)



Ledinaire wall-mounted

[Go to family page >](#)



T8, T5, T8 extreme,
T5 xtra fluorescent lamps




CoreLine panel

[Go to family page >](#)



CoreLine recessed

[Go to family page >](#)



CoreLine surface-mounted

[Go to family page >](#)



CoreLine batten

[Go to family page >](#)



CoreLine waterproof

[Go to family page >](#)



T8, T5 fluorescent lamps



Ledinaire panel

[Go to family page >](#)



Ledinaire recessed

[Go to family page >](#)



Ledinaire surface-mounted

[Go to family page >](#)



Ledinaire batten

[Go to family page >](#)



Ledinaire waterproof

[Go to family page >](#)



③ Upgrade to smart LED lighting

✓ Looking for maximum energy efficiency and sustainability

✓ Open for new ideas and smart lighting solutions



[Go to family page >](#)



[Go to family page >](#)



[Go to family page >](#)



[Go to family page >](#)



[Go to family page >](#)



[Go to family page >](#)



[Go to family page >](#)



[Go to family page >](#)



[Go to family page >](#)



[Go to family page >](#)



[Go to family page >](#)

Meet Interact Pro: Easy. Effective. Smart.

Our products that are labeled Interact Ready work seamlessly with the Interact Pro smart lighting system. Easy to install and set up, the wireless connection automates lighting based on presence and daylight detection for maximum energy savings and comfort. The best thing for you: No special qualifications needed!

See how easy it is to get started on: interact-lighting.com/pro



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.