PHILIPS

LED lighting

REAL PROs REAL QUALITY

Professional LED lighting catalog

Discover our wide portfolio of innovative and efficient LED lamps and luminaires for both indoor and outdoor application areas.

New generation of energy-saving MASTER Ultra Efficient range, CoreLine downlight, Ledinaire slim downlight All-in and recessed downlight.





All-in







a lighting brand by signify

October 2023

A light for every need

Welcome to this comprehensive overview of Philips' professional LED portfolio. Lamps, luminaires, handy overviews and time-saving tools – here you'll find everything you need, whatever your project demands.

Choose Philips LED lighting for:

The best products

- We're setting new standards for high-quality products that result in less maintenance and fewer technical hiccups and that strengthen your reputation as a reliable lighting expert.
- Our products are designed with easy installation in mind, saving you time and money.
- From connected lighting solutions to 3D printed luminaires – with Philips you get LED lighting that's setting the reference in the industry and that keeps you ahead of the competition.

The widest portfolio

Whatever the need, whatever the budget: with our complete portfolio of LED lighting products you'll always have the right solution at hand.



Signify

Signify, previously known as Philips Lighting, is the world leader in connected LED lighting systems, software and services. We proudly market the best lighting brands in the world, including Philips and Interact.

PHILIPS

The Philips brand stands for quality and energy-efficiency in light. For over 125 years, Philips products have been at the forefront of innovation. Today Philips is recognized as the leading brand in lighting.

interact

Interact is the brand of our IoT software and platform that manages smart lighting systems and the data that those systems collect. Smart, simple and scalable, Interact software can be used in a wide range of application areas, from small offices to entire cities.

You and Signify – a reliable partnership

Close cooperation before, during and after projects is important to us. Our local service teams make sure you always get the competent support and information you need.

We are closely working with local wholesalers to offer you flexible and on-time delivery – and product availability you can rely on.

To help you stay on top of your game the Signify Lighting Academy offers a comprehensive range of educational resources for you to grow your expertise and get certified.

Brighter lives, better world

Signify is 100% carbon neutral since September 2020.
We recycle up to 90% of our manufacturing waste.
We use 100% renewable electricity.

Thank you for choosing Philips products offered by Signify and joining us on our mission!



The 2023 bans on fluorescent are in effect!

The time is now — make the big switch!

The clock is ticking and the era of conventional lighting is rapidly coming to an end! With EU regulations being enforced and energy costs skyrocketing, the only sensible decision is to switch to LED now – because soon there will be no alternative. Philips offers 3 options for a smooth transition so you can meet lamp bans and customer demand for energy-saving, sustainable solutions.

① Re-lamping with LED lamps

- Current luminaires need to be kept
- Aiming for solution with low installation effort
- Payback period needs to be less than one year
- Larger invest irrational (e.g. rental property or big invest planned ahead)


② Renovation with LED luminaires

- Interested in modernization
- Medium installation effort estimated
- Ideal for older installations especially if current standards are not met

③ Upgrade to smart LED lighting

- Looking for maximum energy efficiency and sustainability
- Open for new ideas and smart lighting solutions


Find all products and details about the easy big switch to Philips LED at **philips.com/ledconversion**



[1] Products already placed on the market may still be sold after these dates, but they may no longer be placed on the market

Real pros don't look – they find

A partner that understands the challenges you face, saves you time. Which is why we don't only offer a comprehensive portfolio of LED luminaires and lamps, but also a couple of handy online tools that make your life easier.



philips.com/installer

Installer hub

- All latest product information
- Installation videos and training
- Links to all tools
- And more!

philips.com/productfinder

Product finder

- Easily find the perfect LED lamp or luminaire for every budget and application demand

philips.com/tco

Total cost of ownership calculator

- Calculate the total cost of your product in a few simple steps

LED Conversion tool

LED conversion tool

- Use our tool to help clients switch to Philips LEDs and offer them maximized energy savings

Contents

11

Interact Ready

11 CoreLine Panel Office compliant
12 CoreLine Panel Non-office compliant
13 CoreLine Recessed Office compliant
13 CoreLine Surface-mounted Office compliant
14 CoreLine Waterproof
14 CoreLine Wall-mounted
15 CoreLine Batten
15 CoreLine SlimDownlight
16 General lighting downlights
16 CoreLine Highbay Gen5
17 CoreLine Recessed Spot gen2
18 MasterConnect LEDspot GU10
18 MasterConnect LEDtube EM/mains T8
19 Indoor Accessories

24

CoreLine LED luminaires

24 CoreLine Panel Office compliant
27 CoreLine Panel Non-office compliant
29 CoreLine Recessed Office compliant
30 CoreLine Recessed Non-office compliant
31 CoreLine Surface-mounted Office compliant
32 CoreLine Surface-mounted Non-office compliant
33 CoreLine Batten
34 CoreLine Downlight Gen5
35 CoreLine Downlight
37 CoreLine SlimDownlight
38 General lighting downlights
39 CoreLine Waterproof
41 CoreLine tubular waterproof
43 CoreLine Trunking Gen2
45 CoreLine Highbay Gen5
47 CoreLine Value Highbay
48 CoreLine Projector gen2
49 CoreLine Wall-mounted
50 Spots
52 CoreLine Recessed Spot gen2
58 CoreLine tempo X-Large
59 CoreLine tempo large
60 CoreLine tempo medium
60 CoreLine tempo small
61 CoreLine Malaga LED

66

Ledinaire LED luminaires

66 Ledinaire Panel Office compliant
66 Ledinaire Panel Non-office compliant
67 Ledinaire Recessed Non-office compliant
68 Ledinaire Surface-mounted Office compliant
68 Ledinaire Surface-mounted Non-office compliant
69 Ledinaire Wall-mounted WL060V
69 Ledinaire Wall-mounted WL070V
70 Ledinaire Square Wall-mounted
70 Ledinaire Batten
71 Ledinaire High-bay
72 Ledinaire Waterproof
73 Ledinaire Waterproof WT065C
73 Ledinaire Waterproof Tube Housing
74 Ledinaire SlimDownlight DN065B
75 Ledinaire Recessed Downlight
75 Ledinaire ClearAccent RS060/RS061
76 Ledinaire floodlights gen3

Contents

81
LED spots
81 MASTER UltraEfficient GU10
81 SceneSwitch LEDspot
82 MASTER LEDspot ExpertColor LV
83 MASTER LEDspot ExpertColor MV
84 MASTER LEDspot ExpertColor AR111
85 MASTER VALUE LEDspot PAR
86 MASTER VALUE LEDspot LV
87 MASTER VALUE LEDspot MV
88 MASTER LEDspot LV
89 CorePro LEDspot PAR
89 CorePro LEDspot Reflectors
90 CorePro LEDspot LV
91 CorePro LEDspot MV
92 CorePro LEDspot AR111
93 CorePro LEDcapsule LV
94 CorePro LEDcapsule MV
95 CorePro LEDlinear MV

96
LED bulbs
96 SceneSwitch LEDbulbs
97 UltraEfficient LED bulb
98 Classic filament LEDbulbs
99 CorePro LEDbulbs
101 CorePro Glass LED bulbs
103 CorePro Glass High Lumen bulbs
103 CorePro Plastic LED Specialties
104 MASTER Glass LED bulbs
105 MASTER Plastic LED Dusk to Dawn
105 MASTER Plastic LED Sensor
106 MASTER Value Decorative LED bulbs
107 MASTER Value GLASS LED bulbs

110
LED candles & lusters
110 Candle LED
110 SceneSwitch LEDbulbs
111 CorePro GLASS LED candles and lusters
113 CorePro Plastic LEDcandles & lusters
114 CorePro Plastic LED Specialties
114 MASTER UltraEfficient LED candles and lusters
115 MASTER Value Decorative LED candles and lusters
116 MASTER GLASS LED candles and lusters
117 MASTER Value GLASS LED candles and lusters

121
LED tubes
121 MASTER LEDtube T8 Ultra Efficient
122 MASTER LEDtube EM/Mains T8
123 MASTER Value LEDtube EM/mains T8
123 MASTER Value LEDtube Universal T8
124 MASTER LEDtube InstantFit HF T8
125 MASTER LEDtube InstantFit HF T5
127 MASTER LEDtube Mains T5
128 CorePro LEDtube EM/Mains T8
130 CorePro LED tube Universal T8

131
LED PL-lamps
131 CorePro LED PLC 2P
131 CorePro LED PLC 4P
132 CorePro LED PLS
132 CorePro LED PLL

136
TrueForce LED
136 Trueforce Core LED SON-T
136 TrueForce LED Industrial and Retail (Highbay – MH)
137 TrueForce LED Public (Urban/Road – HPL/SON)
138 Trueforce CorePro LED HPL
139 TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)
139 TrueForce LED Public (Road/Area – SOX)
140 TrueForce LED Public (Road – SON)
141 MASTER - LED HID SOX
141 MASTER - LED HID SON-T - Ultra Efficient

Philips Interact Ready

interact ready.

Office



CoreLine recessed



CoreLine downlight



CoreLine surface-mounted



MasterConnect LEDspot



CoreLine panel




MasterConnect LEDtube



CoreLine FastSet

Industry



CoreLine highbay gen5



CoreLine trunking



CoreLine waterproof



CoreLine batten

Parking



CoreLine waterproof



CoreLine wall-mounted



MasterConnect LEDtube

Retail



CoreLine slim downlight



CoreLine recessed spot

Components



RF-DALI connector kit




Wireless sensors



Wireless switches



How the smart lighting system comes together:



Easy. Effective. Smart.

The flexible smart lighting system Interact Pro brings savings and convenience to any business — with little installation effort

Meet Interact Pro: the wireless smart lighting system that's easy to install and set up — and will have an impressive positive effect on your customers' energy savings in no time.

Our award-winning, intuitive software — together with a gateway and Interact Ready lighting — can make any place not only smarter, but also safer, more user-friendly, and altogether more pleasant.

Easy
Not only are the components of the Interact Pro system hassle-free and wireless to install, but setup and commissioning via the Interact Pro app is quick and intuitive.

Effective
Interact Pro is effective in many ways: it's extremely cost-efficient, saving up to 75% energy. It can promote employee well-being, productivity and safety. It also contributes significantly to the sustainability of the building and enables efficient remote monitoring of the system.

Smart
We don't just call Interact Pro smart because it is intelligent lighting. For us, smart also means versatility, flexibility, reliability, safety — and much more.

Learn more about Interact Pro, its benefits, and how easy it is on:
www.interact-lighting.com/pro

Smart benefits for smart installers

Get more done faster
- Quick installation of lights: wireless system, no drilling or cabling needed
- Easy to handle for any installer, even for first-timers
- Convenient project planning and offsite preparation with the Interact Pro app or web portal


Works everywhere
- One system for multiple applications e. g. office, industry, education and many more
- Extensive range of high-quality Philips Interact Ready LED luminaires, lamps, switches and sensors available
- Seamless integration: easily connect to third-party luminaires using a simple kit

Become the preferred partner
- Offer smart lighting benefits at a more affordable total project cost than wired systems
- Enhance your reputation by becoming an expert in lighting solutions beyond LED conversion and empowering your customers on their journey towards sustainability

Convince your customers easily
- Achieve up to 75% reduction in energy costs with LED lighting and simple lighting controls
- Enhance well-being, productivity and safety with lighting that can positively impact people
- Enable owners and users to customize lighting to their preferences via Interact Pro app

Interact Pro features

Convince your customers with a multitude of smart features that will have an impressive effect on energy savings and comfort in any business in no time.



Setup & commissioning

Bluetooth based setup
Easy commissioning thanks to Bluetooth setup using smartphone app.

Multiple installers per project
Faster realization with multiple installers working simultaneously on a single project.

Off-site-project preparation
Prepare projects in advance to save time on-site. Possible via the Interact Pro app as well as via the web portal.

Adapt to any space
Detailed lighting settings such as on/off behaviour, timings and lighting levels allow to perfectly adapt the system to any space.

Monitoring & support

Cloud backup
All project information is securely stored in the cloud to ensure that data is never lost.

Regular app updates
Our team is continuously working to enhance the user experience and bring new features to the system.

Get support
The in-app chatbot Bulbi is here to help you 24/7: visit it for instant troubleshooting.

Unlock more features with the Interact Pro gateway

Remote diagnostics
Know about devices nearing end of lifetime based on burning hours and potential failures at project and light level to improve servicing of the building.

Energy reporting
Up to 12 months of detailed energy consumption reporting. Export in .csv format for further processing.

Over-the-air upgrades
Automatic feature and security upgrades happen in the background with minimal impact on building operations.

Control

Motion sensing
helps conserve energy by activating lights only when in use.

Daylight harvesting
uses sensor data to automatically dim the lights when enough sunlight is illuminating a room.

Wireless switches
can be installed anywhere to make control of the lighting system more accessible to users.

Scene support
Easily create custom scenes and recall them using wireless switches or app.

Organize your lights
Arrange your building lighting in networks (e.g. at floor level). Achieve granular control by further subdividing into groups (e.g. room) and zones (e.g. window areas).

Tunable White*
Set the default colour temperature for your lights or manually control it using wireless switches.

Unlock more features with the Interact Pro gateway

App control
Grant users access to customize the lights around them to their preferences.

Scene scheduling
Automatically cycle through up to 16 scenes per day. These schedules repeat daily.

Remotely control the lights
Remotely turn the lights on, off, or activate a scene via the Interact Pro app or web portal.

* With compatible luminaires

Interact Ready

Now that more and more products are being connected to the internet, they are becoming smarter. This provides more flexibility, saves extra costs and offers more comfort. This means there is an opportunity for the installation sector to be part of the smart lighting on the internet, to offer a better experience for the end user. So far, small and medium-sized enterprises (SMEs) have remained excluded from these developments, but that is now a thing of the past. The luminaires and lamps from the list below are the first Interact Ready LED products and work seamlessly with the intuitive Interact Pro app and dashboard.

CoreLine Panel Office compliant

www.philips.com/interact-ready

L80 /L75 at 100.000

1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	IP rating	IK rating	Motion/Daylight sensor	Warranty	12NC	EOC code
		W	lm	lm/W			K					Years		
NEW	RC132V G5 34S/830 WIA W60L60 OC	28.5	3400	120	Wireless	≥80	3000	19	IP20/44	IK03	-	5	911401857984	95366600
NEW	RC132V G5 34S/830 WIA W60L60 OC W3	28.5	3400	120	Wireless	≥80	3000	19	IP20/44	IK03	-	5	911401858884	95375800
NEW	RC132V G5 36S/840 WIA W30L120 OC	28.5	3600	125	Wireless	≥80	4000	19	IP20/44	IK03	-	5	911401858484	95371000
NEW	RC132V G5 36S/840 WIA W30L120 OC W3	28.5	3600	125	Wireless	≥80	4000	19	IP20/44	IK03	-	5	911401859184	95378900
NEW	RC132V G5 36S/840 WIA W60L60 OC	28.5	3600	125	Wireless	≥80	4000	19	IP20/44	IK03	-	5	911401858084	95367300
NEW	RC132V G5 36S/840 WIA W60L60 OC TP(a)	28.5	3600	125	Wireless	≥80	4000	19	IP20/44	IK03	-	5	911401859284	95379600
NEW	RC132V G5 36S/840 WIA W60L60 OC W3	28.5	3600	125	Wireless	≥80	4000	19	IP20/44	IK03	-	5	911401858984	95376500
NEW	RC133V G5 34S/830 WIA W62L62 OC	28.5	3400	120	Wireless	≥80	3000	19	IP20/44	IK03	-	5	911401858284	95369700
NEW	RC133V G5 36S/840 WIA W62L62 OC	28.5	3600	125	Wireless	≥80	4000	19	IP20/44	IK03	-	5	911401858384	95370300
	RC132V G4 LED36S/840 WIA W60L60 OC	29	3600	-	Wireless	-	-	-	-	-	-	-	910505101187	-
	RC132V G4 LED43S/840 WIA W60L60 OC	29	4300	-	Wireless	-	-	-	-	-	-	-	910505101287	-
NEW	RC132V G5 36/840 WIA W60L60 OC ELB3TP(a)	34	3600	107	Wireless	≥80	4000	19	IP20/44	IK03	-	5	910505102375	01395700
NEW	RC132V G5 36S/840 WIA W30L120 OC ELB3	34	3600	107	Wireless	≥80	4000	19	IP20/44	IK03	-	5	910505102368	01388900
NEW	RC132V G5 36S/840 WIA W30L120 OC ELB3 W4	34	3600	107	Wireless	≥80	4000	19	IP20/44	IK03	-	5	910505102372	01392600
NEW	RC132V G5 36S/840 WIA W60L60 OC ELB3	34	3600	107	Wireless	≥80	4000	19	IP20/44	IK03	-	5	910505102366	01386500
NEW	RC132V G5 36S/840 WIA W60L60 OC ELB3 W4	34	3600	107	Wireless	≥80	4000	19	IP20/44	IK03	-	5	910505102371	01391900
NEW	RC132V G5 43S/840 WIA W60L60 OC ELB3	34	4300	128	Wireless	≥80	4000	19	IP20/44	IK03	-	5	910505102374	01394000
NEW	RC132V G5 43S/840 WIA W60L60 OC ELB3 W4	34	4300	128	Wireless	≥80	4000	19	IP20/44	IK03	-	5	910505102376	01396400
NEW	RC132V G5 43S/840 WIA W60L60 OC	34.5	4300	125	Wireless	≥80	4000	19	IP20/44	IK03	-	5	911401858184	95368000
NEW	RC132V G5 43S/840 WIA W60L60 OC W3	34.5	4300	125	Wireless	≥80	4000	19	IP20/44	IK03	-	5	911401859084	95377200
	RC132V G4 LED43S/840 WIA W60L60 OC W3	34.5	4300	-	Wireless	-	-	-	-	-	-	-	910505101290	-
	RC133V G4 LED43S/840 WIA W62L62 OC	34.5	4300	-	Wireless	-	-	-	-	-	-	-	910505101288	-
NEW	RC132V G5 40S/830 SIA W60L60 OC IA4	36	4000	111	Wireless	≥80	3000	19	IP20	IK03	No	5	910505102378	01398800
NEW	RC132V G5 43S/840 SIA W60L60 OC IA4	36	4300	119	Wireless	≥80	4000	19	IP20	IK03	No	5	910505102377	01397100

Interact Ready

CoreLine Panel Non-office compliant

www.philips.com/interact-ready



1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	IP rating	IK rating	Warranty	12NC	EOC code
		W	lm	lm/W			K				Years		
NEW	1 RC132V G5 34S/830 WIA W60L60 NOC	28.5	3400	120	Wireless	≥80	3000	22	IP20/44	IK03	5	911401857684	95363500
NEW	1 RC132V G5 34S/830 WIA W60L60 NOC W3	28.5	3400	120	Wireless	≥80	3000	22	IP20/44	IK03	5	911401858584	95372700
NEW	2 RC132V G5 36S/840 WIA W30L120 NOC	28.5	3600	125	Wireless	≥80	4000	22	IP20/44	IK03	5	911401857884	95365900
NEW	1 RC132V G5 36S/840 WIA W60L60 NOC	28.5	3600	125	Wireless	≥80	4000	22	IP20/44	IK03	5	911401857784	95364200
NEW	1 RC132V G5 36S/840 WIA W60L60 NOC W3	28.5	3600	125	Wireless	≥80	4000	22	IP20/44	IK03	5	911401858684	95373400
	3 RC132V G4 LED34S/830 WIA W60L60 NOC W3	29	3400	-	Wireless	-	-	-	-	-	-	910505101292	-
	3 RC132V G4 LED36S/840 WIA W60L60 NOC	29	3600	123	Wireless	≥80	4000	23	IP20/44	IK03	5	910505101278	97586900
	3 RC133V G4 LED36S/840 WIA W62L62 NOC	29	3600	-	Wireless	-	-	-	-	-	-	910505101284	-
NEW	1 RC132V G5 36S/840 WIA W60L60 NOC ELB3	34	3600	107	Wireless	≥80	4000	22	IP20/44	IK03	5	910505102367	01387200
NEW	1 RC132V G5 36S/840 WIA W60L60 NOC ELB3 W4	34	3600	107	Wireless	≥80	4000	22	IP20/44	IK03	5	910505102370	01390200
NEW	1 RC132V G5 43S/840 WIA W60L60 NOC ELB3	34	4300	128	Wireless	≥80	4000	22	IP20/44	IK03	5	910505102369	01389600
NEW	1 RC132V G5 43S/840 WIA W60L60 NOC ELB3 W4	34	4300	128	Wireless	≥80	4000	22	IP20/44	IK03	5	910505102373	01393300
NEW	1 RC132V G5 43S/840 WIA W60L60 NOC W3	34.5	4300	125	Wireless	≥80	4000	22	IP20/44	IK03	5	911401858784	95374100
	3 RC132V G4 LED43S/840 WIA W60L60 NOC W3	34.5	4300	-	Wireless	-	-	-	-	-	-	910505101297	-

Interact Ready

CoreLine Recessed Office compliant

www.philips.com/interact-ready

L70 at 100.000 | IP20/44 | IK03 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
RC136B 40S/830 WIA W60L60 OC	31	4000	135	Wireless	≥80	3000	19	911401896681	51504800
RC136B 40S/830 WIA W60L60 OC W3	31	4000	135	Wireless	≥80	3000	19	911401867482	53239700
RC136B 43S/840 WIA W30L120 OC	31	4300	140	Wireless	≥80	4000	19	911401867382	53238000
RC136B 43S/840 WIA W30L120 OC W3	31	4300	140	Wireless	≥80	4000	19	911401867682	53241000
RC136B 43S/840 WIA W60L60 OC	31	4300	140	Wireless	≥80	4000	19	911401896781	51505500
RC136B 43S/840 WIA W60L60 OC W3	31	4300	140	Wireless	≥80	4000	19	911401867582	53240300

CoreLine Surface-mounted Office compliant

www.philips.com/interact-ready



L70 at 100.000 | IP20/44 | IK03 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
SM136V 40S/830 WIA W20L120 OC	31	4000	135	Wireless	≥80	3000	19	911401896881	51506200
SM136V 40S/830 WIA W20L120 OC W3	31	4000	135	Wireless	≥80	3000	19	911401867782	53242700
SM136V 40S/830 WIA W20L150 OC	31	4000	135	Wireless	≥80	3000	19	911401897081	51508600
SM136V 43S/840 WIA W20L120 OC	31	4300	140	Wireless	≥80	4000	19	911401896981	51507900
SM136V 43S/840 WIA W20L120 OC W3	31	4300	140	Wireless	≥80	4000	19	911401867882	53243400
SM136V 43S/840 WIA W20L150 OC	31	4300	140	Wireless	≥80	4000	19	911401897181	51509300

Interact Ready

CoreLine Waterproof

www.philips.com/interact-ready



70 at 100.000 | IP65 | IK08 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
WT120C G2 LED40S/840 WIA L1200	30	4000	133	Wireless	>80	4000	25	910505101269	97576000
WT120C G2 LED40S/840 WIA TW3 L1200	30	4000	133	Wireless	>80	4000	25	910505101273	97580700
WT120C G2 LED40S/840 WIA ELB3 L1200	33	4000	121	Wireless	>80	4000	25	910505101270	97577700
WT120C G2 LED65S/840 WIA L1500	45	6500	144	Wireless	>80	4000	25	910505101271	97578400
WT120C G2 LED65S/840 WIA TW3 L1500	46	6500	141	Wireless	>80	4000	25	910505101274	97581400
WT120C G2 LED65S/840 WIA ELB3 L1500	48	6500	135	Wireless	>80	4000	25	910505101272	97579100
WT120C G2 LED80S/840 WIA TW3 L1500	60	8000	133	Wireless	>80	4000	25	910505103015	96536200
WT120C G2 LED80S/840 WIA L1500	61	8000	131	Wireless	>80	4000	25	910505103013	96534800
WT120C G2 LED80S/840 WIA ELB3 L1500	67	8000	119	Wireless	>80	4000	25	910505103014	96535500

CoreLine Wall-mounted

www.philips.com/interact-ready



80 at 50.000 | IP65 | IK10 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W	°			K			
WL140V LED20S/830 WIA WH	22	2100	95	120	Wireless	>80	3000	24	910505101546	97860000
WL140V LED20S/840 WIA WH	22	2200	100	120	Wireless	>80	4000	24	910505101547	97861700
WL140V LED20S/830 WIA ELB3 WH	25	2100	84	120	Wireless	>80	3000	24	910505101562	97876100
WL140V LED20S/840 WIA ELB3 WH	25	2200	88	120	Wireless	>80	4000	24	910505101563	97877800
WL140V LED34S/830 WIA WH	35.5	3350	94	120	Wireless	>80	3000	25	910505101548	97862400
WL140V LED34S/840 WIA WH	35.5	3400	95	120	Wireless	>80	4000	25	910505101549	97863100
WL140V LED34S/830 WIA ELB3 WH	38.5	3350	87	120	Wireless	>80	3000	25	910505101564	97878500
WL140V LED34S/840 WIA ELB3 WH	38.5	3400	88	120	Wireless	>80	4000	25	910505101565	97879200

Interact Ready

CoreLine Batten

www.philips.com/interact-ready

IP20 · IK04 · 5 Years · 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
BN126C LED41S/840 WIA L1200	34	4100	121	Wireless	>80	4000	26	910505103380	10043500
BN126C LED52S/840 WIA L1500	44	5200	118	Wireless	>80	4000	26	910505103381	10044200
BN126C LED60S/830 WIA L1200	54	6000	111	Wireless	>80	3000	26	910505103401	10063300
BN126C LED64S/840 WIA L1200	54	6400	119	Wireless	>80	4000	26	910505103372	10022000
BN126C LED74S/830 WIA L1500	64	7400	116	Wireless	>80	3000	26	910505103375	10229300
BN126C LED80S/840 WIA L1500	64	8000	125	Wireless	>80	4000	26	910505103374	10026800

CoreLine SlimDownlight

www.philips.com/interact-ready

L70 at 50.000 · IP20/44 · IK02 · 5 Years · 10 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W	°			K			
DN145B LED10S/830 WIA-E WH	13	1100	93	120	Wireless	>80	3000	28	910505101195	97638599
DN145B LED10S/840 WIA-E WH	13	1100	93	120	Wireless	>80	4000	28	910505101196	97640899
DN145B LED20S/830 WIA-E WH	22.5	2100	93	120	Wireless	>80	3000	28	910505101197	97642299
DN145B LED20S/840 WIA-E WH	22.5	2100	93	120	Wireless	>80	4000	28	910505101198	97644699

Interact Ready

General lighting downlights

www.philips.com/interact-ready



L80 at 50.000 | IP20 | IK02 | 5 Years | 1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
		W	lm	lm/W			K			
NEW	DN142B 20S/830 WIA-E UGR19 IP54	20.1	2250	111	Wireless	≥80	3000	19	910505103612	10912400
NEW	DN142B 20S/840 WIA-E WR IP54	20.1	2000	117	Wireless	≥80	4000	25	910505103613	10913100
NEW	DN142B 20S/830 WIA-E WR ELB3 IP54	24.5	2350	95	Wireless	≥80	3000	25	910505103615	10915500
NEW	DN142B 20S/840 WIA-E UGR19 ELB3 IP54	24.5	2250	91	Wireless	≥80	4000	19	910505103618	10918600
NEW	DN142B 20S/840 WIA-E WR ELB3 IP54	24.5	2350	95	Wireless	≥80	4000	25	910505103617	10917900

CoreLine Highbay Gen5

www.philips.com/interact-ready



L75 at 100.000 | IP65 | IK05 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	Motion/Daylight sensor	12NC	EOC code
	W	lm	lm/W			K				
BY122X G5 LED105S/840 SIA NB H4	72	10.500	146	Wireless	>80	4000	22	No	911401631608	95590500
BY122X G5 LED105S/840 SIA WB H4	72	10.500	146	Wireless	>80	4000	25	No	911401631708	95591200
BY122X G5 LED200S/840 SIA NB H4	133	20.000	150	Wireless	>80	4000	22	No	911401631808	95592900
BY122X G5 LED200S/840 SIA WB H4	133	20.000	150	Wireless	>80	4000	25	No	911401631908	95593600
BY122X G5 LED250S/840 SIA NB H4	166	25.000	151	Wireless	>80	4000	22	No	911401632008	95594300
BY122X G5 LED250S/840 SIA WB H4	166	25.000	151	Wireless	>80	4000	25	No	911401632108	95595000
BY122X G5 LED300S/840 SIA NB H4	203	30.000	148	Wireless	>80	4000	22	No	911401633008	95604900
BY122X G5 LED300S/840 SIA WB H4	203	30.000	148	Wireless	>80	4000	25	No	911401633108	95605600

Interact Ready

CoreLine Recessed Spot gen2

www.philips.com/interact-ready



IP20/44 | IK03 | 5 Years | 18 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W	°			K			
RS151B LED12-WB-/830 D78 WIA PI6 WH	12	1280	106	120	Wireless	>80	3000	24	911401898582	54822099
RS151B LED12-WB-/840 D78 WIA PI6 WH	12	1320	110	120	Wireless	>80	4000	24	911401898682	54823799
RS156B LED12-WB-/830 D68 WIA PI6 WH	12	1300	108	120	Wireless	>80	3000	33	911401821984	94093299
RS156B LED12-WB-/840 D68 WIA PI6 WH	12	1380	115	120	Wireless	>80	4000	33	911401822084	94094999

Interact Ready

MasterConnect LEDspot GU10

www.philips.com/interact-ready



10 PACK GU10

	Product Type	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	lm	lm/W	cd	°			K	Hrs.					
NEW	MC LEDspot IA 4.7-50W GU10 927 36D	4.7	345	73	500	36	Wireless Dim	90	2700	25.000	50	100	F	929002253702	69392300
NEW	MC LEDspot IA 4.7-50W GU10 930 36D	4.7	345	73	500	36	Wireless Dim	90	3000	25.000	50	100	F	929002253802	69394700
NEW	MC LEDspot IA 4.7-50W GU10 940 36D	4.7	345	73	500	36	Wireless Dim	90	4000	25.000	50	100	F	929002253902	69396100

MasterConnect LEDtube EM/mains T8

www.philips.com/interact-ready



10 PACK

Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
MC LEDtube IA 600mm HO 7W840 T8	18	7	1050	150	160	Wireless Dim	83	4000	60.000	25.8	600	D	929002295302	71748300
MC LEDtube IA 600mm HO 7W865 T8	18	7	1050	150	160	Wireless Dim	83	6500	60.000	25.8	600	D	929002295402	71750600
MC LEDtube IA 1200mm UO 16W840 T8	36	16	2500	156	160	Wireless Dim	83	4000	60.000	25.8	1,200	D	929002210402	66970600
MC LEDtube IA 1200mm UO 16W865 T8	36	16	2500	156	160	Wireless Dim	83	6500	60.000	25.8	1,200	D	929002210502	66972000
MC LEDtube IA 1500mm UO 25W840 T8	58	25	3700	148	160	Wireless Dim	83	4000	60.000	25.8	1,500	D	929002210802	66976800
MC LEDtube IA 1500mm UO 25W865 T8	58	25	3700	148	160	Wireless Dim	83	6500	60.000	25.8	1,500	D	929002210902	66978200

Interact Ready



10 /20 /50 /1 PACK

Product Type	Dimmable	12NC	EOC code
OCC SENSOR IA CM IP42 WH	Wireless	929001819002	77752700
OCC-DL SENSOR IA CM IP42 WH	Wireless	929001819102	77754100
Interact Ready RF DALI Connector	Wireless	913701047003	26616200
LCN1840/05 Interact Pro wireless gateway	Wireless	913701037703	77579000
LCN3110/05 OCC SENSOR IA CM IP65 WH	Wireless	913701043903	74542400
LCN3120/05 OCC-DL SENSOR IA CM IP65 WH	Wireless	913701044003	74545500
UID8480/10 ZGP Switch Dim 4B	Wireless	913701055803	27380100

Philips CoreLine

Performance

Industry



CoreLine highbay gen5



CoreLine trunking



CoreLine highbay**



CoreLine waterproof



CoreLine Value highbay




CoreLine batten




CoreLine tubular waterproof


Office



CoreLine recessed



CoreLine panel



CoreLine surface-mounted



CoreLine tubular waterproof



CoreLine downlight



CoreLine slim downlight



CoreLine FastSet

Parking



CoreLine wall-mounted



CoreLine waterproof



CoreLine batten

Retail



CoreLine projector



CoreLine recessed spot



CoreLine slim downlight

Outdoor



CoreLine Malaga



CoreLine Tempo

* Only available for selected products, please check the product information on the following pages
** Available only until stock lasts

Real pros bring lighting to new levels



The Philips CoreLine range is the reference for innovative good quality, easy-to-use lighting solutions for every project where light really matters

When lighting really matters, you want to offer your customers the absolute best in quality and choice. Philips CoreLine gives you all that and more with a full range of easy-to-install LED luminaires for every application and situation. All CoreLine luminaires are easy to handle and install – which makes total sense, because the quicker you can finish an installation, the sooner you can move onto the next job. And more installations mean more turnover.

Available in the Philips CoreLine range

All-in

Our latest addition to the Philips CoreLine family, the CoreLine All-in luminaires, integrate up to 9 codes in a single luminaire by offering the MultiLumen and/or Multi ColorTemp feature. Enjoy unparalleled flexibility on-site at the flip of a switch.

interact ready.

Interact Ready luminaires include integrated wireless communications, and are fully compatible with gateways, sensors and software to set up a smart lighting system.

Enjoy more performance and variety with Philips CoreLine – the complete range of high-quality LED lighting that's setting the reference in the market.

Now up to 100K hrs lifetime*

Find out more about the range at philips.com/coreline

Innovative
CoreLine luminaires are Interact Ready and work seamlessly with the intuitive Interact Pro app and dashboard.

Easy-to-install
The efficient design of CoreLine LED luminaires enables replacement of existing lights, with no need for expensive re-wiring or new ceiling configurations.

High-quality
At the heart of CoreLine's high-quality light is LED technology. Its long lifetime enables you to meet every demand and provide the best lighting solution.

* Only available for selected products, please check the product information on the following pages

New: Philips CoreLine All-in

All you need for maximum installation flexibility



CoreLine All-in luminaires integrate up to 9 codes in a single luminaire by combining up to 3 color temperatures and 3 lumen outputs. Enjoy unparalleled flexibility on-site at the flip of a switch.

Here's how it works

- The lumen output and/or color temperature can be adjusted via an integrated switch.*
- Multi ColorTemp: 2700K/3000K/3500K/4000K/6500K*
- Multi Lumen: 1,200/2,000 lm, 2,000/3,400 lm, 2,500/4,100/6,400 lm, 2,700/4,500 lm, 2,800/3,400/4,000 lm, 3,100/3,600/4,300 lm, 3,100/3,700/4,300 lm, 3,500/5,200/8,000 lm, 3,700/6,000 lm*

Multi ColorTemp | Multi Lumen | Easy to switch

Your benefits

- Reduced risk of selecting the wrong luminaire. Just change the setting on location to fit the requirements.
- Fast installation with quick connectors.
- Perfect for maintenance: Pick the right setting on-site while changing luminaires or adjust after installation.
- All-in luminaires fulfill our highest standards to give you peace of mind.

* Depending on product.

CoreLine batten All-in

CoreLine panel All-in



CoreLine wall-mounted All-in

CoreLine surface-mounted All-in



CoreLine recessed All-in



CoreLine slim downlight All-in

CoreLine FastSet All-in

CoreLine waterproof All-in



Product highlight

Philips CoreLine downlight

The perfect downlight for use in general lighting applications



- Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard
- Office-compliant versions available (UGR19)
- Two sizes and lumen outputs available: Ø 150 mm/1,200 lm; Ø 200 mm/2,350 lm
- Reliable DALI
- IP54 and emergency lighting versions optionally available
- External driver
- Lifetime: 50,000 hours (at L80)
- Up to 120 lm/W

interact ready.

Click here to see all products



White reflector



Aluminum reflector (UGR19)

Designed with one thing in mind: you.

You know what really matters on the job. Fast and easy installation, right? You want to be in and out, quickly, efficiently and professionally. The CoreLine range has been designed to help you do exactly that.

No tools, no nonsense

Making your life extra easy is the 3-pole push-in connector: simply detach, wire and re-connect with the luminaire. It comes with a through wiring option for more flexibility and can be found in CoreLine recessed spots, panels, recessed and surface-mounted luminaires and battens.

Other luminaires, such as the CoreLine projectors and highbays, have preassembled connectors, so installation is as quick and straightforward as plug and play.




Push-in connector



Preassembled connector



Lightweight and compact design



Optimized sliders and locks

Easy handling

Here's just a few examples of how we constantly improve our CoreLine luminaires to make them more pleasant to handle:

- Longer sliders and improved locks for easier opening and closing (CoreLine waterproof)
- Light weight and compact size (recessed spot and highbay)
- Modular design for easy replacement of modules or accessories (recessed spot)
- Robust details – such as the metal hinge of the CoreLine projector
- No sharp edges on the panel, recessed and surface-mounted luminaires

Click here for a compilation of handy installation videos for most CoreLine products!

CoreLine LED luminaires

Philips CoreLine offers a full range of LED lighting solutions that keeps installation time to a minimum, while saving a maximum of energy. Whether old or new, optimal lighting can transform a building into something truly special and turn it into a place where people enjoy working and living. Give your customers that "wow" moment with Philips CoreLine: the complete range of high quality LED lighting that's setting the reference in the market. Because when light really matters, you don't want to take a chance.

CoreLine Panel Office compliant

www.philips.com/coreline



L80 at 100.000 | 1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	IP rating	IK rating	Warranty	12NC	EOC code
		W	lm	lm/W			K				Years		
NEW	1 RC132V G5 34S/830 PSD W30L120 OC	28.5	3400	120	Yes	≥80	3000	19	IP20/44	IK03	5	911401841884	95012200
NEW	1 RC132V G5 34S/830 PSD W30L120 OC W5	28.5	3400	120	Yes	≥80	3000	19	IP20/44	IK03	5	911401843484	95028300
NEW	2 RC132V G5 34S/830 PSD W60L60 OC	28.5	3400	120	Yes	≥80	3000	19	IP20/44	IK03	5	911401841484	95008500
NEW	2 RC132V G5 34S/830 PSD W60L60 OC W5	28.5	3400	120	Yes	≥80	3000	19	IP20/44	IK03	5	911401843284	95026900
NEW	2 RC132V G5 34S/830 PSU W60L60 OC	28.5	3400	120	No	≥80	3000	19	IP20/44	IK03	5	911401841084	95004700
NEW	2 RC132V G5 34S/830 PSU W60L60 OC W3	28.5	3400	120	No	≥80	3000	19	IP20/44	IK03	5	911401842884	95022100
NEW	1 RC132V G5 36S/840 PSD W30L120 OC	28.5	3600	125	Yes	≥80	4000	19	IP20/44	IK03	5	911401841984	95013900
NEW	1 RC132V G5 36S/840 PSD W30L120 OC W5	28.5	3600	125	Yes	≥80	4000	19	IP20/44	IK03	5	911401843584	95029000
NEW	2 RC132V G5 36S/840 PSD W60L60 OC	28.5	3600	125	Yes	≥80	4000	19	IP20/44	IK03	5	911401841584	95009200
NEW	2 RC132V G5 36S/840 PSD W60L60 OC TP(a)	28.5	3600	125	Yes	≥80	4000	19	IP20/44	IK03	5	911401859384	95380200
NEW	2 RC132V G5 36S/840 PSD W60L60 OC W5	28.5	3600	125	Yes	≥80	4000	19	IP20/44	IK03	5	911401843384	95027600
NEW	3 RC132V G5 36S/840 PSU W30L120 OC	28.5	3600	125	No	≥80	4000	19	IP20/44	IK03	5	911401841384	95007800
NEW	1 RC132V G5 36S/840 PSU W30L120 OC W3	28.5	3600	125	No	≥80	4000	19	IP20/44	IK03	5	911401843084	95024500
NEW	2 RC132V G5 36S/840 PSU W60L60 OC	28.5	3600	125	No	≥80	4000	19	IP20/44	IK03	5	911401841184	95005400
NEW	2 RC132V G5 36S/840 PSU W60L60 OC W3	28.5	3600	125	No	≥80	4000	19	IP20/44	IK03	5	911401842984	95023800
NEW	4 RC133V G5 36S/840 PSD W62L62 OC	28.5	3600	125	Yes	≥80	4000	19	IP20/44	IK03	5	911401841784	95011500
NEW	4 RC133V G5 36S/840 PSU W62L62 OC	28.5	3600	125	No	≥80	4000	19	IP20/44	IK03	5	911401841284	95006100
	5 RC133V G4 LED36S/840 PSU W62L62 OC	29	3600	-	-	-	-	-	-	-	-	911401878780	-
NEW	4 RC133V G5 34S/830 PSED W62L62 OC	30	3400	113	Yes	≥80	3000	19	IP20/44	IK03	5	910505102357	01377300
NEW	4 RC133V G5 36S/840 PSED W62L62 OC	30	3600	120	Yes	≥80	4000	19	IP20/44	IK03	5	910505102356	01376600
	6 RC132V G4 LED36S/840 PSD W30L120 OC ELB3	33	3600	-	-	-	-	-	-	-	-	910505100537	-
	6 RC132V G4 LED36S/840 PSU W30L120 OC ELB3	33	3600	-	-	-	-	-	-	-	-	910505100536	-
NEW	2 RC132V G5 34S/830 PSD W60L60 OC ELB3	34	3400	100	Yes	≥80	3000	19	IP20/44	IK03	5	910505102354	01374200
NEW	1 RC132V G5 36S/840 PSD W30L120 OC ELB3	34	3600	106	Yes	≥80	4000	19	IP20/44	IK03	5	910505102350	01370400
NEW	1 RC132V G5 36S/840 PSD W30L120OCELB3W4W2	34	3600	106	Yes	≥80	4000	19	IP20/44	IK03	5	910505102363	01383400

CoreLine LED luminaires

CoreLine Panel Office compliant - Continued

www.philips.com/coreline



L80 /L75 at 100.000 | IP20/44 | IK03 | 5 Years | 1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
		W	lm	lm/W			K			
NEW	1 RC132V G5 36S/840 PSD W60L60 OC ELB3	34	3600	106	Yes	≥80	4000	19	910505102347	01367400
NEW	1 RC132V G5 36S/840 PSD W60L60 OC ELB3W4W2	34	3600	106	Yes	≥80	4000	19	910505102360	01380300
NEW	1 RC132V G5 36S/840 PSD W60L60 OCTP(a)ELB3	34	3600	106	No	≥80	4000	19	910505102352	01372800
NEW	2 RC132V G5 36S/840 PSU W30L120 OC ELB3	34	3600	106	No	≥80	4000	19	910505102349	01369800
NEW	3 RC132V G5 36S/840 PSU W30L120 OC ELB3 W4	34	3600	106	No	≥80	4000	19	910505102362	01382700
NEW	1 RC132V G5 36S/840 PSU W60L60 OC ELB3	34	3600	106	No	≥80	4000	19	910505102348	01368100
NEW	1 RC132V G5 36S/840 PSU W60L60 OC ELB3W4	34	3600	106	No	≥80	4000	19	910505102359	01379700
NEW	4 RC132V G5 29_34_40S/830 PSD W60L60 OC	34.5-24.5	2900-3400-4000	120	Yes	≥80	3000	19	911401844284	95036800
NEW	5 RC132V G5 29_34_40S/830 PSU W60L60 OC	34.5-24.5	2900-3400-4000	120	No	≥80	3000	19	911401843684	95030600
NEW	6 RC132V G5 31_36_43S/840 PSD W60L60 OC	34.5-24.5	3100-3600-4300	125	Yes	≥80	4000	19	911401844384	95037500
NEW	7 RC132V G5 31_36_43S/840 PSU W60L60 OC	34.5-24.5	3100-3600-4300	125	No	≥80	4000	19	911401843784	95031300
NEW	1 RC132V G5 36S/940 PSD W60L60 OC	34.5	3600	104	Yes	≥90	4000	19	911401842384	95017700
NEW	2 RC132V G5 36S/940 PSU W30L120 OC	34.5	3600	104	No	≥90	4000	19	911401842284	95016000
NEW	1 RC132V G5 36S/940 PSU W60L60 OC	34.5	3600	104	No	≥90	4000	19	911401842184	95015300

CoreLine Panel Office compliant - Continued

www.philips.com/coreline



L75 at 100.000 | 1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	IP rating	IK rating	Warranty	12NC	EOC code
		W	lm	lm/W			K				Years		
NEW	1 RC133V G5 29_34_40S/830 PSD W62L62 OC	34.5-24.5	2900-3400-4000	120	Yes	≥80	3000	19	IP20/44	IK03	5	911401844484	95038200
NEW	2 RC133V G5 29_34_40S/830 PSU W62L62 OC	34.5-24.5	2900-3400-4000	120	No	≥80	3000	19	IP20/44	IK03	5	911401843884	95032000
NEW	3 RC133V G5 31_36_43S/840 PSD W62L62 OC	34.5-24.5	3100-3600-4300	125	Yes	≥80	4000	19	IP20/44	IK03	5	911401844584	95039900
NEW	4 RC133V G5 31_36_43S/840 PSU W62L62 OC	34.5-24.5	3100-3600-4300	125	No	≥80	4000	19	IP20/44	IK03	5	911401843984	95033700
NEW	5 RC133V G5 31_36_43S/865 PSU W62L62 OC	34.5-24.5	3100-3600-4300	125	No	≥80	6500	19	IP20/44	IK03	5	911401844084	95034400
	6 RC132V G4 LED40S/830 PSD W60L60 OC	35	4000	-	-	-	-	-	-	-	-	911401872082	-
NEW	7 RC133V G5 43S/865 PSED W62L62 OC	37	4300	116	Yes	≥80	6500	19	IP20/44	IK03	5	910505102379	01399500

CoreLine LED luminaires



1



2

L75 /L70 at 100.000 | IP20/44 | IK03 | 5 Years | 1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
		W	lm	lm/W			K			
NEW	1 RC132V G5 31_36_43S/840 PSD W60L60OCELB3	40-28.5	3100-3600-4300	107	Yes	≥80	4000	19	910505102351	01371100
NEW	1 RC132V G5 31_36_43S/840PSD6060OCELB3W4W2	40-28.5	3100-3600-4300	107	Yes	≥80	4000	19	910505102365	01385800
NEW	2 RC132V G5 31_36_43S/940 PSD W30L120 OC	40-28.5	3100-3600-4300	107	Yes	≥90	4000	19	911401844684	95040500
NEW	1 RC132V G5 43S/940 PSD W60L60 OC	40	4300	107	Yes	≥90	4000	19	911401842484	95018400
NEW	1 RC132V G5 48S/840 PSD W60L60 OC	40	4800	120	Yes	≥80	4000	19	911401841684	95010800

CoreLine LED luminaires

CoreLine Panel Non-office compliant

www.philips.com/coreline

L80 /L75 at 100.000

1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	IP rating	IK rating	Warranty	12NC	EOC code
		W	lm	lm/W			K				Years		
NEW	RC132V G5 34S/830 PSU W60L60 NOC	28.5	3400	120	No	≥80	3000	22	IP20/44	IK03	5	911401840584	94999700
NEW	RC132V G5 34S/830 PSU W60L60 NOC W3	28.5	3400	120	No	≥80	3000	22	IP20/44	IK03	5	911401842584	95019100
NEW	RC132V G5 36S/840 PSU W30L120 NOC	28.5	3600	125	No	≥80	4000	22	IP20/44	IK03	5	911401840984	95003000
NEW	RC132V G5 36S/840 PSU W30L120 NOC W3	28.5	3600	125	No	≥80	4000	22	IP20/44	IK03	5	911401842784	95021400
NEW	RC132V G5 36S/840 PSU W60L60 NOC	28.5	3600	125	No	≥80	4000	22	IP20/44	IK03	5	911401840684	95000900
NEW	RC132V G5 36S/840 PSU W60L60 NOC W3	28.5	3600	125	No	≥80	4000	22	IP20/44	IK03	5	911401842684	95020700
NEW	RC133V G5 34S/830 PSU W62L62 NOC	28.5	3400	120	No	≥80	3000	22	IP20/44	IK03	5	911401840784	95001600
NEW	RC133V G5 36S/840 PSU W62L62 NOC	28.5	3600	125	No	≥80	4000	22	IP20/44	IK03	5	911401840884	95002300
	RC133V G4 LED34S/830 PSU W62L62 NOC	29	3400	-	-	-	-	-	-	-	-	911401878380	-
NEW	RC132V G5 36S/840 PSU W30L120 NOC ELB3	34	3600	106	No	≥80	4000	22	IP20/44	IK03	5	910505102355	01375900
NEW	RC132V G5 36S/840 PSU W30L120 NOC ELB3W4	34	3600	106	No	≥80	4000	22	IP20/44	IK03	5	910505102361	01381000
NEW	RC132V G5 36S/840 PSU W60L60 NOC ELB3	34	3600	106	No	≥80	4000	22	IP20/44	IK03	5	910505102353	01373500
NEW	RC132V G5 36S/840 PSU W60L60 NOC ELB3W4	34	3600	106	No	≥80	4000	22	IP20/44	IK03	5	910505102358	01378000
NEW	RC132V G5 31_36_43S/840 PSU W60L60 NOC	34.5-24.5	3100-3600-4300	125	No	≥80	4000	22	IP20/44	IK03	5	911401844184	95035100
NEW	RC132V G5 36S/940 PSU W60L60 NOC	34.5	3600	104	No	≥90	4000	22	IP20/44	IK03	5	911401842084	95014600

CoreLine LED luminaires

CoreLine Panel - Accessory

www.philips.com/coreline



10 /20 PACK

	Product Type	12NC	EOC code
NEW	1 RC132Z G5 SMB W30L120	911401861084	95399499
NEW	2 RC132Z G5 SMB W60L60	911401860884	95397099
NEW	3 RC132Z G5 SMB-PLC	911401861184	95403899
NEW	4 RC132Z G5 SME-3 WH	911401861284	95407699
NEW	4 RC132Z G5 SME-4 WH	911401861384	95408399
NEW	5 RC133Z G5 SMB W62L62	911401860984	95398799

CoreLine LED luminaires

CoreLine Recessed Office compliant www.philips.com/coreline

L70 at 100.000 | IP20/44 | IK03 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
RC136B 28S_34S_40S/830 PSD W30L120 OC	31-22	2800-3400-4000	130	Yes	≥80	3000	19	911401880881	51222100
RC136B 28S_34S_40S/830 PSD W60L60 OC	31	4000	130	Yes	≥80	3000	19	911401880681	51220700
RC136B 28S_34S_40S/830 PSD W60L60 OC W5	31	4000	130	Yes	≥80	3000	19	911401881481	51228300
RC136B 31S_37S_43S/840 PSD W30L120 OC	31-22	3100-3700-4300	140	Yes	≥80	4000	19	911401880981	51223800
RC136B 31S_37S_43S/840 PSD W60L60 OC	31-22	3100-3700-4300	140	Yes	≥80	4000	19	911401880781	51221400
RC136B 31S_37S_43S/840 PSD W60L60 OC W5	31-22	3100-3700-4300	140	Yes	≥80	4000	19	911401881581	51229000
RC136B 31S_37S_43S/840 PSU W60L60 OC	31	4300	140	No	≥80	4000	19	911401880481	51218400
RC136B 31S_37S_43S/840 PSU W60L60 OC W3	31	4300	140	No	≥80	4000	19	911401881281	51226900
RC136B 28S_34S_40S/830 PSD W30L120OCELB3	34	4000	118	Yes	≥80	3000	19	910505101244	97551700
RC136B 31S_37S_43S/840 PSD W30L120OCELB3	34	4300	126	Yes	≥80	4000	19	910505101245	97552400
RC136B 31S_37S_43S/840 PSD W60L60 OCELB3	34	4300	126	Yes	≥80	4000	19	910505101241	97548700
RC136B 31S_37S_43S/840 PSDW60L60OCELB3W5	34	4300	126	Yes	≥80	4000	19	910505101256	97563000
RC136B 31S_37S_43S/840 PSUW60L60OCELB3W3	34-25	3100-3700-4300	126	No	≥80	4000	19	910505101257	97564700

CoreLine LED luminaires

CoreLine Recessed Non-office compliant

www.philips.com/coreline

L70 at 100.000 | IP20/44 | IK03 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
RC136B 28S_34S_40S/830 PSU W60L60 NOC	31-22	2800-3400-4000	130	No	≥80	3000	25	911401880281	51216000
RC136B 28S_34S_40S/830 PSU W60L60 NOC W3	31	4000	130	No	≥80	3000	25	911401881081	51224500
RC136B 31S_37S_43S/840 PSD W60L60 NOC	31	4300	140	Yes	≥80	4000	25	911401880581	51219100
RC136B 31S_37S_43S/840 PSD W60L60 NOC W5	31-22	3100-3700-4300	140	Yes	≥80	4000	25	911401881381	51227600
RC136B 31S_37S_43S/840 PSU W60L60 NOC	31-22	3100-3700-4300	140	No	≥80	4000	25	911401880381	51217700
RC136B 31S_37S_43S/840 PSU W60L60 NOC W3	31	4300	140	No	≥80	4000	25	911401881181	51225200
RC136B 31S_37S_43S/840 PSD W60L60NOCELB3	34	4300	126	Yes	≥80	4000	25	910505101243	97550000
RC136B 31S_37S_43S/840 PSU W60L60NOCELB3	34-25	3100-3700-4300	126	No	≥80	4000	25	910505101242	97549400

CoreLine Recessed - Accessory

www.philips.com/coreline



10 /20 /40 PACK

	Product Type	12NC	EOC code
NEW	1 RC132Z SC	911401892080	36268799
	2 RC132Z SMB W30L120	910930031218	07332299
	3 RC132Z SMB W60L60	910930031018	07330899
	4 RC132Z SMB-PLC	911401892180	36269499
	5 RC132Z SME-4 WH	911401892380	36271799
	3 RC133Z SMB W62L62	910930031118	07331599

CoreLine LED luminaires

CoreLine Surface-mounted Office compliant www.philips.com/coreline



L70 at 100.000 | IP20/44 | IK03 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
SM136V 28S_34S_40S/830 PSD W20L120 OC	31-22	2800-3400-4000	130	Yes	≥80	3000	19	911401882081	51234400
SM136V 28S_34S_40S/830 PSD W20L120 OC W5	31-22	2800-3400-4000	130	Yes	≥80	3000	19	910505101253	97560900
SM136V 28S_34S_40S/830 PSD W20L150 OC	31-22	2800-3400-4000	130	Yes	≥80	3000	19	911401882581	51239900
SM136V 31S_37S_43S/840 PSD W20L120 OC	31-22	3100-3700-4300	140	Yes	≥80	4000	19	911401882181	51235100
SM136V 31S_37S_43S/840 PSD W20L120 OC W5	31-22	3100-3700-4300	140	Yes	≥80	4000	19	910505101250	97557900
SM136V 31S_37S_43S/840 PSD W20L150 OC	31-22	3100-3700-4300	140	Yes	≥80	4000	19	911401882681	51240500
SM136V 31S_37S_43S/840 PSU W20L120 OC	31-22	3100-3700-4300	140	No	≥80	4000	19	911401881881	51232000
SM136V 31S_37S_43S/840 PSU W20L120 OC W3	31-22	3100-3700-4300	140	No	≥80	4000	19	910505101254	97561600
SM136V 31S_37S_43S/840 PSU W20L150 OC	31-22	3100-3700-4300	140	No	≥80	4000	19	911401882481	51238200
SM136V 31S_37S_43S/840 PSD W20L120OCELB3	34-25	3100-3700-4300	126	Yes	≥80	4000	19	910505101247	97554800
SM136V 31S_37S_43S/840 PSD W20L150OCELB3	34-25	3100-3700-4300	126	Yes	≥80	4000	19	910505101248	97555500
SM136V 31S_37S_43S/840PSDW20L120OCELB3W5	34-25	3100-3700-4300	126	Yes	≥80	4000	19	910505101258	97565400
SM136V 31S_37S_43S/840PSUW20L120OCELB3W3	34-25	3100-3700-4300	126	No	≥80	4000	19	910505101259	97566100

CoreLine LED luminaires

CoreLine Surface-mounted Non-office compliant

www.philips.com/coreline



L70 at 100.000 | IP20/44 | IK03 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
SM136V 28S_34S_40S/830 PSU W20L120 NOC	31-22	2800-3400-4000	130	No	≥80	3000	25	911401881681	51230600
SM136V 28S_34S_40S/830 PSU W20L120 NOCW3	31-22	2800-3400-4000	130	No	≥80	3000	25	910505101252	97559300
SM136V 28S_34S_40S/830 PSU W20L150 NOC	31-22	2800-3400-4000	130	No	≥80	3000	25	911401882281	51236800
SM136V 31S_37S_43S/840 PSD W20L120 NOC	31-22	3100-3700-4300	140	Yes	≥80	4000	25	911401881981	51233700
SM136V 31S_37S_43S/840 PSD W20L120 NOCW5	31-22	3100-3700-4300	140	Yes	≥80	4000	25	910505101255	97562300
SM136V 31S_37S_43S/840 PSU W20L120 NOC	31-22	3100-3700-4300	140	No	≥80	4000	25	911401881781	51231300
SM136V 31S_37S_43S/840 PSU W20L120 NOCW3	31-22	3100-3700-4300	140	No	≥80	4000	25	910505101251	97558600
SM136V 31S_37S_43S/840 PSU W20L150 NOC	31-22	3100-3700-4300	140	No	≥80	4000	25	911401882381	51237500
SM136V 31S_37S_43S/840 PSUW20L120NOCELB3	34-25	3100-3700-4300	126	No	≥80	4000	25	910505101246	97553100
SM136V 31S_37S_43S/840 PSUW20L150NOCELB3	34-25	3100-3700-4300	126	No	≥80	4000	25	910505101249	97556200

CoreLine LED luminaires

CoreLine Batten www.philips.com/coreline


IP20 | IK04 | 5 Years | 8 /6 /1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
		W	lm	lm/W			K			
	BN126C LED20S/830 PSU L600	17	2000	120	No	>80	3000	26	911401833684	94875499
	BN126C LED22S/840 PSU L600	17	2200	130	No	>80	4000	26	911401833584	94874799
	BN126C LED23S/830 PSU L1200	18	2300	120	No	>80	3000	26	911401833884	94877899
	BN126C LED25S/840 PSU L1200	18	2500	130	No	>80	4000	26	911401833784	94876199
	BN126C LED32S/830 PSU L1500	25.5	3200	120	No	>80	3000	26	911401834484	94883999
	BN126C LED35S/840 PSU L1500	25.5	3500	130	No	>80	4000	26	911401834384	94882299
	BN126C LED38S/830 PSU L1200	31	3800	120	No	>80	3000	26	911401834084	94879299
	BN126C LED41S/840 PSU L1200	31	4100	130	No	>80	4000	26	911401833984	94878599
	BN126C LED41S/840 PSD L1200	34	4100	121	Yes	>80	4000	26	910505103402	10064000
	BN126C LED41S/840 PSU ELB3 L1200	36	4100	114	No	>80	4000	26	910505103371	10021300
	BN126C LED48S/830 PSU L1500	40	4800	120	No	>80	3000	26	911401834684	94885399
	BN126C LED52S/840 PSU L1500	40	5200	130	No	>80	4000	26	911401834584	94884699
	BN126C LED52S/840 PSD L1500	43	5200	121	Yes	>80	4000	26	910505103403	10065700
	BN126C LED52S/840 PSU ELB3 L1500	44	5200	118	No	>80	4000	26	910505103373	10024400
NEW	BN126C LED25_41_64S/840 PSU L1200	48-19	2500-4100-6400	133	No	>80	4000	28	911401816685	50051899
	BN126C LED60S/830 PSU L1200	49	6000	120	No	>80	3000	26	911401834284	94881599
	BN126C LED60S/830 PSU L1800	49	6000	120	No	>80	3000	26	911401835084	94889199
	BN126C LED64S/840 PSU L1200	49	6400	130	No	>80	4000	26	911401834184	94880899
	BN126C LED64S/840 PSU L1800	49	6400	130	No	>80	4000	26	911401834984	94888499
	BN126C LED64S/840 PSD L1200	54	6400	119	Yes	>80	4000	26	910505103404	10066400
NEW	BN126C LED35_52_80S/840 PSU L1500	59-24.5	3500-5200-8000	136	No	>80	4000	28	911401816885	50053299
	BN126C LED74S/830 PSU L1500	59	7400	120	No	>80	3000	26	911401834884	94887799
	BN126C LED80S/840 PSU L1500	59	8000	130	No	>80	4000	26	911401834784	94886099
	BN126C LED80S/840 PSD L1500	63	8000	127	Yes	>80	4000	26	910505103405	10067100
	BN126C LED80S/840 PSU ELB3 L1500	64	8000	125	No	>80	4000	26	910505103382	10045900
	BN126C LED100S/840 PSU L1800	75	10.000	130	No	>80	4000	26	911401835184	94890799
	BN126C LED94S/830 PSU L1800	75	9400	120	No	>80	3000	26	911401835284	94891499

CoreLine LED luminaires

CoreLine Batten - Accessory

www.philips.com/coreline



IP20 IK04 108 PACK

Product Type	12NC	EOC code
BN126Z SC	911401776802	36574999

CoreLine Downlight Gen5

www.philips.com/coreline



L80 at 50.000 IK02 5 Years 6 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	IP rating	12NC	EOC code
		W	lm	lm/W			K				
NEW	DN142B 10S/830 PSU-E UGR19	9.8	1200	122	No	≥80	3000	19	IP20	911401551232	50303899
NEW	DN142B 10S/830 PSU-E UGR19 IP54	9.8	1200	122	No	≥80	3000	19	IP20/54	911401551332	50302199
NEW	DN142B 10S/830 PSU-E WR	9.8	1200	122	No	≥80	3000	25	IP20	911401551032	50305299
NEW	DN142B 10S/830 PSU-E WR IP54	9.8	1200	122	No	≥80	3000	25	IP20/54	911401551132	50304599
NEW	DN142B 10S/840 PSU-E UGR19	9.8	1200	122	No	≥80	4000	19	IP20	911401551632	50299499
NEW	DN142B 10S/840 PSU-E UGR19 IP54	9.8	1200	122	No	≥80	4000	19	IP20/54	911401551732	50298799
NEW	DN142B 10S/840 PSU-E WR	9.8	1200	122	No	≥80	4000	25	IP20	911401551432	50301499
NEW	DN142B 10S/840 PSU-E WR IP54	9.8	1200	122	No	≥80	4000	25	IP20/54	911401551532	50300799
NEW	DN142B 20S/830 PSU-E UGR19	19.2	2300	120	No	≥80	3000	19	IP20	911401552032	50295699
NEW	DN142B 20S/830 PSU-E UGR19 IP54	19.2	2300	120	No	≥80	3000	19	IP20/54	911401552132	50294999
NEW	DN142B 20S/830 PSU-E WR	19.2	2350	122	No	≥80	3000	25	IP20	911401551832	50297099
NEW	DN142B 20S/830 PSU-E WR IP54	19.2	2350	122	No	≥80	3000	25	IP20/54	911401551932	50296399
NEW	DN142B 20S/840 PSU-E UGR19	19.2	2300	120	No	≥80	4000	19	IP20	911401552432	50291899
NEW	DN142B 20S/840 PSU-E UGR19 IP54	19.2	2300	120	No	≥80	4000	19	IP20/54	911401552532	50290199
NEW	DN142B 20S/840 PSU-E WR	19.2	2350	122	No	≥80	4000	25	IP20	911401552232	50293299
NEW	DN142B 20S/840 PSU-E WR IP54	19.2	2350	122	No	≥80	4000	25	IP20/54	911401552332	50292599

CoreLine LED luminaires


1


2

3

4


5


6

7

L70 at 50.000 | IK | IK02 | 5 Years | 6 /1 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	IP rating	12NC	EOC code
	W	lm	lm/W	°			K				
1 DN140B LED10S/830 PSU C IP54 PI6	9.5	1100	106	120	No	≥80	3000	22	IP20/54	911401633405	32604700
2 DN140B LED10S/830 PSU C PI6	9.5	1100	106	120	No	≥80	3000	22	IP20	911401631805	32588000
3 DN140B LED10S/830 PSU WR IP54 PI6	9.5	1100	115	120	No	≥80	3000	25	IP20/54	911401632605	32596500
4 DN140B LED10S/830 PSU WR PI6	9.5	1100	115	120	No	≥80	3000	25	IP20	911401631005	32580400
1 DN140B LED10S/840 PSU C IP54 PI6	9.5	1100	106	120	No	≥80	4000	22	IP20/54	911401633505	32605400
2 DN140B LED10S/840 PSU C PI6	9.5	1100	106	120	No	≥80	4000	22	IP20	911401631905	32589700
3 DN140B LED10S/840 PSU WR IP54 PI6	9.5	1100	115	120	No	≥80	4000	25	IP20/54	911401632705	32597200
4 DN140B LED10S/840 PSU WR PI6	9.5	1100	115	120	No	≥80	4000	25	IP20	911401631105	32581100
4 DN140B LED10S/830 PSD-E WR	11.5	1100	96	120	Yes	≥80	3000	25	IP20	911401631205	32582800
2 DN140B LED10S/830 PSD-E C	11.5	1100	96	120	Yes	≥80	3000	22	IP20	911401632005	32590300
1 DN140B LED10S/830 PSD-E C IP54	11.5	1100	96	120	Yes	≥80	3000	22	IP20/54	911401633605	32606100
3 DN140B LED10S/830 PSD-E WR IP54	11.5	1100	96	120	Yes	≥80	3000	25	IP20/54	911401632805	32598900
4 DN140B LED10S/840 PSD-E WR	11.5	1100	96	120	Yes	≥80	4000	25	IP20	911401631305	32583500
2 DN140B LED10S/840 PSD-E C	11.5	1100	96	120	Yes	≥80	4000	22	IP20	911401632105	32591000
1 DN140B LED10S/840 PSD-E C IP54	11.5	1100	96	120	Yes	≥80	4000	22	IP20/54	911401633705	32607800
3 DN140B LED10S/840 PSD-E WR IP54	11.5	1100	96	120	Yes	≥80	4000	25	IP20/54	911401632905	32599600
2 DN140B LED10S/830 PSD-E C ELB3	14.5	1100	76	120	Yes	≥80	3000	22	IP20	911401639805	32835500
4 DN140B LED10S/830 PSD-E WR ELB3	14.5	1100	76	120	Yes	≥80	3000	25	IP20	911401639405	32831700
2 DN140B LED10S/840 PSD-E C ELB3	14.5	1100	76	120	Yes	≥80	4000	22	IP20	911401639905	32836200
4 DN140B LED10S/840 PSD-E WR ELB3	14.5	1100	76	120	Yes	≥80	4000	25	IP20	911401639505	32832400
5 DN140B LED20S/830 PSU C IP54 PI6	19	2200	111	120	No	≥80	3000	22	IP20/54	911401633805	32608500
6 DN140B LED20S/830 PSU C PI6	19	2200	111	120	No	≥80	3000	22	IP20	911401632205	32592700
7 DN140B LED20S/830 PSU WR IP54 PI6	19	2200	119	120	No	≥80	3000	25	IP20/54	911401633005	32600900

CoreLine LED luminaires

1


2


3

4

L70 at 50.000 | IK02 | 5 Years | 6 /1 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	IP rating	12NC	EOC code
	W	lm	lm/W	°			K				
1 DN140B LED20S/830 PSU WR PI6	19	2200	119	120	No	≥80	3000	25	IP20	911401631405	32584200
2 DN140B LED20S/840 PSU C IP54 PI6	19	2200	111	120	No	≥80	4000	22	IP20/54	911401633905	32609200
3 DN140B LED20S/840 PSU C PI6	19	2200	111	120	No	≥80	4000	22	IP20	911401632305	32593400
4 DN140B LED20S/840 PSU WR IP54 PI6	19	2200	119	120	No	≥80	4000	25	IP20/54	911401633105	32601600
1 DN140B LED20S/840 PSU WR PI6	19	2200	119	120	No	≥80	4000	25	IP20	911401631505	32585900
1 DN140B LED20S/830 PSD-E WR	20.5	2200	107	120	Yes	≥80	3000	25	IP20	911401631605	32586600
3 DN140B LED20S/830 PSD-E C	20.5	2200	107	120	Yes	≥80	3000	22	IP20	911401632405	32594100
2 DN140B LED20S/830 PSD-E C IP54	20.5	2200	107	120	Yes	≥80	3000	22	IP20/54	911401634005	32610800
4 DN140B LED20S/830 PSD-E WR IP54	20.5	2200	107	120	Yes	≥80	3000	25	IP20/54	911401633205	32602300
1 DN140B LED20S/840 PSD-E WR	20.5	2200	107	120	Yes	≥80	4000	25	IP20	911401631705	32587300
3 DN140B LED20S/840 PSD-E C	20.5	2200	107	120	Yes	≥80	4000	22	IP20	911401632505	32595800
2 DN140B LED20S/840 PSD-E C IP54	20.5	2200	107	120	Yes	≥80	4000	22	IP20/54	911401634105	32611500
4 DN140B LED20S/840 PSD-E WR IP54	20.5	2200	107	120	Yes	≥80	4000	25	IP20/54	911401633305	32603000
3 DN140B LED20S/830 PSD-E C ELB3	23.5	2200	94	120	Yes	≥80	3000	22	IP20	911401640005	32837900
1 DN140B LED20S/830 PSD-E WR ELB3	23.5	2200	94	120	Yes	≥80	3000	25	IP20	911401639605	32833100
3 DN140B LED20S/840 PSD-E C ELB3	23.5	2200	94	120	Yes	≥80	4000	22	IP20	911401640105	32838600
1 DN140B LED20S/840 PSD-E WR ELB3	23.5	2200	94	120	Yes	≥80	4000	25	IP20	911401639705	32834800

CoreLine LED luminaires

70 /L70 at 50.000 | IK02 | 5 Years | 10 /16 PACK

	Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	IP rating	12NC	EOC code
		W	lm	lm/W	°			K				
NEW	DN145B LED6S/830_840 PSU WH	6.5	650	100	-	No	≥80	3000-4000	33	IP20/44	911401816085	50040299
	DN145B LED6S/830 PSU II WH	6.5	650	100	120	No	>80	3000	32	IP20/44	911401805780	33945099
	DN145B LED6S/840 PSU II WH	6.5	650	100	120	No	>80	4000	32	IP20/44	911401805880	33946799
	DN145B LED10S/830 PSU II WH	11	1100	100	120	No	>80	3000	28	IP20/44	911401805980	33947499
	DN145B LED10S/840 PSU II WH	11	1100	100	120	No	>80	4000	28	IP20/44	911401806080	33948199
	DN145C LED10S/830 PSU II WH	11	1100	100	120	No	>80	3000	28	IP44	911401806380	33951199
	DN145C LED10S/840 PSU II WH	11	1100	100	120	No	>80	4000	28	IP44	911401806480	33952899
	DN145B LED10S/830 PSD-E II WH	13	1100	85	120	Yes	>80	3000	28	IP20/44	910500465901	96100899
	DN145B LED10S/840 PSD-E II WH	13	1100	85	120	Yes	>80	4000	28	IP20/44	910500465902	96101599
	DN145B LED20S/830 PSU II WH	21	2100	100	120	No	>80	3000	28	IP20/44	911401806180	33949899
	DN145B LED20S/840 PSU II WH	21	2100	100	120	No	>80	4000	28	IP20/44	911401806280	33950499
	DN145C LED20S/830 PSU II WH	21	2100	100	120	No	>80	3000	28	IP44	911401806580	33953599
	DN145C LED20S/840 PSU II WH	21	2100	100	120	No	>80	4000	28	IP44	911401806680	33954299
	DN145B LED20S/830 PSD-E II WH	22.5	2100	93	120	Yes	>80	3000	28	IP20/44	910500465903	96102299
	DN145B LED20S/840 PSD-E II WH	22.5	2100	93	120	Yes	>80	4000	28	IP20/44	910500465904	96103999

CoreLine LED luminaires



L80 /70 at 50.000

10 /16 /1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	IP rating	IK rating	Warranty	12NC	EOC code
		W	lm	lm/W			K				Years		
NEW	DN142B 10S/830 PSD-E WR	10.4	1000	115	Yes	≥80	3000	25	IP20	IK02	5	910505103586	10887500
NEW	DN142B 10S/830 PSD-E UGR19 IP54	10.4	1000	-	-	-	-	-	-	-	-	910505103589	-
NEW	DN142B 10S/830 PSD-E WR IP54	10.4	1200	115	Yes	≥80	3000	25	IP20/54	IK02	5	910505103587	10888200
NEW	DN142B 10S/840 PSD-E WR	10.4	1200	115	Yes	≥80	4000	25	IP20	IK02	5	910505103590	10891200
NEW	DN142B 10S/840 PSD-E UGR19	10.4	1150	111	Yes	≥80	4000	19	IP20	IK02	5	910505103592	10893600
NEW	DN142B 10S/840 PSD-E UGR19 IP54	10.4	1150	111	Yes	≥80	4000	19	IP20/54	IK02	5	910505103593	10894300
NEW	DN142B 10S/840 PSD-E WR IP54	10.4	1000	115	Yes	≥80	4000	25	IP20/54	IK02	5	910505103591	10892900
NEW	DN145B LED10S/830_840 PSU WH	11	1100	100	No	≥80	3000-4000	27	IP20/44	IK02	5	911401816185	50041999
NEW	DN142B 10S/830 PSD-E UGR19 ELB3	14.9	1150	77	Yes	≥80	3000	19	IP20	IK02	5	910505103604	10904900
NEW	DN142B 10S/830 PSD-E WR ELB3	14.9	1000	80	Yes	≥80	3000	25	IP20	IK02	5	910505103603	10903200
NEW	DN142B 10S/840 PSD-E UGR19 ELB3	14.9	1150	77	Yes	≥80	4000	19	IP20	IK02	5	910505103606	10906300
NEW	DN142B 10S/840 PSD-E WR ELB3	14.9	1000	80	Yes	≥80	4000	25	IP20	IK02	5	910505103605	10905600
NEW	DN142B 20S/830 PSD-E WR IP54	20	2350	118	Yes	≥80	3000	25	IP20/54	IK02	5	910505103595	10896700
NEW	DN142B 20S/840 PSD-E WR	20	2350	118	Yes	≥80	4000	25	IP20	IK02	5	910505103598	10899800
NEW	DN142B 20S/840 PSD-E UGR19	20	2250	113	Yes	≥80	4000	19	IP20	IK02	5	910505103601	10901800
NEW	DN142B 20S/840 PSD-E UGR19 IP54	20	2250	113	Yes	≥80	4000	19	IP20/54	IK02	5	910505103602	10902500
NEW	DN142B 20S/840 PSD-E WR IP54	20	2350	118	Yes	≥80	4000	25	IP20/54	IK02	5	910505103599	10900100
NEW	DN145B LED20S/830_840 PSU WH	21	2100	100	No	≥80	3000-4000	27	IP20/44	IK02	5	911401816285	50042699
NEW	DN142B 20S/830 PSD-E UGR19	22	2000	-	-	-	-	-	-	-	-	910505103596	-
NEW	DN142B 20S/830 PSD-E UGR19 IP54	23	2000	-	-	-	-	-	-	-	-	910505103597	-
NEW	DN142B 20S/830 PSD-E WR ELB3	24.5	2350	96	Yes	≥80	3000	25	IP20	IK02	5	910505103607	10907000
NEW	DN142B 20S/840 PSD-E UGR19 ELB3	24.5	2000	-	-	-	-	-	-	-	-	910505103610	-
NEW	DN142B 20S/840 PSD-E WR ELB3	24.5	2350	96	Yes	≥80	4000	25	IP20	IK02	5	910505103609	10909400

CoreLine LED luminaires

CoreLine Waterproof

www.philips.com/coreline









70 at 100.000 | IP65 | IK08 | 5 Years | 9 /1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	Motion/Daylight sensor	12NC	EOC code
		W	lm	lm/W			K				
NEW	1 WT120C G2 LED19S/840 PSU L600 BN	15	1900	127	No	>80	4000	25	-	911401825885	50215499
	2 WT120C G2 LED18S/840 PSU PCO L600	15	1800	121	No	>80	4000	26	-	911401836980	34976399
	1 WT120C G2 LED19S/840 PSU L600	15	1900	127	No	>80	4000	25	-	911401823480	84045900
	1 WT120C G2 LED19S/840 PSU MDU L600	16.4	1900	116	No	>80	4000	25	No	910505100036	96244900
	1 WT120C G2 LED19S/840 PSD L600	16.5	1900	115	Yes	>80	4000	25	-	910505100038	88306800
	2 WT120C G2 LED25S/840 PSU PCO L1200	20.5	2500	122	No	>80	4000	26	-	911401837080	34977099
	3 WT120C G2 LED27S/840 PSU L1200	20.5	2700	132	No	>80	4000	25	-	911401823580	84046600
NEW	3 WT120C G2 LED27S/840 PSU L1200 BN	21	2700	129	No	>80	4000	25	-	911401826785	50221599
	3 WT120C G2 LED27S/840 PSU TW3 L1200	21.5	2700	126	No	>80	4000	25	-	910505100039	91685800
	3 WT120C G2 LED27S/840 PSD L1200	22	2700	123	Yes	>80	4000	25	-	910505100044	88307500
	3 WT120C G2 LED27S/840 PSU MDU L1200	22	2700	123	No	>80	4000	25	No	910505100040	96248700
	3 WT120C G2 LED27S/840 PSU MDU TW3 L1200	22	2700	123	No	>80	4000	25	No	910505100041	96249400
NEW	4 WT120C G2 LED34S/840 PSU L1500 BN	24	3400	142	No	>80	4000	25	-	911401825985	50216199
	2 WT120C G2 LED31S/840 PSU PCO L1500	24.3	3100	128	No	>80	4000	26	-	911401837180	34978799
	4 WT120C G2 LED34S/840 PSU L1500	24.3	3400	140	No	>80	4000	25	-	911401823680	84047300
	4 WT120C G2 LED34S/865 PSU L1500	24.5	3400	139	No	>80	6500	25	-	911401824481	36934199
	4 WT120C G2 LED34S/840 PSU TW3 L1500	25.5	3400	133	No	>80	4000	25	-	910505100058	91686500
	3 WT120C G2 LED27S/840 PSU ELB3 L1200	26	2700	104	No	>80	4000	25	-	910505100042	85418000
	4 WT120C G2 LED34S/840 PSD L1500	26	3400	131	Yes	>80	4000	25	-	910505100061	88308200
	4 WT120C G2 LED34S/840 PSU MDU L1500	26	3400	131	No	>80	4000	25	No	910505100059	96267800
	4 WT120C G2 LED34S/840 PSU MDU TW3 L1500	26	3400	131	No	>80	4000	25	No	910505100060	96268500
	3 WT120C G2 LED27S/840 PSD ELB3 L1200	27	2700	100	Yes	>80	4000	25	-	910505100045	88311200
	3 WT120C G2 LED37S/830 PSU L1200	28.5	3700	130	No	>80	3000	25	-	911401824681	36936599
	3 WT120C G2 LED40S/865 PSU L1200	28.5	4000	140	No	>80	6500	25	-	911401824381	36933499
	2 WT120C G2 LED37S/840 PSU PCO L1200	28.6	3700	130	No	>80	4000	26	-	911401837280	34979499
	3 WT120C G2 LED40S/840 PSU L1200	28.6	4000	140	No	>80	4000	25	-	911401823780	84048000
NEW	3 WT120C G2 LED40S/840 PSU L1200 BN	29	4000	138	No	>80	4000	25	-	911401826885	50222299
	3 WT120C G2 LED40S/840 PSU WEC L1200	29	4000	138	No	>80	4000	25	-	910505100050	16316700
	3 WT120C G2 LED40S/840 PSU TW1 WEC L1200	29.5	4000	136	No	>80	4000	25	-	910505100051	16317400
	4 WT120C G2 LED34S/840 PSU ELB3 L1500	30	3400	113	No	>80	4000	25	-	910505100062	85420300

CoreLine LED luminaires

CoreLine Waterproof - Continued

www.philips.com/coreline



70 /65 at 100.000 | IP65 | IK08 | 5 Years | 9 /1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	Motion/Daylight sensor	12NC	EOC code
		W	lm	lm/W			K				
	1 WT120C G2 LED40S/840 PSU MDU TW3 L1200	30	4000	133	No	>80	4000	25	No	910505100049	96257900
	1 WT120C G2 LED40S/840 PSU TW3 L1200	30	4000	133	No	>80	4000	25	-	910505100047	91687200
	1 WT120C G2 LED40S/840 PSD L1200	30.5	4000	131	Yes	>80	4000	25	-	910505100053	88309900
	1 WT120C G2 LED40S/840 PSU MDU L1200	30.5	4000	131	No	>80	4000	25	No	910505100048	96256200
	2 WT120C G2 LED34S/840 PSD ELB3 L1500	31	3400	110	Yes	>80	4000	25	-	910505100064	88313600
	2 WT120C G2 LED34S/840 PSU MDU ELB3 L1500	31	3400	110	No	>80	4000	25	No	910505100063	96271500
NEW	3 WT120C G2 LED27_45S/840 PSU L1200	32-18	2700-4500	141	No	>80	4000	25	-	911401814985	50019899
	1 WT120C G2 LED40S/840 PSU ELB3 L1200	33	4000	121	No	>80	4000	25	-	910505100054	85419700
	1 WT120C G2 LED40S/840 PSU MDU ELB3 L1200	35	4000	114	No	>80	4000	25	No	910505100055	96263000
	1 WT120C G2 LED40S/840 PSD ELB3 L1200	35.5	4000	113	Yes	>80	4000	25	-	910505100057	88312900
	4 WT120C G2 LED57S/840 PSU PCO L1500	42.9	5700	133	No	>80	4000	26	-	911401837380	34980099
	2 WT120C G2 LED60S/840 PSU L1500	42.9	6000	140	No	>80	4000	25	-	911401823880	84049700
NEW	5 WT120C G2 LED37_60S/840 PSU L1500	43-25	3700-6000	140	No	>80	4000	25	-	911401815085	50020499
NEW	2 WT120C G2 LED60S/840 PSU L1500 BN	43	6000	140	No	>80	4000	25	-	911401826985	50223999
	2 WT120C G2 LED55S/830 PSU L1500	43	5500	128	No	>80	3000	25	-	911401824781	36937299
	2 WT120C G2 LED60S/865 PSU L1500	43	6000	140	No	>80	6500	25	-	911401824581	36935899
	2 WT120C G2 LED60S/840 PSU TW1 WEC L1500	44	6000	136	No	>80	4000	25	-	910505100070	16319800
	2 WT120C G2 LED60S/840 PSU TW3 L1500	44.5	6000	135	No	>80	4000	25	-	910505100066	91688900
	2 WT120C G2 LED60S/840 PSU WEC L1500	44.5	6000	135	No	>80	4000	25	-	910505100069	16318100
	2 WT120C G2 LED60S/840 PSD L1500	45	6000	133	Yes	>80	4000	25	-	910505100072	88310500
	2 WT120C G2 LED60S/840 PSU MDU L1500	45	6000	133	No	>80	4000	25	No	910505100067	96275300
	2 WT120C G2 LED60S/840 PSU MDU TW3 L1500	45	6000	133	No	>80	4000	25	No	910505100068	96276000
	2 WT120C G2 LED60S/840 PSD ELB3 L1500	49.5	6000	121	Yes	>80	4000	25	-	910505100076	88314300
	2 WT120C G2 LED60S/840 PSU ELB3 L1500	49.5	6000	121	No	>80	4000	25	-	910505100073	85421000
	2 WT120C G2 LED60S/840 PSU MDU ELB3 L1500	50	6000	120	No	>80	4000	25	No	910505100074	96282100
NEW	2 WT120C G2 LED80S/840 PSU L1500 BN	57	8000	140	No	>80	4000	25	-	911401826085	50217899
	4 WT120C G2 LED75S/840 PSU PCO L1500	57.1	7500	131	No	>80	4000	28	-	911401837480	34981799
	2 WT120C G2 LED80S/840 PSU L1500	57.1	8000	140	No	>80	4000	25	-	911401823980	40928900
	2 WT120C G2 LED80S/840 PSU TW3 L1500	60	8000	133	No	>80	4000	25	-	910505100077	40930200
	2 WT120C G2 LED80S/840 PSU MDU L1500	61	8000	131	No	>80	4000	25	No	910505100078	96286900

CoreLine LED luminaires

CoreLine Waterproof - Continued

www.philips.com/coreline



70 at 100.000 | IP65 | IK08 | 5 Years | 9 /1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
WT120C G2 LED80S/840 PSD L1500	62	8000	129	Yes	>80	4000	25	910505100079	40929600
WT120C G2 LED80S/840 PSU L1500 ELB3	63.5	8000	126	No	>80	4000	25	910505100080	40931900

CoreLine tubular waterproof

www.philips.com/coreline



L80 at 50.000 | 5 Years | 6 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	IP rating	IK rating	12NC	EOC code
	W	lm	lm/W			K					
WT210C LED39S/840 PSU TW1 PMMA L1500	28	3900	139	No	>80	4000	26	IP69K	IK06	911401860284	95385799
WT210C LED50S/840 PSU TW1 PC L1200	39	5000	128	No	>80	4000	26	IP68	IK10	911401828084	94737599
WT210C LED50S/840 PSU TW1 PMMA L1200	39	5000	128	No	>80	4000	26	IP69K	IK06	911401827884	94735199
WT210C LED70S/840 PSU TW1 PC L1500	54	7000	130	No	>80	4000	26	IP68	IK10	911401828184	94738299
WT210C LED70S/840 PSU TW1 PMMA L1500	54	7000	130	No	>80	4000	26	IP69K	IK06	911401827984	94736899

CoreLine LED luminaires



100 PACK

Product Type	12NC	EOC code
WT210Z SC	911401867884	95611799
WT210Z SW2	911401867784	95610099

CoreLine LED luminaires

CoreLine Trunking Gen2 www.philips.com/coreline



L75 /L70 at 100.000 | IP20 | IK02 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W	°			K			
LL217X 45S/840 1x PSU WB 5x1.5	28	4500	161	120	No	>80	4000	19	910925868234	61794000
LL212X 53S/840 1x PSD WB 7x1.5 HE	33	5300	161	120	Yes	>80	4000	22	910925867522	10779300
LL212X 53S/840 1x PSD WB 7x1.5	34	5300	156	120	Yes	>80	4000	22	910925867515	10772400
LL217X 80S/840 1x PSD WB 7x1.5 HE	48.5	8000	165	120	Yes	>80	4000	22	910925867560	10817200
LL217X 80S/840 1x PSD WB 7x2.5 HE	48.5	8000	165	120	Yes	>80	4000	22	910925867531	10788500
LL217X 80S/840 1x PSU WB 5x2.5 HE	49	8000	163	120	No	>80	4000	22	910925867533	10790800
LL217X 80S/840 1x PSD O 7x2.5	50	7400	144	120	Yes	>80	4000	28	910925867535	10792200
LL217X 80S/840 1x PSU WB 5x1.5	51	8000	157	120	No	>80	4000	22	910925867537	10794600
LL234X 90S/840 2x PSD WB 7x1.5	55	9000	164	120	Yes	>80	4000	19	910925867561	10818900
LL234X 90S/840 2x PSU WB 5x1.5	56	9000	161	120	No	>80	4000	19	910925868232	61792600
LL217X 120S/840 1x PSD WB 7x1.5 HE	79	12.000	152	120	Yes	>80	4000	22	910925867526	10783000
LL217X 120S/840 1x PSU BV WB HE	80	12.000	150	120	No	>80	4000	22	910925867525	10782300
LL217X 120S/840 1x PSU WB 5x1.5 HE	80	12.000	150	120	No	>80	4000	22	910925867529	10786100
LL234X 160S/840 2x PSD WB 7x1.5 HE	97	16.000	165	120	Yes	>80	4000	22	910925867540	10797700
LL234X 160S/840 2x PSD O 7x2.5	100	15.000	144	120	Yes	>80	4000	28	910925867552	10809700
LL234X 160S/840 2x PSD WB 7x1.5	100	16.000	160	120	Yes	>80	4000	22	910925867553	10810300
LL234X 240S/840 2x PSD WB 7x1.5 HE	158	24.000	152	120	Yes	>80	4000	22	910925867545	10802800
LL234X 240S/840 2x PSU WB 5x1.5 HE	160	24.000	150	120	No	>80	4000	22	910925867548	10805900

CoreLine LED luminaires

CoreLine Trunking Gen2 - Accessory **www.philips.com/coreline**



IP20 IK02 1 PACK

Product Type	12NC	EOC code
LL212X 7x1.5 BC	910925867583	10840000
LL217X 7x1.5 BC	910925867589	10846200
LL234X 7x1.5 BC	910925867595	10852300

CoreLine LED luminaires

CoreLine Highbay Gen5

www.philips.com/coreline



L75 at 100.000 | IP65 | IK08 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
1 BY120P G5 LED105S/840 PSU NB	67	10.500	157	No	>80	4000	22	911401629208	95566000
1 BY120P G5 LED105S/840 PSU WB	67	10.500	157	No	>80	4000	25	911401629308	95567700
1 BY120P G5 LED105S/865 PSU NB	67	10.500	157	No	>80	6500	22	911401630008	95574500
1 BY120P G5 LED105S/865 PSU WB	67	10.500	157	No	>80	6500	25	911401630108	95575200
2 BY121P G5 LED105S/840 PSD NB	72	10.500	146	Yes	>80	4000	22	911401629608	95570700
2 BY121P G5 LED105S/840 PSD WB	72	10.500	146	Yes	>80	4000	25	911401629708	95571400
2 BY121P G5 LED105S/865 PSD NB	72	10.500	146	Yes	>80	6500	22	911401630408	95578300
2 BY121P G5 LED105S/865 PSD WB	72	10.500	146	Yes	>80	6500	25	911401630508	95579000
1 BY120P G5 LED150S/840 PSU NB	95	15.000	158	No	>80	4000	22	911401632208	95596700
1 BY120P G5 LED150S/840 PSU WB	95	15.000	158	No	>80	4000	25	911401632308	95597400
2 BY121P G5 LED150S/840 PSD NB	102	15.000	147	Yes	>80	4000	22	911401632408	95598100
2 BY121P G5 LED150S/840 PSD WB	102	15.000	147	Yes	>80	4000	25	911401632508	95599800
2 BY121P G5 LED200S/840 PSU NB	126	20.000	159	No	>80	4000	22	911401629408	95568400
2 BY121P G5 LED200S/840 PSU WB	126	20.000	159	No	>80	4000	25	911401629508	95569100
2 BY121P G5 LED200S/865 PSU NB	126	20.000	159	No	>80	6500	22	911401630208	95576900
2 BY121P G5 LED200S/865 PSU WB	126	20.000	159	No	>80	6500	25	911401630308	95577600
2 BY121P G5 LED200S/840 PSD NB	134	20.000	149	Yes	>80	4000	22	911401629808	95572100
2 BY121P G5 LED200S/840 PSD WB	134	20.000	149	Yes	>80	4000	25	911401629908	95573800
2 BY121P G5 LED200S/865 PSD NB	134	20.000	149	Yes	>80	6500	22	911401630608	95580600
2 BY121P G5 LED200S/865 PSD WB	134	20.000	149	Yes	>80	6500	25	911401630708	95581300
3 BY122P G5 LED250S/840 PSU NB	157	25.000	159	No	>80	4000	22	911401630808	95582000
3 BY122P G5 LED250S/840 PSU WB	157	25.000	159	No	>80	4000	25	911401630908	95583700
3 BY122P G5 LED250S/865 PSU NB	157	25.000	159	No	>80	6500	22	911401631008	95584400
3 BY122P G5 LED250S/865 PSU WB	157	25.000	159	No	>80	6500	25	911401631108	95585100
3 BY122P G5 LED250S/840 PSD NB	168	25.000	149	Yes	>80	4000	22	911401631208	95586800
3 BY122P G5 LED250S/840 PSD WB	168	25.000	149	Yes	>80	4000	25	911401631308	95587500
3 BY122P G5 LED250S/865 PSD NB	168	25.000	149	Yes	>80	6500	22	911401631408	95588200
3 BY122P G5 LED250S/865 PSD WB	168	25.000	149	Yes	>80	6500	25	911401631508	95589900
3 BY122P G5 LED300S/840 PSU NB	192	30.000	156	No	>80	4000	22	911401632608	95600100
3 BY122P G5 LED300S/840 PSU WB	192	30.000	156	No	>80	4000	25	911401632708	95601800

CoreLine LED luminaires

CoreLine Highbay Gen5 - Continued

www.philips.com/coreline



L75 at 100.000 | IP65 | IK08 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
BY122P G5 LED300S/840 PSD NB	205	30.000	146	Yes	>80	4000	22	911401632808	95602500
BY122P G5 LED300S/840 PSD WB	205	30.000	146	Yes	>80	4000	25	911401632908	95603200

CoreLine Highbay Gen5 - Accessory

www.philips.com/coreline



4 PACK

Product Type	12NC	EOC code
BY121Z G5 BR L200	911401633208	95606399

CoreLine LED luminaires

CoreLine Value Highbay

www.philips.com/coreline



L70 at 50.000 | IP65 | IK06 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
BY100P LED100S/840 PSU WB	77	10.500	136	No	>80	4000	28	911401671107	54298300
BY101P LED200S/840 PSU WB	154	20.500	133	No	>80	4000	30	911401646207	52921200
BY102P LED260S/840 PSU WB	187	25.500	136	No	>80	4000	29	911401646307	52922900

CoreLine Value Highbay - Accessory

www.philips.com/coreline



1



2



3

6 /4 PACK

Product Type	12NC	EOC code
1 BY100Z BR L215	911401676807	54602899
2 BY101Z ALU	911401677107	54583099
3 BY102Z ALU	911401677207	54584799

CoreLine LED luminaires

CoreLine Projector gen2

www.philips.com/coreline



L70 at 50.000 | IP20 | IK03 | 5 Years | 10 PACK

	Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
		W	lm	lm/W	°			K			
NEW	ST151T LED30S/940 MB BK	27	3000	110	25	No	>90	4000	20	911401846682	52856799
NEW	ST151T LED30S/940 MB WH	27	3000	110	25	No	>90	4000	20	911401846882	52858199
NEW	ST151T LED30S/940 WB BK	27	3000	110	38	No	>90	4000	20	911401847082	52860499
NEW	ST151T LED30S/940 WB WH	27	3000	110	38	No	>90	4000	20	911401847282	52862899
NEW	ST151T LED30S/930 MB BK	30	3000	100	25	No	>90	3000	19	911401846582	52855099
NEW	ST151T LED30S/930 MB WH	30	3000	100	25	No	>90	3000	19	911401846782	52857499
NEW	ST151T LED30S/930 WB BK	30	3000	100	38	No	>90	3000	19	911401846982	52859899
NEW	ST151T LED30S/930 WB WH	30	3000	100	38	No	>90	3000	19	911401847182	52861199

CoreLine LED luminaires

IP65 IK10 5 Years 6 /1 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	Motion/Daylight sensor	12NC	EOC code
	W	lm	lm/W	°			K				
WL140V LED12S/830 PSR MDU WH	12	1200	90	120	Yes	>80	3000	22	No	911401851582	53082999
WL140V LED12S/830 PSU WH	12	1275	105	120	No	>80	3000	22	-	911401847382	52871099
WL140V LED12S/840 PSR MDU WH	12	1250	95	120	Yes	>80	4000	22	No	911401851682	53083699
WL140V LED12S/840 PSU WH	12	1350	110	120	No	>80	4000	22	-	911401847482	52872799
WL140V LED12S/830 PSED WH	13.5	1200	88	120	Yes	>80	3000	22	-	910505101534	97848800
WL140V LED12S/840 PSED WH	13.5	1250	92	120	Yes	>80	4000	22	-	910505101535	97849500
WL140V LED12S/830 PSED ELB3 WH	16.5	1200	72	120	Yes	>80	3000	22	-	910505101550	97864800
WL140V LED12S/830 PSR ELB3 MDU WH	16.5	1200	72	120	Yes	>80	3000	22	No	910505101552	97866200
WL140V LED12S/840 PSED ELB3 WH	16.5	1250	75	120	Yes	>80	4000	22	-	910505101551	97865500
WL140V LED12S/840 PSR ELB3 MDU WH	16.5	1250	75	120	Yes	>80	4000	22	No	910505101553	97867900
WL140V LED20S/830 PSU MDU WH	19	1850	95	120	No	>80	3000	24	No	911401847982	52877299
WL140V LED20S/840 PSU MDU WH	19	1950	100	120	No	>80	4000	24	No	911401848082	52878999
WL140V LED20S/830 PSU WH	20	2100	105	120	No	>80	3000	24	-	911401847582	52873499
WL140V LED20S/840 PSU WH	20	2200	110	120	No	>80	4000	24	-	911401847682	52874199
WL140V LED20S/830 PSED WH	22	2100	95	120	Yes	>80	3000	24	-	910505101538	97852500
WL140V LED20S/840 PSED WH	22	2200	100	120	Yes	>80	4000	24	-	910505101539	97853200
WL140V LED20S/830 PSR MDU WH	23	2100	90	120	Yes	>80	3000	24	No	911401851782	53084399
WL140V LED20S/840 PSR MDU WH	23	2200	95	120	Yes	>80	4000	24	No	911401851882	53085099
WL140V LED20S/830 PSED ELB3 WH	25	2100	84	120	Yes	>80	3000	24	-	910505101554	97868600
WL140V LED20S/840 PSED ELB3 WH	25	2200	88	120	Yes	>80	4000	24	-	910505101555	97869300
WL140V LED20S/830 PSR ELB3 MDU WH	28.5	2100	73	120	Yes	>80	3000	24	No	910505101556	97870900
WL140V LED20S/840 PSR ELB3 MDU WH	28.5	2200	77	120	Yes	>80	4000	24	No	910505101557	97871600
WL140V LED34S/830 PSR MDU WH	30	2950	98	120	Yes	>80	3000	25	No	911401851982	53086799
WL140V LED34S/840 PSR MDU WH	30	3100	103	120	Yes	>80	4000	25	No	911401852082	53087499
WL140V LED34S/830 PSU WH	32	3400	105	120	No	>80	3000	25	-	911401847782	52875899
WL140V LED34S/840 PSU WH	32	3550	110	120	No	>80	4000	25	-	911401847882	52876599
WL140V LED12_20S/827_830_840 PSU WH	33-20	1200-2000	100	120	No	>80	2700-3000-4000	24	-	911401848182	52879699
WL140V LED20_34S/827_830_840 PSU WH	33-20	2000-3300	100	120	No	>80	2700-3000-4000	25	-	911401848282	52880299
WL140V LED34S/830 PSED WH	35.5	3350	94	120	Yes	>80	3000	25	-	910505101542	97856300
WL140V LED34S/840 PSED WH	35.5	3400	95	120	Yes	>80	4000	25	-	910505101543	97857000

CoreLine LED luminaires

CoreLine Wall-mounted - Continued

www.philips.com/coreline

80 at 50.000 | IP65 | IK10 | 5 Years | 6 /1 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	Motion/Daylight sensor	12NC	EOC code
	W	lm	lm/W	°			K				
WL140V LED34S/830 PSED ELB3 WH	38.5	3350	87	120	Yes	>80	3000	25	-	910505101558	97872300
WL140V LED34S/830 PSR ELB3 MDU WH	38.5	2900	76	120	Yes	>80	3000	25	No	910505101560	97874700
WL140V LED34S/840 PSED ELB3 WH	38.5	3400	88	120	Yes	>80	4000	25	-	910505101559	97873000
WL140V LED34S/840 PSR ELB3 MDU WH	38.5	3100	80	120	Yes	>80	4000	25	No	910505101561	97875400


Spots

www.philips.com/coreline



Product Type	LED	Lumen Output	12NC	EOC code
	W	lm		
RS140B LED6-32-/827 PSR PI6 ALU	8	650	912401483045	-
RS141B LED6-32-/830 PSR PI6 ALU	8	650	912401483049	-
RS141B LED6-32-/830 PSR PI6 WH	8	650	912401483035	-
RS141B LED6-32-/840 PSR PI6 WH	8	650	912401483036	-
RS142B LED6-32-/827 PSR PI6 WH FR	8	650	912401483119	-

CoreLine LED luminaires



IP20 IK03 18 /6 /12 PACK

Product Type	12NC	EOC code
RS140Z CFRM SQR-ADJUST ALU	912401483135	38458699
RS140Z CFRM SQR-ADJUST WH	912401483134	38456299
RS140Z CFRM SQR-FIX Darklight	912401483161	38508899
RS143Z CFRM GRID 1x1 WH	912401483212	38832499
RS143Z CFRM GRID 1x2 WH	912401483213	38833199
RS143Z CFRM GRID 1x3 WH	912401483214	38834899

CoreLine LED luminaires

CoreLine Recessed Spot gen2

www.philips.com/coreline


1


2


3


4


5


6


7

IK03 | 5 Years | 18 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	IP rating	12NC	EOC code
	W	lm	lm/W	°			K				
1 RS150B LED6-WB-/827 D78 PSR PI6 ALU	7.2	660	90	120	Yes	>80	2700	21	IP20/54	911401824584	94167099
1 RS150B LED6-WB-/830 D78 PSR PI6 ALU	7.2	680	94	120	Yes	>80	3000	21	IP20/54	911401810584	93820599
2 RS150B LED6-WB-/830 D78 PSR PI6 WH	7.2	680	94	120	Yes	>80	3000	21	IP20/54	911401898982	54826899
1 RS150B LED6-WB-/840 D78 PSR PI6 ALU	7.2	720	100	120	Yes	>80	4000	21	IP20/54	911401824484	94166399
2 RS150B LED6-WB-/840 D78 PSR PI6 WH	7.2	720	100	120	Yes	>80	4000	21	IP20/54	911401899082	54827599
3 RS151B LED6-WB-/827 D78 PSR PI6 ALU	7.2	660	90	120	Yes	>80	2700	21	IP20/44	911401897882	54815299
3 RS151B LED6-WB-/830 D78 PSR PI6 ALU	7.2	680	94	120	Yes	>80	3000	21	IP20/44	911401897582	54812199
4 RS151B LED6-WB-/830 D78 PSR PI6 WH	7.2	680	94	120	Yes	>80	3000	21	IP20/44	911401897482	54811499
4 RS151B LED6-WB-/830 D78HALOX PSR PI6 WH	7.2	680	94	120	Yes	>80	3000	21	IP20/44	911401811284	93843499
3 RS151B LED6-WB-/840 D78 PSR PI6 ALU	7.2	720	100	120	Yes	>80	4000	21	IP20/44	911401897782	54814599
4 RS151B LED6-WB-/840 D78 PSR PI6 WH	7.2	720	100	120	Yes	>80	4000	21	IP20/44	911401897682	54813899
5 RS155B LED6-WB-/827 D68 PSR PI6 ALU	7.2	720	100	120	Yes	>80	2700	30	IP20/54	911401824784	94169499
6 RS155B LED6-WB-/840 D68 PSR PI6 ALU	7.2	800	110	120	Yes	>80	4000	30	IP20/54	911401824684	94168799
7 RS155B LED6-WB-/827 D68 PSR PI6 WH	7.2	720	100	120	Yes	>80	2700	30	IP20/54	911401828785	50265999
5 RS155B LED6-WB-/830 D68 PSR PI6 ALU	7.2	750	104	120	Yes	>80	3000	30	IP20/54	911401822484	94098799

CoreLine LED luminaires















IK03 | 5 Years | 18 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	IP rating	12NC	EOC code
	W	lm	lm/W	°			K				
1 RS155B LED6-WB-/830 D68 PSR PI6 WH	7.2	750	104	120	Yes	>80	3000	30	IP20/54	911401822384	94097099
1 RS155B LED6-WB-/840 D68 PSR PI6 WH	7.2	800	110	120	Yes	>80	4000	30	IP20/54	911401822584	94099499
2 RS156B LED6-WB-/827 D68 PSR PI6 ALU	7.2	720	100	120	Yes	>80	2700	30	IP20/44	911401820984	94083399
3 RS156B LED6-WB-/827 D68 PSR PI6 WH	7.2	720	100	120	Yes	>80	2700	30	IP20/44	911401828685	50264299
4 RS156B LED6-WB-/830 D68 PSR PI6 ALU	7.2	750	104	120	Yes	>80	3000	30	IP20/44	911401820684	94080299
3 RS156B LED6-WB-/830 D68 PSR PI6 WH	7.2	750	104	120	Yes	>80	3000	30	IP20/44	911401820584	94079699
3 RS156B LED6-WB-/830 D68HALOX PSR PI6 WH	7.2	750	104	120	Yes	>80	3000	30	IP20/44	911401821084	94084099
4 RS156B LED6-WB-/840 D68 PSR PI6 ALU	7.2	800	110	120	Yes	>80	4000	30	IP20/44	911401820884	94082699
5 RS156B LED6-WB-/840 D68 PSR PI6 WH	7.2	800	110	120	Yes	>80	4000	30	IP20/44	911401820784	94081999
6 RS150B LED9-WB-/830 D78 PSR PI6 ALU	10.2	900	88	120	Yes	>80	3000	22	IP20/54	911401810684	93821299
7 RS150B LED9-WB-/830 D78 PSR PI6 WH	10.2	900	88	120	Yes	>80	3000	22	IP20/54	911401899182	54828299
7 RS150B LED9-WB-/840 D78 PSR PI6 WH	10.2	950	93	120	Yes	>80	4000	22	IP20/54	911401899282	54829999

CoreLine LED luminaires















IK03 | 5 Years | 18 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	IP rating	12NC	EOC code
	W	lm	lm/W	°			K				
1 RS151B LED9-WB-/830 D78 PSR PI6 ALU	10.2	900	88	120	Yes	>80	3000	22	IP20/44	911401898082	54817699
2 RS151B LED9-WB-/830 D78 PSR PI6 WH	10.2	900	88	120	Yes	>80	3000	22	IP20/44	911401897982	54816999
1 RS151B LED9-WB-/840 D78 PSR PI6 ALU	10.2	950	93	120	Yes	>80	4000	22	IP20/44	911401810384	93818299
2 RS151B LED9-WB-/840 D78 PSR PI6 WH	10.2	950	93	120	Yes	>80	4000	22	IP20/44	911401898182	54818399
3 RS155B LED9-WB-/830 D68 PSR PI6 ALU	10.2	1000	98	120	Yes	>80	3000	30	IP20/54	911401822784	94101499
4 RS155B LED9-WB-/830 D68 PSR PI6 WH	10.2	1000	98	120	Yes	>80	3000	30	IP20/54	911401822684	94100799
5 RS155B LED9-WB-/840 D68 PSR PI6 WH	10.2	1080	105	120	Yes	>80	4000	30	IP20/54	911401822884	94102199
6 RS156B LED9-WB-/830 D68 PSR PI6 ALU	10.2	1000	98	120	Yes	>80	3000	30	IP20/44	911401821284	94086499
7 RS156B LED9-WB-/830 D68 PSR PI6 WH	10.2	1000	98	120	Yes	>80	3000	30	IP20/44	911401821184	94085799

CoreLine LED luminaires















IK03 | 5 Years | 18 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	IP rating	12NC	EOC code
	W	lm	lm/W	°			K				
1 RS156B LED9-WB-/840 D68 PSR PI6 ALU	10.2	1080	105	120	Yes	>80	4000	30	IP20/44	911401821484	94088899
2 RS156B LED9-WB-/840 D68 PSR PI6 WH	10.2	1080	105	120	Yes	>80	4000	30	IP20/44	911401821384	94087199
3 RS150B LED12-WB-/830 D78 PSR PI6 ALU	12.3	1280	104	120	Yes	>80	3000	24	IP20/54	911401810784	93822999
4 RS150B LED12-WB-/830 D78 PSR PI6 WH	12.3	1280	104	120	Yes	>80	3000	24	IP20/54	911401899382	54830599
4 RS150B LED12-WB-/840 D78 PSR PI6 WH	12.3	1320	107	120	Yes	>80	4000	24	IP20/54	911401899482	54831299
5 RS151B LED12-WB-/830 D78 PSD PI10 WH	12.3	1280	104	120	Yes	>80	3000	24	IP20/44	911401898782	54824499
5 RS151B LED12-WB-/830 D78 PSR PI6 ALU	12.3	1280	104	120	Yes	>80	3000	24	IP20/44	911401898382	54820699
6 RS151B LED12-WB-/830 D78 PSR PI6 WH	12.3	1280	104	120	Yes	>80	3000	24	IP20/44	911401898282	54819099
6 RS151B LED12-WB-/840 D78 PSD PI10 WH	12.3	1320	107	120	Yes	>80	4000	24	IP20/44	911401898882	54825199
5 RS151B LED12-WB-/840 D78 PSR PI6 ALU	12.3	1320	107	120	Yes	>80	4000	24	IP20/44	911401810484	93819999
6 RS151B LED12-WB-/840 D78 PSR PI6 WH	12.3	1320	107	120	Yes	>80	4000	24	IP20/44	911401898482	54821399
7 RS155B LED12-WB-/830 D68 PSR PI6 ALU	12.3	1300	105	120	Yes	>80	3000	33	IP20/54	911401823084	94104599

CoreLine LED luminaires











- at 75.000 | IK03 | 5 Years | 18 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	IP rating	12NC	EOC code
	W	lm	lm/W	°			K				
1 RS155B LED12-WB-/830 D68 PSR PI6 WH	12.3	1300	105	120	Yes	>80	3000	33	IP20/54	911401822984	94103899
2 RS155B LED12-WB-/840 D68 PSR PI6 WH	12.3	1380	112	120	Yes	>80	4000	33	IP20/54	911401823184	94105299
3 RS156B LED12-WB-/830 D68 PSD PI10 WH	12.3	1300	105	120	Yes	>80	3000	33	IP20/44	911401822184	94095699
4 RS156B LED12-WB-/830 D68 PSR PI6 ALU	12.3	1300	105	120	Yes	>80	3000	33	IP20/44	911401821684	94090199
3 RS156B LED12-WB-/830 D68 PSR PI6 WH	12.3	1300	105	120	Yes	>80	3000	33	IP20/44	911401821584	94089599
3 RS156B LED12-WB-/840 D68 PSD PI10 WH	12.3	1380	112	120	Yes	>80	4000	33	IP20/44	911401822284	94096399
4 RS156B LED12-WB-/840 D68 PSR PI6 ALU	12.3	1380	112	120	Yes	>80	4000	33	IP20/44	911401821884	94092599
5 RS156B LED12-WB-/840 D68 PSR PI6 WH	12.3	1380	112	120	Yes	>80	4000	33	IP20/44	911401821784	94091899

CoreLine LED luminaires



18 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	IP rating	IK rating	Warranty	12NC	EOC code
	W	lm	lm/W	°			K				Years		
RS150Z MODULE LED6-WB-/827 D78 PSR	7.2	660	90	38	Yes	>80	2700	21	IP20/54	IK02	5	911401899582	54832999
RS150Z MODULE LED6-WB-/830 D78 PSR	7.2	680	94	38	Yes	>80	3000	21	IP20/54	IK02	5	911401899682	54833699
RS150Z MODULE LED6-WB-/840 D78 PSR	7.2	720	100	38	Yes	>80	4000	21	IP20/54	IK02	5	911401899782	54834399
RS155Z MODULE LED6-WB-/827 D68 PSR	7.2	720	100	120	Yes	>80	2700	30	IP20/54	IK02	5	911401823284	94106999
RS155Z MODULE LED6-WB-/830 D68 PSR	7.2	750	104	120	Yes	>80	3000	30	IP20/54	IK02	5	911401823384	94107699
RS155Z MODULE LED6-WB-/840 D68 PSR	7.2	800	110	120	Yes	>80	4000	30	IP20/54	IK02	5	911401823484	94108399
RS150Z MODULE LED9-WB-/830 D78 PSR	10.2	900	88	38	Yes	>80	3000	22	IP20/54	IK02	5	911401899882	54835099
RS150Z MODULE LED9-WB-/840 D78 PSR	10.2	950	93	38	Yes	>80	4000	22	IP20/54	IK02	5	911401899982	54836799
RS155Z MODULE LED9-WB-/830 D68 PSR	10.2	1000	98	120	Yes	>80	3000	30	IP20/54	IK02	5	911401823584	94109099
RS155Z MODULE LED9-WB-/840 D68 PSR	10.2	1080	105	120	Yes	>80	4000	30	IP20/54	IK02	5	911401823684	94110699
RS150Z CFRM RND-ADJUST D80 ALU	-	-	-	-	-	-	-	-	-	IK03	-	911401811784	93848999
RS150Z CFRM RND-ADJUST D80 BK	-	-	-	-	-	-	-	-	-	IK03	-	911401811884	93849699
RS150Z CFRM RND-ADJUST D80 WH	-	-	-	-	-	-	-	-	-	IK03	-	911401811684	93847299
RS150Z CFRM RND-ADJUST D80 WH HALOX100	-	-	-	-	-	-	-	-	-	IK03	-	911401812284	93853399
RS150Z CFRM RND-FIX D78 ALU	-	-	-	-	-	-	-	-	-	IK03	-	911401811584	93846599
RS150Z CFRM RND-FIX D78 BK	-	-	-	-	-	-	-	-	-	IK03	-	911401811484	93845899
RS150Z CFRM RND-FIX D78 WH	-	-	-	-	-	-	-	-	-	IK03	-	911401811384	93844199
RS150Z CFRM SQR-ADJUST D80 ALU	-	-	-	-	-	-	-	-	-	IK03	-	911401812084	93851999
RS150Z CFRM SQR-ADJUST D80 WH	-	-	-	-	-	-	-	-	-	IK03	-	911401811984	93850299
RS155Z CFRM RND-ADJUST D70 ALU	-	-	-	-	-	-	-	-	-	IK03	-	911401824184	94115199
RS155Z CFRM RND-ADJUST D70 BK	-	-	-	-	-	-	-	-	-	IK03	-	911401824284	94116899
RS155Z CFRM RND-ADJUST D70 WH	-	-	-	-	-	-	-	-	-	IK03	-	911401824084	94114499
RS155Z CFRM RND-ADJUST D70 WH HALOX100	-	-	-	-	-	-	-	-	-	IK03	-	911401824384	94117599
RS155Z CFRM RND-FIX D68 ALU	-	-	-	-	-	-	-	-	-	IK03	-	911401823984	94113799
RS155Z CFRM RND-FIX D68 BK	-	-	-	-	-	-	-	-	-	IK03	-	911401823884	94112099
RS155Z CFRM RND-FIX D68 WH	-	-	-	-	-	-	-	-	-	IK03	-	911401823784	94111399

CoreLine LED luminaires



L80 at 75.000 | IP66 | IK08 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	12NC	EOC code
	W	lm	lm/W			K		
BVP140 LED360-4S 30K6/740 PSD OFA52 D9	225	30.600	136	Yes	>70	4000	912300024344	87288500
BVP140 LED360-4S 30K6/740 PSU OFA52	225	30.600	136	No	>70	4000	912300024336	87280900
BVP140 LED360-4S 31K3/740 PSD S D9	225	31.320	139	Yes	>70	4000	912300024348	87292200
BVP140 LED360-4S 31K3/740 PSU S	225	31.320	139	No	>70	4000	912300024340	87284700
BVP140 LED360-4S 30K6/730 PSU OFA52	245	30.600	125	No	>70	3000	912300057776	90527900
BVP140 LED360-4S 31K3/730 PSU S	245	31.320	128	No	>70	3000	912300057779	90530900
BVP140 LED420-4S 35K3/740 PSD OFA52 D9	250	35.280	141	Yes	>70	4000	912300024343	87287800
BVP140 LED420-4S 35K3/740 PSU OFA52	250	35.280	141	No	>70	4000	912300024335	87279300
BVP140 LED420-4S 36K1/740 PSD S D9	250	36.120	144	Yes	>70	4000	912300024347	87291500
BVP140 LED420-4S 36K1/740 PSU S	250	36.120	144	No	>70	4000	912300024339	87283000
BVP140 LED420-4S 35K3/730 PSU OFA52	275	35.280	128	No	>70	3000	912300057775	90526200
BVP140 LED420-4S 36K1/730 PSU S	275	36.120	131	No	>70	3000	912300057778	90529300
BVP140 LED450-4S 37K8/730 PSU OFA52	295	37.800	128	No	>70	3000	912300057774	90522400
BVP140 LED450-4S 38K7/730 PSU S	295	38.700	131	No	>70	3000	912300057777	90528600
BVP140 LED480-4S 40K3/740 PSD OFA52 D9	295	40.320	137	Yes	>70	4000	912300024342	87286100
BVP140 LED480-4S 40K3/740 PSU OFA52	295	40.320	137	No	>70	4000	912300024334	87278600
BVP140 LED480-4S 41K3/740 PSD S D9	295	41.280	140	Yes	>70	4000	912300024346	87290800
BVP140 LED480-4S 41K3/740 PSU S	295	41.280	140	No	>70	4000	912300024338	87282300

CoreLine LED luminaires



L80 at 75.000 | IP66 | IK08 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	12NC	EOC code
	W	lm	lm/W			K		
BVP130 LED160-4S/740 PSU OFA52 ALU C1KC3	109	16.000	150	No	70	4000	912300023662	09641000
BVP130 LED160-4S/740 PSU S ALU C1KC3	109	16.000	154	No	70	4000	912300023665	09644100
BVP130 LED160-4S/730 A	114	16.000	142	No	70	3000	912300057770	90520000
BVP130 LED160-4S/730 S	114	16.000	145	No	70	3000	912300057773	90525500
BVP130 LED210-4S/740 PSU OFA52 ALU C1KC3	146	21.000	144	No	70	4000	912300023661	09640300
BVP130 LED210-4S/740 PSU S ALU C1KC3	146	21.000	147	No	70	4000	912300023664	09643400
BVP130 LED210-4S/730 A	153	20.500	135	No	70	3000	912300057769	90516300
BVP130 LED210-4S/730 S	153	20.500	138	No	70	3000	912300057772	90524800
BVP130 LED260-4S/740 PSU OFA52 ALU C1KC3	182	26.000	143	No	70	4000	912300023660	09639700
BVP130 LED260-4S/740 PSU S ALU C1KC3 T35	182	26.000	146	No	70	4000	912300023663	09642700
BVP130 LED260-4S/730 A	191	26.000	133	No	70	3000	912300057768	90517000
BVP130 LED260-4S/730 S	191	26.000	136	No	70	3000	912300057771	90523100

CoreLine LED luminaires

CoreLine tempo medium

www.philips.com/coreline



L80 at 75.000 | IP66 | IK08 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	12NC	EOC code
	W	lm	lm/W			K		
BVP125 LED80-4S/740 PSU OFA52 ALU C1KC3	55	8000	147	No	70	4000	912300024002	45588000
BVP125 LED80-4S/740 PSU S ALU C1KC3	55	8000	150	No	70	4000	912300024004	45590300
BVP125 LED80-4S/730 PSU OFA52 ALU C1KC3	75	8000	135	No	70	3000	912300057765	90518700
BVP125 LED80-4S/730 PSU S ALU C1KC3	75	8000	138	No	70	3000	912300057767	90521700
BVP125 LED120-4S/730 PSU OFA52 ALU C1KC3	86	12.000	139	No	70	3000	912300057764	90515600
BVP125 LED120-4S/730 PSU S ALU C1KC3	86	12.000	142	No	70	3000	912300057766	90519400
BVP125 LED120-4S/740 PSU OFA52 ALU C1KC3	88	12.000	136	No	70	4000	912300024001	45587300
BVP125 LED120-4S/740 PSU S ALU C1KC3	88	12.000	139	No	70	4000	912300024003	45589700

CoreLine tempo small

www.philips.com/coreline



L80 at 75.000 | IP66 | IK08 | 5 Years | 1 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	12NC	EOC code
		W	lm	lm/W			K		
NEW	BVP111 LED49-4S/730 OFA52	31	4263	136	No	70	3000	912300060468	55681200
NEW	BVP111 LED49-4S/730 S	31	4263	136	No	70	3000	912300060470	55735200
NEW	BVP111 LED51-4S/740 OFA52	31	4437	142	No	70	4000	912300060466	55679900
NEW	BVP111 LED51-4S/740 S	31	4437	142	No	70	4000	912300060467	55680500
NEW	BVP111 LED73-4S/740 OFA52	43	6278	145	No	70	4000	912300060469	55682900

CoreLine LED luminaires

CoreLine Malaga LED *

www.philips.com/coreline



L70 at 100.000 | IP65 | IK08 | 5 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	12NC	EOC code
	W	lm	lm/W			K		
BRP101 LED37/740 I DM	29.6	3054	103	No	70	4000	910925865338	99815100
BRP101 LED37/740 II DM	29.6	3054	103	No	70	4000	910925865339	99816800
BRP102 LED55/740 I DM	39	4600	118	No	70	4000	910925865340	99817500
BRP102 LED55/740 II DM	39	4600	118	No	70	4000	910925865341	99818200
BRP102 LED75/740 I DM	56.5	6133	109	No	70	4000	910925865342	99819900
BRP102 LED75/740 II DM	56.5	6133	109	No	70	4000	910925865343	99820500
BRP102 LED110/740 I DM	83	9006	111	No	70	4000	910925865344	99821200
BRP102 LED110/740 II DM	83	9006	111	No	70	4000	910925865345	99822900

*Additionally, the CoreLine malaga LED is available with Warm White LED modules (730) or Dynadimmer. Please contact your Signify representative for ordering options.

Philips Ledinaire

Value

Office



Ledinaire panel



Ledinaire recessed



Ledinaire panel EcoSet



Ledinaire EcoSet sensor, remote and switch



Ledinaire surface-mounted



Ledinaire slim downlight



Ledinaire recessed downlight



Ledinaire ClearAccent



Ledinaire wall-mounted WL060V



Ledinaire wall-mounted WL070V

Industry



Ledinaire batten



Ledinaire waterproof WT060C



Ledinaire waterproof WT065C



Ledinaire highbay

Parking



Ledinaire batten



Ledinaire waterproof WT060C



Ledinaire waterproof WT065C



Ledinaire square wall-mounted

Retail



Ledinaire recessed downlight



Ledinaire slim downlight

Outdoor



Ledinaire floodlight

Real pros count on reliable solutions for daily demands

Philips Ledinaire is the essential range of trusted products for everyday lighting jobs that need good performance

Count on honest, hard-working solutions that deliver what they promise. Get trusted performance and the results you expect with Philips-tested key components. And for a price that's on your side! Philips Ledinaire – the essential range of trusted products for everyday lighting jobs that need good performance.

All-in

Our latest addition to the Ledinaire family, the Ledinaire All-in luminaires offer a MultiLumen and/or Multi ColorTemp feature for maximized installation flexibility on site, be it new installation or maintenance jobs.

Find out more about the range on philips.com/ledinaire

Trusted
What you need and expect is what you get. And that's a promise you can count on every time!

Reliable
Proven Philips quality. Every key component is tested for a maximum of reliability and long-term performance.

Great value
Perfect results don't need to blow the budget. With Ledinaire, you get great value lighting from the leader in LED.

NEW: Philips Ledinaire EcoSet

Small effort. Big savings.

Discover Ledinaire EcoSet for a simple upgrade from regular on-off lighting to an automated solution!



Here's how it works

Ledinaire EcoSet luminaire with integrated wireless controls + External motion and daylight detection sensor = Automated dimming

Your benefits

- **Simple to install and set up:** install just like a regular luminaire
- **Built to last:** the reliable technology and pre-defined settings ensure a robust lighting installation
- **Trusted quality:** you and your customers can rely on the renowned quality of Philips Ledinaire luminaires
- **Great value solution:** revolutionary payback times due to low initial investment and significant annual energy savings

Eco Set Wireless **You can easily recognize the Ledinaire EcoSet products by this icon**

Ledinaire EcoSet for offices



✓ **Lower energy bills** ✓ **Higher comfort** ✓ **Fast payback**

What you'll need



Ledinaire panel EcoSet



Ledinaire office sensor EcoSet



Ledinaire remote EcoSet



Ledinaire wall switch EcoSet (optional)

Coming soon: Philips Ledinaire EcoSet for parking applications!

New: Philips Ledinaire All-in

All you need to pack for your next job

Philips Ledinaire All-in luminaires offer up to 3 color temperatures and up to 2 lumen outputs in a single luminaire. Installation is made easy with our field-proven quick connector. Enjoy greatest convenience and flexibility on-site at the flip of a switch.



Here's how it works

- The lumen output and/or color temperature can be adjusted via an integrated switch.*
- Multi ColorTemp: 2700K/3000K/3500K/4000K/6500K*
- Multi Lumen: 1,100 lm/1,700 lm, 2,900 lm/4,800 lm, 4,100 lm /6,800 lm*



* Depending on product.

Your benefits

- Reduced risk to pick the wrong luminaire. Just change the setting on location.
- Perfect for maintenance: pick the right setting on-site while changing luminaires or adjust after installation to the clients' preferences.
- Enjoy fast installation thanks to quick connectors
- All-in luminaires fulfill our highest standards to give you peace of mind. And happy

Ledinaire panel All-in



Ledinaire slim downlight All-in



Ledinaire ClearAccent All-in



Ledinaire wall-mounted All-in

Ledinaire waterproof All-in



Philips Ledinaire slim downlight

Energy-efficient, professional luminaire for general lighting applications

- Easily adjust color temperature via an integrated switch
- Available color temperature package: 3000K/4000K/6500K
- Different sizes: Round D150 mm and D200 mm
- IP44 front & Direct IC
- Easy quick connector

Click here to see all products



Philips Ledinaire ClearAccent

Reliable lighting performance with precise design

- Easily adjust color temperature via an integrated switch
- Available color temperature package: 2700K/3000K/4000K
- IP65 front & Direct IC
- Easy quick connector loop-in loop-out and plug-in quick connector

Click here to see all products



Ledinaire LED luminaires

Easily make the switch to LED lighting without high investments. The Philips Ledinaire portfolio consists of 9 popular LED luminaires. Choose affordable, reliable and energy-efficient lighting from the leading name in LED.

Ledinaire Panel Office compliant

www.lighting.philips.com/main/products/ledinaire

L70 at 75.000 | IP20 | IK02 | 3 Years | 4 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
		W	lm	lm/W			K			
NEW	RC065B LED34S/830 PSU W60L60 OC	34	3400	100	No	≥80	3000	19	911401850782	53065299
NEW	RC065B LED34S/840 PSD W60L60 OC	34	3400	100	Yes	≥80	4000	19	911401850682	53064599
NEW	RC065B LED34S/840 PSU W60L60 OC	34	3400	100	No	≥80	4000	19	911401884580	38647499
NEW	RC065B LED34S/840 PSU W60L60 OC 2	34	3400	100	No	≥80	4000	19	911401819584	94043799
NEW	RC065B LED34S/865 PSU W60L60 OC	34	3400	100	No	≥80	6500	19	911401884680	36204599
NEW	RC066B LED34S/830 PSU W62L62 OC	34	3400	100	No	≥80	3000	19	911401810184	93814499
NEW	RC066B LED34S/840 PSD W62L62 OC	34	3400	100	Yes	≥80	4000	19	911401810284	93815199
NEW	RC066B LED34S/840 PSU W62L62 OC	34	3400	100	No	≥80	4000	19	911401884780	36558999

Ledinaire Panel Non-office compliant

www.lighting.philips.com/main/products/ledinaire


L70 at 75.000 | IP20 | IK02 | 3 Years | 4 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
		W	lm	lm/W			K			
NEW	RC065B LED34S/830 PSU W60L60 NOC	34	3400	100	No	≥80	3000	22	911401850882	53066999
NEW	RC065B LED34S/840 PSU W60L60 NOC	34	3400	100	No	≥80	4000	22	911401885080	79180399
NEW	RC065B LED34S/840 PSU W60L60 NOC 2	34	3400	100	No	≥80	4000	22	911401819684	94044499
NEW	RC065B LED34S/865 PSU W60L60 NOC	34	3400	100	No	≥80	6500	22	911401885180	36206999
NEW	RC065B LED41S/840 PSU W60L60 NOC	44	4100	93	No	≥80	4000	22	911401823781	36926699

Ledinaire LED luminaires

Ledinaire Panel - Accessory

www.lighting.philips.com/main/products/ledinaire



10 /20 /40 PACK

Product Type	IP rating	IK rating	12NC	EOC code
1 RC065Z SC	IP20	IK02	911401892680	36274899
2 RC065Z SMB W60L60	IP20	IK02	911401892480	36272499
3 RC065Z SME-3 WH	-	-	911401805681	36592399
2 RC066Z SMB W62L62	IP20	IK02	911401892580	36273199

Ledinaire Recessed Non-office compliant

www.lighting.philips.com/main/products/ledinaire

L65 at 75.000 | IP20 | IK03 | 3 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W	°			K			
RC060B LED34S/840 PSU W60L60 NOC	34	3400	100	110	No	≥80	4000	25	911401850780	06958500
RC060B LED40S/840 PSU W60L60 NOC	40	4000	100	110	No	≥80	4000	25	911401842380	35040000

Ledinaire LED luminaires

Ledinaire Surface-mounted Office compliant

www.lighting.philips.com/main/products/ledinaire

L65 at 75.000 | IP20 | IK03 | 3 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W	°			K			
SM060C LED34S/840 PSU W20L120 OC	34	3400	100	80	No	≥80	4000	19	911401842280	35039400

Ledinaire Surface-mounted Non-office compliant

www.lighting.philips.com/main/products/ledinaire

L65 at 75.000 | IP20 | IK03 | 3 Years | 1 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W	°			K			
SM060C LED34S/840 PSU W20L120 NOC	34	3400	100	110	No	≥80	4000	25	911401850680	06962200
SM060C LED40S/840 PSU W20L120 NOC	40	4000	100	110	No	≥80	4000	25	911401842480	35041700

Ledinaire LED luminaires

Ledinaire Wall-mounted WL060V

www.lighting.philips.com/main/products/ledinaire



- at 75.000 | IP44 | IK03 | 3 Years | 5 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	Motion/Daylight sensor	12NC	EOC code
	W	lm	lm/W			K				
WL060V LED11S/830 PSU II WH	11	1100	100	No	>80	3000	22	-	911401887384	96009199
WL060V LED11S/840 PSU II WH	11	1100	100	No	>80	4000	22	-	911401887484	96010799
WL060V LED17S/830 PSU II WH	17	1700	100	No	>80	3000	22	-	911401887584	96011499
WL060V LED17S/840 PSU II WH	17	1700	100	No	>80	4000	22	-	911401887684	96012199
WL060V LED17S/830 PSU MDU II WH	19	1700	90	No	>80	3000	22	No	911401883284	95990399
WL060V LED17S/840 PSU MDU II WH	19	1700	90	No	>80	4000	22	No	911401883384	95991099

Ledinaire Wall-mounted WL070V

www.lighting.philips.com/main/products/ledinaire



IP65 | IK08 | 6 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	Motion/Daylight sensor	Warranty	12NC	EOC code
	W	lm	lm/W	°			K			Years		
NEW WL070V LED11_17S/830_835_840	11-17	1100-1700	100	-	No	≥80	3000-3500-4000	-	-	5	911401833985	50824899
WL070V LED11S/830 PSU II WH	11	1100	95	120	No	>80	3000	25	-	3	911401826382	52266499
WL070V LED11S/840 PSU II WH	11	1100	100	120	No	>80	4000	25	-	3	911401826482	52267199
WL070V LED17S/830 PSU II WH	17	1700	95	120	No	>80	3000	25	-	3	911401826582	52268899
WL070V LED17S/840 PSU II WH	17	1700	100	120	No	>80	4000	25	-	3	911401826682	52269599
WL070V LED17S/830 PSU MDU II WH	19	1700	85	120	No	>80	3000	25	No	3	911401826782	52270199
WL070V LED17S/840 PSU MDU II WH	19	1700	85	120	No	>80	4000	25	No	3	911401826882	52271899

Ledinaire LED luminaires

Ledinaire Square Wall-mounted

www.lighting.philips.com/main/products/ledinaire



L65 at 50.000 | IP65 | IK08 | 3 Years | 12 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	Motion/Daylight sensor	12NC	EOC code
	W	lm	lm/W	°			K				
WL055V LED6S/830 PSR MDU WH	6	600	100	110	Yes	>80	3000	25	No	911401862580	35409599
WL055V LED6S/830 PSU WH	6	600	100	110	No	>80	3000	25	-	911401834880	34941199
WL055V LED6S/840 PSR MDU WH	6	630	105	110	Yes	>80	4000	25	No	911401850580	35064699
WL055V LED6S/840 PSU WH	6	630	105	110	No	>80	4000	25	-	911401834980	34942899
WL055V LED6S/830 PSU EL3 WH	8	600	75	110	No	>80	3000	22	-	910505100602	96774199
WL055V LED6S/840 PSU EL3 WH	8	630	79	110	No	>80	4000	22	-	910505100601	96773499

Ledinaire Batten

www.lighting.philips.com/main/products/ledinaire



L65 at 50.000 | IP20 | IK02 | 3 Years | 40 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
BN021C LED5S/830 L300	5	480	96	No	>80	3000	27	911401841882	52785099
BN021C LED5S/840 L300	5	540	108	No	>80	4000	27	911401841782	52784399
BN021C LED10S/830 L600	10	960	96	No	>80	3000	27	911401842082	52787499
BN021C LED10S/840 L600	10	1050	105	No	>80	4000	27	911401841982	52786799
BN021C LED14S/830 L900	15	1450	96.7	No	>80	3000	27	911401842282	52789899
BN021C LED15S/840 L900	15	1600	106.7	No	>80	4000	27	911401842182	52788199
BN021C LED19S/830 L1200	20	1900	95	No	>80	3000	27	911401842482	52791199
BN021C LED20S/840 L1200	20	2100	105	No	>80	4000	27	911401842382	52790499
BN021C LED24S/830 L1500	24	2400	100	No	>80	3000	27	911401842682	52793599
BN021C LED25S/840 L1500	24	2600	108.3	No	>80	4000	27	911401842582	52792899

Ledinaire LED luminaires

Ledinaire Batten - Accessory

www.lighting.philips.com/main/products/ledinaire



IP20 IK02 10 PACK

Product Type	12NC	EOC code
BN021Z C600	911401846482	52854399

Ledinaire High-bay

www.lighting.philips.com/main/products/ledinaire



L70 at 50.000 IP65 IK06 3 Years 1 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W			K			
BY020P G2 LED105S/840 PSU WB GR	94	10.500	112	No	>80	4000	Not applicable	911401642407	52405700
BY021P G2 LED205S/840 PSU WB GR	168	20.500	122	No	>80	4000	Not applicable	911401642307	52404000


Ledinaire LED luminaires

Ledinaire High-bay - Accessory

www.lighting.philips.com/main/products/ledinaire



1



2

4 PACK

Product Type	12NC	EOC code
1 BY020Z G2 ALU	911401657907	53017199
2 BY021Z G2 ALU	911401658007	53016499

Ledinaire Waterproof

www.lighting.philips.com/main/products/ledinaire



70 at 75.000 | IP66 | IK08 | 3 Years | 12 PACK

Product Type	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
	W	lm	lm/W	°			K			
WT060C LED18S/840 PSU L600 BN	15	1800	120	120	No	>80	4000	26	911401876480	36007299
WT060C LED25S/840 PSU L1200 BN	20	2500	120	120	No	>80	4000	26	911401892780	36291599
WT060C LED25S/840 PSU TW1 L1200 BN	20	2500	120	120	No	>80	4000	26	911401892880	36292299
WT060C LED34S/840 PSU L1500 BN	28	3400	120	120	No	>80	4000	26	911401892980	36293999
WT060C LED34S/840 PSU TW1 L1500 BN	28	3400	120	120	No	>80	4000	26	911401893080	36294699
WT060C LED36S/840 PSU L1200 BN	30	3600	120	120	No	>80	4000	26	911401876680	36009699
WT060C LED36S/840 PSU TW1 L1200 BN	30	3600	120	120	No	>80	4000	26	911401876780	36010299
WT060C LED36S/865 PSU L1200 BN	30	3600	120	120	No	>80	6500	26	911401877280	36015799
WT060C LED56S/840 PSU L1500 BN	46	5600	120	120	No	>80	4000	26	911401876880	36011999
WT060C LED56S/840 PSU TW1 L1500 BN	46	5600	120	120	No	>80	4000	26	911401876980	36012699
WT060C LED56S/865 PSU L1500	46	5600	120	120	No	>80	6500	26	911401877480	36017199

Ledinaire LED luminaires

Ledinaire Waterproof WT065C

www.lighting.philips.com/main/products/ledinaire



L70 at 75.000 | IP65 | IK08 | 3 Years | 9 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
		W	lm	lm/W			K			
NEW	WT065C LED29_48S/840 PSU L1200	42-23	2900-4800	114	No	>80	4000	31	911401815185	50021199
NEW	WT065C LED29_48S/840 PSU L1200 TW1	42-23	2900-4800	114	No	>80	4000	31	911401815385	50023599
NEW	WT065C LED41_68S/840 PSU L1500	53-30	4100-6800	128	No	>80	4000	31	911401815285	50022899
NEW	WT065C LED41_68S/840 PSU L1500 TW1	53-30	4100-6800	128	No	>80	4000	31	911401815485	50024299

Ledinaire Waterproof Tube Housing

www.lighting.philips.com/main/products/ledinaire



IP65 | IK08 | 9 / 12 PACK

Product Type	CRI	12NC	EOC code
WT050C 1xTLED L1200	-	911401807381	36602999
WT050C 1xTLED L1500	-	911401807581	36604399
WT050C 2xTLED L1200	-	911401807481	36603699
WT050C 2xTLED L1500	-	911401807681	36605099

Ledinaire LED luminaires



L65 at 50.000 | 12 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	IP rating	IK rating	Warranty	12NC	EOC code
		W	lm	lm/W			K				Years		
NEW	DN065B G4 LED12/830 12W 220-240V D150 RD	12	1200	100	No	80	3000	28	IP20/44	IK03	3	929003250532	46427800
NEW	DN065B G4 LED12/830 12W 220-240V L150 SQ	12	1200	100	No	80	3000	28	IP20/40	IK03	3	929003251132	46439100
NEW	DN065B G4 LED12/830_840_865 12W D150 RD	12	1200	100	No	80	2700-3000-4000	28	IP20/44	IK03	3	929003251332	46443800
NEW	DN065B G4 LED12/840 12W 220-240V D150 RD	12	1200	100	No	80	4000	28	IP20/40	IK03	3	929003250632	46429200
NEW	DN065B G4 LED12/840 12W 220-240V L150 SQ	12	1200	100	No	80	4000	28	IP20/40	IK03	3	929003251232	46441400
NEW	DN065C G4 LED12/830 12W 220-240V 6-D175	12	1200	100	No	80	3000	28	IP20/40	IK03	3	929003251532	46447600
NEW	DN065C G4 LED12/840 12W 220-240V 6-D175	12	1200	108	No	80	4000	28	IP20/40	IK03	3	929003251632	46449000
NEW	DN065B G4 LED20/830 19W 220-240V D200 RD	19	2000	105	No	80	3000	28	IP20/40	IK03	3	929003250832	46433900
NEW	DN065B G4 LED20/830_840_865 19W D200 RD	19	2000	105	No	80	2700-3000-4000	28	IP20/44	IK03	3	929003251432	46445200
NEW	DN065B G4 LED20/840 19W 220-240V D200 RD	19	2000	105	No	80	4000	28	IP20/40	IK03	3	929003250932	46435300
NEW	DN065C G4 LED20/830 19W 220-240V 8-D225	19	2000	105	No	80	3000	28	IP20/40	IK03	3	929003251732	46451300
NEW	DN065C G4 LED20/840 19W 220-240V 8-D225	19	2000	105	No	80	4000	28	IP20/40	IK03	3	929003251832	46453700
NEW	DN065B G4 Trim Accessory D150 BK	-	-	-	-	-	-	-	-	-	-	929003311602	18563000
NEW	DN065B G4 Trim Accessory D150 SI	-	-	-	-	-	-	-	-	-	-	929003313002	19011500
NEW	DN065B G4 Trim Accessory D200 BK	-	-	-	-	-	-	-	-	-	-	929003311702	18565400
NEW	DN065B G4 Trim Accessory D200 SI	-	-	-	-	-	-	-	-	-	-	929003313102	19013900

Ledinaire LED luminaires

Ledinaire Recessed Downlight

www.lighting.philips.com/main/products/ledinaire



L65 at 50.000 | IP20/54 | IK03 | 3 Years | 8 / 12 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	12NC	EOC code
		W	lm	lm/W			K			
NEW	DN070B LED12/840 12W 220-240V D150 RD EU	12	1200	96	No	80	4000	19	929003165432	35400500
	DN070B LED12/830 12W 220-240V D150 RD EU	12	1200	96	No	80	3000	19	929003165332	35398500
NEW	DN070B LED24/830 24W 220-240V D200 RD EU	24	2400	94	No	80	3000	19	929003165532	35402900
NEW	DN070B LED24/840 24W 220-240V D200 RD EU	24	2400	94	No	80	4000	19	929003165632	35404300

Ledinaire ClearAccent RS060/RS061

www.lighting.philips.com/main/products/ledinaire



L65 at 50.000 | 12 PACK

	Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	UGR	IP rating	IK rating	Warranty	12NC	EOC code
		W	lm	lm/W			K				Years		
NEW	RS071B 5S/827_30_40 40D PSR PI6 IP65 BK	6	550	91	Yes	80	2700-3000-4000	21	IP20(IP65	IK03	3	929003322602	20884100
NEW	RS071B 5S/827_30_40 40D PSR PI6 IP65 WH	6	550	91	Yes	80	2700-3000-4000	21	IP20(IP65	IK03	3	929003322502	20882700
NEW	RS071B 5S/827_30_40 60D PSR PI6 IP65 WH	6	550	91	Yes	80	2700-3000-4000	23	IP20(IP65	IK03	3	929003322702	20886500
	RS071B 5S/827_30_40 60D PSR PI6 IP65 BK	6	550	91	Yes	80	2700-3000-4000	23	IP20(IP65	IK03	3	929003322802	20888900
	RS071B Trim Accessory GD	-	-	-	-	-	-	-	-	-	-	929003322902	20890200
	RS071B Trim Accessory SI	-	-	-	-	-	-	-	-	-	-	929003323002	20892600

Ledinaire LED luminaires

Ledinaire floodlights gen3

www.lighting.philips.com/main/products/ledinaire



80 /75 at 50.000 | IP65 | 3 Years | 10 /6 /16 /4 /24 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	IK rating	Motion/Daylight sensor	12NC	EOC code
	W	lm	lm/W			K				
1 BVP164 LED11/830 PSU 10W SWB CE	10	1100	110	No	>80	3000	IK07	-	911401841483	53364699
2 BVP164 LED11/830 PSU 10W SWB MDU CE	10	1100	110	No	>80	3000	IK07	No	911401883683	53482799
1 BVP164 LED12/840 PSU 10W SWB CE	10	1200	120	No	>80	4000	IK07	-	911401851483	53356199
2 BVP164 LED12/840 PSU 10W SWB MDU CE	10	1200	120	No	>80	4000	IK07	No	911401883783	53481099
1 BVP164 LED12/865 PSU 10W SWB CE	10	1200	120	No	>80	6500	IK07	-	911401861483	53348699
3 BVP164 LED22/830 PSU 20W SWB CE	20	2200	110	No	>80	3000	IK07	-	911401842483	53363999
4 BVP164 LED22/830 PSU 20W SWB MDU CE	20	2200	110	No	>80	3000	IK07	No	911401883983	53480399
3 BVP164 LED24/840 PSU 20W SWB CE	20	2400	120	No	>80	4000	IK07	-	911401852483	53355499
4 BVP164 LED24/840 PSU 20W SWB MDU CE	20	2400	120	No	>80	4000	IK07	No	911401884083	53479799
3 BVP164 LED24/865 PSU 20W SWB CE	20	2400	120	No	>80	6500	IK07	-	911401862483	53347999
3 BVP164 LED33/830 PSU 30W SWB CE	30	3300	110	No	>80	3000	IK07	-	911401843483	53362299
4 BVP164 LED33/830 PSU 30W SWB MDU CE	30	3300	110	No	>80	3000	IK07	No	911401884283	53478099
3 BVP164 LED36/840 PSU 30W SWB CE	30	3600	120	No	>80	4000	IK07	-	911401853483	53354799
4 BVP164 LED36/840 PSU 30W SWB MDU CE	30	3600	120	No	>80	4000	IK07	No	911401884383	53477399
3 BVP164 LED36/865 PSU 30W SWB CE	30	3600	120	No	>80	6500	IK07	-	911401863483	53346299
5 BVP164 LED55/830 PSU 50W SWB CE	50	5500	110	No	>80	3000	IK07	-	911401844483	53361599
4 BVP164 LED55/830 PSU 50W SWB MDU CE	50	5500	110	No	>80	3000	IK07	No	911401884583	53476699
5 BVP164 LED60/840 PSU 50W SWB CE	50	6000	120	No	>80	4000	IK07	-	911401854483	53353099
4 BVP164 LED60/840 PSU 50W SWB MDU CE	50	6000	120	No	>80	4000	IK07	No	911401884683	53475999
5 BVP164 LED60/865 PSU 50W SWB CE	50	6000	120	No	>80	6500	IK07	-	911401864483	53345599
6 BVP164 LED70/830 PSU 70W AWB CE	70	7000	100	No	>80	3000	IK08	-	911401896083	53633399
6 BVP164 LED73/840 PSU 70W AWB CE	70	7350	105	No	>80	4000	IK08	-	911401896183	53496499
5 BVP164 LED77/830 PSU 70W SWB CE	70	7700	110	No	>80	3000	IK08	-	911401845483	53360899
4 BVP164 LED77/830 PSU 70W SWB MDU CE	70	7700	110	No	>80	3000	IK08	No	911401884883	53474299
5 BVP164 LED84/840 PSU 70W SWB CE	70	8400	120	No	>80	4000	IK08	-	911401855483	53352399

Ledinaire LED luminaires



80 /75 at 50.000 | IP65 | IK08 | 10 /6 /16 /4 /24 PACK

Product Type	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	Motion/Daylight sensor	Warranty	12NC	EOC code
	W	lm	lm/W			K		Years		
1 BVP164 LED84/840 PSU 70W SWB MDU CE	70	8400	120	No	>80	4000	No	3	911401884983	53473599
2 BVP164 LED84/865 PSU 70W SWB CE	70	8400	120	No	>80	6500	-	3	911401865483	53344899
3 BVP165 LED100/830 PSU 100W AWB CE	100	10.000	100	No	>80	3000	-	3	911401896383	53632699
3 BVP165 LED105/840 PSU 100W AWB CE	100	10.500	105	No	>80	4000	-	3	911401896483	53495799
4 BVP165 LED110/830 PSU 100W SWB CE	100	11.000	110	No	>80	3000	-	5	911401846483	53359299
4 BVP165 LED120/840 PSU 100W SWB CE	100	12.000	120	No	>80	4000	-	3	911401856483	53351699
4 BVP165 LED120/865 PSU 100W SWB CE	100	12.000	120	No	>80	6500	-	3	911401866483	53343199
3 BVP165 LED150/830 PSU 150W AWB CE	150	15.000	100	No	>80	3000	-	3	911401896683	53631999
3 BVP165 LED157/840 PSU 150W AWB CE	150	15.750	105	No	>80	4000	-	3	911401896783	53494099
4 BVP165 LED165/830 PSU 150W SWB CE	150	16.500	110	No	>80	3000	-	5	911401847483	53358599
4 BVP165 LED180/840 PSU 150W SWB CE	150	18.000	120	No	>80	4000	-	3	911401857483	53350999
4 BVP165 LED180/865 PSU 150W SWB CE	150	18.000	120	No	>80	6500	-	3	911401867483	53342499
3 BVP165 LED200/830 PSU 200W AWB CE	200	20.000	100	No	>80	3000	-	3	911401896983	53630299
3 BVP165 LED210/840 PSU 200W AWB CE	200	21.000	105	No	>80	4000	-	3	911401897083	53493399
4 BVP165 LED220/830 PSU 200W SWB CE	200	22.000	110	No	>80	3000	-	5	911401848483	53357899
4 BVP165 LED240/840 PSU 200W SWB CE	200	24.000	120	No	>80	4000	-	3	911401858483	53349399
4 BVP165 LED240/865 PSU 200W SWB CE	200	24.000	120	No	>80	6500	-	3	911401868483	53341799

Real pros put
LED lamps in the spotlight

From hotels to meeting rooms, from LED spots to decorative LED bulbs – the wide range of Philips LED lamps offers a lighting solution for every style and function.



Creating the perfect ambience for any room and any occasion has never been easier. Philips LED lamps combine classic design with superior technology designed to offer exceptional light quality and high color consistency.

Our innovative features, like DimTone and SceneSwitch, offer the flexibility to go from functional lighting to an inviting and cosy atmosphere with the simple flick of a switch.

Choose CorePro LEDlamps for everyday replacement of conventional lighting in general applications. The MASTER Value range offers a broad selection of dimmable, high-performance LED lamps. With customized spectrum, high CRI, and deep dimming features, the MASTER range delivers superior light and the perfect ambience. MasterConnect LEDspots are Interact Ready and can be integrated into smart lighting systems for personal and automated light control.

Find out more about the range on philips.com/ledlamps

Fast and easy replacements
Philips LED lamps are designed as a 1-on-1 replacement for currently installed conventional lighting

High quality of light
- No flickering
- True constant colors with high CRI
- Maximum dimming compatibility

Energy efficiency and long lifetimes
- 69% more energy-efficient than conventional lamps
- Up to 50,000 hours lifetime (at L70) — for peace of mind and lower maintenance cost

Wide range
The right shape and technology for every kind of application and budget

Philips MasterConnect LEDspots

Take the first step into connected lighting with Philips MasterConnect LEDspots

MasterConnect LEDspots are smart retrofit LED spots that give you an easy and seamless way to upgrade and embrace all the benefits of connected lighting.

Thanks to the proven wireless connected technology, MasterConnect LEDspots maximize energy savings, while providing wireless and automated light for your comfort and convenience.

Works with Interact and Philips MasterConnect apps



- Perfect fit design to retrofit halogen lamps
- 90% energy savings compared with halogen lamps
- Color spectrum that replicates halogen, CRI 90
- Lifetime of up to 25,000 hrs (at L70)
- Perfect for hospitality, restaurant and retail

interact ready.

Find out more about MasterConnect LEDlamps on **philips.com/masterconnect**



Add switches for wireless lighting



Add sensors for automated lighting



Add a gateway for connected lighting

Real pros upgrade to ultra-efficiency

Introducing the first dimmable Philips A-class LED bulb: your choice for next-level savings and sustainability

- Saves 50% energy compared to a standard LED bulb[1]
- Ultra long lifetime of 50,000 hrs (at L70)
- Ultra-efficient with up to 210 lm/W
- Available in full range, from 40W to 100W replacement



New: The first A-class rating[2] dimmable LED bulb

Click here to discover our Ultra Efficient solutions



[1] This calculation compares the Philips MASTER LEDbulb UE with Philips CorePro LEDbulb A60 60W
[2] According to the updated European Energy Labelling regulation (09/2021)

Real pros help

customers realize ultra energy savings


Introducing the Philips MASTER Ultra Efficient range – our most energy-efficient LED lamps yet



Save at least 43% in energy costs[1]

New!

Our Ultra Efficient Light



Did you know there is great potential to save energy, even if you already have LED lights?


Are your customers worried about their energy costs?

With energy costs going through the roof, many companies are more aware of their energy consumption than ever. Lighting on average represents up to 25% of electricity consumption in buildings, so there is much to gain.[2]

Meet our most energy- efficient LED lights yet

Thanks to a great technology breakthrough, Philips Ultra Efficient LED bulbs, spots, tubes and HID replacement lamps allow your customers to immediately save at least 43% energy compared with standard LED alternative.[1]
Not only does this allow for important savings, switching to ultra-efficient LEDs also contributes to improved sustainability.

[1] Energy savings of the Ultra Efficient products compared with the Philips standard alternative products: Philips MASTER LEDbulb UE saves 50% compared to Philips CorePro LEDbulb A60 60W; Philips MASTER LEDspot UE EELA saves 45% compared to Philips LEDspot GU10 50W. Philips MASTER LED SON-T UE lamp saves 43% compared to Philips SON-T 100W E E40; Philips MASTER LEDtube UE saves 43% compared to Philips CorePro LEDtube EM/mains Ultra Output operating on direct mains.
[2] According to Signify modeling and market intelligence data



LED spots

LED lamps save you up to 69% energy and offer the same light quality as conventional lamps. Philips MASTER LED lamps provide you with constant colors, high performance and maximum dimming compatibility. CorePro lamps are good for energy savings of up to 69% and have a lifespan of 15,000 hours. The complete range of Philips LED lamps is designed as a 1-on-1 replacement for currently installed conventional lighting.

MASTER UltraEfficient GU10

www.philips.com/ledlamps



1



2

10 PACK GU10

	Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	cd	°			K	Hrs.					
NEW	1 MAS LEDspot UE 2.1-50W GU10 ND 827 EELA	50	2.1	375	178	680	36	No	80	2700	50.000	50	54	A	929003634602	19485400
NEW	1 MAS LEDspot UE 2.1-50W GU10 ND 830 EELA	50	2.1	375	178	680	36	No	80	3000	50.000	50	54	A	929003610002	17434400
NEW	1 MAS LEDspot UE 2.1-50W GU10 ND 840 EELA	50	2.1	375	178	680	36	No	80	4000	50.000	50	54	A	929003610102	17436800
NEW	2 MAS LEDspot UE 2.4-50W GU10 ND 830 EELB	50	2.4	380	158	900	36	No	80	3000	50.000	50	54	B	929003163102	42174500
NEW	2 MAS LEDspot UE 2.4-50W GU10 ND 840 EELB	50	2.4	380	158	950	36	No	80	4000	50.000	50	54	B	929003163202	42178300

SceneSwitch LEDspot

www.philips.com/ledlamps



4 PACK GU10

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
LED SSW 50W GU10 WW 36D ND SRT4	50	1.5-3.5-4.8	355	73	600	36	No	80	2700-2500-2200	15.000	50	54	F	929002981857	30776600
LED SSW 50W GU10 WW 36D RF ND SRT4	50	1.5-3.5-4.8	355	73	600	36	No	80	2700-2500-2200	15.000	50	54	F	929002981855	30778000

LED spots

MASTER LEDspot ExpertColor LV

www.philips.com/ledlamps



1 2

10 PACK GU5.3

Product Type	Traditional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
1 MAS LED ExpertColor 6.7-35W MR16 927 10D	35	6.7	410	61	4,600	10	Only with specific dimmers	97	2700	40.000	50.5	46	G	929003078802	35847800
2 MAS LED ExpertColor 6.7-35W MR16 927 24D	35	6.7	420	62	2,100	24	Only with specific dimmers	97	2700	40.000	50.5	46	G	929003079102	35853900
2 MAS LED ExpertColor 6.7-35W MR16 927 36D	35	6.7	420	62	1,300	36	Only with specific dimmers	97	2700	40.000	50.5	46	G	929003079402	35859100
2 MAS LED ExpertColor 6.7-35W MR16 927 60D	35	6.7	400	59	410	60	Only with specific dimmers	97	2700	40.000	50.5	46	G	929003078502	35877500
1 MAS LED ExpertColor 6.7-35W MR16 930 10D	35	6.7	430	64	4,800	10	Only with specific dimmers	97	3000	40.000	50.5	46	G	929003078902	35849200
2 MAS LED ExpertColor 6.7-35W MR16 930 24D	35	6.7	440	65	2,200	24	Only with specific dimmers	97	3000	40.000	50.5	46	G	929003079202	35855300
2 MAS LED ExpertColor 6.7-35W MR16 930 36D	35	6.7	440	65	1,400	36	Only with specific dimmers	97	3000	40.000	50.5	46	G	929003079502	35861400
2 MAS LED ExpertColor 6.7-35W MR16 930 60D	35	6.7	440	65	440	60	Only with specific dimmers	97	3000	40.000	50.5	46	G	929003078602	35843000
1 MAS LED ExpertColor 6.7-35W MR16 940 10D	35	6.7	440	65	4,800	10	Only with specific dimmers	97	4000	40.000	50.5	46	G	929003079002	35851500
2 MAS LED ExpertColor 6.7-35W MR16 940 24D	35	6.7	460	68	2,200	24	Only with specific dimmers	97	4000	40.000	50.5	46	G	929003079302	35857700
2 MAS LED ExpertColor 6.7-35W MR16 940 36D	35	6.7	460	68	1,400	36	Only with specific dimmers	97	4000	40.000	50.5	46	G	929003079602	35863800
2 MAS LED ExpertColor 6.7-35W MR16 940 60D	35	6.7	440	65	440	60	Only with specific dimmers	97	4000	40.000	50.5	46	G	929003078702	35845400
1 MAS LED ExpertColor 7.5-43W MR16 927 24D	43	7.5	485	64	2,400	24	Only with specific dimmers	92	2700	40.000	50.5	46	G	929003079702	35865200
1 MAS LED ExpertColor 7.5-43W MR16 927 36D	43	7.5	485	64	1,400	36	Only with specific dimmers	92	2700	40.000	50.5	46	G	929003080002	35871300
1 MAS LED ExpertColor 7.5-43W MR16 930 24D	43	7.5	500	66	2,600	24	Only with specific dimmers	92	3000	40.000	50.5	46	G	929003079802	35867600
1 MAS LED ExpertColor 7.5-43W MR16 930 36D	43	7.5	500	66	1,550	36	Only with specific dimmers	92	3000	40.000	50.5	46	G	929003080102	35873700
1 MAS LED ExpertColor 7.5-43W MR16 940 24D	43	7.5	520	69	2,800	24	Only with specific dimmers	92	4000	40.000	50.5	46	G	929003079902	35869000
1 MAS LED ExpertColor 7.5-43W MR16 940 36D	43	7.5	520	69	1,650	36	Only with specific dimmers	92	4000	40.000	50.5	46	G	929003080202	35875100

LED spots

MASTER LEDspot ExpertColor MV

www.philips.com/ledlamps



10 PACK GU10

Product Type	Traditional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
MAS LED ExpertColor 3.9-35W GU10 927 25D	35	3.9	265	67.95	700	25	Only with specific dimmers	97	2700	40.000	50	54	G	929001346402	70749400
MAS LED ExpertColor 3.9-35W GU10 927 36D	35	3.9	265	67	540	36	Only with specific dimmers	97	2700	40.000	50	54	G	929001346702	70755500
MAS LED ExpertColor 3.9-35W GU10 930 25D	35	3.9	280	71	750	25	Only with specific dimmers	97	3000	40.000	50	54	G	929001346502	70751700
MAS LED ExpertColor 3.9-35W GU10 930 36D	35	3.9	280	71	560	36	Only with specific dimmers	97	3000	40.000	50	54	G	929001346802	70757900
MAS LED ExpertColor 3.9-35W GU10 940 25D	35	3.9	300	76	800	25	Only with specific dimmers	97	4000	40.000	50	54	F	929001346602	70753100
MAS LED ExpertColor 3.9-35W GU10 940 36D	35	3.9	300	76	600	36	Only with specific dimmers	97	4000	40.000	50	54	F	929001346902	70759300
MAS LED ExpertColor 5.5-50W GU10 927 25D	50	5.5	355	64.55	1,000	25	Only with specific dimmers	97	2700	40.000	50	54	G	929001347002	70761600
MAS LED ExpertColor 5.5-50W GU10 927 36D	50	5.5	355	64	800	36	Only with specific dimmers	97	2700	40.000	50	54	G	929001347302	70767800
MAS LED ExpertColor 5.5-50W GU10 930 25D	50	5.5	375	68	1,000	25	Only with specific dimmers	97	3000	40.000	50	54	G	929001347102	70763000
MAS LED ExpertColor 5.5-50W GU10 930 36D	50	5.5	375	68	800	36	Only with specific dimmers	97	3000	40.000	50	54	G	929001347402	70769200
MAS LED ExpertColor 5.5-50W GU10 940 25D	50	5.5	400	72	1,050	25	Only with specific dimmers	97	4000	40.000	50	54	F	929001347202	70765400
MAS LED ExpertColor 5.5-50W GU10 940 36D	50	5.5	400	72	800	36	Only with specific dimmers	97	4000	40.000	50	54	F	929001347502	70771500
MASLED ExpertColor5.5-50W GU10 927 25DUK	50	5.5	355	64	1,000	25	Only with specific dimmers	97	2700	40.000	50	54	G	929001347099	70761601
MASLED ExpertColor5.5-50W GU10 927 36DUK	50	5.5	355	64	800	36	Only with specific dimmers	97	2700	40.000	50	54	G	929001347398	70767801
MASLEDExpertColor 5.5-50W GU10 930 36DUK	50	5.5	375	68	800	36	Only with specific dimmers	97	3000	40.000	50	54	G	929001347499	70769201

LED spots

MASTER LEDspot ExpertColor AR111

www.philips.com/ledlamps



1



2

6 PACK

G53

Product Type	Traditional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
1 MAS ExpertColor 10.8-50W 927 AR111 24D	50	10.8	600	55	3,000	24	Only with specific dimmers	95	2700	40.000	111	61	G	929003043302	33393200
1 MAS ExpertColor 10.8-50W 927 AR111 40D	50	10.8	600	55	1,200	40	Only with specific dimmers	95	2700	40.000	111	61	G	929003043402	33395600
2 MAS ExpertColor 10.8-50W 927 AR111 9D	50	10.8	600	55	8,000	9	Only with specific dimmers	95	2700	40.000	111	61	G	929003043202	33391800
1 MAS ExpertColor 10.8-50W 930 AR111 24D	50	10.8	620	57	3,200	24	Only with specific dimmers	95	3000	40.000	111	61	G	929003043602	33399400
1 MAS ExpertColor 10.8-50W 930 AR111 40D	50	10.8	620	57	1,200	40	Only with specific dimmers	95	3000	40.000	111	61	G	929003043702	33401400
2 MAS ExpertColor 10.8-50W 930 AR111 9D	50	10.8	620	57	8,000	9	Only with specific dimmers	95	3000	40.000	111	61	G	929003043502	33397000
1 MAS ExpertColor 14.8-75W 927 AR111 24D	75	14.8	875	59	3,000	24	Only with specific dimmers	95	2700	40.000	111	61	G	929003042602	33379600
1 MAS ExpertColor 14.8-75W 927 AR111 45D	75	14.8	875	59	1,200	45	Only with specific dimmers	95	2700	40.000	111	61	G	929003042702	33381900
1 MAS ExpertColor 14.8-75W 930 AR111 24D	75	14.8	875	59	3,000	24	Only with specific dimmers	95	3000	40.000	111	61	G	929003042802	33383300
1 MAS ExpertColor 14.8-75W 930 AR111 45D	75	14.8	875	59	1,300	45	Only with specific dimmers	95	3000	40.000	111	61	G	929003042902	33385700
1 MAS ExpertColor 14.8-75W 940 AR111 24D	75	14.8	950	64	3,300	24	Only with specific dimmers	95	4000	40.000	111	61	G	929003043002	33387100
1 MAS ExpertColor 14.8-75W 940 AR111 45D	75	14.8	950	64	1,400	45	Only with specific dimmers	95	4000	40.000	111	61	G	929003043102	33389500
1 MAS LEDspotLV D 20-100W 927 AR111 24D	100	20	1270	63	4,300	24	Only with specific dimmers	91	2700	25.000	111	62	G	929002050302	70511400
1 MAS LEDspotLV D 20-100W 927 AR111 45D	100	20	1270	63	2,100	45	Only with specific dimmers	91	2700	25.000	111	62	G	929002050402	70513800
1 MAS LEDspotLV D 20-100W 930 AR111 24D	100	20	1270	63	4,600	24	Only with specific dimmers	91	3000	25.000	111	62	G	929002050502	70515200
1 MAS LEDspotLV D 20-100W 930 AR111 45D	100	20	1270	63	2,200	45	Only with specific dimmers	91	3000	25.000	111	62	G	929002050602	70517600
1 MAS LEDspotLV D 20-100W 940 AR111 24D	100	20	1270	63	5,000	24	Only with specific dimmers	91	4000	25.000	111	62	G	929002050702	70519000
1 MAS LEDspotLV D 20-100W 940 AR111 45D	100	20	1270	63	2,300	45	Only with specific dimmers	91	4000	25.000	111	62	G	929002050802	70521300

LED spots

MASTER VALUE LEDspot PAR

www.philips.com/ledlamps



6 PACK E27

Product Type	Traditional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
1 MAS LEDspot VLE D 6-50W 927 PAR20 25D	50	6	500	83	1,500	25	Only with specific dimmers	90	2700	25.000	65	85	F	929003485702	44304400
1 MAS LEDspot VLE D 6-50W 927 PAR20 40D	50	6	500	83	1,000	40	Only with specific dimmers	90	2700	25.000	65	85	F	929003486002	44310500
1 MAS LEDspot VLE D 6-50W 930 PAR20 25D	50	6	515	85	1,600	25	Only with specific dimmers	90	3000	25.000	65	85	F	929003485802	44306800
1 MAS LEDspot VLE D 6-50W 930 PAR20 40D	50	6	515	85	1,000	40	Only with specific dimmers	90	3000	25.000	65	85	F	929003486102	44312900
1 MAS LEDspot VLE D 6-50W 940 PAR20 25D	50	6	540	90	1,700	25	Only with specific dimmers	90	4000	25.000	65	85	F	929003485902	44308200
1 MAS LEDspot VLE D 6-50W 940 PAR20 40D	50	6	540	90	1,100	40	Only with specific dimmers	90	4000	25.000	65	85	F	929003486202	44314300
NEW 2 MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	75	9.5	760	80	3,000	25	Only with specific dimmers	90	3000	25.000	95	86	F	929003485502	44322800
2 MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	75	9.5	740	77	3,000	25	Only with specific dimmers	90	2700	25.000	95	86	F	929003485402	44320400
2 MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	75	9.5	820	86	3,000	25	Only with specific dimmers	90	4000	25.000	95	86	F	929003485602	44324200
3 MAS LEDspot VLE D 13-100W 927 PAR38 25D	100	13	1000	76	4,800	25	Only with specific dimmers	90	2700	25.000	122	134	F	929003485202	44330300

LED spots

MASTER VALUE LEDspot LV

www.philips.com/ledlamps



1 2 3 4

10 /12 PACK GU5.3/GU4

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
1 MAS LEDspotLV 3.5-20W 827 MR11 24D	20	3.5	200	57	1,000	24	No	80	2700	40.000	35.1	39.5	G	929003087002	35990100
2 MAS LED spot VLE D 5.8-35W MR16 927 36D	35	5.8	450	77	1,300	36	Only with specific dimmers	90	2700	25.000	50.5	45.5	G	929002492502	30718600
2 MAS LED spot VLE D 5.8-35W MR16 927 60D	35	5.8	450	77	600	60	Only with specific dimmers	90	2700	25.000	50.5	45.5	G	929002492802	30724700
2 MAS LED spot VLE D 5.8-35W MR16 930 36D	35	5.8	460	79	1,300	36	Only with specific dimmers	90	3000	25.000	50.5	45.5	F	929002492602	30720900
2 MAS LED spot VLE D 5.8-35W MR16 930 60D	35	5.8	460	79	600	60	Only with specific dimmers	90	3000	25.000	50.5	45.5	F	929002492902	30726100
2 MAS LED spot VLE D 5.8-35W MR16 940 36D	35	5.8	490	84	1,200	36	Only with specific dimmers	90	4000	25.000	50.5	45.5	F	929002492702	30722300
2 MAS LED spot VLE D 5.8-35W MR16 940 60D	35	5.8	490	84	550	60	Only with specific dimmers	90	4000	25.000	50.5	45.5	F	929002493002	30728500
2 MAS LEDspotLV DimTone 5.8-35W MR16 36D	35	5.8	345	59	800	36	Only with specific dimmers	90	2200-2700	25.000	50.5	45.5	G	929002493102	30730800
2 MAS LED SPOT VLE D 7.5-50W MR16 927 36D	50	7.5	621	82	1,600	36	Only with specific dimmers	90	2700	25.000	50.5	45.5	F	929002493202	30732200
3 MAS LED SPOT VLE D 7.5-50W MR16 927 60D	50	7.5	621	82	750	60	Only with specific dimmers	90	2700	25.000	50.5	45.5	F	929002493502	30738400
2 MAS LED SPOT VLE D 7.5-50W MR16 930 36D	50	7.5	630	84	1,600	36	Only with specific dimmers	90	3000	25.000	50.5	45.5	F	929002493302	30734600
3 MAS LED SPOT VLE D 7.5-50W MR16 930 60D	50	7.5	630	84	800	60	Only with specific dimmers	90	3000	25.000	50.5	45.5	F	929002493602	30740700
2 MAS LED SPOT VLE D 7.5-50W MR16 940 36D	50	7.5	660	88	1,500	36	Only with specific dimmers	90	4000	25.000	50.5	45.5	F	929002493402	30736000
3 MAS LED SPOT VLE D 7.5-50W MR16 940 60D	50	7.5	660	88	770	60	Only with specific dimmers	90	4000	25.000	50.5	45.5	F	929002493702	30742100
4 MAS LEDspotLV DimTone 7.5-50W MR16 36D	50	7.5	621	82	1,100	36	Only with specific dimmers	90	2200-2700	25.000	50.5	45.5	F	929002493802	30744500

LED spots

MASTER VALUE LEDspot MV

www.philips.com/ledlamps



10 /6 PACK GU10

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
1 MAS LED spot VLE D 3.7-35W GU10 927 36D	35	3.7	270	72	500	36	Only with specific dimmers	90	2700	25.000	50	54	F	929002979402	30811400
1 MAS LED spot VLE D 3.7-35W GU10 927 60D	35	3.7	270	72	300	60	Only with specific dimmers	90	2700	25.000	50	54	F	929002979802	31226500
2 MAS LED spot VLE D 3.7-35W GU10 930 36D	35	3.7	270	81	500	36	Only with specific dimmers	90	3000	25.000	50	54	F	929001348302	70775300
1 MAS LED spot VLE D 3.7-35W GU10 930 60D	35	3.7	270	72	300	60	Only with specific dimmers	90	3000	25.000	50	54	F	929002979902	31230200
2 MAS LED spot VLE D 3.7-35W GU10 940 36D	35	3.7	285	85.14	500	36	Only with specific dimmers	90	4000	25.000	50	54	F	929001348402	70777700
2 MAS LED spot VLE D 3.7-35W GU10 940 60D	35	3.7	285	85.14	350	60	Only with specific dimmers	90	4000	25.000	50	54	F	929001348702	70783800
1 MAS LED spot VLE DT 3.7-35W GU10 927 36D	35	3.7	270	72	500	36	Only with specific dimmers	90	2200-2700	25.000	50	54	F	929002979702	31228900
3 MAS LEDspot VLE D 4.7-50W GU10 82736D5CT	50	4.7	345	73	650	36	Only with specific dimmers	80	2700	25.000	50	54	F	929002995452	31212800
3 MAS LEDspot VLE D 4.7-50W GU10 83036D5CT	50	4.7	345	73	650	36	Only with specific dimmers	80	3000	25.000	50	54	F	929002995552	31214200
1 MAS LED spot VLE D 4.8-50W GU10 927 36D	50	4.8	355	73	650	36	Only with specific dimmers	90	2700	25.000	50	54	F	929002980102	30813800
2 MAS LED spot VLE D 4.9-50W GU10 927 60D	50	4.9	355	80.61	400	60	Only with specific dimmers	90	2700	25.000	50	54	F	929001349102	70791300
2 MAS LED spot VLE D 4.9-50W GU10 930 36D	50	4.9	365	82	650	36	Only with specific dimmers	90	3000	25.000	50	54	F	929001348902	70787600
2 MAS LED spot VLE D 4.9-50W GU10 930 60D	50	4.9	365	82.65	400	60	Only with specific dimmers	90	3000	25.000	50	54	F	929001349202	70793700
2 MAS LED spot VLE D 4.9-50W GU10 940 36D	50	4.9	380	85.71	700	36	Only with specific dimmers	90	4000	25.000	50	54	F	929001349002	70789000
2 MAS LED spot VLE D 4.9-50W GU10 940 60D	50	4.9	380	85.71	400	60	Only with specific dimmers	90	4000	25.000	50	54	F	929001349302	70795100
2 MAS LED spot VLE DT 4.9-50W GU10 927 36D	50	4.9	355	80.61	650	36	Only with specific dimmers	90	2700	25.000	50	54	F	929001350302	70811800
2 MAS LED spot VLEDT4.9-50W GU10 927 36DUK	50	4.9	355	72	650	36	Yes	90	2200-2700	25.000	50	54	F	929001350399	70811801
2 MAS LEDspotVLE D 4.9-50W GU10 930 36D UK	50	4.9	365	74	650	36	Yes	90	3000	25.000	50	54	F	929001348998	70787601
2 MAS LEDspotVLE D 4.9-50W GU10 940 36D UK	50	4.9	380	77	700	36	Yes	90	4000	25.000	50	54	F	929001349099	70789001
4 MAS LED spot VLE D 6.2-80W GU10 927 36D	80	6.2	575	92	850	36	Only with specific dimmers	90	2700	25.000	50	54	F	929002059502	67541700
4 MAS LED spot VLE D 6.2-80W GU10 930 36D	80	6.2	575	92	850	36	Only with specific dimmers	90	3000	25.000	50	54	F	929002068402	70525100
4 MAS LED spot VLE D 6.2-80W GU10 940 36D	80	6.2	575	92	850	36	Only with specific dimmers	90	4000	25.000	50	54	F	929002066002	70523700
4 MAS LED spot VLE D 6.2-80W GU10 965 36D	80	6.2	575	92	850	36	Only with specific dimmers	90	6500	25.000	50	54	F	929002209902	70607400
4 MAS LED spot VLE D 650lm GU10 930 120D	-	6.2	650	104	200	120	Only with specific dimmers	90	3000	25.000	50	54	F	929002210002	70609800
4 MAS LED spot VLE D 680lm GU10 940 120D	-	6.2	680	109	200	120	Only with specific dimmers	90	4000	25.000	50	54	F	929002210102	70611100
4 MAS LED spot VLE D 680lm GU10 965 120D	-	6.2	680	109	200	120	Only with specific dimmers	90	6500	25.000	50	54	F	929002210202	70613500
4 MAS LED spot VLE DT 6.2-80W GU10 927 36D	80	6.2	575	92	950	36	Only with specific dimmers	90	2700	25.000	50	56	F	929002065902	66271400
4 MAS LEDspot VLE D 650lm GU10 930 120D UK	-	6.2	650	104	200	120	Yes	90	3000	25.000	50	54	F	929002210099	70609801
4 MASLEDspot VLE D 6.2-80W GU10 927 36D UK	80	6.2	575	92	850	36	Yes	90	2700	25.000	50	54	F	929002059599	67541701
4 MASLEDspot VLE D 6.2-80W GU10 930 36D UK	80	6.2	575	92	850	36	Yes	90	3000	25.000	50	54	F	929002068499	70525101

LED spots

MASTER VALUE LEDspot MV - Continued

www.philips.com/ledlamps



10 /6 PACK GU10

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
MASLEDspot VLE D 6.2-80W GU10 940 36D UK	80	6.2	575	92	850	36	Yes	90	4000	25.000	50	54	F	929002066099	70523701
MASLEDspot VLE D 6.2-80W GU10 965 36D UK	80	6.2	575	92	850	36	Yes	90	6500	25.000	50	54	F	929002209999	70607401

MASTER LEDspot LV

www.philips.com/ledlamps



10 PACK GU5.3

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
MAS LEDspotLV D 7.5-50W 927 MR16 24D	50	7.5	621	82	3,900	24	Only with specific dimmers	90	2700	40.000	50	45.5	F	929002491902	30746900
MAS LEDspotLV D 7.5-50W 927 MR16 36D	50	7.5	621	82	1,850	36	Only with specific dimmers	90	2700	40.000	50	45.5	F	929002492202	30752000
MAS LEDspotLV D 7.5-50W 930 MR16 24D	50	7.5	621	82	4,000	24	Only with specific dimmers	90	3000	40.000	50	45.5	F	929002492002	30748300
MAS LEDspotLV D 7.5-50W 930 MR16 36D	50	7.5	621	82	2,000	36	Only with specific dimmers	90	3000	40.000	50	45.5	F	929002492302	30754400
MAS LEDspotLV D 7.5-50W 940 MR16 24D	50	7.5	670	89	4,400	24	Only with specific dimmers	90	4000	40.000	50	45.5	F	929002492102	30750600
MAS LEDspotLV D 7.5-50W 940 MR16 36D	50	7.5	670	89	2,200	36	Only with specific dimmers	90	4000	40.000	50	45.5	F	929002492402	30756800

LED spots

CorePro LEDspot PAR

www.philips.com/ledlamps



6 PACK E27

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
CorePro LEDspot ND 9-60W 927 PAR38 25D	60	9	750	83	3,600	25	No	90	2700	15.000	122	134	F	929003485302	44342600

CorePro LEDspot Reflectors

www.philips.com/ledlamps



6 PACK

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
1 CoreProLEDspot ND1.4-25W R50 E14 827 36D	25	1.4	105	75	210	36	No	80	2700	15.000	50	84	F	929001891002	81173300
2 CoreProLEDspot ND1.8-30W R39 E14 827 36D	30	1.8	150	83	250	36	No	80	2700	15.000	39	65	F	929001890902	81171900
1 CoreProLEDspot ND2.8-40W R50 E14 827 36D	40	2.8	210	75	400	36	No	80	2700	15.000	50	84	F	929001891102	81175700
3 CoreProLEDspot ND 3-40W R63 E27 827 36D	40	3	210	70	400	36	No	80	2700	15.000	63	102	G	929001891302	81179500
4 CoreProLEDspot ND 4-60W R80 E27 827 36D	60	4	345	86	620	36	No	80	2700	15.000	80	112	F	929001891502	81183200
1 CoreProLEDspot D 4.3-60W R50 E14 827 36D	60	4.3	320	74	550	36	Only with specific dimmers	80	2700	15.000	50	84	F	929001891202	81177100
3 CoreProLEDspot D 4.5-60W R63 E27 827 36D	60	4.5	345	76	620	36	Only with specific dimmers	80	2700	15.000	63	102	F	929001891402	81181800
4 CoreProLEDspot ND 8-100W R80 E27 827 36D	100	8	670	83	1,100	36	No	80	2700	15.000	80	112	F	929001891602	81185600
4 CoreProLEDspot D8.5-100W R80 E27 827 36D	100	9	670	74	1,400	36	Only with specific dimmers	80	2700	15.000	80	112	F	929002996902	31236400

LED spots

CorePro LEDspot LV

www.philips.com/ledlamps



1 2 3 4

10 /6 /12 PACK

GU5.3/GU4

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
1 CorePro LED spot 2.3-20W 827 MR11 36D	20	2.3	184	80	400	36	No	80	2700	25.000	35.5	39.5	F	929002066402	65948600
2 CorePro LED spot ND 2.9-20W MR16 827 36D	20	2.9	230	79	560	36	No	80	2700	15.000	50.5	45.5	F	929002494502	30704900
3 CorePro LED spot ND 4.4-35W MR16 827 36D	35	4.4	345	78	650	36	No	80	2700	15.000	50.5	45.5	F	929002494602	30706300
3 CorePro LED spot ND 4.4-35W MR16 840 36D	35	4.4	390	88	750	36	No	80	4000	15.000	50.5	45.5	F	929002494702	30708700
3 CorePro LED spot ND4.4-35WMR16 827 36DUK	35	4.4	345	78	650	36	No	80	2700	15.000	50.5	45.5	F	929002494699	30706301
3 CorePro LED spot ND4.4-35WMR16 840 36DUK	35	4.4	390	88	750	36	No	80	4000	15.000	50.5	45.5	F	929002494799	30708701
3 CorePro LEDspot 4.4-35W MR16 827 36D 5CT	35	4.4	345	78	650	36	No	80	2700	15.000	50.5	45.5	F	929002494652	30758200
4 CorePro LED spot ND 7-50W MR16 827 36D	50	7	621	88	1,400	36	No	80	2700	15.000	50.5	45	F	929001904802	81471000
4 CorePro LED spot ND 7-50W MR16 830 36D	50	7	621	88	1,400	36	No	80	3000	15.000	50.5	45	F	929001904902	81477200
4 CorePro LED spot ND 7-50W MR16 840 36D	50	7	660	94	1,500	36	No	80	4000	15.000	50.5	45	F	929001905002	81479600

LED spots

CorePro LEDspot MV

www.philips.com/ledlamps



10 /6 PACK GU10

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
1 Corepro LEDspot 2.7-25W GU10 827 36D	25	2.7	215	79	470	36	No	80	2700	15.000	50	53	F	929001217532	75209800
2 Corepro LEDspot 2.7-25W GU10 830 36D	25	2.7	225	83	490	36	No	80	3000	15.000	50	54	F	929001217602	72829100
2 Corepro LEDspot 2.7-25W GU10 840 36D	25	2.7	230	85	500	36	No	80	4000	15.000	50	54	F	929001217702	72831400
3 CorePro LEDspot 3-35W GU10 827 36D DIM	35	3	230	76	500	36	Only with specific dimmers	80	2700	15.000	50	54	F	929002495802	72133900
3 CorePro LEDspot 3-35W GU10 830 36D DIM	35	3	230	76	500	36	Only with specific dimmers	80	3000	15.000	50	54	F	929002068202	72135300
3 CorePro LEDspot 3-35W GU10 840 36D DIM	35	3	240	80	500	36	Only with specific dimmers	80	4000	15.000	50	54	F	929002065602	73022500
3 CoreProLEDspot 3-35W GU10 830 36D DIM UK	35	3	230	76	500	36	Yes	80	3000	15.000	50	54	F	929002068299	72135301
1 Corepro LEDspot 3.5-35W GU10 827 36D	35	3.5	255	72	545	36	No	80	2700	15.000	50	54	F	929001217862	75253100
1 Corepro LEDspot 3.5-35W GU10 827 36D UK	35	3.5	255	72	545	36	No	80	2700	15.000	50	54	F	929001217897	75253101
2 Corepro LEDspot 3.5-35W GU10 830 36D	35	3.5	265	75	565	36	No	80	3000	15.000	50	54	F	929001217902	72833800
2 Corepro LEDspot 3.5-35W GU10 830 36D UK	35	3.5	265	75	565	36	No	80	3000	15.000	50	54	F	929001217999	72833801
2 Corepro LEDspot 3.5-35W GU10 840 36D	35	3.5	275	78	590	36	No	80	4000	15.000	50	54	F	929001218002	72835200
2 Corepro LEDspot 3.5-35W GU10 840 36D UK	35	3.5	275	78	590	36	No	80	4000	15.000	50	54	F	929001218099	72835201
3 CorePro LEDspot 4-50W GU10 827 36D DIM	50	4	345	86	700	36	Only with specific dimmers	80	2700	15.000	50	54	F	929002495902	72137700
4 CorePro LEDspot 4-50W GU10 830 36D DIM	50	4	345	86	700	36	Only with specific dimmers	80	3000	15.000	50	54	F	929002068302	35883600
4 CorePro LEDspot 4-50W GU10 840 36D DIM	50	4	350	87	700	36	Only with specific dimmers	80	4000	15.000	50	54	F	929002065802	35885000
3 CoreProLEDspot 4-50W GU10 827 36D DIM UK	50	4	345	86	700	36	Yes	80	2700	15.000	50	54	F	929002495999	72137701
4 CoreProLEDspot 4-50W GU10 830 36D DIM UK	50	4	345	86	700	36	Yes	80	3000	15.000	50	54	F	929002068399	35883601
4 CoreProLEDspot 4-50W GU10 840 36D DIM UK	50	4	350	87	700	36	Yes	80	4000	15.000	50	54	F	929002065899	35885001
1 Corepro LEDspot 4.6-50W GU10 827 36D	50	4.6	355	77	700	36	No	80	2700	15.000	50	54	F	929001215232	75251700
1 CorePro LEDspot 4.6-50W GU10 827 36D 5CT	50	4.6	355	77	700	36	No	80	2700	15.000	50	54	F	929001215252	70029400
1 Corepro LEDspot 4.6-50W GU10 827 36D UK	50	4.6	355	77	700	36	No	80	2700	15.000	50	54	F	929001215268	75251701
2 Corepro LEDspot 4.6-50W GU10 830 36D	50	4.6	370	80	740	36	No	80	3000	15.000	50	54	F	929001218102	72837600
2 Corepro LEDspot 4.6-50W GU10 830 36D UK	50	4.6	370	80	740	36	No	80	3000	15.000	50	54	F	929001218199	72837601
2 Corepro LEDspot 4.6-50W GU10 840 36D	50	4.6	390	84	770	36	No	80	4000	15.000	50	54	F	929001218202	72839000
2 Corepro LEDspot 4.6-50W GU10 840 36D UK	50	4.6	390	84	770	36	No	80	4000	15.000	50	54	F	929001218299	72839001
2 Corepro LEDspot 4.6-50W GU10 865 36D	50	4.6	390	84	770	36	No	80	6500	15.000	50	54	F	929001218302	72841300
2 Corepro LEDspot 4.6-50W GU10 865 36D UK	50	4.6	390	84	770	36	No	80	6500	15.000	50	54	F	929001218399	72841301
5 LEDspot GU10 50W 830 36D 6CT	50	4.7	345	73	700	36	No	80	3000	15.000	50	54	F	929003132390	42063200
4 CorePro LEDspot 4.9-65W GU10 830 36D ND	65	4.9	460	93	800	36	No	80	3000	15.000	50	54	E	929002981002	30871800

LED spots

CorePro LEDspot MV - Continued

www.philips.com/ledlamps



1 2 3

10 /6 PACK GU10

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
1 CorePro LEDspot 4.9-65W GU10 840 36D ND	65	4.9	485	98	800	36	No	80	4000	15.000	50	54	E	929002981102	30861900
2 Corepro LEDspot 550lm GU10 830 120D	-	4.9	550	112	-	120	No	80	3000	15.000	50	54	E	929002981202	30875600
2 Corepro LEDspot 550lm GU10 840 120D	-	4.9	550	112	-	120	No	80	4000	15.000	50	54	E	929002981302	30865700
2 Corepro LEDspot 550lm GU10 865 120D	-	4.9	550	112	-	120	No	80	6500	15.000	50	54	E	929002981402	30867100
3 Corepro LEDspot 670lm GU10 830 60D	90	6.7	670	100	750	60	No	80	3000	25.000	50	54	E	929002466702	81333101
3 Corepro LEDspot 730lm GU10 840 60D	100	6.7	730	108	750	60	No	80	4000	25.000	50	54	E	929002466802	81335501

CorePro LEDspot AR111

www.philips.com/ledlamps



6 PACK G53

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.					
CorePro LEDspot 7-50W 830 AR111 40D	50	7	550	78	1,100	40	No	80	3000	15.000	110.7	55	F	929002965002	30538000
CorePro LEDspot 10-75W 830 AR111 40D	75	10	800	80	1,700	40	No	80	3000	15.000	110.7	55	F	929002965102	30534200
CorePro LEDspot 14-100W 830 AR111 40D	100	14	1160	82	2,200	40	No	80	3000	15.000	110.7	55	F	929002965202	30536600

LED spots

CorePro LEDcapsule LV

www.philips.com/ledlamps



12 PACK


GY6.35/G4

Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 CorePro LEDcapsuleLV 1-10W G4 827	10	1	115	115	300	No	80	2700	15.000	13	35	F	929002388802	76761700
1 CorePro LEDcapsuleLV 1-10W G4 830	10	1	120	120	300	No	80	3000	15.000	13	35	E	929002388902	76759400
2 CorePro LEDcapsuleLV 1.8-20W G4 827	20	1.8	205	113	300	No	80	2700	15.000	13	35	F	929002389002	76765500
2 CorePro LEDcapsuleLV 1.8-20W G4 830	20	1.8	215	119	300	No	80	3000	15.000	13	35	E	929002389102	76769300
3 CorePro LEDcapsuleLV 1.8-20W GY6.35 827	20	1.8	205	113	300	No	80	2700	15.000	13	35	F	929002389702	76779200
3 CorePro LEDcapsuleLV 1.8-20W GY6.35 830	20	1.8	215	119	300	No	80	3000	15.000	13	35	E	929002389802	76783900
4 CorePro LEDcapsuleLV 2.1-20W G4 827 D	20	2.1	210	100	300	Only with specific dimmers	80	2700	15.000	15	40	F	929002389402	76753200
4 CorePro LEDcapsuleLV 2.7-28W G4 827	28	2.7	315	116	300	No	80	2700	15.000	15	40	F	929002389202	76775400
4 CorePro LEDcapsuleLV 2.7-28W G4 830	28	2.7	330	122	300	No	80	3000	15.000	15	40	E	929002389302	76777800
NEW 5 CorePro LEDcapsuleLV 4.2-40W GY6.35 827D	40	4.2	470	111	-	Only with specific dimmers	80	2700	15.000	18	50	F	929003609002	17102200

LED spots

CorePro LEDcapsule MV

www.philips.com/ledlamps




12 PACK G9

Product Type	Traditional	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.					
1 CorePro LEDcapsule 2-25W ND G9 827	25	2	220	110	No	80	2700	15.000	14.5	48	E	929002495202	30389800
1 CorePro LEDcapsule 2-25W ND G9 830	25	2	220	110	No	80	3000	15.000	14.5	48	E	929002495302	30391100
2 CorePro LEDcapsuleMV 2.6-25W G9 827 D	25	2.6	300	115	Only with specific dimmers	80	2700	15.000	15	52	E	929002389902	76669600
2 CorePro LEDcapsuleMV 2.6-25W G9 827 D UK	25	2.6	300	115	Yes	80	2700	15.000	15	52	E	929002389999	76669601
3 CorePro LEDcapsule 3.2-40W ND G9 827	40	3.2	400	125	No	80	2700	15.000	16.5	54	E	929002495502	30393500
3 CorePro LEDcapsule 3.2-40W ND G9 830	40	3.2	400	125	No	80	3000	15.000	16.5	54	E	929002495602	30395900
4 CorePro LEDcapsuleMV 4-40W G9 827 D	40	4	480	120	Only with specific dimmers	80	2700	15.000	18	59	E	929002390002	76673300
5 CorePro LEDcapsule ND 4.8-60W G9 827	60	4.8	570	118	No	80	2700	15.000	19	60	E	929002055102	65780200
6 CorePro LEDcapsule ND 4.8-60W G9 830	60	4.8	570	118	No	80	3000	15.000	19	60	E	929002059802	65818200

LED spots

CorePro LEDlinear MV


www.philips.com/ledlamps



10 PACK R7S R7S

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.					
1 CorePro R7S 118mm 7.2-60W 830	60	7.2	810	112	No	80	3000	15.000	15	118	E	929002495002	30397300
2 CorePro R7S 118mm 7.2-60W 840	60	7.2	850	118	No	80	4000	15.000	15	118	E	929002495102	30399700
3 CorePro LEDlinear ND 7.5-60W R7S 78mm830	60	7.5	950	126.67	No	80	3000	15.000	29	78	E	929001339002	71394500
3 CorePro LEDlinear ND 7.5-60W R7S 78mm840	60	7.5	1000	133.33	No	80	4000	15.000	29	78	E	929001339102	71396900
4 CorePro LED linear D 14-120W R7S 118 830	120	14	2000	142.86	Yes	80	3000	15.000	29	118	D	929001353602	71400300
4 CorePro LED linear D 14-120W R7S 118 840	120	14	2000	142.86	Yes	80	4000	15.000	29	118	D	929001353702	71406500
5 CorePro R7S 118mm 14-100W 830 D	100	14	1600	114.29	Only with specific dimmers	80	3000	15.000	29	118	E	929001243702	57879700
6 CorePro R7S 118mm 14-100W 840 D	100	14	1800	128.57	Only with specific dimmers	80	4000	15.000	29	118	E	929001243802	57881000
7 CoreProLED linearD 17.5-150W R7S 118 830	150	17.5	2460	140	Only with specific dimmers	80	3000	15.000	42	118	D	929002016602	64673800
7 CoreProLED linearD 17.5-150W R7S 118 840	150	17.5	2460	140	Only with specific dimmers	80	4000	15.000	42	118	D	929002016702	64675200

LED bulbs



10 /4 PACK E27

Product Type	LED	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	lm/W			K	Hrs.					
1 LEDClassic SSW 60W A60 E27 WW FRND 1SRT4	1.6-3-7.5	107	No	80	2700-2500-2200	15.000	60	104	F	929002445558	26396300
2 LEDClassic SSW 60W A60 E27WWCLND RF1SRT4	1.6-3-7.5	107	No	80	2700-2500-2200	15.000	60	104	F	929001888655	77213001
1 LEDClassic SSW 60W A60 E27WWFR ND 1PF/10	1.6-3-7.5	107	No	80	2700-2500-2200	15.000	60	104	F	929002445517	26396301

LED bulbs

UltraEfficient LED bulb

www.philips.com/ledlamps



10 /6 PACK

E27

	Product Type	Tradi tional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
NEW	1 MAS LEDBulbND2.3-40W E27 827 A60 CL G UE	40	2.3	485	210	-	No	80	2700	50.000	60	104	A	929003622702	18829700
NEW	2 MAS LEDBulbND2.3-40W E27 827 A60 FR G UE	40	2.3	485	210	-	No	80	2700	50.000	60	104	A	929003622902	18833400
NEW	1 MAS LEDBulbND2.3-40W E27 830 A60 CL G UE	40	2.3	485	210	-	No	80	3000	50.000	-	-	A	929003702502	25404600
NEW	2 MAS LEDBulbND2.3-40W E27 830 A60 FR G UE	40	2.3	485	210	-	No	80	3000	50.000	-	-	A	929003702702	25408400
NEW	3 MAS LEDBulbND2.3-40W E27 840 A60 CL G UE	40	2.3	485	210	-	No	80	4000	50.000	60	104	A	929003623102	18837200
NEW	2 MAS LEDBulbND2.3-40W E27 840 A60 FR G UE	40	2.3	485	210	-	No	80	4000	50.000	60	104	A	929003623302	18841900
NEW	4 MAS LEDBulbND2.3-40W E27830 A60CL G EELA	40	2.3	485	210	-	No	80	3000	50.000	60	105	A	929003066402	42073100
NEW	5 MAS LEDBulbND2.3-40W E27840 A60CL G EELA	40	2.3	485	210	-	No	80	4000	50.000	60	105	A	929003066502	42075500
NEW	6 MAS LEDBulb D 4-60W E27 827 A60 CL G UE	60	4	840	210	300	Only with specific dimmers	80	2700	50.000	-	-	A	929003691502	24864900
NEW	7 MAS LEDBulb D 4-60W E27 827 A60 FR G UE	60	4	840	210	300	Only with specific dimmers	80	2700	50.000	-	-	A	929003691602	24866300
NEW	6 MAS LEDBulb D 4-60W E27 830 A60 CL G UE	60	4	840	210	300	Only with specific dimmers	80	3000	50.000	-	-	A	929003691702	24868700
NEW	7 MAS LEDBulb D 4-60W E27 830 A60 FR G UE	60	4	840	210	300	Only with specific dimmers	80	3000	50.000	-	-	A	929003691802	24870000
NEW	8 MAS LEDBulbND4-60W E27 827 A60 CL G UE	60	4	840	210	-	No	80	2700	50.000	60	104	A	929003623502	18845700
NEW	2 MAS LEDBulbND4-60W E27 827 A60 FR G UE	60	4	840	210	-	No	80	2700	50.000	60	104	A	929003623702	18849500
NEW	9 MAS LEDBulbND4-60W E27 827 G95 CL G UE	60	4	840	210	-	No	80	2700	50.000	95	140	A	929003642502	20276400
NEW	10 MAS LEDBulbND4-60W E27 827 ST64 CL G UE	60	4	840	210	-	No	80	2700	50.000	64	140	A	929003642402	20274000
NEW	11 MAS LEDBulbND4-60W E27 830 A60 CL G EELA	60	4	840	210	-	No	80	3000	50.000	60	105	A	929003066702	42077900
NEW	8 MAS LEDBulbND4-60W E27 830 A60 CL G UE	60	4	840	210	-	No	80	3000	50.000	-	-	A	929003702902	25412100
NEW	2 MAS LEDBulbND4-60W E27 830 A60 FR G UE	60	4	840	210	-	No	80	3000	50.000	-	-	A	929003703102	25416900
NEW	2 MAS LEDBulbND4-60W E27 830 A60 FR G UE	60	4	840	210	-	No	80	3000	50.000	60	105	A	929003480002	43579700
NEW	12 MAS LEDBulbND4-60W E27 840 A60 CL G EELA	60	4	840	210	-	No	80	4000	50.000	60	105	A	929003066802	42079300

LED bulbs

Classic filament LEDbulbs

www.philips.com/ledlamps



4 /2 PACK

E27

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.				
1 LED double layers 20W E27 smoky DIM	20	6.5	200	30	-	Only with specific dimmers	80	1800	15.000	202	293	929002982301	31372900
2 LED giant 20W E27 A160 1800K smoky D	20	6.5	200	30	-	Only with specific dimmers	80	1800	15.000	162	293	929002982501	31537200
3 LED giant 20W E27 G200 1800K smoky D	20	6.5	200	30	300	Only with specific dimmers	80	1800	15.000	202	286	929002982601	31539600
4 LED giant 20W E27 T65 1800K smoky D	20	6.5	200	30	300	Only with specific dimmers	80	1800	15.000	66	273	929002982701	31541900
5 LED classic 25W G93 E27 GOLD SP D SRT4	25	4	250	62	330	Only with specific dimmers	80	1800	15.000	96	143	929002983001	31547100
6 LED giant crystal 26W E27 smoky DIM	26	7	270	38	-	Only with specific dimmers	80	1800	15.000	103	366	929002982401	31374300
7 LED classic-giant 28W E27 A160 GOLD ND	28	4.5	300	66	330	No	80	1800	15.000	162	293	929002983801	31382800
8 LED classic-giant 28W E27 G200 GOLD ND	28	4.5	300	66	330	No	80	1800	15.000	202	286	929002983901	31384200
9 LED classic-giant 40W E27 A160 GOLD DIM	40	7	470	67	330	Only with specific dimmers	80	1800	15.000	162	293	929002983501	31376700
10 LED classic-giant 40W E27 G200 GOLD DIM	40	7	470	67	330	Only with specific dimmers	80	1800	15.000	202	286	929002983601	31378100
11 LED classic-giant 40W E27 T65 GOLD DIM	40	7	470	67	330	Only with specific dimmers	80	1800	15.000	66	273	929002983701	31380400
12 LEDClassic 40W Mushroom E27 1800K GOLD D	40	5.5	470	85	300	Only with specific dimmers	80	1800	15.000	202	188	929002984001	31386600

LED bulbs

CorePro LEDbulbs

www.philips.com/ledlamps



10 /8 /6 /2 PACK

B22/E27

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 CorePro LEDbulb ND 5-40W A60 B22 930	40	5	470	94	200	No	90	3000	15.000	60	110	F	929003001602	32972000
2 CorePro LEDbulb ND 5-40W A60 E27 830	40	5	470	94	200	No	80	3000	15.000	60	110	F	929001304532	57993000
2 CorePro LEDbulb ND 5-40W A60 E27 840	40	5	470	94	200	No	80	4000	15.000	60	110	F	929001234602	57779000
3 CorePro LEDbulb ND 5-40W A60 E27 930	40	5	470	94	200	No	90	3000	15.000	60	110	F	929003001502	32956000
3 CorePro LEDbulb ND 5-40W A60 E27 940	40	5	470	94	200	No	90	4000	15.000	60	110	F	929003001702	32958400
4 CorePro LEDbulb ND 5.5-40W A60 B22 827	40	5.5	470	85	200	No	80	2700	15.000	60	110	F	929001233802	57765300
2 CorePro LEDbulb ND 5.5-40W A60 E27 827	40	5.5	470	85	200	No	80	2700	15.000	60	110	F	929001234202	57757800
4 CoreProLEDbulb ND 5.5-40W A60 B22 827 UK	40	5.5	470	85	200	No	80	2700	15.000	60	110	F	929001233899	57765301
2 CoreProLEDbulb ND 5.5-40W A60 E27 827 UK	40	5.5	470	85	200	No	80	2700	15.000	60	110	F	929001234299	57757801
1 CorePro LEDbulb ND 7.5-60W A60 B22 930	60	7.5	806	107	200	No	90	3000	15.000	60	110	F	929003002402	32974400
2 CorePro LEDbulb ND 7.5-60W A60 E27 830	60	7.5	806	107	200	No	80	3000	15.000	60	110	F	929001304732	57771400
2 CorePro LEDbulb ND 7.5-60W A60 E27 840	60	7.5	806	107	200	No	80	4000	15.000	60	110	F	929001234702	57777600
3 CorePro LEDbulb ND 7.5-60W A60 E27 930	60	7.5	806	107	200	No	90	3000	15.000	60	110	F	929003002302	32960700
3 CorePro LEDbulb ND 7.5-60W A60 E27 940	60	7.5	806	107	200	No	90	4000	15.000	60	110	F	929003002502	32962100
4 CorePro LEDbulb ND 8-60W A60 B22 827	60	8	806	100	200	No	80	2700	15.000	60	110	F	929001233902	57763900
4 CorePro LEDbulb ND 8-60W A60 B22 827 UK	60	8	806	100	200	No	80	2700	15.000	60	110	F	929001233997	57763901
3 CorePro LEDbulb ND 8-60W A60 E27 827	60	8	806	100	200	No	80	2700	15.000	60	110	F	929001234302	57755400
5 CorePro LEDbulb ND 8-60W A60 E27 827 SKT	60	8	806	100	200	No	80	2700	15.000	60	110	F	929001234350	40437300
3 CorePro LEDbulb ND 8-60W A60 E27 827 UK	60	8	806	100	200	No	80	2700	15.000	60	110	F	929001234385	57755401
3 CorePro LEDbulbND 8-60W A60E27 827 3CT/8	60	8	806	100	200	No	80	2700	15.000	60	110	F	929001234332	70033100
1 CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	60	7.5	806	107	200	No	90	3000	15.000	60	110	F	929003002499	32974401
6 LEDbulb ND 8-60W A60 E27 827 6CT	60	8	806	100	180	No	80	2700	15.000	60	108	F	929002306202	42067000
7 CorePro LEDbulb ND 10-75W A60 E27 840	75	10	1055	105	200	No	80	4000	15.000	60	110	F	929001234802	51032200
8 CorePro LEDbulb ND 10-75W A60 E27 865	75	10	1055	105	200	No	80	6500	15.000	60	110	F	929001163832	49758600
9 CorePro LEDbulb ND 10-75W A60 E27 940	75	10	1055	105	200	No	90	4000	15.000	60	110	F	929003003302	32966900
10 CorePro LEDbulb ND 10.5-75W A60 B22 930	75	10.5	1055	100	200	No	90	3000	15.000	60	110	F	929003003202	32976800
8 CorePro LEDbulb ND 10.5-75W A60 E27 830	75	10.5	1055	100	200	No	80	3000	15.000	60	110	F	929001162332	49752400
9 CorePro LEDbulb ND 10.5-75W A60 E27 930	75	10.5	1055	100	200	No	90	3000	15.000	60	110	F	929003003102	32964500
11 CorePro LEDbulb ND 11-75W A60 B22 827	75	11	1055	95	200	No	80	2700	15.000	60	110	F	929001234002	57761500
11 CorePro LEDbulb ND 11-75W A60 B22 827 UK	75	11	1055	95	200	No	80	2700	15.000	60	110	F	929001234098	51004901

LED bulbs



10 /8 /6 /2 PACK

B22/E27

	Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
	1 CorePro LEDbulb ND 11-75W A60 E27 827	75	11	1055	95	200	No	80	2700	15.000	60	110	F	929001234402	49076100
	2 LEDbulb ND 10-75W A60 E27 827 6CT	75	10	1055	105	180	No	80	2700	15.000	60	108	F	929002306502	42069400
NEW	3 CorePro LEDbulb ND 12.5-100W A60 E27 940	100	12.5	1521	121	200	No	90	4000	15.000	60	110	E	929003004102	32970600
NEW	4 CorePro LEDbulb ND 13-100W A60 B22 930	100	13	1521	117	200	No	90	3000	15.000	60	110	E	929003004002	32978200
NEW	3 CorePro LEDbulb ND 13-100W A60 E27 930	100	13	1521	117	200	No	90	3000	15.000	60	110	E	929003003902	32968300
NEW	4 CoreProLEDbulb ND 13-100W A60 B22 930 UK	100	13	1521	117	200	No	90	3000	15.000	60	110	E	929003004099	32978201
NEW	3 CoreProLEDbulb ND 13-100W A60 E27 930 UK	100	13	1521	117	200	No	90	3000	15.000	60	110	E	929003003999	32968301
	1 CorePro LEDbulb ND 12.5-100W A60 E27 840	100	12.5	1521	121	200	No	80	4000	15.000	60	110	E	929001312402	51030800
	1 CorePro LEDbulb ND 12.5-100W A60 E27 865	100	12.5	1521	121	200	No	80	6500	15.000	60	110	E	929001312502	57781300
	5 CorePro LEDbulb ND 13-100W A60 B22 827	100	13	1521	117	200	No	80	2700	15.000	60	110	E	929001234102	51002500
	1 CorePro LEDbulb ND 13-100W A60 E27 827	100	13	1521	117	200	No	80	2700	15.000	60	110	E	929001234502	49074700
	1 CorePro LEDbulb ND 13-100W A60 E27 830	100	13	1521	117	200	No	80	3000	15.000	60	110	E	929001235002	57767700
	5 CoreProLEDbulb ND 13-100W A60 B22 827 UK	100	13	1521	117	200	No	80	2700	15.000	60	110	E	929001234199	51002501
	1 CoreProLEDbulb ND 13-100W A60 E27 827 UK	100	13	1521	117	200	No	80	2700	15.000	60	110	E	929001234564	49074701

LED bulbs

CorePro Glass LED bulbs

www.philips.com/ledlamps



10 /6 PACK

B22/E27

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.					
1 CorePro LEDBulbND 4-40W E27 ST64 827 CLG	40	4	470	117	No	80	2700	15.000	64	140	E	929001237392	34687100
2 CorePro LEDBulbND 4.3-40W E27 A60827 CLG	40	4.3	470	109	No	80	2700	15.000	60	104	F	929001890092	34716800
3 CorePro LEDBulbND 4.3-40W E27 A60840 CLG	40	4.3	540	125	No	80	4000	15.000	60	104	E	929001890692	35493700
4 CorePro LEDBulbND 4.5-40W E27 A60830 FRG	40	4.5	470	104	No	80	3000	15.000	60	106	F	929002424992	34702100
5 CorePro LEDBulbND4.5-40W E27 A60 827FR G	40	4.5	470	104	No	80	2700	15.000	60	110	F	929001242992	36130000
4 CorePro LEDBulb7-60W E27 A60 840 FR G	60	7	806	115	No	80	4000	15.000	60	106	E	929001323592	37751600
6 CorePro LEDBulbND 7-60W B22 A60 827 CL G	60	7	806	115	No	80	2700	15.000	60	104	E	929001387492	34673400
7 CorePro LEDBulbND 7-60W E27 A60 827FR G	60	7	806	115	No	80	2700	15.000	60	110	E	929001243002	36124900
4 CorePro LEDBulbND 7-60W E27 A60 830 FR G	60	7	806	115	No	80	3000	15.000	60	106	E	929002425092	34647500
8 CorePro LEDBulbND 7-60W E27 A60 840 CL G	60	7	850	121	No	80	4000	15.000	60	106	E	929001815092	35491300
9 CorePro LEDBulbND 7-60W E27 G93 827 CL G	60	7	806	115	No	80	2700	15.000	95	140	E	929001387992	34677200
10 CorePro LEDBulbND 7-60W E27 ST64 827CL G	60	7	806	115	No	80	2700	15.000	64	140	E	929001387692	34675800
11 CorePro LEDBulbND 7-60W E27 WW A60 CL G	60	7	806	115	No	80	2700	15.000	60	104	E	929001387362	38003500
11 CorePro LEDBulbND7-60W E27 WW A60 CLG3pk	60	7	806	115	No	80	2700	15.000	60	104	E	929001387314	38996000
4 CorePro LEDBulb8.5-75W E27 A60 840 FR G	75	8.5	1055	124	No	80	4000	15.000	60	104	E	929002025892	37753000
12 CorePro LEDBulbND 8.5-75W E27 A60 827CLG	75	8.5	1055	124	No	80	2700	15.000	60	104	E	929002025492	34712000
4 CorePro LEDBulbND 8.5-75W E27 A60 830FRG	75	8.5	1055	124	No	80	3000	15.000	60	104	E	929002425192	34704500
12 CorePro LEDBulbND 8.5-75W E27 A60 840CLG	75	8.5	1055	124	No	80	4000	15.000	60	104	E	929002025592	34708300
4 CorePro LEDBulbND8.5-75W E27 A60 827FR G	75	8.5	1055	124	No	80	2700	15.000	60	104	E	929002025702	36126300

LED bulbs



10 /6 PACK

B22/E27

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.					
1 CorePro LEDBulb10.5-100W E27 A60 840 FRG	100	10.5	1521	144	No	80	4000	15.000	60	104	D	929002026592	37755400
2 CorePro LEDBulbND10.5-100W E27A60 827CLG	100	10.5	1521	144	No	80	2700	15.000	60	104	D	929002026192	34714400
1 CorePro LEDBulbND10.5-100W E27A60 827FRG	100	10.5	1521	144	No	80	2700	15.000	60	104	D	929002026402	36128700
3 CorePro LEDBulbND10.5-100W E27A60 830FRG	100	10.5	1521	144	No	80	3000	15.000	60	104	D	929002425292	34706900
2 CorePro LEDBulbND10.5-100W E27A60 840CLG	100	10.5	1521	144	No	80	4000	15.000	60	104	D	929002026292	34710600

LED bulbs

CorePro Glass High Lumen bulbs

www.philips.com/ledlamps



10 /6 PACK E27

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.					
1 CorePro LEDBulbND 120W E27 A67 827 CL G	120	13	2000	153	No	80	2700	15.000	70	121	D	929002371502	34649900
2 CorePro LEDBulbND 120W E27 A67 827 FR G	120	13	2000	153	No	80	2700	15.000	70	121	D	929002371802	34653600
1 CorePro LEDBulbND 120W E27 A67 840 CL G	120	13	2000	153	No	80	4000	15.000	70	121	D	929002371602	34651200
2 CorePro LEDBulbND 120W E27 A67 840 FR G	120	13	2000	153	No	80	4000	15.000	70	121	D	929002371902	34655000
3 CorePro LEDBulbND 120W E27 A67 865 FR G	120	13	2000	153	No	80	6500	15.000	70	121	D	929002372002	34657400
3 CorePro LEDBulbND 150W E27 A67 827 FR G	150	17.5	2452	140	No	80	2700	15.000	70	121	D	929002372602	34661100
4 CorePro LEDBulbND 150W E27 A67 840 CL G	150	17	2452	144	No	80	4000	15.000	70	121	D	929002372402	34659800
3 CorePro LEDBulbND 150W E27 A67 840 FR G	150	17.5	2452	140	No	80	4000	15.000	70	121	D	929002372702	34663500
3 CorePro LEDBulbND 150W E27 A67 865 FR G	150	17.5	2452	140	No	80	6500	15.000	70	121	D	929002372802	34665900
5 CorePro LEDBulbND17-150W E27 A67 827 CLG	150	17	2452	144	No	80	2700	15.000	70	128	D	929002055092	34744100
6 CorePro LEDBulbND 200W E27 A95 827 FR G	200	23	3452	150	No	80	2700	15.000	95	165	D	929002372902	34667300
6 CorePro LEDBulbND 200W E27 A95 840 FR G	200	23	3452	150	No	80	4000	15.000	95	165	D	929002373002	34669700
6 CorePro LEDBulbND 200W E27 A95 865 FR G	200	23	3452	150	No	80	6500	15.000	95	165	D	929002373102	34671000

CorePro Plastic LED Specialties

www.philips.com/ledlamps



10 PACK E27

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
CorePro LED Stick ND 9.5-68W T38 E27 830	68	9.5	950	100	240	No	80	3000	15.000	37.2	114.3	F	929001901402	81451200
CorePro LED Stick ND 9.5-75W T38 E27 840	75	9.5	1050	110	240	No	80	4000	15.000	37.2	114.3	E	929001901502	81453600

LED bulbs

MASTER Glass LED bulbs

www.philips.com/ledlamps



10 PACK B22/E27

	Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W			K	Hrs.					
NEW	1 MAS LEDBulb DT3.4-40W E27 927A60CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	60	104	D	929003009982	44967100
NEW	2 MAS LEDBulbDT3.4-40WB22 927A60CL G UK	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	60	103	D	929003010142	46655500
NEW	2 MASLEDBulbDT3.4-40W B22 927A60CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	60	103	D	929003010182	44969500
	3 MAS LEDBulbDT3.4 -40W E27 927 A60 FR G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	60	104	D	929003010002	32467100
NEW	4 MAS LEDBulb DT5.9-60W B22 927A60CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	25.000	60	103	D	929003010582	44973200
NEW	5 MAS LEDBulbDT5.9-60W E27 927A60CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	25.000	60	104	D	929003010382	44971800
NEW	5 MAS LEDBulbDT5.9-60W E27 927A60CL G UK	60	5.9	806	136	Only with specific dimmers	90	2200-2700	25.000	60	104	D	929003010342	46657900
NEW	4 MAS LEDBulbDT5.9-60WB22 927A60CL G UK	60	5.9	806	136	Only with specific dimmers	90	2200-2700	25.000	60	103	D	929003010542	46659300
	3 MAS LEDBulb DT5.9-60W E27 927 A60 FR G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	25.000	60	104	D	929003010402	32475600
NEW	6 MAS LEDBulb DT7.2-75W B22 927A60CL G	75	7.2	1055	146	Only with specific dimmers	90	2200-2700	25.000	60	103	D	929003011282	46103100
NEW	7 MAS LEDBulb DT7.2-75W E27 927A60CL G	75	7.2	1055	146	Only with specific dimmers	90	2200-2700	25.000	60	104	D	929003011182	44975600
	3 MAS LEDBulb DT7.2-75W E27 927 A60 FR G	75	7.2	1055	146	Only with specific dimmers	90	2200-2700	25.000	60	104	D	929003011302	32493000
NEW	8 MAS LEDBulbDT10.5-100W B22 927A60CLG	100	10.5	1521	144	Only with specific dimmers	90	2200-2700	25.000	60	107	D	929003011682	44979400
NEW	9 MAS LEDBulbDT10.5-100W E27 927A60CLG	100	10.5	1521	144	Only with specific dimmers	90	2200-2700	25.000	60	108	D	929003011582	44977000
	3 MAS LEDBulb DT10.5-100W E27 927A60 FR G	100	10.5	1521	144	Only with specific dimmers	90	2200-2700	25.000	60	108	D	929003011702	32501200

LED bulbs

MASTER Plastic LED Dusk to Dawn

www.philips.com/ledlamps



10 PACK E27

	Product Type	Tradi tional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
NEW	1 MAS LED D2D ND 6.5-60W A60 E27 840	60	6.5	806	124	250	No	80	4000	15.000	62	114	E	929001383732	39965500
NEW	2 MAS LED D2D ND 7.5-60W A60 E27 827	60	7.5	806	107	250	No	80	2700	15.000	62	114	F	929001383602	39947100

MASTER Plastic LED Sensor

www.philips.com/ledlamps




10 PACK E27

	Product Type	Tradi tional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
NEW	MAS LED Sensor ND 8-60W A60 E27 827	60	8	806	100	280	No	80	2700	15.000	62.5	122	F	929002058702	39945700
NEW	MAS LED Sensor ND 8-60W A60 E27 840	60	8	806	100	280	No	80	4000	15.000	62.5	122	F	929002058802	39949500

LED bulbs

MASTER Value Decorative LED bulbs

www.philips.com/ledlamps



10 /6 PACK


E27

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.				
1 MAS VLE LEDBulbD4-25W E27 A60 GOLD SP G	25	4	250	62	Only with specific dimmers	80	1800	15.000	61	106	929002982802	31551800
2 MAS VLE LEDBulbD4-25W E27 ST64 GOLD SP G	25	4	250	62	Only with specific dimmers	80	1800	15.000	65	143	929002982902	31553200
3 MAS VLE LEDBulbD4-25W E27 T32 GOLD SP G	25	4	250	62	Only with specific dimmers	80	1800	15.000	33	137	929002983102	31555600
4 MAS VLE LEDBulbD4-25WE27 G93GOLD SP G	25	4	250	62	Only with specific dimmers	80	1800	15.000	96	143	929002983002	38548100

LED bulbs

MASTER Value GLASS LED bulbs

www.philips.com/ledlamps



10 /6 PACK

B22/E27

	Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W			K	Hrs.					
NEW	1 MAS VLE LEDBulbD3.4-40W E27 940 A60CL G	40	3.4	470	138	Only with specific dimmers	90	4000	15.000	60	104	D	929003526602	44981700
NEW	2 MAS VLE LEDBulbD3.4-40W E27 940 A60FR G	40	3.4	470	138	Only with specific dimmers	90	4000	15.000	60	104	D	929003527002	44989300
	3 MAS VLE LEDBulb DT3.4-40W E27 927A60CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	15.000	60	104	D	929003009902	32465700
	4 MAS VLE LEDBulbD 3.4-40W B22 A60 927FR G	40	3.4	470	138	Only with specific dimmers	90	2700	15.000	60	103	D	929003010202	32471800
	1 MAS VLE LEDBulbD3.4-40W E27 927 A60 CL G	40	3.4	470	138	Only with specific dimmers	90	2700	15.000	60	104	D	929003070502	35481400
	2 MAS VLE LEDBulbD3.4-40W E27 927 A60 FR G	40	3.4	470	138	Only with specific dimmers	90	2700	15.000	60	104	D	929003070702	35483800
	5 MAS VLELEDBulbDT3.4-40W B22 927A60CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	15.000	60	103	D	929003010102	32469500
	5 MAS VLELEDBulbDT3.4-40WB22 927A60CL G UK	40	3.4	470	138	Yes	90	2200-2700	15.000	60	103	D	929003010199	32469501
	6 MAS VLE LEDBulbD7.2-50W E27 A60 827 CM G	50	7.2	650	90	Only with specific dimmers	80	2700	15.000	60	106	F	929002412802	36122500
NEW	7 MAS VLE LEDBulbD5.9-60W E27 940 A60CL G	60	5.9	806	136	Only with specific dimmers	90	4000	15.000	60	104	D	929003526702	44983100
NEW	2 MAS VLE LEDBulbD5.9-60W E27 940 A60FR G	60	5.9	806	136	Only with specific dimmers	90	4000	15.000	60	104	D	929003527102	44991600
	8 MAS VLE EDBulbDT5.9-60W B22 927 G93CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	15.000	95	136	D	929003011002	32487900
	9 MAS VLE EDBulbDT5.9-60W B22 927 ST64CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	15.000	64	139	D	929003010802	32483100
	7 MAS VLE LEDBulb D5.9-60W E27 927 A60CLG	60	5.9	806	136	Only with specific dimmers	90	2700	15.000	60	104	D	929003057502	34784700
	2 MAS VLE LEDBulb D5.9-60W E27 927 A60 FRG	60	5.9	806	136	Only with specific dimmers	90	2700	15.000	60	104	D	929003057702	34786100
	10 MAS VLE LEDBulb D5.9-60W E27 927 G120CLG	60	5.9	806	136	Only with specific dimmers	90	2700	15.000	124	178	D	929003059302	34798400
	11 MAS VLE LEDBulb D5.9-60W E27 927 ST64CLG	60	5.9	806	136	Only with specific dimmers	90	2700	15.000	64	140	D	929003059402	34796000
	12 MAS VLE LEDBulb DT5.9-60W B22 927A60CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	15.000	60	103	D	929003010502	32477000

LED bulbs

MASTER Value GLASS LED bulbs - Continued

www.philips.com/ledlamps



10 /6 PACK

B22/E27

	Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W			K	Hrs.					
	1 MAS VLE LEDBulb DT5.9-60W E27 927G93CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	15.000	95	137	D	929003010902	32485500
	2 MAS VLE LEDBulb DT5.9-60W E27 927ST64CLG	60	5.9	806	136	Only with specific dimmers	90	2200-2700	15.000	64	140	D	929003010702	32481700
	3 MAS VLE LEDBulbD5.9-60W B22 A60 927FR G	60	5.9	806	136	Only with specific dimmers	90	2700	15.000	60	103	D	929003010602	32479400
	4 MAS VLE LEDBulbDT5.9-60W E27 927A60CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	15.000	60	104	D	929003010302	32473200
	3 MASVLE LEDBulbD5.9-60W B22A60 927FR G UK	60	5.9	806	136	Yes	90	2200-2700	15.000	60	103	D	929003010699	32479401
	5 MASVLE LEDBulbDT5.9-60WB22 927A60CL G UK	60	5.9	806	136	Yes	90	2200-2700	15.000	60	103	D	929003010598	32477001
	6 MASVLELEDBulb D5.9-60W E27 927A60FR G UK	60	5.9	806	136	Yes	90	2700	15.000	60	104	D	929003057799	34786101
	4 MASVLELEDBulbDT5.9-60W E27 927A60CL G UK	60	5.9	806	136	Yes	90	2200-2700	15.000	60	104	D	929003010398	32473201
NEW	7 MAS VLE LEDBulbD7.8-75W E27 940 A60CL G	75	7.8	1055	135	Only with specific dimmers	90	4000	15.000	60	104	D	929003526802	44985500
NEW	6 MAS VLE LEDBulbD7.8-75W E27 940 A60FR G	75	7.8	1055	135	Only with specific dimmers	90	4000	15.000	60	104	D	929003527202	44993000
	7 MAS VLE LEDBulb D7.8-75W E27 927 A60 CLG	75	7.8	1055	135	Only with specific dimmers	90	2700	15.000	60	104	D	929003057902	34788500
	6 MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG	75	7.8	1055	135	Only with specific dimmers	90	2700	15.000	60	104	D	929003058102	34790800
	8 MAS VLE LEDBulb DT7.2-75W B22 927A60CL G	75	7.2	1055	146	Only with specific dimmers	90	2200-2700	15.000	60	103	D	929003011202	32491600
	9 MAS VLE LEDBulb DT7.2-75W E27 927A60CL G	75	7.2	1055	146	Only with specific dimmers	90	2200-2700	15.000	60	104	D	929003011102	32489300
	3 MAS VLE LEDBulbD7.2-75W B22 A60 927 FR G	75	7.2	1055	146	Only with specific dimmers	90	2700	15.000	60	103	D	929003011402	32495400
NEW	10 MAS VLE LEDBulbD11.2-100W E27 940A60CLG	100	11.2	1521	135	Only with specific dimmers	90	4000	15.000	60	108	D	929003526902	44987900
NEW	6 MAS VLE LEDBulbD11.2-100W E27 940A60FRG	100	11.2	1521	135	Only with specific dimmers	90	4000	15.000	60	108	D	929003527302	44995400
	3 MAS VLE LEDBulbD10.5-100W B22 A60 927FRG	100	10.5	1521	144	Only with specific dimmers	90	2700	15.000	60	107	D	929003011802	32503600
	10 MAS VLE LEDBulbD11.2-100W E27 927 A60CLG	100	11.2	1521	135	Only with specific dimmers	90	2700	15.000	60	108	D	929003058302	34792200
	6 MAS VLE LEDBulbD11.2-100W E27 927 A60FRG	100	11.2	1521	135	Only with specific dimmers	90	2700	15.000	60	108	D	929003058502	34794600
	11 MAS VLE LEDBulbDT10.5-100W B22 927A60CLG	100	10.5	1521	144	Only with specific dimmers	90	2200-2700	15.000	60	107	D	929003011602	32499200
	12 MAS VLE LEDBulbDT10.5-100W E27 927A60CLG	100	10.5	1521	144	Only with specific dimmers	90	2200-2700	15.000	60	108	D	929003011502	32497800
	3 MASVLE LEDBulbD10.5-100W B22A60 927FRGUK	100	10.5	1521	144	Yes	90	2700	15.000	60	107	D	929003011899	32503601

LED bulbs

MASTER UltraEfficient LED bulb - Continued

www.philips.com/ledlamps



10 /6 PACK

E27

	Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W			K	Hrs.					
NEW	1 MAS LEDBulbND4-60W E27 840 A60 CL G UE	60	4	840	210	No	80	4000	50.000	60	104	A	929003623902	18853200
NEW	2 MAS LEDBulbND4-60W E27 840 A60 FR G UE	60	4	840	210	No	80	4000	50.000	60	104	A	929003624102	28428900
NEW	2 MAS LEDBulbND4-60W E27 840 A60 FR G UE	60	4	840	210	No	80	4000	50.000	60	105	A	929003480102	43581000
NEW	3 MAS LEDBulbND4-60W E27 840 G95 CL G UE	60	4	840	210	No	80	4000	50.000	95	140	A	929003642602	20278800
NEW	4 MAS LEDBulbND5.2-75W E27 827 A60 CL G UE	75	5.2	1095	210	No	80	2700	50.000	60	104	A	929003624302	18861700
NEW	2 MAS LEDBulbND5.2-75W E27 827 A60 FR G UE	75	5.2	1095	210	No	80	2700	50.000	60	104	A	929003624502	18865500
NEW	4 MAS LEDBulbND5.2-75W E27 830 A60 CL G UE	75	5.2	1095	210	No	80	3000	50.000	-	-	A	929003703302	25420600
NEW	2 MAS LEDBulbND5.2-75W E27 830 A60 FR G UE	75	5.2	1095	210	No	80	3000	50.000	-	-	A	929003703502	25424400
NEW	5 MAS LEDBulbND5.2-75W E27 830A70 CLG UE	75	5.2	1095	210	No	80	3000	50.000	70	127	A	929003480402	43587200
NEW	6 MAS LEDBulbND5.2-75W E27 840 A60 CL G UE	75	5.2	1095	210	No	80	4000	50.000	60	104	A	929003624702	18869300
NEW	2 MAS LEDBulbND5.2-75W E27 840 A60 FR G UE	75	5.2	1095	210	No	80	4000	50.000	60	104	A	929003624902	18873000
NEW	5 MAS LEDBulbND5.2-75W E27 840A70 CLG UE	75	5.2	1095	210	No	80	4000	50.000	70	127	A	929003480502	43589600
NEW	7 MAS LEDBulbND7.3-100W E27 827 A60 CL GUE	100	7.3	1535	210	No	80	2700	50.000	60	104	A	929003625102	18877800
NEW	2 MAS LEDBulbND7.3-100W E27 827 A60 FR GUE	100	7.3	1535	210	No	80	2700	50.000	60	104	A	929003625302	18881500
NEW	7 MAS LEDBulbND7.3-100W E27 830 A60 CL GUE	100	7.3	1535	210	No	80	3000	50.000	-	-	A	929003703702	25428200
NEW	2 MAS LEDBulbND7.3-100W E27 830 A60 FR GUE	100	7.3	1535	210	No	80	3000	50.000	-	-	A	929003703902	25432900
NEW	8 MAS LEDBulbND7.3-100W E27 840 A60 CL GUE	100	7.3	1535	210	No	80	4000	50.000	60	104	A	929003625502	18885300
NEW	2 MAS LEDBulbND7.3-100W E27 840 A60 FR GUE	100	7.3	1535	210	No	80	4000	50.000	60	104	A	929003625702	18889100
NEW	9 MAS LEDBulbND7.3-100WE27830 A70 CLG UE	100	7.3	1535	210	No	80	3000	50.000	70	127	A	929003480602	43591900
NEW	10 MAS LEDBulbND7.3-100WE27830 A70 FRG UE	100	7.3	1535	210	No	80	3000	50.000	70	127	A	929003480202	43583400
NEW	9 MAS LEDBulbND7.3-100WE27840 A70 CLG UE	100	7.3	1535	210	No	80	4000	50.000	70	127	A	929003480702	43593300
NEW	10 MAS LEDBulbND7.3-100WE27840 A70 FRG UE	100	7.3	1535	210	No	80	4000	50.000	70	127	A	929003480302	43585800

LED candles & lusters

Candle LED

www.philips.com/ledlamps



6 /4 PACK E14

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 LED 7W T25 E14 WW FR ND 1SRT6	7	0.9	70	77	240	No	80	2700	15.000	25	59	G	929002401355	77169000
2 LED 15W T25 E14 WW FR ND RF 1SRT6	15	1.7	150	88	240	No	80	2700	15.000	25	59	F	929001325755	77193501
3 LED 25W T25 E14 WW FR ND 1SRT4	25	3.2	250	78	160	No	80	2700	15.000	25	71	G	929001325855	77195900

SceneSwitch LEDbulbs

www.philips.com/ledlamps



4 PACK E14

Product Type	LED	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	lm/W			K	Hrs.					
LEDClassic SSW 40W B35 E14 WW CLND 1SRT4	1-2.5-5	94	No	80	2700-2500-2200	15.000	35.5	106	F	929001888855	77215400

LED candles & lusters

CorePro GLASS LED candles and lusters

www.philips.com/ledlamps



10 PACK

B22/E14/E27

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.					
1 CorePro LEDCandleND 2-25W B35 B22 827CLG	25	2	250	125	No	80	2700	15.000	35	93	E	929001815692	34724300
2 CorePro LEDCandleND 2-25W E14B35 827CL G	25	2	250	125	No	80	2700	15.000	35	97	E	929001238392	37757800
1 CorePro LEDCandleND2-25W B22 827 B35 CLG	25	2	250	125	No	80	2700	15.000	35	94	E	929002023992	34736600
3 CorePro LEDCandleND2-25W E14BA35 827CL G	25	2	250	125	No	80	2700	15.000	35	123	E	929001238492	37759200
4 CorePro LEDCandleND2-25W ST35 E14 827CLG	25	2	250	125	No	80	2700	15.000	35	97	E	929001238592	34772400
5 CorePro LEDLusterND2-25W P45 E14 827 CLG	25	2	250	125	No	80	2700	15.000	45	80	E	929001238692	34774800
6 CorePro LEDLusterND2-25W P45 E27 827 CLG	25	2	250	125	No	80	2700	15.000	45	78	E	929001238792	34776200
7 CorePro LEDCandle ND 2.2-25W B35 E14 FRG	25	2.2	250	113	No	80	2700	15.000	35	97	E	929001345292	34679600
8 CorePro LEDCandleND 2.2-25W BA35 E14 FRG	25	2.2	250	113	No	80	2700	15.000	35	123	E	929001345892	34685700
9 CorePro LEDCandleND2.2-25W E14 840B35CLG	25	2.2	250	113	No	80	4000	15.000	35	97	E	929002023792	34734200
10 CorePro LEDLuster ND 2.2-25W P45 E14 FRG	25	2.2	250	113	No	80	2700	15.000	45	80	E	929001345492	34681900
11 CorePro LEDLuster ND 2.2-25W P45 E27 FRG	25	2.2	250	113	No	80	2700	15.000	45	78	E	929001345692	34683300
12 CorePro LEDLusterND2.2-25W E14 840P45CLG	25	2.2	250	113	No	80	4000	15.000	45	80	E	929002024092	34738000
13 CorePro LEDCandleND4.3-40W B22 827B35CLG	40	4.3	470	109	No	80	2700	15.000	35	93	F	929001889992	34728100
14 CorePro LEDCandleND4.3-40W E14 827B35CLG	40	4.3	470	109	No	80	2700	15.000	35	97	F	929001889792	34726700

LED candles & lusters



10 PACK

B22/E14/E27

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.					
1 CorePro LEDCandleND4.3-40W E14 827B35FRG	40	4.3	470	109	No	80	2700	15.000	35	97	F	929001345392	34718200
2 CorePro LEDCandleND4.3-40W E14 840B35CLG	40	4.3	470	109	No	80	4000	15.000	35	97	F	929002024392	34740300
3 CorePro LEDLusterND4.3-40W E14 827P45CLG	40	4.3	470	109	No	80	2700	15.000	45	82	F	929001890492	34730400
4 CorePro LEDLusterND4.3-40W E14 827P45FRG	40	4.3	470	109	No	80	2700	15.000	45	80	F	929001345592	34720500
5 CorePro LEDLusterND4.3-40W E14 840P45CLG	40	4.3	470	109	No	80	4000	15.000	45	80	F	929002024692	34742700
6 CorePro LEDLusterND4.3-40W E27 827P45CLG	40	4.3	470	109	No	80	2700	15.000	45	82	F	929001890592	34732800
7 CorePro LEDLusterND4.3-40W E27 827P45FRG	40	4.3	470	109	No	80	2700	15.000	45	78	F	929001345792	34722900
8 CoreProLEDCandleND4.3-40WE14 827B35CLGUK	40	4.3	470	109	No	80	2700	15.000	35	97	F	929001889719	34726701
9 CorePro LEDCandle ND6.5-60W B35E14827CLG	60	6.5	806	124	No	80	2700	15.000	35	97	E	929002028092	34746500
10 CorePro LEDCandleND6.5-60W B35 E14827FRG	60	6.5	806	124	No	80	2700	15.000	35	97	E	929002028292	34750200
9 CorePro LEDCandleND6.5-60W B35 E14840CLG	60	6.5	806	124	No	80	4000	15.000	35	97	E	929002028192	34748900
10 CorePro LEDCandleND6.5-60W B35E14 865FRG	60	6.5	806	124	No	80	6500	15.000	35	97	E	929002028492	34754000
10 CorePro LEDCandleND6.5-60WB35 E14 840FRG	60	6.5	806	124	No	80	4000	15.000	35	97	E	929002028392	34752600
11 CorePro LEDLusterND6.5-60W P45 E14827CLG	60	6.5	806	124	No	80	2700	15.000	45	80	E	929002028592	34756400
4 CorePro LEDLusterND6.5-60W P45 E14827FRG	60	6.5	806	124	No	80	2700	15.000	45	80	E	929002028792	34760100
11 CorePro LEDLusterND6.5-60W P45 E14840CLG	60	6.5	806	124	No	80	4000	15.000	45	80	E	929002028692	34758800
4 CorePro LEDLusterND6.5-60W P45 E14840FRG	60	6.5	806	124	No	80	4000	15.000	45	80	E	929002028892	34762500
4 CorePro LEDLusterND6.5-60W P45 E14865FRG	60	6.5	806	124	No	80	6500	15.000	45	80	E	929002028992	34764900
12 CorePro LEDLusterND6.5-60W P45 E27827CLG	60	6.5	806	124	No	80	2700	15.000	45	78	E	929002029092	34766300
7 CorePro LEDLusterND6.5-60W P45 E27827FRG	60	6.5	806	124	No	80	2700	15.000	45	78	E	929002029292	34768700
7 CorePro LEDLusterND6.5-60W P45 E27840FRG	60	6.5	806	124	No	80	4000	15.000	45	78	E	929002029392	34770000

LED candles & lusters

CorePro Plastic LEDcandles & lusters www.philips.com/ledlamps



10 PACK

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.					
1 CorePro candle ND 2.8-25W E14 827 B35 FR	25	2.8	250	89	No	80	2700	15.000	35	106	F	929002966802	31240100
1 CorePro candle ND 2.8-25W E14 840 B35 FR	25	2.8	250	89	No	80	4000	15.000	35	106	F	929002967402	31246300
2 CorePro lustre ND 2.8-25W E14 827 P45 FR	25	2.8	250	89	No	80	2700	15.000	35	106	F	929002967102	31244900
2 CorePro lustre ND 2.8-25W E14 840 P45 FR	25	2.8	250	89	No	80	4000	15.000	45	88	F	929002967702	31248700
3 CorePro lustre ND 2.8-25W E27 827 P45 FR	25	2.8	250	89	No	80	2700	15.000	45	88	F	929002966902	31242500
1 CorePro candle ND 5-40W E14 827 B35 FR	40	5	470	94	No	80	2700	15.000	45	87	F	929002968402	31250000
1 CorePro candle ND 5-40W E14 840 B35 FR	40	5	470	94	No	80	4000	15.000	38	114	F	929002968802	31254800
1 CorePro candle ND 5-40W E14 865 B35 FR	40	5	470	94	No	80	6500	15.000	35	106	F	929002969202	31258600
2 CorePro lustre ND 5-40W E14 827 P45 FR	40	5	470	94	No	80	2700	15.000	45	87	F	929002969602	31264700
2 CorePro lustre ND 5-40W E14 840 P45 FR	40	5	470	94	No	80	4000	15.000	45	88	F	929002970002	31268500
2 CorePro lustre ND 5-40W E14 865 P45 FR	40	5	470	94	No	80	6500	15.000	45	88	F	929002970402	31272200
4 Corepro Lustre ND 5-40W E27 827 P45 FR	40	5	470	94	No	80	2700	15.000	45	88	F	929002969402	31262300
5 CorePro candle ND 7-60W E14 827 B38 FR	60	7	806	115	No	80	2700	15.000	38	114	E	929002972502	31296800
5 CorePro candle ND 7-60W E14 840 B38 FR	60	7	806	115	No	80	4000	15.000	38	114	E	929002972702	31298200
5 CorePro candle ND 7-60W E14 865 B38 FR	60	7	806	115	No	80	6500	15.000	48	93	E	929002972902	31300200
6 CorePro lustre ND 7-60W E14 827 P48 FR	60	7	806	115	No	80	2700	15.000	48	93	E	929002973102	31304000
6 CorePro lustre ND 7-60W E14 840 P48 FR	60	7	806	115	No	80	4000	15.000	48	95	E	929002973302	31308800
6 CorePro lustre ND 7-60W E14 865 P48 FR	60	7	806	115	No	80	6500	15.000	35	106	E	929002973502	31310100
7 CorePro lustre ND 7-60W E27 827 P48 FR	60	7	806	115	No	80	2700	15.000	48	95	E	929002973002	31302600
7 CorePro lustre ND 7-60W E27 840 P48 FR	60	7	806	115	No	80	4000	15.000	48	95	E	929002973202	31306400

LED candles & lusters

CorePro Plastic LED Specialties

www.philips.com/ledlamps



12 PACK E14

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
Corepro LED T25 ND 1.7-15W E14 827	15	1.7	150	88	240	No	80	2700	15.000	25	59	F	929001325702	38986100

MASTER UltraEfficient LED candles and lusters

www.philips.com/ledlamps




10 PACK

	Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W			K	Hrs.					
NEW	1 MAS LEDCandleND2.3-40W E14 827 B35CL GUE	40	2.3	485	210	No	80	2700	50.000	35	111	A	929003625902	18893800
NEW	2 MAS LEDCandleND2.3-40W E14 830B35 CLG UE	40	2.3	485	210	No	80	3000	50.000	35	125	A	929003480802	43595700
NEW	3 MAS LEDCandleND2.3-40W E14 840 B35CL GUE	40	2.3	485	210	No	80	4000	50.000	35	111	A	929003626002	18895200
NEW	2 MAS LEDCandleND2.3-40W E14 840B35 CLG UE	40	2.3	485	210	No	80	4000	50.000	35	125	A	929003480902	43597100
NEW	4 MAS LEDLusterND2.3-40W E14 827 P45CL GUE	40	2.3	485	210	No	80	2700	50.000	45	99	A	929003626102	18897600
NEW	5 MAS LEDLusterND2.3-40W E14 840 P45CL GUE	40	2.3	485	210	No	80	4000	50.000	45	99	A	929003626402	18903400
NEW	6 MAS LEDLusterND2.3-40W E27 827 P45CL GUE	40	2.3	485	210	No	80	2700	50.000	45	78	A	929003626202	18899000
NEW	7 MAS LEDLusterND2.3-40W E27 840 P45CL GUE	40	2.3	485	210	No	80	4000	50.000	45	78	A	929003626502	18905800

LED candles & lusters

MASTER Value Decorative LED candles and lusters www.philips.com/ledlamps



10 PACK

	Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	12NC	EOC code
		W	W	lm	lm/W			K	Hrs.				
NEW	1 MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G	15	2.5	136	54	Only with specific dimmers	80	1800	15.000	36	95	929002983202	31603400
NEW	2 MAS VLE LEDLusterD 2.6-15W E14 P45 SP G	15	2.6	136	52	Only with specific dimmers	80	1800	15.000	46	80	929002983302	31605800
	3 MAS VLE LEDBulbD 2.6-15W E27 GOLDP45SP G	15	2.6	136	52	Only with specific dimmers	80	1800	15.000	46	80	929002983402	31607200

LED candles & lusters

MASTER GLASS LED candles and lusters www.philips.com/ledlamps



10 PACK B22/B15/E14/E27

	Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W			K	Hrs.					
NEW	1 MAS LEDCandleDT2.5-25W B22 B35 CL G	25	2.5	340	136	Only with specific dimmers	90	2200-2700	25.000	35	94	D	929003071202	47773500
NEW	2 MAS LEDCandleDT2.5-25W E14 B35 CL G	25	2.5	340	136	Only with specific dimmers	90	2200-2700	25.000	35	97	D	929003011982	44935000
NEW	3 MAS LEDCandleDT2.5-25W E14 BA35 CL G	25	2.5	340	136	Only with specific dimmers	90	2200-2700	25.000	35	119	D	929003071302	47771100
NEW	4 MAS LEDLusterDT2.5-25W E14 927 P45CL G	25	2.5	340	136	Only with specific dimmers	90	2200-2700	25.000	45	80	D	929003012082	44937400
NEW	5 MAS LEDLusterDT2.5-25W E27 927 P45CL G	25	2.5	340	136	Only with specific dimmers	90	2200-2700	25.000	45	78	D	929003012182	44939800
NEW	6 MAS LEDCandleDT3.4-40W B15 927 B35CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	35	96	D	929003012582	44947300
NEW	7 MAS LEDCandleDT3.4-40W B22 927 B35CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	35	94	D	929003012482	44945900
NEW	8 MAS LEDCandleDT3.4-40W E14 927 B35CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	35	97	D	929003012282	44941100
NEW	9 MAS LEDCandleDT3.4-40W E14927 BA35CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	35	119	D	929003013082	44949700
NEW	10 MAS LEDCandleDT3.4-40W E27 927 B35CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	35	95	D	929003012382	44943500
NEW	8 MAS LEDCandleDT3.4-40WE14 927B35CLGUK	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	35	97	D	929003012242	46661600
NEW	11 MAS LEDLusterDT3.4-40W E14 927 P45CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	45	80	D	929003013182	44951000
NEW	12 MAS LEDLusterDT3.5-40W E27 927 P45CL G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	45	78	D	929003013282	44953400
NEW	13 MAS LEDLusterDT3.5-40W E27 927 P45FR G	40	3.4	470	138	Only with specific dimmers	90	2200-2700	25.000	45	78	D	929003013682	44955800
NEW	7 MAS LEDCandleDT5.9-60W B22 927 B35 CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	25.000	35	94	D	929003014082	44959600
NEW	8 MAS LEDCandleDT5.9-60W E14 927 B35 CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	25.000	35	97	D	929003013982	44957200
NEW	14 MAS LEDLusterDT5.9-60W B22 927 P45CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	25.000	45	77	D	929003014282	44963300
NEW	11 MAS LEDLusterDT5.9-60W E14 927 P45 CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	25.000	45	80	D	929003014182	44961900
NEW	12 MAS LEDLusterDT5.9-60W E27 927 P45CL G	60	5.9	806	136	Only with specific dimmers	90	2200-2700	25.000	45	78	D	929003014382	44965700

LED candles & lusters

MASTER Value GLASS LED candles and lusters

www.philips.com/ledlamps



10 PACK

B22/B15/E14/E27

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.					
1 MAS VLE LEDCandleDT2.5-25W E14 B35CL G	25	2.5	340	136	Only with specific dimmers	90	2200-2700	15.000	35	97	D	929003011902	32505000
2 MAS VLE LEDLusterDT2.5-25W E14 927P45CLG	25	2.5	340	136	Only with specific dimmers	90	2200-2700	15.000	45	80	D	929003012002	32507400
3 MAS VLE LEDLusterDT2.5-25W E27 927P45CLG	25	2.5	340	136	Only with specific dimmers	90	2200-2700	15.000	45	78	D	929003012102	32509800
4 MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	40	3.4	470	138	Only with specific dimmers	90	2700	15.000	35	97	D	929003059502	35543900
5 MAS VLE LEDCandleD3.4-40W E14 B35 927FRG	40	3.4	470	138	Only with specific dimmers	90	2700	15.000	35	97	D	929003059702	35545300
6 MAS VLE LEDCandleDT3.4-40W B15 927B35CLG	40	3.4	470	138	Only with specific dimmers	90	2200-2700	15.000	35	96	D	929003012502	32517300
7 MAS VLE LEDCandleDT3.4-40W B22 927B35CLG	40	3.4	470	138	Only with specific dimmers	90	2200-2700	15.000	35	94	D	929003012402	32515900
8 MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	40	3.4	470	138	Only with specific dimmers	90	2200-2700	15.000	35	97	D	929003012202	32511100
9 MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	40	3.4	470	138	Only with specific dimmers	90	2200-2700	15.000	35	119	D	929003013002	32519700
10 MAS VLE LEDCandleDT3.4-40W E27 927B35CLG	40	3.4	470	138	Only with specific dimmers	90	2200-2700	15.000	35	95	D	929003012302	32513500
11 MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	40	3.4	470	138	Only with specific dimmers	90	2700	15.000	45	80	D	929003060002	35547700
12 MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	40	3.4	470	138	Only with specific dimmers	90	2700	15.000	45	80	D	929003060202	35549100
13 MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	40	3.4	470	138	Only with specific dimmers	90	2700	15.000	45	78	D	929003060402	35551400
14 MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	40	3.4	470	138	Only with specific dimmers	90	2700	15.000	45	78	D	929003060602	35553800

LED candles & lusters



10 PACK

B22/B15/E14/E27

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W			K	Hrs.					
1 MAS VLE LEDLusterDT3.4-40W E14 927P45CLG	40	3.4	470	138	Only with specific dimmers	90	2200-2700	15.000	45	80	D	929003013102	32521000
2 MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	40	3.4	470	138	Yes	90	2200-2700	15.000	35	97	D	929003012298	32511101
3 MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	40	3.5	470	134	Yes	90	2200-2700	15.000	45	78	D	929003013202	38774400
4 MAS VLE LEDLusterDT3.5-40W E27 927P45FRG	40	3.5	470	134	Yes	90	2200-2700	15.000	45	78	D	929003013602	38800000

Real pros help their customers

realize ultra energy savings


Introducing the Philips MASTER LEDtube Ultra Efficient T8: our most energy-efficient LED tube yet

Are your customers worried about their energy costs?

With the new Philips Ultra Efficient LEDtube you have the perfect retrofit lamp to help your customers save energy and money with high-quality, long-lasting and ultra energy-efficient LED.

- Saves 44% in energy costs[1]
- Ultra long lifetime of 100,000 hours (at L70) — more than 2× longer[1]
- 210 lm/W ultra efficiency
- 10-year warranty

A-class rating[2] for ultra energy savings



The Philips MASTER LEDtube Ultra Efficient is also available with a class B energy rating.[2] **To learn more visit: www.philips.com/ledtube**

[1] Philips MASTER LEDtube UE compared to Philips CorePro LEDtube EM/mains Ultra Output operating on direct mains
[2] According to the updated European Energy Labelling regulation (09/2021)



Designed for you and the planet


Sustainability meets profitability

With Philips MASTER LEDtube Ultra Efficient you can offer your customers an innovative and value-adding product to minimize their energy consumption. And although ultra-efficient LED tubes require less maintenance and replacement, the higher investment of your customer will give you a higher profit per light point!

Real pros replace

CFL-ni lamps with an energy-efficient alternative

From 24 February 2023, manufacturers will no longer be able to make CFL-ni[1] lamps due to the RoHS[2] ban. Now's the time to make the switch to energy-efficient and long-lasting CorePro PL LED lamps. Upgrade your customers' lighting while lowering their costs!



Why switch to the CorePro PL LED lamp range now?

- Efficiency up to 140 lm/W
- Lifetime of up to 30,000 hours (at L70) reduces maintenance costs
- Simple lamp-for-lamp replacement
- Best value for money solution

Product overview



Click here to see all products


[1] CFL-ni: Compact fluorescent lamps non-integrated
[2] RoHS: Reduction of Hazardous Substances ban

Real pros swap T5 fluorescents for T5 LED tubes

Philips MASTER LEDtube InstantFit HF T5 is energy-efficient, dimmable and compatible with most ballasts



Product highlights



Safe installation
Pin safety for safe installation

True retrofit, true T5 tube
The 15.7 mm diameter ensures an accurate 1:1 fit

No bending
Glass design resists bending

Light quality
High light comfort with reduced glare

No flicker
Flicker-free design complies with 2024 SLR requirement (SVM<0.4)

Industry-leading ballast compatibility
Fixed output ballast
Intelligent/multi-watt ballast
Dimming ballast (DALI, 1-10V)

Typical use cases




Offices
Office space with dimming capability for comfortable light at any moment.



Industry
Increase your energy savings without any hassle.



Classroom
Optimize comfort by adjusting the light level for every task.



Retail
Optimize shelf lighting hassle-free with LED lighting.

Real pros know: One LED tube is all you need

Introducing the new Philips CorePro Universal Ultra Output T8. Your everyday all-round solution for an easy switch to LED.

New!
For a super easy switch to LED



Top reasons for making it your 1st choice

1 Universal compatibility
- Works with electromagnetic ballasts, electronic ballasts and direct mains
- No need to check ballast technology in advance, no double stocking

2 Ultra output and light quality
- Up to 3,500 lm output for similar brightness to fluorescent lamps
- Flicker-free light according to 2024 SLR requirement (SVM<0,4)

3 Higher efficiency and longer lifetime
- Luminous efficiency of 150 lm/W
- 50,000 hrs lifetime (at L70)
- High energy savings and lower maintenance mean short payback times

4 Hassle-free 1:1 replacement
- True retrofit, making it the fastest-to-install solution saving you time and money
- Fits straight into existing luminaires
- Available in many sizes and color temperatures

LED tubes

MASTER LEDtube T8 Ultra Efficient

www.philips.com/ledtube




10 PACK

	Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
NEW	MAS LEDtube 1200mm UE 11.9W 840 T8 EELA	36	11.9	2500	210	160	No	80	4000	100.000	25.8	1,200	A	929003482202	43166900
	MAS LEDtube 1200mm UE 13.5W 840 T8	36	13.5	2500	185	160	No	80	4000	75.000	25.8	1,200	B	929003067002	33972900
	MAS LEDtube 1200mm UE 13.5W 865 T8	36	13.5	2500	185	160	No	80	6500	75.000	25.8	1,200	B	929003067102	33974300
NEW	MAS LEDtube 1500mm UE 17.6W 840 T8 EELA	58	17.6	3700	210	160	No	80	4000	100.000	25.8	1,500	A	929003482302	43168300
	MAS LEDtube 1500mm UE 20W 840 T8	58	20	3700	185	160	No	80	4000	75.000	25.8	1,500	B	929003067202	33976700
	MAS LEDtube 1500mm UE 20W 865 T8	58	20	3700	185	160	No	80	6500	75.000	25.8	1,500	B	929003067302	33978100

LED tubes

MASTER LEDtube EM/Mains T8

www.philips.com/ledtube



10 /40 PACK

Product Type	Tradi tional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 MAS LEDtube 600mm HO 8W830 T8	18	8	1000	125	160	No	83	3000	75.000	25.78	600	E	929001307002	69747400
1 MAS LEDtube 600mm HO 8W840 T8	18	8	1050	131	160	No	83	4000	75.000	25.78	600	E	929001307102	69749800
1 MAS LEDtube 600mm HO 8W865 T8	18	8	1050	131	160	No	83	6500	75.000	25.78	600	E	929001307202	69751100
1 MAS LEDtube 900mm HO 12W 840 T8	30	12	1575	131	160	No	80	4000	75.000	25.78	900	E	929001298402	68708600
1 MAS LEDtube 900mm HO 12W 865 T8	30	12	1575	131	160	No	80	6500	75.000	25.78	900	E	929001298502	68710900
2 MAS LEDtube 1200mm HO 12.5W 830 T8	36	12.5	2000	160	160	No	80	3000	75.000	25.8	1,200	C	929001922602	59235600
2 MAS LEDtube 1200mm HO 12.5W 840 T8	36	12.5	2100	168	160	No	80	4000	75.000	25.8	1,200	C	929001922702	59237000
2 MAS LEDtube 1200mm HO 12.5W 865 T8	36	12.5	2100	168	160	No	80	6500	75.000	25.8	1,200	C	929001922802	59239400
3 MAS LEDtube 1200mm UO 14.7W 830 T8	36	14.7	2300	156	160	No	80	3000	75.000	25.8	1,200	D	929002998202	31656000
3 MAS LEDtube 1200mm UO 14.7W 840 T8	36	14.7	2500	170	160	No	80	4000	75.000	25.8	1,200	C	929002998302	31658400
3 MAS LEDtube 1200mm UO 14.7W 865 T8	36	14.7	2500	170	160	No	80	6500	75.000	25.8	1,200	C	929002998402	31660700
4 MAS LEDtube 1050mm 16W 830 T8	38	16	2300	143	160	No	80	3000	75.000	25.8	1,100	D	929001375602	72855000
2 MAS LEDtube 1050mm 16W 840 T8	38	16	2500	156	160	No	80	4000	75.000	25.8	1,100	D	929001961102	61602100
2 MAS LEDtube 1500mm HO 18.2W 830 T8	58	18.2	2900	159	160	No	80	3000	75.000	25.8	1,500	D	929001922902	59241700
2 MAS LEDtube 1500mm HO 18.2W 840 T8	58	18.2	3100	170	160	No	80	4000	75.000	25.8	1,500	C	929001923002	59243100
2 MAS LEDtube 1500mm HO 18.2W 865 T8	58	18.2	3100	170	160	No	80	6500	75.000	25.8	1,500	C	929001923102	59245500
3 MAS LEDtube 1500mm UO 21.7W 830 T8	58	21.7	3400	156	160	No	80	3000	75.000	25.8	1,500	D	929002998502	31662100
3 MAS LEDtube 1500mm UO 21.7W 840 T8	58	21.7	3700	170	160	No	80	4000	75.000	25.8	1,500	C	929002998602	31664500
3 MAS LEDtube 1500mm UO 21.7W 865 T8	58	21.7	3700	170	160	No	80	6500	75.000	25.8	1,500	C	929002998702	31666900
5 MASTER LEDtube Starter EMP GenIII	-	-	-	-	-	No	-	-	-	-	-	-	929003481702	48537200

LED tubes

MASTER Value LEDtube EM/mains T8

www.philips.com/ledtube



10 PACK

Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 MAS LEDtube VLE 600mm HO 8W 830 T8	18	8	1000	125	190	No	80	3000	60.000	25.8	600	E	929002021102	64679000
1 MAS LEDtube VLE 600mm HO 8W 840 T8	18	8	1050	131	190	No	80	4000	60.000	25.8	600	E	929002021202	64681300
1 MAS LEDtube VLE 600mm HO 8W 865 T8	18	8	1050	131	190	No	80	6500	60.000	25.8	600	E	929002021302	64683700
2 MAS LEDtube VLE 1200mm HO 14W 830 T8	36	14	2000	142	190	No	80	3000	60.000	25.8	1,200	D	929002021402	64685100
2 MAS LEDtube VLE 1200mm HO 14W 840 T8	36	14	2100	150	190	No	80	4000	60.000	25.8	1,200	D	929002021502	64687500
2 MAS LEDtube VLE 1200mm HO 14W 865 T8	36	14	2100	150	190	No	80	6500	60.000	25.8	1,200	D	929002021602	64689900
2 MAS LEDtube VLE 1200mm UO 15.5W 830 T8	36	15.5	2300	148	190	No	80	3000	60.000	25.8	1,200	D	929002997602	31680500
2 MAS LEDtube VLE 1200mm UO 15.5W 840 T8	36	15.5	2500	161	190	No	80	4000	60.000	25.8	1,200	C	929002997702	31682900
2 MAS LEDtube VLE 1200mm UO 15.5W 865 T8	36	15.5	2500	161	190	No	80	6500	60.000	25.8	1,200	C	929002997802	31684300
3 MAS LEDtube VLE 1500mm HO 20.5W 830 T8	58	20.5	2900	141	190	No	80	3000	60.000	25.8	1,500	D	929002021702	64691200
3 MAS LEDtube VLE 1500mm HO 20.5W 840 T8	58	20.5	3100	151	190	No	80	4000	60.000	25.8	1,500	D	929002021802	64693600
3 MAS LEDtube VLE 1500mm HO 20.5W 865 T8	58	20.5	3100	151	190	No	80	6500	60.000	25.8	1,500	D	929002021902	64695000
2 MAS LEDtube VLE 1500mm UO 23W 830 T8	58	23	3400	147	190	No	80	3000	60.000	25.8	1,500	D	929002997902	31686700
2 MAS LEDtube VLE 1500mm UO 23W 840 T8	58	23	3700	160	190	No	80	4000	60.000	25.8	1,500	C	929002998002	31688100
2 MAS LEDtube VLE 1500mm UO 23W 865 T8	58	23	3700	160	190	No	80	6500	60.000	25.8	1,500	C	929002998102	31690400

MASTER Value LEDtube Universal T8

www.philips.com/ledtube



10 PACK

Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
MAS LEDtube VLE UN 1200mm UO 15.5W830 T8	36	15.5	2300	148	190	No	80	3000	60.000	26	1,200	D	929002997002	31668300
MAS LEDtube VLE UN 1200mm UO 15.5W840 T8	36	15.5	2500	161	190	No	80	4000	60.000	26	1,200	C	929002997102	31670600
MAS LEDtube VLE UN 1200mm UO 15.5W865 T8	36	15.5	2500	161	190	No	80	6500	60.000	26	1,200	C	929002997202	31672000
MAS LEDtube VLE UN 1500mm UO 23W830 T8	58	23	3400	147	190	No	80	3000	60.000	26	1,500	D	929002997302	31674400
MAS LEDtube VLE UN 1500mm UO 23W840 T8	58	23	3700	160	190	No	80	4000	60.000	26	1,500	C	929002997402	31676800
MAS LEDtube VLE UN 1500mm UO 23W865 T8	58	23	3700	160	190	No	80	6500	60.000	26	1,500	C	929002997502	31678200

LED tubes

MASTER LEDtube InstantFit HF T8

www.philips.com/ledtube





10 /20 PACK

Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 MAS LEDtube HF 600mm HO 8W830 T8	18	8	1000	125	160	No	80	3000	75.000	25.8	600	E	929001393132	46640100
1 MAS LEDtube HF 600mm HO 8W840 T8	18	8	1050	131	160	No	80	4000	75.000	25.8	600	E	929001393232	46642500
1 MAS LEDtube HF 600mm HO 8W865 T8	18	8	1050	131	160	No	80	6500	75.000	25.8	600	E	929001393332	46644900
2 MAS LEDtube HF 1200mm 14W 833 T8 FOOD	36	14	1000	71	160	No	80	3300	60.000	25.6	1,200	-	929002479402	29616900
2 MAS LEDtube HF 1200mm HO 14W830 T8	36	14	2000	142	160	Yes - Check ballast compatibility	80	3000	75.000	25.8	1,200	E	929003553402	46688300
2 MAS LEDtube HF 1200mm HO 14W840 T8	36	14	2100	150	160	Yes - Check ballast compatibility	80	4000	75.000	25.8	1,200	D	929003553502	46684500
2 MAS LEDtube HF 1200mm HO 14W865 T8	36	14	2100	150	160	Yes - Check ballast compatibility	80	6500	75.000	25.8	1,200	D	929003553602	46686900
2 MAS LEDtube HF 1200mm UO 16W830 T8	36	16	2350	146	160	Yes - Check ballast compatibility	80	3000	75.000	25.8	1,200	D	929003554002	46700200
2 MAS LEDtube HF 1200mm UO 16W840 T8	36	16	2500	156	160	Yes - Check ballast compatibility	80	4000	75.000	25.8	1,200	D	929003554102	46696800
2 MAS LEDtube HF 1200mm UO 16W865 T8	36	16	2500	156	160	Yes - Check ballast compatibility	80	6500	75.000	25.8	1,200	D	929003554202	46698200
2 MAS LEDtube HF 1500mm HO 20W830 T8	58	20	2900	145	160	Yes - Check ballast compatibility	80	3000	75.000	25.8	1,500	E	929003553702	46694400
2 MAS LEDtube HF 1500mm HO 20W840 T8	58	20	3100	155	160	Yes - Check ballast compatibility	80	4000	75.000	25.8	1,500	D	929003553802	46690600
2 MAS LEDtube HF 1500mm HO 20W865 T8	58	20	3100	155	160	Yes - Check ballast compatibility	80	6500	75.000	25.8	1,500	D	929003553902	46692000
2 MAS LEDtube HF 1500mm UO 24W830 T8	58	24	3500	145	160	Yes - Check ballast compatibility	80	3000	75.000	25.8	1,500	D	929003554302	46706400
2 MAS LEDtube HF 1500mm UO 24W840 T8	58	24	3700	154	160	Yes - Check ballast compatibility	80	4000	75.000	25.8	1,500	D	929003554402	46702600
2 MAS LEDtube HF 1500mm UO 24W865 T8	58	24	3700	154	160	Yes - Check ballast compatibility	80	6500	75.000	25.8	1,500	D	929003554502	46704000

LED tubes

MASTER LEDtube InstantFit HF T5

www.philips.com/ledtube



10 PACK G5

	Product Type	Tradi tional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
	1 MAS LEDtube HF 600mm HE 8W 830 T5	14	8	1000	125	200	Yes - Check ballast compatibility	80	3000	60.000	15.5	600	E	929001390702	74323200
	1 MAS LEDtube HF 600mm HE 8W 840 T5	14	8	1050	131	200	Yes - Check ballast compatibility	80	4000	60.000	15.5	600	E	929001390802	74325600
	1 MAS LEDtube HF 600mm HE 8W 865 T5	14	8	1050	131	200	Yes - Check ballast compatibility	80	6500	60.000	15.5	600	E	929001390902	74327000
NEW	1 MAS LEDtube HF 600mm HO 10.5W 830 T5	24	10.5	1500	142	200	Yes - Check ballast compatibility	80	3000	60.000	15.5	600	E	929003596202	16307200
NEW	1 MAS LEDtube HF 600mm HO 10.5W 840 T5	24	10.5	1600	152	200	Yes - Check ballast compatibility	80	4000	60.000	15.5	600	D	929003596302	16309600
NEW	1 MAS LEDtube HF 600mm HO 10.5W 865 T5	24	10.5	1600	152	200	Yes - Check ballast compatibility	80	6500	60.000	15.5	600	D	929003596402	16311900
	1 MAS LEDtube HF 900mm HE 11.5W 830 T5	21	11.5	1600	139	200	Yes - Check ballast compatibility	80	3000	60.000	15.5	900	E	929003596802	16319500
	1 MAS LEDtube HF 900mm HE 11.5W 840 T5	21	11.5	1700	147	200	Yes - Check ballast compatibility	80	4000	60.000	15.5	900	D	929003596902	16321800
	1 MAS LEDtube HF 900mm HE 11.5W 865 T5	21	11.5	1700	147	200	Yes - Check ballast compatibility	80	6500	60.000	15.5	900	D	929003597002	16323200
	1 MAS LEDtube HF 1200mm HE 16.5W 830 T5	28	16.5	2300	139	200	Yes - Check ballast compatibility	80	3000	60.000	15.5	1,200	E	929001391002	74329400
	1 MAS LEDtube HF 1200mm HE 16.5W 840 T5	28	16.5	2500	151	200	Yes - Check ballast compatibility	80	4000	60.000	15.5	1,200	D	929001391102	74331700
	1 MAS LEDtube HF 1200mm HE 16.5W 865 T5	28	16.5	2500	151	200	Yes - Check ballast compatibility	80	6500	60.000	15.5	1,200	D	929001391202	74333100
NEW	1 MAS LEDtube HF 900mm HO 18.5W 830 T5	39	18.5	2600	140	200	Yes - Check ballast compatibility	80	3000	60.000	15.5	900	E	929003596502	16313300
NEW	1 MAS LEDtube HF 900mm HO 18.5W 840 T5	39	18.5	2800	151	200	Yes - Check ballast compatibility	80	4000	60.000	15.5	900	D	929003596602	16315700
NEW	1 MAS LEDtube HF 900mm HO 18.5W 865 T5	39	18.5	2800	151	200	Yes - Check ballast compatibility	80	6500	60.000	15.5	900	D	929003596702	16317100
	1 MAS LEDtube HF 1500mm HE 20W 830 T5	35	20	2800	140	200	Yes - Check ballast compatibility	80	3000	60.000	15.5	1,500	E	929001391302	74335500
	1 MAS LEDtube HF 1500mm HE 20W 840 T5	35	20	3000	150	200	Yes - Check ballast compatibility	80	4000	60.000	15.5	1,500	D	929001391402	74337900
	1 MAS LEDtube HF 1500mm HE 20W 865 T5	35	20	3000	150	200	Yes - Check ballast compatibility	80	6500	60.000	15.5	1,500	D	929001391502	74339300
	2 MAS LEDtube HF 1200mm HO 26W 830 T5 OE	54	26	3700	142	200	Yes - Check ballast compatibility	80	3000	60.000	15.5	1,200	E	929002352002	74951400
	2 MAS LEDtube HF 1200mm HO 26W 840 T5 OE	54	26	3900	150	200	Yes - Check ballast compatibility	80	4000	60.000	15.5	1,200	D	929002352102	74953800
	2 MAS LEDtube HF 1200mm HO 26W 865 T5 OE	54	26	3900	150	200	Yes - Check ballast compatibility	80	6500	60.000	15.5	1,200	D	929002352202	74955200
	2 MAS LEDtube HF 1500mm HO 26W 830 T5 OE	49	26	3700	142	200	Yes - Check ballast compatibility	80	3000	60.000	15.5	1,500	E	929002352302	74957600

OE: Office Enabled LED tube light with the following benefits:

- True Retrofit due to High Compatibility
- Dimmable (1-10V and Dali Ballast)
- Compatible with Multi- Watt ballasts
- Supports UGR 19 applications due to Glass Design with wider beam angle

Please visit the website for the compatibility list of dimmable and non-dimmable ballasts.

LED tubes

MASTER LEDtube InstantFit HF T5 - Continued

www.philips.com/ledtube





10 PACK G5

Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 MAS LEDtube HF 1500mm HO 26W 840 T5 OE	49	26	3900	150	200	Yes - Check ballast compatibility	80	4000	60.000	15.5	1,500	D	929002352402	74959000
1 MAS LEDtube HF 1500mm HO 26W 865 T5 OE	49	26	3900	150	200	Yes - Check ballast compatibility	80	6500	60.000	15.5	1,500	D	929002352502	74961300
2 MAS LEDtube HF 1500mm UO 36W 830 T5	80	36	5200	144	200	Yes - Check ballast compatibility	80	3000	60.000	15.5	1,500	E	929003153902	41905600
2 MAS LEDtube HF 1500mm UO 36W 840 T5	80	36	5600	155	200	Yes - Check ballast compatibility	80	4000	60.000	15.5	1,500	D	929003154002	41907000
2 MAS LEDtube HF 1500mm UO 36W 865 T5	80	36	5600	155	200	Yes - Check ballast compatibility	80	6500	60.000	15.5	1,500	D	929003154102	41909400

LED tubes

MASTER LEDtube Mains T5

www.philips.com/ledtube




10 PACK G5

	Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
	1 MAS LEDtube 600mm HE 8W 830 T5 EU	14	8	1000	125	200	No	80	3000	50.000	15.7	600	E	929003044102	33425000
	1 MAS LEDtube 600mm HE 8W 840 T5 EU	14	8	1050	131	200	No	80	4000	50.000	15.7	600	E	929003044202	33427400
	1 MAS LEDtube 600mm HE 8W 865 T5 EU	14	8	1050	131	200	No	80	6500	50.000	15.7	600	E	929003044302	33429800
NEW	1 MAS LEDtube 600mm HO 10.5W 830 T5	24	10.5	1500	142	200	No	80	3000	50.000	-	563.2	D	929003734302	27521800
NEW	1 MAS LEDtube 600mm HO 10.5W 840 T5	24	10.5	1600	152	200	No	80	4000	50.000	-	563.2	D	929003734402	27531700
NEW	1 MAS LEDtube 600mm HO 10.5W 865 T5	24	10.5	1600	152	200	No	80	6500	50.000	-	563.2	D	929003734502	27523200
NEW	1 MAS LEDtube 900mm HE 11.5W 830 T5 EU	21	11.5	1600	139	200	No	80	3000	50.000	15.7	900	D	929003734002	27062600
NEW	1 MAS LEDtube 900mm HE 11.5W 840 T5 EU	21	11.5	1700	147	200	No	80	4000	50.000	15.7	900	D	929003734102	27064000
NEW	1 MAS LEDtube 900mm HE 11.5W 865 T5 EU	21	11.5	1700	147	200	No	80	6500	50.000	15.7	900	D	929003734202	27066400
	1 MAS LEDtube 1200mm HE 16.5W 830 T5 EU	28	16.5	2300	139	200	No	80	3000	50.000	15.7	1,200	D	929003044402	33431100
	1 MAS LEDtube 1200mm HE 16.5W 840 T5 EU	28	16.5	2500	151	200	No	80	4000	50.000	15.7	1,200	D	929003044502	33433500
	1 MAS LEDtube 1200mm HE 16.5W 865 T5 EU	28	16.5	2500	151	200	No	80	6500	50.000	15.7	1,200	D	929003044602	33435900
NEW	1 MAS LEDtube 900mm HO 18.5W 830 T5	39	18.5	2600	140	200	No	80	3000	50.000	-	863.2	D	929003734602	27525600
NEW	1 MAS LEDtube 900mm HO 18.5W 840 T5	39	18.5	2800	151	200	No	80	4000	50.000	-	863.2	D	929003734702	27527000
NEW	1 MAS LEDtube 900mm HO 18.5W 865 T5	39	18.5	2800	151	200	No	80	6500	50.000	-	863.2	D	929003734802	27529400
	1 MAS LEDtube 1500mm HE 20W 830 T5 EU	35	20	2800	140	200	No	80	3000	50.000	15.7	1,500	D	929002421202	33437300
	1 MAS LEDtube 1500mm HE 20W 840 T5 EU	35	20	3000	150	200	No	80	4000	50.000	15.7	1,500	D	929002421302	33439700
	1 MAS LEDtube 1500mm HE 20W 865 T5 EU	35	20	3000	150	200	No	80	6500	50.000	15.7	1,500	D	929002421402	33441000
	1 MAS LEDtube 1200mm HO 26W 830 T5	54	26	3600	138	200	No	80	3000	50.000	15.5	1,200	D	929001908502	81921000
	1 MAS LEDtube 1200mm HO 26W 840 T5	54	26	3900	150	200	No	80	4000	50.000	15.5	1,200	D	929001908602	81923400
	1 MAS LEDtube 1200mm HO 26W 865 T5	54	26	3900	150	200	No	80	6500	50.000	15.5	1,200	D	929001908702	81925800
	1 MAS LEDtube 1500mm HO 26W 830 T5	49	26	3600	138	200	No	80	3000	50.000	15.5	1,500	D	929001908802	81929600
	1 MAS LEDtube 1500mm HO 26W 840 T5	49	26	3900	150	200	No	80	4000	50.000	15.5	1,500	D	929001908902	81931900
	1 MAS LEDtube 1500mm HO 26W 865 T5	49	26	3900	150	200	No	80	6500	50.000	15.5	1,500	D	929001909002	81933300
	2 MAS LEDtube 1500mm UO 36W 830 T5	80	36	5200	144	200	No	80	3000	50.000	15.5	1,500	D	929002474802	29050100
	2 MAS LEDtube 1500mm UO 36W 840 T5	80	36	5600	155	200	No	80	4000	50.000	15.5	1,500	D	929002474902	29052500
	2 MAS LEDtube 1500mm UO 36W 865 T5	80	36	5600	155	200	No	80	6500	50.000	15.5	1,500	D	929002475002	29054900

LED tubes

CorePro LEDtube EM/Mains T8

www.philips.com/ledtube



10 /20 PACK

	Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
NEW	1 CorePro LEDtube 600mm 8W 840 T8	18	8	800	100	240	No	80	4000	50.000	25.7	600	F	929003547202	45977900
NEW	1 CorePro LEDtube 600mm 8W 865 T8	18	8	800	100	240	No	80	6500	50.000	25.7	600	F	929003547302	45979300
NEW	1 CorePro LEDtube 600mm HO 8W 865 T8	18	8	900	112	240	No	80	6500	50.000	25.7	600	E	929003158702	42105900
	1 CorePro LEDtube 600mm 8W 830 T8	18	8	750	93	240	No	80	3000	50.000	25.7	600	F	929003577132	48638600
	1 CorePro LEDtube 600mm 8W 840 T8	18	8	800	100	240	No	80	4000	50.000	25.7	600	F	929003022102	32531900
	1 CorePro LEDtube 600mm 8W 865 T8	18	8	800	100	240	No	80	6500	50.000	25.7	600	F	929003022202	32533300
	1 CorePro LEDtube 600mm HO 8W 830 T8	18	8	850	106	240	No	80	3000	50.000	25.7	600	F	929003577402	48644700
	1 CorePro LEDtube 600mm HO 8W 840 T8	18	8	900	112	240	No	80	4000	50.000	25.7	600	E	929003158602	42103500
NEW	1 CorePro LEDtube 1200mm 15.5W 840 T8	36	15.5	1800	116	240	No	80	4000	50.000	25.7	1,200	E	929003519702	44807000
NEW	1 CorePro LEDtube 1200mm 15.5W 840 T8	36	15.5	1800	116	240	No	80	4000	50.000	25.7	1,200	E	929003519732	46954900
NEW	1 CorePro LEDtube 1200mm 15.5W 865 T8	36	15.5	1800	116	240	No	80	6500	50.000	25.7	1,200	E	929003519802	44809400
NEW	1 CorePro LEDtube 1200mm 15.5W 865 T8	36	15.5	1800	116	240	No	80	6500	50.000	25.7	1,200	E	929003519832	46956300
	1 CorePro LEDtube 1200mm 15.5W 830 T8	36	15.5	1700	109	240	No	80	3000	50.000	25.7	1,200	F	929003577232	48640900
NEW	1 CorePro LEDtube 1200mm HO 18W 840 T8	36	18	2000	111	240	No	80	4000	50.000	25.7	1,200	E	929001874932	46958700
NEW	1 CorePro LEDtube 1200mm HO 18W 865 T8	36	18	2000	111	240	No	80	6500	50.000	25.7	1,200	E	929001874832	47558800
	1 CorePro LEDtube 1200mm HO 18W 830 T8	36	18	1850	102	240	No	80	3000	50.000	25.7	1,200	F	929003577532	48646100
	1 CorePro LEDtube 1200mm HO 18W 840 T8	36	18	2000	111	240	No	80	4000	50.000	25.7	1,200	E	929001874902	80613500
	1 CorePro LEDtube 1200mm HO 18W 865 T8	36	18	2000	111	240	No	80	6500	50.000	25.7	1,200	E	929001874802	80611100
NEW	1 CorePro LEDtube 1500mm 20W 840 T8	58	20	2200	110	240	No	80	4000	50.000	25.7	1,500	E	929003547402	45981600
	1 CorePro LEDtube 1500mm 20W 830 T8	58	20	2050	102	240	No	80	3000	50.000	25.7	1,500	F	929003577332	48642300
	1 CorePro LEDtube 1500mm 20W 840 T8	58	20	2200	110	240	No	80	4000	50.000	25.7	1,500	E	929003022502	32539500
	1 CorePro LEDtube 1500mm 20W 865 T8	58	20	2200	110	240	No	80	6500	50.000	25.7	1,500	E	929003022602	32541800
	1 CorePro LEDtube 1500mm 20W 865 T8	58	20	2200	110	240	No	80	6500	50.000	25.7	1,500	E	929003547502	45983000
NEW	2 CorePro LEDtube 1800mm 21W 840 T8	70	21	3100	147	160	No	80	4000	50.000	25.8	1,800	D	929002998802	31692800
NEW	2 CorePro LEDtube 1800mm 21W830 T8	70	21	2900	138	160	No	80	3000	50.000	25.8	1,800	D	929003584702	49493000
	2 CorePro LEDtube 1800mm 21W 865 T8	70	21	3100	147	160	No	80	6500	50.000	25.8	1,800	D	929003561802	47381200
	1 CorePro LEDtube 1200mm UO 21.5W 830 T8	36	21.5	2250	104	240	No	80	3000	50.000	25.7	1,200	F	929003577702	48650800
	1 CorePro LEDtube 1200mm UO 21.5W 840 T8	36	21.5	2400	111	240	No	80	4000	50.000	25.7	1,200	E	929003154202	41897400
	1 CorePro LEDtube 1200mm UO 21.5W 865 T8	36	21.5	2400	111	240	No	80	6500	50.000	25.7	1,200	E	929003154302	41899800
NEW	1 CorePro LEDtube 1500mm HO 24W 840 T8	58	24	2700	112	240	No	80	4000	50.000	25.7	1,500	E	929001875132	46960000

LED tubes



10 /20 PACK

	Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
NEW	CorePro LEDtube 1500mm HO 24W 865 T8	58	24	2700	112	240	No	80	6500	50.000	25.7	1,500	E	929001875032	47560100
	CorePro LEDtube 1500mm HO 24W 830 T8	58	24	2500	104	240	No	80	3000	50.000	25.7	1,500	F	929003577632	48648500
	CorePro LEDtube 1500mm HO 24W 840 T8	58	24	2700	112	240	No	80	4000	50.000	25.7	1,500	E	929001875102	80617300
	CorePro LEDtube 1500mm HO 24W 865 T8	58	24	2700	112	240	No	80	6500	50.000	25.7	1,500	E	929001875002	80615900
NEW	CorePro LEDtube 1500mm UO 31.5W 830 T8	58	31.5	3320	105	240	No	80	3000	50.000	25.7	1,500	F	929003577802	48652200
	CorePro LEDtube 1500mm UO 31.5W 840 T8	58	31.5	3500	111	240	No	80	4000	50.000	25.7	1,500	E	929003154402	41901800
	CorePro LEDtube 1500mm UO 31.5W 865 T8	58	31.5	3500	111	240	No	80	6500	50.000	25.7	1,500	E	929003154502	41903200

LED tubes

CorePro LED tube Universal T8

www.philips.com/ledtube



10 /20 PACK

Product Type	Traditional	LED	Lumen Output	Efficiency	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
CorePro LEDtube UN 600mm HO 8W830 T8	18	8	850	106	240	No	80	3000	50.000	25.7	600	F	929002419802	78277100
CorePro LEDtube UN 600mm HO 8W840 T8	18	8	900	112	240	No	80	4000	50.000	25.7	600	E	929002419902	78279500
CorePro LEDtube UN 600mm HO 8W865 T8	18	8	900	112	240	No	80	6500	50.000	25.7	600	E	929002420002	78281800
NEW CorePro LEDtube UN 1200mm UO 15.5W830 T8	36	15.5	2200	141	240	No	80	3000	50.000	26	1,200	D	929003648102	19996500
NEW CorePro LEDtube UN 1200mm UO 15.5W840 T8	36	15.5	2400	154	240	No	80	4000	50.000	26	1,200	D	929003648202	19998900
NEW CorePro LEDtube UN 1200mm UO 15.5W865 T8	36	15.5	2400	154	240	No	80	6500	50.000	26	1,200	D	929003648302	20000500
CorePro LEDtube UN 1200mm HO 18W830 T8	36	18	1850	102	240	No	80	3000	50.000	27.9	1,200	F	929001869202	80166600
CorePro LEDtube UN 1200mm HO 18W840 T8	36	18	2000	111	240	No	80	4000	50.000	27.9	1,200	E	929001869302	80168000
CorePro LEDtube UN 1200mm HO 18W865 T8	36	18	2000	111	240	No	80	6500	50.000	27.9	1,200	E	929001869402	80170300
CorePro LEDtube UN 1500mm HO 23W830 T8	58	23	2500	108	240	No	80	3000	50.000	27.9	1,500	F	929001869502	80172700
CorePro LEDtube UN 1500mm HO 23W840 T8	58	23	2700	117	240	No	80	4000	50.000	27.9	1,500	E	929001869602	80174100
CorePro LEDtube UN 1500mm HO 23W865 T8	58	23	2700	117	240	No	80	6500	50.000	27.9	1,500	E	929001869702	80176500
CorePro LEDtube UN 1500mm UO 23W830 T8	58	23	3200	139	240	No	80	3000	50.000	26	1,500	D	929003648402	20002900
CorePro LEDtube UN 1500mm UO 23W840 T8	58	23	3500	152	240	No	80	4000	50.000	26	1,500	D	929003648502	20004300
CorePro LEDtube UN 1500mm UO 23W865 T8	58	23	3500	152	240	No	80	6500	50.000	26	1,500	D	929003648602	20006700

LED PL-lamps

CorePro LED PLC 2P

www.philips.com/ledlamps



10 PACK G24D

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 CorePro LED PLC 4.5W 830 2P G24d-1	13	4.5	475	105	120	No	83	3000	30.000	24.3	100	F	929001350702	70659600
1 CorePro LED PLC 4.5W 840 2P G24d-1	13	4.5	500	111	120	No	83	4000	30.000	24.3	100	F	929001350802	70661900
2 CorePro LED PLC 6.5W 830 2P G24d-2	18	6.5	650	92.31	120	No	83	3000	30.000	24.3	100	F	929001201402	54127200
2 CorePro LED PLC 6.5W 840 2P G24d-2	18	6.5	700	92.31	120	No	83	4000	30.000	24.3	100	F	929001201502	54129600
3 CorePro LED PLC 8.5W 830 2P G24d-3	26	8.5	950	105.88	120	No	83	3000	30.000	24.3	200	F	929001201202	54123400
3 CorePro LED PLC 8.5W 840 2P G24d-3	26	8.5	1000	105.88	120	No	83	4000	30.000	24.3	200	F	929001201302	54125800

CorePro LED PLC 4P

www.philips.com/ledlamps



10 PACK G24Q

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 CorePro LED PLC 4.5W 830 4P G24q-1	13	4.5	475	105.56	120	No	83	3000	30.000	24.3	100	F	929001351002	70663300
1 CorePro LED PLC 4.5W 840 4P G24q-1	13	4.5	500	111.11	120	No	83	4000	30.000	24.3	100	F	929001351102	70665700
2 CorePro LED PLC 6.5W 830 4P G24q-2	18	6.5	650	92.31	120	No	83	3000	30.000	24.3	100	F	929001201002	54119700
2 CorePro LED PLC 6.5W 840 4P G24q-2	18	6.5	700	92.31	120	No	83	4000	30.000	24.3	100	F	929001201102	54121000
3 CorePro LED PLC 9W 830 4P G24q-3	26	9	950	100	120	No	83	3000	30.000	24.3	200	F	929001200802	54115900
3 CorePro LED PLC 9W 840 4P G24q-3	26	9	1000	100	120	No	83	4000	30.000	24.3	200	F	929001200902	54117300

LED PL-lamps

CorePro LED PLS

www.philips.com/ledlamps




20 PACK G23

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
CorePro LED PLS 5W 830 2P G23	11	5	520	104	120	No	82	3000	30.000	15.8	170	F	929001926302	59666800
CorePro LED PLS 5W 840 2P G23	11	5	550	110	120	No	82	4000	30.000	15.8	170	F	929001926402	59668200

CorePro LED PLL

www.philips.com/ledlamps



10 PACK 2G11

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 CorePro LED PLL HF 16.5W 830 4P 2G11	36	16.5	2000	121	160	No	83	3000	30.000	43.6	400	E	929001381502	73966200
1 CorePro LED PLL HF 16.5W 840 4P 2G11	36	16.5	2100	127	160	No	83	4000	30.000	43.6	405	E	929001381602	73974700
1 CorePro LED PLL HF 16.5W 865 4P 2G11	36	16.5	2100	127	160	No	83	6500	30.000	43.6	400	E	929001381702	73976100
2 CorePro LED PLL HF 24W 830 4P 2G11	55	24	3200	133	160	No	83	3000	30.000	17	540	E	929001920402	82839700
2 CorePro LED PLL HF 24W 840 4P 2G11	55	24	3400	141	160	No	83	4000	30.000	17	540	E	929001920502	82841000
2 CorePro LED PLL HF 24W 865 4P 2G11	55	24	3400	141	160	No	83	6500	30.000	17	540	E	929001920602	82843400

Philips TrueForce

Urban



TrueForce Core LED HPL



MASTER LED HID HPL



TrueForce LED HPL

Retail



TrueForce Core LED HPL



MASTER LED HID HPL



TrueForce LED highbay universal HPI



CorePro LED highbay (HPI)

Industry



TrueForce Core LED highbay HPL



TrueForce LED highbay universal HPI



CorePro LED highbay (HPI)

Road & Street



TrueForce Core LED SON-T



MASTER LED HID SON-T UE



TrueForce LED SON-T



TrueForce LED HPL



TrueForce LED SOX

Real pros replace
HID with "WOW"

Discover the range of Philips LED HPL lamps that offers a perfect LED solution to replace HID lamps for every budget and requirement

Are your customers concerned about rising energy cost? Do they want to convert their HID lamps to LED, but are afraid of the effort and cost of replacing their existing luminaires? With the Philips MASTER and CorePro LED HPL ranges, you can offer them all the benefits of LED combined with very attractive payback times. Both ranges provide greater energy efficiency, longer lifetimes and optimal light distribution. The new MASTER LED HPL is especially convincing with an extra long service life of 50,000 hours, resulting in further reduced maintenance and energy costs.



Perfect fit with existing HID luminaires

- Compact size
- Designed according to HID lamp size
- Low weight
- Compatible with direct mains

Suitable for indoor and outdoor applications

- –20 to 45°C operation temperature
- IP65*
- Surge protection 2KV

* Use suitable IP-rated sockets when installing in outdoor applications



Additional energy savings through mains only connection

Outstanding light quality

- High-power LED filament design for better light quality and uniformity
- High color rendering index CRI 80
- High lumen packages: 2,000/3,000/4,000 lm
- 3000K/4000K
- Long lifetime: 50,000 hrs (Philips MASTER LED HPL; at L70), 25,000 hrs (Philips CorePro LED HPL; at L70)



ED75
2,000/3,000 lm


ED90
4,000 lm

Philips MASTER LED SON-T Ultra Efficient

Introducing the first ultra-efficient Philips LED SON-T lamps to replace conventional HID

- Saves 43% in energy costs[1]
- Very long lifetime of 50,000 hours (at L70)
- 2.3 years potential payback time[1]
- 5-year warranty

Finally on the market: ultra-efficient LED SON-T lamps to replace conventional HID



- Impressive output: Maximum performance meets ultra-efficiency
- Up to 9,000 lm output thanks to mega-filament
- High efficiency GaN driver design
- E27/E40 end caps

Our Ultra Efficient Light

Discover our ultra-efficient solutions at **philips.com/ultraefficientprof**

Cost and CO_2 savings right from the start

	Conventional HID	MASTER LED SON-T UE
Energy savings 43%[1]	100W	42.8W
Lifetime at L70 Longer lifetime	20,000 hrs	50,000 hrs

Number of lamps	100
Burning hours/year	4,100 hrs
Energy costs	0.287 €/kWh

Replacement cost/year/lamp	€ 0.82
Lamp cost/year	€ 13.12

€ 7,046
Total potential savings/year

Make the sustainable choice: Over its lifetime, one new Philips MASTER LED SON-T UE can reduce CO_2 emission by up to 941 kg over its lifetime — which is equal to the emission absorbed by 42.7 trees![1,2]

[1] This calculation compares the Philips MASTER LED SON-T UE lamp with the Philips SON-T 100W E E40. The lights are assumed to be used for 4,100 hours annually. The average energy cost is 0.287 €/kWh. The average CO_2 emission is 0.28 kg/kWh. Both figures are calculated for the professional roads and streets application in Europe, valid in 2022, based on 47 European countries: Albania, Austria, Belarus, Belgium, Bosnia, Bulgaria, Croatia, Cyprus, Czech Republic, Denmark, England, Estonia, Finland, France, Germany, Greece, Hungary, Iceland, Ireland, Israel, Italy, Kazakhstan, Kosovo, Kyrgyzstan, Latvia, Lithuania, Luxembourg, Macedonia, Malta, Moldova, Montenegro, Netherlands, Norway, Poland, Portugal, Romania, Russia, Serbia, Slovakia, Slovenia, Spain, Sweden, Switzerland, Tajikistan, Turkmenistan, Ukraine, Uzbekistan. The data presented is an illustrative forecast based on a proprietary model developed by Signify to help customers understand the impact of lighting on the environment. Signify's "Green Switch conventional light point conversion model" uses input from numerous sources, references, and data points (available upon request) to generate a simulated view of a given market's energy consumption, but the accuracy of which cannot be verified. The thousand separator is a comma (,) and the decimal separator is a period (.).

[2] Based on European Environmental Agency, over one year a mature tree takes up about 22 kilograms of carbon dioxide from the atmosphere, and in exchange release oxygen (the source: https://www.eea.europa.eu/articles/forests-health-and-climate-change).

TrueForce LED

Trueforce Core LED SON-T

www.philips.com/trueforce-led-lamps



6 PACK E40/E27

	Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
NEW	1 TForce Core LED road 17W 727 E27 MV	-	17	2700	158	330	No	70	2700	25.000	38.5	168	D	929003730802	26771800
NEW	2 TForce Core LED road 26W 727 E27 MV	-	26	4000	153	330	No	70	2700	25.000	38.5	214	D	929003730902	26773200
NEW	3 TForce Core LED road 40W 727 E40 MV	-	40	6500	162	330	No	70	2700	25.000	47	229	C	929003731002	26775600
NEW	1 TForce Core LED road 17W 730 E27 MV	50	17	2800	164	-	No	70	3000	25.000	38	170	C	929002484802	31625600
NEW	1 TForce Core LED road 17W 740 E27 MV	50	17	3000	176	-	No	70	4000	25.000	38	170	C	929002484902	31627000
NEW	2 TForce Core LED road 26W 730 E27 MV	70	26	4200	161	-	No	70	3000	25.000	38	210	C	929002485002	31629400
	2 TForce Core LED road 26W 740 E27 MV	70	26	4500	173	-	No	70	4000	25.000	38	210	C	929002485102	31631700
	3 TForce Core LED road 40W 730 E40 MV	100	40	7200	180	-	No	70	3000	25.000	46	225	C	929002485202	31633100
	3 TForce Core LED road 40W 740 E40 MV	100	40	7500	187	-	No	70	4000	25.000	46	225	B	929002485302	31635500

TrueForce LED Industrial and Retail (Highbay – MH)

www.philips.com/trueforce-led-lamps



3 PACK E40

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
TForce LED HPI UN 95W E40 840 NB	250	95	13.000	136	60	No	80	4000	50.000	250	290	F	929002350702	75367200
TForce LED HPI UN 95W E40 840 WB	250	95	13.000	136	120	No	80	4000	50.000	250	290	E	929002350802	75369600
TForce LED HPI UN 140W E40 840 NB	400	140	20.000	142	60	No	80	4000	50.000	250	290	F	929002350902	75371900
TForce LED HPI UN 140W E40 840 WB	400	140	20.000	142	120	No	80	4000	50.000	250	290	D	929002351002	75373300

TrueForce LED

TrueForce LED Public (Urban/Road – HPL/SON)

www.philips.com/trueforce-led-lamps



6 PACK E40/E27

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 TForce LED HPL ND 28-21W E27 830	50	21	2850	135	360	No	80	3000	50.000	75	178	D	929002006102	63814600
1 TForce LED HPL ND 30-21W E27 840	50	21	3000	142	360	No	80	4000	50.000	75	178	D	929002006202	63816000
1 TForce LED HPL ND 38-28W E27 830	80	28	3800	135	360	No	80	3000	50.000	75	178	D	929002006302	63818400
1 TForce LED HPL ND 40-28W E27 840	80	28	4000	142	360	No	80	4000	50.000	75	178	D	929002006402	63820700
2 TForce LED HPL ND 57-42W E27 830	125	42	5700	135	360	No	80	3000	50.000	84	178	D	929002006502	63822100
3 TForce LED HPL ND 57-42W E40 830	125	42	5700	135	360	No	80	3000	50.000	84	191	D	929002006702	63826900
2 TForce LED HPL ND 60-42W E27 840	125	42	6000	142	360	No	80	4000	50.000	84	178	D	929002006602	63824500
3 TForce LED HPL ND 60-42W E40 840	125	42	6000	142	360	No	80	4000	50.000	84	191	D	929002006802	63828300

TrueForce LED

Trueforce CorePro LED HPL

www.philips.com/trueforce-led-lamps



6 PACK E40/E27

	Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
NEW	1 TForce Core LED HPL 13W E27 827 FR	-	13	1800	138	330	No	80	2700	25.000	76	183	D	929003731102	26777000
NEW	1 TForce Core LED HPL 18W E27 827 FR	-	18	2600	144	330	No	80	2700	25.000	76	183	D	929003731202	26779400
NEW	2 TForce Core LED HPL 26W E27 827 FR	-	26	3600	138	330	No	80	2700	25.000	91.5	248	D	929003731302	26781700
NEW	2 TForce Core LED HPL 36W E27 827 FR	-	36	5300	147	330	No	80	2700	25.000	91.5	248	D	929003731402	26783100
NEW	2 TForce Core LED HPL 36W E40 827 FR	-	36	5300	147	330	No	80	2700	25.000	91.5	234	D	929003731502	26785500
	1 TForce Core LED HPL 13W E27 830 FR	50	13	2000	153	300	No	80	3000	25.000	75	180	D	929002349702	75025100
	1 TForce Core LED HPL 13W E27 840 FR	50	13	2000	153	300	No	80	4000	25.000	75	180	D	929002349802	75027500
	1 TForce Core LED HPL 18W E27 830 FR	80	18	3000	166	300	No	80	3000	25.000	75	180	C	929002349902	75029900
	1 TForce Core LED HPL 18W E27 840 FR	80	18	3000	166	300	No	80	4000	25.000	75	180	C	929002350002	75031200
	2 TForce Core LED HPL 26W E27 830 FR	125	26	4000	153	300	No	80	3000	25.000	90	245	D	929002350102	75033600
	2 TForce Core LED HPL 26W E27 840 FR	125	26	4000	153	300	No	80	4000	25.000	90	245	D	929002350202	75035000
	2 TForce Core LED HPL 36W E27 830 FR	200	36	5500	152	300	No	80	3000	25.000	90	245	D	929002481202	29927600
	2 TForce Core LED HPL 36W E27 840 FR	200	36	6000	166	300	No	80	4000	25.000	90	245	C	929002481302	29929000
	3 TForce Core LED HPL 36W E40 830 FR	200	36	5500	152	300	No	80	3000	25.000	90	230	D	929002481402	29931300
	3 TForce Core LED HPL 36W E40 840 FR	200	36	6000	166	300	No	80	4000	25.000	90	230	C	929002481502	29933700

TrueForce LED

TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

www.philips.com/trueforce-led-lamps



6 PACK E40/E27

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 TForce Core HB MV ND 20W E27 830 G3	80	20	2600	130	150	No	80	3000	15.000	80	139	E	929002405702	78101900
1 TForce Core HB MV ND 20W E27 840 G3	80	20	2700	135	150	No	80	4000	15.000	80	139	D	929002405802	78103300
2 TForce Core HB MV ND 30W E27 830 G3	125	30	3700	123	180	No	80	3000	15.000	100	165	E	929002406302	78095100
2 TForce Core HB MV ND 30W E27 840 G3	125	30	4000	133	180	No	80	4000	15.000	100	165	E	929002406402	78097500
3 TForce Core HB MV ND 35W E27 830 G3	125	35	4800	137	180	No	80	3000	15.000	118	193	D	929002406602	78105700
3 TForce Core HB MV ND 35W E27 840 G3	125	35	5000	142	180	No	80	4000	15.000	118	193	D	929002406702	78107100
4 CorePro LED HPI MV 9Klm 65W 840 E40 100D	150	65	9000	138	100	No	80	4000	25.000	140	158	D	929003161602	42121900
NEW 5 CorePro LED HPI MV 15Klm 105W840E40 100D	250	105	15.000	142	100	No	80	4000	25.000	162	168	D	929003161702	42123300

TrueForce LED Public (Road/Area – SOX)

www.philips.com/trueforce-led-lamps



6 PACK B22

Product Type	Tradi tional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.					
1 MAS LED SOX M 2.5Klm 18W 840 B22 FR	26	18	2500	138	230	No	80	4000	50.000	52	312	D	929002496802	30562500
2 MAS LED SOX M 4Klm 28W 840 B22 FR	36	28	4000	142	230	No	80	4000	50.000	52	425	D	929002496902	30564900
2 MAS LED SOX M 5Klm 36W 840 B22 FR	55	36	5000	138	230	No	80	4000	50.000	52	425	D	929002497002	30566300

TrueForce LED

TrueForce LED Public (Road – SON)

www.philips.com/trueforce-led-lamps



6 PACK E40/E27

	Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W			K	Hrs.					
NEW	1 MAS LED SON-T EM 3.6Klm 23W 727 E27	50	23	3600	156	No	70	2700	70.000	61	200	D	929003467818	44903900
NEW	1 MAS LED SON-T EM 4Klm 23W 740 E27	50	23	4000	173	No	70	4000	70.000	61	200	C	929003467918	44905300
NEW	2 MAS LED SON-T IF 3.6Klm 23W 727 E27	50	23	3600	156	No	70	2700	70.000	61	200	D	929003467012	44887200
NEW	2 MAS LED SON-T IF 4Klm 23W 740 E27	50	23	4000	173	No	70	4000	70.000	61	200	C	929003467112	44889600
NEW	1 MAS LED SON-T EM 5.4Klm 34W 727 E27	70	34	5400	158	No	70	2700	70.000	61	200	D	929003468118	44909100
NEW	1 MAS LED SON-T EM 6Klm 34W 740 E27	70	34	6000	176	No	70	4000	70.000	61	200	C	929003468218	44911400
NEW	1 MAS LED SON-T IF 5.4Klm 34W 727 E27	70	34	5400	158	No	70	2700	70.000	61	200	D	929003467212	44891900
NEW	1 MAS LED SON-T IF 6Klm 34W 740 E27	70	34	6000	176	No	70	4000	70.000	61	200	C	929003467312	44893300
NEW	3 MAS LED SON-T EM 8.1Klm 50W 727 E40	100	50	8100	162	No	70	2700	70.000	71	262	C	929003468418	44915200
NEW	3 MAS LED SON-T EM 9Klm 50W 740 E40	100	50	9000	180	No	70	4000	70.000	71	262	C	929003468518	44917600
NEW	3 MAS LED SON-T IF 8.1Klm 50W 727 E40	100	50	8100	162	No	70	2700	70.000	71	262	D	929003467412	44895700
NEW	3 MAS LED SON-T IF 9Klm 50W 740 E40	100	50	9000	180	No	70	4000	70.000	71	262	C	929003467512	44897100
NEW	4 TForce LED Road 112-68W E40 730	100	68	11.200	164	No	70	3000	50.000	71	262	D	929002007602	63908200
NEW	4 TForce LED Road 120-68W E40 740	100	68	12.000	176	No	70	4000	50.000	71	262	C	929002007702	63910500
NEW	3 TForce LED Road 90-55W E40 740	100	55	9000	163	No	70	4000	50.000	71	262	D	929002007502	63906800
NEW	4 MAS LED SON-T EM 10.8Klm 65W 727 E40	150	65	10.800	166	No	70	2700	70.000	71	262	C	929003468718	44921300
NEW	4 MAS LED SON-T EM 12Klm 65W 740 E40	150	65	12.000	184	No	70	4000	70.000	71	262	C	929003468818	44923700
NEW	4 MAS LED SON-T IF 10.8Klm 65W 727 E40	150	65	10.800	166	No	70	2700	70.000	71	262	D	929003467612	44899500
NEW	4 MAS LED SON-T IF 12Klm 65W 740 E40	150	65	12.000	184	No	70	4000	70.000	71	262	C	929003467712	44901500

TrueForce LED

MASTER - LED HID SOX

www.philips.com/trueforce-led-lamps



6 PACK E40/E27

	Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	W	lm	lm/W	°			K	Hrs.					
NEW	1 MAS LED HPL M 2.8Klm 19W 830E27 FR G	80	19	2850	150	300	No	80	3000	50.000	71	186	D	929003530702	45193300
NEW	1 MAS LED HPL M 3Klm 19W 840 E27 FR G	80	19	3100	163	300	No	80	4000	50.000	71	186	C	929003530802	45195700
NEW	2 MAS LED HPL M 3.8Klm 24W 830 E27 FR G	125	24	3850	160	300	No	80	3000	50.000	91	249	C	929003530902	45197100
NEW	2 MAS LED HPL M 4Klm 24W 840 E27 FR G	125	24	4000	166	300	No	80	4000	50.000	91	249	C	929003531002	45199500
NEW	2 MAS LED HPL M 5.6Klm 33.5W 830 E27 FR G	200	33.5	5600	167	300	No	80	3000	50.000	91	249	C	929003531102	45201500
NEW	3 MAS LED HPL M 5.6Klm 33.5W 830 E40 FR G	200	33.5	5600	167	300	No	80	3000	50.000	91	238	C	929003531302	45205300
NEW	2 MAS LED HPL M 6Klm 33.5W 840 E27 FR G	200	33.5	6000	179	300	No	80	4000	50.000	91	249	C	929003531202	45203900
NEW	3 MAS LED HPL M 6Klm 33.5W 840 E40 FR G	200	33.5	6000	179	300	No	80	4000	50.000	91	238	C	929003531402	45207700

MASTER - LED HID SON-T - Ultra Efficient

www.philips.com/trueforce-led-lamps




6 PACK E40/E27

	Product Type	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	Lamp diameter	Total length	EEL	12NC	EOC code
		W	lm	lm/W	°			K	Hrs.					
NEW	1 MAS LED SON-T UE M 3.6Klm 19W 727 E27	19	3600	189	300	No	70	2700	50.000	47	237	B	929003677102	24029200
NEW	1 MAS LED SON-T UE M 4Klm 19W 740 E27	19	4000	210	300	No	70	4000	50.000	47	237	A	929003677202	24031500
NEW	2 MAS LED SON-T UE M 5.4Klm 28.5W 727 E27	28.5	5400	189	300	No	70	2700	50.000	47	237	B	929003677302	24033900
NEW	2 MAS LED SON-T UE M 6Klm 28.5W 740 E27	28.5	6000	210	300	No	70	4000	50.000	47	237	A	929003677402	24035300
NEW	3 MAS LED SON-T UE M 8Klm 42.8W 727 E40	42.8	8000	186	300	No	70	2700	50.000	53	236	B	929003677502	24037700
NEW	3 MAS LED SON-T UE M 9Klm 42.8W 740 E40	42.8	9000	210	300	No	70	4000	50.000	53	236	A	929003677602	24039100

All you need to know, right at your fingertips

We know that installation is about finding the right solutions. **Visit our webpage** created especially for installers and find:

- All latest product information
- Selector tools to help you select the right product for your customers
- Installation videos
- Training



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.