



T8 lamps

Lamp type	Wattage	Driver	12NC	USA	Europe/Asia	Only suitable for <8 switches per day	Lamps on driver
Actinic BL TL-D 15W /Master Actinic/Secura	15	HF-P_118_136 TL-D III	913713031566		X	X	1
		HF-P 218/236 TL-D III 220-240V 50/60Hz	913713031666		X		2
	15	HF-S_118_136 TL-D II	913713032166		X	X	2
		HF-S 218/236 TL-D II 220-240V 50/60Hz	913713032466				2
	15	EB-Ci 1-2 36W/1-4 18W	913713043180		X	X	1
		Advance IUUV-2S18-H1-LD	913710264002	X	X	X	1
		Advance IUUV-2S36-M2-LD	913710263902	X	X	X	1
Actinic BL TL-D 18W /Master Actinic/Secura	18	HF-P 2 22-42 PL-T_C_L_TL5C EII 220-240V	913700630866		X	X	3
TL-D 18W BLB	18	HF-P_118_136 TL-D III	913713031566		X	X	1
		HF-P 218/236 TL-D III 220-240V 50/60Hz	913713031666		X		2
	18	HF-S_118_136 TL-D II	913713032166		X	X	1
		HF-S 218/236 TL-D II 220-240V 50/60Hz	913713032466		X	X	2
	18	EB-Ci 1-2 36W/1-4 18W	913713043180		X		1
		Advance IUUV-2S18-H1-LD	913710264002	X	X	X	1
		Advance IUUV-2S36-M2-LD	913710263902	X	X	X	1
TL-D 25W/10		ICN-2S110-SC	913701212602	X		X	1
		ICN-2S54-90C-N	913701246102	X		X	1
Philips Actinic BL TL-DK 36W /Secura	36	IUV2S60	913710260202	X	X		1 or 2
TL-D 36W BLB 1SL/25	36	ICN2S39N	913701248802	X			1
		ICN2S54-90C-N	913701246102	X			2
		HF-P 118/136 TL-D II 220-240V 50/60Hz	913713031566		X		1
		HF-P 218/236 TL-D III 220-240V 50/60Hz	913713031666		X		2
		HF-S 118/136 TL-D II 220-240V 50/60Hz	913713032166		X		1
		HF-S 218/236 TL-D II 220-240V 50/60Hz	913713032466		X	X	2
		EB-Ci 2 36W/3-4 18W 100-240V	913713043314		X (*)		1 or 2
		EB-Ci 1-2 36W/1-4 18W 220-240V 50/60Hz	913713043180		X (*)		1

(*) for Asia only

TL mini lamps

Lamp type	Wattage	Driver	12NC	USA	Europe/Asia	Only suitable for <8 switches per day	Lamps on driver
Actinic BL TL Mini 6W ; Philips TL Mini 6W BLB	6	HF-M RED 109 SH TL/PL-S 230-240V	913700422866		X	X	1
Actinic BL TL Mini 8W / Secura ; Philips TL Mini 8W BLB	8	HF-M RED 109 SH TL/PL-S 230-240V	913700422866		X	X	1
Actinic BL TL Mini 11W	11	HF-S 158 TL-D II 220-240V 50/60Hz	913713032266		X	X	1
Actinic BL TL Mini 15W	15	HF-S 154 TL5 II 220-240V	913713033666		X	X	1
		HF-S 158 TL-D II 220-240V 50/60Hz	913713032266		X	X	1
TL Mini 4W BLB	4	HF-M RED 109 SH TL/PL-S 230-240V	913700422866		X	X	1



PL-S/PL-L lamps

Lamp type	Wattage	Driver	12NC	USA	Europe/Asia	Only suitable for <8 switches per day	Lamps on driver
Actinic BL PL-S 9W/10 ; PL-S 9W BLB 2P ; PL-S 9W/01 2P, PL-S 9W/52 2P		No Philips driver available - lamps work only on EM Drivers, not part of Philips portfolio	NA				
PL-S 8W/01 4P	9	ICF2S13H1LD	913710207502	X		X	2
Actinic BL PL-S 11W	11	HF-M BLUE 114 LH TL/PL-S/PL-C 230-240V	913700421766		X	X	1
Actinic BL PL-L 18W	18	HF-P 118/136 TL-D II 220-240V 50/60Hz	913713031566		X	X	1
		HF-P 2 22-42 PL-T_C_L_TL5C EII 220-240V	913700630866		X		3
		HF-P 218/236 TL-D III 220-240V 50/60Hz	913713031666		X		2
		HF-Pi 3_4 14_24 TL5_PL-L EII 220-240V	913700657666		X		3
		EB-Ci 2 36W_3-4 18W 100-240V	913713043314		X	X	1
		HF-M RED 124 SH TL_TL5_PLL	913700420666		X		1
Actinic BL PL-L 24W Actinic BL PL-L 36W / Secura	24	ICN2S39N - 8 switches per day	913701248802	X		X	1
		HF-M RED 124 SH TL/TL5/PL-L 230-240V	913700420666		X	X	1
		HF-S 118_136 TL-D II 220-240V 50_60Hz	913713032166		X	X	1
		HF-S 218/236 TL-D II 220-240V 50/60Hz	913713032466		X		2
	36	HF-P 218/236 TL-D III 220-240V 50/60Hz	913713031666		X		2
		HF-S 118_136 TL-D II 220-240V 50_60Hz	913713032166		X		1
		HF-S 218/236 TL-D II 220-240V 50/60Hz	913713032466		X	X	2
		Advance ICN-2S54-90C-N	913701246102	X	X	X	1 or 2

T12 lamps

Lamp type	Wattage	Driver	12NC	USA	Europe/Asia	Only suitable for <8 switches per day	Lamps on driver
TL 20W/12 RS ; TL 20W/01 RS	20	HF-P 118/136 TL-D III 220-240V 50/60Hz	913713031566		X	X	1
		HF-S 118_136 TL-D II 220-240V 50_60Hz	913713032166		X	X	1
Actinic BL TL 40W/10, TL 40W/01 ; TL 40W/12	40	HF-P 158 220-240V 50/60Hz	913713031866		X	X	1
		HF-S 154 TL5 II 220-240V	913713033666		X	X	1
		HF-S 254 TL5 II	913713033766		X		2
BL TL-K 40W/10-R	40	IUV-2S75-M4LD	913710021406	X	X	X (for 1 lamp)	1 or 2
TL 80W/10R	80	IUV2S75 M4LD	913710021406	X	X		1
TL 60W/10R	60	IUV2S75 M4LD	913710021406	X	X		2
TL 100W/01; F72T12/01 ; TL 100W/10R ; TL 100W/12	100	IUV2S75 M4LD	913710021406	X	X		1
TL 120W/01		IUV2S75 M4LD	913710021406	X	X		1