

PHILIPS


Home lighting



Philips Home lighting

COLLECTION **2023**



A photograph of a modern living room. In the foreground, a dark grey, textured sofa is partially visible. Behind it, a large, vertical abstract painting with dark, textured brushstrokes hangs on a light-colored wall. To the left, a white doorway leads to another room, where a white table and a chair are visible. The lighting is soft and even, creating a warm and inviting atmosphere.

You've built a home, and lovingly furnished it to make it your own. A lush sofa set to lounge in comfort, an elegant dining table for family meals and sleek cupboards to hold your possessions. However, no home is complete until the lights are turned on to bathe everything in a welcoming glow.

Philips has lights for every style. For a proud homeowner, Philips offers its exquisite Home Lighting collection consisting of varied design themes like Modern, Contemporary, and Timeless Classics. Choose the products according to the design theme of your home and bring elegance to your home décor like never before.

Light up your
lifestyle today.





Chandeliers	6
Lead Families	42
Pendant & Ceiling	70
Wall Lights	98
Downlighters	138
Profile Lighting	170
Cove Lighting	174
Bathroom	178
Track Light	190
Outdoor	194





CHANDELIERS

Chandeliers bring out the grandeur of your home in a manner that they inspire the onlookers. A perfect chandelier can accentuate the design context of your entire home.

A crystal chandelier is a great amalgam of material and design. The design sensibility and material assurance of genuine crystal in each product ensures that it stays new and retains its shine for many years to come.

With Le Cristal, Philips takes lighting into a different league. A league where art, design and technology come together to create an experience that lives up to individual design preferences.

Philips has a nice assortment of crystal chandeliers to match your taste and aesthetic sensibilities.

**The refined art of elegance,
now in a new light.**



Model No.: 581964

Naica

Model No.: 581964

Premium crystals for sparkling lights to complement your home decor.



Model No.: 581965

Elegant titanium gold and matt black finish with premium crystals offering sparkling illumination.

Model No.: 581966

Stylish wall light with modern theme coupled with premium crystals to complement your Naica chandelier and decorate walls.



	Ceiling	Pendant	Wall Light
Model No.	581964	581965	581966
Colour	MSS titanium gold + Matt black		
Material	Metal & Class A Clear Crystal		
Dimensions (mm)	Dia. 600 x H 310	Dia. 600 x H 1850	W 185 X H 190 X D 93
Lamp Base	E14	E14	G9
Wattage	7x40W Max*	7x40W Max*	1x42W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 240V / 50 Hz | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581976

Gladius

Model No.: 581976

Finest sparkling crystals embellished in an elegant gold finish with contemporary, and elegant designs for your modern home.



Model No.: 581977

Choicest sparkling crystals crafted in a beautiful gold colour makes for a finer style statement.

Model No.: 581978

Premium wall lights decorated with extraordinary golden crystals to complement the chandelier and your ultra- luxurious home.



	Ceiling	Pendant	Wall Light
Model No.	581976	581977	581978
Colour	ABS plated imitation gold + Class A Clear Crystal		
Material	Metal, ABS & Class A Clear Crystal		
Dimensions (mm)	Dia. 510 x H 390	Dia. 510 x H 1910	W 220 X H 280 X D 110
Lamp Base	E14	E14	G9
Wattage	6x40W Max*	6x40W Max*	1x28W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 240V / 50 Hz | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581973

Flagship

Model No.: 581972

Robust metal design and modern looks to make your home decor irresistible.



Model No.: 581975

Unique design of this wall light with elegant white & gold finish draws inspiration.



Model No.: 581974

Experience unique colours emanating from this wall light through the golden foil.



Model No.: 581973

Robust metal design and modern looks of this pendant to make your home decor irresistible.



	Pendant	Pendant	Wall Light	Wall Light
Model No.	581972	581973	581974	581975
Colour	Powdered iron shade in rice + Golden foil			
Material	Metal	Metal	Metal	Metal
Dimensions (mm)	1200 x 250 x 1680	Dia 580 x H 1720	250 x 300 x D120	600 x 120 x D140
Lamp Base	E27	E27	E14	G9
Wattage	4x40W Max*	6x40W Max*	1x40W Max*	2x42W Max*
Lumen/CCT	Non-Integrated LED luminaire			

Voltage: 240V / 50 Hz | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used




Model No.: 581968

Shield

Model No.: 581969

Elegant chrome finish giving premium look to your home decor.



Model No.: 581968

Premium crystals for sparkling lights.

Model No.: 581971

Modern design to complement home decor that is well suited for your chandelier.



Model No.: 581970

Immersive lighting experience with premium Class A crystals.



	Ceiling	Pendant	Wall Light	Pendant
Model No.	581968	581969	581971	581970
Colour	ABS shade chrome colour + clear crystal			
Material	Metal, ABS & Class A Clear Crystal			
Dimensions (mm)	Dia 518 x H 290	Dia 610 x H 1900	260 x 240 x D140	1100 x 300 x 2040
Lamp Base	E27	E27	G9	E14
Wattage	5x40W Max*	6x40W Max*	2x42W Max*	8x40W Max*
Lumen/CCT	Non-Integrated LED luminaire			

Voltage: 240V / 50 Hz | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581963

Inlay



Model No.: 581963

Premium crystals for sparkling lights which are aesthetic & elegant with a gold finish to add a hint of luxury to your home decor.

	Pendant
Model No.	581963
Colour	Painted imitation gold
Material	Metal & Class A Clear Crystal
Dimensions (mm)	Dia 510 x 1980
Lamp Base	E14
Wattage	6x60W Max*
Lumen/CCT	Non-Integrated LED luminaire

Voltage: 240V / 50 Hz | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581967

Crystal



Model No.: 581967

Premium crystals for sparkling lights elegantly designed with titanium gold finish to suit any living space.

	Ceiling
Model No.	581967
Colour	Class A clear crystal with titanium gold round sheet with crystal chains inside
Material	Metal & Class A Clear Crystal
Dimensions (mm)	Dia 480 x H 260
Lamp Base	G9
Wattage	6x42W Max*
Lumen/CCT	Non-Integrated LED luminaire

Voltage: 240V / 50 Hz | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581864

Caesar

Model No.: 581864

Finest crystals in contemporary stainless steel finish for a royal look.




Model No.: 581863

Exclusive crystals in refined stainless steel finish to add glamour to your home.

Model No.: 581865

Premium crystals in aesthetic stainless steel finish for the ultra-modern house that blends seamlessly with your chandelier.



	Chandelier	Chandelier	Wall Light
Model No.	581863	581864	581865
Colour	Mirror stainless steel	Mirror stainless steel	Mirror stainless steel
Material	Beaded with class A clear crystal	Beaded with class A clear crystal	Beaded with class A clear crystal
Dimensions (mm)	400x400x190	Dia. 465 x H 1450	Dia 140 x W 210 x H 110
Lamp Base	G9	G9	G9
Wattage	5x42W Max*	6x42W Max*	1x42W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 240V/50 Hz. | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581846

Corona

Model No.: 581846

Finest crystals in superb chrome finish to add style to your house.



Model No.: 581847

Superior-grade crystals set in mirror stainless steel with chrome finish for refined decor.



Model No.: 581848

Premium crystals for sparkling light with aesthetic elegant chrome finish that is well suited with the chandelier.



Model No.: 581886

Choicest crystals with chrome finish in a contemporary design for a modern feel.

	Chandelier	Chandelier	Chandelier	Wall Light
Model No.	581846	581847	581886	581848
Colour	Chrome	Chrome	Chrome	Chrome
Material	Mirror stainless steel shade with clear crystal		Stainless steel	Stainless steel
Dimensions (mm)	Dia. 510 x H 1440	Dia. 510 x H 180	680x220x750	235x225x190
Lamp Base	G9	G9	G9	G9
Wattage	7x42W Max*	7x42W Max*	5x33W Max*	1x42W Max*
Lumen/CCT	Non-Integrated LED luminaire			

Voltage: 240V/50 Hz. | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581857

Monarch

Model No.: 581885

Choicest crystals with chrome finish in a grand heritage design for a royal feel.



Model No.: 581857

Choicest crystals with chrome finish in a grand heritage design for a royal feel.



Model No.: 581858

Impressive crystals with chrome finish in a bespoke heritage design.

	Chandelier	Chandelier	Wall Light
Model No.	581885	581857	581858
Colour	Chrome	Chrome	Chrome
Material	Woven laser cut anodized silver aluminium rod diffuser with clear crystal		
Dimensions (mm)	Dia. 770 x H 2400	Dia. 660 x H 1800	Dia 180 x H 240
Lamp Base	E14	E14	E14
Wattage	9x60W Max*	6x60W Max*	1x60W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 240V/50 Hz. | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581843

Allure

Model No.: 581842

Exclusive crystal pendant light in chrome finish for homes with a personality.



Model No.: 581843

Unique crystal pendant in a special French gold finish to add a touch of sparkle to your special house.



	Chandelier	Chandelier
Model No.	581842	581843
Colour	Chrome	French gold
Material	Class A clear crystal	Class A clear crystal
Dimensions (mm)	Dia 400 x H 1680	Dia. 300 x H 360
Lamp Base	G9	G9
Wattage	5x42W Max*	4x42W Max*
Lumen/CCT	Lumen/CCT-Non-Integrated LED luminaire	

Voltage: 240V/50 Hz. | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581841

Corral & Chalice

Model No.: 581845

Extraordinary crystals in an elegant stainless steel finish for that wondrous light spread.



Model No.: 581841

Sophisticated chandelier made of the choicest glass crystals in chrome finish to complement your luxurious home.

Model No.: 581906

Exquisite chandelier with beautiful glass crystals in chrome finish for accentuating your home decor.



	Chandelier	Chandelier	Chandelier
Model No.	581845	581841	581906
Colour	Mirror stainless steel	Mirror stainless steel	Chrome
Material	Woven laser cut anodized silver aluminium rod diffuser with clear crystal	Class A clear crystal & cognac glass	Class A clear crystal & cognac glass
Dimensions (mm)	510x510x185	Dia. 520 x H 220	Dia 650 x H 250
Lamp Base	G9	G9	G9
Wattage	5x33W Max*	6x42W Max*	8x33W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 220V/50Hz. | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No. : 581844

Crescent

Model No.: 581844

Sumptuous ivory gold finish crystal pendant to give an exclusive feeling to your house.



Model No.: 581884

Unique crystal pendant in chrome finish to lend an air of luxury to your abode.

	Pendant	Pendant
Model No.	581844	581884
Colour	Ivory gold metal frame clear crystal	Chrome
Material	Metal	Metal
Dimensions (mm)	Dia. 460 x H 1840	Dia. 480 x H 650
Lamp Base	G9	G9
Wattage	5x42W Max*	5x42W Max*
Lumen/CCT	Non-Integrated LED luminaire	

Voltage: 240V/50 Hz. | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used




Model No.: 581849

Cameo

Model No.: 581849

Unequalled crystals set in stainless steel finish chandelier for your plush interiors.



Model No.: 581850

Designer stainless steel finish chandelier with premium crystals for your lavish home.

	Chandelier	Chandelier
Model No.	581849	581850
Colour	Mirror stainless steel	Mirror stainless steel
Material	Mirror stainless steel & clear crystal	Mirror stainless steel & clear crystal
Dimensions (mm)	Dia. 580 x H 250	L 410 x W 410 x H 220
Lamp Base	G9	G9
Wattage	5x33W Max*	5x33W Max*
Lumen/CCT	Non-Integrated LED luminaire	

Voltage: 240V/50 Hz. | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581904

Splendora

Model No.: 581903

Finest crystals in superb chrome finish to add style to your house.



Model No.: 581904

Superior-grade crystals set in mirror stainless steel with chrome finish for refined decor.



Model No.: 581905

Choicest crystals with chrome finish in a grand heritage design for a royal feel that complement well with your chandelier.



	Chandelier	Chandelier	Single Head Wall Light
Model No.	581903	581904	581905
Colour	Chrome	Chrome	Chrome
Material	Metal	Metal	Metal
Dimensions (mm)	Dia. 575 x H 1743	Dia. 575 x H 213	W 190 x H 175 x D 112
Lamp Base	G9	G9	G9
Wattage	7x42W Max*	7x42W Max*	1x42W Max*
Lumen/CCT	Non-Integrated LED luminaire		



Model No.: 581901

Torrent

Model No.: 581901

Finest crystals in contemporary stainless steel finish for a royal look.



Model No.: 581902

Premium crystals in aesthetic stainless steel finish to complement the Torrent chandelier and your ultra-modern house.




	Chandelier	Wall Light
Model No.	581901	581902
Colour	Chrome	Chrome
Material	Stainless steel with clear crystal	
Dimensions (mm)	Dia. 550 X H 570	W 160 X H 240 X D 80
Lamp Base	G9	G9
Wattage	8x33W Max*	2x33W Max*
Lumen/CCT	Non-Integrated LED luminaire	

Voltage: 240V/50 Hz. | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581853



Regalia

Model No.: 581853

Contemporary design made of superior pressed clear glass in chrome finish to brighten up your home.



Model No.: 581852

Classic wall light made of pressed clear glass with chrome finish to complement Regalia and your elite homes.

Model No.: 581851

Wall light made of premium glass to add an exquisite sparkle to your lovely home.



	Chandelier	Double Head Wall Light	Single Head Wall Light
Model No.	581853	581852	581851
Colour	Chrome	Chrome	Chrome
Material	Machine pressed clear glass & metal		
Dimensions (mm)	Dia. 760 x H 1460	100x230x150	90x80x150
Lamp Base	G9	G9	G9
Wattage	12x42W Max*	2x42W Max*	1x42W Max*
Lumen/CCT	Non-Integrated LED luminaire		

Voltage: 240V/50 Hz. | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used



Model No.: 581854

Umбра




Model No.: 581854

Distinctive chandelier in nest glass with chrome & red copper finish for that unique style.

	Chandelier
Model No.	581854
Colour	Chrome & red copper
Material	Borosilicate double capsule glass inside, clear glass outside
Dimensions (mm)	Dia. 720 x H 960
Lamp Base	G9
Wattage	8x33W Max*
Lumen/CCT	Non-Integrated LED luminaire

Voltage: 240V / 50 Hz | *Bulb excluded | Recommended LED, CFL or Incandescent bulbs can be used





LEAD FAMILIES

When you like a design theme, you want your home to be soaked in that theme. To do that, your light fixtures have to follow the same consistency to bring out a well coordinated design.

Philips has an extensive range of coordinated designs to adorn your home. The coordinated ranges reflect all design aesthetics and present all fixtures and forms.

So, go ahead and pamper your home with our carefully assorted line just for the discerning you!



Model No.582065 | 582066

Lucidus



Model No. 582066



Model No. 582065

Heritage Beckons

Give your abode that regal look with this collection of heritage pendant and wall light. Forged in the classical style from premium blown glass and steel, this collection is available in an antique brass finish with a unique petal-shaped glass.

- Antique finish
- Classical Indian appeal
- Beautiful petal glass

	Chandelier	Wall Light
Model No.	582065	582066
Colour	Antique Brass	Antique Brass
Material	MS with frosted glass	MS with frosted glass
Dimensions (mm)	600x600x850	180x255x320
Lamp Base	E27	E27
Wattage	5 x 20W LED (Max.)*	1 X 20W LED (Max.)*
Lumen/CCT	-	-

Voltage: 220V/50Hz | Recommended to be used with Philips Full Glow LED Bulb for optimum light | *Bulb excluded.



Model No. 582026

Ornate



Model No. 582026



Model No. 582084

Urbane allure

Design your space with the good old-world charm of a classic table lamp, crafted in natural wood. The feel of wood, minimal design and a warm glow of light brings richness and joy to your home.

- Natural wood finish
- Minimalistic design
- Warm & soothing light

	Wooden Table Lamp	Wooden Floor Lamp
Model No.	582026	582084
Colour	Natural wood finish	Natural wood finish
Material	Wooden	Wooden
Dimensions (mm)	260x260x485	1500x420x420
Lamp Base	E27	E27
Wattage	1 X 20W (Max.)*	1 X 20W (Max.)*
Lumen/CCT	-	-

Voltage: 220V/50Hz | *Bulb excluded. Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 582011

Marvel



Model No. 582012



Model No. 582011

Elegance redefined

Enhance your homespace with an all-new contemporary collection of glass wall light and pendants. Crafted in superior borosilicate glass and chrome, these pendants emit wonderful light patterns.

- Chrome finish
- Beautiful light pattern
- Superior borosilicate glass

	Glass Pendant	Wall Light
Model No.	582011	582012
Colour	Chrome finish	Chrome finish
Material	Stainless Steel & Borosil Glass	Stainless Steel & Borosil Glass
Dimensions (mm)	204x204x1600	225x152x220
Lamp Base	E27	E27
Wattage	1 X 20W LED (Max.)*	1 X 20W LED (Max.)*

Voltage: 220V/50Hz | Recommended to be used with a bright LED filament bulb for best light patterns | *Bulb excluded.



Model No. 582013

Motif



Model No. 582016



Model No. 582013



Model No. 582015



Model No. 582014

Patterns of beauty

Choose from an expressive, elegant range of Motif pendants and wall light crafted in intricate striking patterns. They create beautiful patterns and an interplay of light and shadow for a fascinating living experience.

- Shiny copper finish
- Beautiful light pattern
- Superior borosilicate glass

	Glass Pendant	Glass Pendant	Glass Pendant	Wall Light
Model No.	582013	582015	582014	582016
Colour	Copper	Copper	Copper	Copper
Material	SS & Borosil Glass	SS & Borosil Glass	SS & Borosil Glass	SS & Borosil Glass
Dimensions (mm)	120x120x1850	160x160x1600	203x203x1500	170x152x260
Lamp Base	E27	E27	E27	E27
Wattage	1 x 20W LED (Max.)*	1 x 20W LED (Max.)*	1 x 20W LED (Max.)*	1 x 20W LED (Max.)*

Voltage: 220V/50Hz | Recommended to be used with a bright LED filament bulb for best light patterns | *Bulb excluded.



Model No. 58145



Model No. 58150



Model No. 58148

Jazz



Model No. 58145



Model No. 58145



Model No. 58150



Model No. 58147



Model No. 58148



Model No. 58149

The heart of your décor

The collection is inspired from the rhythm developed from ragtime and blues and characterized by propulsive syncopated rhythms varying degrees of improvisation. It has rhythm, which will be the heartbeat of the home. These lights are commanding yet sophisticated with its curved stems and shades.

- Beautiful light pattern
- Classic Indian appeal
- Matt gold for superior finish

	Wall Light Single	Wall Light Double	Pendant Single	3 Head Pendant	Table Lamp	Floor Lamp
Model No.	58145	58145	58147	58148	58149	58150
Colour	Matt Gold and Black		Matt Gold	Matt Gold	Matt Gold and Black	
Material	Aluminium & Metal		Aluminium & Metal		Aluminium & Metal	
Dimensions (mm)	256x118x190	256x118x190	225x225x1570	225x225x1675	220x220x620	300x300x1650
Lamp Base	E27	E27	E27	E27	E27	E27
Wattage	1x20W Max	2x20W Max	1x20W Max	3x20W Max	1x20W Max	1x20W Max

Voltage: 220-240V | Recommended to be used with Philips Hue/WiZ smart bulbs, lamp excluded



Model No. 58137



Model No. 58140



Model No. 58135

Roseate



Model No. 58135



Model No. 58137



Model No. 58138



Model No. 58135



Model No. 58140



Model No. 58139

A ray of class

The association of roses is with optimism, and 'Roseate' is no exception. Enjoy the look of this range with elegant hanging, wall, floor & table options. This will be perfect for home designed to inspire class. The design is not only unique but also in-vogue and elegant.


- Beautiful light pattern
- Classic Indian appeal
- Matt gold for superior finish

	Wall Light Single	Wall Light Double	Pendant Single	3 Head Pendant	Table Lamp	Floor Lamp
Model No.	58135	58135	58137	58138	58139	58140
Colour	Matt Gold	Matt Gold	Matt Gold	Matt Gold	Matt Gold	Matt Gold
Material	Aluminium & Metal		Aluminium & Metal		Aluminium & Metal	
Dimensions (mm)	135x175x290	370x175x290	325x325x1675	325x325x1675	220x220x450	325x325x1450
Lamp Base	E27	E27	E27	E27	E27	E27
Wattage	2x20W Max*	2x20W Max*	1x20W Max*	3x20W Max*	1x20W Max*	1x20W Max*

Voltage: 220-240V | Recommended to be used with Philips Hue/WiZ smart bulbs | *Lamp excluded



Model No. 31434



Model No. 31426

Muziris



Model No. 31434



Model No. 31425



Model No. 31426

Delightful by design

The aesthetic design with superior finish will elevate the look of your living space. The minimal clean cut design ensures easy maintenance and cleaning of the fixtures.

- Expressive and elegant form
- Perfect for energy saving lamps
- Premium finish for superior feel

	Single Head Wall Light	Double Head Wall Light	Laminar Wall Light
Model No.	31425	31426	31434
Colour	Bronze	Bronze	Bronze
Material	Metal	Metal	Metal
Dimensions (mm)	150x115x227	150x272x227	200x140x380
Lamp Base	E27	E27	E27
Wattage	1x20W Max	2x20W Max	1x20W Max

Voltage: 220-240V | Recommended to be used with Hue & WiZ bulb



Model No. 31431

Muziris



Model No. 31431



Model No. 31432



Model No. 31429



Model No. 31430

A new form of luxury

- Expressive and elegant form
- Matt black and gold for superior feel
- Perfect for energy saving lamps
- Glass shade

	1 Head Cylindrical Pendant	3 Head Cylindrical Pendant	1 Head Gold Cylindrical Pendant	3 Head Gold Cylindrical Pendant
Model No.	31429	31430	31431	31432
Colour	Black & White	Black & White	Gold	Gold
Material	Metal	Metal	Metal	Metal
Dimensions (mm)	122x122x300	275x275x300	122x122x300	275x275x300
Lamp Base	E27	E27	E27	E27
Wattage	1x20W Max	3x20W Max	1x20W Max	3x20W Max

Voltage: 220-240V | Recommended to be used with Hue & WiZ bulb



Model No. 31402

Muziris



Model No. 31402



Model No. 31403



Model No. 581999

Express mood elegantly

- Flexible neck for adjusting beam
- Bronze finish for superior feel
- Long life LED light source

	Picture Light	Picture Light	Picture Light
Model No.	31402	31403	581999
Colour	Bronze	Bronze	Bronze
Material	Aluminum	Aluminum	Aluminum
Dimensions (mm)	355x180x95	500x80x95	800x190x95
Lamp Base	LED	LED	LED
Wattage	7W	12W	22W
Lumen/CCT	270lm/3000K	420lm/3000K	780lm/3000K

Voltage: 220-240V | Warm White 3000K with good Colour rendering (CRI>80)



Model No. 58072

Grandeur



Model No. 58071



Model No. 58071



Model No. 58072

The warm glow of richness

The word Grandeur describes things that are distinguished, extraordinary & impressive in scope. This range has classic design with hammered glass paired with the warm glow of light to bring richness in the room.

- Expressive and elegant form
- Beautiful light pattern
- Bronze finish for superior feel
- Classic Indian appeal

	Wall Light Single	Wall Light Double	3 Head Pendant
Model No.	58071	58071	58072
Colour	Brush bronze metal base with hammered glass		
Material	Metal	Metal	Metal
Dimensions (mm)	125x125x260	280x160x260	260x260x1500
Lamp Base	E27	E27	E27
Wattage	1x20W Max*	2x20W Max*	3x20W Max*

Voltage: 240V / 50Hz | Recommended to be used with a bright LED filament bulb for best light pattern | *Bulb excluded.



Floret



Model No. 581871



Model No. 581872



Model No. 581873

Let beauty light up your lifestyle

Flowers are a gift to this earth. Enjoy the beautiful floret range to redefine your style statement.

- Modern design for elegant look
- Long life LED light source
- Robust metal construction
- Superior glass quality

	Table Lamp	Single Wall Lamp	Double Wall Lamp
Model No.	581873	581871	581872
Colour	Chrome	Chrome	Chrome
Material	Metal with premium glass	Metal with premium glass	Metal with premium glass
Dimensions (mm)	170x120x400	115x115x150	260x115x150
Lamp Base	LED	LED	LED
Wattage	6W	6W	12W
Lumen/CCT	350lm/3000K	350lm/3000K	700lm/3000K

Voltage: 240V / 50Hz | Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 581876



Model No. 581877



Model No. 581878

Striker



Model No. 581876



Model No. 581877



Model No. 581878


The art of simplicity

You don't always have to make grand entrance to stand out, sometimes simple yet elegant choices make the difference. Enjoy the classic Striker range to highlight your living space.

- Beautiful light pattern
- Premium fabric material
- Superior finish

	Wall Lamp	Table Lamp	Floor Lamp
Model No.	581876	581877	581878
Colour	Chrome with fabric white shade		
Material	Metal		
Dimensions (mm)	250x220x225	220x220x420	350x350x1620
Lamp Base	E27	E27	E27
Wattage	1x40W Max*	1x40W Max*	1x40W Max*

Voltage: 240V / 50Hz | Recommended to be used with Philips Hue/WiZ smart bulbs | *Lamp not included



Model No. 581874

Sierra & Arc



Model No. 581874



Model No. 581875

The magic of minimalism

Enjoy the look of this minimalist floor lamp range designed to inspire class. The design is not only unique but also in-vogue and elegant.

- Minimalist design, looks great with any décor
- Adds elegance to your home or office
- Metal body, fabric shade

	Floor Lamp	Floor Lamp
Model No.	581874	581875
Colour	White	White
Material	Metal	Metal
Dimensions (mm)	340x340x1550	1180x340x1800
Lamp Base	E27	E27
Wattage	1x40W Max	1x40W Max
Lumen/CCT	-	-

Voltage: 220-240V



PENDANT & CEILING

Pendants are the in-thing. They occupy little space and are extremely practical fixtures. These versatile fixtures are a great tool to provide either task, ambient, accent or decorative lighting.

Merge the tasks with the right design and finish and the overall décor of the house gets elevated manifold.

Philips has an extensive collection of pendants for all kinds of moods and requirements. The finishes range from heritage to modern. There are some ranges which are timeless, they justify being placed in any corner of the house and accentuate it for many years!



Model No. 582047

Ritzy



Model No. 582047

Enthralling beauty

Ritzy is designed to evoke a sense of magnificence and grandeur but with simplicity. This pendant, with its ultra-smooth opal white glass will definitely make its presence felt in your home. Be it bedside or that corner of your living room, Ritzy can be used with utmost ease in every part of your house. They can be used single or even as a cluster of pendants to light up any area.

- Smooth matte opal glass
- Simplistic design
- Beautiful light effect

	Pendant
Model No.	582047
Colour	Matte White
Material	Opal Glass
Dimensions (mm)	160x160x1450
Lamp Base	E27
Wattage	1 X 20W (Max.)*
Lumen/CCT	Non-Integrated Luminaire

Voltage: 220V/50Hz | Recommended to be used with Philips Full Glow LED Bulb for optimum light | *Bulb excluded.



Model No. 582019

Gemini



Model No. 582019



Model No. 582017



Model No. 582018

Exquisite elegance

Bring home the elegance of these double-layered pendants which are awesome on the outside and mesmerizing on the inside. These minimalist-style pendants create a delectable ambience in any kind of interior setting.

- Beautiful light pattern
- Modern look
- Minimalistic design

	Double Layered Pendant	Double Layered Pendant	Double Layered Pendant
Model No.	582019	582017	582018
Colour	Ivy League & Matte White	Antique Red & Silver	Antique Silver & Gold
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	250x250x1600	250x250x1600	250x250x1600
Lamp Base	E27	E27	E27
Wattage	1 X 20W (Max.)*	1 X 20W (Max.)*	1 X 20W (Max.)*

Voltage: 220V/50Hz | *Bulb excluded. Recommended to be used with Philips Hue/WiZ smart bulbs.



Model No. 582021

Hemis



Model No. 582021



Model No. 582020

Minimalist inspiration

The elegant and minimal form of these double-layered pendants will elevate your living space, be it bedroom, living room or study room. Enjoy the diffused, subtle light filling every corner of your room, as you sit back and relax.

- Beautiful light pattern
- Modern look
- Vibrant colour

	Double Layered Pendant	Double Layered Pendant
Model No.	582021	582020
Colour	Matte Black & Gold	Crimson Brown & White
Material	Aluminium	Aluminium
Dimensions (mm)	305x305x1600	305x305x1600
Lamp Base	E27	E27
Wattage	1 X 20W Max.	1 X 20W Max.

Voltage: 220V/50Hz | *Bulb excluded. Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 582023

Vivid



Model No. 582025



Model No. 582024



Model No. 582023

Iconic inspiration

Experience a delightful blend of timeless artistry and contemporary look. The minimalist design draped in flamboyant colours energises and enlivens your abode.

- Flamboyant colours
- Modern look
- Minimalistic design

	Pendant	Pendant	Pendant
Model No.	582025	582024	582023
Colour	Ivy League	Matte Gold	Splendid Blue
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	300x300x1450	300x300x1450	300x300x1450
Lamp Base	E27	E27	E27
Wattage	1 X 20W (Max.)*	1 X 20W (Max.)*	1 X 20W (Max.)*

Voltage: 220V/50Hz | *Bulb excluded. Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 30899

Ceiling & Suspension Light



Model No. 30898



Model No. 30899

Sheer elegance

This collection is created to relive the old world, luxurious environment, yet has refinement and relevance to the modern times. These luminaires create an atmosphere of elegance, formality and detail. Fit for a regal home that speaks of status, designed tastefully to experience luxury.

- Premium glass crystals for sparkling light effect
- Comforting night light

	Ceiling Light	Suspension Light
Model No.	30898	30899
Colour	Metallic black	Metallic black
Material	Glass, Crystal	Glass, Crystal
Dimensions (mm)	400x400x220	400x400x1750
Lamp Base	E14	E14
Wattage	4x20W Max*	4x20W Max*

Voltage: 220-240V | *Bulb excluded



Model No. 58074

Beacon



Model No. 58074



Model No. 58074

Let happiness glow

The shine that expresses an emotion of happiness. Made from high quality metal, it diffuses light to a warm even glow. It lights up to delight and soothe.

- High quality material
- Adjustable suspension height

	Pendant	Pendant
Model No.	58074	58074
Colour	Wine & Silver	Rosegold & Silver
Material	Aluminium	Aluminium
Dimensions (mm)	157x157x1500	157x157x1500
Lamp Base	E27	E27
Wattage	1x20W Max*	1x20W Max*

Voltage: 220V/50Hz | *Bulb excluded. Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 58076

Blithe



Model No. 58078

Model No. 58078



Model No. 58076

Model No. 58076

Patterns of beauty

The shine that expresses an emotion of happiness. Made from high quality metal, it diffuses light to a warm even glow. It lights up to delight and soothe.

- Expressive & elegant form
- Beautiful light patterns

	Three Head Pendant	Three Head Pendant	Three Head Pendant	Three Head Pendant
Model No.	58078	58078	58076	58076
Colour	Wine & Silver	Rosegold & Silver	Wine & Silver	Rosegold & Silver
Material	Metal base / Aluminium shade			
Dimensions (mm)	550x350x1500	550x350x1500	350x350x1500	350x350x1500
Lamp Base	E27	E27	E27	E27
Wattage	3x20W Max*	3x20W Max*	3x20W Max*	3x20W Max*

Voltage: 220V/50Hz | *Bulb excluded. Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 58127

Tawny



Model No. 58127

Go iconic, be timeless

Enjoy iconic design with a vintage lamp that perfectly fits your personal style. The Philips Tawny pendant is made of hammered glass with shiny copper base. The timeless design looks great in both modern & retro interiors.

- High quality material
- Beautiful light pattern with premium hammered luster glass
- Adjustable suspension height

	Pendant
Model No.	58127
Colour	Shiny Copper
Material	Metal & Glass
Dimensions (mm)	270x270x1500
Lamp Base	E27
Wattage	1x20W Max*

Voltage: 220V / 50 Hz / 50-60 Hz | Recommended to be used with a bright LED filament bulb for best light pattern | *Bulb excluded



Model No. 41058

Lustre



Model No. 41058

Model No. 41058

Model No. 41058

Model No. 41058

See the bells shine

The Lustre collection makes an eye-catching addition to your space. With its shade akin to an inverted wine glass in high shine metallic paint, this easy to install light casts a focused beam for that added impact.

- Uniform finish for lustre and shine
- Adjustable height
- Easy installation

	Pendant	Pendant	Pendant	Pendant
Model No.	41058	41058	41058	41058
Colour	Gold	Chrome	Black	Copper
Material	Metal	Metal	Metal	Metal
Dimensions (mm)	130x130x1500	130x130x1500	130x130x1500	130x130x1500
Lamp Base	E27	E27	E27	E27
Wattage	1x10W Max*	1x10W Max*	1x10W Max*	1x10W Max*

Voltage: 220V/50Hz | *Bulb excluded. Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 31451

Vintage Cord



Model No. 31452



Model No. 31451

Lights up the corners of your mind

Experience the old world rustic charm with efficacy of the modern LED filament bulbs. These minimal pendants are perfect for creating ambiance at a get together or lighting up a corner.

- Ideal for filament lamps
- Premium vintage-style finish
- Adjustable 1.5 meter cord
- Fits perfectly into any space

	Vintage Cord	Vintage Cord
Model No.	31451	31452
Colour	Rose Gold	Brushed Bronze
Material	Metal	Metal
Dimensions (mm)	140x140x1600	140x140x1600
Lamp Base	E27	E27
Wattage	1x20W Max*	1x20W Max*

*Bulb excluded. Recommended to be used with filament bulb



Model No. 582010

Dome



Model No. 582010

Sleek design, brighter lighting

Dome ceiling light offers cool day light to enable you to assist in important tasks for the day. And when the day winds down, the very same ceiling light can help you relax by enabling you to switch to a warm white light, for that perfect evening! The light output makes this ideal for big rooms and even for places like kitchen where bright light is needed for cooking and the same fixture can help you feel relaxed in warm white light while having food at that kitchen counter of yours.

- Bright light output
- Tunable white
- Exquisite look

	Ceiling Light
Model No.	582010
Colour	White
Material	Polycarbonate
Dimensions (mm)	480x72
Lamp Base	LED Integrated
Wattage	32W
Lumen /CCT	2900lm/(WW/NW/CW on Toggle)

Voltage: 220V/50Hz



Model No. 582057

Saturn



Model No. 582056



Model No. 582056



Model No. 582057



Model No. 582057

Let the elegance speak

Bring home the sleek yet elegant ceiling light with a minimalist design to transform your home space. These lights create a delectable ambience ensuring eye comfort.

- Attractive ring on the edge
- Bright light
- Enhances décor
- Eye comfort

	Ceiling Light	Ceiling Light
Model No.	582056	582057
Colour	Brown/Gold (Outer ring)	Brown/Gold (Outer ring)
Material	Synthetic	Synthetic
Dimensions (mm)	250x250x65	320x320x70
Lamp Base	LED	LED
Wattage	18W	24W
Lumen/CCT	1650lm/WW/CW	2400lm/WW/CW



Model No. 581900

Summit, Crown & Willow



Model No. 581898
Summit



Model No. 581900
Willow




Model No. 581899
Crown

Shine from the top

Ceiling lights are ideal for each section in your home. Light up your space with our wide range of decorative ceiling lamps that are available in different design, size and colour to fit your style and needs!

- High quality diffuser for uniform light effect
- Robust metal construction
- Perfect finish
- Long life LED light source

	Ceiling Lights	Ceiling Lights	Ceiling Lights
Model No.	581898	581899	581900
Colour	Silver	Silver	White & Wood Brown
Material	Aluminium	Aluminium	Metal & Wood
Dimensions (mm)	Dia. 400x100	Dia. 360x100	Dia. 350x150
Lamp Base	LED	LED	LED
Wattage	1x25W	1x22W	1x22W
Lumen/CCT	2300lm/3000K/6500K	1450lm/6500K	900lm/3000K



WALLLIGHTS

Decorative wall lights are as essential to Indian homes as the home themselves. The choice of decorative wall is an extension of the overall décor and design language that the house stands to convey. A great wall light not only complements but also elevates the entire milieu and mood of the house.

Philips has a vast collection of wall lights for all moods and designs.

Have a look at the range and you would definitely pick one for your abode.



Model No. 582063

Ebony



Model No. 582063

Epitome of beauty

Ebony has been crafted keeping minimalism as the heart of its design language. A clean, clear and uncluttered design like Ebony is surely going to lend serenity to your abode. Use this to highlight your personal space around the bed or make those walls much more expressive with just Ebony adorning them.

- 90-degree movability each side
- Minimalistic design
- Indirect light effect

	Wall Light
Model No.	582063
Colour	Matt Black
Material	Aluminium
Dimensions (mm)	675x60x78
Lamp Base	LED Integrated
Wattage	15W
Lumen/CCT	450lm/3000K

Voltage: 220V / 50 Hz



Model No. 582002

Delight



Model No. 582002



Model No. 582003

The epitome of elegance and luxury

Aesthetically designed with symmetrical light distribution for enduring appeal and endless versatility. These wall lights are a perfect mix of contemporary and antique designs that can instantly take your home décor up a notch.

- Perfect chrome finish/attractive white body
- Tunable white for ambience (switch from cool blue light to warm white light through simple switch toggles)
- IP44 protection (makes it suitable for use in moist areas as well)

	Single Head Wall Light	Single Head Wall Light
Model No.	582002	582003
Colour	Chrome	White
Material	Metal	Metal
Dimensions (mm)	150x195x195	150x195x195
Lamp Base	LED Integrated	LED Integrated
Wattage	5W	5W
Lumen/CCT	260lm/(WW/NW/CW on Toggle)	260lm/(WW/NW/CW on Toggle)

Voltage: 220-240V



Model No. 582008

Bling



Model No. 582008



Model No. 582007

Designed elegantly for superior lighting

Ignite the charm of your surroundings with modern and elegantly designed wall light. Now relax, focus, and celebrate every moment with the right light.

- Perfect chrome finish
- Beautiful glass
- Tunable white for ambience (switch from cool blue light to warm white light through simple switch toggles)
- IP44 protection (makes it suitable for use in moist areas as well)
- High lumen efficiency of 110-120 lumen per watt

	Single Head Wall Light	Double Head Wall Light
Model No.	582008	582007
Colour	Chrome	Chrome
Material	Metal	Metal
Dimensions (mm)	120x150x170	340x102x170
Lamp Base	LED Integrated	LED Integrated
Wattage	5W	10W
Lumen/CCT	600lm/(WW/NW/CW on Toggle)	1100lm/(WW/NW/CW on Toggle)

Voltage: 220-240V



Model No. 581923

Aster



Model No. 581923

Easy on the eye, light on the senses

Install a contemporary style lighting with integral swivel head, and easy to adjust focus, to create the perfect ambience.

- Adjustable head with swivel joint
- Robust construction
- Long life LED light source
- Premium glass for reduced glare

	Single Head Wall Light
Model No.	581923
Colour	Chrome
Material	Metal
Dimensions (mm)	115x115x125
Lamp Base	LED Integrated
Wattage	7W
Lumen/CCT	350lm/WW

Voltage: 220-240V



Model No. 58155

Duo



Model No. 58154



Model No. 58155

Complement your abode

Made for illuminating walls, the Philips Duo wall light arches gracefully over your favourite wall & creates unique ambiance through the two light sources combined in one fixture. The energy efficiency and long-lasting performance are other definite advantages.

- Superior illumination
- Perfect finish
- Highlight the indoors
- Robust metal construction
- Long life LED light source

	Single Head Wall Light	Double Head Wall Light
Model No.	58154	58155
Colour	White	White
Material	Aluminium	Aluminium
Dimensions (mm)	120x120x118	270x100x119
Lamp Base	LED	LED
Wattage	10W	20W
Lumen/CCT	700lm/3000K	1400lm/3000K

Voltage: 220-240V



Model No. 581917

Roman



Model No. 581917


Complement your abode

Roman wall light lends uniqueness to your decor through its special design. The lamp shade gets illuminated by the cylindrical light source below. This light source is adjustable and can be pointed away from the lamp shade to achieve a focused light source as well.

- Unique design
- Adjustable light source
- Robust metal construction

	Single Head Wall Light
Model No.	581917
Colour	White and Chrome
Material	Glass & Metal
Dimensions (mm)	270x140x170
Lamp Base	LED
Wattage	6W
Lumen/CCT	250/WW & CW

Voltage: 220-240V



Model No. 582104

Oriel



Model No. 582103



Model No. 582104



Model No. 582105


Mood Lighting for brighter days and warm evenings

This LED integrated fixture is a perfect blend of modern design with sustainability. You can choose to bring down the light intensity when not so much brightness is needed, thereby enabling you to create your own ambience, while being environment conscious at the same time.

- 3-step dimming on switch toggle (15W - 850 lumen, 7W - 450 lumen and 2W - 100 lumen)
- Antique finish
- Slim design

	Oriel Dimmable	Oriel Dimmable	Oriel Dimmable
Model No.	582103	582104	582105
Colour	Bronze	Bronze	Bronze
Material	Metal	Metal	Metal
Dimensions (mm)	317x120x35	317x120x35	317x120x35
Lamp Base	LED	LED	LED
Wattage	15W/7W/2W on toggle	15W/7W/2W on toggle	15W/7W/2W on toggle
Lumen/CCT	850lm/450lm/100lm with 3000k	850lm/450lm/100lm with 3000k	850lm/450lm/100lm with 3000k

Voltage: 220V-240V~, 50Hz



Model No. 30978

Sense of Style



Model No. 30978



Model No. 30979

Express your style with light

Designed to be calming to the mind and eyes, this premium wall light evokes a sense of tranquility with its gentle curves and diffused throw of light. Frosted glass combines a matt white look with the elegance of glass material, blending perfectly in any interior.

- Easy installation and unique aesthetics
- Durable metallic housing
- Frosted glass

	Single Head Wall Light	Double Head Wall Light
Model No.	30978	30979
Colour	Chrome	Chrome
Material	Metal and Glass	Metal and Glass
Dimensions (mm)	280x180x160	370x230x180
Lamp Base	B22	B22
Wattage	1x20W Max	2x20W Max

Voltage: 220V / 50 Hz | *Bulb excluded. | Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 31458

Trunk & Tale



Model No. 31453
Trunk



Model No. 31454
Trunk



Model No. 31457
Tale



Model No. 31458
Tale

The art of entertainment

We proudly present an all new range of decorative wall lights. These wall lights are inspired from eclectic sources and draw design inspiration from things that are common place yet inspire us and make every day a special day, one that is to be looked forward to. Pair these wall lights with our Hue bulbs and get that added zing to everyday activities whether that be entertainment or getting you more productive at things which matter-read, relax, concentrate, and energize.

- Clean contemporary design
- Fits perfectly into any home
- Beautiful glass & glossy finish

	Single Head Wall Light	Double Head Wall Light	Single Head Wall Light	Double Head Wall Light
Model No.	31453	31454	31457	31458
Colour	White & Silver	White & Silver	White & Black	White & Black
Material	Metal	Metal	Metal	Metal
Dimensions (mm)	100x126x201	246x121x202	102x168x184	286x166x180
Lamp Base	E27	E27	E27	E27
Wattage	1x20W Max	2x20W Max	1x20W Max	2x20W Max

Voltage: 220V / 50 Hz | *Bulb excluded. | Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 31455

Chiffe & Labyrinth



Model No. 31455
Chiffe



Model No. 31456
Labyrinth

Relax, focus, celebrate – turn every moment special

These wall lights are inspired from eclectic sources and draw design inspiration from things that are common place yet inspire us and make every day a special day, one that is to be looked forward to. Pair these wall lights with our Hue bulbs and get that added zing to everyday activities whether that be entertainment or getting you more productive at things which matter - read, relax, concentrate, and energize.

- Clean contemporary design
- Fits perfectly into any home
- Premium material
- Beautiful glass & glossy finish

	Single Head Wall Light	Double Head Wall Light
Model No.	31455	31456
Colour	White & Silver	White & Silver
Material	Metal	Metal
Dimensions (mm)	100x125x200	251x127x203
Lamp Base	E27	E27
Wattage	1x20W* Max	2x20W* Max

Voltage: 220V / 50 Hz | *Bulb excluded. | Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 58184

Platina, Glint & Blush



Model No. 58184
Platina



Model No. 58070
Glint



Model No. 58185
Blush

Design the perfect ambience

Experience easy maintenance with a relaxing aura and a touch of class with this wall light collection. The stainless steel base over a predominant frosted glass gives you perfect ambience with minimalist design.

- Expressive and elegant form
- Mirror finish for superior feel
- Classic Indian appeal

	Single Head Wall Light	Single Head Wall Light	Single Head Wall Light
Model No.	58184	58070	58185
Colour	Shiny stainless steel base & glass opal paint finish		
Material	Stainless Steel	Stainless Steel	Stainless Steel
Dimensions (mm)	125x150x240	125x150x240	115x120x255
Lamp Base	E27	E27	E27
Wattage	1x20W* Max	1x20W* Max	1x20W* Max

Voltage: 220V, 50 Hz | *Bulb excluded. | Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 581879



Model No. 581880



Model No. 581881

Aspire & Vista



Model No. 581879
Aspire



Model No. 581881
Vista



Model No. 581880
Aspire

Accentuate your lifestyle

The best choice for modern homes. Modern simplistic design brings about a unique functionality to the product without compromising on design and areas of the home which extend from bedroom to living to kitchen and aesthetics. This well-designed product can be used for multiple applications and many more.

- Perfect finish
- High quality construction
- Adjustable head

	Single Spot Light	Double Spot Light	Vista Wall
Model No.	581879	581880	581881
Colour	White	White	White
Material	Metal	Metal	Metal
Dimensions (mm)	110x110x113	320x110x113	134x134x144
Lamp Base	GU 10	GU 10	E14
Wattage	1x50W Max	2x50W Max	1x40W Max

Voltage: 220V / 50 Hz | *Bulb excluded. | Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 581919

Nixon



Model No. 581919



Model No. 581919

Bring every moment in focus

These wall lights are inspired from eclectic sources and draw design inspiration from things that are common place yet inspire us and make every day a special day, one that is to be looked forward to.

- Modern design for elegant look
- Long life LED light source
- Robust metal construction
- Adjustable head with swivel joint

	LED Wall Light	LED Wall Light
Model No.	581919	581919
Colour	White	Chrome
Material	Metal	Metal
Dimensions (mm)	115x115x125	115x115x125
Lamp Base	LED	LED
Wattage	7W	7W
Lumen/CCT	350lm/3000K	350lm/3000K

Voltage: 220V / 50 Hz



Model No. 34302

Grace, Stylo & Trendo



Model No. 34303
Grace



Model No. 34304
Trendo



Model No. 34302
Stylo


In the spotlight

Bring style into your house in brilliant matt chrome. Always be under the spotlight with these premium metal and synthetic decorative light that comes in 3 different types.

- Easy to maintain
- Designed for energy saving lamps
- Bright without a glare
- Soft indirect lighting

	Single Head Wall Light	Single Head Wall Light	Double Head Wall Light
Model No.	34302	34303	34304
Colour	White	White	White
Material	Metal	Metal	Metal
Dimensions (mm)	270x130x310	210x125x360	225x325x280
Lamp Base	B22	B22	B22
Wattage	1x20W* Max	1x20W* Max	2x20W* Max

Voltage: 220V, 50 Hz | *20W Bulb excluded. | Recommended to be used with Philips Hue/WiZ smart bulbs



Model No. 30975

Bedside Lights



Model No. 30975



Model No. 48042



Model No. 31437
Hint



Model No. 48042

Beautiful bedside lights

Reading in bed just got easier with this collection of adjustable LED bedside lights. Whether your décor matches white, black or chrome, our range of bedside lights will complement the same.

- Easy to adjust
- Gooseneck arm
- Long life LED light source
- Premium material & finish
- Energy saving

	Bedside Light	Bedside Light	Bedside Light	Bedside Light
Model No.	30975	48042	48042	31437
Colour	Grey	White	Black	White
Material	Metal	Metal	Metal	Metal
Dimensions (mm)	470x67x28	500x90x90	500x90x90	151x151x78
Lamp Base	LED	LED	LED	LED
Wattage	2W	3W	3W	7W
Lumen/CCT	50lm/3000K	75lm/3000K	75lm/3000K	400lm/3000K

Voltage: 220-240V~, 50Hz.



Model No. 31440/31441

Picture Light



Model No. 30973



Model No. 48043



Model No. 31440/31441
Nebula

Entertainment is on the walls

Some places in our homes are insipid and unimaginative. These modern aluminium lights turn every space into a canvas. Full of ideas, these artistic lights will fill your head with a string of ideas. Whether it is the study room, bathroom or the kitchen, you'll see these boring places in a new light.

- Flexibility to direct light
- Long life LED light source
- Premium material & finish

	Picture Light	Picture Light	Picture Light
Model No.	31440 / 31441	30973	48043
Colour	Chrome / Silver	Silver	Chrome
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	500x180x95	350x70x87	500x70x95
Lamp Base	LED	LED	LED
Wattage	12W	6W	10W
Lumen/CCT	420lm/3000K	370lm/3000K	700lm/3000K

Voltage: 220V-240V~, 50Hz | Warm White 3000K with good Colour rendering (CRI>80)



Ultron



Model No. 48027
Ultron



Model No. 36283
Ultron Scene Switch

Elegance on your wall, lighting as you like it.

The slim and modern design of Ultron is a visual relief from usual linear products. These uniquely designed products have multiple applications - below cabinets, beneath shelves.

- Premium material and finish
- Long life LED source
- Ultron Scene Switch: Alternate from warm white to natural white to cool white through switch toggle

	Wall Light	Wall Light
Model No.	48027	36283
Colour	Grey	Grey
Material	Synthetic	Synthetic
Dimensions (mm)	534x93x33	868x93x33
Lamp Base	LED	LED
Wattage	17W	24W
Lumen/CCT	1350lm/6500K	2400lm WW/NW/CW on toggle

Voltage: 220V-240V~, 50Hz



Model No. 31438

Desk Lights



Model No. 61013



Model No. 61013



Model No. 31438

Lighten up your reading moments

Perfect combination of task and ambient lighting. The direct lighting takes care of your bedside reading, while the ambient lighting in the table base ensures just the right visibility for comfortable and relaxed sleep. White matt finish blends in the background and does its job silently and effectively.

- Elegance meets dual function
- Convenience at your fingertips
- Separate on/off switches for both lights
- Ideal for reading
- Adjustable head for better beam & focus

	Breeze	AIR	Hint
Model No.	61013	61013	31438
Colour	White	Carbon black	White
Material	Synthetic	Synthetic	Metal
Dimensions (mm)	270x135x370	270x135x370	151x105x450
Lamp Base	LED	LED	LED
Wattage	5W	5W	7W
Lumen/CCT	250lm/6500K	250lm/6500K	400lm/3000K

Voltage: 220V / 50 Hz



Model No. 581931

Rechargeable Desk Lights



Model No. 581931



Model No. 581932



Model No. 581930


Lighten up your reading moments

When style meets functionality, what you get is an impeccable range of Philips Rechargeable Desk Lights. The brightness of these desk lights can be controlled via a simple touch. Their exquisite design and easy adjustability features make them an inspiration on one's desk.

- Rechargeable
- Sleek design, easy to adjust height and direction
- One-touch control for brightness

	SKYY	ORBIT	COSMOS
Model No.	581931	581932	581930
Colour	White	White	White
Material	Synthetic	Polycarbonate	Polycarbonate
Dimensions (mm)	253x379x396	Ø162x320	190x126x395
Lamp Base	LED	LED	LED
Wattage	5W	5W	5W
Lumen/CCT	400lm/CW	400lm/WW/NW/CW through touch	550lm/CW

Voltage: 220V / 50 Hz






DOWNLIGHTERS

Bring out the best in your home with the Philips range of Downlighters.

Equipped with the latest LED technology and designed for excellence in performance and quality, Philips downlighters are the perfect blend of innovation and modern design. Philips downlighters offer energy-saving benefits of LED, good light quality and maintenance free operation.



IP44 COB



Rose Gold



Matt Black



Chrome

Elegant choices for beautiful homes

- Unique honeycomb design to reduce glare
- IP44 splash proof housing
- Focused 36 degree beam angle
- Longer life with 20,000 hours
- Super robust construction with premium aluminum housing
- Wide voltage protection from 160V-360V and surge protection up to 2.5kV
- Multiple colours to choose from
- No harmful UV radiation
- BIS compliant; 2 years warranty

	IP44 COB	IP44 COB	IP44 COB
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminum	Aluminum	Aluminum
Dimensions (mm)	83.5x83.5x48	103.5x103.5x49	128x128x59
Cutout Dia (mm)	73	91	116
Wattage	7W	12W	20W
Lumen/CCT	420lm/3000k/4000k/6500	720lm/3000k/4000k/6500	1200lm/3000k/4000k/6500
Reflector Colour	Rose Gold/Matt Black/Chrome		



Deco COB



Rose Gold



Black



Silver




Chrome

Enhances the décor

- Decorative finish with multiple options to choose from
- Minimalistic outer trim to blend well with the ceiling
- Deep recessed COB for low glare
- Focused 36 degree beam angle
- Longer life with 35,000 hours
- Super robust construction - wide voltage protection from 160V-360V and surge protection up to 2.5kV
- Metal housing for longer life
- No harmful UV radiation, CRI>80
- BIS compliant; 2 years warranty

	LED Spot Light	LED Spot Light
Colour	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium
Dimensions (mm)	76x76x64	86x86x75
Cutout Dia (mm)	66	76
Wattage	7W	12W
Lumen/CCT	560lm/3000K/4000K/6500K	960lm/3000K/4000K/6500K

Voltage: 220V-240V~



Thin Trim Deep Recessed COB



The elegant face of illumination

- Minimalistic outer trim to blend well with the ceiling
- Deep recessed COB for low glare
- Available in 24 and 36 degree beam angle
- Longer life with 25,000 hours
- Super robust construction - Wide voltage protection from 160V-360V and surge protection up to 2.5kV
- Metal housing for longer life
- No harmful UV radiation, CRI>80
- BIS compliant; 2 years warranty

	LED Dimmable Spot Light	LED Dimmable Spot Light	LED Spot Light	LED Spot Light	LED Spot Light
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	55x55x100	75x75x100	55x55x100	75x75x100	92x92x120
Cutout Dia (mm)	52	68	52	68	82
Wattage	7W	12W	7W	12W	18W
Lumen/CCT	350lm/3000K/ 4000K/6500K	760lm/3000K/ 4000K/6500K	410lm/3000K/ 4000K/6500K	840lm/3000K/ 4000K/6500K	1260lm/3000K/ 4000K/6500K

Voltage: 220V-240V~



FlexFocus



Adjustable focused light

- Unique design with flexible focus
- 360 degree rotation to change the light beam
- Available in 30 degree beam angle
- Longer life with 20,000 hours
- Super robust construction
- Wide voltage protection from 160V-360V and surge protection up to 2.5kV
- Premium white aluminum housing
- No harmful UV radiation

	FlexFocus
Colour	WW/CDL/NW
Material	Aluminum
Dimensions (mm)	53x53x50
Cutout Dia (mm)	40
Wattage	3W
Lumen/CCT	210lm/3000K/4000K/6500K

Voltage: 220V-240V~



Surface COB



Focused surface light for your home & shop

- Brighter light output with 85 lm/w
- Premium aluminium material for better heat dissipation and endurance
- Uniform light output over product life of 20,000 hours
- No visible flickering, no UV/IR and low glare to prevent eye strain
- Surge protection up to 2.5kV with wide voltage protection 160-360V
- No harmful UV radiation, CRI>80
- Available in 7W, 12W and 18W CCTs of 6500K, 4000K & 3000K in round shape
- BIS compliant; 2 years warranty

	Surface COB	Surface COB	Surface COB
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	50x50x90	70x70x127	90x90x140
Cutout Dia (mm)	-	-	-
Wattage	7W	12W	18W
Lumen/CCT	595lm/ 3000K/ 4000K/ 6500K	1020lm/ 3000K/ 4000K/ 6500K	1530lm/ 3000K/ 4000K/ 6500K

Voltage: 220V-240V~



FlexSpot



Tiltable Spotlight with adjustable focus

- Direct the light at any angle with 230 degree tilt and 360 Degree rotation
- 36 Degree beam angle.
- Premium Aluminum housing in White & Black
- Longer life with 20,000 hours
- Super robust construction
- Wide voltage protection from 160V – 360V and surge protection up to 2.5kV
- No harmful UV radiation

	FlexSpot
Colour	WW/NW
Material	Aluminum
Dimensions (mm)	56x56x186
Cutout Dia (mm)	75
Wattage	10W
Lumen/CCT	850lm/ 3000K/ 6500K

Voltage: 220V-240V~



Deco Surface COB



Rose Gold



Chrome



Black



White

Feel inspired with beautiful metallic lights

- Premium surface COB range with metallic finish reflectors
- An attractive range of colours to choose from
- Deep recessed light source for low glare
- Focused 36 Degree beam angle
- Longer Life with 20,000 hours
- Super robust construction
- Wide voltage protection from 160V – 360V and surge protection up to 2.5kV
- Premium aluminium housing in White and Black with different combination
- No harmful UV radiation

	LED Spot Light	LED Spot Light
Colour	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium
Dimensions (mm)	56x56x73	80x80x91
Cutout Dia (mm)	-	-
Wattage	7W	12W
Lumen/CCT	525lm/3000K/4000K/6500K	1020lm/3000K/4000K/6500K

Voltage: 220V-240V~



FlexBeam



Rotatable and tiltable focused light

- Super bright light spectrum
- 85lm/ matt lumen efficacy
- Choice of directing the light to any direction with 360 degree rotation
- Deep recessed COB source for low glare
- Focused 36 Degree beam angle
- Longer Life with 20,000 hours
- Super robust construction
- Wide voltage protection from 160V – 360V and surge protection up to 2.5kV
- Premium white aluminum housing
- No harmful UV radiation

	FlexBeam	FlexBeam	FlexBeam	FlexBeam
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	White & Aluminum	White & Aluminum	White & Aluminum	White & Aluminum
Dimensions (mm)	87x87x60	97x97x64	108x108x80	108x108x89
Cutout Dia (mm)	77	88	98	98
Wattage	7W	12W	18W	22W
Lumen/CCT	600lm/3000K/ 4000K/6500K	1020lm/3000K/ 4000K/6500K	1530lm/3000K/ 4000K/6500K	1870lm/3000K/ 4000K/6500K

Voltage: 220V-240V~



COB Pro



Express elegance beautifully

- Super bright light spectrum
- Delivers: 90lm/watt
- Focused 36 degree adjustable beam
- Longer life with 35,000 hours
- Super robust construction
- Premium white aluminium housing
- Wide voltage protection from 160V–360V and surge protection up to 2.5kV
- No harmful UV radiation

	LED Spot Light	LED Spot Light	LED Spot Light	LED Spot Light
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	90x90x50	105x105x52	120x120x65	120x120x80
Cutout Dia (mm)	81	95	110	110
Wattage	7W	12W	18W	22W
Lumen/CCT	630lm/3000K/ 4000K/6500K	1080lm/3000K/ 4000K/6500K	1620lm/3000K/ 4000K/6500K	1980lm/3000K/ 4000K/6500K

Voltage: 220V-240V~



Aura StylEdge Downlighter



Light with style

- Decorative finish downlighter with hallmark silver ring for beautiful aesthetics
- Ultra thin trim for a seamless fit
- High lumen efficiency of 90lm/watt
- Aluminum housing for better performance
- Designed for robustness: wide voltage protection from 160V-360V
- Surge protection up to 2.5kV
- Available in 5W, 7W, 10W & 15W in round shape only

	LED Downlighter	LED Downlighter	LED Downlighter	LED Downlighter
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	87x87x45	110x110x47	121x121x47	150x150x47
Cutout Dia (mm)	78	100	110	137
Wattage	5W	7W	10W	15W
Lumen/CCT	450lm/3000K/ 4000K/6500K	620lm/3000K/ 4000K/6500K	900lm/3000K/ 4000K/6500K	1420lm/3000K/ 4000K/6500K

Voltage: 220V-240V~



PowerGlow

120lm
per watt[^]



Uplift your space with stylish lights

- Designed for diverse commercial spaces
- Ultra slim for a seamless blending with the ceiling
- High lumen efficiency of 120 lm/w
- Deep recessed light source for low glare and eye comfort
- Super robust with wide surge protection from 160-360V
- No harmful UV radiation

	LED Downlighter	LED Downlighter	LED Downlighter	LED Downlighter
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	White; Plastic + Aluminium			
Dimensions (mm)	152x152x44	152x150x44	174x174x52	174x174x52
Cutout Dia (mm)	144	144	164	164
Wattage	8.5W	10W	13.5W	16.5W
Lumen/CCT	1020lm/3000K/ 4000K/6500K	1200lm/3000K/ 4000K/6500K	1620lm/3000K/ 4000K/6500K	1980lm/3000K/ 4000K/6500K

Voltage: 220V-240V~ | Surge protection up to 2.5kV



DuraSlim

105lm
per watt[^]



Slimmest metal panel with 50k life hours!

- Premium aluminium housing with unique slim design
- Longer life of 50k hrs
- Only 10mm thickness to fit into all type of ceiling
- Extra bright light with 105 lm/watt
- Surge protection up to 2.5 kV with wide voltage protection 160-360V
- No visible flickering, no UV/IR and low glare to prevent eye strain
- Even and comfortable light perfected for your eye comfort
- Available in 5 wattages of 7W/12W/15W/18W/22W
- 6500K/4000K and 3000K CCTs in round/square form factor

	LED Downlighter	LED Downlighter	LED Downlighter	LED Downlighter	LED Downlighter
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	R: 120x120x10 S: 110x110x10	R: 160x160x10 S: 140x140x10	R: 180x180x10 S: 170x170x10	R: 20x200x10 S: 180x180x10	R: 225x225x10 S: 225x225x10
Cutout Dia (mm)	R: 105 S: 95	R: 145 S: 120	R: 165 S: 152	R: 185 S: 162	R: 208 S: 208
Wattage	7W	12W	15W	18W	22W
Lumen/CCT	735lm/3000K/ 4000K/6500K	1260lm/3000K/ 4000K/6500K	1575lm/3000K/ 4000K/6500K	1890lm/3000K/ 4000K/6500K	2310lm/3000K/ 4000K/6500K

Voltage: 220V-240V~



Slim Surface Mount+/ Surface Mount+

Sleeker
Design



A sleeker, slimmer, metal surface mount ceiling light

- Die-cast premium aluminium material for reliable performance
- Even and comfortable light perfected for your eye comfort
- No visible flickering, no UV/IR and low glare to prevent eye strain
- Surge protection up to 2.5 kV with wide voltage protection 160-360V
- Improved lumen (80lm/w)
- Life of 35,000 hours
- BIS safety standard, IEC 60598 registered and tested for 35° Ta

	LED Surface Downlighter	LED Surface Downlighter	LED Surface Downlighter	LED Surface Downlighter
Colour	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW	WW/CDL/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	R: 90x90x35 S: 90x90x35	R: 164x164x30 S: 144x144x30	R: 187x187x30 S: 181x181x30	R: 235x235x46 S: 230x230x46
Wattage	3W	12W	15W	22W
Lumen/CCT	190lm/3000K/ 4000K/6500K	920lm/3000K/ 4000K/6500K	1200lm/3000K/ 4000K/6500K	1840lm/3000K/ 4000K/6500K

Voltage: 220V-240V~



Linea Sharp Slim



Brighter light, longer life

- Strong focused 33° beam
- Wide voltage tolerance 160V-360V
- Glare free - easy on the eye
- Slimmer design for minimalistic look
- Super robust construction
- Premium aluminum housing for better heat management
- Wide voltage protection from 160V-360V and surge protection up to 2.5kV

	Linea Sharp Slim	Linea Sharp Slim	Linea Sharp Slim	Linea Sharp Slim	Linea Sharp Slim	Linea Sharp Slim
Colour	WW/NW	WW/NW	WW/NW	WW/NW	WW/NW	WW/NW
Material	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum
Dimensions (mm)	51x32x40	62x32x40	52x52x40	108x32x40	71x71x40	204x32x40
Cutout Dia (mm)	45x26	57x27	47x47	102x26	197x26	197x26
Wattage	2.5W	4W	6W	8W	10W	15W
Lumen/CCT	140lm/ 3000K/4000K	225lm/ 3000K/4000K	400lm/ 3000K/4000K	520lm/ 3000K/4000K	650lm/ 3000K/4000K	975lm/ 3000K/4000K

Voltage: 220V-240V~



Linea Sharp



Brighter light, longer life

- Strong focused 40° beam
- Wide voltage tolerance 160V-360V
- Glare free - easy on the eye

	LED Spotlight	LED Spotlight	LED Spotlight	LED Spotlight	LED Spotlight
Colour	WW/NW	WW/NW	WW/NW	WW/NW	WW/NW
Material	Aluminium	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	45x45x49	75x45x49	147x45x49	280x45x49	413x45x49
Cutout Dia (mm)	37x37	66x36	139x36	271x36	403x36
Wattage	3W	6W	10W	20W	30W
Lumen/CCT	150lm/ 3000K/4000K	525lm/ 3000K/4000K	700lm/ 3000K/4000K	1400lm/ 3000K/4000K	2100lm/ 3000K/4000K

Voltage: 220V-240V~ | Surge Protection up to 2.5kV






PROFILE LIGHTING

Philips profile strips are an innovation in customizable home illumination for the perfect ambience. With increased number of LEDs, these profile lights provide uniform light output when put in any type of profiles.

Take your creativity to the next level and experiment with new designs to accentuate the interiors.



ProGlow Nxt & Slim Edge Profile Strip

1000lm
per Mtr*



600lm
per Mtr*



Turn any ambience perfect

Express yourself with the Philips Profile lighting. This flexible LED tape is perfect solution for most of profile giving you the required design and ambience.

- Accentuates your interiors
- High quality LED for bright and true shades of white
- Flexible and customisable
- Superior adhesive for easy installation

	Profile Strip Light	Profile Strip Light
Colour	WW/CDL/NW	WW/CDL/NW
Material	NA	NA
Dimensions (mm)	5000x10x0.2	5000x5x0.2
No. of LEDs	264 LED/mtr	144 LED/mtr
Recommended driver by Philips	12V 5A	12V 2A
Wattage	50W without driver	70W
Lumen	1000lm/mtr	600lm/mtr





COVER LIGHTING

Philips LED strip lights is an innovation in customizable home illumination for the perfect ambiance to your liking. Unlike fluorescent tubes, flexible LED strip lights can be curved around corners, trimmed and connected to any required length.

Take your creativity off the straight and narrow, and experiment in exploring new ways to use to LED strip lights.



Linea Bright/Glow/Premium/Blue & ColorMagic 3 in 1

500lm per Mtr*

900lm per Mtr*



Low glare light for your enhanced eye comfort

Get enchanted with the beautiful ambience created by LineaBright. The customisable LED tape comes with superior adhesive for ease of installation.

- High quality LED for bright and true shades of white
- Flexible and customisable
- Superior adhesive for easy installation

	LineaBright	Linea Premium	Blue Strip	ColourMagic 3 in 1	LineaGlow
Colour	WW/CDL/NW	WW/CDL/NW	Blue	WW/NW/CDL	(WW/NW/CDL)
Material	NA	NA	NA	NA	NA
Dimensions (mm)	5000x8x0.3 (5 mtr.)	5000x8x0.3 (5 mtr.)	5000x8x0.2 (5 mtr.)	5000x10x0.3	5000x10x2
No. of LEDs	72 LED/mtr	60 LED/mtr	60 LED/mtr	120 LED/mtr	120 LED/mtr
Wattage	28W with driver	50W LED with driver	25W LED	28W with driver	70W without driver
Lumen	500lm/mtr	900lm/mtr	-	3100lm for 5 mtr	1200lm/mtr

Voltage: 220-240V



BATHROOM

Bathroom and kitchen are most involved and intimate spaces in your house. Recreating these spaces with right quality of light and using right form factor for light is extremely important for harmony and wellbeing of the entire family.

The right colour elevates sensory experiences and creates true delight for all. Right form factor ensures that visual fatigue is kept to minimum and space looks light and cheery.



Model No. 582004

Artizy



Model No. 582004



Model No. 582005



Model No. 582006

Bathroom adoration with minimal efforts

These wall lights create ambient light to give a warm and diffused glow in the room. It can light up specific bathroom areas making your bathroom chores smooth like shaving and applying makeup. Now give your bathroom a feel of luxury with these decorative wall lights.

- Perfect chrome finish
- Tunable white for ambience (switch from cool blue light to warm white light through simple switch toggles)
- IP44 protection (makes it perfect for use in bathroom)

	Single Head Wall Light	Double Head Wall Light	Single Head Wall Light
Model No.	582004	582005	582006
Colour	Chrome	Chrome	Chrome
Material	Metal	Metal	Metal
Dimensions (mm)	120x120x85	320x120x95	120x200x92
Lamp Base	LED Integrated	LED Integrated	LED Integrated
Wattage	5W	10W	5W
Lumen/CCT	370lm/ (WW/NW/CW on Toggle)	650lm/ (WW/NW/CW on Toggle)	350lm/ (WW/NW/CW on Toggle)

Voltage: 240V/50 Hz.



Model No. 581915

Poise



Easy on the eye, light on the senses

Want shiny teeth and complexion? Then you'll need to be able to see yourself in the best light. This Philips range is just right for your bathroom with IP44 moisture protection, a reduced glare, premium opal glass housing and chrome mount for a mirror finish.

- Designed for humid environment
- Premium glass for reduced glare
- Long life LED light source
- Robust metal construction
- Adjustable head with swivel joint

	LED Wall Light	LED Wall Light
Model No.	581915	581916
Colour	Chrome	Chrome
Material	Metal	Metal
Dimensions (mm)	175x175x120	345x150x85
Lamp Base	LED Integrated	LED Integrated
Wattage	6W	9W
Lumen/CCT	210lm/3000K	450lm/6000K

Voltage: 240V/50 Hz.



Model No. 581921

Atom, Jade & Emporia



Model No. 581922
Atom



Model No. 581921
Emporia



Model No. 581925
Jade

Fresh, clean, and safe

Get ready fast for school or work, or create an oasis to enjoy a relaxing bath and a good book. Sufficient functional lighting is needed in front of the mirror. Place lights above and to the sides of the mirror, in order to reduce shadows on the face while shaving or applying/removing makeup.

- Designed for humid environment
- Premium glass for reduced glare
- Long life LED light source
- Robust metal construction

	LED Wall Light	LED Wall Light	LED Wall Light
Model No.	581922	581921	581925
Colour	White	Chrome	Chrome
Material	Metal	Metal	Metal
Dimensions (mm)	140x140x125	165x100x165	120x160x220
Lamp Base	LED Integrated	LED Integrated	LED Integrated
Wattage	7W	7W	6W
Lumen/CCT	350lm/3000K	520lm/3000K/6000K	450lm/3000K/6000K

Voltage: 240V/50 Hz.



Model No. 581918

Majesty



Model No. 581918

Add the style, enhance the clarity

It takes more than soap and water to keep a person well groomed. Choose this range for a bright and shiny look for yourself and your bathroom. This coordinated range provides maximum clarity with minimal glare and is just right for your bathroom with IP44 moisture protection, a premium opal glass housing and chrome mount for a mirror finish.

- Robust metal construction
- Designed for humid environment
- Adjustable head with swivel joint
- Premium glass for reduced glare
- Long life LED light source

	Ceiling Light
Model No.	581918
Colour	Chrome
Material	Metal
Dimensions (mm)	500x500x95
Lamp Base	LED Integrated
Wattage	27W
Lumen/CCT	2300lm/3000K

Voltage: 240V / 50 Hz



Model No. 58157

Aquila & Vega



Model No. 58157
Aquila



Model No. 58158
Vega

Light and relaxed

The aesthetic design with chrome finish & bright output of Aquila & Vega will boost the look of every mirror and stay on the wall as modern decorative fixtures.

- Superior illumination
- Polished chrome finish
- White glass shade
- Optimum performance

	Wall Light	Wall Light
Model No.	58157	58158
Colour	Polished chrome finish	Polished chrome finish
Material	Metal	Metal
Dimensions (mm)	395x105x140	595x105x140
Lamp Base	LED Integrated	LED Integrated
Wattage	15W	22W
Lumen/CCT	1275lm/3000K	2000lm/3000K

Voltage: 220-240V





TRACK LIGHT

Be it public spaces or private homes, Track Lights offer an efficient and elegant way to illuminate your spaces - anytime of night or day.

Philips offers a range of versatile Track Lights that are easily installable on ceiling or wall mounted fixtures, and offer a tasteful approach to illumination.

Be it the relaxing glow of 'warm lighting' for intimate home moments, or the energetic spark of 'cold lighting' to enhance retail ambiances and experiences - the Philips Track Light range delivers the best of style, performance and value.



Stanchion Track Light



Model No. 31445



Model No. 31446



Model No. 31447



Model No. 31448



Track 1 meter

Reimagine retail

There's more to things than meets the eye, Philips track light range is a must for every retail outlet which will not only enhance the product appearance but take it from usual to the ultimate best.

- Customizable wattage options
- Long-lasting fixture
- Robust metal construction
- Functional, minimal design
- Perfect fit for any home/outlet

	Track Head	Track Head	Track Head	Track Head
Model No.	31445	31446	31447	31448
Colour	Black&White	Black&White	Black&White	Black
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	180x50x110	158x65x125	165x82x154	122x68x130
Lamp Base	LED	LED	LED	GU10
Wattage	10W	20W	30W	1x10W Max*
Lumen/CCT	700lm/WW,CW, NW	1500lm/WW,CW, NW	2150lm/WW,CW, NW	-

* Not Included





OUTDOOR

Other than the functional requirements of lighting and security, Outdoor lighting truly goes beyond illumination. Outdoor lighting defines the silhouette of the home, the very character of it.

The right combination of design and placement can elevate and take the outdoor experience to an entire next level. The texture and vibrancy of the walls, the garden and the greenery, the fountain and everything else can be accentuated with the wide variety of archetypes available.

Philips lifestyle offers widest variety of Outdoor collection in all design languages. The lasting look and performance of these luminaires are a testimony of great design, sturdy build, and impeccable finish.



Model No. 582049



Model No. 582048

Alfresco




Model No. 582049



Model No. 582048



Model No. 582052



Model No. 582051



Model No. 582050


Designed to light up your walkway

These elegantly designed wall lights are easy to install. It comes with soft corners and anthracite colours accentuate the gentle throw of the light. Now easily light up your balcony/patio, poolside with evenly distributed, comfort lights.

- Dust proof
- No ingress of dust
- Protected against jets of water
- Powder coated aluminium fixture
- Ideal for garden, balcony/patio, poolside

	Round Pattern Wall Light	Square Pattern Wall Light	Wall Light	Wall Light	Wall Light
Model No.	582049	582048	582052	582051	582050
Colour	Anthracite	Anthracite	Anthracite	Anthracite	Anthracite
Material	Aluminium	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	183x41x148	183x42x120	167x167x99	167x167x99	256x85x85
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	12W	12W	10W	10W	10W
Lumen/CCT	720lm/WW	720lm/WW	750lm/WW	450lm/ WW	450lm/WW

Voltage: 220-240V.



Model No. 582009

Russet



Model No. 582009

Beautiful pattern with visual delight

This exquisite decorative wall washer creates a beautiful up and down lighting effect, that adds romantic & harmonious ambience to your room as well as your exterior surroundings.

- Exquisite light effect
- Tunable white for ambience (switch from cool blue light to warm white light through simple switch toggles)
- IP44 protection (makes it perfect for use in moist areas as well)

	Two-way Wall Washer
Model No.	582009
Colour	Outside: Black, Inside: Reddish Brown
Material	Metal
Dimensions (mm)	200x95x127
Lamp Base	LED Integrated
Wattage	10W
Lumen/CCT	850lm/(WW/NW/CW on Toggle)

Voltage: 220-240V.



Model No. 582061



Model No. 582060

Radiant

IP65



Model No. 582060



Model No. 582061

Exquisite pattern with visual delight

With modern, minimalistic design, this wall light exudes a distinct look when installed on the walls of buildings, gardens and along pathways. It can be strategically put to highlight your surroundings with exquisite patterns. The two-way directional light on either side of the wall, illuminates a larger surface area for a magical look.

- Unique shape
- Premium finish
- Beautiful pattern

	One-way Wall Washer	Two-way Wall Washer
Model No.	582060	582061
Colour	Black	Black
Material	Aluminium	Aluminium
Dimensions (mm)	78x87x43	145x87x43
Lamp Base	LED Integrated	LED Integrated
Wattage	5W	10W
Lumen/CCT	475lm/WW	950lm/WW

Voltage: 220-240V.



Model No. 581933

Gamma



Model No. 582088



Model No. 581933



Model No. 581934



Model No. 581935

Designed to delight

These elegantly designed wall washers are a perfect draw out of the modern design. Soft corners and anthracite colour accentuate the gentle throw of the light in two directions. IP65 rating assures product usage both in interiors as well as exteriors.

- Superior illumination
- Classy anthracite finish
- Premium aluminum material
- Optimum performance
- IP65 fixture ideal for outdoor and wet areas

	One-Way Wall Washer	Two-Way Wall Washer	Two-Way Wall Washer	Two-Way Wall Washer
Model No.	582088	581933	581934	581935
Colour	Anthracite	Anthracite	Anthracite	Anthracite
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	79x77x36	79x77x36	119x80x38	168x80x41
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	3W	2W	4W	7W
Lumen/CCT	230lm/3000K	100lm/3000K	250lm/3000K	382lm/3000K

Voltage: 220-240V.



Model No. 58162



Model No. 31450



Model No. 58163

Alpha, Trigon & Propulsio

IP65



Model No. 58162
Alpha



Model No. 58163
Trigon



Model No. 31450
Propulsio

Add charisma to your space

These elegantly designed wall washers are a perfect draw out of the modern design. Soft corners and anthracite colour accentuate the gentle throw of the light in two, three and four directions.

- Superior illumination
- Classy anthracite finish
- Premium aluminium material
- Optimum performance
- Highlight the outdoors
- IP65 fixture ideal for outdoor & wet areas

	Wall Washer	Wall Washer	Wall Washer
Model No.	58162	58163	31450
Colour	Anthracite	Anthracite	Anthracite
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	111x111x100	165x165x49	159x99x66
Lamp Base	LED Integrated	LED Integrated	LED Integrated
Wattage	12W	9W	10W
Lumen/CCT	950lm/3000K	550lm/3000K	670lm/3000K

Voltage: 220-240V.



Model No. 34152

Step Lights



Model No. 31435
Surface



Model No. 30974
Recessed



Model No. 34151
Recessed



Model No. 34152
Recessed



Model No. 31436
Surface

An urbane elevation

The neatly designed modern and minimal step light melds into the background settings and provides just the right ambient illumination to create an interesting setting.

- LED light with beautiful light pattern
- Highlight the outdoors
- Endurance meets contemporary style
- Clean lines, sleek design, warm white light
- Robust finish
- Long life LED source

	Step Light	LED Step Light	LED Step Light	LED Step Light	LED Step Light
Model No.	31435 (IP65)	30974 (IP44)	34151 (IP44)	34152 (IP44)	31436 (IP44)
Colour	Anthracite grey	White	Anthracite grey	Anthracite grey	Anthracite grey
Material	Aluminium	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	104x104x35	85x85x32	84x84x44	115x84x44	201x91x35
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	3W	2W	2W	3W	5W
Lumen/CCT	50lm/3000K	30lm/3000K	30lm/3000K	85lm/3000K	165lm/3000K

Voltage: 220V-240V



Model No. 31385

Garden Spike

IP65



Model No. 581938



Model No. 31385



Model No. 31386

Spike up the gorgeousness

The well-designed modern and rugged Garden Spike is a great addition to highlight your garden spaces. COB integrated lighting keeps the product high on light dispersion and efficiency.

- 80% energy savings
- Outdoor ambient lighting
- Protection against dust & jet of water from any direction
- IP65 fixture ideal for outdoor & wet areas

	Garden Spike	Garden Spike	Garden Spike
Model No.	581938	31385	31386
Colour	Black	Anthracite	Anthracite
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	100x61x47	100x75x75	122x85x85
Lamp Base	LED COB Integrated	LED COB Integrated	LED COB Integrated
Wattage	3W	7W	12W
Lumen/CCT	150lm/3000K	360lm/3000K/4000K Red,Green,Blue,Amber	625lm/3000K/4000K

Voltage: 220V-240V



Model No. 58174 | 58176

Glide

IP65



Model No. 58174



Model No. 58176



Model No. 58175

Walk on the stylish side

The wonderful design of Glide is a stylish way to enjoy your outdoor moments. High-quality materials and classic finish fit perfectly with your personal style.

- Highlight the outdoors
- IP65 fixture ideal for gardens
- Black premium finish

	Wall Lantern	Post Lantern	Pedestal Lantern
Model No.	58174	58175	58176
Colour	Black	Black	Black
Material	Aluminium	Aluminium	Aluminium
Dimensions (mm)	156x260x290	156x156x337	156x156x600
Lamp Base	E27	E27	E27
Wattage	1x9W Max	1x9W Max	1x9W Max

Voltage: 220-240V.



Model No. 58168 | 58169

Yolo & Blade

IP65



Model No. 58168
Yolo



Model No. 58169
Yolo



Model No. 58172
Blade



Model No. 58173
Blade

Light up your path

Enjoy a beautiful garden with an IP 65 range of outdoor lights. This outdoor range is especially designed for harsh outdoor environments.

- LED light with beautiful light pattern
- Highlight the outdoors
- IP65 fixture ideal for gardens
- Black premium finish

	Wall Lantern	Pedestal Lantern	Wall Lantern	Pedestal
Model No.	58168	58169	58172	58173
Colour	Black	Black	Black	White & Black
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	90x125x265	85x85x800	90x125x200	85x85x500
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	9W	9W	9W	9W
Lumen/CCT	460lm/3000K	460lm/3000K	350lm/3000K	350lm/3000K

Voltage: 220-240V



Model No. 58171

Pylon



Outline the outdoors... stunningly.

Enjoy a beautiful garden with an IP 65 range of outdoor lights. This outdoor range is especially designed for harsh outdoor environments.

- LED light with beautiful light pattern
- Highlight the outdoors
- IP65 fixture ideal for gardens
- Black premium finish

	Wall Lantern	Pedestal Lantern	Wall Lantern	Pedestal Lantern
Model No.	58170	58171	58166	58167
Colour	Black	Black	Black	Black
Material	Aluminium	Aluminium	Aluminium	Aluminium
Dimensions (mm)	90x125x200	85x85x650	100x110x137	195x195x650
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	9W	9W	5W	5W
Lumen/CCT	360lm/3000K	360lm/3000K	360lm/3000K	360lm/3000K

Voltage: 220-240V





IP67

All Weather In-Ground Lights

IP65

All Weather Surface Lights



A weather-proof fixture!

Designed for harsh outdoor conditions of dust & water with IP67 rating. The product offers uniform light output ensuring best in class performance.

- An affordable inground light suitable for - gardens & patios, pool areas, other high-exposure areas
- IP67 rating means the fixture is protected in most types of weather (dust & rain + protected from temporary immersion in water)
- Diffused soft light: perfect for outdoor lighting & low on glare
- Able to handle surge protection up to 2 kV
- Dust-proof - No Ingress of dust

	LED Inground Light	LED Inground Light	LED Inground Light	LED Surface Light
Model No.	—	—	—	—
Colour	Grey	Grey	Grey	WW/CW
Material	Metal	Metal	Metal	Rust-free synthetic
Dimensions (mm)	55x55x90.6	65x65x92	75x75x103	205x205x54
Lamp Base	LED Integrated	LED Integrated	LED Integrated	LED Integrated
Wattage	3W	5W	10W	12W
Lumen/CCT	160lm	250lm	500lm	840lm

Voltage: 220-240V

Product Descriptions	MRP
CHANDELIERS	
581964 Naica Chandelier MSS Titanium Bold Black	56,500/-
581965 Naica Pendant MSS Titanium Gold Black	59,500/-
581966 Naica Wall MSS Titanium Gold Black G9	7,990/-
581976 Gladius Chandelier Gold & Clear Crystal	55,990/-
581977 Gladius Pendant Gold & Clear Crystal E1	57,500/-
581978 Gladius Wall Gold & Clear Crystal G9	9,490/-
581972 Flagship Pendant White & Gold E27 4*Max	32,990/-
581973 Flagship Pendant White & Gold E27 6*Max	35,990/-
581974 Flagship Wall White & Gold E14 1*Max 40	6,990/-
581975 Flagship Wall White & Gold E14 2*Max 40W	9,990/-
581968 Shield Chandelier Chrome & Clear Crystal	45,500/-
581969 Shield Pendant Chrome & Clear Crystal E2	55,500/-
581970 Shield Pendant Chrome & Clear Crystal E1	72,500/-
581971 Shield Wall Chrome & Clear Crystal G9	9,900/-
581963 Inlay Pendant Clear Crystal Gold E14	57,500/-
581967 Crystal Chandelier MSS Titanium Gold G9	57,500/-
581865 Caesar Wall Crystal SS G9 1*MAX 42W	8,730/-
581864 Caesar Pendant Crystal SS G9 6*MAX 42W	35,240/-
581863 Caesar Crystal SS G9 5*MAX 42W	25,880/-
581846 Corona Pendant Crystal SS Chrome G9 7*MAX 42W	36,460/-
581847 Corona Crystal SS Chrome G9 7*MAX 42W	32,430/-
581886 Corona Pendant Crystal SS Chrome G9 5*42W	42,100/-
581848 Corona Wall Crystal SS Chrome G9	6,520/-
581857 Monarch Chandelier Crystal Ag Al Rod E14 6*MAX 60W	33,940/-
581858 Monarch Wall Crystal Ag Al Rod E14 1*MAX 60W	6,000/-
581885 Monarch Chandelier Crystal Ag Al Rod E14 9*MAX 60W	41,430/-
581842 Allure Pendant Crystal Chrome G9 5*MAX 42W	49,320/-
581843 Allure Crystal French Gold G9 4*MAX 42W	30,620/-
581845 Corral Chandelier Crystal SS G9 5*MAX 42W	23,430/-
581906 Chalice Chandelier Crystal Cognac Glass SS G9 6*MAX 42W	39,900/-
581841 Chalice Chandelier Crystal Cognac Glass SS G9 6*MAX 42W	28,540/-
581844 Crescent Pendant Crystal Ivory Gold G9 5*MAX 42W	39,840/-
581884 Crescent Pendant Crystal Chrome G9 5*MAX 42W	30,240/-

Product Descriptions	MRP
581849 Cameo Crystal Round G9 5*33W Max	21,450/-
581850 Cameo Crystal Square G9 5*33W Max	16,340/-
581903 Splendora Pendant Anodized G9 7*42W	29,420/-
581904 Splendora Ceiling Anodized G9 7*42W	27,220/-
581905 Splendora Single Wall Light G9 1*42W	6,360/-
581901 Torrent Pendant Clear Crystal SS G9 6*MAX 42W	58,170/-
581902 Torrent 1H Wall Light Clear Crystal SS G9	7,910/-
581853 Regalia Pendant Borosilicate Glass	25,100/-
581852 Regalia Double Wall Clear Glass C	6,790/-
581851 Regalia Single Wall Clear Glass C	4,260/-
581854 Umbra Pendant Borosilicate Glass Chrome & Red CU GG9 8*MAX 33W	31,260/-
LEAD FAMILIES	
582065 Lucidus 5H Pendant Down E27	19,490/-
582066 Lucidus Wall 1H Down E27	5,990/-
582026 Ornate Wood Table Lamp E27 1*Max20W	3,640/-
582084 Ornate Wood Floor Lamp E27	10,990/-
582012 Marvel Wall Light E27 1*Max 10W	5,990/-
582011 Marvel Pendant E27 1*Max 20W	6,330/-
582015 Motif Mesh Droplet E27 1*Max 20W	6,330/-
582014 Motif Mesh Globe E27 1*Max 20W	6,760/-
582013 Motif Mesh Cylinder E27 1*Max 20W	6,970/-
582016 Motif Wall Light E27 1*Max 10W	5,990/-
58145 Jazz Wall Light Single	4,150/-
58145 Jazz Wall Light Double	6,800/-
58147 Jazz Pendant Single	5,800/-
58148 Jazz 3 Head Pendant	10,350/-
58149 Jazz Table Lamp	5,500/-
58150 Jazz Floor Lamp	8,950/-
58135 Roseate Wall Light Double	8,000/-
58135 Roseate Wall Light Single	4,700/-
58137 Roseate Pendant Single	8,000/-
58138 Roseate 3 Head Pendant	12,150/-
58139 Roseate Table Lamp	6,600/-
58140 Roseate Floor Lamp	10,950/-

Product Descriptions	MRP
31425 Muziris Single Head Wall Light	3,050/-
31426 Muziris Double Head Wall Light	5,100/-
31434 Muziris Laminar Wall Light	2,750/-
31429 Muziris 1 Head Cylindrical Pendant	2,750/-
31430 Muziris 3 Head Cylindrical Pendant	7,600/-
31431 Muziris 1 Head Gold Cylindrical Pendant	3,450/-
31432 Muziris 3 Head Gold Cylindrical Pendant	8,300/-
31402 Muziris 7W Picture Light	3,150/-
31403 Muziris 12W Picture Light	3,550/-
581999 Muziris 22W Bronze Picture Light	7,490/-
58071 Grandeur Wall Light Double	5,650/-
58071 Grandeur Wall Light Single	3,150/-
58072 Grandeur Pendant 3 Head Pendant	8,950/-
581871 Floret 6W LED Single Wall Lamp	3,350/-
581872 Floret 12W LED Double Wall Lamp	5,200/-
581873 Floret 6W LED Table Lamp	4,000/-
581876 Striker Single Wall Lamp 1* E27	4,600/-
581877 Striker Table Lamp 1* E27	4,600/-
581878 Striker Floor Lamp 1* E27	8,950/-
581874 Sierra Floor Lamp White 1* E27	9,200/-
581875 Arc Floor Lamp White 1* E27	13,800/-
PENDANTS & CEILING	
582047 Ritzy Pendant Opal E27	8,560/-
582017 Gemini Red+Silver E27 1*Max 20W	5,490/-
582018 Gemini Silver+Gold E27 1*Max 20W	5,490/-
582019 Gemini Ivy League+White E27 Max20W	5,490/-
582021 Hemis Matt Black+Gold E27 1*Max20W	4,830/-
582020 Hemis Crimson Brown E27 1*Max 20W	4,830/-
582025 Vivid Pendant Ivy League E27Max20W	3,990/-
582024 Vivid Pendant Matte Gold E27Max20W	3,990/-
582023 Vivid Pendant Blue E27 1*Max20W	3,990/-
30898 Ceiling lamp chrome 4x42W 230V	24,880/-
30899 Pendant Chrome 4x42W 230V	26,920/-
58074 Beacon Pendant Rose gold and Silver	4,450/-

Product Descriptions	MRP
58074 Beacon Pendant Wine and Silver	4,450/-
58076 Blithe 3 Head Pendant Wine and Silver Round	11,050/-
58076 Blithe 3 Head Pendant Rosegold and Silver Round	11,050/-
58078 Blithe 3 Head Pendant Wine and Silver Linear	10,750/-
58078 Blithe 3 Head Pendant Rosegold and Silver Linear	10,750/-
58127 Tawny Pendant Copper	5,800/-
41058 Lustre Pendant Black 1x24W 230V	4,324/-
41058 Lustre Pendant Chrome 1x24W 230V	4,324/-
41058 Lustre Pendant Copper 1x24W 230V	4,324/-
41058 Lustre Pendant Gold 1x24W 230V	4,324/-
31451 Vintage Cord Rose Gold	1,450/-
31452 Vintage Cord Brush Bronze	1,450/-
582010 Dome Ceiling Light 32W	11,780/-
582056 Saturn 18W LED Ceiling Light IP44 Brown/Gold Outer Ring WW/CW	3,430/-
582057 Saturn 24W LED Ceiling Light IP44 Brown/Gold Outer Ring WW/CW	4,720/-
581898 Summit 25W LED Ceiling Light WW/CW	5,500/-
581899 Crown LED Ceiling Light 1X22W CW	5,650/-
581900 Willow LED Ceiling Light 1X22W WW	10,950/-
WALL LIGHTS	
582063 Ebony Wall Light 15W WW	5,900/-
582002 Delight Wall Light 1H 5W IP44 (Chrome)	7,490/-
582003 Delight Wall Light 1H 5W IP44 (White)	7,490/-
582008 Bling Wall Light 1H 5W IP44	6,410/-
582007 Bling Wall Light 2H 10W IP44	9,630/-
581923 Aster Wall Light 1H 7W	3,000/-
58154 10W Duo Led Wall Light	4,550/-
58155 20W Duo Led Wall Light	6,300/-
581917 Roman 6W LED Wall Light WW/CW	3,350/-
582105 Oriel Jal 15W Dimmable	3,800/-
582104 Oriel Classic 15W Dimmable	3,800/-
582103 Oriel Giraffe 15W Dimmable	3,800/-
30978 Brushed Nickel Wall Light 1H	2,450/-
30979 Brushed Nickel Wall Light 2H	4,250/-
31453 Trunk Wall Light 1H	3,550/-

Product Descriptions	MRP
31454 Trunk Wall Light 2H	6,800/-
31457 Tale Wall Light 1H	3,550/-
31458 Tale Wall Light 2H	6,800/-
31455 Chiffe Wall Light 1H	3,550/-
31456 Labyrinth Wall Light 2H	6,800/-
58184 Platina Wall Light - Single	3,450/-
58070 Glint Wall Light - Single	3,550/-
58185 Blush Wall Light - Single	3,450/-
581879 Aspire Single Spot GU 10	2,750/-
581919 Nixon White 1H 7W WW	2,950 /-
581919 Nixon Chrome 1H 7W WW	3,050/-
581880 Aspire Double Spot GU 10	4,150/-
581881 Vista Single Wall 1* E14	3,450/-
34303 Grace Wall Light - Single	1,500/-
34302 Stylo Wall Light - Single	1,400/-
34304 Trendo Wall Light - Double	2,450/-
30975 Bedside Light LED 2W	1,700/-
48042 Bedside Light 3W LED White 3000K	2,250/-
48042 Bedside Light 3W LED Black 3000K	2,250/-
31437 Hint Bedside Light WH 3000K	3,850/-
31440 Picture Lights 12W Chrome	3,100/-
31441 Picture lights 12W Silver	3,100/-
30973 Picture Light LED 6W 3000K	2,750/-
48043 Picture Light Chrome LED 10W 30K	3,150/-
48027 Ultron LED Wall Light WW/CW 17W 1350lm	1,600/-
48027 Ultron Scene Switch Plus	2,100/-
DESKLIGHTS	
61013 Breeze LED Desklight White	1,450/-
61013 Air LED Desklight Black	1,450/-
581931 SKYY LED Desklight	2,050/-
31438 Hint Table Lamp WH 30K	4,100/-
581932 Orbit LED Desklight	2,200/-
581930 Cosmos Rechargeable LED Desklight	2,900/-

Product Descriptions	MRP
DOWNLIGHTERS	
IP44 Low Glare COB 7W	2,700/-
IP44 Low Glare COB 12W	3,500/-
IP44 Low Glare COB 20W	4,700/-
Deco COB LED Spot Light 7W	2,580/-
Deco COB LED Spot Light 12W	3,230/-
Thin Trim Dimmable Deep Recessed 7W COB	2,050/-
Thin Trim Dimmable Deep Recessed 12W COB	2,740/-
Thin Trim Dimmable Deep Recessed 18W COB	4,110/-
Thin Trim Dimmable Deep Recessed 7W COB Dimmable	2,850/-
Thin Trim Dimmable Deep Recessed 12W COB Dimmable	3,430/-
Surface COB 7W	2,280/-
Surface COB 12W	3,120/-
Surface COB 18W	4,310/-
Deco Surface COB Spot Light 7W	2,590/-
Deco Surface COB Spot Light 12W	3,420/-
FlexBeam COB 7W	1,900/-
FlexBeam COB 12W	2,500/-
FlexBeam COB 18W	3,725/-
FlexBeam COB 22W	4,345/-
FlexSpot COB 10W	4,650/-
FlexFocus COB 3W	1,290/-
COB Pro LED Spot Light 7W	1,870/-
COB Pro LED Spot Light 12W	2,460/-
COB Pro LED Spot Light 18W	3,670/-
COB Pro LED Spot Light 22W	4,280/-
Aura StyleEdge LED Downlighter 5W	1,480/-
Aura StyleEdge LED Downlighter 7W	1,730/-
Aura StyleEdge LED Downlighter 10W	2,090/-
Aura StyleEdge LED Downlighter 15W	2,470/-
PowerGlow LED Downlighter 8.5W	1,670/-
PowerGlow LED Downlighter 10W	1,860/-
PowerGlow LED Downlighter 13.5W	2,110/-

Product Descriptions	MRP
PowerGlow LED Downlighter 16.5W	2,700/-
DuraSlim LED Downlighter 7W	1,270/-
DuraSlim LED Downlighter 12W	1,600/-
DuraSlim LED Downlighter 15W	2,040/-
DuraSlim LED Downlighter 18W	2,560/-
DuraSlim LED Downlighter 22W	3,220/-
Surface Mount+ LED Surface Downlighter 3W	1,260/-
Slim Surface Mount+ LED Surface Downlighter 12W	2,200/-
Slim Surface Mount+ LED Surface Downlighter 15W	2,440/-
Surface Mount+ LED Surface Downlighter 22 W	3,960/-
Linea Sharp 3W	1,580/-
Linea Sharp 6W	2,330/-
Linea Sharp 10W	3,620/-
Linea Sharp 20W	9,040/-
Linea Sharp 30W	11,510/-
Linea Sharp Slim 2.5W	1,580/-
Linea Sharp Slim 4W	2,100/-
Linea Sharp Slim 6W	2,460/-
Linea Sharp Slim 8W	3,510/-
Linea Sharp Slim 10W	3,865/-
Linea Sharp Slim 15W	6,325/-
PROFILE/COVE LIGHTING	
ProGlow Nxt (264 LED/ Mtr)	3,600/-
Slim Edge (144 LED/Mtr)	3,000/-
Linea Bright (72 LED /Mtr)	2,980/-
Linea Premium (60 LED/Mtr)	4,260/-
ColorMagic 3 in 1 (Tunable)	3,575/-
Linea Glow (120 LED/Mtr)	2,450/-
LED Strip Blue	3,290/-
BATHROOM	
582004 Artizy 5W IP44 Round Wall light	5,340/-
582006 Artizy 5W IP44 Vertical Wall light	5,340/-
582005 Artizy 2H 10W IP44 Wall light	8,560/-
581915 Poise 6W IP44 LED Wall Light	3,300/-

Product Descriptions	MRP
581916 Poise 9W IP44 LED Wall Light CW	5,200/-
581922 Atom 7W IP44 LED Wall Light WW	2,150/-
581925 JADE 6W IP44 LED WALL LIGHT WW/CW	4,950/-
581921 Emporia 7W IP44 LED Wall Light WW/CW	3,700 /-
581918 Majesty 27W 2300lm WW IP44 LED	11,500/-
58157 Aquila 15W Led Wall Light	5,100/-
58158 Vega 22W LED Wall Light	6,100/-
TRACK LIGHT	
31442 Stanchion Track 1 Meter White/Black	1,400/-
31445 Track Light Stanchion Track Black/White 10W Head NW/CW/WW	4,450/-
31446 Track Light Stanchion Track Black/White 20W Head NW/CW/WW	5,250/-
31447 Track Light Stanchion Track Black/White 30W Head NW/CW/WW	6,600/-
31448 Track Light Stanchion Track GU10 Head Black	2,050/-
OUTDOOR	
582050 Alfresco HorizLong 10W	7,940/-
582052 Alfresco Square Plain 10W	7,940/-
582048 Alfresco Square Pattern 12W	8,560/-
582049 Alfresco Round Pattern 12W	8,560/-
582051 Alfresco Square Grill 10W	9,630/-
582009 Russet Two-way Wall Washer10W IP44	8,130/-
582060 Radiant One-way Wall Washer 5W	2,360/-
582061 Radiant Two-way Wall Washer10W	3,430/-
582088 Gamma 3W One-Way	2,350/-
58159 Gamma 2W Single Head LED Wall Light	2,900/-
58160 Gamma 4W Double Head LED Wall Light	3,750/-
58161 Gamma 7W, Three Head LED Wall Light	4,550/-
58162 Alpha 12W, LED Wall washer	4,850/-
31450 Propulsio Updown Lighter Anthracite	3,750/-
58163 Trigon 9W Triangular, LED Wall Light	4,550/-
31436 Andromeda Step Grey 30K	3,350/-
31435 Andromeda 5W LED Surface Mount Step Light	2,650/-
30974 Step Light LED 2W	1,000/-
34151 2W Anthracite LED Step Light	1,100/-
34152 3W Anthracite LED Step Light	1,500/-

Product Descriptions	MRP
31386 12W Garden Spike NW/WW	2,450/-
581938 3W Philips Black Garden Spike WW	1,600 /-
31385 7W Garden Spike NW/WW	1,800 /-
31385 7W Garden Spike RED/GREEN/ BLUE/AMBER	2,000/-
58174 Glide Wall Lantern Black E27	5,100/-
58175 Glide Post Black E27	5,100/-
58176 Glide Pedestal Black E27	7,600/-
58168 Yolo Wall Lantern LED Black 1x9W	5,400/-
58169 Yolo Pedestal LED Black 1x9W	8,150/-
58166 YOB Wall Lantern Black 5W	5,400/-
58167 YOB Pedestal LED Black 1x5W	8,150/-
58172 Blade Wall Lantern LED Black 1x9W	5,400/-
58173 Blade Pedestal LED Black 1x9W	8,150/-
58170 Pylon Wall Lantern LED Black 1x9W	5,400/-
58171 Pylon Pedestal LED Black 1x9W	8,150/-
IP67 LED Inground Light 3W	2,230/-
IP67 LED Inground Light 5W	3,280/-
IP65 LED Inground Light 10W	4,370/-
IP65 LED Surface Light 12W	2,620/-

