

# PHILIPS

The time is now –  
make the big switch  
with Philips LED!



Are you ready  
for the upcoming  
fluorescent ban?

Reduce energy and maintenance costs with enhanced lighting results and longer lifetime.

## Five-colour Shatterproof T8 LED Tube



50,000 hr  
Lifetime

CRI  
80

Up to  
122  
lm/W



- Available in 5ft, 4ft and 2ft
- Five-colour temperatures in one tube: 2700K/3000K/4000K/5000K/6500K
- Shatterproof design for food industry compliance

## CorePro T8 LED Tubes New Generation

50,000 hr  
Lifetime

CRI  
80

100  
lm/W



- Available in 5ft, 4ft and 2ft
- Glass housing offering a large 240° beam angle for various applications

## T5 LED Tubes

60,000 hr  
Lifetime


CRI  
80

Up to  
138  
lm/W



- Available in 5ft, 4ft and 2ft
- Retrofit solution with long lifetime of 60,000 hrs
- Mains installation only

a lighting brand by @signify



50,000 hr  
Lifetime

CRI  
80

Up to  
122  
lm/W

| Signify product code (12NC) | Signify short code | Description                           | Consumption (W) | Brightness (lm) | Lifetime (hrs) | Colour Temperature (K)       | Base Cap | Lamp Width (mm) | Lamp Length (mm) | Lamp Shape | Dimmable |
|-----------------------------|--------------------|---------------------------------------|-----------------|-----------------|----------------|------------------------------|----------|-----------------|------------------|------------|----------|
| 929004265719                | LEDT85CCT5FT       | CorePro LEDtube 1500mm 24W 5CCT T8 AU | 24              | 2400-2640       | 50,000         | 2700K-3000K-4000K-5000K-6500 | G13      | 28              | 1500             | T8         | No       |
| 929004265619                | LEDT85CCT4FT       | CorePro LEDtube 1200mm 18W 5CCT T8 AU | 18              | 1800-1980       | 50,000         | 2700-3000-4000-5000-6500     | G13      | 28              | 1200             | T8         | No       |
| 929004265519                | LEDT85CCT2FT       | CorePro LEDtube 600mm 9W 5CCT T8 AU   | 9               | 900-1100        | 50,000         | 2700-3000-4000-5000-6500     | G13      | 28              | 600              | T8         | No       |



50,000 hr  
Lifetime

CRI  
80

100  
lm/W

| Signify product code (12NC) | Signify short code | Description                                | Consumption (W) | Brightness (lm) | Lifetime (hrs) | Colour Temperature (K) | Base Cap | Lamp Width (mm) | Lamp Length (mm) | Lamp Shape | Dimmable |
|-----------------------------|--------------------|--------------------------------------------|-----------------|-----------------|----------------|------------------------|----------|-----------------|------------------|------------|----------|
| 929003547420                | TLED1500840G4      | CorePro LEDtube 1500mm 21.4W 840 T8 AU 1CT | 21.4            | 2200            | 50,000         | 4000                   | G13      | 28              | 1500             | T8         | No       |
| 929003547520                | TLED1500865G4      | CorePro LEDtube 1500mm 21.4W 865 T8 AU 1CT | 21.4            | 2200            | 50,000         | 6500                   | G13      | 28              | 1500             | T8         | No       |
| 929003519720                | TLED1200840G4      | CorePro LEDtube 1200mm 17W 840 T8 AU 1CT   | 17              | 1800            | 50,000         | 4000                   | G13      | 28              | 1200             | T8         | No       |
| 929003519820                | TLED1200865G4      | CorePro LEDtube 1200mm 17W 865 T8 AU 1CT   | 17              | 1800            | 50,000         | 6500                   | G13      | 28              | 1200             | T8         | No       |
| 929003547220                | TLED600840G4       | CorePro LEDtube 600mm 8.8W 840 T8 AU 1CT   | 8.8             | 900             | 50,000         | 4000                   | G13      | 28              | 600              | T8         | No       |
| 929003547320                | TLED600865G4       | CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT   | 8.8             | 900             | 50,000         | 6500                   | G13      | 28              | 600              | T8         | No       |



60,000 hr  
Lifetime

CRI  
80

Up to  
138  
lm/W

| Signify product code (12NC) | Signify short code | Description                            | Consumption (W) | Brightness (lm) | Lifetime (hrs) | Colour Temperature (K) | Base Cap | Lamp Width (mm) | Lamp Length (mm) | Lamp Shape | Dimmable |
|-----------------------------|--------------------|----------------------------------------|-----------------|-----------------|----------------|------------------------|----------|-----------------|------------------|------------|----------|
| 929002421319                | TLEDT51500840      | CorePro LEDtube 1500mm HE 22W 840 T5AU | 22              | 3000            | 60,000         | 4000                   | G5       | 19              | 1500             | T5         | No       |
| 929003044519                | TLEDT51200840      | CorePro LEDtube 1200mm HE 18W 840 T5AU | 18              | 2500            | 60,000         | 4000                   | G5       | 19              | 1200             | T5         | No       |
| 929003795519                | TLEDT5600840       | CorePro LEDtube 600mm HE 7.7W 840 T5AU | 7.7             | 1000            | 60,000         | 4000                   | G5       | 19              | 600              | T5         | No       |

a lighting brand by @signify