




PHILIPS

hue personal
wireless
lighting

**Light your home
smarter**

2022



Table of contents

How Philips Hue works	4
Hue Basics	8
Philips Hue White and Color Ambiance	16
Play HDMI Sync Box	20
Play Gradient lightstrip	22
Play Gradient light tube	24
Play bar	26
Fugato	28
Argenta	30
Centura	32
Centris	34
Gradient Signe	36
Sana / Liane	38
Ensis / Flourish	40
Infuse / Surimu	42
Xamento	44
Lightstrips	46
Moodlighting	48
Hue Iris	50
Outdoor series	
Low Volt accessories	54
Amarant / Calla / Lily / Outdoor Lightstrips	56
Impress	58
Nyro/Resonate/Daylo	60
Econic/Discover/Attract/Appear	62
Philips Hue White Ambiance	64
Filaments	68
Amaze	70
Fair	72
Enrave	74
Cher / Devote	76
Being	78
Still	80
Wellness / Wellner	82
Pillar	84
Runner	86
Buckram	88
Aurelle	90
Milliskin	92
Devere / Struana	94
Adore	96
Philips Hue White	100
Filaments	104
Outdoor series	
Welcome / Fuzo	106
Lucca/Tuar/Turaco	108
Smart accessories	110
Product codes list	112

How Philips Hue works

The possibilities of Philips Hue smart lighting are endless, but the setup — whether with Bluetooth or the Bridge — is simple. Find out how Philips Hue works and how to get started with smart light.



The easy start to smart light

A Bluetooth-controlled system can control lights within Bluetooth range. Set the mood of a single room with any Philips Hue Bluetooth-compatible bulb and the Hue Bluetooth app, which controls up to 10 lights.



Unlock the full experience

Adding a Philips Hue Bridge activates the built-in Zigbee network — a more advanced way to control your lights — and unlocks the full suite of smart lighting features: add up to 50 bulbs, set routines, and more.

Which option is best for you?

	10		50
	Room	Location	House
		Max number of lamps	
		Installation free dimming	
		Pre-defined scenes	
		Create personal scenes	
		Create your ambiance with warm to cool daylight	
		WORKS WITH alexa	
		WORKS WITH Hey Google	
		WORKS WITH Apple HomeKit	
		Set timers and schedules	
		Smart control, home and away	
		Wake up and go to sleep naturally	
		Sync with entertainment	
Philips Hue with Bluetooth	✓ ✓ ✓ ✓ ✓ ✓ ✓ ✗ ✗ ✗ ✗ ✗	Philips Hue with Bridge	✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓

All Philips Hue with Bluetooth products also work with Philips Hue Bridge

Philips Hue with Bluetooth



Easy start to smart light


Add up to 10 Hue smart lights to your room and control them all with the Philips Hue app while within ca 10 meters of the lights.




Create the right atmosphere in one room



Set the right light for every moment



Control up to 10 lights



Control with your voice

Philips Hue Bridge



Unlock the full power of smart lighting


Add a Philips Hue Bridge to your Hue smart lighting system to expand your range of control. It is the heart of your system, managing all your smart LED lights and storing your customised settings – and giving you full control over your smart lights via the Hue app.




Control lights in your entire home and outdoor space



Set up smart accessories




Create smart light routines



Sync light with films, music and games



Automated lights make it look like you're at home




Lights turn on automatically as you arrive

Philips Hue Basics

Setup of the system

Hue brings smart lighting to everyday homes, allowing anyone to create special moments and automate with light. Start with Philips Hue your way: Bluetooth or Bridge. And no worries: even if you start with a Bluetooth-controlled system, you can always add a Bridge.



Voice control:

Amazon Alexa
Google Assistant

Smart Home Partners:

Voice (Google, Siri, Alexa)
Apple HomeKit
Bosch
Innogy
Telekom
Razer
Vodafone V-Home (SmartThings)
...

Philips Hue

smart in so many ways

Smart Philips Hue LED bulbs and luminaires

The smart and energy-efficient LED lights bring Philips Hue to life. They deliver bright and beautiful light for your daily activities, special moments, and immersive experiences. They're practical too. They dim. They flash. They pulse. They do pretty much anything you want. And they're available in different shapes, sizes and models to suit your home.



Smart wireless hub: The Bridge

The bridge is the heart of your Philips Hue system that wirelessly connects your smart device to your Philips Hue lights. You can add up to 50 Philips Hue lights and 12 accessories to one bridge. Linked to your router, it also connects your system to the wider world via the Internet for out-of-home control and other smart features. The Philips Hue bridge is included in all Philips Hue Starter Kits, or you can buy it separately and simply build your own Philips Hue system.




Smart Controls

You can control your Philips Hue system from any device, wherever you are. For the easiest way to set brightness, create timers, change colors (and so much more), choose the Philips Hue app. For even easier control use Hue dimmer switch or Hue tap. Set your favourite scenes and routines and have them always at hand. Battery powered Hue motion sensor will control your lights automatically, set the way you need them and whenever you need them. You don't even have to be at home to control your lights – great for peace of mind.



Smart wireless lighting system

Philips Hue with Bridge is based on ZigBee, a low-power, safe, and reliable technology to control your lights. New features and improvements are continuously added to the system to make it even more useful. Software and firmware updates can be done wirelessly and directly to your lights. The Philips Hue system can be easily integrated with other ZigBee-based systems for additional home automation.



Light up your gaming!

Create immersive experiences by syncing your Philips Hue lights with your entertainment content.

Watch, listen or play in new and exciting ways as your favorite video, audio and gaming effects fill the room. Simply link your Philips Hue smart lighting system to movies, music or games and transform your room into an entertainment arena.



Get in the game with smart lights

Experience a new dimension of spatial immersion by bringing in-game environments and effects to the entire room.



See how music comes to life

Sync your Philips Hue lights with the beat of any song whether you want to sit back and relax or get the party started.

Set up your Hue entertainment and get started

Step 1
Make sure your Philips Hue lights are powered on and connected to the Bridge 2.0.

Step 2
Set up a new entertainment area in the Philips Hue App.

Step 3
Use the Philips Hue Sync App on your PC/Mac or connect with a supporting smart device to start your experience.

Unlock entertainment with Philips Hue Sync

Philips Hue Sync is a free PC/Mac application for unlocking immersive entertainment with your Hue lights. It creates light scripts on the fly for any content you play on your laptop or desktop, from movies and TV series to music and games.

Sync your Philips Hue lights to your TV screen

Create an immersive media experience via the Philips Hue Play HDMI Sync Box, making your lights dance, flash, dim, and brighten in sync with the on-screen content.



Fast and seamless light experience

Experience no delay as your lights sync to your on-screen content — whether you're watching movies, gaming, or playing music — creating an immersive full-room experience. Watch your favorite content like never before with the sync box.



Works with any Philips Hue color-capable lights

The sync box works with all Philips Hue White and color ambiance bulbs or fixtures. Bring your media to life by adding up to 10 Philips Hue color-capable lights to your setup and enjoy surround lighting effects.



Easy to install, set up, and use

A simple setup allows you to easily connect to your Philips Hue Bridge and use your sync box with any TV and HDMI device. Control your entertainment experience and sync box any way you want: with the app, on-product control button, any infrared TV remote, or your voice via Amazon Alexa, Google Assistant and Siri.



Supports high-quality video formats

The Philips Hue Play HDMI Sync Box supports 120Hz with an image resolution of 1080p and 1440p and is compatible with 4K, Dolby Vision, and HDR10+, letting you enjoy the highest quality picture you can get at home — all while your Philips Hue smart lights sync to give you surround lighting.

Unleash your inner rockstar

Turn your bedroom into a concert hall. Crowd surf in your living room. By syncing your smart lights, you can watch your music spill over from your speakers into the room around you in colorful, dynamic light.



Philips Hue + Spotify

Enhance the music experience by using integration between Philips Hue + Spotify. The first of its kind, this deep integration features more precise light scripts — and an even easier way to link your accounts directly in the Philips Hue app.



Hear, see, and feel the music

Music is an emotional experience. Whatever you listen to, you feel. By syncing your lights to a song, you can create your own personal mood music — no matter the genre.



Match light to the beat

We use specially created algorithms to ensure that each light script, which tells your lights how to react to the music, is perfectly tuned to each song — not just the beat but the overall feeling of the music.



Color lights and Hue Bridge required

To see your lights react to music, you need color-capable Philips Hue smart lights and a Hue Bridge.

Philips Hue White and Color Ambiance

Set up your lights to work with your lifestyle

Take color light to new heights

Set the light in your living space to your favorite color and truly create your own atmosphere. Add just a hint of color as an accent light or set your whole home to vivid jewel tones — all with the touch of a button

Set the mood of the room

Instantly change the ambiance by adjusting the brightness, color, and temperature of your lights.

Get light for everyday moments

Use the best light for reading, relaxing, concentrating and energizing.

Control lights with your voice

Use your voice assistant to turn your lights on and off, dim them, and more.

Be creative with million colors

Play with light and choose from 16 million colors to instantly change the look and atmosphere of your room. Set the scene effortlessly with one touch of a button. Use a favourite photo and relive that special moment with splashes of light. Save your favourite light settings and recall them whenever you want with the tap of a finger. Create an atmosphere unlike any other with dynamic scenes that allow the lights in the room or zone to slowly transition through the different colors of your favorite scene.

Sync lights with music and movies

Extend your TV viewing experience to the whole room or sync light to your favorite music and see how light reacts to the rhythm. Download the third party apps and discover the amazing things you can do with Philips Hue.

Light up your gaming

Lift your gaming experience to the next level. Download the third party apps and discover the amazing things you can do with Philips Hue.

800 lm



F

8719514328402
Philips Hue White and
Color Ambiance 6.5 W E27
A60 4-pack



F

8719514328389
Philips Hue White and
Color Ambiance 6.5 W E27
A60 3-pack



F

8719514328365
Philips Hue White and
Color Ambiance 6.5 W E27
A60 2-pack



G

8719514340107
Philips Hue White and
Color Ambiance 4.3 W
GU10 3-pack with Bridge
and Dimmer switch



G

8719514342767
Philips Hue White and
Color Ambiance 4.3 W
GU10 3-pack



G

8719514340084
Philips Hue White and
Color Ambiance 4.3 W
GU10 2-pack

1100 lm



F

8719514291355
Philips Hue White and
Color Ambiance 9 W A60
E27 3-pack with Bridge
and Dimmer switch



F

8719514291515
Philips Hue White and
Color Ambiance 9 W A60
E27 3-pack with Bridge



F

8719514291379
Philips Hue White and
Color Ambiance 9 W A60
E27 2-pack with Bridge
and Dimmer switch



G

8719514339880
Philips Hue White and
Color Ambiance 4.3 W
GU10



G

8719514356719
Philips Hue White and
Color Ambiance 4 W E14
B39 2-pack



G

8719514356610
Philips Hue White and
Color Ambiance 4 W E14
B39

1600 lm



F

8719514288157
Philips Hue White and
Color Ambiance 13.5 W
A60 E27



Philips Hue White and Color Ambiance bulbs

1521 lm (E27 13.5W), 1100 lm (E27 9W), 800 lm (E27 6.5W) at 4000K
470 lm (E14), 350 lm (GU10) at 4000 K
RGB 2200–6500 K, 16 million colors
Lifetime 25 000 hours (E14, E27), 15 000 hours (GU10)

220 V–240 V/50–60 Hz

☉ – IP20

↑ 117 ↔ 39 mm (E14), ↑ 71 ↔ 50 mm (GU10)

↑ 110 ↔ 60 mm (E27 6.5W, 9W)

↑ 131 ↔ 67 mm (E27 13.5W)

Synthetic/Glass (E14), Aluminium/Glass (E27), Synthetic (GU10)

Philips Hue

Play HDMI Sync Box

Play HDMI Sync Box

8718699704803

↔ 182 ↗ 99 ↓ 23 mm

Sync your smart lights to your on-screen TV content with the Philips Hue Play HDMI Sync Box. Four HDMI inputs allow you to connect your media devices to your Hue setup, resulting in a fast, seamless display of colorful smart light that responds to and reflects the content you watch or listen to.

- Sync lights with your home theater and TV
- Connect up to 4 HDMI devices
- Personalize your experience using the app
- **Requires Philips Hue Bridge and Hue color-capable lights**



Philips Hue Play Gradient lightstrip

Gradient lightstrip

Take the excitement of surround lighting to the next level with the Philips Hue Play gradient lightstrip. This LED strip flawlessly blends multiple colors of light at the same time, mimicking the content on the entire screen for an immersive, full-room entertainment experience unlike any other.

RGB 2 000–6 500 K, 16 million colors
Lifetime 25 000 hours
Light source included

Hue White and Color Ambiance
20 W, 1 650 lm per strip
Synthetics

Requires Philips Hue Bridge and Philips Hue Play sync box

8718699784751

Philips Hue Play gradient lightstrip 55" EU

↔ 1 400 ↗ 20 ↓ 20

8718699784775

Philips Hue Play gradient lightstrip 65" EU

↔ 1 650 ↗ 20 ↓ 20

8718699784799

Philips Hue Play gradient lightstrip 75" EU

↔ 1 900 ↗ 20 ↓ 20





Philips Hue

Play gradient light tube

Gradient light tube

Made to sit above or below the TV, the Play gradient light tube features a subtle design (and two sizes!) that blends in with its surroundings — until you see its gradient of colorful light.

RGB 2000–6500 K, 16 million colors
Lifetime 25 000 hours
Light source included

Hue White and Color Ambiance
20 W, 1800 lm (LRG)/ 17.4 W, 1540 lm (CMP)
Aluminium

Requires Philips Hue Bridge and Philips Hue Play sync box

8718696176290
Play gradient light tube CMP white
↔ 877 ↗ 31 ↓ 34

8718696176313
Play gradient light tube LRG white
↔ 1377 ↗ 31 ↓ 34



8718696176306
Play gradient light tube CMP black
↔ 877 ↗ 31 ↓ 34

8718696176320
Play gradient light tube LRG black
↔ 1377 ↗ 31 ↓ 34





Philips Hue Play



8718696170731
Hue Play extension pack black

8718696170809
Hue Play extension pack white



8718696170717
Hue Play single pack black

8718696170748
Hue Play single pack white



8718696170724
Hue Play double pack black

8718696170793
Hue Play double pack white



8718696171189
Hue Play extension cable 5 m black



G Play

RGB 2 000–6 500 K, 16 million colors
Lifetime 25 000 hours
Light source included

Hue White and Color Ambiance
6W, 530 lm per light
⊕ – IP20
Synthetics



8718696171493
Fugato single spot white
1 163 ↔ 82 ↗ 82 mm
5,7 W, 350 lm at 4000 K



8718696171509
Fugato single spot black
1 163 ↔ 82 ↗ 82 mm
5,7 W, 350 lm at 4000 K



8718696171516
Fugato double spot white
1 153 ↔ 195 ↗ 80 mm
2×5,7 W, 2×350 lm at 4000 K



8718696171530
Fugato plate white
1 153 ↔ 195 ↗ 195 mm
3×5,7 W, 3×350 lm at 4000 K



8718696171547
Fugato plate black
1 153 ↔ 195 ↗ 195 mm
3×5,7 W, 3×350 lm at 4000 K



8718696171523
Fugato double spot black
1 153 ↔ 195 ↗ 80 mm
2×5,7 W, 2×350 lm at 4000 K



8718696171554
Fugato 4-spot white
1 153 ↔ 425 ↗ 80 mm
4×5,7 W, 4×350 lm at 4000 K



8718696171561
Fugato 4-spot black
1 153 ↔ 425 ↗ 80 mm
4×5,7 W, 4×350 lm at 4000 K



Fugato

RGB 2 200–6 500 K, 16 million colors
Lifetime 25 000 hours
Light source included

Hue White and Color Ambiance
220 V–240 V/50–60 Hz, GU10
⊕ – IP20
Metal



Philips Hue

Fugato



8718696171578
Argenta single spot white
1 127 ↔ 110 ↗ 90 mm
5,7 W, 350 lm at 4000 K



8718696171615
Argenta single spot aluminium
1 127 ↔ 110 ↗ 90 mm
5,7 W, 350 lm at 4000 K



8718696171585
Argenta double spot white
1 127 ↔ 305 ↗ 90 mm
2×5,7 W, 2×350 lm at 4000 K



8718696171608
Argenta plate white
1 127 ↔ 240 ↗ 240 mm
4×5,7 W, 350 lm at 4000 K



8718696171646
Argenta plate black
1 127 ↔ 240 ↗ 240 mm
4×5,7 W, 350 lm at 4000 K




8718696171622
Argenta double spot aluminium
1 127 ↔ 305 ↗ 90 mm
2×5,7 W, 2×350 lm at 4000 K



8718696171592
Argenta triple spot white
1 127 ↔ 480 ↗ 90 mm
3×5,7 W, 3×350 lm at 4000 K



8718696171639
Argenta triple spot aluminium
1 127 ↔ 480 ↗ 90 mm
3×5,7 W, 3×350 lm at 4000 K



Philips Hue Argenta




Argenta

RGB 2 200–6 500 K, 16 million colors
Lifetime 25 000 hours
Light source included

Hue White and Color Ambiance
220 V–240 V/50–60 Hz, GU10
⊕ – IP20
Metal





Philips Hue Centura



8719514338647
**Centura recessed
white round**
5,7 W, 350 lm at 4000 K



8719514338623
**Centura recessed
aluminium round**
5,7 W, 350 lm at 4000 K



8719514342880
**Centura recessed
white round, 3-pack**
5,7 W, 350 lm at 4000 K



8719514342866
**Centura recessed
aluminium round, 3-pack**
5,7 W, 350 lm at 4000 K



8719514342903
**Centura recessed
black round, 3-pack**
5,7 W, 350 lm at 4000 K



8719514338920
**Centura recessed
white square**
5,7 W, 350 lm at 4000 K



8719514338807
**Centura recessed
aluminium square**
5,7 W, 350 lm at 4000 K




Centura

RGB 2200–6500 K, 16 million colors
Lifetime 25 000 hours
Light source included

Hue White and Color Ambiance
220 V–240 V/50–60 Hz, GU10
⊕ – IP20
↔ 90 / 90 mm
cut-out 70 mm, recessed 100 mm
Synthetic





Philips Hue Centris



8718696176009
Centris Hue 2L - Ceiling White
2x5,7W GU10+ 11W integrated; 1600 lm



8718696175989
Centris Hue 2L - Ceiling Black
2x5,7W GU10+ 11W integrated; 1600 lm




8718696176016
Centris Hue 3L - Ceiling White
3x5,7W GU10+34W integrated; 3550 lm



8718696175996
Centris Hue 3L - Ceiling Black
3x5,7W GU10+34W integrated; 3550 lm



8718696176030
Centris Hue 3Lcross - Ceiling White
3x5,7W GU10+25W integrated; 3050 lm



8718696176023
Centris Hue 3Lcross - Ceiling Black
3x5,7W GU10+25W integrated; 3050lm



8718696176054
Centris Hue 4L - Ceiling White
4x5,7W GU10+40W integrated; 4000 lm



8718696176047
Centris Hue 4L - Ceiling Black
4x5,7W GU10+40W integrated; 4000 lm



Centris



RGB 2 000–6 500 K, 16 million colors
Lifetime 25 000 hours
Light source included

Hue White and Color Ambiance
⊕ – IP20
Aluminium






Philips Hue


Gradient Signe




8718696176252
Gradient Signe floor white
↑ 1458 ↔ 111 ↗ 111 mm
29 W, 2550 lm at 4000 K



8718696176269
Gradient Signe floor black
↑ 1458 ↔ 111 ↗ 111 mm
29 W, 2550 lm at 4000 K



8718696176238
Gradient Signe table white
↑ 553 ↔ 111 ↗ 111 mm
11.8 W, 1040 lm at 4000 K



8718696176245
Gradient Signe table black
↑ 553 ↔ 111 ↗ 111 mm
11.8 W, 1040 lm at 4000 K




Gradient Signe

RGB 2 000–6 500 K, 16 million colors
Lifetime 25 000 hours
Light source included

Hue White and Color Ambiance

⊕ – IP20
Aluminium





8719514343382
Sana Hue wall lamp black
 1 255 → 255 ↗ 52 mm
 20 W, 1500 lm at 4000 K



8719514343405
Sana Hue wall lamp white
 1 255 → 255 ↗ 52 mm
 20 W, 1500 lm at 4000 K



8719514343429
Liane Hue wall lamp black
 1 558 → 31 ↗ 107 mm
 20 W, 900 lm at 4000 K



8719514343443
Liane Hue wall lamp white
 1 558 → 31 ↗ 107 mm
 20 W, 900 lm at 4000 K



Sana / Liane



RGB 2000–6500 K, 16 million colors
 Lifetime 25 000 hours
 Light source included

Hue White and Color Ambiance

⊕ – IP20

Aluminium

Philips Hue

Sana / Liane



Philips Hue

Ensis / Flourish



8719514343368
Ensis Hue pendant black
 1 164–1664 ↔ 1298 ↗ 70 mm
 2 × 39 W, 6000 lm max.



8719514343467
Ensis Hue pendant white
 1 164–1664 ↔ 1298 ↗ 70 mm
 2 × 39 W, 6000 lm max.



F 8719514343481
Flourish Hue table lamp white
 1 175 ↔ 261 ↗ 261 mm
 E27, 9.5 W, 806 lm max.



8719514343504
Flourish Hue ceiling lamp white
 1 141 ↔ 359 ↗ 359 mm
 32 W, 2400 lm max.

Ensis / Flourish
 RGB 2 000–6 500 K, 16 million colors
 Lifetime 25 000 hours
 Light source included
 Hue White and Color Ambiance
 Ⓢ – IP20
 Aluminium (Ensis), Glass (Flourish)



8719514343528
Flourish Hue pendant lamp white
 1 300–1800 ↔ 401 ↗ 401 mm
 31 W, 3000 lm max.



Philips Hue Infuse / Surimu



8718696176498
Hue Infuse M ceiling lamp white
184 ↔ 381 mm
33.5 W, 2350 lm at 4000K



8718696176504
Hue Infuse M ceiling lamp black
184 ↔ 381 mm
33.5 W, 2350 lm at 4000K



8718696176511
Hue Infuse L ceiling lamp white
184 ↔ 425 mm
52.5 W, 3700 lm at 4000K



8718696176528
Hue Infuse L ceiling lamp black
184 ↔ 425 mm
52.5 W, 3700 lm at 4000K



8719514355057
Hue Surimu Rectangle Panel
148 ↔ 1200 ↗ 300 mm
60 W, 4200 lm at 4000K



8719514355071
Hue Surimu Square Panel
148 ↔ 600 ↗ 600 mm
60 W, 4200 lm at 4000K

 **Infuse / Surimu**
 RGB 2000–6500 K, 16 million colors
Lifetime 25000 hours
Light source included
Hue White and Color Ambiance
⊕ – IP20
Metal, synthetics





8718696176559
Hue Xamento M ceiling lamp white
 1 84 ↔ 381 mm
 33.5 W, 2350 lm at 4000K



8718696176566
Hue Xamento L ceiling lamp white
 1 84 ↔ 425 mm
 52.5 W, 3700 lm at 4000K



8719514355392
Hue Xamento recessed chrome 3-pack
 1 90 ↔ 94 mm
 3x5.7 W, 1050 lm at 4000K



8719514355347
Hue Xamento recessed chrome
 1 90 ↔ 94 mm
 5.7 W, 350 lm at 4000K

Philips Hue Xamento



Xamento

RGB 2 000–6 500 K, 16 million colors
 Lifetime 25 000 hours
 Light source included

Hue White and Color Ambiance

⊕ – IP44

Metal, synthetics





8719514339965
Hue gradient lightstrip 2m base kit



8719514339989
Hue gradient lightstrip 1m extension



8718699703424
Hue Lightstrip Plus V4 EMEA 2m base kit



8718699703448
Hue Lightstrip Plus V4 EMEA 1m extension

Lightstrips

-  **Hue gradient lightstrip 2m base kit** ↔ 2000 ↗ 14.5 ↓ 5, 11 W, 1260 lm at 4000 K
-  **Hue gradient lightstrip 1m extension** ↔ 1000 ↗ 14.5 ↓ 5, 11 W, 700 lm at 4000 K
-  **Hue Lightstrip Plus V4 EMEA 2m base kit** ↔ 2000 ↗ 15 ↓ 5, 25 W, 1700 lm at 4000 K
-  **Hue Lightstrip Plus V4 EMEA 1m extension** ↔ 1000 ↗ 15 ↓ 5, 11 W, 1030 lm at 4000 K

RGB 2000–6500 K, 16 million colors
Lifetime 25 000 hours, Ⓢ – IP20, Synthetic

Philips Hue Lightstrips



8718699770983
Hue Bloom white



8718699771126
Hue Bloom black



8718696173992
Hue GO

Philips Hue Moodlighting



Moodlighting



Hue GO ↔ 120 ↗ 120 ↓ 70, 6 W, 530 lm at 4000 K

Hue Bloom ↔ 130 ↗ 126 ↓ 101, 7.1 W, 500 lm at 4000 K

RGB 2000–6500 K, 16 million colors

Lifetime 25 000 hours, ☼ – IP20, Synthetic



Philips Hue Iris

The exclusive, extraordinary, and surprisingly smart lamp.

The Iris smart lamp has an increased lumen output compared to the previous Iris model, making its light brighter than ever. The lamp also offers richer colour options and high-quality design details, such as a textile cord and exclusive metallic colours.



8719514264465
Hue Iris white



8719514264489
Hue Iris black



8719514410732
Hue Iris gold



8719514411524
Hue Iris silver



8719514411586
Hue Iris copper



Iris



Hue Iris ↔ 222 ↗ 165 ↓ 150, 8.1 W, 570 lm at 4000 K

RGB 2000–6500 K, 16 million colors

Lifetime 25 000 hours, Ⓢ – IP20,

Synthetics, metal



Transform your outdoor space with light

Philips Hue smart lighting is for your entire home — inside and out. We have two types of outdoor lights: standard line-voltage (wired into your home's electricity) and low-voltage, which simply plug into any outdoor outlet. Called LowVolt, this collection of lights allows more flexibility in designing your outdoor lighting. Whatever you choose, Philips Hue lets you transform your outdoors with smart light.

Which option is best for you?

Low Volt

Line voltage

24 V

Voltage

220 V



Safe extra low voltage (SELV)



Bridge required



Can be placed anywhere



Direct line-voltage connection



Separate power supply unit required



Low
volt

Easy to install and extend

The products are based on low voltage, safe to use and easy to install. No more complexity to get lighting outdoors: go create and extend as you like. Look for Low Volt icon next to products.

Philips Hue Low Volt accesories




8718696175941
Power Supply 24 V, 100 W, EU
1 40 → 70 ↗ 2200 mm, IP67




8718696176108
Power Supply 24 V, 40 W, EU
1 40 → 70 ↗ 2200 mm, IP67

Examples of possible Low Volt setups

40 W



100 W




8718696168721
Cable extension 5 m
1 7.3 → 7.3 ↗ 5000 mm, IP67



8718696176641
Cable extension 2.5 m
1 7.3 → 7.3 ↗ 2500 mm, IP67



8718696176658
Low Volt T-part
1 80 → 48 ↗ 20 mm



8718696174425
Hue Amarant black
1 795 → 50 ↗ 68 mm
20.5 W, 1420 lm at 4 000 K,
2 000–6 500 K
PSU needed (p. 54)



8718699709839
Hue Outdoor Strip (2m)
1 20 → 2000 ↗ 11 mm
19.5 W, 765 lm at 4 000 K



8718699709853
Hue Outdoor Strip (5m)
20 → 4908 ↗ 11 mm
37.5 W, 1490 lm at 4 000 K

**Outdoor strips are not
extendable, nor cuttable!**



8718696174364
Lily XL spike black
1 190 → 130 ↗ 120 mm
15 W, 1200 lm at 4 000 K,
2 000–6 500 K
PSU needed (p. 54)



8718696170557
**Calla Large extension
pedestal black**
1 400 → 104 ↗ 104 mm
8 W, 590 lm at 4 000 K,
2 000–6 500 K
PSU needed (p. 54)



8718696167991
**Calla extension
pedestal black**
1 255 → 104 ↗ 104 mm
8 W, 590 lm at 4 000 K,
2 000–6 500 K
PSU needed (p. 54)



8718696167960
Lily spike anthracite 3×8 W
1 192 → 84 ↗ 70 mm
8 W, 3×640 lm at 4 000 K,
2 000–6 500 K



8718696169087
Lily spike anthracite 1×8 W
1 192 → 84 ↗ 70 mm
8 W, 640 lm at 4 000 K,
2 000–6 500 K



8718696167977
**Lily spike anthracite
extension**
1 192 → 84 ↗ 70 mm
8 W, 640 lm at 4 000 K,
2 000–6 500 K
PSU needed (p. 54)

G Amarant / Calla / Lily / Outdoor Lightstrip



2 000–6 500 K
Lifetime 25 000 hours
Light source included

Hue White
220 V–240 V/50–60 Hz
⊕ – IP44 (Calla), IP65 (Lily, Lightstrip)
Aluminium (Calla, Lily), synthetics/silicone (Lightstrip)





Philips Hue Impress



8718696170489
**Impress Hue
wall lantern black 2**
↑ 240 → 120 ↗ 141 mm



Low
voltage 8718696170526
**Impress Hue
wall lantern black**
↑ 240 → 120 ↗ 140 mm
PSU needed (p. 54)



8718696170496
**Impress Hue
large wall lantern black**
↑ 240 → 190 ↗ 117 mm



8718696170502
**Impress Hue
pedestal black**
↑ 400 → 100 ↗ 100 mm



Low
voltage 8718696170526
**Impress Hue pedestal
black**
↑ 400 → 100 ↗ 100 mm
PSU needed (p. 54)



8718696170519
Impress Hue post black
↑ 770 → 100 ↗ 100 mm,
24 V

G Impress

2 000–6 500 K
Lifetime 25 000 hours, Light source included,
8 W or 2×8 W, 1180 lm at 4000 K

Hue White and Color Ambiance
220 V–240 V/50–60 Hz, ⚡ – IP44
Aluminium die-cast



8718696174296
Nyro Hue pedestal black
1 400 ↔ 250 ↗ 100 mm



8718696174302
Nyro Hue wall lantern black
1 100 ↔ 250 ↗ 85 mm, 1000 lm



8718696174388
Resonate wall lantern black
1 180 ↔ 120 ↗ 100 mm



8718696174395
Resonate wall lantern inox
1 180 ↔ 120 ↗ 100 mm



8718696174401
Daylo wall lantern black
1 220 ↔ 220 ↗ 75 mm



8718696174418
Daylo wall lantern inox
1 220 ↔ 220 ↗ 75 mm

G Nyro / Resonate / Daylo

2 000–6 500 K
Lifetime 25 000 hours, Light source included,
1×13,5 W (Nyro), 2×8 W (Resonate), 1×15 W (Daylo)
Hue White and Color Ambiance
220 V–240 V/50–60 Hz, Ⓢ – IP44
Aluminium die-cast

Philips Hue

Nyro/Resonate/Daylo



8718696174357
Attract Hue wall lantern black
1 190 → 230 ↗ 250 mm



8718696174371
Appear Hue wall lantern black
1 85 → 120 ↗ 240 mm



8718696176207
Appear Hue wall lantern inox
1 85 → 120 ↗ 240 mm



8718696170571
Econic up wall lantern black
1 244 → 194 ↗ 301 mm



8718696170588
Econic Hue down wall lantern
1 244 → 194 ↗ 312 mm



8718696170595
Econic pedestal black 1x15W
1 163 → 163 ↗ 322 mm



8718696170564
Econic square wall lantern
1 260 → 260 ↗ 115 mm



8718696170601
Econic Hue post black
1 163 → 163 ↗ 1000 mm



8718696170533
Discover Hue wall lantern
1 160 → 220 ↗ 153 mm

G Appear / Attract / Discover / Econic

2 000–6 500 K
Lifetime 25 000 hours
Light source included
79 W, 2300 lm (Discover), 15 W, 1150 lm (Econic),
8 W, 600 lm (Attract), 2 × 8 W, 1200 lm (Appear)

Hue White and Color Ambiance
220 V–240 V/50–60 Hz
⊕ – IP44
Aluminium die-cast

Philips Hue
Appear / Attract / Discover / Econic

Philips Hue White Ambiance

Set up your lights to work with your lifestyle

Wake up and go to sleep naturally

Philips Hue will help get you out of bed the way you like it, helping you start your day feeling refreshed. The light brightness increases gradually mimicking the effect of sunrise and helps you wake up naturally, instead of being woken up by the loud sound of an alarm clock. Start your day, the right way. In the evening, the relaxing warm white light helps you to unwind, relax and prepare your body for a good night's sleep.

Relax, read, concentrate and energize with light recipes

Light influences our mood and behavior. Philips Hue can help you to customize your daily routines into moments you can enjoy. Skip your morning coffee and get ready for the day with cool, bright white daylight that helps to energize your body and mind. Stay focussed with finely tuned bright white light. Or put your feet up and relax with a soft glow of white light for the perfect end of the day.

Improve the functionality by adding a Hue Bridge

Expand your range of control. Add more lights to even the furthest corners of your home.



Boost your energy

Use light to amp up the energy in your home. With its cool white light, the Energize light scene helps you add a little pep to your morning or an extra punch to your workout.



Sharpen your focus

When you need to get things done, Philips Hue can help you direct your full attention to the task at hand. Set the Concentrate light scene to stay focused and keep your head in the game.




Read with ease

Curl up with a good book under the right light. With the Read light scene, Philips Hue adjusts the light from cool to warm for the perfect shade of white, allowing you to comfortably flip through the pages.



Relax your mind

Finding the time to unwind can prove difficult. When you finally do get a moment to yourself, set Philips Hue to the subtle, soft light of the Relax scene and take your tranquility to the next level.



800 lm



F

8719514328280
Philips Hue White Ambiance
6 W E27 A60 4-pack



F

8719514328266
Philips Hue White Ambiance
6 W E27 A60 3-pack



F

8719514328242
Philips Hue White Ambiance
6 W E27 A60 2-pack



G

8719514342804
Philips Hue White Ambiance
4.3 W GU10 3-pack



G

8719514340121
Philips Hue White Ambiance
4.3 W GU10 2-pack



G

8719514339903
Philips Hue White Ambiance
4.3 W GU10

1100 lm



F

8719514291232
Philips Hue White Ambiance
8 W A60 E27 3-pack with
Bridge and Dimmer switch



F

8719514291812
Philips Hue White Ambiance
8 W A60 E27 2-pack with
Bridge and Dimmer switch



F

8719514291256
Philips Hue White Ambiance
8 W A60 E27 2-pack



G

8719514356733
Philips Hue White Ambiance
4 W E14 B39 2-pack



G

8719514356658
Philips Hue White Ambiance
4 W E14 B39



F

8719514291119
Philips Hue White Ambiance
8 W A60 E27

1600 lm



F

8719514288195
Philips Hue White Ambiance
13 W A60 E27



Philips Hue White Ambiance bulbs

1521 lm (E27 13 W), 1100 lm (E27 8 W), 800 lm (E27 6 W) at 4000K
470 lm (E14), 350 lm (GU10) at 4000 K
White Ambiance 2200–6500 K
Lifetime 25 000 hours (E14, E27), 15 000 hours (GU10)

220 V–240 V/50–60 Hz

☉ – IP20

↑ 117 ↔ 39 mm (E14), ↑ 71 ↔ 50 mm (GU10)

↑ 110 ↔ 60 mm (E27 6 W, 8 W)

↑ 131 ↔ 67 mm (E27 13 W)

Synthetic/Glass (E14), Aluminium/Glass (E27), Synthetic (GU10)



8719514301429
**Philips Hue White Ambiance
Filament 7W A60 EUR E27**



8719514301467
**Philips Hue White Ambiance
Filament 7W ST64 EUR E27**



8719514301481
**Philips Hue White Ambiance
Filament 7W G93 EUR E27**



8719514301504
**Philips Hue White Ambiance
Filament 7W ST72 EUR E27**



8719514301542
**Philips Hue White Ambiance
Filament 7W G125 EUR E27**

Philips Hue White Ambiance Filaments



Philips Hue White Ambiance Filaments

550 lm at 2 700 K
7 W, White Ambiance 2200 – 6500 K
Lifetime 15 000 hours
220 V – 240 V/50 – 60 Hz
⊕ – IP20
↑ 115 ↔ 60 mm (A60), ↑ 133 ↔ 60 mm (ST64), ↑ 150 ↔ 95 mm (G93), ↑ 164 ↔ 72 mm (ST72)
↑ 192 ↔ 125 mm (G125)
Glass


All Philips Hue White Ambiance filament bulbs are featuring Bluetooth® and Zigbee technology



Philips Hue Amaze



8719514341098
Amaze Hue pendant white



8719514341074
Amaze Hue pendant black



Amaze

3 000 lm at 4 000 K
2 200 – 6 500 K
Lifetime 25 000 hours
Light source included
220 V – 240 V/50 – 60 Hz
⊕ – IP20
↑ 1 500 ↔ 434 ↗ 434 mm
Aluminium/Synthetic



Dimmer switch remote control included





8719514341319
Fair Hue pendant white



8719514341258
Fair Hue ceiling lamp black



8719514341272
Fair Hue ceiling lamp white



8719514341296
Fair Hue pendant black



3 000 lm at 4 000 K
2 200 – 6 500 K
Lifetime 25 000 hours
Light source included
220 V – 240 V/50 – 60 Hz
⊕ – IP20
↑ 1600 ↔ 444 ↗ 444 mm (pendant)
↑ 99 ↔ 444 ↗ 444 mm (ceiling lamp)
Metal/Glass



Dimmer switch remote control included



Philips Hue
Fair



Philips Hue

Enrave



8718696176412
Hue Enrave S white (Ø 261 mm)

8718696176436
Hue Enrave M white (Ø 381 mm)

8718696176450
Hue Enrave L white (Ø 425 mm)

8718696176474
Hue Enrave XL white (Ø 551 mm)



8718696176429
Hue Enrave S black (Ø 261 mm)

8718696176443
Hue Enrave M black (Ø 381 mm)

8718696176467
Hue Enrave L black (Ø 425 mm)

8718696176481
Hue Enrave XL black (Ø 551 mm)



8718696176573
Hue Enrave pendant white (Ø 425 mm)



8718696176580
Hue Enrave pendant black (Ø 425 mm)



Enrave

1 220 lm (S), 2 450 lm (M), 4 300 lm (L, pendant),
6 100 lm (XL) at 4000 K
2200 – 6500 K
Lifetime 25 000 hours
Light source included
220 V – 240 V/50 – 60 Hz
⊕ – IP20
Metal/Synthetic



Dimmer switch remote
control included





Philips Hue

Cher / Devote



8719514341210
Cher Hue pendant white

8719514341197
Cher Hue pendant black



8718696176573
Cher Hue ceiling lamp black



8718696176573
Devote Hue pendant white
(dimmer switch not included)



Cher

3 000 lm at 4 000 K



2 200–6 500 K

Lifetime 25 000 hours

Light source included

220 V–240 V/50–60 Hz

⊕ – IP20

↑ 1750 ↔ 475 ↗ 475 mm

↑ 95 ↔ 475 ↗ 475 mm (ceiling)

↑ 227 ↔ 475 ↗ 475 mm (ceiling pendant)

Synthetic



Devote

806 lm at 4 000 K (2 200–6 500 K)



Light source included (9.5 W E27 Hue White Ambiance bulb)

⊕ – IP20 / ↑ 2610 ↔ 110 ↗ 110 mm

Synthetic

Dimmer switch remote
control included





Philips Hue Being



8719514341111
Being Hue aluminium




8719514341159
Being Hue white



8719514341135
Being Hue black



8718696175279
Being Hue aluminium



8718696175293
Being Hue white

8718696175286
Being Hue black

Dimmer switch remote
control included



Being



2 400 lm at 4 000 K
2 200 – 6 500 K
Lifetime 25 000 hours
Light source included

220 V – 240 V/50 – 60 Hz
⊕ – IP20
171 ↔ 391 ↗ 391 mm
Metal/Synthetic



8719514341333
Still Hue ceiling lamp
aluminium



8719514341371
Still Hue ceiling lamp
white



8719514341357
Still Hue ceiling lamp
black



Still



2 400 lm at 4 000 K
2 200 – 6 500 K
Lifetime 25 000 hours
Light source included
220 V – 240 V/50 – 60 Hz
⊕ – IP20
↑ 71 → 391 ↗ 391 mm
Metal/Synthetic



Dimmer switch remote
control included



Philips Hue
Still



8719514341395
Wellner Hue table lamp white



8719514341418
Wellness Hue table lamp black

Dimmer switch remote
control included



Wellner / Wellness

 806 lm at 4 000 K
2 200 – 6 500 K
Lifetime 15 000 hours
Light source included

9.5 W E27 Hue White Ambiance
220 V – 240 V/50 – 60 Hz
⊕ – IP20

↑ 192 ↔ 268 ↗ 268 mm (Wellner)
↑ 193 ↔ 186 ↗ 186 mm (Wellness)

Glass (Wellner)

Wood/Glass (Wellness)



Philips Hue

Wellness / Wellner



8719514338449
Pillar Hue black 1L



8719514338524
Pillar Hue black 1L extension
Dimmer switch not included



8719514338425
Pillar Hue black 2L



8719514338487
Pillar Hue white 1L



8719514338500
Pillar Hue white 1L extension
Dimmer switch not included



8719514338463
Pillar Hue white 2L



Pillar



1×350 lm at 4 000 K (1L)
2×350 lm at 4 000 K (2L)
2 200–6 500 K
Lifetime 15 000 hours
Light source included

5.5 W GU10 Hue White Ambiance
220 V–240 V/50–60 Hz
⊕ – IP20
↑ 120 ↔ 103 ↗ 103 mm (1L)
↑ 120 ↔ 193 ↗ 103 mm (2L)
Aluminium



Dimmer switch remote control included



Philips Hue

Pillar



Philips Hue Runner



8719514338203
Runner Hue white 1L



8719514338326
Runner Hue black 1L



8719514338340
Runner Hue white 1L extension
Dimmer switch
not included



8719514338364
Runner Hue black 1L extension
Dimmer switch
not included



8719514338166
Runner Hue black 2L



8719514338401
Runner Hue black 3L



8719514338142
Runner Hue white 2L



8719514338388
Runner Hue white 3L



Runner

1×350 lm at 4000 K
2×350 lm at 4000 K
3×350 lm at 4000 K
2200–6500 K
Lifetime 15 000 hours
Light source included

5.5 W GU10 Hue White Ambiance
220 V–240 V/50–60 Hz
⊕ – IP20
↑ 90 ↔ 110 ↗ 107 mm (1L)
↑ 89 ↔ 305 ↗ 109 mm (2L)
↑ 89 ↔ 480 ↗ 109 mm (3L)
Aluminium



Dimmer switch remote
control included





Philips Hue Buckram



8719514339224
Buckram Hue white 1L



8719514339187
Buckram Hue white 1L extension
Dimmer switch not included



8719514339064
Buckram Hue white 2L



8719514339101
Buckram Hue white 3L



8719514339149
Buckram Hue white 4L



8719514339248
Buckram Hue black 1L



8719514339200
Buckram Hue black 1L extension
Dimmer switch not included



8719514339088
Buckram Hue black 2L



8719514339125
Buckram Hue black 3L



8719514339163
Buckram Hue black 4L



Buckram



1 × 350, 2 × 350, 3 × 350, 4 × 350 lm at 4 000 K
2 200 – 6 500 K
Lifetime 15 000 hours
Light source included

5.5 W GU10 Hue White Ambiance
220 V – 240 V/50 – 60 Hz
⊕ – IP20
↓ 102 ↔ 102 ↗ 103 mm (1L)
↓ 102 ↔ 240 ↗ 103 mm (2L)
↓ 102 ↔ 443 ↗ 103 mm (3L)
↓ 240 ↔ 240 ↗ 103 mm (4L)
Aluminium/Synthetic

Dimmer switch remote
control included





8719514382626
Aurelle ceiling lamp white
↓ 46 → 300 ↗ 300 mm
28 W, 230 V, 2000 lm max.



8719514382640
Aurelle SQ ceiling lamp white
↓ 46 → 600 ↗ 600 mm
55 W, 230 V, 4000 lm max.



8719514382664
Aurelle ceiling lamp white
↓ 46 → 1200 ↗ 300 mm
55 W, 230 V, 4000 lm max.



8719514382688
Aurelle ceiling lamp white
↓ 47 → 395 ↗ 395 mm
28 W, 230 V, 2000 lm max.



Aurelle

2 200 – 6 500 K
Lifetime 25 000 hours
Light source included
Hue White Ambiance
⊕ – IP20
Aluminium



Dimmer switch remote control included



Philips Hue Aurelle



Philips Hue Milliskin



8719514338586
Milliskin Hue aluminium recessed extension



8719514338609
Milliskin Hue white recessed extension



8719514382688
Milliskin Hue aluminium recessed extension



8719514338562
Milliskin Hue white recessed extension



8719514342828
Milliskin Hue aluminium recessed 3-pack



8719514342842
Milliskin Hue white recessed 3-pack



Milliskin



350 lm at 4 000 K
2 200 – 6 500 K
Lifetime 15 000 hours
Light source included

5.5 W GU10 Hue White Ambiance
220 V – 240 V/50 – 60 Hz
⊕ – IP20
↔ 90 / 90 mm
cut-out 70 mm, recessed 100 mm
Synthetic



Dimmer switch
not included





Philips Hue

Devere / Struana



8719514341012
Struana Hue ceiling lamp IP44
195 → 360 ↗ 360 mm



8718696176535
Hue Devere M ceiling lamp white
184 → 381 ↗ 381 mm

8718696176542
Hue Devere L ceiling lamp white
184 → 425 ↗ 425 mm



Devere / Struana



2400 lm at 4000 K (Struana)
2450 lm (Devere M), 4300 lm (Devere L)
at 4000 K
2200–6500 K
Lifetime 25000 hours
Light source included

32 W (Struana), 19.2 W (Devere M), 33.5 W (Devere L)
220 V–240 V/50–60 Hz
⊕ – IP44
Synthetic (Struana)
Metal / Synthetics (Devere)



Dimmer switch remote
control included





Philips Hue

Adore




8719514340978
Adore Hue ceiling lamp chrome
↓ 60 ↔ 407 ↗ 407 mm
1×40 W, 2400 lm max.




8719514340992
Adore Hue wall mirror lamp white
↓ 51 ↔ 560 ↗ 560 mm
40 W, 2400 lm max.



8719514340831
Adore Hue wall lamp chrome
↓ 64 ↔ 595 ↗ 138 mm
1×40 W, 3000 lm max.



8719514340954
Adore Hue bar wall lamp white
↓ 34 ↔ 420 ↗ 116 mm
13 W, 1050 lm max.



8719514340930
Adore Hue bar wall lamp white
↓ 34 ↔ 671 ↗ 116 mm
20 W, 1750 lm max.



Adore

2 200–6 500 K
Lifetime 30 000 hours (20 000 hours
for bar models)
Light source included
Hue White Ambiance
⊕ – IP44
Metal, Aluminium, Glass, Synthetics

Dimmer switch remote
control included





Philips Hue

Adore



F 8719514340916
Adore Hue plate white
1 120 ↔ 275 ↗ 250 mm
3×5.5 W GU10, 230 V, 3×350 lm max.



F 8719514340954
Adore Hue bar white
1 91 ↔ 626 ↗ 122 mm
3×5.5 W GU10, 230 V, 3×350 lm max.



F 8719514340879
Adore Hue bar white
1 90 ↔ 366 ↗ 120 mm
2×5.5 W GU10, 230 V, 2×350 lm max.



F 8719514340855
Adore Hue single spot white
1 136 ↔ 71 ↗ 121 mm
1×5.5 W GU10, 230 V, 350 lm max.



G 8719514340817
Adore Hue recessed chrome
1 70–75 ↔ 94 ↗ 94 mm
3×5 W, GU10, 3×350 lm max.



G 8719514340794
Adore Hue recessed chrome
1 70–75 ↔ 94 ↗ 94 mm
1×5 W, GU10, 350 lm max.
(Dimmer Switch not included)

Dimmer switch remote control included



Adore

2 200–6 500 K
Lifetime 30 000 hours (15 000 hours for GU models)
Light source included
Hue White Ambiance
⊕ – IP44
Metal, Aluminium, Glass, Synthetics



Philips Hue White

Adjust your lights easy and comfortably



Smart control, home and away

With the Philips Hue iOS and Android apps you can control your lights remotely wherever you are. Check if you have forgotten to switch your lights off before you left your home, and switch them on if you are working late.



Set timers for your convenience

Philips Hue can make it seem like you're home when you're not, using the schedule function in the Philips Hue app. Set the lights to come on at a pre-set time, so the lights are on when you arrive home. You can even set rooms to light up at different times. And of course, you can let the lights turn off gradually in the night, so you never have to worry whether you've left any lights on.



Installation free dimming

Experience guaranteed smooth dimming with Philips Hue. No need for wires, an electrician or installation.



Control with your voice

Philips Hue works with Amazon Alexa, Apple HomeKit* and Google Home, powered by the Google Assistant, to allow you to control your lights with your voice. Turn your lights on and off. Dim to the desired brightness for a perfect ambiance.

*Philips Hue Bridge required

800 lm



8719514319141
Philips Hue White
9 W A60 E27 4-pack



8719514329881
Philips Hue White
9 W A60 E27 3-pack



8719514319028
Philips Hue White
9 W A60 E27 2-pack



8719514320666
Philips Hue White
5.5 W E14



8719514320628
Philips Hue White 5.5 W
E14 2-Pack



8719514356696
Philips Hue White 5.7 W
E14 luster



8719514356771
Philips Hue White 5.7 W
E14 luster 2-Pack

1100 lm



8719514289130
Philips Hue White
9.5 W A60 E27 3-pack with
Bridge and Dimmer switch



8719514289116
Philips Hue White
9.5 W A60 E27 2-pack
with Bridge



8719514289192
Philips Hue White
9.5 W A60 E27 2-pack



8719514288232
Philips Hue White
9.5 W A60 E27



8719514340060
Philips Hue White
5.2 W GU10



8719514340145
Philips Hue White 5.2 W
GU10 2-pack

1600 lm



8719514343320
Philips Hue White
15.5 W A60 E27



Philips Hue White bulbs

1600 lm (E27 15.5 W), 1055 lm (E27 9.5 W), 800 lm (E27 9 W) at 2700 K
470 lm (E14), 400 lm (GU10) at 2700 K

White 2700 K

Lifetime 25 000 hours (E14, E27), 15 000 hours (GU10)

220 V – 240 V/50 – 60 Hz

⊕ – IP20

↑ 117 ↔ 39 mm (E14), ↑ 71 ↔ 50 mm (GU10)

↑ 110 ↔ 60 mm (E27 9 W, 9.5 W)

↑ 131 ↔ 67 mm (E27 15.5 W)

Synthetic/Glass (E14), Aluminium/Glass (E27), Synthetic (GU10)

All Philips Hue White bulbs are featuring Bluetooth® and Zigbee technology



8718699688820
**Philips Hue White
Filament 7 W E27 A60**



8718699688882
**Philips Hue White
Filament 7 W E27 G93**



8719514279131
**Philips Hue White
Filament 7 W E27 G125**



8718699688868
**Philips Hue White
Filament 7 W E27 ST64**



8719514279179
**Philips Hue White
Filament 7 W E27 ST72**



8719514302211
**Philips Hue White Filament
4.5 W E14 Candle 2-pack**



8719514302235
**Philips Hue White Filament
4.5 W E14 Candle**



Filament

550 lm, 7 W (E27), 2100 K
Lifetime 15 000 hours

220 V – 240 V/50 – 60 Hz

⊕ – IP20

↑ 114 ↔ 60 mm (A60), ↑ 148 ↔ 93 mm (G93),
↑ 135 ↔ 60 mm (ST64), ↑ 170 ↔ 72 mm (ST72),
↑ 192 ↔ 125 mm (125)

Aluminium/Glass

All Philips Hue White bulbs are featuring Bluetooth® and Zigbee technology

Philips Hue Filaments



Philips Hue

Welcome / Fuzo



8719514382763
Welcome Hue White
1 153 ↔ 220 ↗ 160 mm
28 W, 2300 lm, 2700 K



8719514382787
**Fuzo Hue White wall lantern
black half covered**
1 130 ↔ 130 ↗ 127 mm
15 W, 1150 lm, 2700 K



8719514382800
**Fuzo Hue White wall lantern
black square**
1 130 ↔ 140 ↗ 127 mm
15 W, 1150 lm, 2700 K



8719514382824
**Fuzo Hue White wall lantern
black rectangular**
1 221 ↔ 166 ↗ 75 mm
15 W, 1150 lm, 2700 K



8719514382848
**Fuzo Hue White wall lantern
black pedestal**
1 400 ↔ 100 ↗ 100 mm
15 W, 1150 lm, 2700 K



8719514382862
**Fuzo Hue White wall lantern
black post**
1 770 ↔ 100 ↗ 100 mm
15 W, 1150 lm, 2700 K

E Welcome

2700 K
Lifetime 25 000 hours
Light source included

Hue White
220 V – 240 V/50 – 60 Hz
⊕ – IP44
Aluminium die-cast

E Fuzo

2700 K
Lifetime 25 000 hours
Light source included

Hue White
220 V – 240 V/50 – 60 Hz
⊕ – IP44
Aluminium die-cast



8718696166048
Lucca wall lantern anthracite
1 115 ↔ 215 ↗ 170 mm
9.5 W, 806 lm, 2700 K



8718696166055
Lucca pedestal anthracite
1 400 ↔ 142 ↗ 142 mm
9.5 W, 806 lm, 2700 K



8718696166062
Lucca post anthracite
1 770 ↔ 142 ↗ 140 mm
9.5 W, 806 lm, 2700 K



8718696154465
Turaco wall lantern anthracite
1 212 ↔ 118 ↗ 101 mm
9.5 W, 806 lm, 2700 K



8718696154472
Turaco pedestal anthracite
1 408 ↔ 121 ↗ 121 mm
9.5 W, 806 lm, 2700 K



8718696154489
Turaco post anthracite
1 802 ↔ 121 ↗ 121 mm
9.5 W, 806 lm, 2700 K



8718696166079
Tuar wall lantern inox
1 185 ↔ 150 ↗ 150 mm
9.5 W, 806 lm, 2700 K



8718696166086
Tuar pedestal inox
1 400 ↔ 150 ↗ 150 mm
9.5 W, 806 lm, 2700 K

F Lucca / Tuar / Turaco

E27, 9,5 W, 806 lm, 2700 K
Lifetime 25 000 hours
Light source included

Hue White
220 V – 240 V/50 – 60 Hz
⊕ – IP44
Aluminium

Philips Hue
Lucca/Tuar/Turaco

Smart accessories

The smartest way to control your lights.

Make your lighting smarter and create breathtaking scenes at home with the right Philips Hue accessories. Remote controls work anywhere. Customize to fit your needs. No wires, no electrician, no installation.



8719514342620
Philips Hue Bridge

8719514274617
Philips Hue Dimmer Switch

8718696166079
Philips Hue Motion Sensor

8719514342262
Philips Hue Outdoor Sensor



8719514342347
Philips Hue Smart Plug CZ/SK

8719514342309
Philips Hue Smart Plug EU

8719514318045
Philips Hue Wall switch

8719514318021
Philips Hue Wall switch 2-pack

Smart Accessory

- Philips Hue Bridge** ↓ 88 → 88 ↗ 26 mm, ☹ – IP20, Synthetic
- Philips Hue Dimmer Switch** ↓ 92 → 35 ↗ 11 mm, ☹ – IP20, Synthetic, Bluetooth enabled
- Philips Hue Motion Sensor** 5 m range, 100° angle, ↓ 20 → 55 mm, ☹ – IP42, Synthetic, requires Bridge
- Philips Hue Wall switch** ↓ 43 → 38 ↗ 10 mm, IP20, ☹ – Synthetic, battery powered, requires Bridge
- Philips Hue Outdoor sensor** wireless, range: 12 meter, 160 degrees, battery powered, weatherproof, IP54, ↓ 76 → 76 ↗ 56 mm, synthetic, requires Bridge
- Philips Hue Smart Plug** enables on/off switching, ↓ 50 → 50 ↗ 85 mm, max. 3200 W, IP, Bluetooth enabled

Philips Hue Bridge based Benefits



Smart control
Away-from-home control
Light schedules
Comfort dimming
Create your ambience
Wake-up
Wellbeing
Paint with light
Sync with music
Sync with movies

White and color ambience	White ambience	White
✓	✓	✓
✓	✓	✓
✓	✓	✓
✓	✓	✓
✓	✓	
✓	✓	
✓	✓	
✓		
✓		

LIGHT OUTPUT



Philips Hue works with a range of different smart devices. When products are a Friends of Hue, they simply work together for you in your home. You can connect your Philips Hue system with Amazon Echo, Apple HomeKit, Google Home and many others. Bring your smart home to life with the most connected light in the world.



Philips Hue White and Color Ambiance

929002489604 871951432840200 8719514328402  18	929002489603 871951432838900 8719514328389  18	929002489602 871951432836500 8719514328365  18	929002468801 871951429117100 8719514291171  18	929002468802 871951429131700 8719514291317  18	915005761901 5062131P7 8718696171578  31	915005762301 5062148P7 8718696171615  31	915005762201 5062431P7 8718696171608  31	915005762601 5062448P7 8718696171646  31	915005762001 5062231P7 8718696171585  31
929002468804 871951429135500 8719514291355  18	929002468805 871951429137900 8719514291379  18	929002468811 871951429151500 8719514291515  18	929002468810 871951429149200 8719514291492  18	929002471601 871951428815700 8719514288157  18	915005762401 5062248P7 8718696171622  31	915005762501 5062348P7 8718696171639  31	915005762101 5062331P7 8718696171592  31	915005762101 5062331P7 8718696171592  31	
929002294204 871951435661000 8719514356610  19	929002294205 871951435671900 8719514356719  19	929001953111 871951433988000 8719514339880  19	929001953112 871951434008400 8719514340084  19	929001953115 871951434276700 8719514342767  19	929003047501 871951433864700 8719514338647  33	929003047401 871951433862300 8719514338623  33	929003045201 871951434288000 8719514342880  33	929003045301 871951434286600 8719514342866  33	929003045501 871951434290300 8719514342903  33
929001953113 871951434010700 8719514340107  19	929002275802 871869970480300 8718699704803  21	929002422701 871869978475100 8718699784751  23	929002422801 871869978477500 8718699784775  23	929002422901 871869978479900 8718699784799  23	929003047701 871951433892000 8719514338920  33	929003047601 871951433880700 8719514338807  33	915005928501 5060830P7 8718696176023  35	915005928801 5060731P7 8718696176054  35	915005928701 5060730P7 8718696176047  35
915005987901 871869617629000 8718696176290  25	915005988101 871869617631300 8718696176313  25	915005988001 871869617630600 8718696176306  25	915005988201 871869617632000 8718696176320  25	915005735501 7820331P7 8718696170809  27	915005928301 5061031P7 8718696176009  35	915005928101 5061030P7 8718696175989  35	915005928401 5060931P7 8718696176016  35	915005928201 5060930P7 8718696175996  35	915005928601 5060831P7 8718696176030  35
915005733701 7820130P7 8718696170717  27	915005734401 7820131P7 8718696170748  27	915005733901 7820230P7 8718696170724  27	915005734601 7820231P7 8718696170793  27	915005734101 7820330P7 8718696170731  27	915005986901 871869617623800 8718696176238  37	915005987001 871869617624500 8718696176245  37	915005987101 871869617625200 8718696176252  37	915005987201 871869617626900 8718696176269  37	
915005750101 7820430P7 8718696171189  29	915005761101 5063131P7 8718696171493  29	915005761201 5063130P7 8718696171509  29	915005761301 5063231P7 8718696171516  29	915005761401 5063230P7 8718696171523  29	915005871701 4090130P9 8718696174531  39	915005871801 4090131P9 8718696174548  39	915005871901 4090230P9 8718696174555  39	915005872001 4090231P9 8718696174562  39	
915005761501 5063331P7 8718696171530  29	915005761601 5063330P7 8718696171547  29	915005761701 5063431P7 8718696171554  29	915005761801 5063430P7 8718696171561  29		929003052501 871951434336800 8719514343368  41	929003053301 871951434346700 8719514343467  41	929003053401 871951434348100 8719514343481  41	929003053501 871951434350400 8719514343504  41	929003053601 871951434352800 8719514343528  41

915005997201
4116331P9
8718696176498



43

915005997301
4116330P9
8718696176504



43

915005997401
4116431P9
8718696176511



43

915005997501
4116430P9
8718696176528



43

929002966401
871951435507100
8719514355071



43

915005842601
1746230P7
8718696174364



57

915005629701
1741430P7
8718696167960



57

915005671701
1742830P7
8718696169087



57

915005629801
1741530P7
8718696167977



57

929002966501
871951435505700
8719514355057



43

915005997801
4116731P9
8718696176559



45

915005997901
4116831P9
8718696176566



45

929003074701
871951435534700
8719514355347



45

929003074801
871951435539200
8719514355392



45

915005731801
1743730P7
8718696170557



57

915005630301
1742030P7
8718696167991



57

929002994901
871951433996500
8719514339965



47

929002995001
871951433998900
8719514339989



47

929002269101
871869970342400
8718699703424



47

929002269201
871869970344800
8718699703448



47

915005842101
1745930P7
8718696174333



59

915005730801
1743030P7
8718696170496



59

915005731001
1743130P7
8718696170502



59

915005730601
1742930P7
8718696170489



59

915005731101
1743230P7
8718696170519



59

929002376001
871869977112600
8718699771126



49

929002375901
8718699770983
8718291488668



49

915005821901
7602031P7
8718696173992



49

915005731301
1743430P7
8718696170526



59

929002376101
871951426446500
8719514264465



51

929002376201
871951426448900
8719514264489



51

929002376402
871951441073200
8719514410732



51

929002376703
871951441152400
8719514411524



51

929002376803
871951441158600
8719514411586



51

915005841601
1745530P7
8718696174296



61

915005842901
1746430P7
8718696174388



61

915005843001
1746447P7
8718696174395



61

915005843201
1746530P7
8718696174401



61

915005843301
1746547P7
8718696174418



61

915005922901
1748830PN
8718696175941



54

915005936501
1734830PN
8718696176108



54

915005641701
1742430PN
8718696168721



55

915006001601
1736830PN
8718696176641



55

915006001801
1736930PN
8718696176658



55

915005841701
1745630P7
8718696174302



61

915005731401
1743530P7
8718696170533



63

915005842401
1746130P7
8718696174357



63

915005842801
1746330P7
8718696174371



51

915005976301
1746347P7
8718696176207



51

915005843401
1746630P7
8718696174425



57

929002289002
871869970983900
8718699709839



57

929002289102
871869970985300
8718699709853



57

915005732701
1744230P7
8718696170601



51

915005732101
1743930P7
8718696170571



51

915005732301
1744030P7
8718696170588



51

915005732501
1744130P7
8718696170595



51


915005731901
1743830P7
8718696170564




51

Philips Hue White Ambiance

929002489802 871951432824200 8719514328242  66	929002489803 871951432826600 8719514328266  66	929002489804 871951432828000 8719514328280  66	929002468403 871951429123200 8719514291232  66	929002468406 871951429181200 8719514291812  66	929003054301 871951434119700 8719514341197  77	929003054201 871951434121000 8719514341210  77	929003055601 871951434117300 8719514341173  77	929003055701 871951434123400 8719514341234  77	
929002468404 871951429125600 8719514291256  66	929002468401 871951429111900 8719514291119  66	929002471901 871951428819500 8719514288195  66			929003055101 871951434113500 8719514341135  79	929003055001 871951434115900 8719514341159  79	929003055201 871951434111100 8719514341111  79		
929001953312 871951434280400 8719514342804  67	929001953310 871951434012100 8719514340121  67	929001953309 871951433990300 8719514339903  67	929002294404 871951435673300 8719514356733  67	929002294403 871951435665800 8719514356658  67	915005914601 871869617528600 8718696175286  79	915005914701 871869617529300 8718696175293  79	915005914501 871869617527900 8718696175279  79		
929002477501 871951430142900 8719514301429  69	929002477701 871951430146700 8719514301467  69	929002477801 871951430148100 8719514301481  69	929002477901 871951430150400 8719514301504  69	929002478101 871951430154200 8719514301542  69	929003055401 871951434133300 8719514341333  81	929003055501 871951434135700 8719514341357  81	929003055301 871951434137100 8719514341371  81	929003054101 871951434139500 8719514341395  83	929003054001 871951434148000 8719514341418  83
929003054901 871951434107400 8719514341074  71	929003054801 871951434109800 8719514341098  71	929003054501 871951434129600 8719514341296  73	929003054401 871951434131900 8719514341319  73	929003054701 871951434125800 8719514341258  73	929003046501 871951433844900 8719514338449  85	929003046901 871951433852400 8719514338524  85	929003046401 871951433842500 8719514338425  85	929003046701 871951433848700 8719514338487  85	929003046801 871951433850000 8719514338500  85
929003054601 871951434127200 8719514341272  73	915005998101 4116230P6 8718696176580  75	915005998001 4116231P6 8718696176573  75	915005997101 4116130P6 8718696176481  75	915005997001 4116131P6 8718696176474  75	929003046601 871951433846300 8719514338463  85	929003045901 871951433832600 8719514338326  87	929003046101 871951433836400 8719514338364  87	929003045801 871951433820300 8719514338203  87	929003046001 871951433834000 8719514338340  87
915005996901 4116030P6 8718696176467  75	915005996801 4116031P6 8718696176450  75	915005996701 4115930P6 8718696176443  75	915005996601 4115931P6 8718696176436  75		929003045701 871951433816600 8719514338166  87	929003045601 871951433814200 8719514338142  87	929003046301 871951433840100 8719514338401  87	929003046201 871951433838800 8719514338388  87	
915005996501 4115830P6 8718696176429  75	915005996401 4115831P6 8718696176412  75				929003048401 871951433918700 8719514339187  89	929003048601 871951433922400 8719514339224  89	929003047801 871951433906400 8719514339064  89	929003048001 871951433910100 8719514339101  89	929003048201 871951433914900 8719514339149  89
					929003048501 871951433920000 8719514339200  89	929003048701 871951433924800 8719514339248  89	929003047901 871951433908800 8719514339088  89	929003048101 871951433912500 8719514339125  89	929003048301 871951433916300 8719514339163  89



Philips Hue White



Philips Hue accesories





© 2021-2022 Signify Holding. All rights reserved.

The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

www.philips-hue.com