BRP121 RCA内标
字体: Gill Sans MT
标签大小:50*30mm (尺寸公差±1），红色框线为刀模线，不需要印刷)
材质：白色不干胶不　胶

9114 018 24882 PHILIPS
BRP121 LED26/NW
BRP121 LED26/NW 20W 220-240V GM
LED Road lamp
20W / 36×0.56W LED
220-240V~ 50/60 Hz
λ : 0.9 0.09A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED39/NW
BRP121 LED39/NW 30W 220-240V GM
LED Road lamp
30W / 54×0.56W LED
220-240V~ 50/60 Hz
λ : 0.9 0.13A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

9114 018 24982 PHILIPS
BRP121 LED52/NW
BRP121 LED52/NW 40W 220-240V GM
LED Road lamp
40W / 70×0.56W LED
220-240V~ 50/60 Hz
λ : 0.9 0.17A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

9114 018 25082 PHILIPS
BRP121 LED65/NW
BRP121 LED65/NW 50W 220-240V GM
LED Road lamp
50W / 84×0.6W LED
220-240V~ 50/60 Hz
λ : 0.9 0.22A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

9114 018 25182 PHILIPS
BRP121 LED78/NW
BRP121 LED78/NW 60W 220-240V GM
LED Road lamp
60W / 98×0.61W LED
220-240V~ 50/60 Hz
λ : 0.9 0.26A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED91/NW
BRP121 LED91/NW 70W 220-240V GM
LED Road lamp
70W / 104×0.67W LED
220-240V~ 50/60 Hz
λ : 0.9 0.31A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

9114 018 25282 PHILIPS
BRP121 LED97/NW
BRP121 LED97/NW 80W 220-240V GM
LED Road lamp
80W / 140×0.57W LED
220-240V~ 50/60 Hz
λ : 0.9 0.35A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED26/WW
BRP121 LED26/WW 20W 220-240V GM
LED Road lamp
20W / 36×0.56W LED
220-240V~ 50/60 Hz
λ : 0.9 0.09A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED39/WW
BRP121 LED39/WW 30W 220-240V GM
LED Road lamp
30W / 54×0.56W LED
220-240V~ 50/60 Hz
λ : 0.9 0.13A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED52/WW
BRP121 LED52/WW 40W 220-240V GM
LED Road lamp
40W / 70×0.56W LED
220-240V~ 50/60 Hz
λ : 0.9 0.17A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED65/WW
BRP121 LED65/WW 50W 220-240V GM
LED Road lamp
50W / 84×0.6W LED
220-240V~ 50/60 Hz
λ : 0.9 0.22A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED78/WW
BRP121 LED78/WW 60W 220-240V GM
LED Road lamp
60W / 98×0.61W LED
220-240V~ 50/60 Hz
λ : 0.9 0.26A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED91/WW
BRP121 LED91/WW 70W 220-240V GM
LED Road lamp
70W / 104×0.67W LED
220-240V~ 50/60 Hz
λ : 0.9 0.31A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED97/WW
BRP121 LED97/WW 80W 220-240V GM
LED Road lamp
80W / 140×0.57W LED
220-240V~ 50/60 Hz
λ : 0.9 0.35A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED26/CW
BRP121 LED26/CW 20W 220-240V GM
LED Road lamp
20W / 36×0.56W LED
220-240V~ 50/60 Hz
λ : 0.9 0.09A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED39/CW
BRP121 LED39/CW 30W 220-240V GM
LED Road lamp
30W / 54×0.56W LED
220-240V~ 50/60 Hz
λ : 0.9 0.13A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED52/CW
BRP121 LED52/CW 40W 220-240V GM
LED Road lamp
20W / 70×0.56W LED
220-240V~ 50/60 Hz
λ : 0.9 0.17A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED65/CW
BRP121 LED65/CW 50W 220-240V GM
LED Road lamp
50W / 84×0.6W LED
220-240V~ 50/60 Hz
λ : 0.9 0.22 IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED78/CW
BRP121 LED78/CW 60W 220-240V GM
LED Road lamp
60W / 98×0.61W LED
220-240V~ 50/60 Hz
λ : 0.9 0.26A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED91/CW
BRP121 LED91/CW 70W 220-240V GM
LED Road lamp
70W / 104×0.67W LED
220-240V~ 50/60 Hz
λ : 0.9 0.31A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

********** PHILIPS
BRP121 LED97/CW
BRP121 LED97/CW 80W 220-240V GM
LED Road lamp
80W / 140×0.57W LED
220-240V~ 50/60 Hz
λ : 0.9 0.35A IP66
Class I ta35 ℃ 20W44
Made in China /Signify Luminnaires(Shanghai) C0.,Ltd.

BRP121 RCA内盒贴
字体: Gill Sans MT
标签大小：70*30mm
材质：白色不干胶

PHILIPS QTY:1PCS
BRP121 LED26/NW 20W 220-240V GM
12NC:911401824882
SKU:*********
EOC:82488299
EAN:8719514521520
EH02-YS
20W44
8719514521520
Made in China

PHILIPS QTY:1PCS
BRP121 LED39/NW 30W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED52/NW 40W 220-240V GM
12NC:911401824982
SKU:*********
EOC:82498299
EAN:8719514521537
EH02-YS
20W44
8719514521537
Made in China

PHILIPS QTY:1PCS
BRP121 LED65/NW 50W 220-240V GM
12NC:911401825082
SKU:*********
EOC:82508299
EAN:8719514521544
EH02-YS
20W44
8719514521544
Made in China

PHILIPS QTY:1PCS
BRP121 LED78/NW 60W 220-240V GM
12NC:911401825182
SKU:*********
EOC:82518299
EAN:8719514521551
EH02-YS
20W44
8719514521551
Made in China

PHILIPS QTY:1PCS
BRP121 LED91/NW 70W 220-240V GM
12NC:**********
SKU:******
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED97/NW 80W 220-240V GM
12NC:911401825282
SKU:*********
EOC:82528299
EAN:8719514521568
EH02-YS
20W44
8719514521568
Made in China

PHILIPS QTY:1PCS
BRP121 LED26/WW 20W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED39/WW 30W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED52/WW 40W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED65/WW 50W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED78/WW 60W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED91/WW 70W 220-240V GM
12NC:**********
SKU:******
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED97/WW 80W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED26/CW 20W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED39/CW 30W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED52/CW 40W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED65/CW 50W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED78/CW 60W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED91/CW 70W 220-240V GM
12NC:**********
SKU:******
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:1PCS
BRP121 LED97/CW 80W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

BRP121 RCA外箱贴
字体: Gill Sans MT
标签大小：70*30mm
材质：白色不干胶

PHILIPS QTY:12PCS
BRP121 LED26/NW 20W 220-240V GM
12NC:911401824882
SKU:*********
EOC:82488299
EAN:8719514521575
EH02-YS
20W44
6923828641870
Made in China

PHILIPS QTY:12PCS
BRP121 LED39/NW 30W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED52/NW 40W 220-240V GM
12NC:911401824982
SKU:*********
EOC:82498299
EAN:8719514521582
EH02-YS
20W44
8719514521582
Made in China

PHILIPS QTY:12PCS
BRP121 LED65/NW 50W 220-240V GM
12NC:911401825082
SKU:*********
EOC:82508299
EAN:8719514521599
EH02-YS
20W44
8719514521599
Made in China

PHILIPS QTY:12PCS
BRP121 LED78/NW 60W 220-240V GM
12NC:911401825182
SKU:*********
EOC:82518299
EAN:8719514521605
EH02-YS
20W44
8719514521605
Made in China

PHILIPS QTY:12PCS
BRP121 LED91/NW 70W 220-240V GM
12NC:**********
SKU:******
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED97/NW 80W 220-240V GM
12NC:911401825282
SKU:*********
EOC:82528299
EAN:8719514521612
EH02-YS
20W44
8719514521612
Made in China

PHILIPS QTY:12PCS
BRP121 LED26/WW 20W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED39/WW 30W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED52/WW 40W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED65/WW 50W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED78/WW 60W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED91/WW 70W 220-240V GM
12NC:**********
SKU:******
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED97/WW 80W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED26/CW 20W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED39/CW 30W 220-240V GM
12NC:**********
SKU:*********
EOC:*********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED52/CW 40W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED65/CW 50W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED78/CW 60W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED91/CW 70W 220-240V GM
12NC:**********
SKU:******
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

PHILIPS QTY:12PCS
BRP121 LED97/CW 80W 220-240V GM
12NC:**********
SKU:*********
EOC:********
EAN:**********
EH02-YS
20W44
Made in China

Essential SmartBright Road


BRP121

Mounting Instructions

V1.1

IEC 60598 | IP66 | IK08 | t_a35°C


Product Type	CCT (K)	Power(W)	LEDs	Lumen Output (lm)	Dimension(mm) AxBxC(mm)	S.C.x (m²)	kg	Voltage	Frequency	Surge rating
BRP121 LED26/WW 20W 220-240V GM	3000	20	36	2700	415x107x75	0.024	0.9	220-240 ~	50/60Hz	6KV/6KV
BRP121 LED39/WW 30W 220-240V GM		30	54	4050	415x107x75	0.024	0.9			
BRP121 LED52/WW 40W 220-240V GM		40	70	5600	460x120x75	0.033	1.1			
BRP121 LED65/WW 50W 220-240V GM		50	84	7000	460x120x75	0.033	1.1			
BRP121 LED78/WW 60W 220-240V GM		60	98	8400	494x135x75	0.042	1.3			
BRP121 LED91/WW 70W 220-240V GM		70	104	9800	494x135x75	0.042	1.3			
BRP121 LED97/WW 80W 220-240V GM		80	140	11200	542x163x75	0.062	1.5			
BRP121 LED26/NW 20W 220-240V GM	4000	20	36	2540	415x107x75	0.024	0.9			
BRP121 LED39/NW 30W 220-240V GM		30	54	3810	415x107x75	0.024	0.9			
BRP121 LED52/NW 40W 220-240V GM		40	70	5280	460x120x75	0.033	1.1			
BRP121 LED65/NW 50W 220-240V GM		50	84	6600	460x120x75	0.033	1.1			
BRP121 LED78/NW 60W 220-240V GM		60	98	7920	494x135x75	0.042	1.3			
BRP121 LED91/NW 70W 220-240V GM		70	104	9240	494x135x75	0.042	1.3			
BRP121 LED97/NW 80W 220-240V GM		80	140	10560	542x163x75	0.062	1.5			
BRP121 LED26/CW 20W 220-240V GM	6500	20	36	2700	415x107x75	0.024	0.9			
BRP121 LED39/CW 30W 220-240V GM		30	54	4050	415x107x75	0.024	0.9			
BRP121 LED52/CW 40W 220-240V GM		40	70	5600	460x120x75	0.033	1.1			
BRP121 LED65/CW 50W 220-240V GM		50	84	7000	460x120x75	0.033	1.1			
BRP121 LED78/CW 60W 220-240V GM		60	98	8400	494x135x75	0.042	1.3			
BRP121 LED91/CW 70W 220-240V GM		70	104	9800	494x135x75	0.042	1.3			
BRP121 LED97/CW 80W 220-240V GM		80	140	11200	542x163x75	0.062	1.5			



Type	A	B	C
20W	414	106	75
30W	414	106	75
40W	460	120	75
50W	460	120	75
60W	490	134	75
70W	490	134	75
80W	541	162	75


Unit:mm

This product does not provide any junction box / connector




GB13140.2/GB13140.3

H05RN-F 3x1.0 mm²
60245IEC57
N: blue
L : brown
GND : yellow-green



● Please use IP66 or higher IP grade junction box / connector for wiring




	M6	M8
Torque(Nm)	2.5 ~ 3	8~10



⚠ Install the luminaire according to the national regulation and make sure the luminaire installed safely and firmly to the lamp pole. Make sure the luminaire installed safely and securely to the lamp pole.
Installation with over recommended torque may cause the slippery or crack of spigot.

④



Signify Luminaires (Shanghai) Co., Ltd.
Address: 2F, Building 6, No. 1805, Huyi Highway, Malu Town, Jiading District, Shanghai, P.R.
China Postal code: 201801

PHILIPS

Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.

Product Type	Run Current (A) (@230V)	Start (Inrush) Current(A) /Ipeak (A)	Start Current Duration (μs) /T(@50% of Ipeak) (μs)	* Touch current or protective conductor current (mA)	Maximum Number of Luminaire on MCB 16A Type B (pcs)	Maximum Number of Luminaire on MCB 16A Type C (pcs)
BRP121 20W	0.09	7.5	10	<3.5	106	124
BRP121 30W	0.13	8.5	10	<3.5	73	86
BRP121 40W	0.17	14.6	20	<3.5	56	65
BRP121 50W	0.22	12.5	17	<3.5	43	50
BRP121 60W	0.26	13.3	17	<3.5	36	43
BRP121 70W	0.31	14.7	20	<3.5	30	36
BRP121 80W	0.35	12.8	22	<3.5	27	31

The leakage current *(touch current or protective conductor current) of electrical circuit may be greatly dependent upon electrical supply cables used such as its rating and length, proper connection of electrical supply cables to luminaires and wiring connection topology of luminaires to the supply electrical circuit amongst other site conditions.

* In some cases referred to as Earth Leakage Current.

Please read this manual carefully before using the product.

1. Do not switch on before complete installation.
2. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
3. If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.
4. The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced.
5. The luminaire is complied with GB7000.
6. Luminaire must not be used or stored in corrosive environment where hazardous materials such as Sulphur, Chlorine, phthalates, etc,are present.