

Philips Ledinaire

The essential range of trusted products for everyday lighting jobs that need good performance

Find the **right** solution in our range using the **Selector tool**
productfinder.lighting.philips.com



Trusted



Reliable



Great value

Ledinaire Floodlight



- Good quality finishing and design
- Reliable driver, less early failures
- Light output to meet standard applications
- Easy to install, supplied with stripped cable

Ledinaire Panel



- Metal frame for better robustness
- High quality lightguide, no yellowing
- Reliable driver, fewer early failures
- Office compliant available

Ledinaire Highbay



- Easy to use: light levels tuned to conventional
- Reliable driver, fewer early failures
- High efficacy up to 110 lm/W

Ledinaire

Choose affordable, reliable and energy-efficient lighting from the leading name in LED.

Ledinaire panel

lighting.philips.co.uk/systems/themes/ledinaire



Features

- 3400 lm light output, 100lm/W
- Office compliant (OC=<19UGR) & non-office compliant (NOC) versions
- Accessories for plaster, surface-mount and suspension available, safety cable included
- New increased lifetime: 50,000 hours at L70

Benefits

- Trusted performance: Philips quality tested driver
- Steel frame for extra robustness
- High quality lightguide to avoid early yellowing
- Easy quick connector for fast installation



50000h
at L70



4
PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
NEW RC065B LED34S/840 PSU W60L60 NOC UKI	34	3400	4000	IP20	911401899680	36446999
RC065B LED34S/840 PSU W60L60 OC UKI		3400	4000	IP20	911401899880	36450699
NEW RC065B LED34S/865 PSU W60L60 NOC UKI		3400	6500	IP20	911401899780	36447699
NEW RC065B LED34S/865 PSU W60L60 OC		3400	6500	IP20	911401884680	36204599
NEW RC065B LED34S/840 PSU W60L60 NOC UKI ELB3	37	3400	4000	IP20	919013004385	63499300
NEW RC065B LED34S/840 PSU W60L60 OC UKI ELB3		3400	4000	IP20	919013004386	63500600
NEW RC065B LED34S/865 PSU W60L60 NOC UKI ELB3		3400	6500	IP20	919013004387	63501300
RC007Z Plaster ceiling set	-	-	-	-	911401824180	34716599
RC065Z Safety cable	-	-	-	-	911401892680	36274899
RC065Z Surface-mounting set W60L60	-	-	-	-	911401892480	36272499
RC065Z Suspension set-3 WH (ceiling rose suspension kit)	-	-	-	-	911401805681	36592399

Ledinaire recessed and Ledinaire surface-mounted



Features

- Square and rectangular versions available
- Recessed and surface-mounted versions
- 3000K & 4000K versions
- 3400 lm light output

Benefits

- Philips quality and reliability
- Energy saving
- Diffuse comfortable light



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
RC060B LED34S/840 PSU W60L60 NOC	34	3400	4000	IP20	911401850780	06958500
SM060C LED34S/840 PSU W20L120 NOC		3400	4000	IP20	911401850680	06962200
SM060C LED34S/840 PSU W20L120 OC		3400	4000	IP20	911401842280	35039400
SM060C LED32S/830 PSU W20L120	36	3200	3000	IP20	910503910207	06963900

Ledinaire

Ledinaire recessed and Ledinaire surface-mounted – Continued



Features

- Square and rectangular versions available
- Recessed and surface-mounted versions
- 3000K & 4000K versions
- 3400 lm light output

Benefits

- Philips quality and reliability
- Energy saving
- Diffuse comfortable light



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
RC060B LED40S/840 PSU W60L60 NOC	40	4000	4000	IP20	911401842380	35040000
SM060C LED40S/840 PSU W20L120 NOC		4000	4000	IP20	911401842480	35041700
RC060B/SM060C LED32S EM PACK ELB3	-	-	-	-	919913999632	62949400
Emergency pack for Ledinaire Recessed RC060B & Surface Mounted SM060C	-	-	-	-	919913999632	62949400

Ledinaire wall-mounted



Features

- 1100 lm & 1700 lm light output
- 3000K & 4000K versions
- Possibility for through wiring
- Optional motion detection and daylight sensor.

Benefits

- Philips quality and reliability
- Energy saving
- Diffuse comfortable light
- Easy to install



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
WLO60V LED11S/830 PSU II WH	12	1100	3000	IP44	911401802080	33909299
WLO60V LED11S/840 PSU II WH		1100	4000	IP44	911401802180	33910899
WLO60V LED17S/830 PSU II WH	18.5	1700	3000	IP44	911401802280	33911599
WLO60V LED17S/830 PSU II WH ELB3		1700	3000	IP44	919013004303	63417700
WLO60V LED17S/840 PSU II WH		1700	4000	IP44	911401802380	33912299
WLO60V LED17S/840 PSU II WH ELB3	19.5	1700	3000	IP44	919013004304	63418400
WLO60V LED17S/830 PSU MDU II WH		1700	3000	IP44	911401802480	33913999
WLO60V LED17S/830 PSU MDU II WH ELB3		1700	4000	IP44	919013004305	63419100
WLO60V LED17S/840 PSU MDU II WH		1700	4000	IP44	911401802580	33914699
WLO60V LED17S/840 PSU MDU II WH ELB3		1700	4000	IP44	919013004306	63420700

Ledinaire downlight DN060B



Features

- 800 lm & 1800 lm light output
- 3000K & 4000K versions
- Modern, unobtrusive design

Benefits

- Philips quality and reliability
- Energy saving
- Diffuse comfortable light



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
DN060B LED8S/830 PSU WH	9	800	3000	IP20	911401532031	30662999
DN060B LED8S/840 PSU WH		800	4000	IP20	911401532231	30664399
DN060B LED18S/830 PSU WH	18	1800	3000	IP20	911401531931	30661299
DN060B LED18S/840 PSU WH		1800	4000	IP20	911401532131	30663699
DN060B LED18S EM PACK ELB3	-	-	-	-	919913999631	62948700
DN060B LED8S EM PACK ELB3	-	-	-	-	919913999630	62947000

Ledinaire downlight DN029B



Features

- 800lm, 1200lm, 2000lm light output
- Deep CCT switch
- Modern, unobtrusive design

Benefits

- Philips quality and reliability
- Energy saving
- Diffuse comfortable light



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
2 DN029B LED8/CCT 8W 220-240V D90 EU	8.5	800	3000, 4300 and 6500	IP44	929002066119	66018500
2 DN029B LED12/CCT 14W 220-240V D150 EU	14	1200	3000, 4300 and 6500	IP44	929002066219	66020800
1 DN029B LED20/CCT 24W 220-240V D200 EU	24	2000	3000, 4300 and 6500	IP44	929002066319	66022200

Ledinaire

Ledinaire SlimDownlight



Features

- WH White or ALU Aluminium finish available
- 2700K, 3000K & 4000K versions
- Kits with different LED lamps available

Benefits

- Philips quality and reliability
- Energy saving
- Replaceable LED lamps
- High performance dimming
- Superior light quality with CRI90



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
DN065B G2 LED10/830 11W 220V D150 RD EU	11	950	3000	IP20	929002220432	67939200
DN065B G2 LED10/840 11W 220V D150 RD EU		1000	4000	IP20	929002220532	67941500
DN065B G2 LED19/830 22W 220V D200 RD EU	22	1900	3000	IP20	929002220632	67943900
DN065B G2 LED20/840 22W 220V D200 RD EU		2000	4000	IP20	929002220732	67945300

Ledinaire Zadora



Features

- WH White or ALU Aluminium finish available
- 2700K, 3000K & 4000K versions
- Kits with different LED lamps available

Benefits

- Philips quality and reliability
- Energy saving
- Replaceable LED lamps
- High performance dimming
- Superior light quality with CRI90



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
RS049B LED-MS-40-5W-2700-GU10 ALU 50W	5	355	2700	IP20	912401483106	07014799
RS049B LED-MS-40-5W-3000-GU10 WH 50W		365	3000	IP20	912401483107	07015499
RS049B LED-MS-40-5W-3000-GU10 WH 50W		375	3000	IP20	910503910195	07015499

Ledinaire ClearAccent



1



2

Features

- Fixed and adjustable versions available
- 3000K & 4000K versions
- 500 lm light output
- Modern, unobtrusive design

Benefits

- Philips quality and reliability
- Energy saving
- Facetted reflector look and feel
- Easy installation with driver on-board



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
1 RS060B LED5-36-/830 PSR II WH	6	500	3000	IP20	910503910182	07267799
1 RS060B LED5-36-/840 PSR II WH		500	4000	IP20	910503910183	07268499
2 RS061B LED5-36-/830 PSR II WH		500	3000	IP20	910503910184	07269199
2 RS061B LED5-36-/840 PSR II WH		500	4000	IP20	910503910185	07270799

Ledinaire waterproof



Features

- Robust and waterproof luminaire, new slim design
- New 6ft version available (8400lm)
- Mounting bracket can be positioned over full length
- Through-wiring versions available
- Increased efficiency to up to 120lm/W

Benefits

- Low height design with less dust accumulation
- New connector for easy installation
- Diff use comfortable light
- Philips quality and reliability



50000h
at L65



4/9 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
NEW WT065C LED24S/840 PSU L1200	20	2400	4000	IP65	911401825281	36951899
NEW WT065C LED24S/840 PSU L1200 ELB3	23	2400	4000	IP65	919013004422	56635365
NEW WT065C LED48S/840 PSU L1200	43.5	4800	4000	IP65	911401825381	36952599
NEW WT065C LED48S/840 PSU L1200 ELB3	46.5	4800	4000	IP65	919013004423	56635372
NEW WT065C LED35S/840 PSU L1500	28	3500	4000	IP65	911401825481	36953299
NEW WT065C LED35S/840 PSU L1500 ELB3	31	3500	4000	IP65	919013004424	56635389
NEW WT065C LED68S/840 PSU L1500	55	6800	4000	IP65	911401825581	36954999
NEW WT065C LED68S/840 PSU L1500 ELB3	58	6800	4000	IP65	919013004425	56635396
NEW WT065C LED44S/840 PSU L1800	44	4400	4000	IP65	911401825681	36955699
NEW WT065C LED44S/840 PSU L1800 ELB3	47	4400	4000	IP65	919013004426	56635402
NEW WT065C LED84S/840 PSU L1800	65	8400	4000	IP65	911401825781	36956399
NEW WT065C LED84S/840 PSU L1800 ELB3	68	8400	4000	IP65	919013004427	56635419

Ledinaire

Ledinaire FloodLight Mini



Features

- Available with or without motion sensor
- 10W/20W/50W
- IP65
- IK07
- Symmetrical beam
- 50,000 hours at L70
- Rewired connection
- Remote control included in the MDU versions

Benefits

- Good quality finishing and design
- Reliable driver, less early failures
- Light output to meet standard applications
- Easy to install, supplied with stripped cable



Product Type	LED	Lumen Output	Colour Temp	Motion/Daylight sensor	IP rating	12NC	EOC code
	W	lm	K				
1 BVP154 LED10/830 PSU 10W VWB CE	10	1050	3000	-	IP65	911401730422	32970399
2 BVP154 LED10/830 PSU 10W VWB Motion Detection Unit CE		1050	3000	motion and daylight sensor	IP65	911401733332	33131799
1 BVP154 LED10/840 PSU 10W VWB CE		1050	4000	-	IP65	911401730432	32971099
2 BVP154 LED10/840 PSU 10W VWB Motion Detection Unit CE		1050	4000	motion and daylight sensor	IP65	911401733342	33132499
3 BVP154 LED20/830 PSU 20W VWB CE	20	2100	3000	-	IP65	911401730442	32972799
2 BVP154 LED20/830 PSU 20W VWB Motion Detection Unit CE		2100	3000	motion and daylight sensor	IP65	911401733352	33133199
3 BVP154 LED21/840 PSU 20W VWB CE		2100	4000	-	IP65	911401730452	32973499
2 BVP154 LED21/840 PSU 20W VWB Motion Detection Unit CE		2100	4000	motion and daylight sensor	IP65	911401733362	33134899
3 BVP154 LED50/830 PSU 50W VWB CE	50	5250	3000	-	IP65	911401730462	32974199
4 BVP154 LED50/830 PSU 50W VWB Motion Detection Unit CE		5250	3000	motion and daylight sensor	IP65	911401733372	33135599
5 BVP154 LED52/840 PSU 50W VWB CE		5250	4000	-	IP65	911401730472	32975899
4 BVP154 LED52/840 PSU 50W VWB Motion Detection Unit CE		5250	4000	motion and daylight sensor	IP65	911401733382	33136299

Ledinaire FloodLight Maxi



Features

- Available with motion sensor
- 100W/150W/200W
- IP65
- IK08
- Asymmetrical and symmetrical beam options
- 50,000 hours at L70
- Prewired connection

Benefits

- Good quality finishing and design
- Reliable driver, less early failures
- Light output to meet standard applications
- Easy to install, supplied with stripped cable



50000h
at L70



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
1 BVP155 LED100/840 PSU 100W AWB CE	100	10000	4000	IP65	911401733302	33128799
1 BVP155 LED105/840 PSU 100W VWB CE		10500	4000	IP65	911401733272	33125699
2 BVP155 LED150/840 PSU 150W AWB CE	150	15000	4000	IP65	911401733312	33129499
2 BVP155 LED157/840 PSU 150W VWB CE		15750	4000	IP65	911401733282	33126399
3 BVP155 LED200/840 PSU 200W AWB CE	200	20000	4000	IP65	911401733322	33130099
3 BVP155 LED210/840 PSU 200W VWB CE		21000	4000	IP65	911401733292	33127099

Ledinaire batten



Features

- BESA fixing
- Multiple lengths and light levels available (up to 8000lm and 6ft)
- Integral Emergency versions available, Philips quality driver

Benefits

- Easy to install and connect thanks to retainer cables and push-in connectors
- Possible through-wiring for flexibility in the installation thanks to: knock-out holes on both sides and loop-in loop-out terminal



50000h
at L65



6/8 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
NEW BNO65C LED25S/840 PSU L1200 UKI	22.5	2500	4000	IP20	911401825881	36963199
NEW BNO65C LED25S/840 PSU L1200 UKI ELB3	25.5	2500	4000	IP20	919013004428	56635426
NEW BNO65C LED35S/840 PSU L1500 UKI	32	3500	4000	IP20	911401826081	36965599
NEW BNO65C LED35S/840 PSU L1500 UKI ELB3	35	3500	4000	IP20	919013004430	56635440
NEW BNO65C LED43S/840 PSU L1800 UKI	39	4300	4000	IP20	911401826281	36967999
NEW BNO65C LED43S/840 PSU L1800 UKI ELB3	42	4300	4000	IP20	919013004432	56635464
NEW BNO65C LED52S/840 PSU L1200 UKI	47	5200	4000	IP20	911401825981	36964899
NEW BNO65C LED52S/840 PSU L1200 UKI ELB3	50	5200	4000	IP20	919013004429	56635433
NEW BNO65C LED60S/840 PSU L1500 UKI	55	6000	4000	IP20	911401826181	36966299
NEW BNO65C LED60S/840 PSU L1500 UKI ELB3	58	6000	4000	IP20	919013004431	56635457
NEW BNO65C LED80S/840 PSU L1800 UKI	73	8000	4000	IP20	911401826381	36968699
NEW BNO65C LED80S/840 PSU L1800 UKI ELB3	76	8000	4000	IP20	919013004433	56635471

Ledinaire

Ledinaire Core Lighting Batten



Features

- LEDtube-based 1600 & 3200 lm
- Light line up to ten battens for LEDtube version
- Mounting accessories included

Benefits

- Trusted performance, low early failures
- LEDtube versions for easy replacement of light sources



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
1 BN013C LED5S/830 L300	5	475	3000	IP20	911401835880	34953499
1 BN013C LED5S/840 L300		500	4000	IP20	911401835780	34952799
1 BN013C LED10S/830 L600	10	940	3000	IP20	911401836080	34955899
1 BN013C LED10S/840 L600		1000	4000	IP20	911401835980	34954199
1 BN013C LED14S/830 L900	15	1410	3000	IP20	911401836280	34957299
1 BN013C LED15S/840 L900		1500	4000	IP20	911401836180	34956599
2 BN060C 1xTLED16/840 L1200	18	1600	4000	IP20	910503910118	07007999
1 BN013C LED19S/830 L1200	20	1880	3000	IP20	911401836480	34959699
1 BN013C LED20S/840 L1200		2000	4000	IP20	911401836380	34958999
1 BN013C LED24S/830 L1500	24	2350	3000	IP20	911401836680	34961999
1 BN013C LED25S/840 L1500		2500	4000	IP20	911401836580	34960299
2 BN060C 2xTLED16/840 L1200	36	3200	4000	IP20	910503910119	07009399

Ledinaire Pentura mini LED



Features

- Ultra-slim LED batten
- Available in 300, 600, 900 and 1200 mm lengths
- 3000K & 4000K versions
- Non-trunkable version with on/off switch available.

Benefits

- Philips quality and reliability
- Energy saving
- Compact design



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
BN132C LED3S/830 PSU L300	4	350	3000	IP40	910503910163	07250999
BN132C LED3S/840 PSU L300		350	4000	IP40	910503910162	07249399
BN132C LED6S/830 PSU L600	7	650	3000	IP40	910503910161	07248699
BN132C LED6S/840 PSU L600		650	4000	IP40	910503910160	07247999
BN132C LED9S/830 PSU L900	10	950	3000	IP40	910503910159	07246299
BN132C LED9S/840 PSU L900		950	4000	IP40	910503910158	07245599
BN132C LED12S/830 PSU L1200	14	1250	3000	IP40	910503910157	07244899
BN132C LED12S/840 PSU L1200		1250	4000	IP40	910503910156	07243199

Ledinaire highbay



Features

- Modern, unobtrusive design
- Two lumen packages and sizes; 10,000lm with 24cm diameter, 20,000lm with 34cm diameter
- The IP65 rating is perfect for any application
- Including IP65 connector

- Single suspension with installation hook (included) or pipe mounting(not included)
- Optional reflector accessory for medium beam
- Non-dimming with driver on board

Benefits

- Philips quality and reliability
- Energy savings
- Wide application coverage



50000h
at L65



1 PACK

Product Type	LED	Lumen Output	Colour Temp	IP rating	12NC	EOC code
	W	lm	K			
BY020P LED100S/840 PSU WB GR	97	10000	4000	IP65	911401599651	333996299
BY021P LED200S/840 PSU WB GR	190	20000	4000	IP65	911401599751	333998699
BY020Z AC (reflector)					911401597351	333992499
BY021Z AC (reflector)					911401597451	333994899