

Ledinaire



Trusted



Reliable



Great value

5
Year
Warranty

Second rate or simply great?

Ledinaire Panel

Energy efficient, professional luminaire, ideal for office applications

Features

- ✓ 3400 lm light output, 100 lm/W
- ✓ Office compliant (<19UGR) & non-office compliant (NOC) versions
- ✓ Accessories for plaster, surface-mount and suspension available, safety cable
- ✓ **New increased lifetime:** 50,000 hours (L70)
- ✓ New back-lit architecture

Benefits

- ✓ Trusted performance: Philips quality tested driver
- ✓ Steel frame for extra robustness
- ✓ High quality lightguide to avoid early yellowing
- ✓ Easy, quick connector for fast installation

Ledinaire Panel

Product Short ID	Product EAN ID	Product Material Name	Input power	Lumen output	CCT	Efficacy	Colour	IP	IK	Height	Length	Width
919013004385	501635663499300	RC065B LED34S/840 PSU W60L60 NOC UKI ELB3	37W	3400lm	4000K	92lm/W	White	IP20	IK02	35mm	595mm	595mm
919013004386	501635663500600	RC065B LED34S/840 PSU W60L60 OC UKI ELB3	37W	3400lm	4000K	92lm/W	White	IP20	IK02	36mm	595mm	595mm
919013004387	501635663501300	RC065B LED34S/865 PSU W60L60 NOC UKI ELB3	37W	3400lm	6500K	92lm/W	White	IP20	IK02	35mm	595mm	595mm
911401899680	871016336446999	RC065B LED34S/840 PSU W60L60 NOC UKI	34W	3400lm	4000K	100 lm/W	White	IP20	IK02	35mm	595mm	595mm
911401899780	871016336447699	RC065B LED34S/865 PSU W60L60 NOC UKI	34W	3400lm	6500K	100 lm/W	White	IP20	IK02	35mm	595mm	595mm
911401899880	871016336450699	RC065B LED34S/840 PSU W60L60 OC UKI	34W	3400lm	4000K	100 lm/W	White	IP20	IK02	36mm	595mm	595mm
911401884680	871016336204599	RC065B LED34S/865 PSU W60L60 OC	34W	3400lm	6500K	100 lm/W	White	IP20	IK02	36mm	595mm	595mm

Accessories

911401892480	871016336272499	RC065Z Surface mounting set W60L60
911401824180	871016334716599	RC007Z Plaster ceiling set
911401805681	871016336592399	RC065Z Suspension set-3 WH
911401892680	871016336274899	RC065Z Safety cable



For warranty conditions, visit www.lighting.philips.com/main/support/support/warranty

© 2020 Signify Holding All technical information can be found at www.philips.com
Errors and omissions excepted, only the technical data sheets apply.

