

PHILIPS

Ledinaire



Trusted



Reliable



Great value

5
Year
Warranty

NEW Philips Ledinaire batten.

Efficient, great value and ready to perform.

The **Ledinaire Batten** range provides maximum performance and durability with an equally attractive price, sporting a traditional design with high efficacy and long lifetime while being very easy to install.

Features and benefits

- ✓ BESA fixing
- ✓ Multiple lengths and light levels available (up to 8000lm and 6ft)
- ✓ Easy to install and connect thanks to the retainer cable and the push-in connectors
- ✓ Possible through-wiring for flexibility in the installation thanks to: knock-out holes on both sides, and loop-in loop out terminal
- ✓ Philips quality driver
- ✓ Integral Emergency versions available

Applications

- ✓ Utility Spaces
- ✓ Storage Areas
- ✓ Workshops

REAL
PROs
REAL
QUALITY

New versions
available



For warranty conditions, visit
www.lighting.philips.com/main/support/support/warranty

Order information

Product Short	Product EOC	Product Material Name	Market Descriptions	Input power	Lumen output	CCT	Efficacy
911401825881	871016336963199	BN065C LED25S/840 PSU L1200 UKI	4ft 'Single' IP20 Batten 4000k 2500lm	22.5W	2500lm	4000K	109lm/W
911401825981	871016336964899	BN065C LED52S/840 PSU L1200 UKI	4ft 'Twin' IP20 Batten 4000k 5200lm	47W	5200lm	4000K	111lm/W
911401826081	871016336965599	BN065C LED35S/840 PSU L1500 UKI	5ft 'Single' IP20 Batten 4000k 3500lm	32W	3500lm	4000K	109lm/W
911401826181	871016336966299	BN065C LED60S/840 PSU L1500 UKI	5ft 'Twin' IP20 Batten 4000k 6300lm	55W	6000lm	4000K	109lm/W
911401826281	871016336967999	BN065C LED43S/840 PSU L1800 UKI	6ft 'Single' IP20 Batten 4000k 4300lm	39W	4300lm	4000K	110lm/W
911401826381	871016336968699	BN065C LED80S/840 PSU L1800 UKI	6ft 'Twin' IP20 Batten 4000k 8000lm	73W	8000lm	4000K	110lm/W
919013004428	5016356635426	BN065C LED25S/840 PSU L1200 UKI ELB3	4ft 'Single' IP20 Batten 4000k 2500lm E3	25.5W	2500lm	4000K	98lm/W
919013004429	5016356635433	BN065C LED52S/840 PSU L1200 UKI ELB3	4ft 'Twin' IP20 Batten 4000k 5200lm E3	50W	5200lm	4000K	104lm/W
919013004430	5016356635440	BN065C LED35S/840 PSU L1500 UKI ELB3	5ft 'Single' IP20 Batten 4000k 3500lm E3	35W	3500lm	4000K	100lm/W
919013004431	5016356635457	BN065C LED60S/840 PSU L1500 UKI ELB3	5ft 'Twin' IP20 Batten 4000k 6300lm E3	58W	6000lm	4000K	103lm/W
919013004432	5016356635464	BN065C LED43S/840 PSU L1800 UKI ELB3	6ft 'Single' IP20 Batten 4000k 4300lm E3	42W	4300lm	4000K	102lm/W
919013004433	5016356635471	BN065C LED80S/840 PSU L1800 UKI ELB3	6ft 'Twin' IP20 Batten 4000k 8000lm E3	76W	8000lm	4000K	105lm/W

Dimensions

