

PHILIPS

Ledinaire



Trusted



Reliable



Great value

5
Year
Warranty

NEW Philips Ledinaire waterproof.

Efficient, great value and ready to perform.

The **Ledinaire waterproof** range provides maximum performance and durability with an equally attractive price. As an off-the-shelf LED luminaire solution, it comes in a variety of lengths and lumen packages and can be installed in a wide range of locations.

REAL
PROs
REAL
QUALITY

Features and benefits

- ✓ Robust (IK08) and waterproof (IP65) luminaire
- ✓ Multiple lengths and light levels available (new 6ft option, up to 8400lm)
- ✓ Improved ease of installation with metal clips, longer sliders, and glands available as accessories if required for through-wiring
- ✓ Tested Philips quality
- ✓ Ceiling-mounted brackets and suspension hooks also included as accessories
- ✓ Emergency Integral versions available

Applications

- ✓ Covered car parks
- ✓ Industrial halls
- ✓ (Cold) storage rooms
- ✓ Under canopy

New versions
available




For warranty conditions, visit
www.lighting.philips.com/main/support/support/warranty

Order information


| Product Short | Product EOC | Product Material Name | Market Descriptions | Input power | Lumen output | CCT | Efficacy |
|---------------|-----------------|----------------------------------|--|-------------|--------------|-------|----------|
| 911401825281 | 871016336951899 | WT065C LED24S/840 PSU L1200 | 4ft 'Single' IP65 Waterproof 4000k 2400lm | 20W | 2400lm | 4000K | 120lm/W |
| 911401825381 | 871016336952599 | WT065C LED48S/840 PSU L1200 | 4ft 'Twin' IP65 Waterproof 4000k 4800lm | 43.5W | 4800lm | 4000K | 110lm/W |
| 911401825481 | 871016336953299 | WT065C LED35S/840 PSU L1500 | 5ft 'Single' IP65 Waterproof 4000k 3500lm | 28W | 3500lm | 4000K | 125lm/W |
| 911401825581 | 871016336954999 | WT065C LED68S/840 PSU L1500 | 5ft 'Twin' IP65 Waterproof 4000k 6800lm | 55W | 6800lm | 4000K | 120lm/W |
| 911401825681 | 871016336955699 | WT065C LED44S/840 PSU L1800 | 6ft 'Single' IP65 Waterproof 4000k 4400lm | 44W | 4400lm | 4000K | 100lm/W |
| 911401825781 | 871016336956399 | WT065C LED84S/840 PSU L1800 | 6ft 'Twin' IP65 Waterproof 4000k 8400lm | 65W | 8400lm | 4000K | 129lm/W |
| 919013004422 | 5016356635365 | WT065C LED24S/840 PSU L1200 ELB3 | 4ft 'Single' IP65 Waterproof 4000k 2400lm E3 | 23W | 2400lm | 4000K | 104lm/W |
| 919013004423 | 5016356635372 | WT065C LED48S/840 PSU L1200 ELB3 | 4ft 'Twin' IP65 Waterproof 4000k 4800lm E3 | 46.5W | 4800lm | 4000K | 103lm/W |
| 919013004424 | 5016356635389 | WT065C LED35S/840 PSU L1500 ELB3 | 5ft 'Single' IP65 Waterproof 4000k 3500lm E3 | 31W | 3500lm | 4000K | 113lm/W |
| 919013004425 | 5016356635396 | WT065C LED68S/840 PSU L1500 ELB3 | 5ft 'Twin' IP65 Waterproof 4000k 6800lm E3 | 58W | 6800lm | 4000K | 117lm/W |
| 919013004426 | 5016356635402 | WT065C LED44S/840 PSU L1800 ELB3 | 6ft 'Single' IP65 Waterproof 4000k 4400lm E3 | 47W | 4400lm | 4000K | 94lm/W |
| 919013004427 | 5016356635419 | WT065C LED84S/840 PSU L1800 ELB3 | 6ft 'Twin' IP65 Waterproof 4000k 8400lm E3 | 68W | 8400lm | 4000K | 123lm/W |

Dimensions

WT065C (1200+1500)




WT065C (L1800)




| WT065C (mm) | A | B | C | D | E min | E max | F |
|----------------------|----|------|----|----|-------|-------|----|
| LED24S/840 PSU L1200 | 76 | 1215 | 80 | 38 | 538 | 1062 | 85 |
| LED48S/840 PSU L1200 | 76 | 1215 | 80 | 38 | 538 | 1062 | 85 |
| LED35S/840 PSU L1500 | 76 | 1515 | 80 | 38 | 838 | 1362 | 85 |
| LED68S/840 PSU L1500 | 76 | 1515 | 80 | 38 | 838 | 1362 | 85 |

| WT065C (mm) | A | B | C | D | E min | E max | F |
|-------------|----|------|----|----|-------|-------|----|
| LED44S/840 | 83 | 1870 | 97 | 56 | 851 | 1120 | 90 |
| LED84S/840 | 83 | 1870 | 97 | 56 | 851 | 1120 | 90 |

WT065C



WT065C TW



| WT065C (mm) | A | B | C | D | E | F | G |
|-------------|----|----|----|------|---------|---------|-------|
| L1200 | 69 | 59 | 90 | 1201 | 200~250 | 200~250 | |
| L1500 | 69 | 59 | 90 | 1501 | 100~150 | 100~150 | |
| L1800 | 69 | 59 | 90 | 1801 | 150~250 | 150~250 | 900.5 |

| WT065C TW (mm) | A | B | C | D | E | F |
|----------------|----|----|----|------|---------|---------|
| L1200 | 69 | 59 | 90 | 1258 | 230~280 | 230~280 |
| L1500 | 69 | 59 | 90 | 1558 | 180~280 | 180~280 |

