

# PHILIPS

LED lamps

CorePro Dimmable  
MR16 Lamps



## Affordable, high-quality lamps, **perfect for accent lighting**

**The CorePro LED MR16** lamps are an affordable and ideal solution for spot and general retrofit lighting applications in the hospitality and retail industries.

These lamps have a new look and feel with a single optics lens, while providing a crisp and uniform beam.

### Easy to experience

- 25,000-hr life<sup>1</sup>
- Suitable for use in enclosed fixtures<sup>2</sup>
- “Perfect fit” mechanical design fits most MR16 fixtures

1. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 50,000 hours is for bare lamp without fixture.

2. See Technical Application Guide for complete details. All lamps include an over temperature protection (OTP) feature that systematically reduces the lamp power and consequently its internal temperature should it be subjected to abnormally high ambient temperature conditions.

# CorePro dimmable MR16 lamps

Ordering, electrical and technical data (Subject to change without notice)



Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Beam Angle	Lumens (lm)	Volts (V)	CRI (min)	Lifetime <sup>1</sup> (hrs)	CCT (K)	Dimmable	Release date	
<b>CorePro MR16 50W replacement lamps</b>												
D	533117	929001880704	7.3MR16/LED/827/F25/DIM 12V 10/1FB	7.3	25	515	12V	80	25,000	2700	Yes	Nov 2018
D	533125	929001880804	7.3MR16/LED/830/F25/DIM 12V 10/1FB	7.3	25	515	12V	80	25,000	3000	Yes	Nov 2018
D	533141	929001881004	7.3MR16/LED/827/F35/DIM 12V 10/1FB	7.3	35	515	12V	80	25,000	2700	Yes	Nov 2018
D	533158	929001881104	7.3MR16/LED/830/F35/DIM 12V 10/1FB	7.3	35	515	12V	80	25,000	3000	Yes	Nov 2018
<b>CorePro MR16 75W replacement lamps</b>												
D	533513	929001881304	8.5MR16/LED/827/F25/DIM 12V 10/1FB	8.5	25	600	12V	80	25,000	2700	Yes	Nov 2018
D	533174	929001881404	8.5MR16/LED/830/F25/DIM 12V 10/1FB	8.5	25	620	12V	80	25,000	3000	Yes	Nov 2018
D	533521	929001881504	8.5MR16/LED/840/F25/DIM 12V 10/1FB	8.5	25	660	12V	80	25,000	4000	Yes	Nov 2018
D	533182	929001881604	8.5MR16/LED/827/F35/DIM 12V 10/1FB	8.5	35	600	12V	80	25,000	2700	Yes	Nov 2018
D	533190	929001881704	8.5MR16/LED/830/F35/DIM 12V 10/1FB	8.5	35	620	12V	80	25,000	3000	Yes	Nov 2018
D	533331	929001881804	8.5MR16/LED/840/F35/DIM 12V 10/1FB	8.5	35	660	12V	80	25,000	4000	Yes	Nov 2018

1. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 50,000 hours is for bare lamp without fixture.

D = Damp location ■ = ENERGY STAR® qualified



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-18136BN 05/20 philips.com/lighting



Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.