

PHILIPS

LED lamps

UFO lamps



A modern take on lighting **that is out of this world**

Philips LED UFO decorative lamps are perfect for those applications where you need light and only have a socket to work with. Highly efficient and a modern aesthetic for locations with low ceilings or ornamental areas.

Benefits

- Rugged plastic design
- Contains no mercury
- Up to a 15,000-hour life¹
- Installs into existing medium base fixtures
- Great for closets, attics, workrooms and more
- Lowers maintenance costs by reducing re-lamp frequency
- Less glare through increased surface space

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.

Philips LED UFO lamps



Ordering, electrical and technical data (Subject to change without notice)

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Base	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend
UFO - 75W lamp equivalent non-dimming													
D 561654	929002010503	16UFO/LED/830/FR/P/ND 4/1FB	16	1150	E26	110-240	80	3000	15,000	MC	Plastic	Frosted	A
D 561639	929002441103	16UFO/LED/850/FR/P/ND 4/1FB	16	1200	E26	110-240	80	5000	15,000	MC	Plastic	Frosted	A
D 545110	929002010605	16UFO/LED/865/FR/P/ND 6/1FB	16	1200	E26	110-240	80	6500	15,000	MC	Plastic	Frosted	A
UFO - 125W lamp equivalent non-dimming													
D 561662	929002010703	26UFO/LED/830/FR/P/ND 4/1FB	26	1950	E26	110-240	80	3000	15,000	MC	Plastic	Frosted	B
D 561647	929002441203	26UFO/LED/850/FR/P/ND 4/1FB	26	2050	E26	110-240	80	5000	15,000	MC	Plastic	Frosted	B
D 545137	929002010805	26UFO/LED/865/FR/P/ND 6/1FB	26	2050	E26	110-240	80	6500	15,000	MC	Plastic	Frosted	B

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
 2. MC/CP = MasterClass or CorePro product.
- D** = Damp location



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.