

PHILIPS

LED lamps

Specialty lamps



Special applications deserve only the benefits of LED

Philips specialty lamps allow you to maintain a classic feel while enjoying the saving of LED.

Benefits

- Lowers Maintenance cost by reducing re-lamp frequency
- Huge energy savings when comparing to halogen counterparts
- Suitable for damp applications

Features

- Rugged plastic design on many models
- Capsule lamps fit into existing landscape lighting
- C7 is ideal for night-light for night time visibility
- Up to 15,000 hour life

Philips LED Specialty lamps



Ordering, electrical and technical data (Subject to change without notice)

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	Bulb	Base	Volts (V)	CRI (min)	CCT (K)	Legend	
MasterClass non-dimming												
D E	477166	929001844003	1T3/LED/830/G4/ND/12V 6/1BC	1	10	100	T3	G4	12	80	3000	A
D E	477174	929001844203	2T3/LED/830/G4/ND 12V 6/1BC	2	20	200	T3	G4	12	80	3000	B
D E	477240	929001844425	2T3/PER/830/ND/GY6.35/12V 6/1BC	2	20	200	T3	GY6.35	12	80	3000	C
D E	477208	929001840625	2.2T3/PER/830/ND/G8/120V 6/1	2.2	20	200	T4	G8	120	80	3000	D
D E	465138	929001266825	3T3/PER/830/ND/G9/120V 6/1BC	3	25	250	T3	G9	120	80	3000	E
D E	534263	929001840835	3.6T3/PER/830/ND/G9/120V 6/1BC	3.6	40	370	T3	G9	120	80	3000	F
D E	463448	929001236903	1.2T5/SPC/830/ND/12V/BC/2PK 6/2	1.2	7	120	T5	Wedge	12	80	3000	G
D E	475418	929002389636	2T5/LED/830/ND/12V 6/2BC	2	18	200	T5	Wedge	12	80	3000	H
D	471946	929001357525	7.5R7S/PER/830/ND/120V 4/1BC	7.5	100	800	T3	Double end R7	120	80	3000	I
D	471952	929001373325	14R7S/PER/830/ND/120V 4/1BC	14	200	1500	T3	Double end R7	120	80	3000	J
D	462977	929001224603	BC0.5C7/LED/827/E12/ND 120V 2pk	0.5	7	30	C7	E12	120	80	2700	K

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.
D = Damp location **E** = Suitable for enclosed fixtures **■** = Not regulated by Title 20



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.