



Contents

Type A

T8 Instant-start other	1
T8 UniversalFit	1
T8 FlexFit	1
T8 Instant-start 4ft	2
T8 Program start (FO) other	9
T8 Program start (FO) 4ft.	10
T8 Dimmable Ballasts	13
PL-L Ballasts	14
Emergency Ballasts	15

Type C

InstanFit Drivers	16
-------------------	----

Type A

PL-C/T Ballasts 4-pin	17
Emergency PL-C/T Ballasts 4-pin	18
PL-S/C Ballasts 2-pin	18
T12 Electronic Ballasts	19
T12 Rapid-Start Magnetic Ballasts	19
T5 HO Ballasts	20
T5 HE Ballasts	20
T8/T12 8' Slimline Ballasts	21

LATAM

T8 Ballasts	21
FA8 Ballasts	21

T8 Instant-Start Ballasts

		7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	13W 2100 lm (U-Bent) ²	12.5 W 1800 lm (4 ft.)	16 W 1800 lm (4 ft.)
		469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888 545814, 544874 544882	FlexFit 560193, 600189 600197	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Philips Advance	ICN-1P32-N				System Certified	
Philips Advance	ICN-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICN-3P32-N	System Certified	System Certified		System Certified	
Philips Advance	ICN-4P32-N	System Certified	System Certified		System Certified	System Certified
Philips Advance	IOPA-1P32-N	Not Recommended		Not Recommended	System Certified	Not Recommended
Philips Advance	IOPA-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-3P32-N	System Certified	System Certified		System Certified	System Certified
Philips Advance	IOPA-4P32-N	System Certified	System Certified		System Certified	System Certified
Philips Advance	IOPA-2P32-LW-N	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-3P32-LW-N	System Certified	System Certified		System Certified	System Certified
Philips Advance	IOPA-4P32-LW-N	System Certified	System Certified		System Certified	System Certified
Philips Advance	IOPA-1P32-HL-N	System Certified	System Certified			
Philips Advance	IOPA-2P32-HL-N	System Certified	System Certified	System Certified	System Certified	
Philips Advance	IOPA-3P32-HL-N	System Certified	System Certified		System Certified	System Certified
Philips Advance	IOPA-4P32-HL-SC	System Certified	System Certified		Not Recommended	System Certified
Philips Advance	GOPA-1P32-SC	System Certified			System Certified	System Certified
Philips Advance	GOPA-2P32-SC	System Certified			System Certified	
Philips Advance	GOPA-3P32-SC	System Certified	System Certified		System Certified	System Certified
Philips Advance	GOPA-4P32-SC	System Certified	System Certified		System Certified	System Certified
Philips Advance	GOPA-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-2P32-LW-N	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-1P32-LW-SC	System Certified		System Certified	System Certified	System Certified
Philips Advance	GOPA-2P32-LW-SC	System Certified			System Certified	System Certified
Philips Advance	GOPA-3P32-LW-SC	System Certified			System Certified	System Certified
Philips Advance	GOPA-4P32-LW-SC	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	REB-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	REB-2P32-SC	System Certified	System Certified		System Certified	System Certified
Philips Advance	REB-4P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WH3-120-L	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WH3-277-L	System Certified	System Certified		System Certified	System Certified
Fulham Co., Inc	WH5-120-L	System Certified	System Certified			
Fulham Co., Inc	WH5-277-L	System Certified	System Certified		System Certified	System Certified
Fulham Co., Inc	WHSG1-UNV-T8-IS	Not Recommended	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WHSG2-UNV-T8-IS	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WHSG2-UNV-T8-LB		System Certified		System Certified	System Certified
Fulham Co., Inc	WHSG3-UNV-T8-IS	Not Recommended	Not Recommended			

- System performance “System Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance “Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance “blank” field means consult factory.
- Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start Ballasts

		10 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	16W 1800 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	13 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft.)
		541986, 541994	470096, 470104 470112, 470120	542084, 542092 542100, 545616 544502, 544510 544486, 544494 544759, 545624 544916	545178, 533372 545194, 545200	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	473926, 473934 473942, 473958	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Philips Advance	ICN-1P32-N								
Philips Advance	ICN-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICN-3P32-N		System Certified		System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICN-4P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-1P32-N			Not Recommended	Not Recommended			Not Recommended	Not Recommended
Philips Advance	IOPA-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-3P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-4P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-2P32-LW-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-3P32-LW-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-4P32-LW-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-1P32-HL-N			System Certified		System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-2P32-HL-N	System Certified	System Certified		System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-3P32-HL-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-4P32-HL-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-1P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-2P32-SC	System Certified	System Certified		System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-3P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-4P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-2P32-LW-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-1P32-LW-SC	System Certified	System Certified		System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-2P32-LW-SC	System Certified	System Certified		System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-3P32-LW-SC	System Certified	System Certified		System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-4P32-LW-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	REB-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	REB-2P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified		System Certified
Philips Advance	REB-4P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WH3-120-L	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WH3-277-L	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WH5-120-L					System Certified	System Certified		
Fulham Co., Inc	WH5-277-L	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WHSG1-UNV-T8-IS	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WHSG2-UNV-T8-IS	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WHSG2-UNV-T8-LB	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WHSG3-UNV-T8-IS					System Certified	System Certified		

1. System performance “System Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
 System performance “Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
 System performance “blank” field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start Ballasts

		7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	13W 2100 lm (U-Bent) ²	12.5 W 1800 lm (4 ft.)	16 W 1800 lm (4 ft.)
		469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888 545814, 544874 544882	FlexFit 560193, 600189 600197	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Fulham Co., Inc	WHSG3-UNV-T8-LB	Not Recommended	Not Recommended		System Certified	System Certified
Fulham Co., Inc	WHSG3-UNV-T8-HB	Not Recommended	Not Recommended	System Certified	System Certified	System Certified
Fulham Co., Inc	WH42-UNV-L	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WH43-UNV-L	Not Recommended	Not Recommended	System Certified	System Certified	System Certified
Fulham Co., Inc	WH44-UNV-L	Not Recommended	Not Recommended			
Fulham Co., Inc / Leviton	Zipline (361RC-Z03)	Not Recommended	Not Recommended			
Universal Lighting Technologies	B132IUNVHP-N	Certified	Certified		Certified	Certified
Universal Lighting Technologies	B232IUNVHP-N	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B332IUNVHP-A		Certified		Certified	Certified
Universal Lighting Technologies	B432IUNVHP-A	Certified	Certified		Certified	Certified
Universal Lighting Technologies	B132IUNVHE-A	Certified	Certified		Certified	Certified
Universal Lighting Technologies	B232IUNVHE-A	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B332IUNVHE-A	Certified	Certified		Certified	Certified
Universal Lighting Technologies	B432IUNVHE-A	Certified	Certified		Certified	Certified
Universal Lighting Technologies	B132IUNVEL-A	Certified	Certified		Certified	Certified
Universal Lighting Technologies	B232IUNVEL-A	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B332IUNVEL-A	Certified	Certified		Certified	Certified
Universal Lighting Technologies	B432IUNVEL-A	Certified	Certified		Certified	Certified
Universal Lighting Technologies	B232IUNVHEH-A	Certified	Certified		Certified	Certified
Universal Lighting Technologies	B332IUNVHEH-A	Certified	Certified		Certified	Certified
Universal Lighting Technologies	B432I277HEH	Certified			Certified	Certified
Universal Lighting Technologies	B232I347HP-A	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B432I347HP	Certified			Certified	Certified
General Electric	GE-132-MV-N				Certified	Certified
General Electric	GE-232-MV-N	Certified	Certified	Certified	Certified	Certified
General Electric	GE-332-MV-N	Certified	Certified		Certified	Certified
General Electric	GE-232-MV-N-DIY	Certified	Certified	Certified	Certified	Certified
General Electric	GE-332-MV-N-DIY	Certified	Certified		Certified	Certified
General Electric	GE-432-MV-N-DIY	Certified	Certified		Certified	Certified
General Electric	GE232MAX-N/ULTRA	Certified	Certified	Certified	Certified	Certified
General Electric	GE332MAX-N/ULTRA	Certified			Certified	Certified
General Electric	GE432MAX-N/ULTRA	Certified			Certified	Certified
General Electric	GE232MAX-L/ULTRA	Certified	Certified	Certified	Certified	Certified
General Electric	GE332MAX-L/ULTRA	Certified	Certified		Certified	Certified
General Electric	GE432MAX-L/ULTRA	Certified	Not Recommended		Certified	Certified
General Electric	GE132MAX-H/ULTRA				Certified	Certified

1. System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance "blank" field means consult factory.
2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start Ballasts

		10 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	16W 1800 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	13 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft.)
		541986, 541994	470096, 470104 470112, 470120	542084, 542092 542100, 545616 544502, 544510 544486, 544494 544759, 545624 544916	545178, 533372 545194, 545200	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	473926, 473934 473942, 473958	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Fulham Co., Inc	WHSG3-UNV-T8-LB	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WHSG3-UNV-T8-HB	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WH42-UNV-L	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WH43-UNV-L	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	WH44-UNV-L					System Certified	System Certified		
Fulham Co., Inc / Leviton	Zipline (361RC-Z03)					System Certified	System Certified		
Universal Lighting Technologies	B132IUNVHP-N	Certified	Certified	Certified		Certified	Certified	Certified	Certified
Universal Lighting Technologies	B232IUNVHP-N	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B332IUNVHP-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B432IUNVHP-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B132IUNVHE-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B232IUNVHE-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B332IUNVHE-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B432IUNVHE-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B132IUNVEL-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B232IUNVEL-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B332IUNVEL-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B432IUNVEL-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B232IUNVHEH-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B332IUNVHEH-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B432I277HEH	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B232I347HP-A	Certified	Certified	Certified	Certified	Certified	Certified		Certified
Universal Lighting Technologies	B432I347HP	Certified	Certified	Certified	Certified	Certified		Certified	
General Electric	GE-132-MV-N	Certified	Certified		Certified			Certified	Certified
General Electric	GE-232-MV-N	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE-332-MV-N	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE-232-MV-N-DIY	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE-332-MV-N-DIY	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE-432-MV-N-DIY	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE232MAX-N/ULTRA	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE332MAX-N/ULTRA	Not Recommended	Not Recommended		Certified			Certified	Certified
General Electric	GE432MAX-N/ULTRA	Certified	Certified	Certified		Not Recommended	Not Recommended	Certified	Certified
General Electric	GE232MAX-L/ULTRA	Certified	Certified		Certified	Certified	Certified	Certified	Certified
General Electric	GE332MAX-L/ULTRA	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE432MAX-L/ULTRA	Not Recommended	Not Recommended		Certified			Certified	Certified
General Electric	GE132MAX-H/ULTRA	Certified	Certified			Certified	Certified	Certified	Certified

1. System performance “System Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
 System performance “Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
 System performance “blank” field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start Ballasts

7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	13W 2100 lm (U-Bent) ²	12.5 W 1800 lm (4 ft.)	16 W 1800 lm (4 ft.)
469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888 545814, 544874 544882	FlexFit 560193, 600189 600197	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704

Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
General Electric	GE232MAX-H/ULTRA	Certified	Certified	Certified	Certified	Not Recommended
General Electric	GE332MAX-H/ULTRA	Certified	Certified		Certified	Certified
General Electric	GE432MAX-H/ULTRA	Certified	Certified		Certified	Certified
General Electric	GE232MAX347-N	Certified	Certified	Certified	Certified	Certified
General Electric	GE432MAX347-N	Certified	Certified		Certified	Certified
General Electric	GE232-120RES-DIY	Certified	Certified	Certified	Certified	Certified
General Electric	GE432-120RES-DIY	Certified	Certified		Certified	Certified
Osram Sylvania	QTP 1x32T8/UNV ISN-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QTP 2x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QTP 3x32T8/UNV ISN-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QTP 4x32T8/UNV ISN-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QTP 2X32T8/347 ISN-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISN-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 3x32T8/UNV ISN-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISN-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 4X32T8/347 ISN-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISL-SC	Certified			Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISL-SC	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 3x32T8/UNV ISL-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISL-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISH-SC	Certified			Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISH-SC	Certified		Certified	Certified	Certified
Osram Sylvania	QHE 3x32T8/UNV ISH-SC	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISH	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISH HT SC	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISH HT SC	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4X32T8/UNV ISH-HT-1	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISN-SC-1	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISN-SC-1	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 3x32T8/UNV ISN-SC-1	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISN-SC-1	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISL-SC-1	Certified	Certified		Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISL-SC-1	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISL-SC-1	Certified	Certified		Certified	Certified
Ultrasave	UT232347	Certified	Certified	Certified	Certified	Certified

1. System performance “System Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance “Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance “blank” field means consult factory.
2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start Ballasts

		10 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	16W 1800 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	13 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft.)
		541986, 541994	470096, 470104 470112, 470120	542084, 542092 542100, 545616 544502, 544510 544486, 544494 544759, 545624 544916	545178, 533372 545194, 545200	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	473926, 473934 473942, 473958	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
General Electric	GE232MAX-H/ULTRA			Not Recommended	Not Recommended		Certified	Certified	Certified
General Electric	GE332MAX-H/ULTRA	Certified	Certified	Certified	Certified	Not Recommended	Not Recommended	Certified	Certified
General Electric	GE432MAX-H/ULTRA	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE232MAX347-N	Certified	Certified		Certified	Certified	Certified	Certified	Certified
General Electric	GE432MAX347-N				Certified	Certified	Certified	Certified	Certified
General Electric	GE232-120RES-DIY	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE432-120RES-DIY	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QTP 1x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QTP 2x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QTP 3x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QTP 4x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QTP 2X32T8/347 ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISN-SC	Certified	Certified		Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 3x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4X32T8/347 ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISL-SC	Certified	Certified		Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISL-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 3x32T8/UNV ISL-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISL-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISH-SC	Certified	Certified		Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISH-SC	Certified	Certified		Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 3x32T8/UNV ISH-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISH	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISH HT SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISH HT SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4X32T8/UNV ISH-HT-1	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISN-SC-1	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISN-SC-1	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 3x32T8/UNV ISN-SC-1	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISN-SC-1	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISL-SC-1	Certified	Certified		Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 2x32T8/UNV ISL-SC-1		Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISL-SC-1	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Ultrasave	UT232347	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified

- System performance “System Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance “Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance “blank” field means consult factory.
- Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start Ballasts

		7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	13W 2100 lm (U-Bent) ²	12.5 W 1800 lm (4 ft.)	16 W 1800 lm (4 ft.)
		469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888 545814, 544874 544882	FlexFit 560193, 600189 600197	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Ultrasave	UT432347	Certified			Certified	Certified
Hatch	HL232AIS/UV/HE/W	Certified	Certified	Certified	Certified	Certified
Hatch	HL332AIS/UV/HE/W	Certified	Certified		Certified	Certified
Hatch	HL232BIS/UV/HE/W	Certified	Certified	Certified	Certified	Certified
Hatch	HL432BIS/UV/HE/W	Certified	Certified			Certified
Hatch	HL232AIS/34/HE/W	Certified	Certified	Certified	Certified	Certified
Hatch	HL432AIS/34/HE/W	Certified	Certified		Certified	Certified
Accupro	AK-RC-232IP-UNV	Certified	Certified	Certified	Certified	Certified
Accupro	AP-232IP-UNV-M			Certified	Certified	Certified
Accupro	AP-332IP-UNV	Certified	Certified	Certified	Certified	Certified
Howard Industries	EP2/32IS/MV/MC/HE	Certified		Certified	Certified	Certified
Howard Industries	EP4/32IS/MV/MC	Certified	Certified		Certified	Certified
Howard Industries	EP4/32IS/MV/MC/HE	Certified			Certified	Certified
Fusion	FB232347E-N	Certified	Certified			
Fusion	FB232MVE	Certified	Certified	Certified	Certified	Certified
Fusion	FB432MVE-N	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-132-UV-IS-N-P	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-232RIS-1-TP-SL	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-232-UV-IS-L-P	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-232-UV-IS-N-P	Certified	Certified	Certified		Certified
Keystone	KTEB-332-UV-IS-L-P	Certified	Certified		Certified	Certified
Keystone	KTEB-332-UV-IS-N-P	Certified	Certified		Certified	Certified
Keystone	KTEB-432RIS-1-TP-SL	Certified	Certified		Certified	Certified
Keystone	KTEB-432-UV-IS-N-P	Certified	Certified		Certified	Certified
Keystone	KTEB-432-UV-PS-N-P	Certified	Certified		Certified	Certified
ESPEN	VE232120HIP	Certified	Certified	Certified	Certified	Certified
ESPEN	VE232MVHIPE	Certified	Certified	Certified	Certified	Certified
ESPEN	VE232MVHIPHE	Certified		Certified	Certified	Certified
ESPEN	VE232MVHIPL	Certified	Certified	Certified		Certified
ESPEN	VE332120MIP	Certified	Certified		Certified	Certified
ESPEN	VE332MVHIPHE	Certified	Certified		Certified	Certified
ESPEN	VE432120MIP	Certified	Certified		Certified	Certified
ESPEN	VE432MVHIPE	Certified			Certified	Certified
ESPEN	VE432MVHIPH	Certified	Certified			
ESPEN	VE432MVHIPHE	Certified			Certified	Certified
ESPEN	VE432MVHIPL	Certified	Certified		Certified	Certified

- System performance “System Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance “Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance “blank” field means consult factory.
- Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start Ballasts

		10 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	16W 1800 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	13 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft.)
		541986, 541994	470096, 470104 470112, 470120	542084, 542092 542100, 545616 544502, 544510 544486, 544494 544759, 545624 544916	545178, 533372 545194, 545200	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	473926, 473934 473942, 473958	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Ultrasave	UT432347				Certified	Certified	Certified	Certified	Certified
Hatch	HL232AIS/UV/HE/W	Certified			Certified	Certified	Certified	Certified	Certified
Hatch	HL332AIS/UV/HE/W	Certified		Certified	Certified	Certified	Certified	Certified	Certified
Hatch	HL232BIS/UV/HE/W	Certified		Certified	Certified	Certified	Certified	Certified	Certified
Hatch	HL432BIS/UV/HE/W	Certified		Certified	Certified	Certified	Certified	Certified	Certified
Hatch	HL232AIS/34/HE/W			Certified		Certified			
Hatch	HL432AIS/34/HE/W	Certified			Certified	Certified	Certified	Certified	Certified
Accupro	AK-RC-232IP-UNV	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Accupro	AP-232IP-UNV-M	Certified		Certified	Certified	Certified			
Accupro	AP-332IP-UNV	Certified	Certified	Certified		Certified	Certified	Certified	Certified
Howard Industries	EP2/32IS/MV/MC/HE	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Howard Industries	EP4/32IS/MV/MC			Certified	Certified	Certified	Certified	Certified	Certified
Howard Industries	EP4/32IS/MV/MC/HE	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Fusion	FB232347E-N								
Fusion	FB232MVE	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Fusion	FB432MVE-N	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-132-UV-IS-N-P	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-232RIS-1-TP-SL	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-232-UV-IS-L-P	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-232-UV-IS-N-P	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-332-UV-IS-L-P	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-332-UV-IS-N-P	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-432RIS-1-TP-SL	Certified	Certified	Certified					
Keystone	KTEB-432-UV-IS-N-P	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Keystone	KTEB-432-UV-PS-N-P	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
ESPEN	VE232120HIP	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
ESPEN	VE232MVIHPE	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
ESPEN	VE232MVIHPE	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
ESPEN	VE232MVIHPE	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
ESPEN	VE332120MIP	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
ESPEN	VE332MVIHPE	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
ESPEN	VE432120MIP	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
ESPEN	VE432MVIHPE	Certified	Certified	Certified					
ESPEN	VE432MVIHIPH			Certified	Certified	Certified	Certified	Certified	Certified
ESPEN	VE432MVIHPE	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
ESPEN	VE432MVIHPE	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified

1. System performance “System Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
 System performance “Certified” means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
 System performance “blank” field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Programmed-Start Ballasts

(Fixed Output)

		7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	13W 2100 lm (U-Bent) ²
		469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹
Philips Advance	IOP-1PSP32-N			
Philips Advance	IOP-2PSP32-N			
Philips Advance	IOP-3PSP32-SC	System Certified	System Certified	
Philips Advance	IOP-4PSP32-SC	System Certified	System Certified	
Philips Advance	IOP-1PSP32-LW-N			
Philips Advance	IOP-2PSP32-LW-N			
Philips Advance	IOP-3PSP32-LW-SC	System Certified	System Certified	
Philips Advance	IOP-4PSP32-LW-SC	System Certified	System Certified	
Philips Advance	HOP-2PSP32-HL-L			
Philips Advance	HOP-4PSP32-HL-G			
Universal Lighting Technologies	B232PUNVHE-B	Certified	Certified	
Universal Lighting Technologies	B332PUNVHE-A	Certified	Certified	
Universal Lighting Technologies	B432PUNVHE-A	Certified	Certified	
Universal Lighting Technologies	B232PUNVHEH-A			
Universal Lighting Technologies	B332PUNVHEH-A			
Universal Lighting Technologies	B232PUNVEL-B			
Universal Lighting Technologies	B332PUNVEL-A			
Universal Lighting Technologies	B432PUNVEL-A			
General Electric	GE-232MVPS-XL			
General Electric	GE-332MVPS-XL			
General Electric	GE-132MVPS-L			
General Electric	GE-232MVPS-L			
General Electric	GE-332MVPS-L			
General Electric	GE-432MVPS-L			
General Electric	GE-132MVPS-N			
General Electric	GE-232MVPS-N	Certified	Certified	Certified
General Electric	GE-332MVPS-N	Certified	Certified	
General Electric	GE-432MVPS-N	Certified	Certified	
General Electric	GE-132MVPS-H			
General Electric	GE-232MVPS-H			
General Electric	GE-332MVPS-H			
General Electric	GE-432MVPS-H			
Osram Sylvania	QHE 1X32T8/UNV PSX-MC			
Osram Sylvania	QHE 2X32T8/UNV PSX-MC			
Osram Sylvania	QHE 3X32T8/UNV PSX-SC			
Osram Sylvania	QHE 4X32T8/UNV PSX-SC			
Osram Sylvania	QHE 1X32T8/UNV PSN-MC			

- System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer. System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only. System performance "blank" field means consult factory.
- Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Programmed-Start Ballasts (Fixed Output)

		9.5 W 1600 lm (4 ft.)	13 W 2100 lm (4 ft.)	10 W 1600 lm (4 ft.)	10 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	16 W 1800 lm (4 ft.)
		473974, 473982 473990, 474007 540807	473926, 473934 473942, 473958	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	541986, 541994	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686	470096, 470104 470112, 470120	545178, 533372 545194, 545200	539972, 539980 539148, 539155 539163, 542688 542696, 542704
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Philips Advance	IOP-1PSP32-N		System Certified						System Certified
Philips Advance	IOP-2PSP32-N		System Certified			System Certified			System Certified
Philips Advance	IOP-3PSP32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOP-4PSP32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOP-1PSP32-LW-N		System Certified						System Certified
Philips Advance	IOP-2PSP32-LW-N		System Certified			System Certified			
Philips Advance	IOP-3PSP32-LW-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	IOP-4PSP32-LW-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	HOP-2PSP32-HL-L		System Certified			System Certified			System Certified
Philips Advance	HOP-4PSP32-HL-G		System Certified			System Certified			System Certified
Universal Lighting Technologies	B232PUNVHE-B	Certified	Certified	Certified	Certified	Certified	Certified		
Universal Lighting Technologies	B332PUNVHE-A	Certified	Certified	Certified	Certified	Certified	Certified		
Universal Lighting Technologies	B432PUNVHE-A	Certified	Certified	Certified	Certified	Certified	Certified		
Universal Lighting Technologies	B232PUNVHEH-A		Certified			Certified			Certified
Universal Lighting Technologies	B332PUNVHEH-A		Certified			Certified			Certified
Universal Lighting Technologies	B232PUNVEL-B		Certified			Certified			Certified
Universal Lighting Technologies	B332PUNVEL-A		Certified			Certified			Certified
Universal Lighting Technologies	B432PUNVEL-A		Certified			Certified			Certified
General Electric	GE-232MVPS-XL		Certified			Certified			Certified
General Electric	GE-332MVPS-XL		Certified			Certified			Certified
General Electric	GE-132MVPS-L		Certified			Certified			Certified
General Electric	GE-232MVPS-L		Certified			Certified			Certified
General Electric	GE-332MVPS-L		Certified			Certified			Certified
General Electric	GE-432MVPS-L		Certified			Certified			Certified
General Electric	GE-132MVPS-N		Certified			Certified			Certified
General Electric	GE-232MVPS-N	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE-332MVPS-N	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE-432MVPS-N	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE-132MVPS-H		Certified			Certified			Certified
General Electric	GE-232MVPS-H		Certified			Certified			Certified
General Electric	GE-332MVPS-H		Certified			Certified			Certified
General Electric	GE-432MVPS-H		Certified			Certified			Certified
Osram Sylvania	QHE 1X32T8/UNV PSX-MC		Certified						Certified
Osram Sylvania	QHE 2X32T8/UNV PSX-MC		Certified						Certified
Osram Sylvania	QHE 3X32T8/UNV PSX-SC		Certified			Certified			Certified
Osram Sylvania	QHE 4X32T8/UNV PSX-SC		Certified			Certified			Certified
Osram Sylvania	QHE 1X32T8/UNV PSN-MC		Certified			Certified			Certified

- System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance "blank" field means consult factory.
- Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Programmed-Start Ballasts

(Fixed Output)

		7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	13W 2100 lm (U-Bent) ²
		469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹
Osram Sylvania	QHE 2X32T8/UNV PSN-MC	Certified	Certified	Certified
Osram Sylvania	QHE 3X32T8/UNV PSN-SC	Certified	Certified	
Osram Sylvania	QHE 4X32T8/UNV PSN-SC	Certified	Certified	
Osram Sylvania	QHES 2X32T8/UNV PSL-SC			
Osram Sylvania	QHE 2X32T8/UNV PSH-HT			
Osram Sylvania	QHE 3X32T8/UNV PSH-HT-SC			
Osram Sylvania	QHE 4X32T8/UNV PSH-HT			
Hatch	HL232APS/UV/HE/W			
Hatch	HL332APS/UV/HE/W			
Hatch	HL432APS/UV/HE/W			
Hatch	HL232BPS/UV/HE/W			
Hatch	HL332BPS/UV/HE/W			
Hatch	HL432BPS/UV/HE/W			
Hatch	HL232CPS/UV/HE/W			
Hatch	HL332CPS/UV/HE/W			

1. System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer. System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only. System performance "blank" field means consult factory.
2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Programmed-Start Ballasts (Fixed Output)

		9.5 W 1600 lm (4 ft.)	13 W 2100 lm (4 ft.)	10 W 1600 lm (4 ft.)	10 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	16 W 1800 lm (4 ft.)
		473974, 473982 473990, 474007 540807	473926, 473934 473942, 473958	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	541986, 541994	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686	470096, 470104 470112, 470120	545178, 533372 545194, 545200	539972, 539980 539148, 539155 539163, 542688 542696, 542704
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Osram Sylvania	QHE 2X32T8/UNV PSN-MC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 3X32T8/UNV PSN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4X32T8/UNV PSN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 2X32T8/UNV PSL-SC					Certified			
Osram Sylvania	QHE 2X32T8/UNV PSH-HT		Certified			Certified			Certified
Osram Sylvania	QHE 3X32T8/UNV PSH-HT-SC		Certified			Certified			Certified
Osram Sylvania	QHE 4X32T8/UNV PSH-HT		Certified			Certified			Certified
Hatch	HL232APS/UV/HE/W		Certified			Certified			Certified
Hatch	HL332APS/UV/HE/W		Certified			Certified			Certified
Hatch	HL432APS/UV/HE/W		Certified			Certified			Certified
Hatch	HL232BPS/UV/HE/W		Certified			Certified			Certified
Hatch	HL332BPS/UV/HE/W		Certified			Certified			Certified
Hatch	HL432BPS/UV/HE/W		Certified			Certified			Certified
Hatch	HL232CPS/UV/HE/W		Certified			Certified			Certified
Hatch	HL332CPS/UV/HE/W		Certified			Certified			Certified

- System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance "blank" field means consult factory.
- Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Dimmable Ballasts

		7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	9.5 W 1600 lm (4 ft.)	13 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft.)		
		469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	473974, 473982 473990, 474007 540807	473926, 473934 473942, 473958	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686		
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Dimmers	
Philips Advance	IZT-2S32-SC						Use Compatible 0-10V dimmer	
Philips Advance	IZT-4S32						Use Compatible 0-10V dimmer	
Philips Advance	REZ-132-SC				System Certified	System Certified	Philips Lightolier - V1500EBUW	Lutron - MRF2-6ND-120
Philips Advance	REZ-2S32-SC				System Certified	System Certified	Philips Lightolier - V1500EBUW	Lutron - MRF2-6ND-120
Philips Advance	REZ-3S32-SC				System Certified	System Certified	Philips Lightolier - V1500EBUW	Lutron - MRF2-6ND-120
General Electric	GE132MVPSN-V03	Certified	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE232MVPSN-V03	Certified	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE332MVPSN-V03	Certified	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE432MVPSN-V03	Certified	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE232MVPSH-V03	Certified	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE332MVPSH-V03	Certified	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE432MVPSH-V03	Certified	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	

T8 Dimmable Ballasts

		15.5 W 2500 lm (4 ft.)	10 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	13W 2100 lm (U-Bent) ²		
		545178, 533372 545194, 545200	541986, 541994	470096, 470104 470112, 470120	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888		
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Dimmers	
Philips Advance	IZT-2S32-SC					Use Compatible 0-10V dimmer	
Philips Advance	IZT-4S32					Use Compatible 0-10V dimmer	
Philips Advance	REZ-132-SC					Philips Lightolier - V1500EBUW	Lutron - MRF2-6ND-120
Philips Advance	REZ-2S32-SC					Philips Lightolier - V1500EBUW	Lutron - MRF2-6ND-120
Philips Advance	REZ-3S32-SC					Philips Lightolier - V1500EBUW	Lutron - MRF2-6ND-120
General Electric	GE132MVPSN-V03	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE232MVPSN-V03	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE332MVPSN-V03	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE432MVPSN-V03	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE232MVPSH-V03	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE332MVPSH-V03	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	
General Electric	GE432MVPSH-V03	Certified	Certified	Certified	Certified	Use Compatible 0-10V dimmer	

1. System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance "blank" field means consult factory.
2. Typical application for U-Bent lamps is with 2-lamp ballasts.

PL-L Ballasts

		16.5 W 2100 lm (PL-L 2 ft.)	16.5 W 2300 lm (PL-L 2 ft.)
		456632, 456640, 456657	532895, 532903, 532911
Manufacturer	Ballast Model	Performance ¹	Performance ¹
Philips Advance	ICN-1TTP40-SC	System Certified	System Certified
Philips Advance	ICN-2TTP40-SC	System Certified*	System Certified*
Philips Advance	ICN-3TTP40-SC	System Certified	
Philips Advance	ICN-2S24-N		System Certified
Philips Advance	ICN-2S24-T		System Certified
Philips Advance	ICN-2S39-N		System Certified
Philips Advance	ICN-2S39-T		System Certified
Philips Advance	ICF-2S42-M2-BS		System Certified
Philips Advance	ICF-2S42-M2-LD		System Certified
Philips Advance	ICF-2S42-90C-M2-BS		System Certified
Philips Advance	ICF-2S42-90C-M2-LD		System Certified
General Electric	GE140MAX-A	Certified	Certified
General Electric	GE240MAX-A	Certified	Certified
General Electric	GE340MAX-A	Certified	Certified
General Electric	GEC242-MVPS		Certified
General Electric	GEC240MVPS-A		Certified
General Electric	GEC225MVPS-A		Certified
Osram Sylvania	QHE1X40DL/UNV ISN-SC	Certified	Certified
Osram Sylvania	QHE2X40DL/UNV ISN-SC	Certified	Certified
Osram Sylvania	QHE3X40DL/UNV ISN-SC	Certified	Certified
Osram Sylvania	QTP 1x40TT5/277 PSN-F		Certified
Osram Sylvania	QTP 2x40TT5/120 PSN-F		Certified
Osram Sylvania	QTP 2x40TT5/277 PSN-F		Certified
Osram Sylvania	QTP 3x40TT5/120 PSN-B		Certified
Osram Sylvania	QTP 3x40TT5/277 PSN-B		Certified
Osram Sylvania	QTP 2X26/32/42CF/UNV DM		Certified

1. System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
 System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
 System performance "blank" field means consult factory.

* Not recommended for one(1) lamp 277V operation.

Emergency Ballasts

(contact the emergency ballast manufacturer for wiring diagrams)

			7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	13W 2100 lm (U-Bent) ³	10 W 1600 lm (4 ft.)	13 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft. Glass)	T5 HO	T5 HE
			469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	469320, 469338 469346, 469353 469452, 469478 469460, 539858 539874, 539882 539866	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966 473974, 473982 473990, 474007		468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686	470096, 470104 470112, 470120	467126, 467134 467142, 467159	476499, 476507 476515, 476523
Manufacturer	Ballast Model	# of lamps in emergency	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Philips Bodine	B50*	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Bodine	B50CT	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Bodine	B50-CAN	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Bodine	B30HV	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Bodine	PEL12	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Bodine	LP600	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Bodine	LP600STU	1	Not Recommended	Not Recommended	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Chloride	DEB-6LP	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Iota Engineering	I-320	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified		System Certified
Iota Engineering	I-1605	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Iota Engineering	I-162	2	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Iota Engineering	ISL-54	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Iota Engineering	ISL-540	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	FH7-UNV-500L	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	FH11-UNV-750L-xx	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham Co., Inc	FH12-UNV-1400K-xx	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified

1. System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
 System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
 System performance "blank" field means consult factory.

* Must use 12 NC: 913702456401.

InstantFit Drivers

(UL/CSA classified
with the listed drivers)

		7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	13W 2100 lm (U-Bent) ³	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	10 W 1800 lm (4 ft. Glass)	13 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)
		469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847		469379, 469387 469395, 469403 469411, 470625	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	541986, 541994	473926, 473934 473942, 473958	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686	470096, 470104 470112, 470120	545178, 533372 545194, 545200
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Philips Advance	ICN-2P13-TLED-N			System Certified				System Certified			
Philips Advance	ICN-2P15-TLED-N	System Certified	System Certified	System Certified							System Certified
Philips Advance	ICN-2P16-TLED-N	System Certified	System Certified		System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICN-3P13-TLED-N							System Certified			
Philips Advance	ICN-3P15-TLED-N	System Certified	System Certified								System Certified
Philips Advance	ICN-3P16-TLED-N	System Certified	System Certified		System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICN-4P13-TLED-N							System Certified			
Philips Advance	ICN-4P15-TLED-N	System Certified	System Certified								System Certified
Philips Advance	ICN-4P16-TLED-N	System Certified	System Certified		System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICN-2P16-TLED-EL-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICN-2P16-TLED-HL-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICN-4P16-TLED-HL-SC	System Certified	System Certified		System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IZT-2P16-TLED-SC	System Certified	System Certified	System Certified	System Certified		System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IZT-4P16-TLED-SC		System Certified		System Certified			System Certified	System Certified		System Certified

InstantFit Drivers

		T5HO 3500 lm (4 ft.)	35W 4200 lm (8ft. Plastic)	30W 4200 lm (8ft. Glass)
		467126, 467134 467142, 467159	469239, 469247 469254, 469262	533000, 533018 533026, 533034
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹
Philips Advance	ICN-2S24-TLED-90C-N	System Certified		
Philips Advance	ICN-4S24-TLED-90C-2LS-G	System Certified		
Philips Advance	ICN-2P35-TLED-N		System Certified	System Certified

- System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance "blank" field means consult factory.

PL-C/T Ballasts 4-pin

(UL/CSA classified with the listed ballasts)

		Vertical Lamp 10.5W	Horizontal Lamp 8.5W	Vertical Lamp 12W	Horizontal Lamp 12W	Vertical Lamp 5.5W	Horizontal Lamp 5.5W
		458406, 458414 458422, 458430	458364, 458372 458380, 458398	476101, 476119 476127, 476135	476069, 476077 476085, 476093	532432, 532440 532457, 532465	532390, 532408 532416, 532424
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Philips Advance	ICF-2S13-M1-BS	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICF-2S13-H1-LD	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICF-2S13-M1-BS-QS	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICF-2S26-H1-LD	System Certified	System Certified*	System Certified	System Certified*		
Philips Advance	ICF-2S26-M1-BS	System Certified	System Certified	System Certified	System Certified		
Philips Advance	ICF-2S26-M1-BS-QS	System Certified	System Certified	System Certified	System Certified		
Philips Advance	ICF-2S18-H1-LD	System Certified	System Certified	System Certified	System Certified		
Philips Advance	ICF-2S18-M1-BS	System Certified	System Certified	System Certified	System Certified		
Philips Advance	ICF-2S18-M1-BS-QS	System Certified	System Certified	System Certified	System Certified		
Philips Advance	ICF-2S42-M2-LD	System Certified	System Certified	System Certified**	System Certified**		
Philips Advance	ICF-2S42-M2-BS	System Certified	System Certified	System Certified**	System Certified**		
Philips Advance	ICF-2S42-90C-M2-BS	System Certified	System Certified	System Certified**	System Certified**		
Philips Advance	ICF-2S42-90C-M2-LD	System Certified	System Certified	System Certified**	System Certified**		
Philips Advance	I2T-2S26-M5-LD	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	REB-113-M6-EL	System Certified	System Certified	System Certified	System Certified		
Philips Advance	REB-113-M6-BLS					System Certified	System Certified
Philips Advance	REB-118-M6-BLS	System Certified	System Certified	System Certified	System Certified		
Philips Advance	REB-2S18-M6-EL	System Certified	System Certified	System Certified	System Certified		
Philips Advance	REB-126-M6-BLS	System Certified	System Certified	System Certified	System Certified		
General Electric	GEC218-MVPS-SE	Certified	Certified	Certified	Certified		
General Electric	GEC226-MVPS-3W	Certified	Certified	Certified	Certified		
General Electric	GEC242-MVPS-SE	Certified	Certified	Certified	Certified		
Universal Lighting Technologies	C213UNVME					Certified	Certified
Universal Lighting Technologies	C218UNVME	Certified	Certified	Certified	Certified		
Universal Lighting Technologies	C2642UNVME	Certified	Certified	Certified	Certified		
Universal Lighting Technologies	C242UNVME	Certified	Certified	Certified	Certified		
Universal Lighting Technologies	C218UNVBE	Certified	Certified	Certified	Certified		
Universal Lighting Technologies	C2642UNVBE	Certified	Certified	Certified	Certified		
Osram Sylvania	QTP 1/2X18CF/UNV DM	Certified	Certified	Certified	Certified		
Osram Sylvania	QTP 2X26CF/UNV DM	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QTP2x26CF/UNV	Certified	Certified	Certified	Certified		
Howard Industries	EP2/26CF/MV/2	Certified	Certified	Certified	Certified		
Howard Industries	EP2CF26PS/MV/DC/K	Certified	Certified	Certified	Certified		
Motorola	M2-CF-26-B-S-277	Certified	Certified	Certified	Certified		
Keystone	CAT.NO.KTEB-226-UV-RS-DW	Certified	Certified	Certified	Certified		
Fulham	WH2-120-C					Certified	Certified
Fulham	WH2-120-L					Certified	Certified
Fulham	NPY-120-226-CFL	Certified	Certified	Certified	Certified		
Robertson	REDIL10-120H	Certified	Certified	Certified	Certified		

1. System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
 System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
 System performance "blank" field means consult factory.

* This ballast is compatible for two(2) lamp horizontal configuration only.
 ** When used with one(1) lamp, can only be operated at 120V.

PL-C/T Ballasts 4-pin

(UL/CSA classified with the listed ballasts)

		Vertical Lamp 10.5W	Horizontal Lamp 8.5W	Vertical Lamp 12W	Horizontal Lamp 12W	Vertical Lamp 5.5W	Horizontal Lamp 5.5W
		458406, 458414 458422, 458430	458364, 458372 458380, 458398	476101, 476119 476127, 476135	476069, 476077 476085, 476093	532432, 532440 532457, 532465	532390, 532408 532416, 532424
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
ACE	CSD-332PBM	Certified	Certified	Certified	Certified		
Hatch	HC226PS/UV/D	Certified	Certified	Certified	Certified		
Deltek	CFL226MVRSL	Certified	Certified	Certified	Certified		
Espen	VE226120MR-1	Certified	Certified	Certified	Certified		
Sunpark	LC 12010T					Certified	Certified
Sunpark	SL15T	Certified	Certified	Certified	Certified		
Topstar Premium	BB-PL/UNH-1/2X26-1X42	Certified	Certified	Certified	Certified		
Topstar Premium	BB-PL/UVH-1/2X13-18	Certified	Certified	Certified	Certified		
Antron	16X952 CSD-113PNPF	Certified	Certified	Certified	Certified		
Standard	E528-120V/STD/EOL	Certified	Certified	Certified	Certified		
Radionic	RPL26-42R-M	Certified	Certified	Certified	Certified		
DAMAR	23350D					Certified	Certified

Emergency PL-C/T Ballasts 4-pin

(UL/CSA classified with the listed ballasts, UL 924 listed)

		Vertical Lamp 18W/26W	Horizontal Lamp 18W/26W	Vertical Lamp 32W	Horizontal Lamp 32W	Vertical Lamp 32W	Horizontal Lamp 32W
		458406, 458414 458422, 458430	458364, 458372 458380, 458398	476101, 476119 476127, 476135	476069, 476077 476085, 476093	476101, 476119 476127, 476135	476069, 476077 476085, 476093
Manufacturer	Ballast Model	# of lamps in emergency	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Iota	I-42	1 or 2		System Certified		System Certified	System Certified
Iota	I-420	1	System Certified	System Certified	System Certified	System Certified	System Certified
Iota	I-420	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified
Iota	I-160	1	System Certified		System Certified		System Certified
Iota	I-160	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham	FH11-UNV-750L	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham	FH12-UNV-1400L	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified

PL-S/C Ballasts 2-pin**

(UL/CSA classified with the listed ballasts)

		Horizontal Lamp PLS 5W	Vertical Lamp PLC 5W	Horizontal Lamp PLC 5W
		529511, 529560 529578, 529586	532358, 532366 532374, 532382	532309, 532317 532333, 532341
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹
Philips Advance	VH-1B13-TP-W	System Certified	System Certified	System Certified
Philips Advance	H-1B13-TP-W	System Certified	System Certified	System Certified
Philips Advance	VLO-13-TP	System Certified	System Certified	System Certified
Philips Advance	H-2B13-TP-BLS	System Certified	System Certified	System Certified
Philips Advance	LC-13-TP	System Certified	System Certified	System Certified
Robertson	S1P	Certified	Certified	Certified
Robertson	O1527P(3P10104)	Certified*	Certified*	Certified*
Robertson	HP213P(3P10073)	Certified	Certified	Certified

1. System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance "blank" field means consult factory.

* This ballast is compatible for one(1) lamp configuration only.
**Lamps are only compatible when used with a parallel wiring configuration.

T12 Electronic Ballasts

		13 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft.)	16 W 1800 lm (4 ft.)
		473926, 473934 473942, 473958	468306, 468314 468322, 468330 469061, 469619 469627, 469635	539972, 539980 539148, 539155 539163, 542688 542696, 542704
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹
Philips Advance	ICN-2S40-N	System Certified	System Certified	System Certified
Philips Advance	RELB-2S40-N	System Certified	System Certified	System Certified

T12 Rapid-Start Magnetic Ballasts

		16 W 1800 lm (4 ft.)	20 W 2100 lm (4 ft.)
		539972, 539980 539148, 539155 539163, 542688 542696, 542704	463117, 463125
Manufacturer	Ballast Model	Performance ¹	Performance ¹
Philips Advance	R-140-1-TP	System Certified	System Certified
Philips Advance	X-140-TP	System Certified	System Certified
Philips Advance	R-2S40-1-TP	System Certified	System Certified
Philips Advance	XQM-2S40-TP	System Certified	System Certified
Philips Advance	V-2S40-1-TP	System Certified	System Certified
Philips Advance	RQM-2S40-3-TP	System Certified	System Certified
Philips Advance	R-2S34-TP-5	System Certified	System Certified
Philips Advance	V-2S34-TP	System Certified	System Certified
Philips Advance	RM-2S35-TP	System Certified	System Certified
General Electric	GEM240RS277	Certified	Certified
General Electric	GEM240RS120 -1	Certified	Certified
Howard Industries	M1/40RS-120	Certified	Certified
Howard Industries	M2/40RS-277	Certified	Certified
Howard Industries	M2/40RS-240 -1	Certified	Certified
Universal Lighting Technologies	412-L-SLH-TC-P	Certified	Certified
Universal Lighting Technologies	458-L-SLH-TC-P	Certified	Certified
Universal Lighting Technologies	540-L-TC-P	Certified	Certified
Universal Lighting Technologies	CAT.NO.446-L-LH-TC-P-7	Certified	Certified
Universal Lighting Technologies	443-L-SLH-TC-P	Certified	Certified
Universal Lighting Technologies	446-L-SLH-TC-P	Certified	Certified
Osram Sylvania	MB1x40/277 RS-1	Certified	Certified
Osram Sylvania	MB1x40/120RS-1	Certified	Certified
Osram Sylvania	MB2x40/120RS-1	Certified	Certified
Osram Sylvania	MB2x40/277RS-1	Certified	Certified
Industrias Sola Basics S A DE C V	E420-F-234 IC -1	Certified	Certified
Radionic Industries Inc.	CAT.NO.ES24OHTP	Certified	Certified

- System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance "blank" field means consult factory.

T5 HO Ballasts

467126, 467134
467142, 467159

Manufacturer	Ballast Model	Performance ¹
Philips Advance	ICN-2S54-N	System Certified
Philips Advance	ICN-2S54-90C-N	System Certified
Philips Advance	ICN-2S54-T	System Certified
Philips Advance	ICN-2S54-90C-T	System Certified
Philips Advance	ICN-2S54-N(L)	System Certified
Philips Advance	ICN-4S54-90C-2LS-G	System Certified
Philips Advance	HCN-2S54-90C-WL	System Certified
Philips Advance	HCN-4S54-90C-2LS-G	System Certified
Philips Advance	IZT-2S54-D	System Certified
Philips Advance	REZ-2S54	System Certified
General Electric	GE254MVPS-A	Certified
General Electric	GE254MVPS-D	Certified
General Electric	GE454MVPS90-E-S	Certified
General Electric	GE454MVPS90-F	Certified
General Electric	GE454MVPS90-G	Certified
General Electric	GE254MVPS90-A	Certified
Osram Sylvania	QHE 2x54T5HO/UNV PSN	Certified
Osram Sylvania	QHE 2x54T5HO/UNV PSN HT	Certified
Osram Sylvania	QHE 2x54T5HO/UNV PSN(L)	Certified
Osram Sylvania	QTP 2X54T5HO/UNV PSN HT	Certified
Universal Lighting Technologies	B254PUNV-D	Certified
Universal Lighting Technologies	B254PUNVHB-D	Certified
Universal Lighting Technologies	B454PUNV-E	Certified
Universal Lighting Technologies	B454PUNVHB-E	Certified
Hatch	HL454HO/PS/UV/W	Certified
Hatch	HL254HO/PS/UV/W	Certified
ESPEN	VE254MVHRP	Certified
ESPEN	VE454MVHRP	Certified
Fulham	RHA-UNV-254-LT5	Certified
Fulham	RHA-UNV-454-LT5	Certified
Keystone Inc.	KTEB-254HO-UV-PS-SL	Certified
Keystone Inc.	KTEB-454HO-UV-TP-PS	Certified
Sunpark	U-2/54T5HO	Certified
MAGG	2x54W LFL T5 AFP	Certified

- System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer. System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only. System performance "blank" field means consult factory.

T5 HE Ballasts

Manufacturer	Ballast Model	8 W 1050 lm (2 ft. Glass)	11 W 1500 lm (3 ft. Glass)	14 W 2100 lm (4 ft. Glass)
		Performance ¹	Performance ¹	Performance ¹
Philips Advance	ICN-2S24-N	System Certified	System Certified	
Philips Advance	ICN-2S24-T	System Certified	System Certified	
Philips Advance	ICN-2S28-N	System Certified	System Certified	System Certified
Philips Advance	ICN-2S28-T	System Certified	System Certified	System Certified
Philips Advance	GCN-2S28-L	System Certified	System Certified	System Certified
Philips Advance	IZT-2S28-D	System Certified	System Certified	System Certified
Osram Sylvania	QHE 2X39-24T5HO/UNV PSN	Certified	Certified	
Osram Sylvania	QTP 2X28T5/UNV PSN	Certified	Certified	Certified
Osram Sylvania	QHE 2X28T5/UNV PSN	Certified*	Certified*	Certified
General Electric	GE228MVPS-MC	Certified*	Certified*	Certified*
General Electric	GE228MVPS-MC-H	Certified	Certified	Certified
Universal Lighting Technologies	B224PUNV-C	Certified	Certified	
Universal Lighting Technologies	B228PUNV-C	Certified	Certified	Certified
Universal Lighting Technologies	B228PUNV-N	Certified	Certified	Certified
Universal Lighting Technologies	B228PUNV85-D	Certified	Certified	Certified
Universal Lighting Technologies	B239PUNV-D	Certified*	Certified*	
Keystone	KTEB-228HE-UV-PS	Certified	Certified	Certified
Keystone	KTEB-228HE-UV-PS-SL	Certified	Certified	Certified
Fulham	RHA-UNV-228-LT5	Certified	Certified	Certified
Robertson	PSA228T5MV	Certified	Certified	Certified

- System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer. System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only. System performance "blank" field means consult factory.

* This ballast is compatible for two(2) lamp configuration only.

LATAM T8 Ballasts

		7W 1150 lm (2 ft.)	10W 1600lm (4 ft.)	13W 2100lm (4 ft.)	17W 2100lm (4 ft.)	13W 2100lm (U-Bent) ³
		929001311004 929001311104	929001397404 929001397504	929001397804 929001397904	929001343503	929001311804 929001311904 929001312004 929001312104
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Philips Advance	ICN-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	RES-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	REM-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified
ISB Sola Basic	758-232-MC	Certified	Certified	Certified	Certified	Certified
ISB Sola Basic	758-432-SC	Certified	Certified	Certified	Certified	Certified
ISB Sola Basic	758-U-432-SC	Certified	Certified	Certified	Certified	Certified
ISB Sola Basic	E-758-U-232-SC	Certified	Certified	Certified	Certified	Certified
ISB Sola Basic	E18-232	Certified	Certified	Certified	Certified	Certified
Magg	B04341	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QTP 1X32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	
Osram Sylvania	QTP 2X32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QTP 3X32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	
Osram Sylvania	QTP 4X32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	

T8 / T12 8' Slimline Ballasts

		469239, 469247 469254, 469262	533000, 533018 533026, 533034
Manufacturer	Ballast Model	Performance ¹	Performance ¹
Philips Advance	IOP-2P59-N	System Certified	System Certified
Philips Advance	ICN-2P60-N	System Certified	System Certified
General Electric	GE259MAX-L/ULTRA	Certified	Certified
General Electric	GE259MAXP-N/ULTRA	Certified	Certified
General Electric	GE-259-MV-N 30194	Certified	Certified
General Electric	GE259MAX-G-N 74469	Certified	Certified
General Electric	GE259MAXP-N-DIY 23954	Certified	Certified
Howard Industries	EP2/59IS/MV/MC/HE	Certified	Certified
Howard Industries	E2/75IS-120MC	Certified	Certified
Fulham	WH5-277-L	Certified	Certified
Universal Lighting Technologies	B260IUNVHP	Certified	Certified
Universal Lighting Technologies	B260I120M-A	Certified	Certified
Osram Sylvania	OSRAM QT 2X96/120 IS	Certified	Certified
Osram Sylvania	OSRAM QT 2X96/277 IS	Certified	Certified
Osram Sylvania	2X75W T12(96")	Certified	Certified
Industrias Sola Basics S A DE C V	EIO-260-MC	Certified	Certified
Industrias Sola Basics S A DE C V	EOI-230/32-MC	Certified	Certified

LATAM FA8 Ballasts

		13W 1600lm (4 ft.)	26W 3200lm (8 ft.)
		929001273412	929001273612
Manufacturer	Ballast Model	Performance ¹	Performance ¹
Philips Advance	ICN-2P59-N	System Certified	System Certified
Philips Advance	REL-275-N	System Certified	System Certified
Philips Advance	REL-239-N	System Certified	System Certified
ISB Sola Basic	758-U-259-SC	Certified	Certified
ISB Sola Basic	12-EI-139	Certified	Certified
ISB Sola Basic	EIO-230/232-MC	Certified	Certified
ISB Sola Basic	758-259-SC	Certified	Certified
ISB Sola Basic	EIO-U-260-SC	Certified	Certified
ISB Sola Basic	EIO-260-MC	Certified	Certified

- System performance "System Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp and ballast manufacturer.
System performance "Certified" means Philips InstantFit LED T8 lamps and ballast have been evaluated by the lamp manufacturer only.
System performance "blank" field means consult factory.
- Typical application for U-Bent lamps is with 2-lamp ballasts.

Notes



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-16118CR 09/20 philips.com/lighting

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.