

PHILIPS

LED lamps

Designer
decorative lamps




Designed to be seen whether it's on or off

Philips designer decorative LED lamps transform your facility with a perfect blend of warm white light or a modern, cool lighting experience. With very long lifetime, up to 90% energy savings, this lamp as a fixture approach, will also evenly distribute light with trendy and stylish charm for a welcoming space.

Benefits

- Long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps
- Perfect fit and high quality finishing
- Increased energy savings when compared to traditional incandescent lamps
- Vintage, modern and clear colors for multiple room themes
- Perfect for decorative installations including residential applications, hospitality, and restaurants

Philips LED Designer decorative lamps



Ordering, electrical and technical data (Subject to change without notice)

	Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	Material	Finish	Legend
MasterClass R20 lamps												
w ■ ■	556530	929002296003	8ST19/PER/927-922/CL/G/E26/WGX PF T20	8	800	120	90	2700-2200	15,000	Glass	Clear	A
w ■ ■	556548	929002296103	8.8ST19/PER/950/CL/G/E26/DIM 1PF T20	8.8	800	120	90	5000	15,000	Glass	Clear	A
w ■ ■	556803	929001951033	5ST19/VIN/820/E26/CL/GL/DIM 4/1FB T20	5	350	120	80	2000	15,000	Glass	Amber	B
w ■ ■	543140	929002001003	4ST19/MOD/840/E26/CL/GL/DIM 4/1BC	4	150	120	80	4000	15,000	Glass	Smokey	C
w ■ ■	556837	929001951533	4.5T10/VIN/820/E26/CL/GL/DIM 4/FBH T20	4.5	300	120	80	2000	15,000	Glass	Amber	D
w ■ ■	543132	929002000903	4T10/MOD/840/E26/CL/GL/DIM 4/1BC	4	150	120	80	4000	15,000	Glass	Smokey	E
w ■ ■	536268	929001936303	7.5G63/VIN/820/CL/G/DIM 2/ICT	7.5	400	120	80	2000	15,000	Glass	Amber	F
w ■ ■	536292	929001936603	7.5G63/modern/840/CL/G/DIM 2/ICT	7.5	250	120	80	4000	15,000	Glass	Smokey	G
w ■ ■	536276	929001936403	7.5A50/VIN/820/CL/G/DIM 2/ICT	7.5	400	120	80	2000	15,000	Glass	Amber	H
w ■ ■	536300	929001936703	7.5A50/modern/840/CL/G/DIM 2/ICT	7.5	250	120	80	4000	15,000	Glass	Smokey	I
w ■ ■	536284	929001936503	7.5T20/VIN/820/CL/G/DIM 2/ICT	7.5	400	120	80	2000	15,000	Glass	Amber	J
w ■ ■	536318	929001936803	7.5T20/modern/840/CL/G/DIM 2/ICT	7.5	250	120	80	4000	15,000	Glass	Smokey	K

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

w = Wet location ■ = ENERGY STAR® qualified ■ = Title 20 compliant ■ = Not regulated by Title 20



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-18134BN 01/21 philips.com/lighting



Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.