



# T8

## 15.5T8/COR/48-840/MF21/G/BAA 25/1

Philips MainsFit (UL Type B) T8 LED lamps use a double-ended design which significantly simplifies installation, saving time and costs. This product is proudly assembled in the USA and is BAA (Buy American Act) compliant. This product can replace either T8 or T12 lamps in fixtures containing shunted or non-shunted G13 (medium bi-pin) lamp holders. Available in 4ft and 2ft lengths.

### Product data

General Information		Lamp Current (Min)	
Base	G13 [ Medium Bi-Pin Fluorescent]		65 mA
EU RoHS compliant	Yes	Starting Time (Nom)	0.9 s
Nominal Lifetime (Nom)	50000 h	Warm Up Time to 60% Light (Nom)	0.9 s
Switching Cycle	50000X	Power Factor (Nom)	0.9
Technical Type	15.5-32W	Voltage (Nom)	120-277 V
Light Technical		Temperature	
Color Code	841 [ CCT of 4100K (841)]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	240 °	T-Ambient (Min)	-20 °C
Initial lumen (Nom)	2200 lm	T-Storage (Max)	65 °C
Color Designation	Cool White (CW)	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	4000 K	T-Case Maximum (Nom)	70 °C
Luminous Efficacy (rated) (Nom)	141.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	No
Color Rendering Index (Nom)	80	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Frosted
Operating and Electrical		Bulb Material	Glass
Input Frequency	50 to 60 Hz	Product Length	48 in
Power (Rated) (Nom)	15.5 W		
Lamp Current (Max)	132 mA		

# T8

## Approval and Application


Energy Efficiency Label (EEL)	Not applicable
Energy Saving Product	Yes
Approbation Marks	DLC compliance
Approbation Marks	RoHS compliance UL certificate
Energy Consumption kWh/1000 h	- kWh

## Product Data

Order product name	15.5T8/COR/48-840/MF21/G/BAA 25/1
--------------------	-----------------------------------

EAN/UPC - Product	046677563738
Order code	563734
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	929002497704
Net Weight (Piece)	0.206 kg
Model Number	9290024977


## Dimensional drawing



Product	D1	D2	A1	A2	A3
15.5T8/COR/48-840/ MF21/G/BAA 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm


TLED T8 120-277V 15.5-32W 2200lm 4000K

## Photometric data




©2020 Philips Lighting B.V. Page 11

LEDtube COR 15,5W G13 2200lm 840




LEDtube COR 11W G13 1700lm 840

Photometric data




LEDtube COR 11W G13 1650lm


Lifetime



LEDtube 50K-LED



LEDtube 50K FailureRate-LED



LEDtube COR 11W 50K LumenVsTc



LEDtube 50K-LMP

Lifetime



LEDtube 50K LifetimeVsTc-LED

