



Philips GreenPower Interlighting

	2.0 m	2.5 m
Length	1.95 m · 76.7 in	2.42 m · 95.3 in
Width	6.5 cm · 2.6 in	6.5 cm · 2.6 in
Height	7.6 cm · 3.0 in	7.6 cm · 3.0 in
Weight	2.2 kg · 4.9 lb	2.5 kg · 5.5 lb

Input voltage
Beam angle
L90
L70
Warranty
UL/CSA rated

200V – 400V
Bi-directional 120°
36,000 hrs
50,000 hrs
5 year limited
Damp/wet

IP rating
Ambient operating temp
Frequency
Power factor
Total harmonic distortion

IP66
0° C Min. · 40° C Max
40° F Min. · 104° F Max
50/60 Hz
> 0.90
<10%

Philips LED Interlighting 3.1 High Output (HO)

Interlighting 3.1 High Output (HO)	12 NC	Power (W)	Amps 208V	Amps 240V	Amps 277V	Amps 347V	Photon Flux $\mu\text{mol/s}$	Efficacy $\mu\text{mol/J}$
GPL IL 300 DRB L250 200-400V G3.1 S NA	9290 021 00154	92	0.44	0.38	0.33	0.26	300	3.3
GPL IL 240 DRB L200 200-400V G3.1 S NA	9290 021 00155	74	0.36	0.31	0.27	0.21	240	3.2

Philips LED Interlighting 3.0 Regular Output (RO)

Interlighting 3.0 Regular Output (RO)	12 NC	Power (W)	Amps 208V	Amps 240V	Amps 277V	Amps 347V	Photon Flux $\mu\text{mol/s}$	Efficacy $\mu\text{mol/J}$
GP LED interlighting mod DR/B 250 RO NA	9290 015 55006	79	0.38	0.33	0.29	0.23	220	2.8
GP LED interlighting mod DR/B 200 RO NA	9290 015 55306	64	0.31	0.27	0.23	0.18	175	2.7

Interlighting Accessories	12 NC
IL 3.0 Mounting Bracket 3.3 (171 mm)	9290 016 13106
IL 3.0 Mounting Bracket 3.4 (271 mm)	9290 016 13206
IL 3.0 Mains Power Cable (6.5 m)	9290 015 56606
IL 3.0 Jumper Cable (1 m)	9290 015 56906
IL 3.0 Female Connector	9290 015 99406
End Cap (universal)	9290 009 15606